

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333169-830

Luminaire Tested: **S125DIP-S610D590U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333169-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D590U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4609.6 lumens
Efficiency: N/A
Efficacy: 140.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 32.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	82	76	71	83	77	71	67	65	61	58	55	52	50	45	43	42	37
3	82	73	65	60	76	67	61	56	58	53	49	49	45	42	40	38	36	32
4	75	64	57	51	69	60	53	48	51	46	42	44	40	36	36	33	31	27
5	69	57	49	43	64	54	46	41	46	40	36	39	35	32	33	30	27	24
6	64	52	43	38	59	48	41	36	42	36	32	35	31	28	30	26	24	21
7	59	47	39	33	54	43	36	31	38	32	28	32	28	25	27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5448	5448	5448	5448
5°	6309	5466	4786	5466
10°	7340	5438	4194	5438
15°	8125	5398	3869	5398
20°	9095	5335	3608	5335
25°	10655	5264	3480	5264
30°	11508	5193	3370	5193
35°	9462	5062	3297	5062
40°	6726	4878	3217	4878
45°	5167	4631	3172	4631
50°	4410	4324	3166	4324
55°	3926	4023	3193	4023
60°	3543	3695	3274	3695
65°	3272	3365	3359	3365
70°	2974	3021	3408	3021
75°	2628	2662	3376	2662
80°	2213	2168	3087	2168
85°	1756	1564	2490	1564



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	1.8
10°-20°	241.8	5.2
20°-30°	392.6	8.5
30°-40°	478.9	10.4
40°-50°	435.7	9.5
50°-60°	347.0	7.5
60°-70°	241.7	5.2
70°-80°	128.9	2.8
80°-90°	34.0	0.7
90°-100°	26.4	0.6
100°-110°	162.5	3.5
110°-120°	294.7	6.4
120°-130°	378.2	8.2
130°-140°	406.7	8.8
140°-150°	381.8	8.3
150°-160°	308.8	6.7
160°-170°	199.7	4.3
170°-180°	68.9	1.5
0°-30°	715.6	15.5
0°-40°	1194.5	25.9
0°-60°	1977.3	42.9
0°-90°	2381.9	51.7
90°-120°	483.5	10.5
90°-150°	1650.2	35.8
90°-180°	2228.0	48.3
0°-180°	4609.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	844	844	844	844	844	
5°	973	843	738	843	973	98
15°	1215	807	579	807	1215	348
25°	1495	739	488	739	1495	683
35°	1200	642	418	642	1200	735
45°	566	507	347	507	566	453
55°	349	357	284	357	349	314
65°	214	220	220	220	214	212
75°	105	107	135	107	105	113
85°	24	21	34	21	24	28
90°	13	1	13	1	13	6
95°	11	31	11	31	11	9
105°	160	158	160	158	160	144
115°	295	297	295	297	295	293
125°	422	422	422	422	422	376
135°	524	526	524	526	524	405
145°	609	610	609	610	609	380
155°	667	672	667	672	667	308
165°	706	709	706	709	706	199
175°	722	726	722	726	722	69
180°	726	726	726	726	726	



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	892.3	891.1	889.9	887.7	889.4	884.5	882.2	878.3	873.4	871.7	869.6
5°	973.2	975.0	976.8	969.2	970.0	965.0	953.5	944.1	936.7	927.0	920.2
7.5°	1070.5	1066.3	1066.0	1061.1	1052.7	1046.0	1034.0	1018.6	1003.8	986.9	973.0
10°	1119.3	1119.6	1116.4	1110.7	1101.7	1095.2	1079.5	1064.5	1046.2	1024.7	1009.4
12.5°	1155.9	1157.4	1153.4	1145.7	1141.2	1126.8	1114.5	1096.6	1074.9	1057.7	1034.3
15°	1215.2	1211.3	1208.4	1198.7	1191.2	1176.2	1156.5	1137.8	1114.3	1092.4	1070.5
17.5°	1272.3	1275.5	1270.2	1261.3	1238.0	1220.4	1194.0	1168.6	1139.1	1109.8	1083.7
20°	1323.3	1326.3	1318.0	1302.6	1274.7	1257.1	1222.4	1189.4	1155.5	1117.9	1089.2
22.5°	1387.0	1384.7	1373.6	1350.1	1326.0	1293.5	1255.9	1215.8	1173.2	1130.7	1092.6
25°	1495.2	1480.2	1473.4	1444.4	1412.5	1364.9	1313.3	1254.6	1201.6	1145.4	1096.7
27.5°	1555.2	1550.5	1542.9	1522.7	1489.2	1438.3	1377.5	1306.0	1231.1	1160.3	1096.5
30°	1543.2	1543.9	1544.6	1538.1	1516.7	1478.4	1417.9	1340.9	1252.1	1172.2	1098.5
32.5°	1436.6	1449.6	1462.2	1476.9	1482.9	1475.6	1437.7	1368.1	1276.8	1186.0	1097.3
35°	1200.1	1204.1	1244.6	1284.7	1339.1	1381.4	1409.7	1378.8	1301.8	1197.7	1096.0
37.5°	935.8	955.2	983.2	1028.5	1107.0	1177.3	1267.8	1309.4	1284.5	1201.5	1093.4
40°	797.8	815.7	833.9	880.1	946.3	1031.5	1134.3	1222.0	1242.5	1189.4	1084.9
42.5°	691.2	705.4	725.7	760.3	815.7	891.2	989.4	1104.0	1174.5	1154.5	1066.9
45°	565.7	574.7	590.4	618.0	658.1	717.2	803.8	929.2	1038.3	1074.5	1024.0
47.5°	484.2	484.2	496.4	515.5	544.4	594.6	658.6	756.9	873.5	959.8	955.7
50°	438.9	437.2	446.9	463.4	486.3	519.5	580.8	659.2	771.3	869.0	896.2
52.5°	400.0	400.2	406.1	418.3	437.5	466.0	511.7	582.4	678.2	778.4	829.7
55°	348.7	347.3	354.1	362.3	376.4	394.9	427.9	481.9	559.6	658.5	725.0
57.5°	301.8	305.7	308.4	314.1	325.7	338.2	366.0	405.7	467.3	552.1	622.5
60°	274.3	278.2	280.3	286.1	295.4	306.1	327.6	359.9	411.8	484.8	554.6
62.5°	249.6	252.7	253.4	258.5	266.2	276.6	293.5	320.6	361.7	425.5	493.9
65°	214.1	214.1	215.6	220.9	224.5	233.8	246.7	266.4	299.4	349.1	407.5
67.5°	179.8	181.6	181.3	183.6	186.9	194.2	203.4	219.6	244.0	280.3	327.1
70°	157.5	159.0	158.6	160.4	164.0	168.6	176.2	191.5	209.1	240.3	280.3
72.5°	137.5	138.1	137.1	139.5	141.7	145.7	154.1	162.3	178.7	205.0	238.0
75°	105.3	105.9	106.7	108.1	110.3	112.4	116.7	125.0	135.7	155.4	176.5
77.5°	78.9	77.6	79.3	79.1	80.3	81.9	85.7	90.1	98.9	111.3	127.7
80°	59.5	59.8	59.8	60.1	61.9	63.1	66.3	69.5	76.3	85.6	97.0
82.5°	43.4	44.3	43.7	44.4	45.9	46.7	48.4	51.1	55.0	62.4	70.7
85°	23.7	21.9	22.5	23.3	23.3	23.7	25.1	26.1	28.3	31.1	34.4
87.5°	9.4	10.0	10.2	10.1	10.3	10.2	11.2	11.1	11.9	12.6	13.6
90°	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8	9.2	8.6	7.7
92.5°	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8	9.2	8.6	7.8
95°	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8	9.2	8.6	13.1
97.5°	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7	23.1	26.5	35.4
100°	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0	75.8	93.6	93.1
102.5°	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6	116.0	119.4	119.1
105°	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9	202.8	202.8	202.6
110°	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5	230.9	231.2	231.0



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9	258.4	258.7	258.6
115°	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1	299.6	300.1	299.9
117.5°	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9	339.6	340.2	339.7
120°	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7	364.9	365.1	364.8
122.5°	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2	389.5	389.6	389.5
125°	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0	425.5	425.9	425.9
127.5°	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6	457.9	458.2	458.3
130°	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0	479.3	479.7	479.6
132.5°	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9	499.0	499.1	499.3
135°	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1	528.4	528.6	528.9
137.5°	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3	555.3	555.3	555.5
140°	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1	571.8	571.7	571.7
142.5°	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5	588.4	588.4	588.2
145°	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7	611.5	611.4	611.4
147.5°	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5	631.4	631.2	631.0
150°	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1	643.9	643.7	643.5
152.5°	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3	655.2	654.9	654.6
155°	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8	670.4	670.1	669.8
157.5°	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5	683.2	682.8	682.7
160°	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4	691.0	690.5	690.3
162.5°	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7	698.0	697.4	697.2
165°	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0	707.3	706.6	706.5
167.5°	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1	714.3	713.4	713.2
170°	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8	717.7	716.8	716.7
172.5°	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5	720.7	719.8	719.6
175°	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6	723.7	722.7	722.6
177.5°	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9	725.3	724.5	724.4
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	867.9	865.9	863.7	859.6	854.7	852.2	848.2	845.6	840.4	836.1	831.5
5°	911.9	902.7	894.1	883.0	870.8	862.9	853.6	843.2	832.5	821.3	809.2
7.5°	957.5	941.1	923.2	903.9	885.1	867.8	851.2	835.0	819.8	801.4	785.9
10°	988.3	967.4	945.3	919.1	893.7	871.5	848.9	829.2	809.2	787.7	768.7
12.5°	1018.9	991.2	959.9	931.1	900.6	873.8	847.3	822.1	796.9	773.1	751.0
15°	1040.5	1016.2	987.1	946.3	911.9	875.1	840.0	807.4	776.9	750.5	722.6
17.5°	1054.7	1023.4	992.2	953.1	908.0	866.8	827.0	789.8	755.4	721.8	694.9
20°	1057.3	1025.1	992.5	954.2	908.0	860.7	821.0	776.3	739.3	704.6	671.7
22.5°	1056.5	1019.9	984.5	945.0	900.0	856.5	808.4	762.8	722.7	688.6	654.2
25°	1048.4	1009.4	965.0	925.2	880.8	834.6	785.9	738.7	697.9	658.8	624.8
27.5°	1041.6	991.0	940.8	894.4	851.5	809.2	762.6	714.2	668.9	629.3	597.3
30°	1033.3	977.8	921.2	872.9	828.9	787.7	743.7	696.4	649.1	610.5	576.1
32.5°	1025.9	961.2	901.5	848.9	802.3	762.2	721.6	676.7	630.3	591.0	556.7
35°	1011.5	936.7	868.3	808.8	759.0	717.9	683.9	642.0	599.4	561.4	528.5
37.5°	993.3	904.5	831.0	768.7	714.2	670.8	639.1	607.0	566.1	529.5	499.7
40°	978.9	881.6	803.8	740.1	683.5	638.4	609.1	578.6	544.6	510.6	479.1
42.5°	960.8	860.9	776.3	707.8	651.8	607.8	576.9	551.1	521.1	489.4	460.1
45°	927.7	823.5	731.9	658.1	601.5	558.2	526.3	507.0	484.5	454.4	429.7
47.5°	878.9	778.6	683.8	607.7	549.3	509.2	479.3	460.7	444.9	422.5	400.1
50°	835.7	745.1	649.1	573.6	515.2	474.8	447.2	430.4	416.8	399.5	380.6
52.5°	787.3	702.9	615.1	540.4	482.6	442.7	415.7	400.9	389.6	377.2	358.5
55°	710.4	638.8	557.1	486.3	432.9	393.9	370.2	357.3	348.0	338.7	327.3
57.5°	625.7	569.7	497.3	432.5	383.4	347.9	325.8	313.3	306.0	301.2	294.5
60°	566.1	518.1	455.8	396.7	348.7	317.3	295.8	286.1	280.0	276.1	271.1
62.5°	510.8	471.4	413.7	359.8	317.8	288.0	268.8	259.5	253.6	251.8	247.5
65°	429.3	398.9	351.3	306.5	270.7	245.2	229.1	220.2	216.6	214.4	214.8
67.5°	349.0	330.5	292.3	254.1	225.5	204.2	191.2	184.4	182.6	179.7	179.6
70°	300.0	286.1	253.8	220.6	195.1	178.7	167.2	160.0	158.3	156.8	156.5
72.5°	256.7	244.6	216.6	189.9	167.1	152.6	143.2	138.8	135.9	135.1	135.0
75°	193.0	186.2	164.0	142.9	127.1	117.1	110.7	106.7	104.5	104.2	104.5
77.5°	137.2	131.3	117.2	102.2	92.3	84.6	79.2	77.9	75.4	75.5	75.1
80°	103.1	99.2	90.2	78.4	70.2	63.7	60.9	58.3	57.7	56.6	57.7
82.5°	74.7	70.5	64.5	56.9	50.1	46.3	43.4	42.6	42.1	41.7	41.8
85°	36.9	37.2	33.6	27.9	25.1	22.9	21.1	21.1	20.7	20.5	20.7
87.5°	13.9	13.3	12.0	10.9	9.2	8.2	7.7	7.8	7.2	7.1	7.5
90°	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6	1.5	2.5	3.4
92.5°	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3	7.6	7.0	6.3
95°	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6	30.3	30.0	29.6
97.5°	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0	64.7	65.3	65.9
100°	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8	90.2	90.5	90.9
102.5°	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0	116.5	117.0	117.4
105°	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1	158.5	159.1	159.6
107.5°	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8	201.8	201.8	201.8
110°	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2	230.2	230.2	230.2



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8	257.1	257.4	257.7
115°	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8	297.5	298.0	298.6
117.5°	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3	338.2	338.2	338.2
120°	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1	363.9	363.8	363.7
122.5°	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8	387.3	387.8	388.2
125°	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2	423.0	423.8	424.6
127.5°	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8	456.4	457.0	457.6
130°	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5	477.0	477.7	478.2
132.5°	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1	497.8	498.5	499.2
135°	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5	527.2	527.9	528.6
137.5°	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5	554.1	554.7	555.3
140°	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1	571.4	571.6	571.8
142.5°	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0	587.2	587.3	587.5
145°	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4	610.6	610.9	611.1
147.5°	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7	630.7	630.7	630.7
150°	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.5	643.2	643.0
152.5°	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2	655.6	655.2	654.6
155°	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2	671.5	670.8	670.1
157.5°	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6	684.1	683.7	683.2
160°	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1	692.5	691.7	691.0
162.5°	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0	699.4	698.6	697.9
165°	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3	708.6	707.8	707.2
167.5°	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1	715.5	714.7	714.0
170°	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1	719.3	718.4	717.6
172.5°	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6	721.8	721.0	720.1
175°	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5	724.7	724.0	723.3
177.5°	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7	726.1	725.6	725.0
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	829.0	825.8	823.2	817.5	814.4	810.0	806.6	810.3	806.3	808.0	805.5
5°	803.1	793.1	785.9	775.5	766.6	758.4	752.2	751.2	748.3	746.9	742.6
7.5°	772.0	759.5	747.2	733.6	722.1	710.5	702.9	696.8	692.8	687.4	683.7
10°	753.7	736.9	722.6	706.1	691.7	679.2	669.2	664.2	659.5	652.7	650.3
12.5°	731.0	713.7	696.2	678.5	664.9	650.8	642.2	634.7	631.5	623.8	623.0
15°	703.9	677.8	660.6	642.7	623.7	612.3	605.1	596.9	593.3	588.0	584.0
17.5°	671.6	648.2	626.7	608.2	591.9	582.3	573.3	567.7	561.6	558.1	551.6
20°	648.1	625.8	604.4	584.7	572.1	561.1	553.9	548.6	542.1	540.3	533.9
22.5°	628.3	603.8	583.2	566.7	553.0	540.5	532.7	529.0	524.6	519.1	517.8
25°	596.2	570.7	553.2	536.7	524.5	513.1	507.7	503.0	498.8	494.8	493.4
27.5°	568.4	545.6	524.8	509.9	499.4	488.9	484.2	478.5	475.3	472.2	468.3
30°	548.9	525.7	507.4	493.0	481.5	472.3	467.2	463.4	460.4	457.6	455.4
32.5°	528.9	507.3	489.6	475.6	464.1	457.1	452.6	449.9	446.7	443.3	440.5
35°	502.4	478.7	461.6	449.3	440.4	435.0	430.0	427.5	424.0	424.0	421.0
37.5°	472.5	452.0	436.9	425.7	417.7	412.9	407.6	405.9	403.5	402.0	401.1
40°	454.7	435.7	421.4	410.3	401.7	397.8	393.5	390.6	389.2	387.4	386.7
42.5°	436.4	418.3	404.5	394.3	386.8	383.4	379.5	377.5	374.6	372.2	371.8
45°	408.5	391.0	378.4	370.2	363.8	359.9	357.3	353.1	351.6	348.7	348.4
47.5°	382.1	365.2	353.0	346.2	340.5	337.3	333.4	329.1	327.4	326.0	325.9
50°	362.3	346.9	335.5	329.0	323.7	319.1	315.1	312.3	311.1	311.1	311.9
52.5°	342.3	329.2	319.4	311.6	306.5	301.5	297.9	296.1	294.5	296.2	297.6
55°	312.9	299.7	292.6	285.0	280.0	274.3	272.5	271.7	270.7	273.5	274.9
57.5°	281.8	272.6	264.2	256.7	252.2	248.9	246.5	246.1	248.1	249.4	254.1
60°	262.1	251.4	243.8	238.1	232.7	230.5	229.9	229.1	230.5	234.5	240.6
62.5°	240.3	231.6	223.5	219.2	215.3	211.7	211.5	212.0	214.8	219.3	225.5
65°	208.4	200.9	195.5	190.5	187.3	185.1	185.9	187.3	190.5	196.6	203.4
67.5°	176.0	170.8	166.0	161.9	158.8	158.8	159.6	161.7	165.5	172.5	178.7
70°	155.0	149.3	145.3	143.5	141.1	139.7	141.8	145.3	148.5	155.0	160.4
72.5°	134.1	129.2	126.2	125.0	123.9	122.7	123.5	127.3	131.7	138.2	144.4
75°	103.1	101.3	99.2	97.7	96.7	97.4	98.1	101.7	105.3	112.1	119.2
77.5°	75.3	73.4	72.1	71.7	71.2	71.5	73.5	76.2	79.7	84.6	90.1
80°	56.9	56.2	55.5	55.1	55.1	55.5	58.3	60.1	63.3	68.1	72.3
82.5°	41.5	41.0	40.9	40.8	41.1	41.2	42.9	45.2	47.9	51.5	55.1
85°	21.9	21.1	22.2	22.5	21.9	22.9	23.7	25.1	26.1	27.9	29.7
87.5°	8.0	8.8	8.7	9.1	9.3	10.0	9.9	11.1	11.8	12.5	12.3
90°	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8	10.4	11.0	11.5
92.5°	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8	10.4	11.0	11.4
95°	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8	10.4	11.0	11.3
97.5°	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7	16.3	13.0	11.3
100°	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0	40.2	22.3	13.2
102.5°	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6	109.2	105.9	100.2
105°	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9	202.9	202.9	202.7
110°	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5	230.2	229.8	229.7



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9	257.4	256.9	256.7
115°	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1	298.6	298.1	297.6
117.5°	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9	338.3	337.7	337.2
120°	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7	364.4	364.2	363.7
122.5°	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2	389.0	388.7	388.2
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0	424.4	424.0	423.6
127.5°	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6	457.4	457.1	456.6
130°	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0	478.6	478.2	477.8
132.5°	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9	498.8	498.8	498.4
135°	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1	527.9	527.6	527.2
137.5°	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3	555.4	555.4	555.2
140°	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1	572.3	572.6	572.3
142.5°	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5	588.5	588.6	588.2
145°	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7	611.8	611.9	611.6
147.5°	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5	631.7	631.8	631.4
150°	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1	644.4	644.6	644.3
152.5°	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3	655.6	655.8	655.5
155°	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8	671.1	671.5	671.2
157.5°	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5	683.9	684.3	684.0
160°	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4	691.9	692.4	692.1
162.5°	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7	699.4	700.0	699.8
165°	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0	708.8	709.5	709.4
167.5°	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1	716.0	716.8	716.7
170°	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8	719.7	720.7	720.6
172.5°	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5	722.5	723.3	723.2
175°	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6	725.6	726.6	726.5
177.5°	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9	726.6	727.3	727.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	803.7	805.8	804.1	806.3	804.1	805.8	803.7	805.5	808.0	806.3	810.3
5°	740.8	737.5	739.7	738.3	739.7	737.5	740.8	742.6	746.9	748.3	751.2
7.5°	682.7	679.6	676.1	674.4	676.1	679.6	682.7	683.7	687.4	692.8	696.8
10°	646.3	642.3	642.0	639.5	642.0	642.3	646.3	650.3	652.7	659.5	664.2
12.5°	619.6	616.0	611.9	610.9	611.9	616.0	619.6	623.0	623.8	631.5	634.7
15°	581.8	579.0	576.5	578.6	576.5	579.0	581.8	584.0	588.0	593.3	596.9
17.5°	550.4	548.0	547.6	545.0	547.6	548.0	550.4	551.6	558.1	561.6	567.7
20°	530.7	528.9	529.5	524.9	529.5	528.9	530.7	533.9	540.3	542.1	548.6
22.5°	514.9	511.3	511.0	510.0	511.0	511.3	514.9	517.8	519.1	524.6	529.0
25°	490.2	488.4	486.6	488.4	486.6	488.4	490.2	493.4	494.8	498.8	503.0
27.5°	468.6	466.5	466.0	466.2	466.0	466.5	468.6	468.3	472.2	475.3	478.5
30°	455.4	451.9	452.2	451.9	452.2	451.9	455.4	455.4	457.6	460.4	463.4
32.5°	441.1	438.7	438.2	437.5	438.2	438.7	441.1	440.5	443.3	446.7	449.9
35°	420.0	420.0	418.2	418.2	418.2	420.0	420.0	421.0	424.0	424.0	427.5
37.5°	400.1	399.8	398.7	398.9	398.7	399.8	400.1	401.1	402.0	403.5	405.9
40°	385.2	384.9	383.8	381.6	383.8	384.9	385.2	386.7	387.4	389.2	390.6
42.5°	371.0	369.8	369.2	368.5	369.2	369.8	371.0	371.8	372.2	374.6	377.5
45°	348.4	348.4	347.7	347.3	347.7	348.4	348.4	348.4	348.7	351.6	353.1
47.5°	326.5	327.2	328.5	328.3	328.5	327.2	326.5	325.9	326.0	327.4	329.1
50°	313.3	313.7	314.7	315.1	314.7	313.7	313.3	311.9	311.1	311.1	312.3
52.5°	298.7	300.8	302.1	301.9	302.1	300.8	298.7	297.6	296.2	294.5	296.1
55°	278.2	280.7	283.2	283.6	283.2	280.7	278.2	274.9	273.5	270.7	271.7
57.5°	258.0	261.5	264.1	264.9	264.1	261.5	258.0	254.1	249.4	248.1	246.1
60°	244.2	248.8	252.0	253.5	252.0	248.8	244.2	240.6	234.5	230.5	229.1
62.5°	231.0	236.2	239.5	239.8	239.5	236.2	231.0	225.5	219.3	214.8	212.0
65°	209.4	214.8	217.7	219.8	217.7	214.8	209.4	203.4	196.6	190.5	187.3
67.5°	186.2	191.6	194.8	196.5	194.8	191.6	186.2	178.7	172.5	165.5	161.7
70°	169.4	174.7	179.0	180.5	179.0	174.7	169.4	160.4	155.0	148.5	145.3
72.5°	152.8	157.5	161.0	162.7	161.0	157.5	152.8	144.4	138.2	131.7	127.3
75°	123.9	130.4	133.6	135.3	133.6	130.4	123.9	119.2	112.1	105.3	101.7
77.5°	95.6	101.4	103.3	104.2	103.3	101.4	95.6	90.1	84.6	79.7	76.2
80°	76.6	80.2	82.8	83.0	82.8	80.2	76.6	72.3	68.1	63.3	60.1
82.5°	58.9	61.8	62.7	63.6	62.7	61.8	58.9	55.1	51.5	47.9	45.2
85°	32.2	33.6	34.0	33.6	34.0	33.6	32.2	29.7	27.9	26.1	25.1
87.5°	13.0	12.7	12.8	13.5	12.8	12.7	13.0	12.3	12.5	11.8	11.1
90°	11.9	12.2	12.5	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8
92.5°	11.5	11.7	11.9	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8
95°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8
97.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7
100°	12.7	12.3	11.8	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0
102.5°	92.0	83.9	75.8	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6
105°	160.0	159.9	159.9	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2
107.5°	202.5	202.1	201.7	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9
110°	229.8	229.9	230.1	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	256.5	256.3	256.2	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9
115°	296.8	296.1	295.4	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1
117.5°	337.0	336.6	336.3	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9
120°	363.2	362.6	361.9	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7
122.5°	387.6	386.8	386.2	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2
125°	423.2	422.8	422.5	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0
127.5°	455.6	454.8	453.9	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6
130°	477.2	476.5	476.0	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0
132.5°	497.9	497.2	496.6	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9
135°	526.5	525.8	525.0	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1
137.5°	554.6	553.9	553.4	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3
140°	571.7	570.9	570.2	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1
142.5°	587.6	586.8	586.1	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5
145°	610.9	610.2	609.4	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7
147.5°	630.6	629.7	628.9	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5
150°	643.4	642.3	641.4	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1
152.5°	654.7	653.8	652.9	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3
155°	670.2	669.3	668.4	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8
157.5°	683.1	682.0	681.1	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5
160°	691.2	690.2	689.3	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4
162.5°	698.8	697.8	696.7	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7
165°	708.4	707.5	706.5	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0
167.5°	715.7	714.5	713.5	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1
170°	719.5	718.4	717.4	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8
172.5°	722.1	721.0	719.9	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5
175°	725.5	724.3	723.3	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6
177.5°	726.4	725.7	724.9	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	806.6	810.0	814.4	817.5	823.2	825.8	829.0	831.5	836.1	840.4	845.6
5°	752.2	758.4	766.6	775.5	785.9	793.1	803.1	809.2	821.3	832.5	843.2
7.5°	702.9	710.5	722.1	733.6	747.2	759.5	772.0	785.9	801.4	819.8	835.0
10°	669.2	679.2	691.7	706.1	722.6	736.9	753.7	768.7	787.7	809.2	829.2
12.5°	642.2	650.8	664.9	678.5	696.2	713.7	731.0	751.0	773.1	796.9	822.1
15°	605.1	612.3	623.7	642.7	660.6	677.8	703.9	722.6	750.5	776.9	807.4
17.5°	573.3	582.3	591.9	608.2	626.7	648.2	671.6	694.9	721.8	755.4	789.8
20°	553.9	561.1	572.1	584.7	604.4	625.8	648.1	671.7	704.6	739.3	776.3
22.5°	532.7	540.5	553.0	566.7	583.2	603.8	628.3	654.2	688.6	722.7	762.8
25°	507.7	513.1	524.5	536.7	553.2	570.7	596.2	624.8	658.8	697.9	738.7
27.5°	484.2	488.9	499.4	509.9	524.8	545.6	568.4	597.3	629.3	668.9	714.2
30°	467.2	472.3	481.5	493.0	507.4	525.7	548.9	576.1	610.5	649.1	696.4
32.5°	452.6	457.1	464.1	475.6	489.6	507.3	528.9	556.7	591.0	630.3	676.7
35°	430.0	435.0	440.4	449.3	461.6	478.7	502.4	528.5	561.4	599.4	642.0
37.5°	407.6	412.9	417.7	425.7	436.9	452.0	472.5	499.7	529.5	566.1	607.0
40°	393.5	397.8	401.7	410.3	421.4	435.7	454.7	479.1	510.6	544.6	578.6
42.5°	379.5	383.4	386.8	394.3	404.5	418.3	436.4	460.1	489.4	521.1	551.1
45°	357.3	359.9	363.8	370.2	378.4	391.0	408.5	429.7	454.4	484.5	507.0
47.5°	333.4	337.3	340.5	346.2	353.0	365.2	382.1	400.1	422.5	444.9	460.7
50°	315.1	319.1	323.7	329.0	335.5	346.9	362.3	380.6	399.5	416.8	430.4
52.5°	297.9	301.5	306.5	311.6	319.4	329.2	342.3	358.5	377.2	389.6	400.9
55°	272.5	274.3	280.0	285.0	292.6	299.7	312.9	327.3	338.7	348.0	357.3
57.5°	246.5	248.9	252.2	256.7	264.2	272.6	281.8	294.5	301.2	306.0	313.3
60°	229.9	230.5	232.7	238.1	243.8	251.4	262.1	271.1	276.1	280.0	286.1
62.5°	211.5	211.7	215.3	219.2	223.5	231.6	240.3	247.5	251.8	253.6	259.5
65°	185.9	185.1	187.3	190.5	195.5	200.9	208.4	214.8	214.4	216.6	220.2
67.5°	159.6	158.8	158.8	161.9	166.0	170.8	176.0	179.6	179.7	182.6	184.4
70°	141.8	139.7	141.1	143.5	145.3	149.3	155.0	156.5	156.8	158.3	160.0
72.5°	123.5	122.7	123.9	125.0	126.2	129.2	134.1	135.0	135.1	135.9	138.8
75°	98.1	97.4	96.7	97.7	99.2	101.3	103.1	104.5	104.2	104.5	106.7
77.5°	73.5	71.5	71.2	71.7	72.1	73.4	75.3	75.1	75.5	75.4	77.9
80°	58.3	55.5	55.1	55.1	55.5	56.2	56.9	57.7	56.6	57.7	58.3
82.5°	42.9	41.2	41.1	40.8	40.9	41.0	41.5	41.8	41.7	42.1	42.6
85°	23.7	22.9	21.9	22.5	22.2	21.1	21.9	20.7	20.5	20.7	21.1
87.5°	9.9	10.0	9.3	9.1	8.7	8.8	8.0	7.5	7.1	7.2	7.8
90°	9.2	8.6	7.7	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6
92.5°	9.2	8.6	7.8	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3
95°	9.2	8.6	13.1	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6
97.5°	23.1	26.5	35.4	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0
100°	75.8	93.6	93.1	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8
102.5°	116.0	119.4	119.1	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0
105°	160.2	160.2	160.2	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1
107.5°	202.8	202.8	202.6	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8
110°	230.9	231.2	231.0	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	258.4	258.7	258.6	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8
115°	299.6	300.1	299.9	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8
117.5°	339.6	340.2	339.7	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3
120°	364.9	365.1	364.8	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1
122.5°	389.5	389.6	389.5	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2
127.5°	457.9	458.2	458.3	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8
130°	479.3	479.7	479.6	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5
132.5°	499.0	499.1	499.3	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1
135°	528.4	528.6	528.9	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5
137.5°	555.3	555.3	555.5	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5
140°	571.8	571.7	571.7	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1
142.5°	588.4	588.4	588.2	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0
145°	611.5	611.4	611.4	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4
147.5°	631.4	631.2	631.0	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7
150°	643.9	643.7	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7
152.5°	655.2	654.9	654.6	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2
155°	670.4	670.1	669.8	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2
157.5°	683.2	682.8	682.7	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6
160°	691.0	690.5	690.3	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1
162.5°	698.0	697.4	697.2	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0
165°	707.3	706.6	706.5	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3
167.5°	714.3	713.4	713.2	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1
170°	717.7	716.8	716.7	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1
172.5°	720.7	719.8	719.6	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6
175°	723.7	722.7	722.6	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5
177.5°	725.3	724.5	724.4	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	848.2	852.2	854.7	859.6	863.7	865.9	867.9	869.6	871.7	873.4	878.3
5°	853.6	862.9	870.8	883.0	894.1	902.7	911.9	920.2	927.0	936.7	944.1
7.5°	851.2	867.8	885.1	903.9	923.2	941.1	957.5	973.0	986.9	1003.8	1018.6
10°	848.9	871.5	893.7	919.1	945.3	967.4	988.3	1009.4	1024.7	1046.2	1064.5
12.5°	847.3	873.8	900.6	931.1	959.9	991.2	1018.9	1034.3	1057.7	1074.9	1096.6
15°	840.0	875.1	911.9	946.3	987.1	1016.2	1040.5	1070.5	1092.4	1114.3	1137.8
17.5°	827.0	866.8	908.0	953.1	992.2	1023.4	1054.7	1083.7	1109.8	1139.1	1168.6
20°	821.0	860.7	908.0	954.2	992.5	1025.1	1057.3	1089.2	1117.9	1155.5	1189.4
22.5°	808.4	856.5	900.0	945.0	984.5	1019.9	1056.5	1092.6	1130.7	1173.2	1215.8
25°	785.9	834.6	880.8	925.2	965.0	1009.4	1048.4	1096.7	1145.4	1201.6	1254.6
27.5°	762.6	809.2	851.5	894.4	940.8	991.0	1041.6	1096.5	1160.3	1231.1	1306.0
30°	743.7	787.7	828.9	872.9	921.2	977.8	1033.3	1098.5	1172.2	1252.1	1340.9
32.5°	721.6	762.2	802.3	848.9	901.5	961.2	1025.9	1097.3	1186.0	1276.8	1368.1
35°	683.9	717.9	759.0	808.8	868.3	936.7	1011.5	1096.0	1197.7	1301.8	1378.8
37.5°	639.1	670.8	714.2	768.7	831.0	904.5	993.3	1093.4	1201.5	1284.5	1309.4
40°	609.1	638.4	683.5	740.1	803.8	881.6	978.9	1084.9	1189.4	1242.5	1222.0
42.5°	576.9	607.8	651.8	707.8	776.3	860.9	960.8	1066.9	1154.5	1174.5	1104.0
45°	526.3	558.2	601.5	658.1	731.9	823.5	927.7	1024.0	1074.5	1038.3	929.2
47.5°	479.3	509.2	549.3	607.7	683.8	778.6	878.9	955.7	959.8	873.5	756.9
50°	447.2	474.8	515.2	573.6	649.1	745.1	835.7	896.2	869.0	771.3	659.2
52.5°	415.7	442.7	482.6	540.4	615.1	702.9	787.3	829.7	778.4	678.2	582.4
55°	370.2	393.9	432.9	486.3	557.1	638.8	710.4	725.0	658.5	559.6	481.9
57.5°	325.8	347.9	383.4	432.5	497.3	569.7	625.7	622.5	552.1	467.3	405.7
60°	295.8	317.3	348.7	396.7	455.8	518.1	566.1	554.6	484.8	411.8	359.9
62.5°	268.8	288.0	317.8	359.8	413.7	471.4	510.8	493.9	425.5	361.7	320.6
65°	229.1	245.2	270.7	306.5	351.3	398.9	429.3	407.5	349.1	299.4	266.4
67.5°	191.2	204.2	225.5	254.1	292.3	330.5	349.0	327.1	280.3	244.0	219.6
70°	167.2	178.7	195.1	220.6	253.8	286.1	300.0	280.3	240.3	209.1	191.5
72.5°	143.2	152.6	167.1	189.9	216.6	244.6	256.7	238.0	205.0	178.7	162.3
75°	110.7	117.1	127.1	142.9	164.0	186.2	193.0	176.5	155.4	135.7	125.0
77.5°	79.2	84.6	92.3	102.2	117.2	131.3	137.2	127.7	111.3	98.9	90.1
80°	60.9	63.7	70.2	78.4	90.2	99.2	103.1	97.0	85.6	76.3	69.5
82.5°	43.4	46.3	50.1	56.9	64.5	70.5	74.7	70.7	62.4	55.0	51.1
85°	21.1	22.9	25.1	27.9	33.6	37.2	36.9	34.4	31.1	28.3	26.1
87.5°	7.7	8.2	9.2	10.9	12.0	13.3	13.9	13.6	12.6	11.9	11.1
90°	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8
92.5°	7.6	7.0	6.3	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8
95°	30.3	30.0	29.6	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8
97.5°	64.7	65.3	65.9	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7
100°	90.2	90.5	90.9	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0
102.5°	116.5	117.0	117.4	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6
105°	158.5	159.1	159.6	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.8	201.8	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9
110°	230.2	230.2	230.2	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	257.1	257.4	257.7	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9
115°	297.5	298.0	298.6	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1
117.5°	338.2	338.2	338.2	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9
120°	363.9	363.8	363.7	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7
122.5°	387.3	387.8	388.2	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2
125°	423.0	423.8	424.6	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0
127.5°	456.4	457.0	457.6	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6
130°	477.0	477.7	478.2	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0
132.5°	497.8	498.5	499.2	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9
135°	527.2	527.9	528.6	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1
137.5°	554.1	554.7	555.3	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3
140°	571.4	571.6	571.8	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1
142.5°	587.2	587.3	587.5	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5
145°	610.6	610.9	611.1	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7
147.5°	630.7	630.7	630.7	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5
150°	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1
152.5°	655.6	655.2	654.6	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3
155°	671.5	670.8	670.1	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8
157.5°	684.1	683.7	683.2	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5
160°	692.5	691.7	691.0	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4
162.5°	699.4	698.6	697.9	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7
165°	708.6	707.8	707.2	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0
167.5°	715.5	714.7	714.0	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1
170°	719.3	718.4	717.6	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8
172.5°	721.8	721.0	720.1	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5
175°	724.7	724.0	723.3	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6
177.5°	726.1	725.6	725.0	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	843.6	843.6	843.6	843.6	843.6	843.6	843.6
2.5°	882.2	884.5	889.4	887.7	889.9	891.1	892.3
5°	953.5	965.0	970.0	969.2	976.8	975.0	973.2
7.5°	1034.0	1046.0	1052.7	1061.1	1066.0	1066.3	1070.5
10°	1079.5	1095.2	1101.7	1110.7	1116.4	1119.6	1119.3
12.5°	1114.5	1126.8	1141.2	1145.7	1153.4	1157.4	1155.9
15°	1156.5	1176.2	1191.2	1198.7	1208.4	1211.3	1215.2
17.5°	1194.0	1220.4	1238.0	1261.3	1270.2	1275.5	1272.3
20°	1222.4	1257.1	1274.7	1302.6	1318.0	1326.3	1323.3
22.5°	1255.9	1293.5	1326.0	1350.1	1373.6	1384.7	1387.0
25°	1313.3	1364.9	1412.5	1444.4	1473.4	1480.2	1495.2
27.5°	1377.5	1438.3	1489.2	1522.7	1542.9	1550.5	1555.2
30°	1417.9	1478.4	1516.7	1538.1	1544.6	1543.9	1543.2
32.5°	1437.7	1475.6	1482.9	1476.9	1462.2	1449.6	1436.6
35°	1409.7	1381.4	1339.1	1284.7	1244.6	1204.1	1200.1
37.5°	1267.8	1177.3	1107.0	1028.5	983.2	955.2	935.8
40°	1134.3	1031.5	946.3	880.1	833.9	815.7	797.8
42.5°	989.4	891.2	815.7	760.3	725.7	705.4	691.2
45°	803.8	717.2	658.1	618.0	590.4	574.7	565.7
47.5°	658.6	594.6	544.4	515.5	496.4	484.2	484.2
50°	580.8	519.5	486.3	463.4	446.9	437.2	438.9
52.5°	511.7	466.0	437.5	418.3	406.1	400.2	400.0
55°	427.9	394.9	376.4	362.3	354.1	347.3	348.7
57.5°	366.0	338.2	325.7	314.1	308.4	305.7	301.8
60°	327.6	306.1	295.4	286.1	280.3	278.2	274.3
62.5°	293.5	276.6	266.2	258.5	253.4	252.7	249.6
65°	246.7	233.8	224.5	220.9	215.6	214.1	214.1
67.5°	203.4	194.2	186.9	183.6	181.3	181.6	179.8
70°	176.2	168.6	164.0	160.4	158.6	159.0	157.5
72.5°	154.1	145.7	141.7	139.5	137.1	138.1	137.5
75°	116.7	112.4	110.3	108.1	106.7	105.9	105.3
77.5°	85.7	81.9	80.3	79.1	79.3	77.6	78.9
80°	66.3	63.1	61.9	60.1	59.8	59.8	59.5
82.5°	48.4	46.7	45.9	44.4	43.7	44.3	43.4
85°	25.1	23.7	23.3	23.3	22.5	21.9	23.7
87.5°	11.2	10.2	10.3	10.1	10.2	10.0	9.4
90°	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	10.4	11.0	11.4	11.5	11.7	11.9	12.1
95°	10.4	11.0	11.3	11.3	11.3	11.3	11.3
97.5°	16.3	13.0	11.3	11.3	11.3	11.3	11.3
100°	40.2	22.3	13.2	12.7	12.3	11.8	11.3
102.5°	109.2	105.9	100.2	92.0	83.9	75.8	67.7
105°	160.2	160.2	160.2	160.0	159.9	159.9	159.7
107.5°	202.9	202.9	202.7	202.5	202.1	201.7	201.3
110°	230.2	229.8	229.7	229.8	229.9	230.1	230.2



TEST NUMBER: P333169-830

CATALOG NUMBER: S125DIP-S610D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	257.4	256.9	256.7	256.5	256.3	256.2	256.0
115°	298.6	298.1	297.6	296.8	296.1	295.4	294.7
117.5°	338.3	337.7	337.2	337.0	336.6	336.3	336.0
120°	364.4	364.2	363.7	363.2	362.6	361.9	361.4
122.5°	389.0	388.7	388.2	387.6	386.8	386.2	385.5
125°	424.4	424.0	423.6	423.2	422.8	422.5	422.2
127.5°	457.4	457.1	456.6	455.6	454.8	453.9	453.0
130°	478.6	478.2	477.8	477.2	476.5	476.0	475.4
132.5°	498.8	498.8	498.4	497.9	497.2	496.6	496.1
135°	527.9	527.6	527.2	526.5	525.8	525.0	524.3
137.5°	555.4	555.4	555.2	554.6	553.9	553.4	552.7
140°	572.3	572.6	572.3	571.7	570.9	570.2	569.5
142.5°	588.5	588.6	588.2	587.6	586.8	586.1	585.4
145°	611.8	611.9	611.6	610.9	610.2	609.4	608.7
147.5°	631.7	631.8	631.4	630.6	629.7	628.9	628.0
150°	644.4	644.6	644.3	643.4	642.3	641.4	640.5
152.5°	655.6	655.8	655.5	654.7	653.8	652.9	652.1
155°	671.1	671.5	671.2	670.2	669.3	668.4	667.3
157.5°	683.9	684.3	684.0	683.1	682.0	681.1	680.1
160°	691.9	692.4	692.1	691.2	690.2	689.3	688.3
162.5°	699.4	700.0	699.8	698.8	697.8	696.7	695.6
165°	708.8	709.5	709.4	708.4	707.5	706.5	705.5
167.5°	716.0	716.8	716.7	715.7	714.5	713.5	712.4
170°	719.7	720.7	720.6	719.5	718.4	717.4	716.3
172.5°	722.5	723.3	723.2	722.1	721.0	719.9	718.9
175°	725.6	726.6	726.5	725.5	724.3	723.3	722.2
177.5°	726.6	727.3	727.2	726.4	725.7	724.9	724.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5

(END OF REPORT)