

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333600-830

Luminaire Tested: **S125RDIP-S1090D1035U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333600-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7517.4 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46				46
2	91	83	77	72	84	78	72	68	67	63	59	57	54	51	47	45	44	39				39
3	83	74	66	61	77	69	62	57	59	54	50	50	47	44	42	40	38	34				34
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33	29				29
5	70	58	50	44	65	55	47	42	47	42	38	41	36	33	34	31	29	25				25
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22				22
7	60	47	40	34	55	44	37	32	39	33	29	34	29	26	29	25	23	20				20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18				18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16				16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	22	19	17	15				15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	2.0
10°-20°	435.5	5.8
20°-30°	690.5	9.2
30°-40°	832.7	11.1
40°-50°	743.6	9.9
50°-60°	570.3	7.6
60°-70°	370.6	4.9
70°-80°	180.2	2.4
80°-90°	45.6	0.6
90°-100°	338.3	4.5
100°-110°	727.2	9.7
110°-120°	682.5	9.1
120°-130°	553.1	7.4
130°-140°	443.9	5.9
140°-150°	334.9	4.5
150°-160°	235.8	3.1
160°-170°	139.0	1.8
170°-180°	45.2	0.6
0°-30°	1274.6	17.0
0°-40°	2107.3	28.0
0°-60°	3421.2	45.5
0°-90°	4017.6	53.4
90°-120°	1747.9	23.3
90°-150°	3079.8	41.0
90°-180°	3500.0	46.6
0°-180°	7517.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	22	1	22	1	22	16
95°	221	31	221	31	221	313
105°	1247	106	1247	106	1247	1239
115°	1389	190	1389	190	1389	1357
125°	1094	263	1094	263	1094	990
135°	909	309	909	309	909	704
145°	717	359	717	359	717	456
155°	601	410	601	410	601	280
165°	527	448	527	448	527	151
175°	473	466	473	466	473	46
180°	467	467	467	467	467	



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	15.6	15.0	14.3	14.3	14.8	15.5	14.8	14.0	13.9	13.7	13.9
90°	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0	16.0	15.1	13.2
92.5°	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7	245.5	303.3	308.2
95°	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6	815.8	833.7	680.3
97.5°	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6	1032.2	890.3	607.5
100°	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3	1084.9	849.6	542.0
102.5°	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8	1053.3	778.2	492.3
105°	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0	952.3	682.1	444.1
107.5°	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9	849.0	616.1	423.8
110°	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6	790.3	585.2	417.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9	746.7	567.2	417.7
115°	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3	699.1	547.6	420.6
117.5°	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3	670.7	538.0	426.8
120°	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2	654.9	533.5	432.8
122.5°	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9	641.3	529.7	438.1
125°	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4	622.9	525.0	447.0
127.5°	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2	606.0	522.7	456.9
130°	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4	594.7	521.2	463.0
132.5°	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6	585.6	521.2	469.7
135°	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1	574.9	521.2	478.9
137.5°	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4	565.3	522.4	487.4
140°	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1	560.8	523.1	491.2
142.5°	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3	557.0	523.9	493.4
145°	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5	551.4	523.1	495.9
147.5°	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5	545.5	520.7	496.8
150°	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8	541.0	518.4	496.8
152.5°	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2	535.7	515.5	496.1
155°	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9	526.9	510.0	494.0
157.5°	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6	518.6	504.4	491.5
160°	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1	511.9	500.6	489.3
162.5°	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9	505.9	496.1	487.0
165°	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4	496.8	489.3	483.6
167.5°	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4	488.0	482.7	478.3
170°	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4	482.7	478.9	476.1
172.5°	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6	477.4	474.4	473.1
175°	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3	470.4	469.5	469.5
177.5°	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2	467.4	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	14.1	13.8	14.1	13.8	12.8	15.0	16.1	16.5	15.6	15.0	14.3
90°	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9	1.9	3.8	5.7
92.5°	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5	13.9	21.9	33.5
95°	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0	32.0	39.5	49.9
97.5°	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6	52.7	58.0	68.3
100°	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9	67.8	71.5	81.8
102.5°	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7	82.8	85.8	96.9
105°	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3	106.3	111.0	120.5
107.5°	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4	132.3	136.8	144.5
110°	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7	149.6	153.4	161.8



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0	166.9	169.9	178.4
115°	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1	191.9	194.7	203.2
117.5°	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6	215.5	218.5	227.0
120°	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7	230.5	234.3	242.8
122.5°	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6	245.5	248.5	257.0
125°	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4	265.3	270.0	278.5
127.5°	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1	281.9	287.9	298.7
130°	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9	291.7	299.3	311.4
132.5°	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4	299.9	309.0	322.7
135°	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6	312.4	323.7	338.7
137.5°	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0	326.9	337.4	352.5
140°	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1	335.9	347.2	362.2
142.5°	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7	345.7	356.2	371.3
145°	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4	361.3	370.7	383.9
147.5°	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0	377.1	385.2	397.5
150°	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8	387.7	394.3	406.5
152.5°	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3	397.5	403.3	414.0
155°	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2	410.2	415.8	425.3
157.5°	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6	422.4	427.0	435.1
160°	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9	430.0	433.8	440.4
162.5°	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7	436.8	440.5	446.4
165°	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9	446.0	448.8	453.6
167.5°	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7	453.7	455.4	458.1
170°	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2	458.3	459.2	461.1
172.5°	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2	460.5	461.5	463.3
175°	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7	463.8	464.8	465.7
177.5°	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4	465.9	465.9	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	14.2	14.6	14.3	15.6	14.3	15.3	15.5	15.1	15.3	15.5	15.4
90°	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0	17.9	18.9	20.7
92.5°	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7	121.0	91.0	77.2
95°	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6	533.5	417.7	338.7
97.5°	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6	907.2	794.5	684.6
100°	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3	1111.3	1014.3	916.4
102.5°	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8	1236.1	1189.7	1123.4
105°	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0	1306.9	1348.3	1337.9
107.5°	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9	1243.9	1350.2	1399.3
110°	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6	1172.3	1305.0	1385.1



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9	1101.6	1235.8	1330.1
115°	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3	1000.2	1129.1	1231.6
117.5°	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3	930.0	1041.0	1135.1
120°	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2	890.1	993.6	1076.4
122.5°	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9	861.5	953.7	1031.2
125°	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4	823.3	905.1	972.9
127.5°	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2	786.8	863.2	926.6
130°	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4	761.2	834.6	895.8
132.5°	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6	737.1	803.7	862.6
135°	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1	700.0	760.3	813.9
137.5°	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4	666.9	717.0	762.5
140°	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1	647.3	690.6	730.2
142.5°	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3	630.7	668.1	702.3
145°	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5	609.7	638.9	664.3
147.5°	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5	592.2	614.6	633.8
150°	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8	582.4	600.3	617.3
152.5°	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2	572.6	589.0	602.2
155°	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9	558.0	571.2	581.5
157.5°	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6	544.0	554.2	562.3
160°	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1	533.5	542.9	549.5
162.5°	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9	524.4	532.3	538.2
165°	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4	511.0	516.6	521.2
167.5°	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4	497.8	502.1	505.5
170°	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4	490.2	493.0	494.9
172.5°	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6	483.4	485.5	486.6
175°	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3	473.3	475.1	475.1
177.5°	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2	468.9	468.9	468.9
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	15.8	15.4	15.6	15.6	15.6	15.4	15.8	15.4	15.5	15.3	15.1
90°	20.7	20.7	21.7	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0
92.5°	65.1	62.9	61.5	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7
95°	271.9	243.7	236.2	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6
97.5°	626.5	573.7	546.5	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6
100°	851.5	783.8	748.9	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3
102.5°	1054.0	1005.9	968.0	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8
105°	1307.9	1276.9	1258.0	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0
107.5°	1414.6	1414.4	1408.2	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9
110°	1427.4	1445.2	1451.8	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1391.9	1422.7	1439.1	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9
115°	1305.0	1350.2	1376.6	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3
117.5°	1208.5	1255.2	1281.3	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3
120°	1146.0	1191.2	1216.6	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2
122.5°	1093.3	1134.7	1160.2	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9
125°	1025.6	1064.1	1084.9	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4
127.5°	974.4	1008.4	1028.0	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2
130°	942.8	973.8	992.7	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4
132.5°	909.6	940.8	958.0	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6
135°	855.3	886.4	903.2	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1
137.5°	799.6	827.8	843.5	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4
140°	765.0	789.5	803.5	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1
142.5°	731.9	752.5	765.9	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3
145°	686.8	702.9	713.2	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5
147.5°	651.7	664.5	670.5	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5
150°	631.3	642.6	646.4	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8
152.5°	614.1	623.1	626.8	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2
155°	590.9	597.5	600.3	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9
157.5°	569.7	575.0	577.7	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6
160°	556.1	560.8	562.7	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1
162.5°	543.3	547.2	547.6	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9
165°	525.0	526.9	526.9	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4
167.5°	507.4	509.1	508.3	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4
170°	496.8	497.8	497.8	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4
172.5°	487.0	488.7	487.2	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6
175°	475.1	476.1	474.2	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3
177.5°	468.2	468.9	466.7	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	15.5	15.3	14.3	15.6	14.3	14.6	14.2	14.3	15.0	15.6	16.5
90°	16.0	15.1	13.2	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9
92.5°	245.5	303.3	308.2	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5
95°	815.8	833.7	680.3	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0
97.5°	1032.2	890.3	607.5	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6
100°	1084.9	849.6	542.0	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9
102.5°	1053.3	778.2	492.3	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7
105°	952.3	682.1	444.1	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3
107.5°	849.0	616.1	423.8	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4
110°	790.3	585.2	417.7	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	746.7	567.2	417.7	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0
115°	699.1	547.6	420.6	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1
117.5°	670.7	538.0	426.8	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6
120°	654.9	533.5	432.8	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7
122.5°	641.3	529.7	438.1	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6
125°	622.9	525.0	447.0	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4
127.5°	606.0	522.7	456.9	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1
130°	594.7	521.2	463.0	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9
132.5°	585.6	521.2	469.7	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4
135°	574.9	521.2	478.9	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6
137.5°	565.3	522.4	487.4	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0
140°	560.8	523.1	491.2	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1
142.5°	557.0	523.9	493.4	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7
145°	551.4	523.1	495.9	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4
147.5°	545.5	520.7	496.8	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0
150°	541.0	518.4	496.8	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8
152.5°	535.7	515.5	496.1	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3
155°	526.9	510.0	494.0	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2
157.5°	518.6	504.4	491.5	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6
160°	511.9	500.6	489.3	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9
162.5°	505.9	496.1	487.0	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7
165°	496.8	489.3	483.6	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9
167.5°	488.0	482.7	478.3	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7
170°	482.7	478.9	476.1	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2
172.5°	477.4	474.4	473.1	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2
175°	470.4	469.5	469.5	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7
177.5°	467.4	466.7	466.7	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.1	15.0	12.8	13.8	14.1	13.8	14.1	13.9	13.7	13.9	14.0
90°	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0
92.5°	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7
95°	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6
97.5°	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6
100°	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3
102.5°	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8
105°	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0
107.5°	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9
110°	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9
115°	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3
117.5°	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3
120°	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2
122.5°	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9
125°	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4
127.5°	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2
130°	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4
132.5°	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6
135°	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1
137.5°	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4
140°	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1
142.5°	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3
145°	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5
147.5°	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5
150°	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8
152.5°	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2
155°	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9
157.5°	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6
160°	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1
162.5°	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9
165°	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4
167.5°	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4
170°	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4
172.5°	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6
175°	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3
177.5°	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	14.8	15.5	14.8	14.3	14.3	15.0	15.6
90°	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333600-830

CATALOG NUMBER: S125RDIP-S1090D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)