

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333606-830

Luminaire Tested: **S125RDIP-S1090D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333606-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8091.7 lumens  
Efficiency: N/A  
Efficacy: 123.7 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43				
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	44	43	41	36				
3	82	73	66	60	75	68	61	56	58	53	49	48	45	42	40	37	35	31				
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27				
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24				
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	21				
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19				
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	17				
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15				
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.6	1.8
10°-20°	435.5	5.4
20°-30°	690.5	8.5
30°-40°	832.7	10.3
40°-50°	743.6	9.2
50°-60°	570.3	7.0
60°-70°	370.6	4.6
70°-80°	180.2	2.2
80°-90°	46.0	0.6
90°-100°	393.7	4.9
100°-110°	846.4	10.5
110°-120°	794.4	9.8
120°-130°	643.8	8.0
130°-140°	516.6	6.4
140°-150°	389.9	4.8
150°-160°	274.4	3.4
160°-170°	161.8	2.0
170°-180°	52.6	0.7
0°-30°	1274.6	15.8
0°-40°	2107.3	26.0
0°-60°	3421.2	42.3
0°-90°	4018.0	49.7
90°-120°	2034.5	25.1
90°-150°	3584.8	44.3
90°-180°	4074.0	50.3
0°-180°	8091.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	25	1	25	1	25	19
95°	257	36	257	36	257	365
105°	1451	124	1451	124	1451	1442
115°	1616	221	1616	221	1616	1579
125°	1274	307	1274	307	1274	1152
135°	1058	359	1058	359	1058	820
145°	834	418	834	418	834	530
155°	700	478	700	478	700	326
165°	613	521	613	521	613	175
175°	551	542	551	542	551	54
180°	543	543	543	543	543	



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	16.2	15.7	15.0	15.0	15.6	16.1	15.4	14.6	14.4	14.2	14.2
90°	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7	18.7	17.5	15.4
92.5°	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1	285.9	353.1	358.8
95°	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4	949.5	970.3	791.8
97.5°	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7	1201.5	1036.2	707.1
100°	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1	1262.7	988.9	630.8
102.5°	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8	1226.0	905.7	573.0
105°	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2	1108.3	794.0	516.9
107.5°	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6	988.4	717.1	493.2
110°	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5	919.9	681.2	486.3



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7	869.1	660.2	486.3
115°	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5	813.7	637.4	489.6
117.5°	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1	780.6	626.2	496.8
120°	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7	762.2	620.9	503.8
122.5°	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0	746.5	616.6	509.9
125°	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6	725.0	611.1	520.2
127.5°	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5	705.3	608.5	531.8
130°	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7	692.2	606.7	538.9
132.5°	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7	681.6	606.7	546.7
135°	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2	669.2	606.7	557.4
137.5°	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2	658.0	608.0	567.3
140°	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0	652.7	608.9	571.7
142.5°	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6	648.4	609.8	574.3
145°	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7	641.8	608.9	577.2
147.5°	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8	635.0	606.1	578.2
150°	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8	629.7	603.4	578.2
152.5°	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1	623.6	599.9	577.4
155°	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9	613.3	593.6	575.0
157.5°	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8	603.7	587.0	572.1
160°	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0	595.8	582.7	569.5
162.5°	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4	588.8	577.4	566.8
165°	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0	578.2	569.5	562.9
167.5°	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3	568.0	561.8	556.8
170°	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3	561.8	557.4	554.2
172.5°	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4	555.7	552.2	550.6
175°	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9	547.6	546.5	546.5
177.5°	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0	544.1	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	14.5	14.1	14.4	13.9	13.0	15.1	16.2	16.5	15.7	15.1	14.5
90°	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1	2.2	4.3	6.6
92.5°	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4	16.2	25.4	39.0
95°	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1	37.2	46.0	58.1
97.5°	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0	61.4	67.5	79.6
100°	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6	78.9	83.2	95.3
102.5°	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1	96.4	99.9	112.8
105°	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8	123.8	129.2	140.2
107.5°	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7	154.0	159.2	168.2
110°	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9	174.2	178.5	188.4





TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1	194.3	197.7	207.6
115°	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2	223.4	226.7	236.6
117.5°	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5	250.8	254.3	264.2
120°	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0	268.3	272.7	282.6
122.5°	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4	285.9	289.4	299.2
125°	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6	308.9	314.3	324.1
127.5°	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8	328.1	335.2	347.6
130°	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2	339.5	348.3	362.5
132.5°	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0	349.1	359.7	375.7
135°	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2	363.6	376.7	394.3
137.5°	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2	380.5	392.8	410.3
140°	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7	391.0	404.2	421.7
142.5°	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9	402.4	414.6	432.2
145°	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4	420.6	431.5	446.9
147.5°	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6	438.9	448.4	462.6
150°	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0	451.2	458.9	473.2
152.5°	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3	462.6	469.4	481.9
155°	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5	477.5	484.1	495.0
157.5°	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0	491.7	497.0	506.4
160°	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6	500.5	504.9	512.6
162.5°	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4	508.4	512.7	519.5
165°	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3	519.2	522.5	527.9
167.5°	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2	528.1	530.1	533.1
170°	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4	533.4	534.4	536.7
172.5°	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0	536.0	537.1	539.2
175°	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2	539.9	541.0	542.2
177.5°	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1	542.3	542.3	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	14.5	14.9	14.6	16.1	14.8	15.7	15.9	15.6	15.8	16.1	16.0
90°	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7	20.8	21.9	24.1
92.5°	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1	140.8	106.0	89.8
95°	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4	620.9	486.3	394.3
97.5°	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7	1056.0	924.8	796.8
100°	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1	1293.5	1180.6	1066.7
102.5°	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8	1438.9	1384.8	1307.7
105°	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2	1521.3	1569.4	1557.4
107.5°	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6	1447.8	1571.6	1628.8
110°	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5	1364.6	1519.0	1612.1



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7	1282.2	1438.4	1548.1
115°	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5	1164.2	1314.2	1433.6
117.5°	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1	1082.5	1211.7	1321.3
120°	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7	1036.0	1156.5	1252.9
122.5°	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0	1002.8	1110.1	1200.3
125°	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6	958.3	1053.6	1132.5
127.5°	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5	915.8	1004.8	1078.6
130°	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7	886.0	971.5	1042.6
132.5°	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7	858.0	935.5	1004.1
135°	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2	814.8	885.0	947.3
137.5°	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2	776.3	834.5	887.6
140°	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0	753.5	803.9	849.9
142.5°	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6	734.2	777.6	817.5
145°	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7	709.6	743.7	773.2
147.5°	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8	689.3	715.4	737.7
150°	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8	678.0	698.7	718.4
152.5°	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1	666.6	685.6	701.0
155°	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9	649.4	664.8	676.8
157.5°	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8	633.2	645.1	654.5
160°	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0	620.9	631.9	639.6
162.5°	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4	610.5	619.6	626.4
165°	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0	594.7	601.2	606.7
167.5°	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3	579.4	584.4	588.3
170°	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3	570.6	573.9	576.1
172.5°	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4	562.7	565.1	566.5
175°	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9	550.9	553.1	553.1
177.5°	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0	545.8	545.8	545.8
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	16.5	16.0	16.2	16.2	16.2	16.0	16.5	16.0	16.1	15.8	15.6
90°	24.1	24.1	25.2	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7
92.5°	75.8	73.1	71.6	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1
95°	316.5	283.6	274.9	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4
97.5°	729.2	667.9	636.1	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7
100°	991.2	912.3	871.8	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1
102.5°	1226.8	1170.7	1126.7	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8
105°	1522.3	1486.2	1464.2	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2
107.5°	1646.5	1646.3	1639.1	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6
110°	1661.4	1682.2	1689.9	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1620.2	1656.0	1675.0	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7
115°	1519.0	1571.6	1602.2	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5
117.5°	1406.7	1461.0	1491.5	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1
120°	1334.0	1386.5	1416.1	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7
122.5°	1272.6	1320.8	1350.4	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0
125°	1193.7	1238.7	1262.7	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6
127.5°	1134.2	1173.8	1196.7	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5
130°	1097.4	1133.5	1155.5	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7
132.5°	1058.9	1095.0	1115.1	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7
135°	995.5	1031.7	1051.4	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2
137.5°	930.7	963.6	981.8	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2
140°	890.4	918.9	935.3	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0
142.5°	851.9	875.9	891.5	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6
145°	799.5	818.1	830.2	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7
147.5°	758.6	773.5	780.4	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8
150°	734.9	748.0	752.4	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8
152.5°	714.7	725.2	729.6	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1
155°	687.8	695.4	698.7	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9
157.5°	663.0	669.4	672.4	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8
160°	647.2	652.7	655.0	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0
162.5°	632.4	637.0	637.4	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4
165°	611.1	613.3	613.3	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0
167.5°	590.5	592.5	591.6	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3
170°	578.2	579.4	579.4	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3
172.5°	566.8	568.8	567.1	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4
175°	553.1	554.2	552.0	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9
177.5°	545.0	545.8	543.2	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	15.9	15.7	14.8	16.1	14.6	14.9	14.5	14.5	15.1	15.7	16.5
90°	18.7	17.5	15.4	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1
92.5°	285.9	353.1	358.8	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4
95°	949.5	970.3	791.8	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1
97.5°	1201.5	1036.2	707.1	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0
100°	1262.7	988.9	630.8	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6
102.5°	1226.0	905.7	573.0	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1
105°	1108.3	794.0	516.9	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8
107.5°	988.4	717.1	493.2	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7
110°	919.9	681.2	486.3	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	869.1	660.2	486.3	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1
115°	813.7	637.4	489.6	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2
117.5°	780.6	626.2	496.8	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5
120°	762.2	620.9	503.8	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0
122.5°	746.5	616.6	509.9	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4
125°	725.0	611.1	520.2	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6
127.5°	705.3	608.5	531.8	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8
130°	692.2	606.7	538.9	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2
132.5°	681.6	606.7	546.7	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0
135°	669.2	606.7	557.4	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2
137.5°	658.0	608.0	567.3	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2
140°	652.7	608.9	571.7	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7
142.5°	648.4	609.8	574.3	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9
145°	641.8	608.9	577.2	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4
147.5°	635.0	606.1	578.2	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6
150°	629.7	603.4	578.2	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0
152.5°	623.6	599.9	577.4	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3
155°	613.3	593.6	575.0	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5
157.5°	603.7	587.0	572.1	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0
160°	595.8	582.7	569.5	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6
162.5°	588.8	577.4	566.8	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4
165°	578.2	569.5	562.9	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3
167.5°	568.0	561.8	556.8	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2
170°	561.8	557.4	554.2	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4
172.5°	555.7	552.2	550.6	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0
175°	547.6	546.5	546.5	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2
177.5°	544.1	543.2	543.2	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.2	15.1	13.0	13.9	14.4	14.1	14.5	14.2	14.2	14.4	14.6
90°	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7
92.5°	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1
95°	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4
97.5°	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7
100°	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1
102.5°	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8
105°	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2
107.5°	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6
110°	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5





TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7
115°	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5
117.5°	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1
120°	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7
122.5°	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0
125°	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6
127.5°	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5
130°	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7
132.5°	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7
135°	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2
137.5°	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2
140°	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0
142.5°	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6
145°	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7
147.5°	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8
150°	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8
152.5°	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1
155°	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9
157.5°	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8
160°	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0
162.5°	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4
165°	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0
167.5°	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3
170°	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3
172.5°	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4
175°	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9
177.5°	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	15.4	16.1	15.6	15.0	15.0	15.7	16.2
90°	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333606-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)