

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333609-830

Luminaire Tested: **S125RDIP-S1090D1205U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333609-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8056.6 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333609-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333609-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	36
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	34	30
4	75	64	56	50	69	59	53	47	51	45	41	43	39	35	35	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	32	29	26	23
6	63	51	43	38	58	48	41	35	41	35	31	35	30	27	29	26	23	20
7	59	46	38	33	54	43	36	31	37	32	28	32	27	24	26	23	21	18
8	54	42	34	29	50	39	32	28	34	28	25	29	25	21	24	21	18	16
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15
10	47	35	28	23	44	33	27	22	29	23	20	25	20	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333609-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	2.0
10°-20°	442.7	5.5
20°-30°	642.0	8.0
30°-40°	731.6	9.1
40°-50°	713.2	8.9
50°-60°	600.3	7.5
60°-70°	420.8	5.2
70°-80°	216.3	2.7
80°-90°	57.7	0.7
90°-100°	393.7	4.9
100°-110°	846.4	10.5
110°-120°	794.4	9.9
120°-130°	643.8	8.0
130°-140°	516.6	6.4
140°-150°	389.9	4.8
150°-160°	274.4	3.4
160°-170°	161.8	2.0
170°-180°	52.6	0.7
0°-30°	1243.1	15.4
0°-40°	1974.7	24.5
0°-60°	3288.2	40.8
0°-90°	3983.0	49.4
90°-120°	2034.5	25.3
90°-150°	3584.8	44.5
90°-180°	4074.0	50.6
0°-180°	8056.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	10	18	23	25	5
95°	36	107	970	440	257	38
105°	124	173	794	1563	1451	130
115°	221	267	637	1374	1616	218
125°	307	359	611	1093	1274	272
135°	359	432	607	916	1058	279
145°	418	479	609	758	834	262
155°	478	514	594	671	700	220
165°	521	536	570	604	613	147
175°	542	542	546	553	551	51
180°	543	543	543	543	543	



TEST NUMBER: P333609-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.7	22.2	21.1	20.0	18.9	18.4	18.4	18.6	18.6	18.8	19.0
90°	1.1	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7
92.5°	13.4	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9
95°	36.1	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5
97.5°	60.0	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5
100°	76.6	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7
102.5°	95.1	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0
105°	123.8	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3
107.5°	151.7	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4
110°	171.9	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9



TEST NUMBER: P333609-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	192.1	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1
115°	221.2	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7
117.5°	247.5	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6
120°	265.0	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2
122.5°	283.4	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5
125°	306.6	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0
127.5°	324.8	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3
130°	336.2	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2
132.5°	345.0	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6
135°	359.2	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2
137.5°	377.2	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0
140°	387.7	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7
142.5°	399.9	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4
145°	418.4	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8
147.5°	437.6	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0
150°	449.0	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7
152.5°	461.3	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6
155°	477.5	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3
157.5°	492.0	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7
160°	501.6	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8
162.5°	509.4	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8
165°	521.3	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2
167.5°	529.2	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0
170°	534.4	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8
172.5°	538.0	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7
175°	542.2	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6
177.5°	544.1	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333609-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	19.2	19.4	19.6	20.0	19.8	19.5	19.5	19.3
90°	19.7	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	194.1	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	787.4	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1172.7	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1347.1	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1405.8	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1371.2	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1247.6	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1156.5	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333609-830

CATALOG NUMBER: S125RDIP-S1090D1205U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1084.7	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	994.5	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	936.1	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	904.7	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	881.0	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	846.6	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	811.5	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	789.7	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	767.7	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	739.2	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	715.2	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	702.0	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	690.6	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	675.7	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	661.8	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	653.8	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	645.1	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	631.9	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	618.8	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	610.0	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	600.4	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	587.0	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	574.3	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	567.3	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	559.4	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.0	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)