

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333583-830

Luminaire Tested: **S125RDIP-S1090D365U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333583-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D365U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 365 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5361.0 lumens  
Efficiency: N/A  
Efficacy: 123.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 43.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333583-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333583-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78	74
1	104	99	95	92	98	94	91	88	86	83	80	77	75	74	70	68	67	63
2	95	87	81	76	90	83	77	73	75	71	67	68	65	62	62	59	57	53
3	87	77	69	63	82	73	67	61	67	61	57	61	56	53	55	52	49	46
4	79	68	60	54	75	65	58	52	60	54	49	54	49	45	49	46	42	39
5	73	61	53	47	69	59	51	45	54	47	42	49	44	40	45	40	37	34
6	68	55	47	41	64	53	45	40	48	42	37	44	39	35	41	36	33	30
7	63	50	42	36	59	48	40	35	44	38	33	41	35	31	37	33	29	27
8	58	46	38	32	55	44	36	31	40	34	30	37	32	28	34	30	26	24
9	54	42	34	29	52	40	33	28	37	31	27	34	29	25	32	27	24	22
10	51	39	31	26	48	37	30	26	34	28	24	32	27	23	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333583-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.4	3.0
10°-20°	442.7	8.3
20°-30°	642.0	12.0
30°-40°	731.6	13.6
40°-50°	713.2	13.3
50°-60°	600.3	11.2
60°-70°	420.8	7.8
70°-80°	216.3	4.0
80°-90°	55.6	1.0
90°-100°	16.3	0.3
100°-110°	100.7	1.9
110°-120°	182.6	3.4
120°-130°	234.3	4.4
130°-140°	252.0	4.7
140°-150°	236.5	4.4
150°-160°	191.3	3.6
160°-170°	123.8	2.3
170°-180°	42.7	0.8
0°-30°	1243.1	23.2
0°-40°	1974.7	36.8
0°-60°	3288.2	61.3
0°-90°	3980.9	74.3
90°-120°	299.6	5.6
90°-150°	1022.4	19.1
90°-180°	1380.0	25.7
0°-180°	5361.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	0	3	5	7	8	4
95°	19	17	5	7	7	24
105°	98	99	99	99	99	104
115°	184	186	186	185	183	182
125°	262	264	264	263	262	234
135°	326	328	328	327	325	251
145°	378	379	379	379	377	236
155°	416	415	415	416	414	192
165°	439	438	438	440	437	124
175°	449	448	448	450	447	43
180°	449	449	449	449	449	



TEST NUMBER: P333583-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.5	22.1	20.5	19.0	17.6	16.9	16.7	16.6	16.5	16.3	16.4
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	5.1	4.7	4.3	3.9	3.5	3.5	4.0	4.4	4.9	5.4	5.7
95°	18.9	18.8	18.6	18.3	18.1	16.6	13.8	10.9	8.1	5.4	5.7
97.5°	39.7	40.1	40.4	40.8	41.3	38.6	33.1	27.5	22.0	16.4	14.3
100°	55.6	55.9	56.1	56.3	56.6	56.7	57.1	57.4	57.7	58.0	46.9
102.5°	71.9	72.2	72.5	72.8	73.0	73.2	73.4	73.6	73.8	74.0	71.9
105°	97.9	98.2	98.6	98.9	99.2	99.2	99.2	99.2	99.2	99.2	99.2
107.5°	125.0	125.0	125.0	125.0	125.0	125.1	125.3	125.4	125.5	125.6	125.6
110°	142.6	142.6	142.6	142.6	142.6	142.7	142.8	143.0	143.1	143.3	143.1



TEST NUMBER: P333583-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.1	159.3	159.5	159.7	159.9	159.9	160.0	160.1	160.2	160.3	160.0
115°	183.9	184.3	184.6	185.0	185.4	185.6	185.7	185.8	185.9	185.9	185.6
117.5°	209.5	209.5	209.5	209.5	209.5	209.6	209.9	210.2	210.5	210.8	210.4
120°	225.6	225.5	225.5	225.4	225.3	225.4	225.6	225.7	226.0	226.2	226.1
122.5°	239.7	240.0	240.3	240.5	240.8	241.0	241.1	241.2	241.3	241.4	241.3
125°	261.6	262.0	262.6	263.1	263.6	263.9	263.9	263.9	263.9	263.9	263.5
127.5°	282.4	282.8	283.1	283.5	283.9	284.1	284.0	284.0	283.9	283.9	283.7
130°	295.2	295.6	296.0	296.3	296.7	296.9	297.0	297.0	297.1	297.2	297.0
132.5°	308.0	308.4	308.9	309.2	309.7	309.8	309.7	309.5	309.3	309.2	309.2
135°	326.2	326.6	327.1	327.5	327.9	328.1	327.9	327.8	327.6	327.5	327.3
137.5°	342.9	343.3	343.7	344.0	344.4	344.6	344.4	344.3	344.1	344.0	344.0
140°	353.8	354.0	354.1	354.3	354.4	354.5	354.4	354.3	354.2	354.2	354.3
142.5°	363.7	363.8	363.9	363.9	364.0	364.1	364.3	364.4	364.5	364.6	364.6
145°	378.1	378.3	378.4	378.6	378.7	378.8	378.8	378.8	378.8	378.8	378.9
147.5°	390.8	390.8	390.8	390.7	390.7	390.7	390.8	390.9	391.0	391.1	391.2
150°	398.8	398.7	398.5	398.3	398.2	398.2	398.3	398.5	398.7	398.8	399.0
152.5°	406.5	406.2	405.9	405.6	405.2	405.1	405.3	405.5	405.6	405.8	405.9
155°	416.5	416.0	415.6	415.1	414.7	414.5	414.7	414.8	415.0	415.1	415.4
157.5°	424.1	423.9	423.6	423.3	423.1	422.9	422.9	423.0	423.0	423.0	423.2
160°	429.4	429.0	428.6	428.1	427.7	427.5	427.5	427.6	427.7	427.8	428.1
162.5°	433.8	433.3	432.8	432.3	432.0	431.8	431.9	431.9	432.0	432.1	432.4
165°	439.4	439.0	438.6	438.1	437.7	437.5	437.5	437.6	437.7	437.8	438.2
167.5°	443.7	443.3	442.8	442.3	441.9	441.7	441.8	441.9	442.0	442.0	442.5
170°	446.1	445.6	445.1	444.6	444.0	443.8	443.9	443.9	444.0	444.1	444.7
172.5°	447.7	447.2	446.7	446.2	445.6	445.4	445.5	445.7	445.8	446.0	446.5
175°	449.4	449.0	448.6	448.1	447.7	447.5	447.5	447.6	447.7	447.8	448.4
177.5°	450.3	449.9	449.5	449.2	448.8	448.7	448.7	448.8	448.8	448.9	449.3
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4



TEST NUMBER: P333583-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	16.5	16.6	16.6	16.6	16.4	16.2	16.0	15.8
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	6.0	6.4	6.8	7.1	7.2	7.3	7.4	7.4
95°	6.0	6.4	6.8	7.0	7.0	7.0	7.0	7.0
97.5°	12.3	10.1	8.0	7.0	7.0	7.0	7.0	7.0
100°	35.9	24.9	13.9	8.2	7.9	7.6	7.3	7.0
102.5°	69.7	67.7	65.6	62.0	57.0	52.0	46.9	41.9
105°	99.2	99.2	99.2	99.2	99.2	99.1	99.1	99.0
107.5°	125.7	125.7	125.7	125.6	125.5	125.2	125.0	124.7
110°	142.8	142.6	142.4	142.3	142.4	142.4	142.5	142.6





TEST NUMBER: P333583-830

CATALOG NUMBER: S125RDIP-S1090D365U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.8	159.5	159.2	159.0	158.9	158.8	158.7	158.6
115°	185.3	185.0	184.7	184.4	183.9	183.5	183.0	182.6
117.5°	210.0	209.6	209.2	209.0	208.8	208.6	208.4	208.2
120°	225.9	225.7	225.6	225.4	225.0	224.6	224.2	223.9
122.5°	241.1	241.0	240.8	240.5	240.1	239.7	239.2	238.8
125°	263.3	263.0	262.7	262.4	262.2	262.0	261.7	261.6
127.5°	283.5	283.3	283.2	282.9	282.3	281.7	281.3	280.7
130°	296.7	296.5	296.3	296.0	295.7	295.3	294.9	294.5
132.5°	309.1	309.1	309.0	308.8	308.4	308.0	307.6	307.4
135°	327.3	327.1	326.9	326.6	326.2	325.7	325.3	324.8
137.5°	344.1	344.1	344.1	343.9	343.6	343.2	342.8	342.4
140°	354.5	354.6	354.8	354.6	354.2	353.7	353.3	352.8
142.5°	364.6	364.7	364.7	364.5	364.0	363.5	363.2	362.7
145°	379.0	379.0	379.1	378.9	378.5	378.1	377.6	377.1
147.5°	391.2	391.3	391.4	391.2	390.7	390.1	389.6	389.1
150°	399.1	399.3	399.4	399.2	398.6	398.0	397.4	396.8
152.5°	406.0	406.1	406.3	406.1	405.6	405.1	404.5	404.0
155°	415.6	415.8	416.0	415.8	415.3	414.6	414.1	413.5
157.5°	423.5	423.7	424.0	423.8	423.2	422.5	422.0	421.4
160°	428.4	428.7	429.0	428.9	428.2	427.6	427.1	426.5
162.5°	432.9	433.3	433.8	433.6	432.9	432.3	431.7	431.0
165°	438.7	439.1	439.6	439.5	438.9	438.3	437.7	437.2
167.5°	443.1	443.6	444.1	444.0	443.4	442.7	442.1	441.4
170°	445.3	445.9	446.5	446.5	445.8	445.2	444.4	443.7
172.5°	447.0	447.6	448.1	448.1	447.4	446.7	446.0	445.4
175°	448.9	449.6	450.2	450.2	449.4	448.7	448.1	447.4
177.5°	449.8	450.2	450.5	450.5	450.1	449.6	449.1	448.7
180°	449.4	449.4	449.4	449.4	449.4	449.4	449.4	449.4

(END OF REPORT)