

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333588-830

Luminaire Tested: **S125RDIP-S1090D590U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333588-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D590U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6016.3 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	80	75	88	81	76	72	73	69	65	65	61	59	57	55	53	49
3	86	76	69	63	80	72	66	60	65	59	55	58	54	50	51	48	45	42
4	79	68	60	54	74	64	57	52	58	52	48	52	47	43	46	42	39	36
5	72	61	53	47	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	55	46	41	63	52	45	39	47	41	36	42	37	33	38	34	31	28
7	62	50	41	36	58	47	40	35	43	37	32	38	33	30	35	30	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	2.5
10°-20°	435.5	7.2
20°-30°	690.5	11.5
30°-40°	832.7	13.8
40°-50°	743.6	12.4
50°-60°	570.3	9.5
60°-70°	370.6	6.2
70°-80°	180.2	3.0
80°-90°	44.5	0.7
90°-100°	193.3	3.2
100°-110°	415.5	6.9
110°-120°	390.0	6.5
120°-130°	316.0	5.3
130°-140°	253.6	4.2
140°-150°	191.4	3.2
150°-160°	134.7	2.2
160°-170°	79.4	1.3
170°-180°	25.8	0.4
0°-30°	1274.6	21.2
0°-40°	2107.3	35.0
0°-60°	3421.2	56.9
0°-90°	4016.5	66.8
90°-120°	998.8	16.6
90°-150°	1759.9	29.3
90°-180°	2000.0	33.2
0°-180°	6016.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	12	1	12	1	12	10
95°	126	18	126	18	126	179
105°	712	61	712	61	712	708
115°	794	109	794	109	794	775
125°	625	150	625	150	625	566
135°	519	176	519	176	519	402
145°	410	205	410	205	410	260
155°	344	234	344	234	344	160
165°	301	256	301	256	301	86
175°	270	266	270	266	270	26
180°	267	267	267	267	267	



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	13.7	13.2	12.5	12.5	13.0	13.9	13.2	12.6	12.5	12.4	12.7
90°	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7	9.1	8.6	7.5
92.5°	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3	140.3	173.3	176.2
95°	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5	466.2	476.4	388.7
97.5°	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7	589.8	508.7	347.1
100°	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3	619.9	485.5	309.7
102.5°	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1	601.8	444.6	281.3
105°	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2	544.1	389.8	253.7
107.5°	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5	485.2	352.0	242.1
110°	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8	451.7	334.4	238.7



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5	426.7	324.1	238.7
115°	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1	399.4	312.9	240.3
117.5°	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6	383.2	307.5	243.8
120°	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1	374.2	304.8	247.3
122.5°	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5	366.5	302.7	250.3
125°	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6	355.9	300.0	255.4
127.5°	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4	346.3	298.7	261.1
130°	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7	339.8	297.8	264.6
132.5°	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9	334.6	297.8	268.4
135°	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9	328.5	297.8	273.6
137.5°	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1	323.0	298.5	278.5
140°	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6	320.5	299.0	280.7
142.5°	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0	318.3	299.4	281.9
145°	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8	315.1	299.0	283.3
147.5°	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9	311.7	297.6	283.9
150°	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9	309.2	296.2	283.9
152.5°	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7	306.1	294.5	283.4
155°	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2	301.0	291.4	282.3
157.5°	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8	296.3	288.1	280.9
160°	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4	292.5	286.1	279.6
162.5°	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7	289.1	283.4	278.3
165°	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1	283.9	279.6	276.4
167.5°	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9	278.8	275.8	273.3
170°	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5	275.8	273.6	272.0
172.5°	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7	272.8	271.1	270.3
175°	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4	268.8	268.2	268.2
177.5°	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5	267.1	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	13.1	12.9	13.3	13.1	12.3	14.7	16.0	16.4	15.5	14.7	13.9
90°	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6	1.0	2.2	3.2
92.5°	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6	7.9	12.4	19.1
95°	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7	18.3	22.6	28.5
97.5°	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5	30.1	33.1	39.0
100°	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6	38.7	40.9	46.8
102.5°	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7	47.3	49.0	55.4
105°	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8	60.8	63.4	68.8
107.5°	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6	75.6	78.1	82.6
110°	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5	85.5	87.7	92.5



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3	95.4	97.1	102.0
115°	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6	109.7	111.3	116.1
117.5°	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5	123.1	124.9	129.7
120°	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1	131.8	133.8	138.7
122.5°	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1	140.3	142.0	146.8
125°	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5	151.7	154.3	159.1
127.5°	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5	161.1	164.6	170.7
130°	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0	166.6	171.0	178.0
132.5°	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4	171.4	176.5	184.5
135°	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3	178.5	184.9	193.6
137.5°	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2	186.8	192.8	201.4
140°	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3	191.9	198.4	207.0
142.5°	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3	197.6	203.6	212.2
145°	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4	206.4	211.8	219.3
147.5°	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8	215.5	220.1	227.1
150°	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5	221.5	225.3	232.2
152.5°	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5	227.1	230.5	236.6
155°	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4	234.4	237.6	243.0
157.5°	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5	241.4	244.0	248.6
160°	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3	245.7	247.9	251.7
162.5°	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2	249.6	251.8	255.1
165°	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9	254.9	256.5	259.1
167.5°	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8	259.3	260.2	261.7
170°	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4	261.8	262.4	263.4
172.5°	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1	263.2	263.6	264.8
175°	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2	265.0	265.6	266.2
177.5°	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1	266.3	266.3	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	13.6	13.8	13.4	14.6	13.2	13.9	14.0	13.7	13.8	13.9	13.6
90°	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7	10.2	10.7	11.8
92.5°	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3	69.2	52.0	44.1
95°	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5	304.8	238.7	193.6
97.5°	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7	518.4	454.0	391.2
100°	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3	635.0	579.6	523.7
102.5°	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1	706.3	679.8	642.0
105°	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2	746.8	770.4	764.5
107.5°	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5	710.8	771.6	799.6
110°	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8	670.0	745.7	791.5



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5	629.5	706.2	760.1
115°	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1	571.6	645.2	703.8
117.5°	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6	531.4	594.8	648.7
120°	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1	508.6	567.8	615.1
122.5°	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5	492.3	545.0	589.3
125°	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6	470.4	517.3	555.9
127.5°	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4	449.6	493.2	529.5
130°	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7	435.0	476.9	511.8
132.5°	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9	421.2	459.3	492.9
135°	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9	400.0	434.4	465.1
137.5°	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1	381.1	409.7	435.7
140°	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6	369.9	394.6	417.3
142.5°	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0	360.4	381.7	401.3
145°	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8	348.4	365.0	379.6
147.5°	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9	338.4	351.2	362.1
150°	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9	332.8	343.0	352.7
152.5°	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7	327.3	336.6	344.1
155°	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2	318.9	326.3	332.2
157.5°	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8	310.9	316.7	321.3
160°	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4	304.8	310.2	314.0
162.5°	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7	299.7	304.2	307.6
165°	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1	291.9	295.2	297.8
167.5°	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9	284.5	286.9	288.8
170°	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5	280.1	281.7	282.8
172.5°	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7	276.3	277.4	278.1
175°	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4	270.4	271.5	271.5
177.5°	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5	268.0	268.0	268.0
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	14.0	13.6	13.7	13.7	13.7	13.6	14.0	13.6	13.9	13.8	13.7
90°	11.8	11.8	12.3	12.3	12.3	11.8	11.8	11.8	10.7	10.2	9.7
92.5°	37.2	35.9	35.2	34.3	35.2	35.9	37.2	44.1	52.0	69.2	95.3
95°	155.4	139.2	135.0	126.4	135.0	139.2	155.4	193.6	238.7	304.8	386.5
97.5°	358.0	327.8	312.3	305.4	312.3	327.8	358.0	391.2	454.0	518.4	575.7
100°	486.5	447.9	428.0	419.3	428.0	447.9	486.5	523.7	579.6	635.0	661.3
102.5°	602.3	574.8	553.2	546.7	553.2	574.8	602.3	642.0	679.8	706.3	690.1
105°	747.3	729.6	718.9	712.4	718.9	729.6	747.3	764.5	770.4	746.8	673.2
107.5°	808.3	808.2	804.6	800.3	804.6	808.2	808.3	799.6	771.6	710.8	612.5
110°	815.6	825.9	829.6	829.6	829.6	825.9	815.6	791.5	745.7	670.0	567.8



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	795.4	812.9	822.3	826.1	822.3	812.9	795.4	760.1	706.2	629.5	532.5
115°	745.7	771.6	786.6	793.6	786.6	771.6	745.7	703.8	645.2	571.6	488.1
117.5°	690.6	717.3	732.2	736.5	732.2	717.3	690.6	648.7	594.8	531.4	459.6
120°	654.9	680.7	695.2	699.5	695.2	680.7	654.9	615.1	567.8	508.6	444.1
122.5°	624.7	648.4	662.9	666.8	662.9	648.4	624.7	589.3	545.0	492.3	432.5
125°	586.1	608.1	619.9	625.3	619.9	608.1	586.1	555.9	517.3	470.4	415.6
127.5°	556.8	576.3	587.4	589.8	587.4	576.3	556.8	529.5	493.2	449.6	398.4
130°	538.8	556.5	567.2	570.4	567.2	556.5	538.8	511.8	476.9	435.0	387.7
132.5°	519.8	537.5	547.4	551.1	547.4	537.5	519.8	492.9	459.3	421.2	376.9
135°	488.7	506.4	516.1	519.3	516.1	506.4	488.7	465.1	434.4	400.0	362.9
137.5°	456.9	473.1	481.9	485.5	481.9	473.1	456.9	435.7	409.7	381.1	351.1
140°	437.2	451.1	459.1	461.8	459.1	451.1	437.2	417.3	394.6	369.9	344.6
142.5°	418.2	430.0	437.6	439.9	437.6	430.0	418.2	401.3	381.7	360.4	339.0
145°	392.5	401.6	407.6	409.7	407.6	401.6	392.5	379.6	365.0	348.4	331.8
147.5°	372.4	379.7	383.1	384.1	383.1	379.7	372.4	362.1	351.2	338.4	324.9
150°	360.8	367.2	369.4	369.9	369.4	367.2	360.8	352.7	343.0	332.8	320.9
152.5°	350.9	356.0	358.2	358.7	358.2	356.0	350.9	344.1	336.6	327.3	316.7
155°	337.6	341.4	343.0	343.6	343.0	341.4	337.6	332.2	326.3	318.9	310.2
157.5°	325.5	328.6	330.1	330.0	330.1	328.6	325.5	321.3	316.7	310.9	303.8
160°	317.7	320.5	321.5	320.9	321.5	320.5	317.7	314.0	310.2	304.8	299.4
162.5°	310.5	312.7	312.9	312.8	312.9	312.7	310.5	307.6	304.2	299.7	294.7
165°	300.0	301.0	301.0	301.0	301.0	301.0	300.0	297.8	295.2	291.9	288.1
167.5°	289.9	290.9	290.4	290.3	290.4	290.9	289.9	288.8	286.9	284.5	281.9
170°	283.9	284.5	284.5	283.9	284.5	284.5	283.9	282.8	281.7	280.1	278.5
172.5°	278.3	279.3	278.4	277.9	278.4	279.3	278.3	278.1	277.4	276.3	274.7
175°	271.5	272.0	271.0	270.4	271.0	272.0	271.5	271.5	271.5	270.4	270.4
177.5°	267.5	268.0	266.6	266.6	266.6	268.0	267.5	268.0	268.0	268.0	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	14.0	13.9	13.2	14.6	13.4	13.8	13.6	13.9	14.7	15.5	16.4
90°	9.1	8.6	7.5	7.0	5.9	5.4	4.3	3.2	2.2	1.0	0.6
92.5°	140.3	173.3	176.2	122.7	73.4	44.1	28.4	19.1	12.4	7.9	6.6
95°	466.2	476.4	388.7	240.3	122.1	64.6	40.3	28.5	22.6	18.3	17.7
97.5°	589.8	508.7	347.1	191.8	105.2	67.1	49.7	39.0	33.1	30.1	29.5
100°	619.9	485.5	309.7	174.2	104.3	73.1	57.0	46.8	40.9	38.7	37.6
102.5°	601.8	444.6	281.3	166.9	108.2	80.4	64.8	55.4	49.0	47.3	46.7
105°	544.1	389.8	253.7	164.0	116.1	92.5	77.4	68.8	63.4	60.8	60.8
107.5°	485.2	352.0	242.1	168.9	128.0	105.1	91.5	82.6	78.1	75.6	74.6
110°	451.7	334.4	238.7	173.6	136.6	114.5	100.6	92.5	87.7	85.5	84.5



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	426.7	324.1	238.7	179.6	144.8	123.6	110.0	102.0	97.1	95.4	94.3
115°	399.4	312.9	240.3	188.7	157.5	137.6	124.2	116.1	111.3	109.7	108.6
117.5°	383.2	307.5	243.8	199.1	170.7	151.8	138.8	129.7	124.9	123.1	121.5
120°	374.2	304.8	247.3	205.9	180.1	161.3	147.9	138.7	133.8	131.8	130.1
122.5°	366.5	302.7	250.3	213.7	189.2	170.3	156.9	146.8	142.0	140.3	139.1
125°	355.9	300.0	255.4	224.2	201.0	183.3	169.4	159.1	154.3	151.7	150.5
127.5°	346.3	298.7	261.1	233.8	212.5	195.5	181.5	170.7	164.6	161.1	159.5
130°	339.8	297.8	264.6	240.3	219.9	203.2	189.3	178.0	171.0	166.6	165.0
132.5°	334.6	297.8	268.4	245.9	226.8	210.1	196.1	184.5	176.5	171.4	169.4
135°	328.5	297.8	273.6	253.7	236.0	219.3	204.8	193.6	184.9	178.5	176.3
137.5°	323.0	298.5	278.5	259.6	242.6	227.4	212.4	201.4	192.8	186.8	185.2
140°	320.5	299.0	280.7	263.4	247.3	231.8	217.3	207.0	198.4	191.9	190.3
142.5°	318.3	299.4	281.9	265.6	250.3	235.6	222.0	212.2	203.6	197.6	196.3
145°	315.1	299.0	283.3	268.8	255.4	241.4	229.0	219.3	211.8	206.4	205.4
147.5°	311.7	297.6	283.9	270.8	258.6	246.4	235.4	227.1	220.1	215.5	214.8
150°	309.2	296.2	283.9	272.0	260.8	248.9	239.8	232.2	225.3	221.5	220.5
152.5°	306.1	294.5	283.4	272.9	262.9	251.9	243.6	236.6	230.5	227.1	226.5
155°	301.0	291.4	282.3	273.6	265.0	255.9	248.4	243.0	237.6	234.4	234.4
157.5°	296.3	288.1	280.9	274.2	266.9	259.0	253.4	248.6	244.0	241.4	241.5
160°	292.5	286.1	279.6	274.2	267.8	260.8	255.9	251.7	247.9	245.7	246.3
162.5°	289.1	283.4	278.3	273.8	268.6	262.5	258.5	255.1	251.8	249.6	250.2
165°	283.9	279.6	276.4	273.1	268.8	264.6	261.3	259.1	256.5	254.9	255.9
167.5°	278.8	275.8	273.3	271.8	268.8	265.2	263.3	261.7	260.2	259.3	259.8
170°	275.8	273.6	272.0	271.0	268.8	266.2	264.6	263.4	262.4	261.8	262.4
172.5°	272.8	271.1	270.3	270.1	268.4	266.2	265.4	264.8	263.6	263.2	264.1
175°	268.8	268.2	268.2	268.8	267.8	266.2	266.2	266.2	265.6	265.0	266.2
177.5°	267.1	266.6	266.6	267.5	267.1	266.3	266.3	266.6	266.3	266.3	267.1
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.0	14.7	12.3	13.1	13.3	12.9	13.1	12.7	12.4	12.5	12.6
90°	1.0	2.2	3.2	4.3	5.4	5.9	7.0	7.5	8.6	9.1	9.7
92.5°	7.9	12.4	19.1	28.4	44.1	73.4	122.7	176.2	173.3	140.3	95.3
95°	18.3	22.6	28.5	40.3	64.6	122.1	240.3	388.7	476.4	466.2	386.5
97.5°	30.1	33.1	39.0	49.7	67.1	105.2	191.8	347.1	508.7	589.8	575.7
100°	38.7	40.9	46.8	57.0	73.1	104.3	174.2	309.7	485.5	619.9	661.3
102.5°	47.3	49.0	55.4	64.8	80.4	108.2	166.9	281.3	444.6	601.8	690.1
105°	60.8	63.4	68.8	77.4	92.5	116.1	164.0	253.7	389.8	544.1	673.2
107.5°	75.6	78.1	82.6	91.5	105.1	128.0	168.9	242.1	352.0	485.2	612.5
110°	85.5	87.7	92.5	100.6	114.5	136.6	173.6	238.7	334.4	451.7	567.8



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	95.4	97.1	102.0	110.0	123.6	144.8	179.6	238.7	324.1	426.7	532.5
115°	109.7	111.3	116.1	124.2	137.6	157.5	188.7	240.3	312.9	399.4	488.1
117.5°	123.1	124.9	129.7	138.8	151.8	170.7	199.1	243.8	307.5	383.2	459.6
120°	131.8	133.8	138.7	147.9	161.3	180.1	205.9	247.3	304.8	374.2	444.1
122.5°	140.3	142.0	146.8	156.9	170.3	189.2	213.7	250.3	302.7	366.5	432.5
125°	151.7	154.3	159.1	169.4	183.3	201.0	224.2	255.4	300.0	355.9	415.6
127.5°	161.1	164.6	170.7	181.5	195.5	212.5	233.8	261.1	298.7	346.3	398.4
130°	166.6	171.0	178.0	189.3	203.2	219.9	240.3	264.6	297.8	339.8	387.7
132.5°	171.4	176.5	184.5	196.1	210.1	226.8	245.9	268.4	297.8	334.6	376.9
135°	178.5	184.9	193.6	204.8	219.3	236.0	253.7	273.6	297.8	328.5	362.9
137.5°	186.8	192.8	201.4	212.4	227.4	242.6	259.6	278.5	298.5	323.0	351.1
140°	191.9	198.4	207.0	217.3	231.8	247.3	263.4	280.7	299.0	320.5	344.6
142.5°	197.6	203.6	212.2	222.0	235.6	250.3	265.6	281.9	299.4	318.3	339.0
145°	206.4	211.8	219.3	229.0	241.4	255.4	268.8	283.3	299.0	315.1	331.8
147.5°	215.5	220.1	227.1	235.4	246.4	258.6	270.8	283.9	297.6	311.7	324.9
150°	221.5	225.3	232.2	239.8	248.9	260.8	272.0	283.9	296.2	309.2	320.9
152.5°	227.1	230.5	236.6	243.6	251.9	262.9	272.9	283.4	294.5	306.1	316.7
155°	234.4	237.6	243.0	248.4	255.9	265.0	273.6	282.3	291.4	301.0	310.2
157.5°	241.4	244.0	248.6	253.4	259.0	266.9	274.2	280.9	288.1	296.3	303.8
160°	245.7	247.9	251.7	255.9	260.8	267.8	274.2	279.6	286.1	292.5	299.4
162.5°	249.6	251.8	255.1	258.5	262.5	268.6	273.8	278.3	283.4	289.1	294.7
165°	254.9	256.5	259.1	261.3	264.6	268.8	273.1	276.4	279.6	283.9	288.1
167.5°	259.3	260.2	261.7	263.3	265.2	268.8	271.8	273.3	275.8	278.8	281.9
170°	261.8	262.4	263.4	264.6	266.2	268.8	271.0	272.0	273.6	275.8	278.5
172.5°	263.2	263.6	264.8	265.4	266.2	268.4	270.1	270.3	271.1	272.8	274.7
175°	265.0	265.6	266.2	266.2	266.2	267.8	268.8	268.2	268.2	268.8	270.4
177.5°	266.3	266.3	266.6	266.3	266.3	267.1	267.5	266.6	266.6	267.1	267.5
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6	266.6



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	13.2	13.9	13.0	12.5	12.5	13.2	13.7
90°	10.2	10.7	11.8	11.8	11.8	12.3	12.3
92.5°	69.2	52.0	44.1	37.2	35.9	35.2	34.3
95°	304.8	238.7	193.6	155.4	139.2	135.0	126.4
97.5°	518.4	454.0	391.2	358.0	327.8	312.3	305.4
100°	635.0	579.6	523.7	486.5	447.9	428.0	419.3
102.5°	706.3	679.8	642.0	602.3	574.8	553.2	546.7
105°	746.8	770.4	764.5	747.3	729.6	718.9	712.4
107.5°	710.8	771.6	799.6	808.3	808.2	804.6	800.3
110°	670.0	745.7	791.5	815.6	825.9	829.6	829.6



TEST NUMBER: P333588-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	629.5	706.2	760.1	795.4	812.9	822.3	826.1
115°	571.6	645.2	703.8	745.7	771.6	786.6	793.6
117.5°	531.4	594.8	648.7	690.6	717.3	732.2	736.5
120°	508.6	567.8	615.1	654.9	680.7	695.2	699.5
122.5°	492.3	545.0	589.3	624.7	648.4	662.9	666.8
125°	470.4	517.3	555.9	586.1	608.1	619.9	625.3
127.5°	449.6	493.2	529.5	556.8	576.3	587.4	589.8
130°	435.0	476.9	511.8	538.8	556.5	567.2	570.4
132.5°	421.2	459.3	492.9	519.8	537.5	547.4	551.1
135°	400.0	434.4	465.1	488.7	506.4	516.1	519.3
137.5°	381.1	409.7	435.7	456.9	473.1	481.9	485.5
140°	369.9	394.6	417.3	437.2	451.1	459.1	461.8
142.5°	360.4	381.7	401.3	418.2	430.0	437.6	439.9
145°	348.4	365.0	379.6	392.5	401.6	407.6	409.7
147.5°	338.4	351.2	362.1	372.4	379.7	383.1	384.1
150°	332.8	343.0	352.7	360.8	367.2	369.4	369.9
152.5°	327.3	336.6	344.1	350.9	356.0	358.2	358.7
155°	318.9	326.3	332.2	337.6	341.4	343.0	343.6
157.5°	310.9	316.7	321.3	325.5	328.6	330.1	330.0
160°	304.8	310.2	314.0	317.7	320.5	321.5	320.9
162.5°	299.7	304.2	307.6	310.5	312.7	312.9	312.8
165°	291.9	295.2	297.8	300.0	301.0	301.0	301.0
167.5°	284.5	286.9	288.8	289.9	290.9	290.4	290.3
170°	280.1	281.7	282.8	283.9	284.5	284.5	283.9
172.5°	276.3	277.4	278.1	278.3	279.3	278.4	277.9
175°	270.4	271.5	271.5	271.5	272.0	271.0	270.4
177.5°	268.0	268.0	268.0	267.5	268.0	266.6	266.6
180°	266.6	266.6	266.6	266.6	266.6	266.6	266.6

(END OF REPORT)