

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333590-830

Luminaire Tested: **S125RDIP-S1090D590U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333590-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D590U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5909.5 lumens
Efficiency: N/A
Efficacy: 121.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333590-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333590-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	79	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	54	57	53	50	51	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333590-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	2.7
10°-20°	442.7	7.5
20°-30°	642.0	10.9
30°-40°	731.6	12.4
40°-50°	713.2	12.1
50°-60°	600.3	10.2
60°-70°	420.8	7.1
70°-80°	216.3	3.7
80°-90°	56.1	0.9
90°-100°	46.3	0.8
100°-110°	136.7	2.3
110°-120°	231.5	3.9
120°-130°	304.6	5.2
130°-140°	341.3	5.8
140°-150°	334.5	5.7
150°-160°	281.0	4.8
160°-170°	186.8	3.2
170°-180°	65.4	1.1
0°-30°	1243.1	21.0
0°-40°	1974.7	33.4
0°-60°	3288.2	55.6
0°-90°	3981.4	67.4
90°-120°	414.4	7.0
90°-150°	1394.9	23.6
90°-180°	1928.0	32.6
0°-180°	5909.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	5	9	11	13	5
95°	35	36	41	45	46	37
105°	123	125	128	132	133	131
115°	232	234	235	234	234	229
125°	338	341	342	341	340	303
135°	440	443	444	444	442	339
145°	533	535	537	536	535	333
155°	610	610	610	612	610	281
165°	663	662	662	664	661	187
175°	689	687	687	690	687	65
180°	691	691	691	691	691	



TEST NUMBER: P333590-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.6	22.1	20.7	19.3	17.9	17.2	17.2	17.2	17.1	17.0	17.2
90°	0.6	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2
92.5°	13.0	13.7	14.3	15.0	15.6	16.5	17.5	18.6	19.6	20.6	21.4
95°	35.0	35.2	35.4	35.6	35.9	36.7	37.8	39.0	40.2	41.4	42.2
97.5°	58.1	58.2	58.2	58.3	58.4	59.3	61.0	62.6	64.3	65.9	66.7
100°	75.3	75.3	75.3	75.3	75.3	76.1	77.6	79.2	80.7	82.3	83.3
102.5°	93.8	94.3	94.7	95.2	95.7	96.3	97.1	97.9	98.7	99.4	100.7
105°	122.6	123.2	123.8	124.4	125.0	125.6	126.4	127.1	127.8	128.5	129.2
107.5°	154.4	155.0	155.6	156.2	156.8	157.4	158.0	158.4	159.0	159.6	159.9
110°	176.3	176.9	177.6	178.1	178.8	179.3	179.6	179.9	180.3	180.7	181.1



TEST NUMBER: P333590-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	198.7	199.1	199.3	199.6	200.0	200.4	200.9	201.2	201.7	202.2	202.4
115°	231.8	232.2	232.7	233.2	233.7	234.0	234.2	234.5	234.7	235.0	234.9
117.5°	264.9	265.0	265.3	265.5	265.7	266.0	266.2	266.4	266.6	266.8	266.9
120°	285.5	286.2	286.7	287.3	287.9	288.2	288.4	288.5	288.6	288.7	288.7
122.5°	307.9	308.1	308.3	308.5	308.8	309.0	309.3	309.6	309.9	310.3	310.2
125°	338.2	338.9	339.6	340.4	341.1	341.5	341.6	341.8	341.9	342.0	341.8
127.5°	370.5	370.9	371.3	371.6	372.1	372.4	372.5	372.7	372.8	373.0	372.9
130°	389.8	390.4	391.1	391.6	392.2	392.7	392.9	393.1	393.3	393.6	393.5
132.5°	409.2	410.2	411.1	412.1	413.1	413.6	413.5	413.5	413.4	413.4	413.3
135°	439.8	440.5	441.3	442.0	442.7	443.1	443.3	443.4	443.5	443.6	443.6
137.5°	468.6	469.4	470.0	470.7	471.5	471.9	472.2	472.4	472.7	473.0	473.1
140°	487.1	487.8	488.3	488.9	489.6	490.0	490.4	490.8	491.1	491.4	491.7
142.5°	505.7	506.1	506.6	507.2	507.7	508.1	508.6	509.1	509.5	509.9	510.1
145°	532.8	533.3	533.9	534.3	534.8	535.2	535.6	535.9	536.3	536.6	536.6
147.5°	558.0	558.3	558.6	558.8	559.1	559.3	559.6	560.0	560.2	560.5	560.8
150°	574.8	574.7	574.6	574.5	574.3	574.5	575.0	575.4	575.9	576.4	576.4
152.5°	588.5	588.7	588.9	589.1	589.2	589.4	589.6	589.7	589.9	590.2	590.5
155°	609.7	609.7	609.7	609.7	609.7	609.8	609.9	610.0	610.2	610.3	610.8
157.5°	628.7	628.4	628.1	627.9	627.6	627.5	627.6	627.8	627.9	628.0	628.5
160°	639.9	639.5	639.1	638.8	638.4	638.3	638.4	638.6	638.7	638.8	639.2
162.5°	649.8	649.5	649.2	648.9	648.7	648.6	648.6	648.7	648.7	648.7	649.2
165°	663.0	662.7	662.5	662.2	662.0	661.9	662.0	662.2	662.3	662.4	662.9
167.5°	674.2	673.7	673.2	672.7	672.2	672.0	672.0	672.0	672.0	672.0	672.7
170°	680.1	679.7	679.2	678.7	678.3	678.1	678.1	678.1	678.1	678.1	678.7
172.5°	684.5	684.0	683.5	683.1	682.6	682.3	682.3	682.3	682.3	682.3	683.1
175°	689.3	688.8	688.3	687.9	687.4	687.2	687.2	687.2	687.2	687.2	687.9
177.5°	691.8	691.4	691.1	690.7	690.2	690.0	689.9	689.8	689.8	689.7	690.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0



TEST NUMBER: P333590-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	17.2	17.3	17.4	17.4	17.2	17.2	17.0	16.9
90°	9.8	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	22.2	23.0	23.8	24.3	24.6	24.9	25.1	25.4
95°	43.1	43.9	44.8	45.2	45.5	45.8	46.0	46.3
97.5°	67.5	68.3	69.1	69.6	69.7	69.8	69.9	70.1
100°	84.5	85.5	86.5	87.2	87.5	87.8	87.9	88.2
102.5°	101.8	103.0	104.2	104.9	105.3	105.6	105.9	106.2
105°	130.0	130.6	131.4	132.0	132.2	132.6	133.0	133.4
107.5°	160.3	160.7	161.0	161.2	161.2	161.2	161.1	161.1
110°	181.3	181.7	182.1	182.2	182.1	182.0	181.8	181.7



TEST NUMBER: P333590-830

CATALOG NUMBER: S125RDIP-S1090D590U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	202.6	202.6	202.8	202.8	202.6	202.4	202.2	202.0
115°	234.7	234.6	234.5	234.4	234.2	234.1	234.0	233.9
117.5°	267.0	267.1	267.2	267.0	266.6	266.1	265.6	265.0
120°	288.7	288.7	288.7	288.5	288.0	287.6	287.1	286.6
122.5°	310.1	310.0	309.9	309.6	309.2	308.9	308.5	308.1
125°	341.5	341.3	341.0	340.8	340.7	340.6	340.4	340.4
127.5°	372.7	372.6	372.5	372.3	372.0	371.8	371.6	371.4
130°	393.3	393.2	393.1	392.9	392.7	392.5	392.2	392.0
132.5°	413.1	413.0	412.9	412.6	412.4	412.0	411.7	411.3
135°	443.6	443.6	443.6	443.4	442.9	442.4	442.0	441.5
137.5°	473.3	473.3	473.5	473.3	472.7	472.1	471.6	470.9
140°	491.9	492.2	492.4	492.2	491.6	491.1	490.4	489.8
142.5°	510.2	510.4	510.5	510.3	509.7	509.1	508.5	507.9
145°	536.6	536.6	536.6	536.4	536.1	535.7	535.4	535.0
147.5°	561.1	561.4	561.7	561.4	560.5	559.8	558.9	558.2
150°	576.4	576.4	576.4	576.3	576.1	575.8	575.6	575.3
152.5°	590.8	591.1	591.4	591.3	590.8	590.4	589.9	589.6
155°	611.2	611.7	612.2	612.2	611.5	611.0	610.3	609.7
157.5°	629.0	629.4	629.9	629.8	629.0	628.2	627.5	626.6
160°	639.7	640.2	640.6	640.6	640.1	639.4	638.9	638.3
162.5°	649.8	650.4	651.0	650.9	650.3	649.5	648.8	648.1
165°	663.4	663.8	664.4	664.2	663.5	662.8	662.0	661.4
167.5°	673.4	674.2	674.9	674.9	674.1	673.4	672.6	671.9
170°	679.5	680.1	680.9	680.8	680.0	679.2	678.3	677.5
172.5°	683.8	684.5	685.2	685.2	684.5	683.7	683.0	682.2
175°	688.6	689.3	690.0	689.9	689.2	688.3	687.5	686.6
177.5°	690.8	691.4	691.9	691.9	691.3	690.6	689.8	689.2
180°	691.0	691.0	691.0	691.0	691.0	691.0	691.0	691.0

(END OF REPORT)