

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333593-830

Luminaire Tested: **S125RDIP-S1090D810U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020


Test Information

Test Method: LM-79-08
Report Number: P333593-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6659.8 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	58	56	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48	44
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	42	39	36	33
5	71	60	51	46	66	56	49	44	50	44	39	44	39	36	38	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	31	35	31	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	29	25	30	26	22	27	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.6	2.2
10°-20°	435.5	6.5
20°-30°	690.5	10.4
30°-40°	832.7	12.5
40°-50°	743.6	11.2
50°-60°	570.3	8.6
60°-70°	370.6	5.6
70°-80°	180.2	2.7
80°-90°	45.1	0.7
90°-100°	63.4	1.0
100°-110°	187.3	2.8
110°-120°	317.3	4.8
120°-130°	417.5	6.3
130°-140°	467.9	7.0
140°-150°	458.6	6.9
150°-160°	385.1	5.8
160°-170°	256.0	3.8
170°-180°	89.6	1.3
0°-30°	1274.6	19.1
0°-40°	2107.3	31.6
0°-60°	3421.2	51.4
0°-90°	4017.1	60.3
90°-120°	568.0	8.5
90°-150°	1912.0	28.7
90°-180°	2643.0	39.7
0°-180°	6659.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	18	1	18	1	18	12
95°	63	48	63	48	63	65
105°	183	168	183	168	183	194
115°	321	318	321	318	321	317
125°	467	464	467	464	467	417
135°	605	603	605	603	605	467
145°	733	730	733	730	733	458
155°	836	836	836	836	836	385
165°	906	909	906	909	906	256
175°	941	945	941	945	941	89
180°	947	947	947	947	947	



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	14.7	14.1	13.5	13.4	13.9	14.7	14.0	13.4	13.2	13.0	13.3
90°	17.7	17.2	16.7	16.2	15.7	15.1	14.2	13.4	12.6	11.8	10.7
92.5°	34.8	34.4	34.0	33.7	33.4	32.6	31.6	30.4	29.4	28.3	26.9
95°	63.3	63.1	62.8	62.4	62.1	61.4	60.2	59.0	57.9	56.7	55.1
97.5°	96.1	96.0	95.7	95.5	95.3	94.7	93.6	92.6	91.4	90.4	88.1
100°	120.8	120.6	120.2	119.9	119.6	118.7	117.2	115.7	114.2	112.7	110.7
102.5°	145.6	145.2	144.7	144.3	143.8	142.8	141.2	139.6	138.0	136.4	135.3
105°	182.8	182.3	181.8	181.3	180.8	180.1	179.1	178.1	177.1	176.2	175.1
107.5°	220.8	220.8	220.8	220.9	220.9	220.7	220.2	219.7	219.2	218.8	218.0
110°	249.1	249.3	249.4	249.6	249.8	249.6	249.1	248.6	248.2	247.6	247.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	276.8	277.1	277.4	277.7	278.1	278.1	277.8	277.6	277.4	277.1	276.5
115°	320.7	320.7	320.9	321.1	321.2	321.4	321.6	321.8	321.9	322.1	321.8
117.5°	363.4	364.0	364.7	365.3	366.0	366.3	366.1	366.0	365.8	365.7	365.4
120°	392.9	393.5	394.2	394.8	395.5	395.8	395.8	395.8	395.8	395.8	395.6
122.5°	422.4	422.8	423.4	423.9	424.4	424.7	424.9	425.0	425.1	425.3	424.8
125°	466.6	466.7	466.8	467.0	467.2	467.4	467.8	468.1	468.4	468.7	468.5
127.5°	509.0	509.3	509.6	510.0	510.3	510.6	510.7	510.9	511.0	511.2	511.0
130°	537.2	537.6	537.9	538.3	538.6	538.9	539.0	539.1	539.3	539.5	539.1
132.5°	563.8	564.3	564.8	565.2	565.6	566.0	566.1	566.3	566.5	566.7	566.7
135°	605.1	605.8	606.4	607.1	607.8	608.0	608.0	608.0	608.0	608.0	607.8
137.5°	645.5	646.3	647.1	647.9	648.8	649.0	648.8	648.7	648.5	648.3	647.9
140°	671.5	672.2	673.1	673.9	674.7	675.0	674.6	674.3	674.0	673.6	673.2
142.5°	696.2	697.0	697.9	698.6	699.5	699.7	699.6	699.4	699.2	699.0	698.3
145°	733.3	733.9	734.3	734.8	735.3	735.6	735.6	735.6	735.6	735.6	735.1
147.5°	765.1	766.2	767.2	768.4	769.5	769.9	769.5	769.0	768.6	768.3	767.9
150°	788.6	788.9	789.3	789.6	789.9	790.1	790.1	790.1	790.1	790.1	789.5
152.5°	808.0	808.7	809.3	809.8	810.4	810.5	810.1	809.7	809.4	809.0	808.7
155°	835.8	836.6	837.4	838.2	839.1	839.1	838.5	837.8	837.2	836.5	836.3
157.5°	858.9	860.0	861.1	862.1	863.3	863.5	862.8	862.1	861.5	860.8	860.6
160°	874.9	875.6	876.5	877.3	878.2	878.2	877.5	876.9	876.3	875.6	875.4
162.5°	888.4	889.4	890.3	891.3	892.2	892.3	891.6	890.7	889.9	889.2	889.1
165°	906.5	907.5	908.5	909.5	910.5	910.6	910.0	909.4	908.7	908.0	907.9
167.5°	921.0	922.0	923.0	924.1	925.0	925.1	924.1	923.1	922.1	921.1	921.1
170°	928.7	929.8	930.9	932.1	933.2	933.3	932.4	931.3	930.4	929.3	929.3
172.5°	935.1	936.1	937.2	938.2	939.2	939.2	938.2	937.3	936.2	935.3	935.3
175°	941.2	942.4	943.5	944.6	945.7	945.8	944.9	943.9	942.9	941.9	941.9
177.5°	944.7	945.7	946.6	947.4	948.4	948.5	947.6	946.9	946.1	945.3	945.5
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	13.6	13.4	13.7	13.4	12.6	14.9	16.2	16.4	15.6	14.9	14.1
90°	9.5	8.4	7.2	5.9	4.7	3.4	2.1	0.8	2.1	3.4	4.7
92.5°	25.4	24.0	22.6	21.5	20.5	19.7	18.8	17.8	18.8	19.7	20.5
95°	53.4	51.8	50.2	49.2	48.9	48.5	48.3	47.9	48.3	48.5	48.9
97.5°	85.9	83.6	81.3	80.1	80.0	79.8	79.7	79.6	79.7	79.8	80.0
100°	108.5	106.4	104.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.2
102.5°	134.2	133.1	132.1	131.2	130.5	129.9	129.2	128.6	129.2	129.9	130.5
105°	174.2	173.2	172.2	171.4	170.5	169.7	168.9	168.1	168.9	169.7	170.5
107.5°	217.3	216.5	215.7	215.0	214.1	213.3	212.4	211.7	212.4	213.3	214.1
110°	246.7	246.2	245.7	245.1	244.2	243.4	242.6	241.8	242.6	243.4	244.2



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	275.9	275.2	274.7	274.1	273.7	273.2	272.9	272.4	272.9	273.2	273.7
115°	321.4	321.1	320.7	320.3	319.6	319.0	318.3	317.6	318.3	319.0	319.6
117.5°	365.1	364.9	364.6	364.2	363.9	363.6	363.4	363.1	363.4	363.6	363.9
120°	395.5	395.3	395.1	394.6	393.8	393.0	392.2	391.3	392.2	393.0	393.8
122.5°	424.4	424.0	423.6	423.2	422.9	422.6	422.4	422.0	422.4	422.6	422.9
125°	468.4	468.3	468.1	467.5	466.6	465.5	464.6	463.5	464.6	465.5	466.6
127.5°	510.8	510.6	510.4	510.0	509.4	508.9	508.4	507.8	508.4	508.9	509.4
130°	538.9	538.5	538.2	537.6	536.8	536.0	535.2	534.3	535.2	536.0	536.8
132.5°	566.8	566.8	566.8	566.3	564.9	563.5	562.2	560.9	562.2	563.5	564.9
135°	607.8	607.6	607.4	606.8	605.9	604.8	603.9	602.9	603.9	604.8	605.9
137.5°	647.5	647.2	646.9	646.2	645.3	644.3	643.4	642.4	643.4	644.3	645.3
140°	672.7	672.1	671.7	671.0	670.2	669.4	668.5	667.8	668.5	669.4	670.2
142.5°	697.8	697.1	696.5	695.9	695.1	694.5	693.8	693.1	693.8	694.5	695.1
145°	734.5	734.1	733.6	733.0	732.4	731.7	731.0	730.4	731.0	731.7	732.4
147.5°	767.5	767.1	766.7	766.3	766.0	765.6	765.3	764.9	765.3	765.6	766.0
150°	788.8	788.2	787.5	787.2	787.4	787.6	787.7	787.9	787.7	787.6	787.4
152.5°	808.4	808.1	807.9	807.7	807.5	807.2	807.0	806.7	807.0	807.2	807.5
155°	836.2	836.0	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8	835.8
157.5°	860.5	860.4	860.2	860.3	860.6	861.0	861.4	861.8	861.4	861.0	860.6
160°	875.2	875.1	875.0	875.1	875.6	876.1	876.6	877.0	876.6	876.1	875.6
162.5°	889.1	889.0	889.0	889.2	889.6	889.9	890.2	890.6	890.2	889.9	889.6
165°	907.7	907.5	907.4	907.5	907.8	908.1	908.4	908.8	908.4	908.1	907.8
167.5°	921.1	921.1	921.1	921.4	922.1	922.7	923.4	924.1	923.4	922.7	922.1
170°	929.3	929.3	929.3	929.7	930.4	931.0	931.7	932.4	931.7	931.0	930.4
172.5°	935.3	935.3	935.3	935.6	936.2	936.9	937.5	938.2	937.5	936.9	936.2
175°	941.9	941.9	941.9	942.3	942.9	943.6	944.2	944.9	944.2	943.6	942.9
177.5°	945.6	945.7	945.8	946.1	946.7	947.3	947.7	948.3	947.7	947.3	946.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	13.9	14.1	13.9	15.2	13.9	14.6	14.7	14.4	14.5	14.7	14.3
90°	5.9	7.2	8.4	9.5	10.7	11.8	12.6	13.4	14.2	15.1	15.7
92.5°	21.5	22.6	24.0	25.4	26.9	28.3	29.4	30.4	31.6	32.6	33.4
95°	49.2	50.2	51.8	53.4	55.1	56.7	57.9	59.0	60.2	61.4	62.1
97.5°	80.1	81.3	83.6	85.9	88.1	90.4	91.4	92.6	93.6	94.7	95.3
100°	103.2	104.2	106.4	108.5	110.7	112.7	114.2	115.7	117.2	118.7	119.6
102.5°	131.2	132.1	133.1	134.2	135.3	136.4	138.0	139.6	141.2	142.8	143.8
105°	171.4	172.2	173.2	174.2	175.1	176.2	177.1	178.1	179.1	180.1	180.8
107.5°	215.0	215.7	216.5	217.3	218.0	218.8	219.2	219.7	220.2	220.7	220.9
110°	245.1	245.7	246.2	246.7	247.1	247.6	248.2	248.6	249.1	249.6	249.8



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	274.1	274.7	275.2	275.9	276.5	277.1	277.4	277.6	277.8	278.1	278.1
115°	320.3	320.7	321.1	321.4	321.8	322.1	321.9	321.8	321.6	321.4	321.2
117.5°	364.2	364.6	364.9	365.1	365.4	365.7	365.8	366.0	366.1	366.3	366.0
120°	394.6	395.1	395.3	395.5	395.6	395.8	395.8	395.8	395.8	395.8	395.5
122.5°	423.2	423.6	424.0	424.4	424.8	425.3	425.1	425.0	424.9	424.7	424.4
125°	467.5	468.1	468.3	468.4	468.5	468.7	468.4	468.1	467.8	467.4	467.2
127.5°	510.0	510.4	510.6	510.8	511.0	511.2	511.0	510.9	510.7	510.6	510.3
130°	537.6	538.2	538.5	538.9	539.1	539.5	539.3	539.1	539.0	538.9	538.6
132.5°	566.3	566.8	566.8	566.8	566.7	566.7	566.5	566.3	566.1	566.0	565.6
135°	606.8	607.4	607.6	607.8	607.8	608.0	608.0	608.0	608.0	608.0	607.8
137.5°	646.2	646.9	647.2	647.5	647.9	648.3	648.5	648.7	648.8	649.0	648.8
140°	671.0	671.7	672.1	672.7	673.2	673.6	674.0	674.3	674.6	675.0	674.7
142.5°	695.9	696.5	697.1	697.8	698.3	699.0	699.2	699.4	699.6	699.7	699.5
145°	733.0	733.6	734.1	734.5	735.1	735.6	735.6	735.6	735.6	735.6	735.3
147.5°	766.3	766.7	767.1	767.5	767.9	768.3	768.6	769.0	769.5	769.9	769.5
150°	787.2	787.5	788.2	788.8	789.5	790.1	790.1	790.1	790.1	790.1	789.9
152.5°	807.7	807.9	808.1	808.4	808.7	809.0	809.4	809.7	810.1	810.5	810.4
155°	835.8	835.8	836.0	836.2	836.3	836.5	837.2	837.8	838.5	839.1	839.1
157.5°	860.3	860.2	860.4	860.5	860.6	860.8	861.5	862.1	862.8	863.5	863.3
160°	875.1	875.0	875.1	875.2	875.4	875.6	876.3	876.9	877.5	878.2	878.2
162.5°	889.2	889.0	889.0	889.1	889.1	889.2	889.9	890.7	891.6	892.3	892.2
165°	907.5	907.4	907.5	907.7	907.9	908.0	908.7	909.4	910.0	910.6	910.5
167.5°	921.4	921.1	921.1	921.1	921.1	921.1	922.1	923.1	924.1	925.1	925.0
170°	929.7	929.3	929.3	929.3	929.3	929.3	930.4	931.3	932.4	933.3	933.2
172.5°	935.6	935.3	935.3	935.3	935.3	935.3	936.2	937.3	938.2	939.2	939.2
175°	942.3	941.9	941.9	941.9	941.9	941.9	942.9	943.9	944.9	945.8	945.7
177.5°	946.1	945.8	945.7	945.6	945.5	945.3	946.1	946.9	947.6	948.5	948.4
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	15.0	14.5	14.6	14.7	14.6	14.5	15.0	14.3	14.7	14.5	14.4
90°	16.2	16.7	17.2	17.7	17.2	16.7	16.2	15.7	15.1	14.2	13.4
92.5°	33.7	34.0	34.4	34.8	34.4	34.0	33.7	33.4	32.6	31.6	30.4
95°	62.4	62.8	63.1	63.3	63.1	62.8	62.4	62.1	61.4	60.2	59.0
97.5°	95.5	95.7	96.0	96.1	96.0	95.7	95.5	95.3	94.7	93.6	92.6
100°	119.9	120.2	120.6	120.8	120.6	120.2	119.9	119.6	118.7	117.2	115.7
102.5°	144.3	144.7	145.2	145.6	145.2	144.7	144.3	143.8	142.8	141.2	139.6
105°	181.3	181.8	182.3	182.8	182.3	181.8	181.3	180.8	180.1	179.1	178.1
107.5°	220.9	220.8	220.8	220.8	220.8	220.8	220.9	220.9	220.7	220.2	219.7
110°	249.6	249.4	249.3	249.1	249.3	249.4	249.6	249.8	249.6	249.1	248.6



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	277.7	277.4	277.1	276.8	277.1	277.4	277.7	278.1	278.1	277.8	277.6
115°	321.1	320.9	320.7	320.7	320.7	320.9	321.1	321.2	321.4	321.6	321.8
117.5°	365.3	364.7	364.0	363.4	364.0	364.7	365.3	366.0	366.3	366.1	366.0
120°	394.8	394.2	393.5	392.9	393.5	394.2	394.8	395.5	395.8	395.8	395.8
122.5°	423.9	423.4	422.8	422.4	422.8	423.4	423.9	424.4	424.7	424.9	425.0
125°	467.0	466.8	466.7	466.6	466.7	466.8	467.0	467.2	467.4	467.8	468.1
127.5°	510.0	509.6	509.3	509.0	509.3	509.6	510.0	510.3	510.6	510.7	510.9
130°	538.3	537.9	537.6	537.2	537.6	537.9	538.3	538.6	538.9	539.0	539.1
132.5°	565.2	564.8	564.3	563.8	564.3	564.8	565.2	565.6	566.0	566.1	566.3
135°	607.1	606.4	605.8	605.1	605.8	606.4	607.1	607.8	608.0	608.0	608.0
137.5°	647.9	647.1	646.3	645.5	646.3	647.1	647.9	648.8	649.0	648.8	648.7
140°	673.9	673.1	672.2	671.5	672.2	673.1	673.9	674.7	675.0	674.6	674.3
142.5°	698.6	697.9	697.0	696.2	697.0	697.9	698.6	699.5	699.7	699.6	699.4
145°	734.8	734.3	733.9	733.3	733.9	734.3	734.8	735.3	735.6	735.6	735.6
147.5°	768.4	767.2	766.2	765.1	766.2	767.2	768.4	769.5	769.9	769.5	769.0
150°	789.6	789.3	788.9	788.6	788.9	789.3	789.6	789.9	790.1	790.1	790.1
152.5°	809.8	809.3	808.7	808.0	808.7	809.3	809.8	810.4	810.5	810.1	809.7
155°	838.2	837.4	836.6	835.8	836.6	837.4	838.2	839.1	839.1	838.5	837.8
157.5°	862.1	861.1	860.0	858.9	860.0	861.1	862.1	863.3	863.5	862.8	862.1
160°	877.3	876.5	875.6	874.9	875.6	876.5	877.3	878.2	878.2	877.5	876.9
162.5°	891.3	890.3	889.4	888.4	889.4	890.3	891.3	892.2	892.3	891.6	890.7
165°	909.5	908.5	907.5	906.5	907.5	908.5	909.5	910.5	910.6	910.0	909.4
167.5°	924.1	923.0	922.0	921.0	922.0	923.0	924.1	925.0	925.1	924.1	923.1
170°	932.1	930.9	929.8	928.7	929.8	930.9	932.1	933.2	933.3	932.4	931.3
172.5°	938.2	937.2	936.1	935.1	936.1	937.2	938.2	939.2	939.2	938.2	937.3
175°	944.6	943.5	942.4	941.2	942.4	943.5	944.6	945.7	945.8	944.9	943.9
177.5°	947.4	946.6	945.7	944.7	945.7	946.6	947.4	948.4	948.5	947.6	946.9
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	14.7	14.6	13.9	15.2	13.9	14.1	13.9	14.1	14.9	15.6	16.4
90°	12.6	11.8	10.7	9.5	8.4	7.2	5.9	4.7	3.4	2.1	0.8
92.5°	29.4	28.3	26.9	25.4	24.0	22.6	21.5	20.5	19.7	18.8	17.8
95°	57.9	56.7	55.1	53.4	51.8	50.2	49.2	48.9	48.5	48.3	47.9
97.5°	91.4	90.4	88.1	85.9	83.6	81.3	80.1	80.0	79.8	79.7	79.6
100°	114.2	112.7	110.7	108.5	106.4	104.2	103.2	103.2	103.2	103.2	103.2
102.5°	138.0	136.4	135.3	134.2	133.1	132.1	131.2	130.5	129.9	129.2	128.6
105°	177.1	176.2	175.1	174.2	173.2	172.2	171.4	170.5	169.7	168.9	168.1
107.5°	219.2	218.8	218.0	217.3	216.5	215.7	215.0	214.1	213.3	212.4	211.7
110°	248.2	247.6	247.1	246.7	246.2	245.7	245.1	244.2	243.4	242.6	241.8



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	277.4	277.1	276.5	275.9	275.2	274.7	274.1	273.7	273.2	272.9	272.4
115°	321.9	322.1	321.8	321.4	321.1	320.7	320.3	319.6	319.0	318.3	317.6
117.5°	365.8	365.7	365.4	365.1	364.9	364.6	364.2	363.9	363.6	363.4	363.1
120°	395.8	395.8	395.6	395.5	395.3	395.1	394.6	393.8	393.0	392.2	391.3
122.5°	425.1	425.3	424.8	424.4	424.0	423.6	423.2	422.9	422.6	422.4	422.0
125°	468.4	468.7	468.5	468.4	468.3	468.1	467.5	466.6	465.5	464.6	463.5
127.5°	511.0	511.2	511.0	510.8	510.6	510.4	510.0	509.4	508.9	508.4	507.8
130°	539.3	539.5	539.1	538.9	538.5	538.2	537.6	536.8	536.0	535.2	534.3
132.5°	566.5	566.7	566.7	566.8	566.8	566.8	566.3	564.9	563.5	562.2	560.9
135°	608.0	608.0	607.8	607.8	607.6	607.4	606.8	605.9	604.8	603.9	602.9
137.5°	648.5	648.3	647.9	647.5	647.2	646.9	646.2	645.3	644.3	643.4	642.4
140°	674.0	673.6	673.2	672.7	672.1	671.7	671.0	670.2	669.4	668.5	667.8
142.5°	699.2	699.0	698.3	697.8	697.1	696.5	695.9	695.1	694.5	693.8	693.1
145°	735.6	735.6	735.1	734.5	734.1	733.6	733.0	732.4	731.7	731.0	730.4
147.5°	768.6	768.3	767.9	767.5	767.1	766.7	766.3	766.0	765.6	765.3	764.9
150°	790.1	790.1	789.5	788.8	788.2	787.5	787.2	787.4	787.6	787.7	787.9
152.5°	809.4	809.0	808.7	808.4	808.1	807.9	807.7	807.5	807.2	807.0	806.7
155°	837.2	836.5	836.3	836.2	836.0	835.8	835.8	835.8	835.8	835.8	835.8
157.5°	861.5	860.8	860.6	860.5	860.4	860.2	860.3	860.6	861.0	861.4	861.8
160°	876.3	875.6	875.4	875.2	875.1	875.0	875.1	875.6	876.1	876.6	877.0
162.5°	889.9	889.2	889.1	889.1	889.0	889.0	889.2	889.6	889.9	890.2	890.6
165°	908.7	908.0	907.9	907.7	907.5	907.4	907.5	907.8	908.1	908.4	908.8
167.5°	922.1	921.1	921.1	921.1	921.1	921.1	921.4	922.1	922.7	923.4	924.1
170°	930.4	929.3	929.3	929.3	929.3	929.3	929.7	930.4	931.0	931.7	932.4
172.5°	936.2	935.3	935.3	935.3	935.3	935.3	935.6	936.2	936.9	937.5	938.2
175°	942.9	941.9	941.9	941.9	941.9	941.9	942.3	942.9	943.6	944.2	944.9
177.5°	946.1	945.3	945.5	945.6	945.7	945.8	946.1	946.7	947.3	947.7	948.3
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.2	14.9	12.6	13.4	13.7	13.4	13.6	13.3	13.0	13.2	13.4
90°	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6	13.4
92.5°	18.8	19.7	20.5	21.5	22.6	24.0	25.4	26.9	28.3	29.4	30.4
95°	48.3	48.5	48.9	49.2	50.2	51.8	53.4	55.1	56.7	57.9	59.0
97.5°	79.7	79.8	80.0	80.1	81.3	83.6	85.9	88.1	90.4	91.4	92.6
100°	103.2	103.2	103.2	103.2	104.2	106.4	108.5	110.7	112.7	114.2	115.7
102.5°	129.2	129.9	130.5	131.2	132.1	133.1	134.2	135.3	136.4	138.0	139.6
105°	168.9	169.7	170.5	171.4	172.2	173.2	174.2	175.1	176.2	177.1	178.1
107.5°	212.4	213.3	214.1	215.0	215.7	216.5	217.3	218.0	218.8	219.2	219.7
110°	242.6	243.4	244.2	245.1	245.7	246.2	246.7	247.1	247.6	248.2	248.6



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	272.9	273.2	273.7	274.1	274.7	275.2	275.9	276.5	277.1	277.4	277.6
115°	318.3	319.0	319.6	320.3	320.7	321.1	321.4	321.8	322.1	321.9	321.8
117.5°	363.4	363.6	363.9	364.2	364.6	364.9	365.1	365.4	365.7	365.8	366.0
120°	392.2	393.0	393.8	394.6	395.1	395.3	395.5	395.6	395.8	395.8	395.8
122.5°	422.4	422.6	422.9	423.2	423.6	424.0	424.4	424.8	425.3	425.1	425.0
125°	464.6	465.5	466.6	467.5	468.1	468.3	468.4	468.5	468.7	468.4	468.1
127.5°	508.4	508.9	509.4	510.0	510.4	510.6	510.8	511.0	511.2	511.0	510.9
130°	535.2	536.0	536.8	537.6	538.2	538.5	538.9	539.1	539.5	539.3	539.1
132.5°	562.2	563.5	564.9	566.3	566.8	566.8	566.8	566.7	566.7	566.5	566.3
135°	603.9	604.8	605.9	606.8	607.4	607.6	607.8	607.8	608.0	608.0	608.0
137.5°	643.4	644.3	645.3	646.2	646.9	647.2	647.5	647.9	648.3	648.5	648.7
140°	668.5	669.4	670.2	671.0	671.7	672.1	672.7	673.2	673.6	674.0	674.3
142.5°	693.8	694.5	695.1	695.9	696.5	697.1	697.8	698.3	699.0	699.2	699.4
145°	731.0	731.7	732.4	733.0	733.6	734.1	734.5	735.1	735.6	735.6	735.6
147.5°	765.3	765.6	766.0	766.3	766.7	767.1	767.5	767.9	768.3	768.6	769.0
150°	787.7	787.6	787.4	787.2	787.5	788.2	788.8	789.5	790.1	790.1	790.1
152.5°	807.0	807.2	807.5	807.7	807.9	808.1	808.4	808.7	809.0	809.4	809.7
155°	835.8	835.8	835.8	835.8	835.8	836.0	836.2	836.3	836.5	837.2	837.8
157.5°	861.4	861.0	860.6	860.3	860.2	860.4	860.5	860.6	860.8	861.5	862.1
160°	876.6	876.1	875.6	875.1	875.0	875.1	875.2	875.4	875.6	876.3	876.9
162.5°	890.2	889.9	889.6	889.2	889.0	889.0	889.1	889.1	889.2	889.9	890.7
165°	908.4	908.1	907.8	907.5	907.4	907.5	907.7	907.9	908.0	908.7	909.4
167.5°	923.4	922.7	922.1	921.4	921.1	921.1	921.1	921.1	921.1	922.1	923.1
170°	931.7	931.0	930.4	929.7	929.3	929.3	929.3	929.3	929.3	930.4	931.3
172.5°	937.5	936.9	936.2	935.6	935.3	935.3	935.3	935.3	935.3	936.2	937.3
175°	944.2	943.6	942.9	942.3	941.9	941.9	941.9	941.9	941.9	942.9	943.9
177.5°	947.7	947.3	946.7	946.1	945.8	945.7	945.6	945.5	945.3	946.1	946.9
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	14.0	14.7	13.9	13.4	13.5	14.1	14.7
90°	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	31.6	32.6	33.4	33.7	34.0	34.4	34.8
95°	60.2	61.4	62.1	62.4	62.8	63.1	63.3
97.5°	93.6	94.7	95.3	95.5	95.7	96.0	96.1
100°	117.2	118.7	119.6	119.9	120.2	120.6	120.8
102.5°	141.2	142.8	143.8	144.3	144.7	145.2	145.6
105°	179.1	180.1	180.8	181.3	181.8	182.3	182.8
107.5°	220.2	220.7	220.9	220.9	220.8	220.8	220.8
110°	249.1	249.6	249.8	249.6	249.4	249.3	249.1



TEST NUMBER: P333593-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	277.8	278.1	278.1	277.7	277.4	277.1	276.8
115°	321.6	321.4	321.2	321.1	320.9	320.7	320.7
117.5°	366.1	366.3	366.0	365.3	364.7	364.0	363.4
120°	395.8	395.8	395.5	394.8	394.2	393.5	392.9
122.5°	424.9	424.7	424.4	423.9	423.4	422.8	422.4
125°	467.8	467.4	467.2	467.0	466.8	466.7	466.6
127.5°	510.7	510.6	510.3	510.0	509.6	509.3	509.0
130°	539.0	538.9	538.6	538.3	537.9	537.6	537.2
132.5°	566.1	566.0	565.6	565.2	564.8	564.3	563.8
135°	608.0	608.0	607.8	607.1	606.4	605.8	605.1
137.5°	648.8	649.0	648.8	647.9	647.1	646.3	645.5
140°	674.6	675.0	674.7	673.9	673.1	672.2	671.5
142.5°	699.6	699.7	699.5	698.6	697.9	697.0	696.2
145°	735.6	735.6	735.3	734.8	734.3	733.9	733.3
147.5°	769.5	769.9	769.5	768.4	767.2	766.2	765.1
150°	790.1	790.1	789.9	789.6	789.3	788.9	788.6
152.5°	810.1	810.5	810.4	809.8	809.3	808.7	808.0
155°	838.5	839.1	839.1	838.2	837.4	836.6	835.8
157.5°	862.8	863.5	863.3	862.1	861.1	860.0	858.9
160°	877.5	878.2	878.2	877.3	876.5	875.6	874.9
162.5°	891.6	892.3	892.2	891.3	890.3	889.4	888.4
165°	910.0	910.6	910.5	909.5	908.5	907.5	906.5
167.5°	924.1	925.1	925.0	924.1	923.0	922.0	921.0
170°	932.4	933.3	933.2	932.1	930.9	929.8	928.7
172.5°	938.2	939.2	939.2	938.2	937.2	936.1	935.1
175°	944.9	945.8	945.7	944.6	943.5	942.4	941.2
177.5°	947.6	948.5	948.4	947.4	946.6	945.7	944.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1

(END OF REPORT)