

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333594-830

Luminaire Tested: **S125RDIP-S1090D810U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333594-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D810U830-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6758.2 lumens  
Efficiency: N/A  
Efficacy: 124.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	94	90	87	84	79	76	74	68	66	65	58	57	56	51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37
4	77	66	59	53	72	62	56	50	55	50	45	48	44	40	42	38	36	32
5	71	59	51	45	66	56	49	43	49	44	39	43	39	35	38	34	31	28
6	65	53	45	40	61	50	43	38	45	39	34	39	35	31	34	31	28	25
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	31	28	25	22
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	52	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10008	10008	10008	10008
5°	11514	10022	8851	10022
10°	13208	9971	7810	9971
15°	14266	9868	6942	9868
20°	15731	9750	6410	9750
25°	18206	9592	5947	9592
30°	19812	9426	5646	9426
35°	16712	9234	5367	9234
40°	11671	8887	5127	8887
45°	8658	8419	4892	8419
50°	6903	7932	4691	7932
55°	5860	7328	4513	7328
60°	5062	6788	4224	6788
65°	4511	6203	3636	6203
70°	3964	5682	3316	5682
75°	3429	4921	3112	4921
80°	2600	4139	2600	4139
85°	2164	3253	2453	3253



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.6	2.2
10°-20°	435.5	6.4
20°-30°	690.5	10.2
30°-40°	832.7	12.3
40°-50°	743.6	11.0
50°-60°	570.3	8.4
60°-70°	370.6	5.5
70°-80°	180.2	2.7
80°-90°	45.0	0.7
90°-100°	264.9	3.9
100°-110°	569.6	8.4
110°-120°	534.5	7.9
120°-130°	433.2	6.4
130°-140°	347.7	5.1
140°-150°	262.4	3.9
150°-160°	184.7	2.7
160°-170°	108.8	1.6
170°-180°	35.4	0.5
0°-30°	1274.6	18.9
0°-40°	2107.3	31.2
0°-60°	3421.2	50.6
0°-90°	4017.0	59.4
90°-120°	1369.1	20.3
90°-150°	2412.3	35.7
90°-180°	2741.0	40.6
0°-180°	6758.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1550	1550	1550	1550	1550	
5°	1776	1546	1365	1546	1776	177
15°	2134	1476	1038	1476	2134	611
25°	2555	1346	835	1346	2555	1173
35°	2120	1171	681	1171	2120	1280
45°	948	922	536	922	948	756
55°	520	651	401	651	520	472
65°	295	406	238	406	295	294
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	17	1	17	1	17	13
95°	173	24	173	24	173	245
105°	976	83	976	83	976	971
115°	1088	149	1088	149	1088	1063
125°	857	206	857	206	857	775
135°	712	242	712	242	712	552
145°	562	282	562	282	562	357
155°	471	321	471	321	471	219
165°	413	351	413	351	413	118
175°	371	365	371	365	371	36
180°	366	366	366	366	366	



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1630.1	1629.1	1631.2	1625.5	1626.1	1617.4	1617.4	1610.8	1602.1	1595.5	1592.4
5°	1776.1	1777.4	1774.9	1765.4	1759.0	1749.5	1738.6	1719.6	1703.6	1688.4	1676.3
7.5°	1926.6	1927.4	1919.0	1916.1	1900.1	1888.4	1864.3	1838.3	1815.3	1786.1	1763.7
10°	2014.1	2013.5	2004.5	1997.5	1983.6	1965.8	1942.2	1911.7	1883.0	1851.2	1820.7
12.5°	2065.0	2063.3	2060.5	2052.0	2039.0	2023.3	2003.3	1973.2	1938.0	1903.2	1867.6
15°	2133.7	2129.2	2121.0	2110.2	2091.7	2073.2	2051.0	2024.3	1990.6	1951.1	1918.1
17.5°	2218.7	2218.8	2206.1	2191.0	2166.0	2133.4	2099.0	2056.0	2010.2	1966.8	1931.6
20°	2288.9	2287.0	2274.3	2245.0	2216.4	2175.7	2136.3	2083.4	2027.4	1970.9	1926.9
22.5°	2389.7	2384.7	2371.4	2333.1	2288.7	2236.3	2176.0	2111.4	2043.7	1979.4	1921.8
25°	2554.9	2551.0	2524.9	2480.4	2418.1	2337.2	2258.3	2169.9	2072.7	1988.0	1918.1
27.5°	2667.8	2663.6	2644.3	2607.3	2549.8	2464.7	2358.0	2239.8	2118.3	2001.9	1901.0
30°	2656.7	2666.2	2663.6	2646.5	2603.2	2526.9	2428.3	2295.3	2150.9	2014.1	1893.9
32.5°	2496.8	2505.4	2527.7	2561.5	2564.0	2533.5	2459.8	2337.0	2187.5	2031.9	1888.3
35°	2119.7	2131.2	2174.4	2242.5	2331.6	2405.9	2421.2	2355.0	2220.8	2053.5	1879.9
37.5°	1629.6	1692.1	1728.6	1800.3	1934.9	2071.7	2203.4	2251.9	2194.7	2044.7	1866.2
40°	1384.3	1399.6	1464.4	1545.2	1658.5	1801.0	1988.7	2124.1	2128.6	2024.3	1844.8
42.5°	1184.8	1204.1	1248.7	1313.2	1410.1	1552.7	1746.4	1925.1	2008.0	1968.3	1816.8
45°	947.9	962.5	994.9	1044.6	1119.0	1236.7	1403.4	1610.1	1774.2	1838.5	1741.8
47.5°	778.6	786.6	814.8	852.6	907.7	993.4	1122.5	1301.9	1498.8	1636.8	1623.2
50°	687.0	696.0	717.6	746.2	792.7	865.2	968.3	1117.8	1320.7	1489.2	1523.0
52.5°	615.8	623.2	636.7	663.7	702.1	757.8	841.0	976.3	1158.9	1338.1	1416.1
55°	520.4	525.5	536.3	551.6	582.1	622.2	694.1	787.6	935.2	1115.8	1230.3
57.5°	441.8	444.3	451.2	465.3	486.4	515.7	567.6	646.9	752.7	915.4	1041.8
60°	391.9	394.5	403.3	412.8	429.4	456.1	496.8	552.1	653.9	788.2	916.1
62.5°	352.1	353.7	357.5	367.0	381.5	402.2	434.2	479.4	560.3	678.3	799.0
65°	295.2	295.8	297.1	304.7	313.6	328.9	349.9	381.7	442.8	531.9	638.7
67.5°	240.4	241.4	245.8	248.5	257.8	265.8	278.1	302.5	345.4	405.5	488.6
70°	209.9	209.3	213.8	217.0	220.1	229.7	237.9	257.7	284.4	330.2	399.5
72.5°	181.4	179.7	181.7	182.9	187.0	193.5	201.8	213.9	234.5	266.1	319.1
75°	137.4	138.1	138.1	139.3	142.5	145.1	147.6	153.9	165.4	186.4	215.0
77.5°	96.4	95.4	98.1	98.5	100.4	103.2	105.4	107.9	112.6	121.2	136.0
80°	69.9	69.9	70.6	72.5	71.9	73.1	76.3	78.9	84.6	89.7	94.8
82.5°	53.7	53.2	53.8	54.2	54.1	55.3	56.5	57.0	59.2	61.7	65.2
85°	29.2	29.2	29.9	29.9	30.5	30.5	31.2	31.2	31.2	31.8	32.4
87.5°	14.6	14.0	13.4	13.4	13.9	14.6	14.0	13.4	13.2	13.0	13.3
90°	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3	12.5	11.8	10.3
92.5°	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6	192.4	237.6	241.4
95°	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9	638.9	653.0	532.8
97.5°	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2	808.4	697.3	475.8
100°	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4	849.7	665.5	424.5
102.5°	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9	825.0	609.4	385.6
105°	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7	745.8	534.3	347.9
107.5°	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5	665.1	482.6	332.0
110°	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3	619.1	458.4	327.3



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9	584.8	444.2	327.3
115°	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2	547.5	429.0	329.4
117.5°	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0	525.3	421.4	334.3
120°	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7	512.9	417.8	339.0
122.5°	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9	502.3	414.9	343.1
125°	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7	487.9	411.2	350.1
127.5°	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1	474.6	409.4	357.9
130°	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3	465.8	408.3	362.6
132.5°	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6	458.7	408.3	367.9
135°	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5	450.3	408.3	375.1
137.5°	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3	442.8	409.2	381.7
140°	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4	439.2	409.7	384.7
142.5°	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8	436.3	410.4	386.4
145°	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7	431.9	409.7	388.4
147.5°	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3	427.3	407.8	389.1
150°	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0	423.8	406.0	389.1
152.5°	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0	419.6	403.7	388.5
155°	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3	412.7	399.4	386.9
157.5°	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4	406.2	395.0	385.0
160°	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5	401.0	392.1	383.2
162.5°	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0	396.2	388.5	381.4
165°	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0	389.1	383.2	378.8
167.5°	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4	382.2	378.1	374.7
170°	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7	378.1	375.1	372.9
172.5°	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5	373.9	371.6	370.5
175°	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7	368.4	367.8	367.8
177.5°	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7	366.1	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1592.4	1588.8	1582.2	1576.1	1568.5	1561.9	1557.4	1551.7	1544.6	1536.0	1528.8
5°	1662.9	1648.9	1630.5	1614.6	1594.2	1578.3	1561.8	1545.9	1529.9	1509.6	1491.8
7.5°	1741.1	1712.1	1684.0	1648.7	1616.6	1588.0	1560.5	1532.7	1505.4	1476.5	1448.7
10°	1788.9	1753.9	1715.1	1670.6	1629.8	1591.0	1555.4	1520.4	1483.6	1451.0	1416.1
12.5°	1833.7	1788.5	1744.1	1687.9	1639.0	1591.6	1546.2	1502.6	1463.2	1421.1	1383.6
15°	1874.2	1829.6	1780.0	1711.3	1643.2	1585.9	1532.5	1475.9	1426.9	1379.8	1337.8
17.5°	1889.8	1843.0	1785.5	1719.4	1645.0	1573.0	1504.1	1442.1	1384.4	1329.6	1282.3
20°	1883.7	1838.5	1779.3	1716.4	1636.8	1561.8	1487.3	1418.6	1354.4	1296.5	1246.2
22.5°	1868.9	1822.2	1765.1	1698.6	1623.1	1543.4	1464.0	1390.6	1323.3	1263.4	1208.6
25°	1846.8	1783.2	1724.7	1659.7	1587.9	1509.0	1426.9	1346.1	1274.2	1213.1	1153.4
27.5°	1823.7	1744.4	1669.9	1605.4	1529.5	1459.1	1380.0	1297.1	1221.5	1159.3	1098.0
30°	1802.9	1713.8	1631.7	1558.6	1486.7	1419.9	1344.8	1264.0	1186.5	1122.2	1059.9
32.5°	1776.9	1682.2	1592.0	1507.7	1438.3	1372.1	1304.1	1226.9	1151.3	1085.1	1021.7
35°	1744.4	1623.5	1525.5	1435.8	1358.9	1294.6	1233.5	1171.2	1095.5	1026.8	965.1
37.5°	1701.6	1564.4	1451.0	1353.4	1272.1	1207.7	1159.4	1102.5	1033.4	967.6	910.3
40°	1675.7	1521.7	1397.6	1301.0	1215.7	1147.6	1102.5	1054.1	991.2	929.4	872.1
42.5°	1641.1	1482.5	1343.7	1242.9	1157.2	1091.7	1045.9	1003.7	950.9	892.8	831.4
45°	1573.2	1406.6	1260.8	1152.7	1066.2	1001.9	959.3	921.8	881.7	828.3	774.9
47.5°	1484.9	1327.3	1174.9	1056.8	972.0	912.4	871.0	841.4	812.8	767.3	715.4
50°	1414.2	1262.2	1113.2	998.8	908.4	851.8	813.0	789.5	763.4	722.1	678.8
52.5°	1330.7	1195.0	1049.1	932.1	846.9	793.8	756.5	733.0	711.5	677.8	636.5
55°	1199.2	1080.2	946.6	840.4	762.1	708.7	673.1	650.8	638.1	609.4	577.0
57.5°	1047.4	962.1	844.3	741.9	672.7	619.9	593.8	574.9	560.4	540.3	517.4
60°	941.5	881.7	776.1	678.8	615.2	564.9	541.4	525.5	512.1	494.9	477.1
62.5°	834.2	790.6	698.8	615.2	556.7	514.5	492.5	478.2	462.8	451.2	433.9
65°	690.2	651.4	587.8	522.3	468.3	434.5	418.6	405.9	396.3	383.6	371.6
67.5°	537.0	521.1	477.2	432.1	393.2	363.3	349.5	340.6	329.1	321.5	313.2
70°	442.8	435.2	404.0	374.1	337.8	317.4	304.7	300.9	286.9	279.3	273.5
72.5°	359.3	355.7	337.8	317.1	291.5	273.7	261.9	257.7	248.7	242.6	238.9
75°	246.2	247.5	244.3	230.9	221.4	209.9	199.7	197.2	190.9	185.8	182.6
77.5°	155.7	162.2	162.5	161.8	158.1	151.0	146.8	145.0	138.6	136.8	136.0
80°	106.9	113.9	120.3	119.6	118.3	116.4	113.2	111.3	108.1	106.2	105.0
82.5°	71.3	77.8	83.0	86.5	86.2	84.4	82.2	81.3	80.7	79.3	79.0
85°	33.7	35.0	36.9	41.4	44.5	45.1	44.5	43.9	41.9	42.6	43.3
87.5°	13.7	13.3	13.7	13.4	12.6	14.8	16.1	16.4	15.6	14.8	14.1
90°	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8	1.5	2.9	4.4
92.5°	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0	10.9	17.1	26.2
95°	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3	25.1	30.9	39.0
97.5°	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3	41.3	45.4	53.5
100°	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6	53.1	56.0	64.1
102.5°	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0	64.8	67.2	75.9
105°	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3	83.3	87.0	94.3
107.5°	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2	103.6	107.2	113.2
110°	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7	117.2	120.1	126.8





TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2	130.7	133.1	139.7
115°	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8	150.3	152.6	159.2
117.5°	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5	168.8	171.2	177.8
120°	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3	180.6	183.5	190.1
122.5°	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8	192.4	194.7	201.3
125°	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3	207.8	211.5	218.1
127.5°	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6	220.8	225.6	233.9
130°	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2	228.5	234.3	243.9
132.5°	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1	235.0	242.0	252.8
135°	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8	244.7	253.5	265.3
137.5°	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8	256.0	264.3	276.1
140°	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9	263.1	271.9	283.7
142.5°	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1	270.8	279.0	290.8
145°	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5	283.0	290.4	300.7
147.5°	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5	295.4	301.7	311.3
150°	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2	303.6	308.8	318.4
152.5°	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4	311.3	315.8	324.2
155°	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3	321.3	325.7	333.1
157.5°	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0	330.9	334.4	340.7
160°	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5	336.8	339.8	344.9
162.5°	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8	342.1	345.1	349.6
165°	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8	349.3	351.6	355.2
167.5°	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1	355.3	356.7	358.7
170°	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7	358.9	359.7	361.1
172.5°	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0	360.7	361.4	362.9
175°	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8	363.4	364.1	364.8
177.5°	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1	365.0	365.0	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1523.7	1516.6	1511.6	1501.4	1494.2	1491.2	1485.5	1484.0	1489.6	1485.5	1485.1
5°	1478.5	1460.0	1445.4	1430.7	1414.9	1404.7	1389.4	1386.9	1383.0	1377.2	1376.0
7.5°	1424.1	1400.1	1381.2	1357.1	1336.1	1319.2	1300.0	1291.0	1286.1	1278.7	1268.8
10°	1387.4	1358.9	1333.4	1309.2	1283.2	1262.2	1243.0	1228.4	1218.9	1209.9	1206.2
12.5°	1351.3	1322.2	1289.6	1260.4	1231.2	1207.7	1186.6	1177.0	1166.5	1156.0	1147.2
15°	1295.2	1256.4	1220.8	1187.0	1162.2	1136.8	1116.4	1102.5	1086.6	1082.1	1065.0
17.5°	1235.7	1197.6	1155.9	1120.4	1091.7	1063.7	1041.2	1025.4	1013.4	997.0	989.1
20°	1198.5	1153.4	1112.7	1080.2	1048.4	1015.3	992.4	979.0	967.6	954.2	947.9
22.5°	1158.9	1114.7	1073.0	1034.9	1002.6	970.1	953.8	939.9	926.9	914.5	906.2
25°	1100.5	1056.0	1012.1	972.7	939.0	915.4	896.4	880.4	873.5	861.4	852.4
27.5°	1042.9	995.6	950.1	910.7	884.3	861.0	845.4	832.7	820.1	809.5	801.8
30°	1005.8	957.4	907.8	876.7	848.7	826.3	809.2	797.1	787.6	778.1	772.3
32.5°	968.7	918.8	874.7	841.0	814.5	795.3	777.6	766.1	756.0	745.5	738.7
35°	909.1	858.2	822.6	789.5	763.4	745.6	733.5	717.0	708.7	701.1	694.1
37.5°	853.8	806.4	767.9	738.9	716.1	698.5	682.9	673.9	663.7	656.9	651.0
40°	813.0	769.8	734.8	704.3	687.7	668.0	653.4	641.9	634.2	625.4	619.0
42.5°	776.4	736.1	702.2	674.7	654.1	637.4	623.3	611.9	602.2	595.9	590.5
45°	724.6	684.5	651.4	625.9	606.9	591.0	576.4	570.6	557.9	550.3	547.7
47.5°	671.0	635.2	603.2	579.8	560.2	545.2	531.4	519.7	512.7	505.2	501.1
50°	634.9	600.5	570.6	547.7	528.7	512.1	499.4	491.7	482.2	475.2	470.1
52.5°	598.8	566.9	537.1	515.2	498.6	482.1	467.9	460.2	451.2	446.7	443.2
55°	547.1	513.4	488.0	466.3	449.1	433.9	420.5	412.8	407.2	402.7	401.4
57.5°	488.6	461.8	438.2	418.7	400.9	386.5	374.8	367.6	362.5	361.8	358.1
60°	450.4	426.2	404.6	383.6	368.3	355.0	344.8	336.5	331.4	330.8	329.5
62.5°	412.3	389.1	369.0	350.5	336.8	324.0	314.2	305.0	301.9	298.8	296.0
65°	355.6	334.6	318.1	303.4	288.8	278.0	268.4	262.8	255.7	251.9	245.0
67.5°	300.0	283.7	267.9	255.5	244.0	233.8	225.8	217.4	212.6	209.5	204.4
70°	263.3	250.6	234.8	221.4	212.4	204.2	197.8	188.3	185.1	182.6	180.0
72.5°	228.8	217.5	204.2	193.4	184.5	176.7	169.4	164.9	161.7	159.2	157.7
75°	180.0	169.2	157.8	150.1	143.7	137.4	133.6	130.4	129.1	128.5	125.9
77.5°	132.2	126.5	117.3	111.2	107.0	104.4	101.0	99.3	99.2	96.4	95.6
80°	101.1	97.9	90.3	87.8	84.6	82.1	80.1	77.0	73.8	72.5	70.6
82.5°	75.2	72.0	69.0	64.8	62.2	60.7	58.8	57.6	58.1	56.3	55.3
85°	40.1	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.1	32.4	33.1
87.5°	13.9	14.2	13.9	15.2	13.8	14.6	14.7	14.3	14.5	14.6	14.4
90°	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3	14.0	14.7	16.2
92.5°	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6	94.8	71.4	60.4
95°	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9	417.8	327.3	265.3
97.5°	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2	710.6	622.3	536.2
100°	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4	870.3	794.5	717.8
102.5°	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9	968.3	931.8	880.0
105°	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7	1023.7	1056.1	1048.0
107.5°	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5	974.3	1057.5	1096.0
110°	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3	918.2	1022.2	1084.8



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9	862.8	967.9	1041.8
115°	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2	783.4	884.4	964.7
117.5°	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0	728.4	815.4	889.1
120°	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7	697.2	778.3	843.1
122.5°	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9	674.8	747.0	807.8
125°	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7	644.9	709.0	762.0
127.5°	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1	616.2	676.1	725.8
130°	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3	596.3	653.7	701.6
132.5°	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6	577.3	629.5	675.6
135°	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5	548.3	595.5	637.4
137.5°	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3	522.4	561.6	597.2
140°	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4	507.0	540.9	571.8
142.5°	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8	494.1	523.2	550.1
145°	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7	477.6	500.4	520.3
147.5°	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3	463.8	481.4	496.4
150°	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0	456.2	470.1	483.4
152.5°	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0	448.6	461.4	471.6
155°	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3	437.1	447.3	455.4
157.5°	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4	426.1	434.0	440.5
160°	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5	417.8	425.3	430.4
162.5°	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0	410.8	417.0	421.5
165°	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0	400.2	404.6	408.3
167.5°	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4	389.8	393.2	395.9
170°	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7	384.0	386.2	387.7
172.5°	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5	378.6	380.3	381.2
175°	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7	370.7	372.2	372.2
177.5°	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7	367.3	367.3	367.3
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1484.5	1478.9	1477.4	1479.4	1477.4	1478.9	1484.5	1485.1	1485.5	1489.6	1484.0
5°	1369.7	1363.3	1366.5	1365.2	1366.5	1363.3	1369.7	1376.0	1377.2	1383.0	1386.9
7.5°	1268.7	1260.7	1252.4	1255.0	1252.4	1260.7	1268.7	1268.8	1278.7	1286.1	1291.0
10°	1197.9	1191.6	1187.7	1190.9	1187.7	1191.6	1197.9	1206.2	1209.9	1218.9	1228.4
12.5°	1138.3	1134.5	1131.2	1129.8	1131.2	1134.5	1138.3	1147.2	1156.0	1166.5	1177.0
15°	1057.3	1049.7	1046.5	1038.2	1046.5	1049.7	1057.3	1065.0	1082.1	1086.6	1102.5
17.5°	982.6	980.1	971.8	968.3	971.8	980.1	982.6	989.1	997.0	1013.4	1025.4
20°	938.3	935.8	927.6	932.6	927.6	935.8	938.3	947.9	954.2	967.6	979.0
22.5°	901.7	896.1	893.4	891.9	893.4	896.1	901.7	906.2	914.5	926.9	939.9
25°	849.9	841.6	838.5	834.6	838.5	841.6	849.9	852.4	861.4	873.5	880.4
27.5°	798.2	793.8	789.6	788.6	789.6	793.8	798.2	801.8	809.5	820.1	832.7
30°	764.7	760.3	757.1	757.1	757.1	760.3	764.7	772.3	778.1	787.6	797.1
32.5°	734.6	731.2	728.0	727.5	728.0	731.2	734.6	738.7	745.5	756.0	766.1
35°	690.9	685.8	684.5	680.7	684.5	685.8	690.9	694.1	701.1	708.7	717.0
37.5°	645.5	641.2	641.1	640.7	641.1	641.2	645.5	651.0	656.9	663.7	673.9
40°	616.4	613.2	612.7	608.1	612.7	613.2	616.4	619.0	625.4	634.2	641.9
42.5°	585.4	583.7	581.5	579.7	581.5	583.7	585.4	590.5	595.9	602.2	611.9
45°	543.3	538.9	538.9	535.6	538.9	538.9	543.3	547.7	550.3	557.9	570.6
47.5°	499.7	496.3	496.7	493.4	496.7	496.3	499.7	501.1	505.2	512.7	519.7
50°	470.8	468.8	468.3	466.9	468.3	468.8	470.8	470.1	475.2	482.2	491.7
52.5°	441.8	440.8	443.3	440.5	443.3	440.8	441.8	443.2	446.7	451.2	460.2
55°	402.7	400.8	404.6	400.8	404.6	400.8	402.7	401.4	402.7	407.2	412.8
57.5°	357.8	356.0	359.4	357.5	359.4	356.0	357.8	358.1	361.8	362.5	367.6
60°	328.3	324.4	326.3	327.0	326.3	324.4	328.3	329.5	330.8	331.4	336.5
62.5°	293.1	290.9	292.3	289.4	292.3	290.9	293.1	296.0	298.8	301.9	305.0
65°	243.6	241.8	239.2	237.9	239.2	241.8	243.6	245.0	251.9	255.7	262.8
67.5°	204.7	200.1	200.0	201.0	200.0	200.1	204.7	204.4	209.5	212.6	217.4
70°	176.3	176.3	175.6	175.6	175.6	176.3	176.3	180.0	182.6	185.1	188.3
72.5°	156.4	155.9	154.7	154.2	154.7	155.9	156.4	157.7	159.2	161.7	164.9
75°	125.9	126.6	125.4	124.7	125.4	126.6	125.9	125.9	128.5	129.1	130.4
77.5°	93.0	90.3	91.7	90.3	91.7	90.3	93.0	95.6	96.4	99.2	99.3
80°	70.6	69.9	71.9	69.9	71.9	69.9	70.6	70.6	72.5	73.8	77.0
82.5°	55.9	55.2	56.1	54.7	56.1	55.2	55.9	55.3	56.3	58.1	57.6
85°	33.7	33.1	32.4	33.1	32.4	33.1	33.7	33.1	32.4	33.1	33.7
87.5°	15.0	14.4	14.6	14.6	14.6	14.4	15.0	14.4	14.6	14.5	14.3
90°	16.2	16.2	17.0	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3
92.5°	51.0	49.2	48.2	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6
95°	213.0	190.9	185.0	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9
97.5°	490.7	449.4	428.0	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2
100°	666.9	613.9	586.6	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4
102.5°	825.6	787.8	758.2	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9
105°	1024.4	1000.0	985.3	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7
107.5°	1108.0	1107.8	1103.0	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5
110°	1117.9	1132.0	1137.2	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1090.2	1114.3	1127.1	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9
115°	1022.2	1057.5	1078.2	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2
117.5°	946.6	983.1	1003.6	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0
120°	897.6	933.0	952.9	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7
122.5°	856.4	888.8	908.7	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9
125°	803.3	833.5	849.7	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7
127.5°	763.2	789.9	805.2	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1
130°	738.5	762.8	777.5	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3
132.5°	712.5	736.8	750.4	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6
135°	669.9	694.2	707.5	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5
137.5°	626.3	648.4	660.6	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3
140°	599.2	618.3	629.3	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4
142.5°	573.3	589.5	599.9	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8
145°	538.0	550.5	558.6	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7
147.5°	510.4	520.5	525.2	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3
150°	494.6	503.3	506.3	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0
152.5°	481.0	488.0	491.0	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0
155°	462.8	468.0	470.1	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3
157.5°	446.2	450.4	452.5	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4
160°	435.5	439.2	440.7	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5
162.5°	425.6	428.6	429.0	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0
165°	411.2	412.7	412.7	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0
167.5°	397.4	398.7	398.1	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4
170°	389.1	389.8	389.8	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7
172.5°	381.4	382.8	381.6	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5
175°	372.2	372.9	371.5	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7
177.5°	366.7	367.3	365.5	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1485.5	1491.2	1494.2	1501.4	1511.6	1516.6	1523.7	1528.8	1536.0	1544.6	1551.7
5°	1389.4	1404.7	1414.9	1430.7	1445.4	1460.0	1478.5	1491.8	1509.6	1529.9	1545.9
7.5°	1300.0	1319.2	1336.1	1357.1	1381.2	1400.1	1424.1	1448.7	1476.5	1505.4	1532.7
10°	1243.0	1262.2	1283.2	1309.2	1333.4	1358.9	1387.4	1416.1	1451.0	1483.6	1520.4
12.5°	1186.6	1207.7	1231.2	1260.4	1289.6	1322.2	1351.3	1383.6	1421.1	1463.2	1502.6
15°	1116.4	1136.8	1162.2	1187.0	1220.8	1256.4	1295.2	1337.8	1379.8	1426.9	1475.9
17.5°	1041.2	1063.7	1091.7	1120.4	1155.9	1197.6	1235.7	1282.3	1329.6	1384.4	1442.1
20°	992.4	1015.3	1048.4	1080.2	1112.7	1153.4	1198.5	1246.2	1296.5	1354.4	1418.6
22.5°	953.8	970.1	1002.6	1034.9	1073.0	1114.7	1158.9	1208.6	1263.4	1323.3	1390.6
25°	896.4	915.4	939.0	972.7	1012.1	1056.0	1100.5	1153.4	1213.1	1274.2	1346.1
27.5°	845.4	861.0	884.3	910.7	950.1	995.6	1042.9	1098.0	1159.3	1221.5	1297.1
30°	809.2	826.3	848.7	876.7	907.8	957.4	1005.8	1059.9	1122.2	1186.5	1264.0
32.5°	777.6	795.3	814.5	841.0	874.7	918.8	968.7	1021.7	1085.1	1151.3	1226.9
35°	733.5	745.6	763.4	789.5	822.6	858.2	909.1	965.1	1026.8	1095.5	1171.2
37.5°	682.9	698.5	716.1	738.9	767.9	806.4	853.8	910.3	967.6	1033.4	1102.5
40°	653.4	668.0	687.7	704.3	734.8	769.8	813.0	872.1	929.4	991.2	1054.1
42.5°	623.3	637.4	654.1	674.7	702.2	736.1	776.4	831.4	892.8	950.9	1003.7
45°	576.4	591.0	606.9	625.9	651.4	684.5	724.6	774.9	828.3	881.7	921.8
47.5°	531.4	545.2	560.2	579.8	603.2	635.2	671.0	715.4	767.3	812.8	841.4
50°	499.4	512.1	528.7	547.7	570.6	600.5	634.9	678.8	722.1	763.4	789.5
52.5°	467.9	482.1	498.6	515.2	537.1	566.9	598.8	636.5	677.8	711.5	733.0
55°	420.5	433.9	449.1	466.3	488.0	513.4	547.1	577.0	609.4	638.1	650.8
57.5°	374.8	386.5	400.9	418.7	438.2	461.8	488.6	517.4	540.3	560.4	574.9
60°	344.8	355.0	368.3	383.6	404.6	426.2	450.4	477.1	494.9	512.1	525.5
62.5°	314.2	324.0	336.8	350.5	369.0	389.1	412.3	433.9	451.2	462.8	478.2
65°	268.4	278.0	288.8	303.4	318.1	334.6	355.6	371.6	383.6	396.3	405.9
67.5°	225.8	233.8	244.0	255.5	267.9	283.7	300.0	313.2	321.5	329.1	340.6
70°	197.8	204.2	212.4	221.4	234.8	250.6	263.3	273.5	279.3	286.9	300.9
72.5°	169.4	176.7	184.5	193.4	204.2	217.5	228.8	238.9	242.6	248.7	257.7
75°	133.6	137.4	143.7	150.1	157.8	169.2	180.0	182.6	185.8	190.9	197.2
77.5°	101.0	104.4	107.0	111.2	117.3	126.5	132.2	136.0	136.8	138.6	145.0
80°	80.1	82.1	84.6	87.8	90.3	97.9	101.1	105.0	106.2	108.1	111.3
82.5°	58.8	60.7	62.2	64.8	69.0	72.0	75.2	79.0	79.3	80.7	81.3
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.1	43.3	42.6	41.9	43.9
87.5°	14.7	14.6	13.8	15.2	13.9	14.2	13.9	14.1	14.8	15.6	16.4
90°	12.5	11.8	10.3	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8
92.5°	192.4	237.6	241.4	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0
95°	638.9	653.0	532.8	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3
97.5°	808.4	697.3	475.8	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3
100°	849.7	665.5	424.5	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6
102.5°	825.0	609.4	385.6	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0
105°	745.8	534.3	347.9	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3
107.5°	665.1	482.6	332.0	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2
110°	619.1	458.4	327.3	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	584.8	444.2	327.3	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2
115°	547.5	429.0	329.4	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8
117.5°	525.3	421.4	334.3	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5
120°	512.9	417.8	339.0	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3
122.5°	502.3	414.9	343.1	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8
125°	487.9	411.2	350.1	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3
127.5°	474.6	409.4	357.9	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6
130°	465.8	408.3	362.6	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2
132.5°	458.7	408.3	367.9	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1
135°	450.3	408.3	375.1	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8
137.5°	442.8	409.2	381.7	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8
140°	439.2	409.7	384.7	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9
142.5°	436.3	410.4	386.4	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1
145°	431.9	409.7	388.4	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5
147.5°	427.3	407.8	389.1	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5
150°	423.8	406.0	389.1	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2
152.5°	419.6	403.7	388.5	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4
155°	412.7	399.4	386.9	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3
157.5°	406.2	395.0	385.0	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0
160°	401.0	392.1	383.2	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5
162.5°	396.2	388.5	381.4	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8
165°	389.1	383.2	378.8	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8
167.5°	382.2	378.1	374.7	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1
170°	378.1	375.1	372.9	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7
172.5°	373.9	371.6	370.5	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0
175°	368.4	367.8	367.8	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8
177.5°	366.1	365.5	365.5	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1557.4	1561.9	1568.5	1576.1	1582.2	1588.8	1592.4	1592.4	1595.5	1602.1	1610.8
5°	1561.8	1578.3	1594.2	1614.6	1630.5	1648.9	1662.9	1676.3	1688.4	1703.6	1719.6
7.5°	1560.5	1588.0	1616.6	1648.7	1684.0	1712.1	1741.1	1763.7	1786.1	1815.3	1838.3
10°	1555.4	1591.0	1629.8	1670.6	1715.1	1753.9	1788.9	1820.7	1851.2	1883.0	1911.7
12.5°	1546.2	1591.6	1639.0	1687.9	1744.1	1788.5	1833.7	1867.6	1903.2	1938.0	1973.2
15°	1532.5	1585.9	1643.2	1711.3	1780.0	1829.6	1874.2	1918.1	1951.1	1990.6	2024.3
17.5°	1504.1	1573.0	1645.0	1719.4	1785.5	1843.0	1889.8	1931.6	1966.8	2010.2	2056.0
20°	1487.3	1561.8	1636.8	1716.4	1779.3	1838.5	1883.7	1926.9	1970.9	2027.4	2083.4
22.5°	1464.0	1543.4	1623.1	1698.6	1765.1	1822.2	1868.9	1921.8	1979.4	2043.7	2111.4
25°	1426.9	1509.0	1587.9	1659.7	1724.7	1783.2	1846.8	1918.1	1988.0	2072.7	2169.9
27.5°	1380.0	1459.1	1529.5	1605.4	1669.9	1744.4	1823.7	1901.0	2001.9	2118.3	2239.8
30°	1344.8	1419.9	1486.7	1558.6	1631.7	1713.8	1802.9	1893.9	2014.1	2150.9	2295.3
32.5°	1304.1	1372.1	1438.3	1507.7	1592.0	1682.2	1776.9	1888.3	2031.9	2187.5	2337.0
35°	1233.5	1294.6	1358.9	1435.8	1525.5	1623.5	1744.4	1879.9	2053.5	2220.8	2355.0
37.5°	1159.4	1207.7	1272.1	1353.4	1451.0	1564.4	1701.6	1866.2	2044.7	2194.7	2251.9
40°	1102.5	1147.6	1215.7	1301.0	1397.6	1521.7	1675.7	1844.8	2024.3	2128.6	2124.1
42.5°	1045.9	1091.7	1157.2	1242.9	1343.7	1482.5	1641.1	1816.8	1968.3	2008.0	1925.1
45°	959.3	1001.9	1066.2	1152.7	1260.8	1406.6	1573.2	1741.8	1838.5	1774.2	1610.1
47.5°	871.0	912.4	972.0	1056.8	1174.9	1327.3	1484.9	1623.2	1636.8	1498.8	1301.9
50°	813.0	851.8	908.4	998.8	1113.2	1262.2	1414.2	1523.0	1489.2	1320.7	1117.8
52.5°	756.5	793.8	846.9	932.1	1049.1	1195.0	1330.7	1416.1	1338.1	1158.9	976.3
55°	673.1	708.7	762.1	840.4	946.6	1080.2	1199.2	1230.3	1115.8	935.2	787.6
57.5°	593.8	619.9	672.7	741.9	844.3	962.1	1047.4	1041.8	915.4	752.7	646.9
60°	541.4	564.9	615.2	678.8	776.1	881.7	941.5	916.1	788.2	653.9	552.1
62.5°	492.5	514.5	556.7	615.2	698.8	790.6	834.2	799.0	678.3	560.3	479.4
65°	418.6	434.5	468.3	522.3	587.8	651.4	690.2	638.7	531.9	442.8	381.7
67.5°	349.5	363.3	393.2	432.1	477.2	521.1	537.0	488.6	405.5	345.4	302.5
70°	304.7	317.4	337.8	374.1	404.0	435.2	442.8	399.5	330.2	284.4	257.7
72.5°	261.9	273.7	291.5	317.1	337.8	355.7	359.3	319.1	266.1	234.5	213.9
75°	199.7	209.9	221.4	230.9	244.3	247.5	246.2	215.0	186.4	165.4	153.9
77.5°	146.8	151.0	158.1	161.8	162.5	162.2	155.7	136.0	121.2	112.6	107.9
80°	113.2	116.4	118.3	119.6	120.3	113.9	106.9	94.8	89.7	84.6	78.9
82.5°	82.2	84.4	86.2	86.5	83.0	77.8	71.3	65.2	61.7	59.2	57.0
85°	44.5	45.1	44.5	41.4	36.9	35.0	33.7	32.4	31.8	31.2	31.2
87.5°	16.1	14.8	12.6	13.4	13.7	13.3	13.7	13.3	13.0	13.2	13.4
90°	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3
92.5°	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6
95°	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9
97.5°	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2
100°	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4
102.5°	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9
105°	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7
107.5°	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5
110°	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3





TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9
115°	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2
117.5°	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0
120°	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7
122.5°	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9
125°	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7
127.5°	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1
130°	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3
132.5°	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6
135°	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5
137.5°	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3
140°	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4
142.5°	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8
145°	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7
147.5°	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3
150°	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0
152.5°	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0
155°	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3
157.5°	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4
160°	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5
162.5°	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0
165°	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0
167.5°	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4
170°	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7
172.5°	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5
175°	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7
177.5°	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7	1549.7
2.5°	1617.4	1617.4	1626.1	1625.5	1631.2	1629.1	1630.1
5°	1738.6	1749.5	1759.0	1765.4	1774.9	1777.4	1776.1
7.5°	1864.3	1888.4	1900.1	1916.1	1919.0	1927.4	1926.6
10°	1942.2	1965.8	1983.6	1997.5	2004.5	2013.5	2014.1
12.5°	2003.3	2023.3	2039.0	2052.0	2060.5	2063.3	2065.0
15°	2051.0	2073.2	2091.7	2110.2	2121.0	2129.2	2133.7
17.5°	2099.0	2133.4	2166.0	2191.0	2206.1	2218.8	2218.7
20°	2136.3	2175.7	2216.4	2245.0	2274.3	2287.0	2288.9
22.5°	2176.0	2236.3	2288.7	2333.1	2371.4	2384.7	2389.7
25°	2258.3	2337.2	2418.1	2480.4	2524.9	2551.0	2554.9
27.5°	2358.0	2464.7	2549.8	2607.3	2644.3	2663.6	2667.8
30°	2428.3	2526.9	2603.2	2646.5	2663.6	2666.2	2656.7
32.5°	2459.8	2533.5	2564.0	2561.5	2527.7	2505.4	2496.8
35°	2421.2	2405.9	2331.6	2242.5	2174.4	2131.2	2119.7
37.5°	2203.4	2071.7	1934.9	1800.3	1728.6	1692.1	1629.6
40°	1988.7	1801.0	1658.5	1545.2	1464.4	1399.6	1384.3
42.5°	1746.4	1552.7	1410.1	1313.2	1248.7	1204.1	1184.8
45°	1403.4	1236.7	1119.0	1044.6	994.9	962.5	947.9
47.5°	1122.5	993.4	907.7	852.6	814.8	786.6	778.6
50°	968.3	865.2	792.7	746.2	717.6	696.0	687.0
52.5°	841.0	757.8	702.1	663.7	636.7	623.2	615.8
55°	694.1	622.2	582.1	551.6	536.3	525.5	520.4
57.5°	567.6	515.7	486.4	465.3	451.2	444.3	441.8
60°	496.8	456.1	429.4	412.8	403.3	394.5	391.9
62.5°	434.2	402.2	381.5	367.0	357.5	353.7	352.1
65°	349.9	328.9	313.6	304.7	297.1	295.8	295.2
67.5°	278.1	265.8	257.8	248.5	245.8	241.4	240.4
70°	237.9	229.7	220.1	217.0	213.8	209.3	209.9
72.5°	201.8	193.5	187.0	182.9	181.7	179.7	181.4
75°	147.6	145.1	142.5	139.3	138.1	138.1	137.4
77.5°	105.4	103.2	100.4	98.5	98.1	95.4	96.4
80°	76.3	73.1	71.9	72.5	70.6	69.9	69.9
82.5°	56.5	55.3	54.1	54.2	53.8	53.2	53.7
85°	31.2	30.5	30.5	29.9	29.9	29.2	29.2
87.5°	14.0	14.6	13.9	13.4	13.4	14.0	14.6
90°	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2



TEST NUMBER: P333594-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)