

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333595-830

Luminaire Tested: **S125RDIP-S1090D810U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333595-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7035.5 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333595-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333595-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	95	91	88	92	89	85	82	77	74	72	66	64	62	55	54	53	48
2	91	83	77	72	84	78	73	68	68	63	60	58	55	52	49	47	45	41
3	83	74	66	60	77	69	62	57	60	55	51	51	48	45	44	41	39	35
4	76	65	57	51	71	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	29	26	23
7	60	47	39	34	55	45	37	32	39	33	29	34	30	26	29	26	23	21
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333595-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	2.3
10°-20°	442.7	6.3
20°-30°	642.0	9.1
30°-40°	731.6	10.4
40°-50°	713.2	10.1
50°-60°	600.3	8.5
60°-70°	420.8	6.0
70°-80°	216.3	3.1
80°-90°	56.7	0.8
90°-100°	36.1	0.5
100°-110°	222.7	3.2
110°-120°	403.9	5.7
120°-130°	518.4	7.4
130°-140°	557.5	7.9
140°-150°	523.3	7.4
150°-160°	423.3	6.0
160°-170°	273.8	3.9
170°-180°	94.4	1.3
0°-30°	1243.1	17.7
0°-40°	1974.7	28.1
0°-60°	3288.2	46.7
0°-90°	3982.0	56.6
90°-120°	662.7	9.4
90°-150°	2262.0	32.2
90°-180°	3054.0	43.4
0°-180°	7035.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	7	12	15	18	5
95°	42	38	12	15	16	54
105°	217	219	220	220	219	230
115°	407	410	411	408	404	403
125°	579	584	584	581	579	517
135°	722	726	725	723	719	556
145°	837	838	838	839	834	523
155°	921	917	918	920	915	424
165°	972	968	969	972	967	275
175°	994	990	991	996	990	95
180°	994	994	994	994	994	



TEST NUMBER: P333595-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.6	22.2	20.9	19.6	18.3	17.6	17.6	17.6	17.6	17.6	17.8
90°	0.8	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6
92.5°	11.3	10.5	9.5	8.6	7.7	7.7	8.8	9.8	10.7	11.8	12.6
95°	42.0	41.6	41.0	40.5	40.1	36.7	30.4	24.2	18.0	11.8	12.6
97.5°	87.8	88.6	89.4	90.4	91.2	85.6	73.2	60.9	48.5	36.3	31.7
100°	123.1	123.6	124.0	124.6	125.1	125.6	126.3	127.0	127.6	128.3	103.9
102.5°	159.1	159.7	160.3	160.9	161.6	162.0	162.5	162.9	163.2	163.6	159.0
105°	216.7	217.4	218.0	218.7	219.3	219.6	219.6	219.6	219.6	219.6	219.6
107.5°	276.5	276.5	276.5	276.5	276.5	276.7	277.0	277.4	277.7	278.1	278.1
110°	315.5	315.5	315.5	315.5	315.5	315.7	315.9	316.3	316.6	317.0	316.5



TEST NUMBER: P333595-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.0	352.4	352.8	353.3	353.6	353.9	354.1	354.3	354.5	354.7	354.1
115°	406.9	407.7	408.5	409.3	410.2	410.7	410.9	410.9	411.1	411.3	410.7
117.5°	463.6	463.6	463.5	463.5	463.5	463.8	464.4	465.1	465.7	466.3	465.4
120°	499.0	498.9	498.7	498.5	498.3	498.5	499.0	499.5	500.0	500.5	500.2
122.5°	530.3	530.9	531.5	532.2	532.7	533.2	533.4	533.7	533.9	534.1	533.8
125°	578.6	579.8	580.9	582.1	583.2	583.8	583.8	583.8	583.8	583.8	583.2
127.5°	624.8	625.6	626.4	627.3	628.0	628.4	628.3	628.2	628.1	628.0	627.6
130°	653.1	653.9	654.7	655.5	656.4	656.9	657.0	657.1	657.3	657.5	657.0
132.5°	681.4	682.3	683.2	684.2	685.2	685.5	685.1	684.8	684.4	684.0	683.9
135°	721.6	722.6	723.6	724.6	725.6	725.9	725.6	725.2	724.9	724.6	724.2
137.5°	758.7	759.5	760.3	761.2	762.0	762.3	762.0	761.8	761.5	761.1	761.2
140°	782.8	783.2	783.4	783.8	784.1	784.2	784.0	783.9	783.7	783.5	783.9
142.5°	804.6	804.8	805.0	805.2	805.4	805.6	805.9	806.1	806.3	806.5	806.6
145°	836.6	837.0	837.3	837.6	837.9	838.1	838.1	838.1	838.1	838.1	838.3
147.5°	864.6	864.6	864.5	864.4	864.4	864.4	864.6	864.8	865.1	865.3	865.4
150°	882.3	882.0	881.7	881.4	881.0	881.0	881.4	881.7	882.0	882.3	882.7
152.5°	899.5	898.7	898.0	897.3	896.5	896.4	896.6	897.0	897.3	897.7	898.0
155°	921.4	920.4	919.5	918.4	917.5	917.1	917.5	917.8	918.1	918.4	918.9
157.5°	938.3	937.7	937.2	936.6	935.9	935.7	935.8	935.8	935.8	935.9	936.3
160°	950.2	949.1	948.2	947.2	946.2	945.8	945.9	946.1	946.3	946.4	947.1
162.5°	959.6	958.6	957.6	956.6	955.6	955.3	955.4	955.5	955.7	955.9	956.8
165°	972.2	971.3	970.3	969.3	968.3	967.9	968.1	968.3	968.4	968.6	969.6
167.5°	981.7	980.7	979.7	978.6	977.6	977.2	977.3	977.5	977.7	977.9	979.0
170°	987.0	985.8	984.7	983.5	982.4	981.9	982.0	982.2	982.4	982.6	983.9
172.5°	990.5	989.4	988.3	987.1	985.9	985.5	985.8	986.1	986.4	986.7	987.9
175°	994.4	993.3	992.4	991.5	990.4	990.0	990.1	990.3	990.5	990.7	992.0
177.5°	996.2	995.3	994.6	993.8	993.0	992.7	992.8	992.9	993.1	993.2	994.1
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4



TEST NUMBER: P333595-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	17.9	18.1	18.3	18.3	18.2	18.0	17.9	17.8
90°	13.5	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	13.5	14.2	15.1	15.6	15.8	16.0	16.3	16.5
95°	13.5	14.2	15.1	15.5	15.5	15.5	15.5	15.5
97.5°	27.1	22.4	17.8	15.5	15.5	15.5	15.5	15.5
100°	79.5	55.0	30.6	18.1	17.4	16.8	16.1	15.5
102.5°	154.4	149.8	145.2	137.3	126.1	115.0	103.9	92.7
105°	219.6	219.6	219.6	219.6	219.4	219.2	219.0	219.0
107.5°	278.1	278.1	278.1	278.0	277.5	276.9	276.4	276.0
110°	315.9	315.5	315.0	314.8	315.0	315.2	315.3	315.5



TEST NUMBER: P333595-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	353.5	352.8	352.2	351.8	351.6	351.3	351.1	350.9
115°	410.0	409.3	408.7	407.8	406.9	405.9	404.9	404.0
117.5°	464.6	463.7	462.9	462.2	461.8	461.4	461.0	460.5
120°	499.8	499.5	499.2	498.6	497.8	497.0	496.2	495.3
122.5°	533.5	533.1	532.8	532.2	531.2	530.3	529.3	528.4
125°	582.5	581.8	581.2	580.6	580.1	579.6	579.1	578.6
127.5°	627.3	627.0	626.6	625.8	624.6	623.4	622.2	620.9
130°	656.5	656.0	655.5	654.9	654.0	653.3	652.4	651.6
132.5°	683.8	683.7	683.6	683.2	682.4	681.6	680.7	680.0
135°	724.0	723.6	723.3	722.6	721.6	720.7	719.6	718.7
137.5°	761.3	761.3	761.4	761.0	760.2	759.3	758.5	757.6
140°	784.2	784.6	784.9	784.6	783.5	782.6	781.6	780.6
142.5°	806.7	806.7	806.8	806.3	805.4	804.4	803.4	802.4
145°	838.4	838.6	838.8	838.3	837.4	836.4	835.4	834.4
147.5°	865.6	865.8	866.0	865.5	864.3	863.2	862.0	860.8
150°	883.0	883.4	883.6	883.2	881.8	880.5	879.2	877.9
152.5°	898.3	898.6	899.0	898.5	897.4	896.2	895.0	893.8
155°	919.5	919.9	920.4	920.0	918.7	917.4	916.1	914.7
157.5°	936.9	937.5	937.9	937.5	936.2	934.9	933.6	932.3
160°	947.7	948.4	949.0	948.8	947.4	946.1	944.8	943.5
162.5°	957.7	958.7	959.5	959.3	957.8	956.4	955.0	953.6
165°	970.5	971.5	972.5	972.3	971.0	969.7	968.4	967.0
167.5°	980.2	981.4	982.6	982.4	980.9	979.5	978.0	976.6
170°	985.1	986.5	987.8	987.7	986.3	984.8	983.3	981.8
172.5°	989.0	990.2	991.5	991.3	989.8	988.4	986.8	985.3
175°	993.3	994.6	995.9	995.8	994.4	992.9	991.5	990.0
177.5°	995.0	995.9	996.8	996.8	995.7	994.7	993.6	992.6
180°	994.4	994.4	994.4	994.4	994.4	994.4	994.4	994.4

(END OF REPORT)