

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333596-830

Luminaire Tested: **S125RDIP-S1090D810U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333596-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D810U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6624.8 lumens  
Efficiency: N/A  
Efficacy: 121.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 54.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333596-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333596-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	60
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	84	78	73	85	79	74	69	69	65	61	60	57	54	52	49	47	43
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	46	43	41	37
4	77	66	58	52	71	62	55	49	55	49	45	48	43	40	41	38	35	32
5	71	59	51	45	66	55	48	43	49	43	39	43	38	35	37	34	31	28
6	65	53	45	39	61	50	43	37	44	38	34	39	34	30	34	30	27	25
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22
8	56	44	36	30	52	41	34	29	37	31	27	32	28	24	28	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333596-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.4	2.4
10°-20°	442.7	6.7
20°-30°	642.0	9.7
30°-40°	731.6	11.0
40°-50°	713.2	10.8
50°-60°	600.3	9.1
60°-70°	420.8	6.4
70°-80°	216.3	3.3
80°-90°	56.7	0.9
90°-100°	63.4	1.0
100°-110°	187.3	2.8
110°-120°	317.3	4.8
120°-130°	417.5	6.3
130°-140°	467.9	7.1
140°-150°	458.6	6.9
150°-160°	385.1	5.8
160°-170°	256.0	3.9
170°-180°	89.6	1.4
0°-30°	1243.1	18.8
0°-40°	1974.7	29.8
0°-60°	3288.2	49.6
0°-90°	3982.0	60.1
90°-120°	568.0	8.6
90°-150°	1912.0	28.9
90°-180°	2643.0	39.9
0°-180°	6624.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	7	12	15	18	6
95°	48	50	57	62	63	51
105°	168	172	176	180	183	180
115°	318	320	322	321	321	314
125°	464	468	469	467	467	415
135°	603	607	608	608	605	465
145°	730	733	736	735	733	456
155°	836	836	836	839	836	385
165°	909	907	908	911	906	256
175°	945	942	942	946	941	90
180°	947	947	947	947	947	



TEST NUMBER: P333596-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.6	22.2	20.9	19.6	18.3	17.6	17.6	17.6	17.6	17.6	17.8
90°	0.8	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6
92.5°	17.8	18.8	19.7	20.5	21.5	22.6	24.0	25.4	26.9	28.3	29.4
95°	47.9	48.3	48.5	48.9	49.2	50.2	51.8	53.4	55.1	56.7	57.9
97.5°	79.6	79.7	79.8	80.0	80.1	81.3	83.6	85.9	88.1	90.4	91.4
100°	103.2	103.2	103.2	103.2	103.2	104.2	106.4	108.5	110.7	112.7	114.2
102.5°	128.6	129.2	129.9	130.5	131.2	132.1	133.1	134.2	135.3	136.4	138.0
105°	168.1	168.9	169.7	170.5	171.4	172.2	173.2	174.2	175.1	176.2	177.1
107.5°	211.7	212.4	213.3	214.1	215.0	215.7	216.5	217.3	218.0	218.8	219.2
110°	241.8	242.6	243.4	244.2	245.1	245.7	246.2	246.7	247.1	247.6	248.2



TEST NUMBER: P333596-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.4	272.9	273.2	273.7	274.1	274.7	275.2	275.9	276.5	277.1	277.4
115°	317.6	318.3	319.0	319.6	320.3	320.7	321.1	321.4	321.8	322.1	321.9
117.5°	363.1	363.4	363.6	363.9	364.2	364.6	364.9	365.1	365.4	365.7	365.8
120°	391.3	392.2	393.0	393.8	394.6	395.1	395.3	395.5	395.6	395.8	395.8
122.5°	422.0	422.4	422.6	422.9	423.2	423.6	424.0	424.4	424.8	425.3	425.1
125°	463.5	464.6	465.5	466.6	467.5	468.1	468.3	468.4	468.5	468.7	468.4
127.5°	507.8	508.4	508.9	509.4	510.0	510.4	510.6	510.8	511.0	511.2	511.0
130°	534.3	535.2	536.0	536.8	537.6	538.2	538.5	538.9	539.1	539.5	539.3
132.5°	560.9	562.2	563.5	564.9	566.3	566.8	566.8	566.8	566.7	566.7	566.5
135°	602.9	603.9	604.8	605.9	606.8	607.4	607.6	607.8	607.8	608.0	608.0
137.5°	642.4	643.4	644.3	645.3	646.2	646.9	647.2	647.5	647.9	648.3	648.5
140°	667.8	668.5	669.4	670.2	671.0	671.7	672.1	672.7	673.2	673.6	674.0
142.5°	693.1	693.8	694.5	695.1	695.9	696.5	697.1	697.8	698.3	699.0	699.2
145°	730.4	731.0	731.7	732.4	733.0	733.6	734.1	734.5	735.1	735.6	735.6
147.5°	764.9	765.3	765.6	766.0	766.3	766.7	767.1	767.5	767.9	768.3	768.6
150°	787.9	787.7	787.6	787.4	787.2	787.5	788.2	788.8	789.5	790.1	790.1
152.5°	806.7	807.0	807.2	807.5	807.7	807.9	808.1	808.4	808.7	809.0	809.4
155°	835.8	835.8	835.8	835.8	835.8	835.8	836.0	836.2	836.3	836.5	837.2
157.5°	861.8	861.4	861.0	860.6	860.3	860.2	860.4	860.5	860.6	860.8	861.5
160°	877.0	876.6	876.1	875.6	875.1	875.0	875.1	875.2	875.4	875.6	876.3
162.5°	890.6	890.2	889.9	889.6	889.2	889.0	889.0	889.1	889.1	889.2	889.9
165°	908.8	908.4	908.1	907.8	907.5	907.4	907.5	907.7	907.9	908.0	908.7
167.5°	924.1	923.4	922.7	922.1	921.4	921.1	921.1	921.1	921.1	921.1	922.1
170°	932.4	931.7	931.0	930.4	929.7	929.3	929.3	929.3	929.3	929.3	930.4
172.5°	938.2	937.5	936.9	936.2	935.6	935.3	935.3	935.3	935.3	935.3	936.2
175°	944.9	944.2	943.6	942.9	942.3	941.9	941.9	941.9	941.9	941.9	942.9
177.5°	948.3	947.7	947.3	946.7	946.1	945.8	945.7	945.6	945.5	945.3	946.1
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333596-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	17.9	18.1	18.3	18.3	18.2	18.0	17.9	17.8
90°	13.4	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	30.4	31.6	32.6	33.4	33.7	34.0	34.4	34.8
95°	59.0	60.2	61.4	62.1	62.4	62.8	63.1	63.3
97.5°	92.6	93.6	94.7	95.3	95.5	95.7	96.0	96.1
100°	115.7	117.2	118.7	119.6	119.9	120.2	120.6	120.8
102.5°	139.6	141.2	142.8	143.8	144.3	144.7	145.2	145.6
105°	178.1	179.1	180.1	180.8	181.3	181.8	182.3	182.8
107.5°	219.7	220.2	220.7	220.9	220.9	220.8	220.8	220.8
110°	248.6	249.1	249.6	249.8	249.6	249.4	249.3	249.1





TEST NUMBER: P333596-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	277.6	277.8	278.1	278.1	277.7	277.4	277.1	276.8
115°	321.8	321.6	321.4	321.2	321.1	320.9	320.7	320.7
117.5°	366.0	366.1	366.3	366.0	365.3	364.7	364.0	363.4
120°	395.8	395.8	395.8	395.5	394.8	394.2	393.5	392.9
122.5°	425.0	424.9	424.7	424.4	423.9	423.4	422.8	422.4
125°	468.1	467.8	467.4	467.2	467.0	466.8	466.7	466.6
127.5°	510.9	510.7	510.6	510.3	510.0	509.6	509.3	509.0
130°	539.1	539.0	538.9	538.6	538.3	537.9	537.6	537.2
132.5°	566.3	566.1	566.0	565.6	565.2	564.8	564.3	563.8
135°	608.0	608.0	608.0	607.8	607.1	606.4	605.8	605.1
137.5°	648.7	648.8	649.0	648.8	647.9	647.1	646.3	645.5
140°	674.3	674.6	675.0	674.7	673.9	673.1	672.2	671.5
142.5°	699.4	699.6	699.7	699.5	698.6	697.9	697.0	696.2
145°	735.6	735.6	735.6	735.3	734.8	734.3	733.9	733.3
147.5°	769.0	769.5	769.9	769.5	768.4	767.2	766.2	765.1
150°	790.1	790.1	790.1	789.9	789.6	789.3	788.9	788.6
152.5°	809.7	810.1	810.5	810.4	809.8	809.3	808.7	808.0
155°	837.8	838.5	839.1	839.1	838.2	837.4	836.6	835.8
157.5°	862.1	862.8	863.5	863.3	862.1	861.1	860.0	858.9
160°	876.9	877.5	878.2	878.2	877.3	876.5	875.6	874.9
162.5°	890.7	891.6	892.3	892.2	891.3	890.3	889.4	888.4
165°	909.4	910.0	910.6	910.5	909.5	908.5	907.5	906.5
167.5°	923.1	924.1	925.1	925.0	924.1	923.0	922.0	921.0
170°	931.3	932.4	933.3	933.2	932.1	930.9	929.8	928.7
172.5°	937.3	938.2	939.2	939.2	938.2	937.2	936.1	935.1
175°	943.9	944.9	945.8	945.7	944.6	943.5	942.4	941.2
177.5°	946.9	947.6	948.5	948.4	947.4	946.6	945.7	944.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1

(END OF REPORT)