

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333597-830

Luminaire Tested: **S125RDIP-S1090D810U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333597-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D810U830-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6723.2 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333597-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333597-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	50
2	91	84	78	73	85	79	73	69	69	65	61	59	56	54	51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	45	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24	22
8	56	43	36	30	52	41	34	29	36	31	27	32	27	24	28	24	22	19
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	17
10	49	37	29	24	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333597-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	2.4
10°-20°	442.7	6.6
20°-30°	642.0	9.5
30°-40°	731.6	10.9
40°-50°	713.2	10.6
50°-60°	600.3	8.9
60°-70°	420.8	6.3
70°-80°	216.3	3.2
80°-90°	56.7	0.8
90°-100°	264.9	3.9
100°-110°	569.6	8.5
110°-120°	534.5	8.0
120°-130°	433.2	6.4
130°-140°	347.7	5.2
140°-150°	262.4	3.9
150°-160°	184.7	2.7
160°-170°	108.8	1.6
170°-180°	35.4	0.5
0°-30°	1243.1	18.5
0°-40°	1974.7	29.4
0°-60°	3288.2	48.9
0°-90°	3982.0	59.2
90°-120°	1369.1	20.4
90°-150°	2412.3	35.9
90°-180°	2741.0	40.8
0°-180°	6723.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	7	12	15	17	5
95°	24	72	653	296	173	26
105°	83	116	534	1052	976	88
115°	149	179	429	925	1088	146
125°	206	242	411	736	857	183
135°	242	291	408	616	712	188
145°	282	322	410	510	562	176
155°	321	346	399	451	471	148
165°	351	360	383	406	413	99
175°	365	365	368	372	371	35
180°	366	366	366	366	366	



TEST NUMBER: P333597-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.6	22.1	20.8	19.5	18.3	17.6	17.5	17.6	17.5	17.6	17.8
90°	0.8	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5
92.5°	9.0	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4
95°	24.3	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9
97.5°	40.3	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4
100°	51.6	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7
102.5°	64.0	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0
105°	83.3	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8
107.5°	102.2	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1
110°	115.7	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1



TEST NUMBER: P333597-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.2	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8
115°	148.8	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5
117.5°	166.5	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3
120°	178.3	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9
122.5°	190.8	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3
125°	206.3	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9
127.5°	218.6	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6
130°	226.2	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8
132.5°	232.1	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7
135°	241.8	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3
137.5°	253.8	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8
140°	260.9	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2
142.5°	269.1	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3
145°	281.5	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9
147.5°	294.5	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3
150°	302.2	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8
152.5°	310.4	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6
155°	321.3	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7
157.5°	331.0	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2
160°	337.5	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0
162.5°	342.8	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2
165°	350.8	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1
167.5°	356.1	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2
170°	359.7	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1
172.5°	362.0	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9
175°	364.8	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4
177.5°	366.1	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333597-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	17.9	18.1	18.2	18.4	18.2	17.9	17.9	17.6
90°	13.3	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	130.6	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	529.9	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	789.2	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	906.4	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	945.9	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	922.7	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	839.5	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	778.3	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2



TEST NUMBER: P333597-830

CATALOG NUMBER: S125RDIP-S1090D810U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	729.9	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	669.2	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	630.0	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	608.7	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	592.9	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	569.7	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	546.1	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	531.3	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	516.6	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	497.5	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	481.3	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	472.4	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	464.8	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	454.7	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	445.3	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	440.0	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	434.0	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	425.3	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	416.4	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	410.5	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	404.0	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	395.0	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	386.4	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	381.7	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	376.5	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	366.7	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)