

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333630-830

Luminaire Tested: **S125RDIP-S1270D1035U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333630-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8139.4 lumens
Efficiency: N/A
Efficacy: 121.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	61	78	70	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	50	54	49	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	43	49	43	39	42	38	34	36	33	30	27
6	65	53	45	39	60	50	43	37	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	34	29	36	31	27	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.6	2.1
10°-20°	503.0	6.2
20°-30°	797.5	9.8
30°-40°	961.7	11.8
40°-50°	858.8	10.6
50°-60°	658.6	8.1
60°-70°	428.0	5.3
70°-80°	208.1	2.6
80°-90°	52.3	0.6
90°-100°	338.3	4.2
100°-110°	727.2	8.9
110°-120°	682.5	8.4
120°-130°	553.1	6.8
130°-140°	443.9	5.5
140°-150°	334.9	4.1
150°-160°	235.8	2.9
160°-170°	139.0	1.7
170°-180°	45.2	0.6
0°-30°	1472.1	18.1
0°-40°	2433.8	29.9
0°-60°	3951.3	48.5
0°-90°	4639.6	57.0
90°-120°	1747.9	21.5
90°-150°	3079.8	37.8
90°-180°	3500.0	43.0
0°-180°	8139.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	39
90°	22	1	22	1	22	17
95°	221	31	221	31	221	313
105°	1247	106	1247	106	1247	1239
115°	1389	190	1389	190	1389	1357
125°	1094	263	1094	263	1094	990
135°	909	309	909	309	909	704
145°	717	359	717	359	717	456
155°	601	410	601	410	601	280
165°	527	448	527	448	527	151
175°	473	466	473	466	473	46
180°	467	467	467	467	467	



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	17.2	16.7	15.9	15.9	16.5	17.2	16.5	15.7	15.6	15.4	15.6
90°	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0	16.0	15.1	13.2
92.5°	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7	245.5	303.3	308.2
95°	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6	815.8	833.7	680.3
97.5°	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6	1032.2	890.3	607.5
100°	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3	1084.9	849.6	542.0
102.5°	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8	1053.3	778.2	492.3
105°	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0	952.3	682.1	444.1
107.5°	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9	849.0	616.1	423.8
110°	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6	790.3	585.2	417.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9	746.7	567.2	417.7
115°	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3	699.1	547.6	420.6
117.5°	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3	670.7	538.0	426.8
120°	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2	654.9	533.5	432.8
122.5°	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9	641.3	529.7	438.1
125°	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4	622.9	525.0	447.0
127.5°	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2	606.0	522.7	456.9
130°	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4	594.7	521.2	463.0
132.5°	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6	585.6	521.2	469.7
135°	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1	574.9	521.2	478.9
137.5°	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4	565.3	522.4	487.4
140°	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1	560.8	523.1	491.2
142.5°	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3	557.0	523.9	493.4
145°	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5	551.4	523.1	495.9
147.5°	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5	545.5	520.7	496.8
150°	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8	541.0	518.4	496.8
152.5°	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2	535.7	515.5	496.1
155°	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9	526.9	510.0	494.0
157.5°	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6	518.6	504.4	491.5
160°	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1	511.9	500.6	489.3
162.5°	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9	505.9	496.1	487.0
165°	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4	496.8	489.3	483.6
167.5°	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4	488.0	482.7	478.3
170°	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4	482.7	478.9	476.1
172.5°	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6	477.4	474.4	473.1
175°	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3	470.4	469.5	469.5
177.5°	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2	467.4	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	15.9	15.6	16.0	15.6	14.6	17.2	18.6	19.0	18.0	17.2	16.4
90°	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9	1.9	3.8	5.7
92.5°	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5	13.9	21.9	33.5
95°	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0	32.0	39.5	49.9
97.5°	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6	52.7	58.0	68.3
100°	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9	67.8	71.5	81.8
102.5°	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7	82.8	85.8	96.9
105°	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3	106.3	111.0	120.5
107.5°	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4	132.3	136.8	144.5
110°	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7	149.6	153.4	161.8



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0	166.9	169.9	178.4
115°	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1	191.9	194.7	203.2
117.5°	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6	215.5	218.5	227.0
120°	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7	230.5	234.3	242.8
122.5°	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6	245.5	248.5	257.0
125°	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4	265.3	270.0	278.5
127.5°	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1	281.9	287.9	298.7
130°	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9	291.7	299.3	311.4
132.5°	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4	299.9	309.0	322.7
135°	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6	312.4	323.7	338.7
137.5°	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0	326.9	337.4	352.5
140°	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1	335.9	347.2	362.2
142.5°	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7	345.7	356.2	371.3
145°	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4	361.3	370.7	383.9
147.5°	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0	377.1	385.2	397.5
150°	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8	387.7	394.3	406.5
152.5°	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3	397.5	403.3	414.0
155°	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2	410.2	415.8	425.3
157.5°	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6	422.4	427.0	435.1
160°	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9	430.0	433.8	440.4
162.5°	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7	436.8	440.5	446.4
165°	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9	446.0	448.8	453.6
167.5°	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7	453.7	455.4	458.1
170°	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2	458.3	459.2	461.1
172.5°	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2	460.5	461.5	463.3
175°	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7	463.8	464.8	465.7
177.5°	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4	465.9	465.9	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	16.2	16.6	16.2	17.7	16.1	17.2	17.3	16.9	17.1	17.2	17.1
90°	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0	17.9	18.9	20.7
92.5°	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7	121.0	91.0	77.2
95°	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6	533.5	417.7	338.7
97.5°	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6	907.2	794.5	684.6
100°	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3	1111.3	1014.3	916.4
102.5°	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8	1236.1	1189.7	1123.4
105°	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0	1306.9	1348.3	1337.9
107.5°	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9	1243.9	1350.2	1399.3
110°	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6	1172.3	1305.0	1385.1



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9	1101.6	1235.8	1330.1
115°	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3	1000.2	1129.1	1231.6
117.5°	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3	930.0	1041.0	1135.1
120°	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2	890.1	993.6	1076.4
122.5°	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9	861.5	953.7	1031.2
125°	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4	823.3	905.1	972.9
127.5°	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2	786.8	863.2	926.6
130°	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4	761.2	834.6	895.8
132.5°	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6	737.1	803.7	862.6
135°	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1	700.0	760.3	813.9
137.5°	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4	666.9	717.0	762.5
140°	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1	647.3	690.6	730.2
142.5°	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3	630.7	668.1	702.3
145°	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5	609.7	638.9	664.3
147.5°	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5	592.2	614.6	633.8
150°	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8	582.4	600.3	617.3
152.5°	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2	572.6	589.0	602.2
155°	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9	558.0	571.2	581.5
157.5°	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6	544.0	554.2	562.3
160°	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1	533.5	542.9	549.5
162.5°	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9	524.4	532.3	538.2
165°	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4	511.0	516.6	521.2
167.5°	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4	497.8	502.1	505.5
170°	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4	490.2	493.0	494.9
172.5°	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6	483.4	485.5	486.6
175°	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3	473.3	475.1	475.1
177.5°	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2	468.9	468.9	468.9
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	17.6	17.1	17.2	17.2	17.2	17.1	17.6	17.1	17.2	17.1	16.9
90°	20.7	20.7	21.7	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0
92.5°	65.1	62.9	61.5	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7
95°	271.9	243.7	236.2	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6
97.5°	626.5	573.7	546.5	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6
100°	851.5	783.8	748.9	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3
102.5°	1054.0	1005.9	968.0	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8
105°	1307.9	1276.9	1258.0	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0
107.5°	1414.6	1414.4	1408.2	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9
110°	1427.4	1445.2	1451.8	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1391.9	1422.7	1439.1	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9
115°	1305.0	1350.2	1376.6	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3
117.5°	1208.5	1255.2	1281.3	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3
120°	1146.0	1191.2	1216.6	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2
122.5°	1093.3	1134.7	1160.2	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9
125°	1025.6	1064.1	1084.9	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4
127.5°	974.4	1008.4	1028.0	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2
130°	942.8	973.8	992.7	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4
132.5°	909.6	940.8	958.0	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6
135°	855.3	886.4	903.2	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1
137.5°	799.6	827.8	843.5	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4
140°	765.0	789.5	803.5	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1
142.5°	731.9	752.5	765.9	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3
145°	686.8	702.9	713.2	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5
147.5°	651.7	664.5	670.5	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5
150°	631.3	642.6	646.4	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8
152.5°	614.1	623.1	626.8	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2
155°	590.9	597.5	600.3	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9
157.5°	569.7	575.0	577.7	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6
160°	556.1	560.8	562.7	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1
162.5°	543.3	547.2	547.6	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9
165°	525.0	526.9	526.9	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4
167.5°	507.4	509.1	508.3	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4
170°	496.8	497.8	497.8	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4
172.5°	487.0	488.7	487.2	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6
175°	475.1	476.1	474.2	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3
177.5°	468.2	468.9	466.7	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	17.3	17.2	16.1	17.7	16.2	16.6	16.2	16.4	17.2	18.0	19.0
90°	16.0	15.1	13.2	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9
92.5°	245.5	303.3	308.2	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5
95°	815.8	833.7	680.3	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0
97.5°	1032.2	890.3	607.5	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6
100°	1084.9	849.6	542.0	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9
102.5°	1053.3	778.2	492.3	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7
105°	952.3	682.1	444.1	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3
107.5°	849.0	616.1	423.8	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4
110°	790.3	585.2	417.7	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	746.7	567.2	417.7	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0
115°	699.1	547.6	420.6	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1
117.5°	670.7	538.0	426.8	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6
120°	654.9	533.5	432.8	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7
122.5°	641.3	529.7	438.1	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6
125°	622.9	525.0	447.0	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4
127.5°	606.0	522.7	456.9	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1
130°	594.7	521.2	463.0	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9
132.5°	585.6	521.2	469.7	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4
135°	574.9	521.2	478.9	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6
137.5°	565.3	522.4	487.4	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0
140°	560.8	523.1	491.2	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1
142.5°	557.0	523.9	493.4	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7
145°	551.4	523.1	495.9	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4
147.5°	545.5	520.7	496.8	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0
150°	541.0	518.4	496.8	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8
152.5°	535.7	515.5	496.1	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3
155°	526.9	510.0	494.0	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2
157.5°	518.6	504.4	491.5	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6
160°	511.9	500.6	489.3	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9
162.5°	505.9	496.1	487.0	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7
165°	496.8	489.3	483.6	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9
167.5°	488.0	482.7	478.3	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7
170°	482.7	478.9	476.1	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2
172.5°	477.4	474.4	473.1	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2
175°	470.4	469.5	469.5	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7
177.5°	467.4	466.7	466.7	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.6	17.2	14.6	15.6	16.0	15.6	15.9	15.6	15.4	15.6	15.7
90°	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0
92.5°	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7
95°	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6
97.5°	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6
100°	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3
102.5°	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8
105°	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0
107.5°	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9
110°	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9
115°	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3
117.5°	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3
120°	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2
122.5°	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9
125°	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4
127.5°	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2
130°	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4
132.5°	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6
135°	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1
137.5°	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4
140°	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1
142.5°	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3
145°	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5
147.5°	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5
150°	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8
152.5°	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2
155°	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9
157.5°	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6
160°	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1
162.5°	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9
165°	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4
167.5°	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4
170°	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4
172.5°	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6
175°	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3
177.5°	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	16.5	17.2	16.5	15.9	15.9	16.7	17.2
90°	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333630-830

CATALOG NUMBER: S125RDIP-S1270D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)