

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333612-830

Luminaire Tested: **S125RDIP-S1270D365U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333612-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D365U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5877.0 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79
1	105	101	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	89	83	77	92	85	80	75	78	74	70	72	68	65	66	63	61	58
3	88	79	71	65	84	75	69	63	70	64	60	64	60	56	59	56	53	50
4	81	70	62	56	77	67	60	54	62	56	51	58	53	49	53	49	46	43
5	75	63	54	48	71	60	53	47	56	50	45	52	47	42	48	44	40	38
6	69	57	48	42	66	55	47	41	51	44	39	47	42	37	44	39	36	33
7	64	51	43	38	61	50	42	37	46	40	35	43	37	33	40	35	32	30
8	60	47	39	33	57	45	38	33	42	36	31	39	34	30	37	32	29	26
9	56	43	35	30	53	42	34	29	39	33	28	36	31	27	34	29	26	24
10	52	40	32	27	50	38	31	27	36	30	26	34	28	25	32	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.6	2.9
10°-20°	503.0	8.6
20°-30°	797.5	13.6
30°-40°	961.7	16.4
40°-50°	858.8	14.6
50°-60°	658.6	11.2
60°-70°	428.0	7.3
70°-80°	208.1	3.5
80°-90°	50.6	0.9
90°-100°	119.8	2.0
100°-110°	257.4	4.4
110°-120°	241.6	4.1
120°-130°	195.8	3.3
130°-140°	157.1	2.7
140°-150°	118.6	2.0
150°-160°	83.5	1.4
160°-170°	49.2	0.8
170°-180°	16.0	0.3
0°-30°	1472.1	25.0
0°-40°	2433.8	41.4
0°-60°	3951.3	67.2
0°-90°	4638.0	78.9
90°-120°	618.8	10.5
90°-150°	1090.3	18.6
90°-180°	1239.0	21.1
0°-180°	5877.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	39
90°	8	0	8	0	8	7
95°	78	11	78	11	78	111
105°	441	38	441	38	441	439
115°	492	67	492	67	492	480
125°	387	93	387	93	387	350
135°	322	109	322	109	322	249
145°	254	127	254	127	254	161
155°	213	145	213	145	213	99
165°	186	158	186	158	186	53
175°	168	165	168	165	168	16
180°	165	165	165	165	165	



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	14.4	13.9	13.2	13.2	13.9	14.9	14.2	13.6	13.5	13.4	13.9
90°	7.6	7.6	7.4	7.4	7.4	6.7	6.3	6.0	5.7	5.4	4.6
92.5°	21.2	21.8	22.2	23.1	27.3	32.2	42.8	59.0	86.9	107.4	109.1
95°	78.3	83.6	86.2	96.2	119.9	147.9	188.9	239.5	288.8	295.1	240.8
97.5°	189.2	193.5	203.1	221.8	242.3	281.3	321.2	356.7	365.4	315.2	215.1
100°	259.9	265.1	277.5	301.4	324.4	359.1	393.4	409.7	384.1	300.8	191.9
102.5°	338.7	342.7	356.1	373.2	397.8	421.2	437.6	427.5	372.9	275.5	174.3
105°	441.4	445.4	452.0	463.0	473.7	477.3	462.7	417.1	337.1	241.5	157.2
107.5°	495.9	498.5	500.8	500.8	495.4	478.0	440.4	379.5	300.6	218.1	150.1
110°	514.0	514.0	511.6	505.3	490.3	462.0	415.1	351.8	279.8	207.2	147.9



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	511.9	509.4	503.7	492.8	470.9	437.5	390.0	329.9	264.4	200.8	147.9
115°	491.6	487.3	478.0	462.0	436.0	399.7	354.1	302.5	247.5	193.9	148.9
117.5°	456.3	453.6	444.4	427.8	401.9	368.5	329.2	284.7	237.4	190.5	151.1
120°	433.4	430.7	421.7	405.8	381.1	351.8	315.1	275.1	231.9	188.9	153.3
122.5°	413.1	410.8	401.7	387.1	365.0	337.6	305.0	268.0	227.1	187.6	155.0
125°	387.4	384.1	376.7	363.1	344.4	320.5	291.4	257.5	220.6	185.9	158.3
127.5°	365.4	363.9	357.0	345.0	328.0	305.6	278.5	246.9	214.5	185.1	161.7
130°	353.5	351.5	344.8	333.8	317.2	295.5	269.5	240.2	210.6	184.5	163.9
132.5°	341.4	339.1	333.0	322.1	305.4	284.6	261.0	233.5	207.4	184.5	166.3
135°	321.8	319.8	313.8	302.8	288.1	269.2	247.8	224.9	203.5	184.5	169.6
137.5°	300.8	298.6	293.0	283.0	269.9	253.8	236.1	217.5	200.1	184.9	172.6
140°	286.2	284.5	279.5	270.8	258.4	244.5	229.1	213.5	198.5	185.2	173.9
142.5°	272.6	271.2	266.5	259.1	248.6	236.5	223.3	210.1	197.2	185.5	174.7
145°	253.8	252.5	248.8	243.2	235.2	226.2	215.8	205.6	195.2	185.2	175.5
147.5°	238.0	237.3	235.3	230.7	224.4	217.6	209.6	201.2	193.1	184.4	175.9
150°	229.1	228.8	227.5	223.5	218.5	212.5	206.2	198.9	191.5	183.5	175.9
152.5°	222.3	221.9	220.6	217.4	213.2	208.5	202.7	196.2	189.6	182.5	175.6
155°	212.8	212.5	211.5	209.2	205.9	202.2	197.6	192.2	186.5	180.6	174.8
157.5°	204.4	204.5	203.6	201.7	199.1	196.2	192.6	188.2	183.6	178.5	174.0
160°	198.9	199.2	198.5	196.9	194.5	192.2	188.9	185.6	181.3	177.2	173.2
162.5°	193.8	193.9	193.7	192.4	190.6	188.5	185.7	182.6	179.1	175.6	172.4
165°	186.5	186.5	186.5	185.9	184.5	182.9	180.9	178.5	175.9	173.2	171.3
167.5°	179.8	179.9	180.2	179.6	179.0	177.8	176.3	174.7	172.8	170.9	169.4
170°	175.9	176.3	176.3	175.9	175.2	174.6	173.5	172.6	170.9	169.6	168.5
172.5°	172.1	172.5	173.1	172.4	172.3	171.9	171.2	170.1	169.0	168.0	167.5
175°	167.6	167.9	168.5	168.2	168.2	168.2	167.6	167.6	166.5	166.3	166.3
177.5°	165.2	165.2	166.0	165.8	166.0	166.0	166.0	165.8	165.5	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	14.4	14.2	14.8	14.6	13.9	16.7	18.4	18.9	17.7	16.7	15.6
90°	4.3	3.7	3.3	2.6	2.0	1.3	0.7	0.4	0.7	1.3	2.0
92.5°	76.0	45.5	27.3	17.6	11.9	7.7	4.9	4.1	4.9	7.7	11.9
95°	148.9	75.6	40.0	25.0	17.6	13.9	11.3	11.0	11.3	13.9	17.6
97.5°	118.9	65.1	41.6	30.8	24.2	20.5	18.7	18.3	18.7	20.5	24.2
100°	107.9	64.7	45.3	35.3	28.9	25.4	23.9	23.3	23.9	25.4	28.9
102.5°	103.4	67.0	49.9	40.2	34.3	30.3	29.3	28.9	29.3	30.3	34.3
105°	101.6	71.9	57.3	48.0	42.6	39.3	37.6	37.6	37.6	39.3	42.6
107.5°	104.6	79.3	65.1	56.7	51.2	48.4	46.8	46.2	46.8	48.4	51.2
110°	107.6	84.6	71.0	62.3	57.3	54.3	53.0	52.3	53.0	54.3	57.3



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	111.3	89.6	76.5	68.1	63.2	60.1	59.1	58.4	59.1	60.1	63.2
115°	116.9	97.6	85.3	76.9	71.9	69.0	68.0	67.3	68.0	69.0	71.9
117.5°	123.3	105.8	94.1	86.1	80.3	77.4	76.3	75.3	76.3	77.4	80.3
120°	127.6	111.6	99.9	91.6	86.0	82.9	81.6	80.6	81.6	82.9	86.0
122.5°	132.3	117.2	105.6	97.2	91.0	88.0	86.9	86.2	86.9	88.0	91.0
125°	138.9	124.6	113.6	104.9	98.6	95.6	94.0	93.3	94.0	95.6	98.6
127.5°	144.9	131.7	121.1	112.4	105.8	101.9	99.8	98.8	99.8	101.9	105.8
130°	148.9	136.2	125.9	117.3	110.3	105.9	103.3	102.3	103.3	105.9	110.3
132.5°	152.4	140.5	130.2	121.5	114.2	109.4	106.2	104.9	106.2	109.4	114.2
135°	157.2	146.2	135.9	127.0	119.9	114.6	110.6	109.2	110.6	114.6	119.9
137.5°	160.8	150.3	140.9	131.7	124.8	119.4	115.7	114.7	115.7	119.4	124.8
140°	163.2	153.3	143.5	134.6	128.3	122.9	118.9	117.9	118.9	122.9	128.3
142.5°	164.6	155.0	146.0	137.5	131.5	126.1	122.3	121.7	122.3	126.1	131.5
145°	166.5	158.3	149.6	141.9	135.9	131.2	127.9	127.2	127.9	131.2	135.9
147.5°	167.8	160.2	152.6	145.9	140.7	136.4	133.5	133.1	133.5	136.4	140.7
150°	168.5	161.6	154.2	148.5	143.9	139.6	137.2	136.6	137.2	139.6	143.9
152.5°	169.1	162.9	156.1	151.0	146.6	142.8	140.7	140.3	140.7	142.8	146.6
155°	169.6	164.2	158.5	153.9	150.5	147.2	145.2	145.2	145.2	147.2	150.5
157.5°	169.8	165.3	160.5	156.9	154.0	151.2	149.6	149.7	149.6	151.2	154.0
160°	169.8	165.9	161.6	158.5	155.9	153.5	152.2	152.6	152.2	153.5	155.9
162.5°	169.7	166.5	162.6	160.1	158.1	156.0	154.7	155.0	154.7	156.0	158.1
165°	169.2	166.5	163.9	161.9	160.5	158.9	157.9	158.5	157.9	158.9	160.5
167.5°	168.4	166.5	164.4	163.1	162.1	161.3	160.6	161.0	160.6	161.3	162.1
170°	167.9	166.5	164.9	163.9	163.2	162.6	162.2	162.6	162.2	162.6	163.2
172.5°	167.4	166.3	164.9	164.4	164.0	163.3	163.1	163.6	163.1	163.3	164.0
175°	166.5	165.9	164.9	164.9	164.9	164.6	164.2	164.9	164.2	164.6	164.9
177.5°	165.8	165.5	164.9	164.9	165.2	164.9	164.9	165.5	164.9	164.9	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	15.3	15.4	14.8	16.1	14.4	15.2	15.3	14.7	14.8	14.9	14.4
90°	2.6	3.3	3.7	4.3	4.6	5.4	5.7	6.0	6.3	6.7	7.4
92.5°	17.6	27.3	45.5	76.0	109.1	107.4	86.9	59.0	42.8	32.2	27.3
95°	25.0	40.0	75.6	148.9	240.8	295.1	288.8	239.5	188.9	147.9	119.9
97.5°	30.8	41.6	65.1	118.9	215.1	315.2	365.4	356.7	321.2	281.3	242.3
100°	35.3	45.3	64.7	107.9	191.9	300.8	384.1	409.7	393.4	359.1	324.4
102.5°	40.2	49.9	67.0	103.4	174.3	275.5	372.9	427.5	437.6	421.2	397.8
105°	48.0	57.3	71.9	101.6	157.2	241.5	337.1	417.1	462.7	477.3	473.7
107.5°	56.7	65.1	79.3	104.6	150.1	218.1	300.6	379.5	440.4	478.0	495.4
110°	62.3	71.0	84.6	107.6	147.9	207.2	279.8	351.8	415.1	462.0	490.3



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	68.1	76.5	89.6	111.3	147.9	200.8	264.4	329.9	390.0	437.5	470.9
115°	76.9	85.3	97.6	116.9	148.9	193.9	247.5	302.5	354.1	399.7	436.0
117.5°	86.1	94.1	105.8	123.3	151.1	190.5	237.4	284.7	329.2	368.5	401.9
120°	91.6	99.9	111.6	127.6	153.3	188.9	231.9	275.1	315.1	351.8	381.1
122.5°	97.2	105.6	117.2	132.3	155.0	187.6	227.1	268.0	305.0	337.6	365.0
125°	104.9	113.6	124.6	138.9	158.3	185.9	220.6	257.5	291.4	320.5	344.4
127.5°	112.4	121.1	131.7	144.9	161.7	185.1	214.5	246.9	278.5	305.6	328.0
130°	117.3	125.9	136.2	148.9	163.9	184.5	210.6	240.2	269.5	295.5	317.2
132.5°	121.5	130.2	140.5	152.4	166.3	184.5	207.4	233.5	261.0	284.6	305.4
135°	127.0	135.9	146.2	157.2	169.6	184.5	203.5	224.9	247.8	269.2	288.1
137.5°	131.7	140.9	150.3	160.8	172.6	184.9	200.1	217.5	236.1	253.8	269.9
140°	134.6	143.5	153.3	163.2	173.9	185.2	198.5	213.5	229.1	244.5	258.4
142.5°	137.5	146.0	155.0	164.6	174.7	185.5	197.2	210.1	223.3	236.5	248.6
145°	141.9	149.6	158.3	166.5	175.5	185.2	195.2	205.6	215.8	226.2	235.2
147.5°	145.9	152.6	160.2	167.8	175.9	184.4	193.1	201.2	209.6	217.6	224.4
150°	148.5	154.2	161.6	168.5	175.9	183.5	191.5	198.9	206.2	212.5	218.5
152.5°	151.0	156.1	162.9	169.1	175.6	182.5	189.6	196.2	202.7	208.5	213.2
155°	153.9	158.5	164.2	169.6	174.8	180.6	186.5	192.2	197.6	202.2	205.9
157.5°	156.9	160.5	165.3	169.8	174.0	178.5	183.6	188.2	192.6	196.2	199.1
160°	158.5	161.6	165.9	169.8	173.2	177.2	181.3	185.6	188.9	192.2	194.5
162.5°	160.1	162.6	166.5	169.7	172.4	175.6	179.1	182.6	185.7	188.5	190.6
165°	161.9	163.9	166.5	169.2	171.3	173.2	175.9	178.5	180.9	182.9	184.5
167.5°	163.1	164.4	166.5	168.4	169.4	170.9	172.8	174.7	176.3	177.8	179.0
170°	163.9	164.9	166.5	167.9	168.5	169.6	170.9	172.6	173.5	174.6	175.2
172.5°	164.4	164.9	166.3	167.4	167.5	168.0	169.0	170.1	171.2	171.9	172.3
175°	164.9	164.9	165.9	166.5	166.3	166.3	166.5	167.6	167.6	168.2	168.2
177.5°	164.9	164.9	165.5	165.8	165.2	165.2	165.5	165.8	166.0	166.0	166.0
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	15.0	14.4	14.4	14.4	14.4	14.4	15.0	14.4	14.9	14.8	14.7
90°	7.4	7.4	7.6	7.6	7.6	7.4	7.4	7.4	6.7	6.3	6.0
92.5°	23.1	22.2	21.8	21.2	21.8	22.2	23.1	27.3	32.2	42.8	59.0
95°	96.2	86.2	83.6	78.3	83.6	86.2	96.2	119.9	147.9	188.9	239.5
97.5°	221.8	203.1	193.5	189.2	193.5	203.1	221.8	242.3	281.3	321.2	356.7
100°	301.4	277.5	265.1	259.9	265.1	277.5	301.4	324.4	359.1	393.4	409.7
102.5°	373.2	356.1	342.7	338.7	342.7	356.1	373.2	397.8	421.2	437.6	427.5
105°	463.0	452.0	445.4	441.4	445.4	452.0	463.0	473.7	477.3	462.7	417.1
107.5°	500.8	500.8	498.5	495.9	498.5	500.8	500.8	495.4	478.0	440.4	379.5
110°	505.3	511.6	514.0	514.0	514.0	511.6	505.3	490.3	462.0	415.1	351.8



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	492.8	503.7	509.4	511.9	509.4	503.7	492.8	470.9	437.5	390.0	329.9
115°	462.0	478.0	487.3	491.6	487.3	478.0	462.0	436.0	399.7	354.1	302.5
117.5°	427.8	444.4	453.6	456.3	453.6	444.4	427.8	401.9	368.5	329.2	284.7
120°	405.8	421.7	430.7	433.4	430.7	421.7	405.8	381.1	351.8	315.1	275.1
122.5°	387.1	401.7	410.8	413.1	410.8	401.7	387.1	365.0	337.6	305.0	268.0
125°	363.1	376.7	384.1	387.4	384.1	376.7	363.1	344.4	320.5	291.4	257.5
127.5°	345.0	357.0	363.9	365.4	363.9	357.0	345.0	328.0	305.6	278.5	246.9
130°	333.8	344.8	351.5	353.5	351.5	344.8	333.8	317.2	295.5	269.5	240.2
132.5°	322.1	333.0	339.1	341.4	339.1	333.0	322.1	305.4	284.6	261.0	233.5
135°	302.8	313.8	319.8	321.8	319.8	313.8	302.8	288.1	269.2	247.8	224.9
137.5°	283.0	293.0	298.6	300.8	298.6	293.0	283.0	269.9	253.8	236.1	217.5
140°	270.8	279.5	284.5	286.2	284.5	279.5	270.8	258.4	244.5	229.1	213.5
142.5°	259.1	266.5	271.2	272.6	271.2	266.5	259.1	248.6	236.5	223.3	210.1
145°	243.2	248.8	252.5	253.8	252.5	248.8	243.2	235.2	226.2	215.8	205.6
147.5°	230.7	235.3	237.3	238.0	237.3	235.3	230.7	224.4	217.6	209.6	201.2
150°	223.5	227.5	228.8	229.1	228.8	227.5	223.5	218.5	212.5	206.2	198.9
152.5°	217.4	220.6	221.9	222.3	221.9	220.6	217.4	213.2	208.5	202.7	196.2
155°	209.2	211.5	212.5	212.8	212.5	211.5	209.2	205.9	202.2	197.6	192.2
157.5°	201.7	203.6	204.5	204.4	204.5	203.6	201.7	199.1	196.2	192.6	188.2
160°	196.9	198.5	199.2	198.9	199.2	198.5	196.9	194.5	192.2	188.9	185.6
162.5°	192.4	193.7	193.9	193.8	193.9	193.7	192.4	190.6	188.5	185.7	182.6
165°	185.9	186.5	186.5	186.5	186.5	186.5	185.9	184.5	182.9	180.9	178.5
167.5°	179.6	180.2	179.9	179.8	179.9	180.2	179.6	179.0	177.8	176.3	174.7
170°	175.9	176.3	176.3	175.9	176.3	176.3	175.9	175.2	174.6	173.5	172.6
172.5°	172.4	173.1	172.5	172.1	172.5	173.1	172.4	172.3	171.9	171.2	170.1
175°	168.2	168.5	167.9	167.6	167.9	168.5	168.2	168.2	168.2	167.6	167.6
177.5°	165.8	166.0	165.2	165.2	165.2	166.0	165.8	166.0	166.0	166.0	165.8
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	15.3	15.2	14.4	16.1	14.8	15.4	15.3	15.6	16.7	17.7	18.9
90°	5.7	5.4	4.6	4.3	3.7	3.3	2.6	2.0	1.3	0.7	0.4
92.5°	86.9	107.4	109.1	76.0	45.5	27.3	17.6	11.9	7.7	4.9	4.1
95°	288.8	295.1	240.8	148.9	75.6	40.0	25.0	17.6	13.9	11.3	11.0
97.5°	365.4	315.2	215.1	118.9	65.1	41.6	30.8	24.2	20.5	18.7	18.3
100°	384.1	300.8	191.9	107.9	64.7	45.3	35.3	28.9	25.4	23.9	23.3
102.5°	372.9	275.5	174.3	103.4	67.0	49.9	40.2	34.3	30.3	29.3	28.9
105°	337.1	241.5	157.2	101.6	71.9	57.3	48.0	42.6	39.3	37.6	37.6
107.5°	300.6	218.1	150.1	104.6	79.3	65.1	56.7	51.2	48.4	46.8	46.2
110°	279.8	207.2	147.9	107.6	84.6	71.0	62.3	57.3	54.3	53.0	52.3



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	264.4	200.8	147.9	111.3	89.6	76.5	68.1	63.2	60.1	59.1	58.4
115°	247.5	193.9	148.9	116.9	97.6	85.3	76.9	71.9	69.0	68.0	67.3
117.5°	237.4	190.5	151.1	123.3	105.8	94.1	86.1	80.3	77.4	76.3	75.3
120°	231.9	188.9	153.3	127.6	111.6	99.9	91.6	86.0	82.9	81.6	80.6
122.5°	227.1	187.6	155.0	132.3	117.2	105.6	97.2	91.0	88.0	86.9	86.2
125°	220.6	185.9	158.3	138.9	124.6	113.6	104.9	98.6	95.6	94.0	93.3
127.5°	214.5	185.1	161.7	144.9	131.7	121.1	112.4	105.8	101.9	99.8	98.8
130°	210.6	184.5	163.9	148.9	136.2	125.9	117.3	110.3	105.9	103.3	102.3
132.5°	207.4	184.5	166.3	152.4	140.5	130.2	121.5	114.2	109.4	106.2	104.9
135°	203.5	184.5	169.6	157.2	146.2	135.9	127.0	119.9	114.6	110.6	109.2
137.5°	200.1	184.9	172.6	160.8	150.3	140.9	131.7	124.8	119.4	115.7	114.7
140°	198.5	185.2	173.9	163.2	153.3	143.5	134.6	128.3	122.9	118.9	117.9
142.5°	197.2	185.5	174.7	164.6	155.0	146.0	137.5	131.5	126.1	122.3	121.7
145°	195.2	185.2	175.5	166.5	158.3	149.6	141.9	135.9	131.2	127.9	127.2
147.5°	193.1	184.4	175.9	167.8	160.2	152.6	145.9	140.7	136.4	133.5	133.1
150°	191.5	183.5	175.9	168.5	161.6	154.2	148.5	143.9	139.6	137.2	136.6
152.5°	189.6	182.5	175.6	169.1	162.9	156.1	151.0	146.6	142.8	140.7	140.3
155°	186.5	180.6	174.8	169.6	164.2	158.5	153.9	150.5	147.2	145.2	145.2
157.5°	183.6	178.5	174.0	169.8	165.3	160.5	156.9	154.0	151.2	149.6	149.7
160°	181.3	177.2	173.2	169.8	165.9	161.6	158.5	155.9	153.5	152.2	152.6
162.5°	179.1	175.6	172.4	169.7	166.5	162.6	160.1	158.1	156.0	154.7	155.0
165°	175.9	173.2	171.3	169.2	166.5	163.9	161.9	160.5	158.9	157.9	158.5
167.5°	172.8	170.9	169.4	168.4	166.5	164.4	163.1	162.1	161.3	160.6	161.0
170°	170.9	169.6	168.5	167.9	166.5	164.9	163.9	163.2	162.6	162.2	162.6
172.5°	169.0	168.0	167.5	167.4	166.3	164.9	164.4	164.0	163.3	163.1	163.6
175°	166.5	166.3	166.3	166.5	165.9	164.9	164.9	164.9	164.6	164.2	164.9
177.5°	165.5	165.2	165.2	165.8	165.5	164.9	164.9	165.2	164.9	164.9	165.5
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.4	16.7	13.9	14.6	14.8	14.2	14.4	13.9	13.4	13.5	13.6
90°	0.7	1.3	2.0	2.6	3.3	3.7	4.3	4.6	5.4	5.7	6.0
92.5°	4.9	7.7	11.9	17.6	27.3	45.5	76.0	109.1	107.4	86.9	59.0
95°	11.3	13.9	17.6	25.0	40.0	75.6	148.9	240.8	295.1	288.8	239.5
97.5°	18.7	20.5	24.2	30.8	41.6	65.1	118.9	215.1	315.2	365.4	356.7
100°	23.9	25.4	28.9	35.3	45.3	64.7	107.9	191.9	300.8	384.1	409.7
102.5°	29.3	30.3	34.3	40.2	49.9	67.0	103.4	174.3	275.5	372.9	427.5
105°	37.6	39.3	42.6	48.0	57.3	71.9	101.6	157.2	241.5	337.1	417.1
107.5°	46.8	48.4	51.2	56.7	65.1	79.3	104.6	150.1	218.1	300.6	379.5
110°	53.0	54.3	57.3	62.3	71.0	84.6	107.6	147.9	207.2	279.8	351.8



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	59.1	60.1	63.2	68.1	76.5	89.6	111.3	147.9	200.8	264.4	329.9
115°	68.0	69.0	71.9	76.9	85.3	97.6	116.9	148.9	193.9	247.5	302.5
117.5°	76.3	77.4	80.3	86.1	94.1	105.8	123.3	151.1	190.5	237.4	284.7
120°	81.6	82.9	86.0	91.6	99.9	111.6	127.6	153.3	188.9	231.9	275.1
122.5°	86.9	88.0	91.0	97.2	105.6	117.2	132.3	155.0	187.6	227.1	268.0
125°	94.0	95.6	98.6	104.9	113.6	124.6	138.9	158.3	185.9	220.6	257.5
127.5°	99.8	101.9	105.8	112.4	121.1	131.7	144.9	161.7	185.1	214.5	246.9
130°	103.3	105.9	110.3	117.3	125.9	136.2	148.9	163.9	184.5	210.6	240.2
132.5°	106.2	109.4	114.2	121.5	130.2	140.5	152.4	166.3	184.5	207.4	233.5
135°	110.6	114.6	119.9	127.0	135.9	146.2	157.2	169.6	184.5	203.5	224.9
137.5°	115.7	119.4	124.8	131.7	140.9	150.3	160.8	172.6	184.9	200.1	217.5
140°	118.9	122.9	128.3	134.6	143.5	153.3	163.2	173.9	185.2	198.5	213.5
142.5°	122.3	126.1	131.5	137.5	146.0	155.0	164.6	174.7	185.5	197.2	210.1
145°	127.9	131.2	135.9	141.9	149.6	158.3	166.5	175.5	185.2	195.2	205.6
147.5°	133.5	136.4	140.7	145.9	152.6	160.2	167.8	175.9	184.4	193.1	201.2
150°	137.2	139.6	143.9	148.5	154.2	161.6	168.5	175.9	183.5	191.5	198.9
152.5°	140.7	142.8	146.6	151.0	156.1	162.9	169.1	175.6	182.5	189.6	196.2
155°	145.2	147.2	150.5	153.9	158.5	164.2	169.6	174.8	180.6	186.5	192.2
157.5°	149.6	151.2	154.0	156.9	160.5	165.3	169.8	174.0	178.5	183.6	188.2
160°	152.2	153.5	155.9	158.5	161.6	165.9	169.8	173.2	177.2	181.3	185.6
162.5°	154.7	156.0	158.1	160.1	162.6	166.5	169.7	172.4	175.6	179.1	182.6
165°	157.9	158.9	160.5	161.9	163.9	166.5	169.2	171.3	173.2	175.9	178.5
167.5°	160.6	161.3	162.1	163.1	164.4	166.5	168.4	169.4	170.9	172.8	174.7
170°	162.2	162.6	163.2	163.9	164.9	166.5	167.9	168.5	169.6	170.9	172.6
172.5°	163.1	163.3	164.0	164.4	164.9	166.3	167.4	167.5	168.0	169.0	170.1
175°	164.2	164.6	164.9	164.9	164.9	165.9	166.5	166.3	166.3	166.5	167.6
177.5°	164.9	164.9	165.2	164.9	164.9	165.5	165.8	165.2	165.2	165.5	165.8
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2	165.2



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	14.2	14.9	13.9	13.2	13.2	13.9	14.4
90°	6.3	6.7	7.4	7.4	7.4	7.6	7.6
92.5°	42.8	32.2	27.3	23.1	22.2	21.8	21.2
95°	188.9	147.9	119.9	96.2	86.2	83.6	78.3
97.5°	321.2	281.3	242.3	221.8	203.1	193.5	189.2
100°	393.4	359.1	324.4	301.4	277.5	265.1	259.9
102.5°	437.6	421.2	397.8	373.2	356.1	342.7	338.7
105°	462.7	477.3	473.7	463.0	452.0	445.4	441.4
107.5°	440.4	478.0	495.4	500.8	500.8	498.5	495.9
110°	415.1	462.0	490.3	505.3	511.6	514.0	514.0



TEST NUMBER: P333612-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	390.0	437.5	470.9	492.8	503.7	509.4	511.9
115°	354.1	399.7	436.0	462.0	478.0	487.3	491.6
117.5°	329.2	368.5	401.9	427.8	444.4	453.6	456.3
120°	315.1	351.8	381.1	405.8	421.7	430.7	433.4
122.5°	305.0	337.6	365.0	387.1	401.7	410.8	413.1
125°	291.4	320.5	344.4	363.1	376.7	384.1	387.4
127.5°	278.5	305.6	328.0	345.0	357.0	363.9	365.4
130°	269.5	295.5	317.2	333.8	344.8	351.5	353.5
132.5°	261.0	284.6	305.4	322.1	333.0	339.1	341.4
135°	247.8	269.2	288.1	302.8	313.8	319.8	321.8
137.5°	236.1	253.8	269.9	283.0	293.0	298.6	300.8
140°	229.1	244.5	258.4	270.8	279.5	284.5	286.2
142.5°	223.3	236.5	248.6	259.1	266.5	271.2	272.6
145°	215.8	226.2	235.2	243.2	248.8	252.5	253.8
147.5°	209.6	217.6	224.4	230.7	235.3	237.3	238.0
150°	206.2	212.5	218.5	223.5	227.5	228.8	229.1
152.5°	202.7	208.5	213.2	217.4	220.6	221.9	222.3
155°	197.6	202.2	205.9	209.2	211.5	212.5	212.8
157.5°	192.6	196.2	199.1	201.7	203.6	204.5	204.4
160°	188.9	192.2	194.5	196.9	198.5	199.2	198.9
162.5°	185.7	188.5	190.6	192.4	193.7	193.9	193.8
165°	180.9	182.9	184.5	185.9	186.5	186.5	186.5
167.5°	176.3	177.8	179.0	179.6	180.2	179.9	179.8
170°	173.5	174.6	175.2	175.9	176.3	176.3	175.9
172.5°	171.2	171.9	172.3	172.4	173.1	172.5	172.1
175°	167.6	168.2	168.2	168.2	168.5	167.9	167.6
177.5°	166.0	166.0	166.0	165.8	166.0	165.2	165.2
180°	165.2	165.2	165.2	165.2	165.2	165.2	165.2

(END OF REPORT)