

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333614-830

Luminaire Tested: **S125RDIP-S1270D365U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333614-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D365U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5792.0 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333614-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333614-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79
1	105	100	96	93	100	96	93	89	88	85	83	81	79	77	74	72	71	68
2	96	88	82	77	91	84	79	74	78	73	69	71	68	65	66	63	60	57
3	88	78	70	64	83	75	68	62	69	63	59	63	59	55	58	55	52	49
4	80	69	61	55	77	67	59	53	61	55	50	57	52	48	52	48	45	42
5	74	62	54	47	70	60	52	46	55	49	44	51	46	42	47	43	39	37
6	68	56	47	41	65	54	46	40	50	43	39	46	41	37	43	38	35	32
7	63	51	42	37	61	49	41	36	46	39	34	42	37	33	39	35	31	29
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	32	28	26
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	34	29	25	23
10	52	39	32	27	49	38	31	26	36	29	25	33	28	24	31	27	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333614-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	3.2
10°-20°	511.3	8.8
20°-30°	741.4	12.8
30°-40°	845.0	14.6
40°-50°	823.6	14.2
50°-60°	693.3	12.0
60°-70°	486.0	8.4
70°-80°	249.8	4.3
80°-90°	64.0	1.1
90°-100°	28.7	0.5
100°-110°	84.7	1.5
110°-120°	143.4	2.5
120°-130°	188.7	3.3
130°-140°	211.5	3.7
140°-150°	207.3	3.6
150°-160°	174.1	3.0
160°-170°	115.7	2.0
170°-180°	40.5	0.7
0°-30°	1435.7	24.8
0°-40°	2280.6	39.4
0°-60°	3797.6	65.6
0°-90°	4597.5	79.4
90°-120°	256.8	4.4
90°-150°	864.2	14.9
90°-180°	1195.0	20.6
0°-180°	5792.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	0	3	5	7	8	5
95°	22	22	26	28	29	23
105°	76	78	80	82	83	81
115°	144	145	146	145	145	142
125°	210	211	212	211	211	188
135°	272	274	275	275	274	210
145°	330	331	332	332	332	206
155°	378	378	378	379	378	174
165°	411	410	410	412	410	116
175°	427	426	426	427	425	41
180°	428	428	428	428	428	



TEST NUMBER: P333614-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.4	23.7	22.0	20.3	19.3	19.1	19.0	18.9	18.7	18.8
90°	0.4	0.9	1.5	2.1	2.7	3.3	3.8	4.3	4.8	5.4	5.7
92.5°	8.1	8.5	8.9	9.3	9.7	10.3	10.8	11.5	12.2	12.8	13.3
95°	21.7	21.8	22.0	22.1	22.2	22.7	23.5	24.1	24.9	25.6	26.2
97.5°	36.0	36.0	36.1	36.2	36.2	36.8	37.8	38.8	39.8	40.8	41.4
100°	46.7	46.7	46.7	46.7	46.7	47.1	48.1	49.0	50.0	51.0	51.7
102.5°	58.1	58.4	58.7	59.0	59.3	59.7	60.1	60.6	61.2	61.6	62.4
105°	76.0	76.3	76.7	77.1	77.5	77.9	78.3	78.7	79.2	79.6	80.0
107.5°	95.7	96.0	96.4	96.8	97.2	97.6	97.8	98.2	98.5	98.9	99.1
110°	109.2	109.6	110.0	110.4	110.7	111.0	111.2	111.5	111.7	112.0	112.2



TEST NUMBER: P333614-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	123.1	123.3	123.5	123.7	123.9	124.1	124.4	124.7	125.0	125.3	125.4
115°	143.5	143.8	144.2	144.5	144.8	145.0	145.2	145.2	145.4	145.6	145.5
117.5°	164.1	164.2	164.4	164.5	164.7	164.8	164.9	165.0	165.1	165.3	165.3
120°	176.9	177.3	177.7	178.0	178.3	178.6	178.7	178.7	178.8	178.9	178.9
122.5°	190.8	190.9	191.1	191.1	191.2	191.4	191.6	191.8	192.0	192.2	192.2
125°	209.5	210.0	210.5	210.8	211.3	211.6	211.7	211.7	211.8	211.9	211.7
127.5°	229.5	229.8	230.1	230.3	230.5	230.7	230.8	230.9	231.0	231.0	231.0
130°	241.5	241.9	242.2	242.6	243.0	243.3	243.4	243.6	243.7	243.8	243.7
132.5°	253.5	254.1	254.8	255.3	255.9	256.3	256.2	256.2	256.2	256.1	256.0
135°	272.5	273.0	273.4	273.8	274.3	274.6	274.7	274.7	274.8	274.8	274.8
137.5°	290.4	290.8	291.2	291.6	292.1	292.4	292.6	292.7	292.8	293.0	293.1
140°	301.8	302.2	302.6	302.9	303.3	303.6	303.8	304.1	304.3	304.4	304.6
142.5°	313.3	313.6	313.9	314.2	314.5	314.8	315.1	315.4	315.7	315.9	316.0
145°	330.2	330.5	330.7	331.0	331.3	331.6	331.8	332.1	332.2	332.4	332.4
147.5°	345.7	345.9	346.0	346.2	346.4	346.6	346.8	346.9	347.0	347.2	347.4
150°	356.1	356.1	356.0	355.9	355.8	355.9	356.2	356.6	356.8	357.1	357.1
152.5°	364.7	364.8	364.9	365.0	365.0	365.1	365.3	365.4	365.5	365.6	365.8
155°	377.8	377.8	377.8	377.8	377.8	377.8	377.9	378.0	378.1	378.1	378.4
157.5°	389.5	389.4	389.2	389.0	388.9	388.8	388.9	389.0	389.0	389.1	389.4
160°	396.4	396.2	396.0	395.8	395.6	395.5	395.6	395.6	395.7	395.8	396.1
162.5°	402.6	402.4	402.3	402.1	401.9	401.8	401.8	401.9	401.9	401.9	402.3
165°	410.8	410.6	410.5	410.3	410.2	410.1	410.2	410.3	410.4	410.4	410.8
167.5°	417.6	417.4	417.1	416.8	416.5	416.3	416.3	416.3	416.3	416.3	416.8
170°	421.4	421.1	420.8	420.6	420.2	420.1	420.1	420.1	420.1	420.1	420.6
172.5°	424.0	423.8	423.5	423.2	422.9	422.7	422.7	422.7	422.7	422.7	423.2
175°	427.1	426.8	426.5	426.2	425.9	425.7	425.7	425.7	425.7	425.7	426.2
177.5°	428.6	428.4	428.1	427.9	427.6	427.5	427.4	427.4	427.3	427.3	427.6
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1



TEST NUMBER: P333614-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	18.9	18.9	19.0	18.9	18.7	18.5	18.3	18.1
90°	6.0	6.4	6.8	7.1	7.4	7.5	7.7	8.0
92.5°	13.8	14.2	14.7	15.1	15.3	15.4	15.6	15.7
95°	26.7	27.2	27.7	28.1	28.2	28.4	28.5	28.7
97.5°	41.8	42.3	42.8	43.1	43.2	43.3	43.4	43.5
100°	52.3	53.0	53.6	54.0	54.2	54.4	54.5	54.7
102.5°	63.1	63.8	64.6	65.0	65.2	65.4	65.6	65.8
105°	80.5	81.0	81.4	81.7	81.9	82.2	82.4	82.7
107.5°	99.3	99.5	99.7	99.9	99.8	99.8	99.8	99.8
110°	112.4	112.6	112.8	112.9	112.8	112.7	112.6	112.6



TEST NUMBER: P333614-830

CATALOG NUMBER: S125RDIP-S1270D365U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	125.5	125.5	125.6	125.6	125.5	125.4	125.3	125.2
115°	145.4	145.3	145.2	145.2	145.2	145.1	145.0	144.9
117.5°	165.4	165.5	165.5	165.4	165.1	164.9	164.6	164.2
120°	178.9	178.9	178.9	178.7	178.4	178.1	177.9	177.6
122.5°	192.1	192.0	192.0	191.8	191.6	191.3	191.1	190.9
125°	211.6	211.4	211.3	211.1	211.1	211.0	210.9	210.8
127.5°	230.9	230.8	230.7	230.6	230.5	230.4	230.2	230.1
130°	243.7	243.6	243.6	243.5	243.3	243.2	243.0	242.9
132.5°	256.0	255.9	255.8	255.7	255.4	255.2	255.1	254.9
135°	274.8	274.8	274.8	274.7	274.4	274.1	273.8	273.5
137.5°	293.2	293.3	293.4	293.2	292.8	292.5	292.1	291.7
140°	304.8	304.9	305.1	305.0	304.6	304.3	303.9	303.5
142.5°	316.1	316.2	316.3	316.1	315.8	315.4	315.1	314.7
145°	332.4	332.4	332.4	332.3	332.2	331.9	331.7	331.5
147.5°	347.6	347.8	348.0	347.8	347.3	346.8	346.3	345.8
150°	357.1	357.1	357.1	357.0	356.9	356.8	356.6	356.5
152.5°	366.0	366.2	366.4	366.3	366.1	365.8	365.5	365.2
155°	378.7	379.0	379.3	379.3	378.9	378.5	378.1	377.8
157.5°	389.6	390.0	390.3	390.2	389.7	389.2	388.7	388.2
160°	396.3	396.6	396.9	396.9	396.5	396.2	395.8	395.4
162.5°	402.6	402.9	403.3	403.3	402.8	402.4	402.0	401.5
165°	411.0	411.3	411.6	411.5	411.0	410.7	410.2	409.7
167.5°	417.3	417.6	418.1	418.1	417.6	417.2	416.7	416.3
170°	420.9	421.4	421.9	421.8	421.3	420.8	420.3	419.7
172.5°	423.7	424.0	424.5	424.5	424.0	423.6	423.1	422.6
175°	426.6	427.1	427.5	427.4	427.0	426.4	425.9	425.4
177.5°	428.0	428.4	428.7	428.7	428.3	427.8	427.4	427.0
180°	428.1	428.1	428.1	428.1	428.1	428.1	428.1	428.1

(END OF REPORT)