

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333619-830

Luminaire Tested: **S125RDIP-S1270D590U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333619-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D590U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6825.7 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333619-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333619-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	79	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	54	57	53	50	51	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333619-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.7
10°-20°	511.3	7.5
20°-30°	741.4	10.9
30°-40°	845.0	12.4
40°-50°	823.6	12.1
50°-60°	693.3	10.2
60°-70°	486.0	7.1
70°-80°	249.8	3.7
80°-90°	64.6	0.9
90°-100°	26.4	0.4
100°-110°	162.5	2.4
110°-120°	294.7	4.3
120°-130°	378.2	5.5
130°-140°	406.7	6.0
140°-150°	381.8	5.6
150°-160°	308.8	4.5
160°-170°	199.7	2.9
170°-180°	68.9	1.0
0°-30°	1435.7	21.0
0°-40°	2280.6	33.4
0°-60°	3797.6	55.6
0°-90°	4598.0	67.4
90°-120°	483.5	7.1
90°-150°	1650.2	24.2
90°-180°	2228.0	32.6
0°-180°	6825.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	5	9	11	13	5
95°	31	28	9	11	11	39
105°	158	160	160	160	160	168
115°	297	299	300	298	295	294
125°	422	426	426	424	422	377
135°	526	529	529	527	524	406
145°	610	611	611	612	609	382
155°	672	669	670	671	667	310
165°	709	706	707	709	706	200
175°	726	722	723	727	722	69
180°	726	726	726	726	726	



TEST NUMBER: P333619-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.5	23.8	22.2	20.6	19.7	19.6	19.5	19.4	19.3	19.5
90°	0.6	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2
92.5°	8.3	7.6	7.0	6.3	5.6	5.7	6.4	7.2	7.8	8.6	9.2
95°	30.6	30.3	30.0	29.6	29.2	26.8	22.2	17.7	13.1	8.6	9.2
97.5°	64.0	64.7	65.3	65.9	66.5	62.4	53.4	44.4	35.4	26.5	23.1
100°	89.8	90.2	90.5	90.9	91.2	91.6	92.2	92.7	93.1	93.6	75.8
102.5°	116.0	116.5	117.0	117.4	117.8	118.2	118.5	118.9	119.1	119.4	116.0
105°	158.1	158.5	159.1	159.6	160.0	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.8	201.8	201.8	201.8	201.9	202.1	202.4	202.6	202.8	202.8
110°	230.2	230.2	230.2	230.2	230.2	230.3	230.5	230.7	231.0	231.2	230.9



TEST NUMBER: P333619-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.8	257.1	257.4	257.7	258.0	258.2	258.4	258.4	258.6	258.7	258.4
115°	296.8	297.5	298.0	298.6	299.3	299.6	299.7	299.8	299.9	300.1	299.6
117.5°	338.3	338.2	338.2	338.2	338.2	338.4	338.8	339.3	339.7	340.2	339.6
120°	364.1	363.9	363.8	363.7	363.5	363.7	364.1	364.4	364.8	365.1	364.9
122.5°	386.8	387.3	387.8	388.2	388.7	389.0	389.2	389.4	389.5	389.6	389.5
125°	422.2	423.0	423.8	424.6	425.5	425.9	425.9	425.9	425.9	425.9	425.5
127.5°	455.8	456.4	457.0	457.6	458.2	458.5	458.4	458.4	458.3	458.2	457.9
130°	476.5	477.0	477.7	478.2	478.8	479.2	479.3	479.5	479.6	479.7	479.3
132.5°	497.1	497.8	498.5	499.2	499.8	500.1	499.8	499.5	499.3	499.1	499.0
135°	526.5	527.2	527.9	528.6	529.3	529.6	529.3	529.0	528.9	528.6	528.4
137.5°	553.5	554.1	554.7	555.3	555.9	556.2	555.9	555.7	555.5	555.3	555.3
140°	571.1	571.4	571.6	571.8	572.0	572.1	572.0	571.8	571.7	571.7	571.8
142.5°	587.0	587.2	587.3	587.5	587.6	587.8	588.0	588.1	588.2	588.4	588.4
145°	610.4	610.6	610.9	611.1	611.3	611.4	611.4	611.4	611.4	611.4	611.5
147.5°	630.7	630.7	630.7	630.7	630.6	630.7	630.7	630.9	631.0	631.2	631.4
150°	643.7	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.9
152.5°	656.2	655.6	655.2	654.6	654.0	653.9	654.1	654.4	654.6	654.9	655.2
155°	672.2	671.5	670.8	670.1	669.3	669.1	669.3	669.6	669.8	670.1	670.4
157.5°	684.6	684.1	683.7	683.2	682.9	682.7	682.7	682.7	682.7	682.8	683.2
160°	693.1	692.5	691.7	691.0	690.3	690.0	690.1	690.2	690.3	690.5	691.0
162.5°	700.0	699.4	698.6	697.9	697.2	696.9	697.0	697.1	697.2	697.4	698.0
165°	709.3	708.6	707.8	707.2	706.4	706.2	706.2	706.3	706.5	706.6	707.3
167.5°	716.1	715.5	714.7	714.0	713.2	712.9	713.0	713.1	713.2	713.4	714.3
170°	720.1	719.3	718.4	717.6	716.7	716.3	716.4	716.6	716.7	716.8	717.7
172.5°	722.6	721.8	721.0	720.1	719.3	719.0	719.2	719.4	719.6	719.8	720.7
175°	725.5	724.7	724.0	723.3	722.6	722.3	722.4	722.6	722.6	722.7	723.7
177.5°	726.7	726.1	725.6	725.0	724.4	724.2	724.2	724.3	724.4	724.5	725.3
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333619-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	19.6	19.7	19.8	19.8	19.6	19.4	19.2	19.0
90°	9.8	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	9.8	10.4	11.0	11.4	11.5	11.7	11.9	12.1
95°	9.8	10.4	11.0	11.3	11.3	11.3	11.3	11.3
97.5°	19.7	16.3	13.0	11.3	11.3	11.3	11.3	11.3
100°	58.0	40.2	22.3	13.2	12.7	12.3	11.8	11.3
102.5°	112.6	109.2	105.9	100.2	92.0	83.9	75.8	67.7
105°	160.2	160.2	160.2	160.2	160.0	159.9	159.9	159.7
107.5°	202.9	202.9	202.9	202.7	202.5	202.1	201.7	201.3
110°	230.5	230.2	229.8	229.7	229.8	229.9	230.1	230.2



TEST NUMBER: P333619-830

CATALOG NUMBER: S125RDIP-S1270D590U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	257.9	257.4	256.9	256.7	256.5	256.3	256.2	256.0
115°	299.1	298.6	298.1	297.6	296.8	296.1	295.4	294.7
117.5°	338.9	338.3	337.7	337.2	337.0	336.6	336.3	336.0
120°	364.7	364.4	364.2	363.7	363.2	362.6	361.9	361.4
122.5°	389.2	389.0	388.7	388.2	387.6	386.8	386.2	385.5
125°	425.0	424.4	424.0	423.6	423.2	422.8	422.5	422.2
127.5°	457.6	457.4	457.1	456.6	455.6	454.8	453.9	453.0
130°	479.0	478.6	478.2	477.8	477.2	476.5	476.0	475.4
132.5°	498.9	498.8	498.8	498.4	497.9	497.2	496.6	496.1
135°	528.1	527.9	527.6	527.2	526.5	525.8	525.0	524.3
137.5°	555.3	555.4	555.4	555.2	554.6	553.9	553.4	552.7
140°	572.1	572.3	572.6	572.3	571.7	570.9	570.2	569.5
142.5°	588.5	588.5	588.6	588.2	587.6	586.8	586.1	585.4
145°	611.7	611.8	611.9	611.6	610.9	610.2	609.4	608.7
147.5°	631.5	631.7	631.8	631.4	630.6	629.7	628.9	628.0
150°	644.1	644.4	644.6	644.3	643.4	642.3	641.4	640.5
152.5°	655.3	655.6	655.8	655.5	654.7	653.8	652.9	652.1
155°	670.8	671.1	671.5	671.2	670.2	669.3	668.4	667.3
157.5°	683.5	683.9	684.3	684.0	683.1	682.0	681.1	680.1
160°	691.4	691.9	692.4	692.1	691.2	690.2	689.3	688.3
162.5°	698.7	699.4	700.0	699.8	698.8	697.8	696.7	695.6
165°	708.0	708.8	709.5	709.4	708.4	707.5	706.5	705.5
167.5°	715.1	716.0	716.8	716.7	715.7	714.5	713.5	712.4
170°	718.8	719.7	720.7	720.6	719.5	718.4	717.4	716.3
172.5°	721.5	722.5	723.3	723.2	722.1	721.0	719.9	718.9
175°	724.6	725.6	726.6	726.5	725.5	724.3	723.3	722.2
177.5°	725.9	726.6	727.3	727.2	726.4	725.7	724.9	724.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5

(END OF REPORT)