

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333624-830

Luminaire Tested: **S125RDIP-S1270D810U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333624-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U830-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7380.3 lumens  
Efficiency: N/A  
Efficacy: 121.6 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54
2	93	85	79	74	87	80	75	71	71	67	63	62	59	57	54	52	50	46
3	85	75	68	62	79	71	65	60	63	58	54	55	52	48	48	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	37	34
5	72	60	52	46	67	57	49	44	51	45	40	45	40	36	39	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11559	11559	11559	11559
5°	13299	11575	10222	11575
10°	15255	11516	9020	11516
15°	16477	11397	8017	11397
20°	18168	11260	7403	11260
25°	21026	11078	6869	11078
30°	22881	10887	6520	10887
35°	19301	10664	6199	10664
40°	13478	10264	5922	10264
45°	9999	9724	5650	9724
50°	7973	9161	5419	9161
55°	6767	8463	5212	8463
60°	5846	7839	4879	7839
65°	5210	7163	4199	7163
70°	4577	6562	3828	6562
75°	3960	5682	3593	5682
80°	3005	4783	3005	4783
85°	2505	3757	2831	3757



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.6	2.3
10°-20°	503.0	6.8
20°-30°	797.5	10.8
30°-40°	961.7	13.0
40°-50°	858.8	11.6
50°-60°	658.6	8.9
60°-70°	428.0	5.8
70°-80°	208.1	2.8
80°-90°	51.7	0.7
90°-100°	264.9	3.6
100°-110°	569.6	7.7
110°-120°	534.5	7.2
120°-130°	433.2	5.9
130°-140°	347.7	4.7
140°-150°	262.4	3.6
150°-160°	184.7	2.5
160°-170°	108.8	1.5
170°-180°	35.4	0.5
0°-30°	1472.1	19.9
0°-40°	2433.8	33.0
0°-60°	3951.3	53.5
0°-90°	4639.1	62.9
90°-120°	1369.1	18.6
90°-150°	2412.3	32.7
90°-180°	2741.0	37.1
0°-180°	7380.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1790	1790	1790	1790	1790	
5°	2051	1785	1577	1785	2051	205
15°	2464	1705	1199	1705	2464	706
25°	2951	1555	964	1555	2951	1355
35°	2448	1353	786	1353	2448	1479
45°	1095	1065	619	1065	1095	874
55°	601	752	463	752	601	545
65°	341	469	275	469	341	339
75°	159	228	144	228	159	169
85°	34	51	38	51	34	39
90°	17	1	17	1	17	13
95°	173	24	173	24	173	245
105°	976	83	976	83	976	971
115°	1088	149	1088	149	1088	1063
125°	857	206	857	206	857	775
135°	712	242	712	242	712	552
145°	562	282	562	282	562	357
155°	471	321	471	321	471	219
165°	413	351	413	351	413	118
175°	371	365	371	365	371	36
180°	366	366	366	366	366	



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1882.6	1881.5	1883.9	1877.4	1877.9	1867.9	1867.9	1860.3	1850.3	1842.7	1839.2
5°	2051.3	2052.9	2049.8	2038.8	2031.6	2020.5	2008.0	1985.9	1967.6	1949.9	1936.0
7.5°	2225.1	2226.1	2216.4	2213.0	2194.4	2180.9	2153.1	2123.2	2096.6	2062.8	2036.9
10°	2326.1	2325.4	2315.1	2307.1	2290.8	2270.3	2243.2	2207.8	2174.8	2138.1	2102.8
12.5°	2384.9	2383.0	2379.7	2369.9	2354.9	2336.8	2313.7	2279.0	2238.3	2198.0	2156.8
15°	2464.3	2459.1	2449.6	2437.0	2415.7	2394.4	2368.7	2337.9	2299.0	2253.4	2215.2
17.5°	2562.4	2562.6	2547.9	2530.5	2501.6	2464.0	2424.3	2374.5	2321.6	2271.4	2230.8
20°	2643.5	2641.3	2626.7	2592.8	2559.8	2512.7	2467.2	2406.2	2341.6	2276.1	2225.4
22.5°	2760.0	2754.2	2738.9	2694.5	2643.3	2582.7	2513.0	2438.5	2360.4	2286.1	2219.6
25°	2950.6	2946.2	2916.1	2864.7	2792.7	2699.3	2608.3	2506.1	2393.8	2296.0	2215.2
27.5°	3081.2	3076.3	3053.9	3011.2	2944.8	2846.6	2723.3	2586.8	2446.5	2312.1	2195.5
30°	3068.2	3079.2	3076.3	3056.5	3006.5	2918.3	2804.4	2650.9	2484.1	2326.1	2187.3
32.5°	2883.6	2893.5	2919.3	2958.3	2961.2	2925.9	2840.9	2699.1	2526.4	2346.7	2180.8
35°	2448.1	2461.4	2511.3	2589.9	2692.7	2778.7	2796.3	2720.0	2564.9	2371.7	2171.1
37.5°	1882.1	1954.4	1996.4	2079.2	2234.6	2392.7	2544.8	2600.8	2534.8	2361.4	2155.4
40°	1598.7	1616.4	1691.3	1784.6	1915.4	2080.0	2296.8	2453.2	2458.3	2337.9	2130.7
42.5°	1368.4	1390.7	1442.1	1516.6	1628.6	1793.2	2016.9	2223.5	2319.1	2273.2	2098.4
45°	1094.8	1111.6	1149.1	1206.5	1292.4	1428.3	1620.8	1859.5	2049.2	2123.4	2011.7
47.5°	899.3	908.4	941.0	984.7	1048.3	1147.4	1296.4	1503.6	1731.0	1890.5	1874.7
50°	793.5	803.8	828.8	861.9	915.5	999.2	1118.2	1290.9	1525.3	1720.0	1759.0
52.5°	711.2	719.7	735.3	766.6	810.9	875.2	971.3	1127.5	1338.4	1545.4	1635.5
55°	601.0	606.9	619.3	637.0	672.3	718.6	801.5	909.6	1080.1	1288.7	1421.0
57.5°	510.2	513.1	521.0	537.3	561.8	595.6	655.5	747.1	869.3	1057.2	1203.2
60°	452.6	455.5	465.8	476.8	496.0	526.8	573.8	637.7	755.3	910.3	1058.0
62.5°	406.7	408.5	412.9	424.0	440.7	464.5	501.5	553.6	647.1	783.3	922.8
65°	340.9	341.7	343.1	351.9	362.2	379.8	404.1	440.8	511.3	614.3	737.6
67.5°	277.8	278.7	283.9	287.0	297.7	307.0	321.2	349.3	399.0	468.3	564.3
70°	242.4	241.8	246.9	250.5	254.2	265.2	274.8	297.6	328.4	381.4	461.4
72.5°	209.5	207.6	209.8	211.1	216.0	223.5	233.1	247.0	270.8	307.3	368.5
75°	158.7	159.5	159.5	160.9	164.6	167.5	170.4	177.8	191.1	215.3	248.4
77.5°	111.4	110.2	113.3	113.8	115.9	119.1	121.7	124.6	130.1	140.1	157.1
80°	80.8	80.8	81.5	83.8	83.0	84.5	88.1	91.1	97.7	103.6	109.4
82.5°	62.0	61.5	62.1	62.6	62.5	63.9	65.2	65.8	68.3	71.3	75.4
85°	33.8	33.8	34.5	34.5	35.3	35.3	36.0	36.0	36.0	36.8	37.5
87.5°	16.3	15.7	15.0	15.0	15.6	16.5	15.7	15.0	14.9	14.7	15.0
90°	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3	12.5	11.8	10.3
92.5°	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6	192.4	237.6	241.4
95°	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9	638.9	653.0	532.8
97.5°	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2	808.4	697.3	475.8
100°	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4	849.7	665.5	424.5
102.5°	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9	825.0	609.4	385.6
105°	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7	745.8	534.3	347.9
107.5°	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5	665.1	482.6	332.0
110°	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3	619.1	458.4	327.3



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9	584.8	444.2	327.3
115°	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2	547.5	429.0	329.4
117.5°	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0	525.3	421.4	334.3
120°	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7	512.9	417.8	339.0
122.5°	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9	502.3	414.9	343.1
125°	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7	487.9	411.2	350.1
127.5°	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1	474.6	409.4	357.9
130°	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3	465.8	408.3	362.6
132.5°	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6	458.7	408.3	367.9
135°	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5	450.3	408.3	375.1
137.5°	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3	442.8	409.2	381.7
140°	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4	439.2	409.7	384.7
142.5°	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8	436.3	410.4	386.4
145°	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7	431.9	409.7	388.4
147.5°	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3	427.3	407.8	389.1
150°	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0	423.8	406.0	389.1
152.5°	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0	419.6	403.7	388.5
155°	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3	412.7	399.4	386.9
157.5°	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4	406.2	395.0	385.0
160°	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5	401.0	392.1	383.2
162.5°	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0	396.2	388.5	381.4
165°	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0	389.1	383.2	378.8
167.5°	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4	382.2	378.1	374.7
170°	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7	378.1	375.1	372.9
172.5°	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5	373.9	371.6	370.5
175°	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7	368.4	367.8	367.8
177.5°	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7	366.1	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1839.2	1835.0	1827.4	1820.3	1811.6	1803.9	1798.6	1792.2	1784.0	1774.0	1765.7
5°	1920.5	1904.4	1883.1	1864.7	1841.3	1822.9	1803.7	1785.4	1767.0	1743.5	1723.0
7.5°	2010.8	1977.5	1944.9	1904.1	1867.1	1834.0	1802.2	1770.1	1738.6	1705.2	1673.1
10°	2066.1	2025.6	1980.8	1929.4	1882.4	1837.6	1796.4	1756.0	1713.4	1675.9	1635.5
12.5°	2117.8	2065.6	2014.3	1949.4	1892.9	1838.1	1785.8	1735.4	1689.9	1641.2	1597.9
15°	2164.5	2113.1	2055.8	1976.4	1897.8	1831.6	1769.9	1704.6	1647.9	1593.7	1545.1
17.5°	2182.6	2128.6	2062.1	1985.8	1899.9	1816.7	1737.2	1665.5	1598.9	1535.6	1481.0
20°	2175.5	2123.4	2055.0	1982.3	1890.5	1803.7	1717.8	1638.4	1564.2	1497.3	1439.4
22.5°	2158.5	2104.5	2038.5	1961.7	1874.5	1782.6	1690.7	1606.1	1528.3	1459.2	1395.8
25°	2132.9	2059.5	1991.9	1916.8	1833.9	1742.8	1647.9	1554.6	1471.7	1401.1	1332.1
27.5°	2106.3	2014.6	1928.6	1854.2	1766.4	1685.2	1593.7	1498.1	1410.8	1339.0	1268.1
30°	2082.2	1979.3	1884.5	1800.1	1717.0	1639.9	1553.2	1459.9	1370.3	1296.1	1224.1
32.5°	2052.2	1942.9	1838.7	1741.3	1661.2	1584.7	1506.2	1417.0	1329.7	1253.1	1180.0
35°	2014.6	1875.0	1761.9	1658.3	1569.3	1495.2	1424.7	1352.6	1265.2	1185.8	1114.6
37.5°	1965.2	1806.9	1675.9	1563.0	1469.3	1394.8	1339.1	1273.3	1193.4	1117.5	1051.4
40°	1935.2	1757.5	1614.2	1502.5	1404.0	1325.4	1273.3	1217.5	1144.7	1073.5	1007.3
42.5°	1895.3	1712.2	1551.9	1435.5	1336.4	1260.7	1208.1	1159.2	1098.3	1031.1	960.3
45°	1816.9	1624.5	1456.2	1331.3	1231.4	1157.2	1108.0	1064.6	1018.3	956.6	894.8
47.5°	1715.0	1533.0	1356.9	1220.5	1122.7	1053.8	1006.0	971.8	938.7	886.2	826.2
50°	1633.3	1457.7	1285.7	1153.5	1049.1	983.8	939.0	911.8	881.7	833.9	783.9
52.5°	1536.9	1380.1	1211.7	1076.5	978.1	916.8	873.7	846.6	821.7	782.8	735.2
55°	1385.0	1247.5	1093.3	970.5	880.2	818.5	777.3	751.6	737.0	703.9	666.4
57.5°	1209.7	1111.2	975.2	856.9	776.9	716.0	685.8	663.9	647.3	624.0	597.5
60°	1087.4	1018.3	896.4	783.9	710.5	652.4	625.3	606.9	591.4	571.7	551.0
62.5°	963.4	913.1	807.0	710.5	642.9	594.3	568.8	552.2	534.4	521.0	501.1
65°	797.2	752.3	678.9	603.2	540.7	501.8	483.4	468.7	457.7	443.0	429.0
67.5°	620.1	601.9	551.2	499.0	454.2	419.5	403.7	393.4	380.1	371.4	361.7
70°	511.3	502.6	466.6	432.1	390.1	366.6	351.9	347.5	331.4	322.5	315.9
72.5°	415.0	410.9	390.1	366.2	336.7	316.0	302.6	297.6	287.3	280.2	276.0
75°	284.4	285.8	282.1	266.7	255.7	242.4	230.7	227.7	220.5	214.5	210.8
77.5°	179.8	187.4	187.7	186.9	182.5	174.5	169.6	167.4	160.1	158.0	157.1
80°	123.5	131.5	138.8	138.1	136.7	134.5	130.8	128.6	124.9	122.7	121.2
82.5°	82.3	89.8	96.0	99.9	99.6	97.5	94.9	93.9	93.1	91.5	91.2
85°	38.9	40.4	42.6	47.8	51.5	52.1	51.5	50.7	48.4	49.2	50.0
87.5°	15.5	15.2	15.6	15.3	14.4	17.1	18.5	18.9	17.9	17.1	16.2
90°	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8	1.5	2.9	4.4
92.5°	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0	10.9	17.1	26.2
95°	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3	25.1	30.9	39.0
97.5°	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3	41.3	45.4	53.5
100°	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6	53.1	56.0	64.1
102.5°	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0	64.8	67.2	75.9
105°	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3	83.3	87.0	94.3
107.5°	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2	103.6	107.2	113.2
110°	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7	117.2	120.1	126.8





TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2	130.7	133.1	139.7
115°	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8	150.3	152.6	159.2
117.5°	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5	168.8	171.2	177.8
120°	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3	180.6	183.5	190.1
122.5°	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8	192.4	194.7	201.3
125°	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3	207.8	211.5	218.1
127.5°	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6	220.8	225.6	233.9
130°	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2	228.5	234.3	243.9
132.5°	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1	235.0	242.0	252.8
135°	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8	244.7	253.5	265.3
137.5°	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8	256.0	264.3	276.1
140°	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9	263.1	271.9	283.7
142.5°	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1	270.8	279.0	290.8
145°	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5	283.0	290.4	300.7
147.5°	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5	295.4	301.7	311.3
150°	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2	303.6	308.8	318.4
152.5°	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4	311.3	315.8	324.2
155°	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3	321.3	325.7	333.1
157.5°	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0	330.9	334.4	340.7
160°	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5	336.8	339.8	344.9
162.5°	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8	342.1	345.1	349.6
165°	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8	349.3	351.6	355.2
167.5°	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1	355.3	356.7	358.7
170°	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7	358.9	359.7	361.1
172.5°	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0	360.7	361.4	362.9
175°	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8	363.4	364.1	364.8
177.5°	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1	365.0	365.0	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1759.8	1751.6	1745.7	1733.9	1725.7	1722.2	1715.7	1713.9	1720.4	1715.7	1715.1
5°	1707.5	1686.2	1669.3	1652.4	1634.0	1622.3	1604.7	1601.7	1597.3	1590.6	1589.2
7.5°	1644.7	1617.0	1595.3	1567.4	1543.0	1523.5	1501.5	1491.0	1485.4	1476.8	1465.4
10°	1602.4	1569.3	1540.0	1512.0	1482.0	1457.7	1435.7	1418.7	1407.7	1397.4	1393.1
12.5°	1560.7	1527.0	1489.4	1455.7	1422.0	1394.8	1370.4	1359.4	1347.2	1335.1	1324.8
15°	1495.9	1451.0	1409.9	1371.0	1342.4	1313.0	1289.4	1273.3	1254.9	1249.8	1229.9
17.5°	1427.1	1383.2	1335.0	1294.0	1260.7	1228.4	1202.6	1184.2	1170.4	1151.5	1142.4
20°	1384.2	1332.1	1285.1	1247.5	1210.8	1172.6	1146.1	1130.8	1117.5	1102.1	1094.8
22.5°	1338.4	1287.4	1239.2	1195.2	1157.9	1120.3	1101.5	1085.5	1070.4	1056.2	1046.5
25°	1271.1	1219.7	1168.9	1123.4	1084.5	1057.2	1035.2	1016.8	1008.8	994.9	984.5
27.5°	1204.5	1149.8	1097.2	1051.8	1021.2	994.4	976.3	961.8	947.2	935.0	926.0
30°	1161.6	1105.8	1048.5	1012.5	980.1	954.4	934.5	920.6	909.6	898.5	891.9
32.5°	1118.7	1061.1	1010.2	971.3	940.8	918.5	898.1	884.8	873.2	860.9	853.2
35°	1049.9	991.2	950.0	911.8	881.7	861.1	847.2	828.0	818.5	809.6	801.5
37.5°	986.0	931.3	886.8	853.3	827.2	806.7	788.6	778.4	766.6	758.7	752.0
40°	939.0	889.0	848.6	813.3	794.3	771.5	754.6	741.3	732.5	722.3	714.9
42.5°	896.6	850.3	811.0	779.3	755.4	736.2	719.9	706.6	695.5	688.2	681.9
45°	836.9	790.6	752.3	722.9	701.0	682.6	665.6	659.0	644.3	635.6	632.6
47.5°	775.0	733.6	696.6	669.6	647.0	629.6	613.8	600.3	592.2	583.5	578.8
50°	733.3	693.6	659.0	632.6	610.6	591.4	576.7	568.0	556.9	548.8	543.0
52.5°	691.5	654.8	620.3	594.9	575.9	556.8	540.4	531.5	521.0	515.9	511.8
55°	631.9	593.0	563.5	538.6	518.7	501.1	485.7	476.8	470.2	465.1	463.6
57.5°	564.3	533.4	506.1	483.6	463.0	446.4	432.9	424.5	418.7	417.9	413.5
60°	520.2	492.3	467.3	443.0	425.4	410.0	398.2	388.7	382.8	382.0	380.6
62.5°	476.1	449.3	426.1	404.8	389.0	374.1	363.0	352.2	348.7	345.1	341.8
65°	410.7	386.4	367.4	350.4	333.6	321.0	310.1	303.4	295.4	291.0	282.9
67.5°	346.5	327.7	309.3	295.1	281.8	269.9	260.8	251.0	245.5	242.0	236.1
70°	304.2	289.5	271.1	255.7	245.4	235.8	228.5	217.4	213.8	210.8	207.9
72.5°	264.2	251.3	235.8	223.4	213.1	204.1	195.6	190.4	186.8	183.8	182.1
75°	207.9	195.5	182.2	173.4	166.1	158.7	154.3	150.6	149.1	148.5	145.4
77.5°	152.7	146.1	135.4	128.5	123.6	120.6	116.7	114.8	114.6	111.4	110.4
80°	116.8	113.1	104.3	101.4	97.7	94.8	92.6	88.9	85.2	83.8	81.5
82.5°	86.8	83.1	79.6	74.9	71.8	70.1	67.9	66.5	67.0	64.9	63.9
85°	46.3	42.6	41.2	40.4	38.9	40.4	39.7	38.9	38.2	37.5	38.2
87.5°	15.8	16.2	15.7	17.2	15.6	16.5	16.6	16.2	16.3	16.5	16.2
90°	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3	14.0	14.7	16.2
92.5°	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6	94.8	71.4	60.4
95°	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9	417.8	327.3	265.3
97.5°	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2	710.6	622.3	536.2
100°	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4	870.3	794.5	717.8
102.5°	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9	968.3	931.8	880.0
105°	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7	1023.7	1056.1	1048.0
107.5°	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5	974.3	1057.5	1096.0
110°	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3	918.2	1022.2	1084.8



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9	862.8	967.9	1041.8
115°	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2	783.4	884.4	964.7
117.5°	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0	728.4	815.4	889.1
120°	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7	697.2	778.3	843.1
122.5°	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9	674.8	747.0	807.8
125°	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7	644.9	709.0	762.0
127.5°	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1	616.2	676.1	725.8
130°	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3	596.3	653.7	701.6
132.5°	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6	577.3	629.5	675.6
135°	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5	548.3	595.5	637.4
137.5°	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3	522.4	561.6	597.2
140°	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4	507.0	540.9	571.8
142.5°	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8	494.1	523.2	550.1
145°	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7	477.6	500.4	520.3
147.5°	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3	463.8	481.4	496.4
150°	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0	456.2	470.1	483.4
152.5°	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0	448.6	461.4	471.6
155°	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3	437.1	447.3	455.4
157.5°	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4	426.1	434.0	440.5
160°	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5	417.8	425.3	430.4
162.5°	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0	410.8	417.0	421.5
165°	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0	400.2	404.6	408.3
167.5°	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4	389.8	393.2	395.9
170°	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7	384.0	386.2	387.7
172.5°	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5	378.6	380.3	381.2
175°	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7	370.7	372.2	372.2
177.5°	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7	367.3	367.3	367.3
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1714.6	1708.1	1706.3	1708.6	1706.3	1708.1	1714.6	1715.1	1715.7	1720.4	1713.9
5°	1581.9	1574.5	1578.2	1576.7	1578.2	1574.5	1581.9	1589.2	1590.6	1597.3	1601.7
7.5°	1465.2	1456.0	1446.3	1449.4	1446.3	1456.0	1465.2	1465.4	1476.8	1485.4	1491.0
10°	1383.5	1376.1	1371.7	1375.4	1371.7	1376.1	1383.5	1393.1	1397.4	1407.7	1418.7
12.5°	1314.8	1310.3	1306.5	1304.9	1306.5	1310.3	1314.8	1324.8	1335.1	1347.2	1359.4
15°	1221.1	1212.3	1208.6	1199.1	1208.6	1212.3	1221.1	1229.9	1249.8	1254.9	1273.3
17.5°	1134.8	1131.9	1122.4	1118.2	1122.4	1131.9	1134.8	1142.4	1151.5	1170.4	1184.2
20°	1083.7	1080.8	1071.2	1077.1	1071.2	1080.8	1083.7	1094.8	1102.1	1117.5	1130.8
22.5°	1041.4	1034.9	1031.8	1030.1	1031.8	1034.9	1041.4	1046.5	1056.2	1070.4	1085.5
25°	981.6	972.0	968.4	963.9	968.4	972.0	981.6	984.5	994.9	1008.8	1016.8
27.5°	921.9	916.8	911.9	910.8	911.9	916.8	921.9	926.0	935.0	947.2	961.8
30°	883.2	878.0	874.3	874.3	874.3	878.0	883.2	891.9	898.5	909.6	920.6
32.5°	848.5	844.5	840.8	840.3	840.8	844.5	848.5	853.2	860.9	873.2	884.8
35°	798.0	792.0	790.6	786.2	790.6	792.0	798.0	801.5	809.6	818.5	828.0
37.5°	745.5	740.6	740.5	740.0	740.5	740.6	745.5	752.0	758.7	766.6	778.4
40°	711.9	708.2	707.6	702.4	707.6	708.2	711.9	714.9	722.3	732.5	741.3
42.5°	676.1	674.2	671.7	669.5	671.7	674.2	676.1	681.9	688.2	695.5	706.6
45°	627.5	622.3	622.3	618.6	622.3	622.3	627.5	632.6	635.6	644.3	659.0
47.5°	577.2	573.3	573.6	569.9	573.6	573.3	577.2	578.8	583.5	592.2	600.3
50°	543.7	541.5	540.7	539.3	540.7	541.5	543.7	543.0	548.8	556.9	568.0
52.5°	510.2	509.2	512.0	508.7	512.0	509.2	510.2	511.8	515.9	521.0	531.5
55°	465.1	462.9	467.3	462.9	467.3	462.9	465.1	463.6	465.1	470.2	476.8
57.5°	413.2	411.1	415.1	412.9	415.1	411.1	413.2	413.5	417.9	418.7	424.5
60°	379.1	374.8	376.9	377.7	376.9	374.8	379.1	380.6	382.0	382.8	388.7
62.5°	338.6	335.9	337.5	334.1	337.5	335.9	338.6	341.8	345.1	348.7	352.2
65°	281.4	279.2	276.3	274.8	276.3	279.2	281.4	282.9	291.0	295.4	303.4
67.5°	236.4	231.1	231.0	232.1	231.0	231.1	236.4	236.1	242.0	245.5	251.0
70°	203.5	203.5	202.7	202.7	202.7	203.5	203.5	207.9	210.8	213.8	217.4
72.5°	180.6	180.0	178.7	178.1	178.7	180.0	180.6	182.1	183.8	186.8	190.4
75°	145.4	146.2	144.8	144.0	144.8	146.2	145.4	145.4	148.5	149.1	150.6
77.5°	107.4	104.3	105.9	104.3	105.9	104.3	107.4	110.4	111.4	114.6	114.8
80°	81.5	80.8	83.0	80.8	83.0	80.8	81.5	81.5	83.8	85.2	88.9
82.5°	64.5	63.8	64.8	63.2	64.8	63.8	64.5	63.9	64.9	67.0	66.5
85°	38.9	38.2	37.5	38.2	37.5	38.2	38.9	38.2	37.5	38.2	38.9
87.5°	16.8	16.2	16.3	16.3	16.3	16.2	16.8	16.2	16.5	16.3	16.2
90°	16.2	16.2	17.0	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3
92.5°	51.0	49.2	48.2	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6
95°	213.0	190.9	185.0	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9
97.5°	490.7	449.4	428.0	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2
100°	666.9	613.9	586.6	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4
102.5°	825.6	787.8	758.2	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9
105°	1024.4	1000.0	985.3	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7
107.5°	1108.0	1107.8	1103.0	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5
110°	1117.9	1132.0	1137.2	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1090.2	1114.3	1127.1	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9
115°	1022.2	1057.5	1078.2	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2
117.5°	946.6	983.1	1003.6	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0
120°	897.6	933.0	952.9	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7
122.5°	856.4	888.8	908.7	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9
125°	803.3	833.5	849.7	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7
127.5°	763.2	789.9	805.2	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1
130°	738.5	762.8	777.5	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3
132.5°	712.5	736.8	750.4	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6
135°	669.9	694.2	707.5	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5
137.5°	626.3	648.4	660.6	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3
140°	599.2	618.3	629.3	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4
142.5°	573.3	589.5	599.9	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8
145°	538.0	550.5	558.6	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7
147.5°	510.4	520.5	525.2	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3
150°	494.6	503.3	506.3	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0
152.5°	481.0	488.0	491.0	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0
155°	462.8	468.0	470.1	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3
157.5°	446.2	450.4	452.5	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4
160°	435.5	439.2	440.7	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5
162.5°	425.6	428.6	429.0	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0
165°	411.2	412.7	412.7	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0
167.5°	397.4	398.7	398.1	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4
170°	389.1	389.8	389.8	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7
172.5°	381.4	382.8	381.6	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5
175°	372.2	372.9	371.5	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7
177.5°	366.7	367.3	365.5	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1715.7	1722.2	1725.7	1733.9	1745.7	1751.6	1759.8	1765.7	1774.0	1784.0	1792.2
5°	1604.7	1622.3	1634.0	1652.4	1669.3	1686.2	1707.5	1723.0	1743.5	1767.0	1785.4
7.5°	1501.5	1523.5	1543.0	1567.4	1595.3	1617.0	1644.7	1673.1	1705.2	1738.6	1770.1
10°	1435.7	1457.7	1482.0	1512.0	1540.0	1569.3	1602.4	1635.5	1675.9	1713.4	1756.0
12.5°	1370.4	1394.8	1422.0	1455.7	1489.4	1527.0	1560.7	1597.9	1641.2	1689.9	1735.4
15°	1289.4	1313.0	1342.4	1371.0	1409.9	1451.0	1495.9	1545.1	1593.7	1647.9	1704.6
17.5°	1202.6	1228.4	1260.7	1294.0	1335.0	1383.2	1427.1	1481.0	1535.6	1598.9	1665.5
20°	1146.1	1172.6	1210.8	1247.5	1285.1	1332.1	1384.2	1439.4	1497.3	1564.2	1638.4
22.5°	1101.5	1120.3	1157.9	1195.2	1239.2	1287.4	1338.4	1395.8	1459.2	1528.3	1606.1
25°	1035.2	1057.2	1084.5	1123.4	1168.9	1219.7	1271.1	1332.1	1401.1	1471.7	1554.6
27.5°	976.3	994.4	1021.2	1051.8	1097.2	1149.8	1204.5	1268.1	1339.0	1410.8	1498.1
30°	934.5	954.4	980.1	1012.5	1048.5	1105.8	1161.6	1224.1	1296.1	1370.3	1459.9
32.5°	898.1	918.5	940.8	971.3	1010.2	1061.1	1118.7	1180.0	1253.1	1329.7	1417.0
35°	847.2	861.1	881.7	911.8	950.0	991.2	1049.9	1114.6	1185.8	1265.2	1352.6
37.5°	788.6	806.7	827.2	853.3	886.8	931.3	986.0	1051.4	1117.5	1193.4	1273.3
40°	754.6	771.5	794.3	813.3	848.6	889.0	939.0	1007.3	1073.5	1144.7	1217.5
42.5°	719.9	736.2	755.4	779.3	811.0	850.3	896.6	960.3	1031.1	1098.3	1159.2
45°	665.6	682.6	701.0	722.9	752.3	790.6	836.9	894.8	956.6	1018.3	1064.6
47.5°	613.8	629.6	647.0	669.6	696.6	733.6	775.0	826.2	886.2	938.7	971.8
50°	576.7	591.4	610.6	632.6	659.0	693.6	733.3	783.9	833.9	881.7	911.8
52.5°	540.4	556.8	575.9	594.9	620.3	654.8	691.5	735.2	782.8	821.7	846.6
55°	485.7	501.1	518.7	538.6	563.5	593.0	631.9	666.4	703.9	737.0	751.6
57.5°	432.9	446.4	463.0	483.6	506.1	533.4	564.3	597.5	624.0	647.3	663.9
60°	398.2	410.0	425.4	443.0	467.3	492.3	520.2	551.0	571.7	591.4	606.9
62.5°	363.0	374.1	389.0	404.8	426.1	449.3	476.1	501.1	521.0	534.4	552.2
65°	310.1	321.0	333.6	350.4	367.4	386.4	410.7	429.0	443.0	457.7	468.7
67.5°	260.8	269.9	281.8	295.1	309.3	327.7	346.5	361.7	371.4	380.1	393.4
70°	228.5	235.8	245.4	255.7	271.1	289.5	304.2	315.9	322.5	331.4	347.5
72.5°	195.6	204.1	213.1	223.4	235.8	251.3	264.2	276.0	280.2	287.3	297.6
75°	154.3	158.7	166.1	173.4	182.2	195.5	207.9	210.8	214.5	220.5	227.7
77.5°	116.7	120.6	123.6	128.5	135.4	146.1	152.7	157.1	158.0	160.1	167.4
80°	92.6	94.8	97.7	101.4	104.3	113.1	116.8	121.2	122.7	124.9	128.6
82.5°	67.9	70.1	71.8	74.9	79.6	83.1	86.8	91.2	91.5	93.1	93.9
85°	39.7	40.4	38.9	40.4	41.2	42.6	46.3	50.0	49.2	48.4	50.7
87.5°	16.6	16.5	15.6	17.2	15.7	16.2	15.8	16.2	17.1	17.9	18.9
90°	12.5	11.8	10.3	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8
92.5°	192.4	237.6	241.4	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0
95°	638.9	653.0	532.8	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3
97.5°	808.4	697.3	475.8	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3
100°	849.7	665.5	424.5	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6
102.5°	825.0	609.4	385.6	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0
105°	745.8	534.3	347.9	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3
107.5°	665.1	482.6	332.0	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2
110°	619.1	458.4	327.3	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	584.8	444.2	327.3	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2
115°	547.5	429.0	329.4	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8
117.5°	525.3	421.4	334.3	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5
120°	512.9	417.8	339.0	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3
122.5°	502.3	414.9	343.1	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8
125°	487.9	411.2	350.1	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3
127.5°	474.6	409.4	357.9	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6
130°	465.8	408.3	362.6	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2
132.5°	458.7	408.3	367.9	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1
135°	450.3	408.3	375.1	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8
137.5°	442.8	409.2	381.7	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8
140°	439.2	409.7	384.7	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9
142.5°	436.3	410.4	386.4	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1
145°	431.9	409.7	388.4	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5
147.5°	427.3	407.8	389.1	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5
150°	423.8	406.0	389.1	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2
152.5°	419.6	403.7	388.5	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4
155°	412.7	399.4	386.9	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3
157.5°	406.2	395.0	385.0	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0
160°	401.0	392.1	383.2	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5
162.5°	396.2	388.5	381.4	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8
165°	389.1	383.2	378.8	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8
167.5°	382.2	378.1	374.7	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1
170°	378.1	375.1	372.9	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7
172.5°	373.9	371.6	370.5	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0
175°	368.4	367.8	367.8	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8
177.5°	366.1	365.5	365.5	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1798.6	1803.9	1811.6	1820.3	1827.4	1835.0	1839.2	1839.2	1842.7	1850.3	1860.3
5°	1803.7	1822.9	1841.3	1864.7	1883.1	1904.4	1920.5	1936.0	1949.9	1967.6	1985.9
7.5°	1802.2	1834.0	1867.1	1904.1	1944.9	1977.5	2010.8	2036.9	2062.8	2096.6	2123.2
10°	1796.4	1837.6	1882.4	1929.4	1980.8	2025.6	2066.1	2102.8	2138.1	2174.8	2207.8
12.5°	1785.8	1838.1	1892.9	1949.4	2014.3	2065.6	2117.8	2156.8	2198.0	2238.3	2279.0
15°	1769.9	1831.6	1897.8	1976.4	2055.8	2113.1	2164.5	2215.2	2253.4	2299.0	2337.9
17.5°	1737.2	1816.7	1899.9	1985.8	2062.1	2128.6	2182.6	2230.8	2271.4	2321.6	2374.5
20°	1717.8	1803.7	1890.5	1982.3	2055.0	2123.4	2175.5	2225.4	2276.1	2341.6	2406.2
22.5°	1690.7	1782.6	1874.5	1961.7	2038.5	2104.5	2158.5	2219.6	2286.1	2360.4	2438.5
25°	1647.9	1742.8	1833.9	1916.8	1991.9	2059.5	2132.9	2215.2	2296.0	2393.8	2506.1
27.5°	1593.7	1685.2	1766.4	1854.2	1928.6	2014.6	2106.3	2195.5	2312.1	2446.5	2586.8
30°	1553.2	1639.9	1717.0	1800.1	1884.5	1979.3	2082.2	2187.3	2326.1	2484.1	2650.9
32.5°	1506.2	1584.7	1661.2	1741.3	1838.7	1942.9	2052.2	2180.8	2346.7	2526.4	2699.1
35°	1424.7	1495.2	1569.3	1658.3	1761.9	1875.0	2014.6	2171.1	2371.7	2564.9	2720.0
37.5°	1339.1	1394.8	1469.3	1563.0	1675.9	1806.9	1965.2	2155.4	2361.4	2534.8	2600.8
40°	1273.3	1325.4	1404.0	1502.5	1614.2	1757.5	1935.2	2130.7	2337.9	2458.3	2453.2
42.5°	1208.1	1260.7	1336.4	1435.5	1551.9	1712.2	1895.3	2098.4	2273.2	2319.1	2223.5
45°	1108.0	1157.2	1231.4	1331.3	1456.2	1624.5	1816.9	2011.7	2123.4	2049.2	1859.5
47.5°	1006.0	1053.8	1122.7	1220.5	1356.9	1533.0	1715.0	1874.7	1890.5	1731.0	1503.6
50°	939.0	983.8	1049.1	1153.5	1285.7	1457.7	1633.3	1759.0	1720.0	1525.3	1290.9
52.5°	873.7	916.8	978.1	1076.5	1211.7	1380.1	1536.9	1635.5	1545.4	1338.4	1127.5
55°	777.3	818.5	880.2	970.5	1093.3	1247.5	1385.0	1421.0	1288.7	1080.1	909.6
57.5°	685.8	716.0	776.9	856.9	975.2	1111.2	1209.7	1203.2	1057.2	869.3	747.1
60°	625.3	652.4	710.5	783.9	896.4	1018.3	1087.4	1058.0	910.3	755.3	637.7
62.5°	568.8	594.3	642.9	710.5	807.0	913.1	963.4	922.8	783.3	647.1	553.6
65°	483.4	501.8	540.7	603.2	678.9	752.3	797.2	737.6	614.3	511.3	440.8
67.5°	403.7	419.5	454.2	499.0	551.2	601.9	620.1	564.3	468.3	399.0	349.3
70°	351.9	366.6	390.1	432.1	466.6	502.6	511.3	461.4	381.4	328.4	297.6
72.5°	302.6	316.0	336.7	366.2	390.1	410.9	415.0	368.5	307.3	270.8	247.0
75°	230.7	242.4	255.7	266.7	282.1	285.8	284.4	248.4	215.3	191.1	177.8
77.5°	169.6	174.5	182.5	186.9	187.7	187.4	179.8	157.1	140.1	130.1	124.6
80°	130.8	134.5	136.7	138.1	138.8	131.5	123.5	109.4	103.6	97.7	91.1
82.5°	94.9	97.5	99.6	99.9	96.0	89.8	82.3	75.4	71.3	68.3	65.8
85°	51.5	52.1	51.5	47.8	42.6	40.4	38.9	37.5	36.8	36.0	36.0
87.5°	18.5	17.1	14.4	15.3	15.6	15.2	15.5	15.0	14.7	14.9	15.0
90°	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3
92.5°	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6
95°	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9
97.5°	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2
100°	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4
102.5°	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9
105°	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7
107.5°	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5
110°	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3





TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9
115°	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2
117.5°	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0
120°	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7
122.5°	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9
125°	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7
127.5°	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1
130°	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3
132.5°	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6
135°	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5
137.5°	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3
140°	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4
142.5°	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8
145°	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7
147.5°	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3
150°	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0
152.5°	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0
155°	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3
157.5°	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4
160°	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5
162.5°	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0
165°	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0
167.5°	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4
170°	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7
172.5°	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5
175°	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7
177.5°	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8	1789.8
2.5°	1867.9	1867.9	1877.9	1877.4	1883.9	1881.5	1882.6
5°	2008.0	2020.5	2031.6	2038.8	2049.8	2052.9	2051.3
7.5°	2153.1	2180.9	2194.4	2213.0	2216.4	2226.1	2225.1
10°	2243.2	2270.3	2290.8	2307.1	2315.1	2325.4	2326.1
12.5°	2313.7	2336.8	2354.9	2369.9	2379.7	2383.0	2384.9
15°	2368.7	2394.4	2415.7	2437.0	2449.6	2459.1	2464.3
17.5°	2424.3	2464.0	2501.6	2530.5	2547.9	2562.6	2562.4
20°	2467.2	2512.7	2559.8	2592.8	2626.7	2641.3	2643.5
22.5°	2513.0	2582.7	2643.3	2694.5	2738.9	2754.2	2760.0
25°	2608.3	2699.3	2792.7	2864.7	2916.1	2946.2	2950.6
27.5°	2723.3	2846.6	2944.8	3011.2	3053.9	3076.3	3081.2
30°	2804.4	2918.3	3006.5	3056.5	3076.3	3079.2	3068.2
32.5°	2840.9	2925.9	2961.2	2958.3	2919.3	2893.5	2883.6
35°	2796.3	2778.7	2692.7	2589.9	2511.3	2461.4	2448.1
37.5°	2544.8	2392.7	2234.6	2079.2	1996.4	1954.4	1882.1
40°	2296.8	2080.0	1915.4	1784.6	1691.3	1616.4	1598.7
42.5°	2016.9	1793.2	1628.6	1516.6	1442.1	1390.7	1368.4
45°	1620.8	1428.3	1292.4	1206.5	1149.1	1111.6	1094.8
47.5°	1296.4	1147.4	1048.3	984.7	941.0	908.4	899.3
50°	1118.2	999.2	915.5	861.9	828.8	803.8	793.5
52.5°	971.3	875.2	810.9	766.6	735.3	719.7	711.2
55°	801.5	718.6	672.3	637.0	619.3	606.9	601.0
57.5°	655.5	595.6	561.8	537.3	521.0	513.1	510.2
60°	573.8	526.8	496.0	476.8	465.8	455.5	452.6
62.5°	501.5	464.5	440.7	424.0	412.9	408.5	406.7
65°	404.1	379.8	362.2	351.9	343.1	341.7	340.9
67.5°	321.2	307.0	297.7	287.0	283.9	278.7	277.8
70°	274.8	265.2	254.2	250.5	246.9	241.8	242.4
72.5°	233.1	223.5	216.0	211.1	209.8	207.6	209.5
75°	170.4	167.5	164.6	160.9	159.5	159.5	158.7
77.5°	121.7	119.1	115.9	113.8	113.3	110.2	111.4
80°	88.1	84.5	83.0	83.8	81.5	80.8	80.8
82.5°	65.2	63.9	62.5	62.6	62.1	61.5	62.0
85°	36.0	35.3	35.3	34.5	34.5	33.8	33.8
87.5°	15.7	16.5	15.6	15.0	15.0	15.7	16.3
90°	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2



TEST NUMBER: P333624-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)