

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333626-830

Luminaire Tested: **S125RDIP-S1270D810U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333626-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D810U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7241.4 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333626-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333626-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91		79	79	79		69	69	69	64
1	101	97	93	89	95	91	88	85	80	78	75		70	68	67		61	60	58	54
2	92	85	79	74	86	80	74	70	71	66	63		62	59	56		54	52	50	46
3	84	75	67	62	79	71	64	59	62	57	53		55	51	48		48	45	43	39
4	77	66	58	52	72	63	56	50	56	50	46		49	45	41		43	40	37	34
5	71	59	51	45	67	56	49	43	50	44	40		44	40	36		39	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35		40	35	32		35	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31		37	32	28		32	29	25	23
8	57	44	36	31	53	42	35	30	38	32	27		34	29	25		30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25		31	26	23		28	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22		29	24	21		26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333626-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.5
10°-20°	511.3	7.1
20°-30°	741.4	10.2
30°-40°	845.0	11.7
40°-50°	823.6	11.4
50°-60°	693.3	9.6
60°-70°	486.0	6.7
70°-80°	249.8	3.4
80°-90°	65.2	0.9
90°-100°	63.4	0.9
100°-110°	187.3	2.6
110°-120°	317.3	4.4
120°-130°	417.5	5.8
130°-140°	467.9	6.5
140°-150°	458.6	6.3
150°-160°	385.1	5.3
160°-170°	256.0	3.5
170°-180°	89.6	1.2
0°-30°	1435.7	19.8
0°-40°	2280.6	31.5
0°-60°	3797.6	52.4
0°-90°	4598.6	63.5
90°-120°	568.0	7.8
90°-150°	1912.0	26.4
90°-180°	2643.0	36.5
0°-180°	7241.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	7	12	15	18	6
95°	48	50	57	62	63	51
105°	168	172	176	180	183	180
115°	318	320	322	321	321	314
125°	464	468	469	467	467	415
135°	603	607	608	608	605	465
145°	730	733	736	735	733	456
155°	836	836	836	839	836	385
165°	909	907	908	911	906	256
175°	945	942	942	946	941	90
180°	947	947	947	947	947	



TEST NUMBER: P333626-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.6	24.0	22.5	20.9	20.1	20.1	20.1	20.0	20.0	20.2
90°	0.8	2.1	3.4	4.7	5.9	7.2	8.4	9.5	10.7	11.8	12.6
92.5°	17.8	18.8	19.7	20.5	21.5	22.6	24.0	25.4	26.9	28.3	29.4
95°	47.9	48.3	48.5	48.9	49.2	50.2	51.8	53.4	55.1	56.7	57.9
97.5°	79.6	79.7	79.8	80.0	80.1	81.3	83.6	85.9	88.1	90.4	91.4
100°	103.2	103.2	103.2	103.2	103.2	104.2	106.4	108.5	110.7	112.7	114.2
102.5°	128.6	129.2	129.9	130.5	131.2	132.1	133.1	134.2	135.3	136.4	138.0
105°	168.1	168.9	169.7	170.5	171.4	172.2	173.2	174.2	175.1	176.2	177.1
107.5°	211.7	212.4	213.3	214.1	215.0	215.7	216.5	217.3	218.0	218.8	219.2
110°	241.8	242.6	243.4	244.2	245.1	245.7	246.2	246.7	247.1	247.6	248.2



TEST NUMBER: P333626-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	272.4	272.9	273.2	273.7	274.1	274.7	275.2	275.9	276.5	277.1	277.4
115°	317.6	318.3	319.0	319.6	320.3	320.7	321.1	321.4	321.8	322.1	321.9
117.5°	363.1	363.4	363.6	363.9	364.2	364.6	364.9	365.1	365.4	365.7	365.8
120°	391.3	392.2	393.0	393.8	394.6	395.1	395.3	395.5	395.6	395.8	395.8
122.5°	422.0	422.4	422.6	422.9	423.2	423.6	424.0	424.4	424.8	425.3	425.1
125°	463.5	464.6	465.5	466.6	467.5	468.1	468.3	468.4	468.5	468.7	468.4
127.5°	507.8	508.4	508.9	509.4	510.0	510.4	510.6	510.8	511.0	511.2	511.0
130°	534.3	535.2	536.0	536.8	537.6	538.2	538.5	538.9	539.1	539.5	539.3
132.5°	560.9	562.2	563.5	564.9	566.3	566.8	566.8	566.8	566.7	566.7	566.5
135°	602.9	603.9	604.8	605.9	606.8	607.4	607.6	607.8	607.8	608.0	608.0
137.5°	642.4	643.4	644.3	645.3	646.2	646.9	647.2	647.5	647.9	648.3	648.5
140°	667.8	668.5	669.4	670.2	671.0	671.7	672.1	672.7	673.2	673.6	674.0
142.5°	693.1	693.8	694.5	695.1	695.9	696.5	697.1	697.8	698.3	699.0	699.2
145°	730.4	731.0	731.7	732.4	733.0	733.6	734.1	734.5	735.1	735.6	735.6
147.5°	764.9	765.3	765.6	766.0	766.3	766.7	767.1	767.5	767.9	768.3	768.6
150°	787.9	787.7	787.6	787.4	787.2	787.5	788.2	788.8	789.5	790.1	790.1
152.5°	806.7	807.0	807.2	807.5	807.7	807.9	808.1	808.4	808.7	809.0	809.4
155°	835.8	835.8	835.8	835.8	835.8	835.8	836.0	836.2	836.3	836.5	837.2
157.5°	861.8	861.4	861.0	860.6	860.3	860.2	860.4	860.5	860.6	860.8	861.5
160°	877.0	876.6	876.1	875.6	875.1	875.0	875.1	875.2	875.4	875.6	876.3
162.5°	890.6	890.2	889.9	889.6	889.2	889.0	889.0	889.1	889.1	889.2	889.9
165°	908.8	908.4	908.1	907.8	907.5	907.4	907.5	907.7	907.9	908.0	908.7
167.5°	924.1	923.4	922.7	922.1	921.4	921.1	921.1	921.1	921.1	921.1	922.1
170°	932.4	931.7	931.0	930.4	929.7	929.3	929.3	929.3	929.3	929.3	930.4
172.5°	938.2	937.5	936.9	936.2	935.6	935.3	935.3	935.3	935.3	935.3	936.2
175°	944.9	944.2	943.6	942.9	942.3	941.9	941.9	941.9	941.9	941.9	942.9
177.5°	948.3	947.7	947.3	946.7	946.1	945.8	945.7	945.6	945.5	945.3	946.1
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1



TEST NUMBER: P333626-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	20.4	20.5	20.6	20.6	20.5	20.4	20.2	20.0
90°	13.4	14.2	15.1	15.7	16.2	16.7	17.2	17.7
92.5°	30.4	31.6	32.6	33.4	33.7	34.0	34.4	34.8
95°	59.0	60.2	61.4	62.1	62.4	62.8	63.1	63.3
97.5°	92.6	93.6	94.7	95.3	95.5	95.7	96.0	96.1
100°	115.7	117.2	118.7	119.6	119.9	120.2	120.6	120.8
102.5°	139.6	141.2	142.8	143.8	144.3	144.7	145.2	145.6
105°	178.1	179.1	180.1	180.8	181.3	181.8	182.3	182.8
107.5°	219.7	220.2	220.7	220.9	220.9	220.8	220.8	220.8
110°	248.6	249.1	249.6	249.8	249.6	249.4	249.3	249.1



TEST NUMBER: P333626-830

CATALOG NUMBER: S125RDIP-S1270D810U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	277.6	277.8	278.1	278.1	277.7	277.4	277.1	276.8
115°	321.8	321.6	321.4	321.2	321.1	320.9	320.7	320.7
117.5°	366.0	366.1	366.3	366.0	365.3	364.7	364.0	363.4
120°	395.8	395.8	395.8	395.5	394.8	394.2	393.5	392.9
122.5°	425.0	424.9	424.7	424.4	423.9	423.4	422.8	422.4
125°	468.1	467.8	467.4	467.2	467.0	466.8	466.7	466.6
127.5°	510.9	510.7	510.6	510.3	510.0	509.6	509.3	509.0
130°	539.1	539.0	538.9	538.6	538.3	537.9	537.6	537.2
132.5°	566.3	566.1	566.0	565.6	565.2	564.8	564.3	563.8
135°	608.0	608.0	608.0	607.8	607.1	606.4	605.8	605.1
137.5°	648.7	648.8	649.0	648.8	647.9	647.1	646.3	645.5
140°	674.3	674.6	675.0	674.7	673.9	673.1	672.2	671.5
142.5°	699.4	699.6	699.7	699.5	698.6	697.9	697.0	696.2
145°	735.6	735.6	735.6	735.3	734.8	734.3	733.9	733.3
147.5°	769.0	769.5	769.9	769.5	768.4	767.2	766.2	765.1
150°	790.1	790.1	790.1	789.9	789.6	789.3	788.9	788.6
152.5°	809.7	810.1	810.5	810.4	809.8	809.3	808.7	808.0
155°	837.8	838.5	839.1	839.1	838.2	837.4	836.6	835.8
157.5°	862.1	862.8	863.5	863.3	862.1	861.1	860.0	858.9
160°	876.9	877.5	878.2	878.2	877.3	876.5	875.6	874.9
162.5°	890.7	891.6	892.3	892.2	891.3	890.3	889.4	888.4
165°	909.4	910.0	910.6	910.5	909.5	908.5	907.5	906.5
167.5°	923.1	924.1	925.1	925.0	924.1	923.0	922.0	921.0
170°	931.3	932.4	933.3	933.2	932.1	930.9	929.8	928.7
172.5°	937.3	938.2	939.2	939.2	938.2	937.2	936.1	935.1
175°	943.9	944.9	945.8	945.7	944.6	943.5	942.4	941.2
177.5°	946.9	947.6	948.5	948.4	947.4	946.6	945.7	944.7
180°	947.1	947.1	947.1	947.1	947.1	947.1	947.1	947.1

(END OF REPORT)