

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333509-830

Luminaire Tested: **S125RDIP-S375D1035U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333509-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1035U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4751.3 lumens  
Efficiency: N/A  
Efficacy: 127.4 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	53	53	53	37	37	37	29				
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25				
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23	18				
4	71	61	53	48	63	55	48	44	44	39	35	33	30	28	23	22	20	16				
5	65	54	46	41	58	49	42	37	39	34	31	30	26	24	21	19	17	14				
6	60	48	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	12				
7	55	44	36	31	50	40	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	1.1
10°-20°	149.1	3.1
20°-30°	236.4	5.0
30°-40°	285.1	6.0
40°-50°	254.6	5.4
50°-60°	195.2	4.1
60°-70°	126.9	2.7
70°-80°	61.7	1.3
80°-90°	17.4	0.4
90°-100°	81.0	1.7
100°-110°	239.1	5.0
110°-120°	405.1	8.5
120°-130°	533.1	11.2
130°-140°	597.3	12.6
140°-150°	585.5	12.3
150°-160°	491.7	10.3
160°-170°	326.9	6.9
170°-180°	114.4	2.4
0°-30°	436.4	9.2
0°-40°	721.4	15.2
0°-60°	1171.3	24.7
0°-90°	1377.2	29.0
90°-120°	725.2	15.3
90°-150°	2441.1	51.4
90°-180°	3374.0	71.0
0°-180°	4751.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	23	1	23	1	23	13
95°	81	61	81	61	81	82
105°	233	214	233	214	233	247
115°	409	406	409	406	409	405
125°	596	592	596	592	596	532
135°	772	770	772	770	772	596
145°	936	933	936	933	936	584
155°	1067	1067	1067	1067	1067	491
165°	1157	1160	1157	1160	1157	326
175°	1202	1206	1202	1206	1202	114
180°	1209	1209	1209	1209	1209	



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	8.4	8.0	7.7	7.6	7.6	7.8	7.4	7.1	6.9	6.7	6.6
90°	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2	16.1	15.1	13.6
92.5°	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9	37.5	36.1	34.3
95°	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4	73.9	72.5	70.4
97.5°	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1	116.8	115.4	112.4
100°	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7	145.8	143.9	141.3
102.5°	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1	176.2	174.1	172.7
105°	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4	226.1	224.9	223.7
107.5°	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5	279.9	279.3	278.3
110°	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4	316.8	316.1	315.6



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4	354.1	353.8	353.0
115°	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8	411.0	411.2	410.8
117.5°	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2	467.1	466.9	466.6
120°	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3	505.3	505.3	505.1
122.5°	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6	542.8	542.9	542.4
125°	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7	598.0	598.5	598.2
127.5°	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2	652.4	652.7	652.4
130°	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3	688.6	688.8	688.3
132.5°	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0	723.2	723.4	723.5
135°	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3	776.3	776.3	776.1
137.5°	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2	827.9	827.6	827.3
140°	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9	860.4	860.1	859.4
142.5°	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0	892.7	892.4	891.6
145°	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1	939.1	939.1	938.5
147.5°	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8	981.4	980.9	980.3
150°	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7	1008.7	1008.7	1007.9
152.5°	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9	1033.3	1032.8	1032.5
155°	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7	1068.8	1068.0	1067.8
157.5°	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7	1099.9	1099.1	1098.9
160°	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6	1118.7	1117.9	1117.7
162.5°	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2	1136.2	1135.2	1135.2
165°	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9	1160.2	1159.3	1159.0
167.5°	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6	1177.3	1176.0	1176.0
170°	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1	1187.9	1186.6	1186.6
172.5°	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7	1195.3	1194.1	1194.1
175°	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1	1203.8	1202.6	1202.6
177.5°	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9	1208.0	1206.9	1207.1
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	6.4	6.1	6.0	5.7	5.2	5.7	5.9	5.7	5.7	5.7	5.7
90°	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9	2.6	4.2	5.9
92.5°	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8	23.9	25.1	26.3
95°	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2	61.5	62.0	62.4
97.5°	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6	101.8	102.0	102.2
100°	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8	131.8	131.8	131.8
102.5°	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1	164.9	165.8	166.6
105°	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5	215.6	216.6	217.7
107.5°	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2	271.3	272.3	273.4
110°	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7	309.7	310.8	311.8





TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8	348.4	348.8	349.4
115°	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6	406.4	407.3	408.1
117.5°	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5	463.9	464.3	464.7
120°	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6	500.7	501.7	502.8
122.5°	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9	539.2	539.6	540.0
125°	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9	593.1	594.4	595.7
127.5°	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4	649.0	649.8	650.4
130°	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2	683.2	684.3	685.3
132.5°	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0	717.8	719.5	721.2
135°	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8	771.0	772.2	773.5
137.5°	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2	821.3	822.6	823.8
140°	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5	853.6	854.6	855.6
142.5°	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9	885.8	886.6	887.5
145°	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6	933.4	934.2	935.0
147.5°	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6	977.0	977.5	978.0
150°	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9	1005.7	1005.5	1005.3
152.5°	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0	1030.3	1030.6	1030.9
155°	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2	1099.8	1099.3	1098.8
160°	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7	1119.2	1118.5	1117.9
162.5°	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1	1136.6	1136.1	1135.7
165°	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3	1159.8	1159.4	1159.0
167.5°	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8	1178.9	1178.2	1177.3
170°	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3	1189.5	1188.6	1187.9
172.5°	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9	1197.0	1196.2	1195.3
175°	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4	1205.5	1204.7	1203.8
177.5°	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7	1210.0	1209.4	1208.6
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	5.8	6.2	6.3	7.0	6.7	7.2	7.4	7.4	7.6	7.8	7.8
90°	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2	18.2	19.2	20.1
92.5°	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9	40.2	41.7	42.6
95°	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4	76.8	78.3	79.3
97.5°	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1	119.5	120.9	121.7
100°	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7	149.6	151.5	152.7
102.5°	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1	180.2	182.3	183.6
105°	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4	228.7	229.9	230.8
107.5°	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5	281.2	281.8	282.1
110°	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4	318.0	318.7	318.9



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4	354.7	355.0	355.0
115°	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8	410.6	410.4	410.2
117.5°	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2	467.4	467.6	467.2
120°	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3	505.3	505.3	504.9
122.5°	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6	542.4	542.2	541.9
125°	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7	597.2	596.8	596.4
127.5°	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2	652.1	651.9	651.5
130°	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3	688.2	688.0	687.7
132.5°	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0	722.8	722.6	722.2
135°	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3	776.3	776.3	775.9
137.5°	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2	828.4	828.7	828.3
140°	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9	861.3	861.8	861.4
142.5°	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0	893.2	893.4	893.1
145°	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1	939.1	939.1	938.8
147.5°	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8	982.4	982.9	982.4
150°	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7	1008.7	1008.7	1008.5
152.5°	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9	1034.3	1034.8	1034.7
155°	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7	1070.5	1071.4	1071.3
157.5°	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7	1101.5	1102.4	1102.1
160°	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6	1120.4	1121.2	1121.2
162.5°	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2	1138.2	1139.3	1139.2
165°	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9	1161.8	1162.6	1162.4
167.5°	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6	1179.8	1181.1	1181.0
170°	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1	1190.3	1191.6	1191.5
172.5°	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7	1197.9	1199.1	1199.1
175°	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1	1206.4	1207.6	1207.5
177.5°	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9	1209.9	1210.9	1210.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	8.1	8.1	8.2	8.4	8.2	8.1	8.1	7.8	7.8	7.6	7.4
90°	20.7	21.3	22.0	22.6	22.0	21.3	20.7	20.1	19.2	18.2	17.2
92.5°	43.1	43.5	43.9	44.4	43.9	43.5	43.1	42.6	41.7	40.2	38.9
95°	79.6	80.1	80.5	81.0	80.5	80.1	79.6	79.3	78.3	76.8	75.4
97.5°	122.0	122.2	122.4	122.7	122.4	122.2	122.0	121.7	120.9	119.5	118.1
100°	153.1	153.4	153.9	154.3	153.9	153.4	153.1	152.7	151.5	149.6	147.7
102.5°	184.2	184.7	185.4	186.0	185.4	184.7	184.2	183.6	182.3	180.2	178.1
105°	231.5	232.1	232.7	233.4	232.7	232.1	231.5	230.8	229.9	228.7	227.4
107.5°	282.0	282.0	282.0	281.9	282.0	282.0	282.0	282.1	281.8	281.2	280.5
110°	318.7	318.5	318.3	318.0	318.3	318.5	318.7	318.9	318.7	318.0	317.4



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	354.6	354.2	353.8	353.5	353.8	354.2	354.6	355.0	355.0	354.7	354.4
115°	409.9	409.7	409.5	409.3	409.5	409.7	409.9	410.2	410.4	410.6	410.8
117.5°	466.4	465.6	464.8	463.9	464.8	465.6	466.4	467.2	467.6	467.4	467.2
120°	504.1	503.2	502.4	501.5	502.4	503.2	504.1	504.9	505.3	505.3	505.3
122.5°	541.2	540.5	539.9	539.2	539.9	540.5	541.2	541.9	542.2	542.4	542.6
125°	596.3	596.1	595.9	595.7	595.9	596.1	596.3	596.4	596.8	597.2	597.7
127.5°	651.1	650.6	650.3	649.9	650.3	650.6	651.1	651.5	651.9	652.1	652.2
130°	687.2	686.8	686.4	686.0	686.4	686.8	687.2	687.7	688.0	688.2	688.3
132.5°	721.6	721.0	720.5	719.8	720.5	721.0	721.6	722.2	722.6	722.8	723.0
135°	775.1	774.2	773.4	772.5	773.4	774.2	775.1	775.9	776.3	776.3	776.3
137.5°	827.3	826.2	825.2	824.2	825.2	826.2	827.3	828.3	828.7	828.4	828.2
140°	860.4	859.3	858.3	857.2	858.3	859.3	860.4	861.4	861.8	861.3	860.9
142.5°	892.0	891.0	889.9	888.8	889.9	891.0	892.0	893.1	893.4	893.2	893.0
145°	938.2	937.5	936.9	936.3	936.9	937.5	938.2	938.8	939.1	939.1	939.1
147.5°	981.0	979.6	978.2	976.8	978.2	979.6	981.0	982.4	982.9	982.4	981.8
150°	1008.1	1007.7	1007.3	1006.8	1007.3	1007.7	1008.1	1008.5	1008.7	1008.7	1008.7
152.5°	1034.0	1033.2	1032.5	1031.7	1032.5	1033.2	1034.0	1034.7	1034.8	1034.3	1033.9
155°	1070.3	1069.1	1068.1	1067.1	1068.1	1069.1	1070.3	1071.3	1071.4	1070.5	1069.7
157.5°	1100.8	1099.4	1098.0	1096.6	1098.0	1099.4	1100.8	1102.1	1102.4	1101.5	1100.7
160°	1120.1	1119.1	1118.0	1116.9	1118.0	1119.1	1120.1	1121.2	1121.2	1120.4	1119.6
162.5°	1137.9	1136.7	1135.5	1134.3	1135.5	1136.7	1137.9	1139.2	1139.3	1138.2	1137.2
165°	1161.2	1159.9	1158.7	1157.4	1158.7	1159.9	1161.2	1162.4	1162.6	1161.8	1160.9
167.5°	1179.8	1178.5	1177.1	1175.8	1177.1	1178.5	1179.8	1181.0	1181.1	1179.8	1178.6
170°	1190.1	1188.5	1187.1	1185.6	1187.1	1188.5	1190.1	1191.5	1191.6	1190.3	1189.1
172.5°	1197.8	1196.6	1195.2	1193.9	1195.2	1196.6	1197.8	1199.1	1199.1	1197.9	1196.7
175°	1206.1	1204.6	1203.1	1201.6	1203.1	1204.6	1206.1	1207.5	1207.6	1206.4	1205.1
177.5°	1209.7	1208.5	1207.3	1206.2	1207.3	1208.5	1209.7	1210.9	1210.9	1209.9	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	7.4	7.2	6.7	7.0	6.3	6.2	5.8	5.7	5.7	5.7	5.7
90°	16.1	15.1	13.6	12.2	10.7	9.2	7.6	5.9	4.2	2.6	0.9
92.5°	37.5	36.1	34.3	32.5	30.7	28.9	27.4	26.3	25.1	23.9	22.8
95°	73.9	72.5	70.4	68.2	66.2	64.1	62.9	62.4	62.0	61.5	61.2
97.5°	116.8	115.4	112.4	109.6	106.7	103.9	102.3	102.2	102.0	101.8	101.6
100°	145.8	143.9	141.3	138.6	135.8	133.1	131.8	131.8	131.8	131.8	131.8
102.5°	176.2	174.1	172.7	171.4	169.9	168.5	167.5	166.6	165.8	164.9	164.1
105°	226.1	224.9	223.7	222.3	221.1	219.9	218.8	217.7	216.6	215.6	214.5
107.5°	279.9	279.3	278.3	277.4	276.4	275.4	274.5	273.4	272.3	271.3	270.2
110°	316.8	316.1	315.6	314.9	314.2	313.7	312.8	311.8	310.8	309.7	308.7



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	354.1	353.8	353.0	352.2	351.5	350.6	350.0	349.4	348.8	348.4	347.8
115°	411.0	411.2	410.8	410.4	409.9	409.5	408.9	408.1	407.3	406.4	405.6
117.5°	467.1	466.9	466.6	466.2	465.8	465.4	465.1	464.7	464.3	463.9	463.5
120°	505.3	505.3	505.1	504.9	504.6	504.4	503.9	502.8	501.7	500.7	499.6
122.5°	542.8	542.9	542.4	541.9	541.3	540.7	540.4	540.0	539.6	539.2	538.9
125°	598.0	598.5	598.2	598.0	597.9	597.7	596.9	595.7	594.4	593.1	591.9
127.5°	652.4	652.7	652.4	652.1	652.0	651.7	651.2	650.4	649.8	649.0	648.4
130°	688.6	688.8	688.3	688.0	687.6	687.1	686.4	685.3	684.3	683.2	682.2
132.5°	723.2	723.4	723.5	723.6	723.7	723.8	722.9	721.2	719.5	717.8	716.0
135°	776.3	776.3	776.1	775.9	775.7	775.5	774.8	773.5	772.2	771.0	769.8
137.5°	827.9	827.6	827.3	826.8	826.3	825.9	825.0	823.8	822.6	821.3	820.2
140°	860.4	860.1	859.4	858.8	858.2	857.5	856.7	855.6	854.6	853.6	852.5
142.5°	892.7	892.4	891.6	890.9	890.0	889.3	888.4	887.5	886.6	885.8	884.9
145°	939.1	939.1	938.5	937.8	937.3	936.6	935.9	935.0	934.2	933.4	932.6
147.5°	981.4	980.9	980.3	979.9	979.4	978.9	978.4	978.0	977.5	977.0	976.6
150°	1008.7	1008.7	1007.9	1007.1	1006.3	1005.4	1005.1	1005.3	1005.5	1005.7	1005.9
152.5°	1033.3	1032.8	1032.5	1032.2	1031.8	1031.5	1031.1	1030.9	1030.6	1030.3	1030.0
155°	1068.8	1068.0	1067.8	1067.6	1067.4	1067.1	1067.1	1067.1	1067.1	1067.1	1067.1
157.5°	1099.9	1099.1	1098.9	1098.6	1098.4	1098.3	1098.3	1098.8	1099.3	1099.8	1100.2
160°	1118.7	1117.9	1117.7	1117.5	1117.3	1117.1	1117.3	1117.9	1118.5	1119.2	1119.7
162.5°	1136.2	1135.2	1135.2	1135.1	1135.1	1135.0	1135.3	1135.7	1136.1	1136.6	1137.1
165°	1160.2	1159.3	1159.0	1158.9	1158.7	1158.5	1158.6	1159.0	1159.4	1159.8	1160.3
167.5°	1177.3	1176.0	1176.0	1176.0	1176.0	1176.0	1176.5	1177.3	1178.2	1178.9	1179.8
170°	1187.9	1186.6	1186.6	1186.6	1186.6	1186.6	1187.0	1187.9	1188.6	1189.5	1190.3
172.5°	1195.3	1194.1	1194.1	1194.1	1194.1	1194.1	1194.6	1195.3	1196.2	1197.0	1197.9
175°	1203.8	1202.6	1202.6	1202.6	1202.6	1202.6	1203.0	1203.8	1204.7	1205.5	1206.4
177.5°	1208.0	1206.9	1207.1	1207.2	1207.4	1207.6	1208.0	1208.6	1209.4	1210.0	1210.7
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	5.9	5.7	5.2	5.7	6.0	6.1	6.4	6.6	6.7	6.9	7.1
90°	2.6	4.2	5.9	7.6	9.2	10.7	12.2	13.6	15.1	16.1	17.2
92.5°	23.9	25.1	26.3	27.4	28.9	30.7	32.5	34.3	36.1	37.5	38.9
95°	61.5	62.0	62.4	62.9	64.1	66.2	68.2	70.4	72.5	73.9	75.4
97.5°	101.8	102.0	102.2	102.3	103.9	106.7	109.6	112.4	115.4	116.8	118.1
100°	131.8	131.8	131.8	131.8	133.1	135.8	138.6	141.3	143.9	145.8	147.7
102.5°	164.9	165.8	166.6	167.5	168.5	169.9	171.4	172.7	174.1	176.2	178.1
105°	215.6	216.6	217.7	218.8	219.9	221.1	222.3	223.7	224.9	226.1	227.4
107.5°	271.3	272.3	273.4	274.5	275.4	276.4	277.4	278.3	279.3	279.9	280.5
110°	309.7	310.8	311.8	312.8	313.7	314.2	314.9	315.6	316.1	316.8	317.4





TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	348.4	348.8	349.4	350.0	350.6	351.5	352.2	353.0	353.8	354.1	354.4
115°	406.4	407.3	408.1	408.9	409.5	409.9	410.4	410.8	411.2	411.0	410.8
117.5°	463.9	464.3	464.7	465.1	465.4	465.8	466.2	466.6	466.9	467.1	467.2
120°	500.7	501.7	502.8	503.9	504.4	504.6	504.9	505.1	505.3	505.3	505.3
122.5°	539.2	539.6	540.0	540.4	540.7	541.3	541.9	542.4	542.9	542.8	542.6
125°	593.1	594.4	595.7	596.9	597.7	597.9	598.0	598.2	598.5	598.0	597.7
127.5°	649.0	649.8	650.4	651.2	651.7	652.0	652.1	652.4	652.7	652.4	652.2
130°	683.2	684.3	685.3	686.4	687.1	687.6	688.0	688.3	688.8	688.6	688.3
132.5°	717.8	719.5	721.2	722.9	723.8	723.7	723.6	723.5	723.4	723.2	723.0
135°	771.0	772.2	773.5	774.8	775.5	775.7	775.9	776.1	776.3	776.3	776.3
137.5°	821.3	822.6	823.8	825.0	825.9	826.3	826.8	827.3	827.6	827.9	828.2
140°	853.6	854.6	855.6	856.7	857.5	858.2	858.8	859.4	860.1	860.4	860.9
142.5°	885.8	886.6	887.5	888.4	889.3	890.0	890.9	891.6	892.4	892.7	893.0
145°	933.4	934.2	935.0	935.9	936.6	937.3	937.8	938.5	939.1	939.1	939.1
147.5°	977.0	977.5	978.0	978.4	978.9	979.4	979.9	980.3	980.9	981.4	981.8
150°	1005.7	1005.5	1005.3	1005.1	1005.4	1006.3	1007.1	1007.9	1008.7	1008.7	1008.7
152.5°	1030.3	1030.6	1030.9	1031.1	1031.5	1031.8	1032.2	1032.5	1032.8	1033.3	1033.9
155°	1067.1	1067.1	1067.1	1067.1	1067.1	1067.4	1067.6	1067.8	1068.0	1068.8	1069.7
157.5°	1099.8	1099.3	1098.8	1098.3	1098.3	1098.4	1098.6	1098.9	1099.1	1099.9	1100.7
160°	1119.2	1118.5	1117.9	1117.3	1117.1	1117.3	1117.5	1117.7	1117.9	1118.7	1119.6
162.5°	1136.6	1136.1	1135.7	1135.3	1135.0	1135.1	1135.1	1135.2	1135.2	1136.2	1137.2
165°	1159.8	1159.4	1159.0	1158.6	1158.5	1158.7	1158.9	1159.0	1159.3	1160.2	1160.9
167.5°	1178.9	1178.2	1177.3	1176.5	1176.0	1176.0	1176.0	1176.0	1176.0	1177.3	1178.6
170°	1189.5	1188.6	1187.9	1187.0	1186.6	1186.6	1186.6	1186.6	1186.6	1187.9	1189.1
172.5°	1197.0	1196.2	1195.3	1194.6	1194.1	1194.1	1194.1	1194.1	1194.1	1195.3	1196.7
175°	1205.5	1204.7	1203.8	1203.0	1202.6	1202.6	1202.6	1202.6	1202.6	1203.8	1205.1
177.5°	1210.0	1209.4	1208.6	1208.0	1207.6	1207.4	1207.2	1207.1	1206.9	1208.0	1208.9
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	7.4	7.8	7.6	7.6	7.7	8.0	8.4
90°	18.2	19.2	20.1	20.7	21.3	22.0	22.6
92.5°	40.2	41.7	42.6	43.1	43.5	43.9	44.4
95°	76.8	78.3	79.3	79.6	80.1	80.5	81.0
97.5°	119.5	120.9	121.7	122.0	122.2	122.4	122.7
100°	149.6	151.5	152.7	153.1	153.4	153.9	154.3
102.5°	180.2	182.3	183.6	184.2	184.7	185.4	186.0
105°	228.7	229.9	230.8	231.5	232.1	232.7	233.4
107.5°	281.2	281.8	282.1	282.0	282.0	282.0	281.9
110°	318.0	318.7	318.9	318.7	318.5	318.3	318.0



TEST NUMBER: P333509-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	354.7	355.0	355.0	354.6	354.2	353.8	353.5
115°	410.6	410.4	410.2	409.9	409.7	409.5	409.3
117.5°	467.4	467.6	467.2	466.4	465.6	464.8	463.9
120°	505.3	505.3	504.9	504.1	503.2	502.4	501.5
122.5°	542.4	542.2	541.9	541.2	540.5	539.9	539.2
125°	597.2	596.8	596.4	596.3	596.1	595.9	595.7
127.5°	652.1	651.9	651.5	651.1	650.6	650.3	649.9
130°	688.2	688.0	687.7	687.2	686.8	686.4	686.0
132.5°	722.8	722.6	722.2	721.6	721.0	720.5	719.8
135°	776.3	776.3	775.9	775.1	774.2	773.4	772.5
137.5°	828.4	828.7	828.3	827.3	826.2	825.2	824.2
140°	861.3	861.8	861.4	860.4	859.3	858.3	857.2
142.5°	893.2	893.4	893.1	892.0	891.0	889.9	888.8
145°	939.1	939.1	938.8	938.2	937.5	936.9	936.3
147.5°	982.4	982.9	982.4	981.0	979.6	978.2	976.8
150°	1008.7	1008.7	1008.5	1008.1	1007.7	1007.3	1006.8
152.5°	1034.3	1034.8	1034.7	1034.0	1033.2	1032.5	1031.7
155°	1070.5	1071.4	1071.3	1070.3	1069.1	1068.1	1067.1
157.5°	1101.5	1102.4	1102.1	1100.8	1099.4	1098.0	1096.6
160°	1120.4	1121.2	1121.2	1120.1	1119.1	1118.0	1116.9
162.5°	1138.2	1139.3	1139.2	1137.9	1136.7	1135.5	1134.3
165°	1161.8	1162.6	1162.4	1161.2	1159.9	1158.7	1157.4
167.5°	1179.8	1181.1	1181.0	1179.8	1178.5	1177.1	1175.8
170°	1190.3	1191.6	1191.5	1190.1	1188.5	1187.1	1185.6
172.5°	1197.9	1199.1	1199.1	1197.8	1196.6	1195.2	1193.9
175°	1206.4	1207.6	1207.5	1206.1	1204.6	1203.1	1201.6
177.5°	1209.9	1210.9	1210.9	1209.7	1208.5	1207.3	1206.2
180°	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2	1209.2

(END OF REPORT)