

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333510-830

Luminaire Tested: **S125RDIP-S375D1035U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333510-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1035U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4876.9 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 37.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	48	36	29	24	43	33	26	22	26	21	18	20	17	15	14	12	11	9
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.0
10°-20°	149.1	3.1
20°-30°	236.4	4.8
30°-40°	285.1	5.8
40°-50°	254.6	5.2
50°-60°	195.2	4.0
60°-70°	126.9	2.6
70°-80°	61.7	1.3
80°-90°	17.3	0.4
90°-100°	338.3	6.9
100°-110°	727.2	14.9
110°-120°	682.5	14.0
120°-130°	553.1	11.3
130°-140°	443.9	9.1
140°-150°	334.9	6.9
150°-160°	235.8	4.8
160°-170°	139.0	2.8
170°-180°	45.2	0.9
0°-30°	436.4	8.9
0°-40°	721.4	14.8
0°-60°	1171.3	24.0
0°-90°	1377.1	28.2
90°-120°	1747.9	35.8
90°-150°	3079.8	63.2
90°-180°	3500.0	71.8
0°-180°	4876.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	22	1	22	1	22	15
95°	221	31	221	31	221	313
105°	1247	106	1247	106	1247	1239
115°	1389	190	1389	190	1389	1357
125°	1094	263	1094	263	1094	990
135°	909	309	909	309	909	704
145°	717	359	717	359	717	456
155°	601	410	601	410	601	280
165°	527	448	527	448	527	151
175°	473	466	473	466	473	46
180°	467	467	467	467	467	



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	8.2	8.0	7.6	7.6	7.8	7.7	7.4	7.1	6.9	6.7	6.5
90°	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0	16.0	15.1	13.2
92.5°	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7	245.5	303.3	308.2
95°	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6	815.8	833.7	680.3
97.5°	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6	1032.2	890.3	607.5
100°	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3	1084.9	849.6	542.0
102.5°	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8	1053.3	778.2	492.3
105°	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0	952.3	682.1	444.1
107.5°	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9	849.0	616.1	423.8
110°	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6	790.3	585.2	417.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9	746.7	567.2	417.7
115°	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3	699.1	547.6	420.6
117.5°	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3	670.7	538.0	426.8
120°	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2	654.9	533.5	432.8
122.5°	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9	641.3	529.7	438.1
125°	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4	622.9	525.0	447.0
127.5°	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2	606.0	522.7	456.9
130°	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4	594.7	521.2	463.0
132.5°	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6	585.6	521.2	469.7
135°	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1	574.9	521.2	478.9
137.5°	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4	565.3	522.4	487.4
140°	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1	560.8	523.1	491.2
142.5°	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3	557.0	523.9	493.4
145°	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5	551.4	523.1	495.9
147.5°	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5	545.5	520.7	496.8
150°	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8	541.0	518.4	496.8
152.5°	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2	535.7	515.5	496.1
155°	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9	526.9	510.0	494.0
157.5°	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6	518.6	504.4	491.5
160°	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1	511.9	500.6	489.3
162.5°	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9	505.9	496.1	487.0
165°	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4	496.8	489.3	483.6
167.5°	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4	488.0	482.7	478.3
170°	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4	482.7	478.9	476.1
172.5°	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6	477.4	474.4	473.1
175°	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3	470.4	469.5	469.5
177.5°	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2	467.4	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	6.4	6.0	6.0	5.7	5.1	5.7	5.7	5.7	5.6	5.7	5.7
90°	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9	1.9	3.8	5.7
92.5°	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5	13.9	21.9	33.5
95°	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0	32.0	39.5	49.9
97.5°	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6	52.7	58.0	68.3
100°	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9	67.8	71.5	81.8
102.5°	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7	82.8	85.8	96.9
105°	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3	106.3	111.0	120.5
107.5°	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4	132.3	136.8	144.5
110°	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7	149.6	153.4	161.8



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0	166.9	169.9	178.4
115°	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1	191.9	194.7	203.2
117.5°	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6	215.5	218.5	227.0
120°	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7	230.5	234.3	242.8
122.5°	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6	245.5	248.5	257.0
125°	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4	265.3	270.0	278.5
127.5°	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1	281.9	287.9	298.7
130°	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9	291.7	299.3	311.4
132.5°	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4	299.9	309.0	322.7
135°	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6	312.4	323.7	338.7
137.5°	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0	326.9	337.4	352.5
140°	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1	335.9	347.2	362.2
142.5°	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7	345.7	356.2	371.3
145°	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4	361.3	370.7	383.9
147.5°	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0	377.1	385.2	397.5
150°	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8	387.7	394.3	406.5
152.5°	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3	397.5	403.3	414.0
155°	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2	410.2	415.8	425.3
157.5°	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6	422.4	427.0	435.1
160°	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9	430.0	433.8	440.4
162.5°	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7	436.8	440.5	446.4
165°	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9	446.0	448.8	453.6
167.5°	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7	453.7	455.4	458.1
170°	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2	458.3	459.2	461.1
172.5°	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2	460.5	461.5	463.3
175°	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7	463.8	464.8	465.7
177.5°	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4	465.9	465.9	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	5.8	6.2	6.2	7.0	6.6	7.2	7.4	7.4	7.5	7.7	8.0
90°	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0	17.9	18.9	20.7
92.5°	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7	121.0	91.0	77.2
95°	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6	533.5	417.7	338.7
97.5°	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6	907.2	794.5	684.6
100°	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3	1111.3	1014.3	916.4
102.5°	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8	1236.1	1189.7	1123.4
105°	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0	1306.9	1348.3	1337.9
107.5°	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9	1243.9	1350.2	1399.3
110°	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6	1172.3	1305.0	1385.1



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9	1101.6	1235.8	1330.1
115°	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3	1000.2	1129.1	1231.6
117.5°	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3	930.0	1041.0	1135.1
120°	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2	890.1	993.6	1076.4
122.5°	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9	861.5	953.7	1031.2
125°	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4	823.3	905.1	972.9
127.5°	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2	786.8	863.2	926.6
130°	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4	761.2	834.6	895.8
132.5°	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6	737.1	803.7	862.6
135°	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1	700.0	760.3	813.9
137.5°	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4	666.9	717.0	762.5
140°	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1	647.3	690.6	730.2
142.5°	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3	630.7	668.1	702.3
145°	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5	609.7	638.9	664.3
147.5°	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5	592.2	614.6	633.8
150°	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8	582.4	600.3	617.3
152.5°	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2	572.6	589.0	602.2
155°	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9	558.0	571.2	581.5
157.5°	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6	544.0	554.2	562.3
160°	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1	533.5	542.9	549.5
162.5°	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9	524.4	532.3	538.2
165°	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4	511.0	516.6	521.2
167.5°	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4	497.8	502.1	505.5
170°	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4	490.2	493.0	494.9
172.5°	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6	483.4	485.5	486.6
175°	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3	473.3	475.1	475.1
177.5°	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2	468.9	468.9	468.9
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	8.1	8.0	8.2	8.2	8.2	8.0	8.1	8.0	7.7	7.5	7.4
90°	20.7	20.7	21.7	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0
92.5°	65.1	62.9	61.5	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7
95°	271.9	243.7	236.2	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6
97.5°	626.5	573.7	546.5	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6
100°	851.5	783.8	748.9	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3
102.5°	1054.0	1005.9	968.0	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8
105°	1307.9	1276.9	1258.0	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0
107.5°	1414.6	1414.4	1408.2	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9
110°	1427.4	1445.2	1451.8	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1391.9	1422.7	1439.1	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9
115°	1305.0	1350.2	1376.6	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3
117.5°	1208.5	1255.2	1281.3	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3
120°	1146.0	1191.2	1216.6	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2
122.5°	1093.3	1134.7	1160.2	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9
125°	1025.6	1064.1	1084.9	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4
127.5°	974.4	1008.4	1028.0	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2
130°	942.8	973.8	992.7	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4
132.5°	909.6	940.8	958.0	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6
135°	855.3	886.4	903.2	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1
137.5°	799.6	827.8	843.5	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4
140°	765.0	789.5	803.5	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1
142.5°	731.9	752.5	765.9	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3
145°	686.8	702.9	713.2	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5
147.5°	651.7	664.5	670.5	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5
150°	631.3	642.6	646.4	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8
152.5°	614.1	623.1	626.8	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2
155°	590.9	597.5	600.3	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9
157.5°	569.7	575.0	577.7	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6
160°	556.1	560.8	562.7	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1
162.5°	543.3	547.2	547.6	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9
165°	525.0	526.9	526.9	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4
167.5°	507.4	509.1	508.3	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4
170°	496.8	497.8	497.8	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4
172.5°	487.0	488.7	487.2	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6
175°	475.1	476.1	474.2	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3
177.5°	468.2	468.9	466.7	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	7.4	7.2	6.6	7.0	6.2	6.2	5.8	5.7	5.7	5.6	5.7
90°	16.0	15.1	13.2	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9
92.5°	245.5	303.3	308.2	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5
95°	815.8	833.7	680.3	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0
97.5°	1032.2	890.3	607.5	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6
100°	1084.9	849.6	542.0	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9
102.5°	1053.3	778.2	492.3	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7
105°	952.3	682.1	444.1	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3
107.5°	849.0	616.1	423.8	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4
110°	790.3	585.2	417.7	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	746.7	567.2	417.7	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0
115°	699.1	547.6	420.6	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1
117.5°	670.7	538.0	426.8	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6
120°	654.9	533.5	432.8	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7
122.5°	641.3	529.7	438.1	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6
125°	622.9	525.0	447.0	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4
127.5°	606.0	522.7	456.9	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1
130°	594.7	521.2	463.0	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9
132.5°	585.6	521.2	469.7	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4
135°	574.9	521.2	478.9	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6
137.5°	565.3	522.4	487.4	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0
140°	560.8	523.1	491.2	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1
142.5°	557.0	523.9	493.4	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7
145°	551.4	523.1	495.9	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4
147.5°	545.5	520.7	496.8	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0
150°	541.0	518.4	496.8	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8
152.5°	535.7	515.5	496.1	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3
155°	526.9	510.0	494.0	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2
157.5°	518.6	504.4	491.5	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6
160°	511.9	500.6	489.3	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9
162.5°	505.9	496.1	487.0	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7
165°	496.8	489.3	483.6	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9
167.5°	488.0	482.7	478.3	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7
170°	482.7	478.9	476.1	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2
172.5°	477.4	474.4	473.1	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2
175°	470.4	469.5	469.5	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7
177.5°	467.4	466.7	466.7	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	5.7	5.7	5.1	5.7	6.0	6.0	6.4	6.5	6.7	6.9	7.1
90°	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0
92.5°	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7
95°	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6
97.5°	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6
100°	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3
102.5°	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8
105°	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0
107.5°	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9
110°	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9
115°	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3
117.5°	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3
120°	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2
122.5°	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9
125°	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4
127.5°	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2
130°	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4
132.5°	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6
135°	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1
137.5°	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4
140°	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1
142.5°	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3
145°	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5
147.5°	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5
150°	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8
152.5°	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2
155°	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9
157.5°	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6
160°	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1
162.5°	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9
165°	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4
167.5°	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4
170°	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4
172.5°	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6
175°	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3
177.5°	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	7.4	7.7	7.8	7.6	7.6	8.0	8.2
90°	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333510-830

CATALOG NUMBER: S125RDIP-S375D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)