

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333515-830

Luminaire Tested: **S125RDIP-S375D1205U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333515-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U830-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5304.9 lumens
Efficiency: N/A
Efficacy: 125.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26				
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29	22				
2	84	77	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19				
3	77	68	61	56	69	61	55	51	48	44	40	35	33	31	24	23	21	16				
4	71	60	53	47	63	54	48	43	42	38	35	32	29	26	22	20	18	14				
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16	12				
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11				
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10				
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9				
9	47	36	28	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8				
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.0
10°-20°	149.1	2.8
20°-30°	236.4	4.5
30°-40°	285.1	5.4
40°-50°	254.6	4.8
50°-60°	195.2	3.7
60°-70°	126.9	2.4
70°-80°	61.7	1.2
80°-90°	17.8	0.3
90°-100°	94.3	1.8
100°-110°	278.4	5.2
110°-120°	471.5	8.9
120°-130°	620.5	11.7
130°-140°	695.3	13.1
140°-150°	681.4	12.8
150°-160°	572.4	10.8
160°-170°	380.5	7.2
170°-180°	133.1	2.5
0°-30°	436.4	8.2
0°-40°	721.4	13.6
0°-60°	1171.3	22.1
0°-90°	1377.6	26.0
90°-120°	844.1	15.9
90°-150°	2841.4	53.6
90°-180°	3927.0	74.0
0°-180°	5304.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	26	1	26	1	26	16
95°	94	71	94	71	94	96
105°	272	250	272	250	272	288
115°	476	472	476	472	476	471
125°	693	689	693	689	693	619
135°	899	896	899	896	899	694
145°	1090	1085	1090	1085	1090	680
155°	1242	1242	1242	1242	1242	572
165°	1347	1350	1347	1350	1347	380
175°	1399	1404	1399	1404	1399	133
180°	1407	1407	1407	1407	1407	



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	9.0	8.8	8.5	8.3	8.3	8.5	8.1	7.6	7.4	7.2	7.0
90°	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0	18.8	17.5	15.8
92.5°	51.7	51.2	50.6	50.0	49.6	48.4	46.8	45.2	43.6	42.0	40.0
95°	94.2	93.7	93.2	92.7	92.3	91.1	89.4	87.8	86.1	84.4	81.9
97.5°	142.8	142.5	142.2	141.9	141.7	140.7	139.1	137.5	135.9	134.3	130.9
100°	179.6	179.2	178.6	178.1	177.7	176.3	174.2	171.9	169.8	167.6	164.4
102.5°	216.4	215.7	215.1	214.4	213.7	212.2	209.8	207.4	205.0	202.6	201.0
105°	271.6	270.9	270.1	269.5	268.7	267.6	266.2	264.7	263.3	261.7	260.3
107.5°	328.1	328.2	328.3	328.3	328.4	328.0	327.3	326.5	325.8	325.1	324.0
110°	370.2	370.4	370.7	370.9	371.2	370.9	370.2	369.5	368.7	368.0	367.3



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	411.4	411.8	412.3	412.7	413.1	413.2	412.8	412.6	412.2	411.8	410.9
115°	476.5	476.6	476.9	477.2	477.4	477.7	477.9	478.2	478.4	478.6	478.2
117.5°	540.0	540.9	542.0	542.9	543.8	544.2	544.0	543.8	543.7	543.5	543.0
120°	583.8	584.8	585.7	586.7	587.7	588.1	588.1	588.1	588.1	588.1	588.0
122.5°	627.6	628.4	629.1	629.9	630.7	631.2	631.4	631.6	631.8	632.0	631.3
125°	693.3	693.5	693.8	694.1	694.3	694.7	695.1	695.6	696.1	696.6	696.4
127.5°	756.4	756.9	757.3	757.9	758.4	758.7	758.9	759.2	759.4	759.7	759.4
130°	798.4	798.9	799.5	799.9	800.4	800.8	801.0	801.3	801.5	801.7	801.3
132.5°	837.9	838.6	839.2	839.9	840.7	841.0	841.3	841.6	841.8	842.1	842.2
135°	899.2	900.2	901.2	902.1	903.1	903.6	903.6	903.6	903.6	903.6	903.3
137.5°	959.2	960.5	961.7	962.9	964.1	964.6	964.3	964.0	963.7	963.4	962.9
140°	997.8	999.0	1000.2	1001.5	1002.7	1003.1	1002.6	1002.0	1001.5	1001.1	1000.3
142.5°	1034.6	1035.9	1037.1	1038.2	1039.4	1039.9	1039.6	1039.3	1039.1	1038.8	1037.8
145°	1089.8	1090.5	1091.3	1092.0	1092.7	1093.1	1093.1	1093.1	1093.1	1093.1	1092.3
147.5°	1136.9	1138.6	1140.2	1141.9	1143.5	1144.1	1143.5	1142.9	1142.3	1141.7	1141.1
150°	1172.0	1172.4	1172.9	1173.4	1173.9	1174.1	1174.1	1174.1	1174.1	1174.1	1173.2
152.5°	1200.9	1201.7	1202.6	1203.5	1204.4	1204.5	1203.9	1203.3	1202.8	1202.2	1201.8
155°	1242.1	1243.3	1244.4	1245.7	1246.9	1247.1	1246.0	1245.1	1244.2	1243.1	1242.9
157.5°	1276.5	1278.1	1279.7	1281.3	1282.9	1283.2	1282.2	1281.2	1280.3	1279.3	1279.0
160°	1300.1	1301.3	1302.5	1303.7	1305.0	1305.0	1304.1	1303.2	1302.1	1301.2	1301.0
162.5°	1320.2	1321.6	1323.0	1324.5	1325.9	1326.1	1324.8	1323.7	1322.5	1321.4	1321.3
165°	1347.2	1348.7	1350.1	1351.6	1353.0	1353.3	1352.3	1351.3	1350.4	1349.3	1349.2
167.5°	1368.7	1370.2	1371.7	1373.2	1374.7	1374.7	1373.3	1371.8	1370.4	1368.9	1368.9
170°	1380.1	1381.8	1383.5	1385.2	1386.9	1387.0	1385.5	1384.0	1382.6	1381.1	1381.1
172.5°	1389.7	1391.2	1392.7	1394.2	1395.7	1395.7	1394.3	1392.8	1391.4	1389.9	1389.9
175°	1398.6	1400.3	1402.1	1403.8	1405.5	1405.6	1404.1	1402.7	1401.2	1399.8	1399.8
177.5°	1403.9	1405.3	1406.7	1408.1	1409.4	1409.5	1408.3	1407.1	1406.0	1404.8	1405.0
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	6.8	6.5	6.3	5.9	5.4	5.8	6.0	5.7	5.8	5.8	5.9
90°	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1	3.0	5.0	7.0
92.5°	37.9	35.8	33.6	32.0	30.6	29.2	27.9	26.5	27.9	29.2	30.6
95°	79.5	77.0	74.6	73.1	72.7	72.2	71.6	71.2	71.6	72.2	72.7
97.5°	127.5	124.2	120.8	119.0	118.9	118.7	118.5	118.3	118.5	118.7	118.9
100°	161.3	158.1	155.0	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4
102.5°	199.4	197.8	196.2	194.9	194.0	192.9	192.0	191.1	192.0	192.9	194.0
105°	258.8	257.4	255.9	254.6	253.4	252.1	250.9	249.7	250.9	252.1	253.4
107.5°	322.8	321.7	320.6	319.4	318.2	317.0	315.8	314.5	315.8	317.0	318.2
110°	366.6	365.8	365.0	364.1	362.9	361.7	360.4	359.3	360.4	361.7	362.9



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	410.0	409.1	408.1	407.4	406.7	406.0	405.5	404.8	405.5	406.0	406.7
115°	477.7	477.2	476.6	476.0	474.9	474.0	473.1	472.0	473.1	474.0	474.9
117.5°	542.6	542.2	541.7	541.3	540.8	540.5	540.0	539.5	540.0	540.5	540.8
120°	587.7	587.4	587.2	586.4	585.2	584.0	582.8	581.5	582.8	584.0	585.2
122.5°	630.7	630.1	629.4	628.9	628.5	628.0	627.6	627.2	627.6	628.0	628.5
125°	696.1	695.9	695.6	694.7	693.3	691.8	690.4	688.9	690.4	691.8	693.3
127.5°	759.1	758.8	758.6	758.0	757.1	756.3	755.4	754.7	755.4	756.3	757.1
130°	800.8	800.3	799.8	798.9	797.8	796.5	795.3	794.1	795.3	796.5	797.8
132.5°	842.3	842.4	842.4	841.5	839.5	837.5	835.5	833.5	835.5	837.5	839.5
135°	903.1	902.9	902.7	901.8	900.3	898.9	897.4	896.0	897.4	898.9	900.3
137.5°	962.3	961.8	961.3	960.3	958.8	957.4	956.0	954.6	956.0	957.4	958.8
140°	999.7	998.9	998.2	997.2	996.0	994.8	993.5	992.3	993.5	994.8	996.0
142.5°	1036.9	1035.9	1035.1	1034.1	1033.0	1032.1	1031.0	1030.0	1031.0	1032.1	1033.0
145°	1091.7	1090.9	1090.1	1089.3	1088.4	1087.4	1086.4	1085.4	1086.4	1087.4	1088.4
147.5°	1140.6	1140.0	1139.3	1138.8	1138.3	1137.7	1137.2	1136.7	1137.2	1137.7	1138.3
150°	1172.1	1171.2	1170.3	1169.9	1170.2	1170.4	1170.6	1170.8	1170.6	1170.4	1170.2
152.5°	1201.4	1201.0	1200.6	1200.2	1200.0	1199.6	1199.2	1198.9	1199.2	1199.6	1200.0
155°	1242.6	1242.5	1242.2	1242.1	1242.1	1242.1	1242.1	1242.1	1242.1	1242.1	1242.1
157.5°	1278.8	1278.6	1278.3	1278.5	1279.0	1279.5	1280.1	1280.6	1280.1	1279.5	1279.0
160°	1300.7	1300.4	1300.2	1300.4	1301.2	1301.9	1302.7	1303.3	1302.7	1301.9	1301.2
162.5°	1321.3	1321.2	1321.2	1321.4	1321.9	1322.5	1323.0	1323.5	1323.0	1322.5	1321.9
165°	1348.9	1348.7	1348.4	1348.5	1349.1	1349.5	1350.0	1350.5	1350.0	1349.5	1349.1
167.5°	1368.9	1368.9	1368.9	1369.3	1370.4	1371.3	1372.2	1373.3	1372.2	1371.3	1370.4
170°	1381.1	1381.1	1381.1	1381.7	1382.6	1383.6	1384.6	1385.5	1384.6	1383.6	1382.6
172.5°	1389.9	1389.9	1389.9	1390.4	1391.4	1392.3	1393.4	1394.3	1393.4	1392.3	1391.4
175°	1399.8	1399.8	1399.8	1400.2	1401.2	1402.2	1403.2	1404.1	1403.2	1402.2	1401.2
177.5°	1405.2	1405.4	1405.6	1406.1	1406.8	1407.6	1408.4	1409.2	1408.4	1407.6	1406.8
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	6.1	6.5	6.7	7.4	7.2	7.7	7.9	8.0	8.2	8.5	8.5
90°	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0	21.2	22.4	23.4
92.5°	32.0	33.6	35.8	37.9	40.0	42.0	43.6	45.2	46.8	48.4	49.6
95°	73.1	74.6	77.0	79.5	81.9	84.4	86.1	87.8	89.4	91.1	92.3
97.5°	119.0	120.8	124.2	127.5	130.9	134.3	135.9	137.5	139.1	140.7	141.7
100°	153.4	155.0	158.1	161.3	164.4	167.6	169.8	171.9	174.2	176.3	177.7
102.5°	194.9	196.2	197.8	199.4	201.0	202.6	205.0	207.4	209.8	212.2	213.7
105°	254.6	255.9	257.4	258.8	260.3	261.7	263.3	264.7	266.2	267.6	268.7
107.5°	319.4	320.6	321.7	322.8	324.0	325.1	325.8	326.5	327.3	328.0	328.4
110°	364.1	365.0	365.8	366.6	367.3	368.0	368.7	369.5	370.2	370.9	371.2



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	407.4	408.1	409.1	410.0	410.9	411.8	412.2	412.6	412.8	413.2	413.1
115°	476.0	476.6	477.2	477.7	478.2	478.6	478.4	478.2	477.9	477.7	477.4
117.5°	541.3	541.7	542.2	542.6	543.0	543.5	543.7	543.8	544.0	544.2	543.8
120°	586.4	587.2	587.4	587.7	588.0	588.1	588.1	588.1	588.1	588.1	587.7
122.5°	628.9	629.4	630.1	630.7	631.3	632.0	631.8	631.6	631.4	631.2	630.7
125°	694.7	695.6	695.9	696.1	696.4	696.6	696.1	695.6	695.1	694.7	694.3
127.5°	758.0	758.6	758.8	759.1	759.4	759.7	759.4	759.2	758.9	758.7	758.4
130°	798.9	799.8	800.3	800.8	801.3	801.7	801.5	801.3	801.0	800.8	800.4
132.5°	841.5	842.4	842.4	842.3	842.2	842.1	841.8	841.6	841.3	841.0	840.7
135°	901.8	902.7	902.9	903.1	903.3	903.6	903.6	903.6	903.6	903.6	903.1
137.5°	960.3	961.3	961.8	962.3	962.9	963.4	963.7	964.0	964.3	964.6	964.1
140°	997.2	998.2	998.9	999.7	1000.3	1001.1	1001.5	1002.0	1002.6	1003.1	1002.7
142.5°	1034.1	1035.1	1035.9	1036.9	1037.8	1038.8	1039.1	1039.3	1039.6	1039.9	1039.4
145°	1089.3	1090.1	1090.9	1091.7	1092.3	1093.1	1093.1	1093.1	1093.1	1093.1	1092.7
147.5°	1138.8	1139.3	1140.0	1140.6	1141.1	1141.7	1142.3	1142.9	1143.5	1144.1	1143.5
150°	1169.9	1170.3	1171.2	1172.1	1173.2	1174.1	1174.1	1174.1	1174.1	1174.1	1173.9
152.5°	1200.2	1200.6	1201.0	1201.4	1201.8	1202.2	1202.8	1203.3	1203.9	1204.5	1204.4
155°	1242.1	1242.2	1242.5	1242.6	1242.9	1243.1	1244.2	1245.1	1246.0	1247.1	1246.9
157.5°	1278.5	1278.3	1278.6	1278.8	1279.0	1279.3	1280.3	1281.2	1282.2	1283.2	1282.9
160°	1300.4	1300.2	1300.4	1300.7	1301.0	1301.2	1302.1	1303.2	1304.1	1305.0	1305.0
162.5°	1321.4	1321.2	1321.2	1321.3	1321.3	1321.4	1322.5	1323.7	1324.8	1326.1	1325.9
165°	1348.5	1348.4	1348.7	1348.9	1349.2	1349.3	1350.4	1351.3	1352.3	1353.3	1353.0
167.5°	1369.3	1368.9	1368.9	1368.9	1368.9	1368.9	1370.4	1371.8	1373.3	1374.7	1374.7
170°	1381.7	1381.1	1381.1	1381.1	1381.1	1381.1	1382.6	1384.0	1385.5	1387.0	1386.9
172.5°	1390.4	1389.9	1389.9	1389.9	1389.9	1389.9	1391.4	1392.8	1394.3	1395.7	1395.7
175°	1400.2	1399.8	1399.8	1399.8	1399.8	1399.8	1401.2	1402.7	1404.1	1405.6	1405.5
177.5°	1406.1	1405.6	1405.4	1405.2	1405.0	1404.8	1406.0	1407.1	1408.3	1409.5	1409.4
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	8.9	8.8	9.0	9.0	9.0	8.8	8.9	8.5	8.5	8.2	8.0
90°	24.1	24.8	25.5	26.3	25.5	24.8	24.1	23.4	22.4	21.2	20.0
92.5°	50.0	50.6	51.2	51.7	51.2	50.6	50.0	49.6	48.4	46.8	45.2
95°	92.7	93.2	93.7	94.2	93.7	93.2	92.7	92.3	91.1	89.4	87.8
97.5°	141.9	142.2	142.5	142.8	142.5	142.2	141.9	141.7	140.7	139.1	137.5
100°	178.1	178.6	179.2	179.6	179.2	178.6	178.1	177.7	176.3	174.2	171.9
102.5°	214.4	215.1	215.7	216.4	215.7	215.1	214.4	213.7	212.2	209.8	207.4
105°	269.5	270.1	270.9	271.6	270.9	270.1	269.5	268.7	267.6	266.2	264.7
107.5°	328.3	328.3	328.2	328.1	328.2	328.3	328.3	328.4	328.0	327.3	326.5
110°	370.9	370.7	370.4	370.2	370.4	370.7	370.9	371.2	370.9	370.2	369.5



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	412.7	412.3	411.8	411.4	411.8	412.3	412.7	413.1	413.2	412.8	412.6
115°	477.2	476.9	476.6	476.5	476.6	476.9	477.2	477.4	477.7	477.9	478.2
117.5°	542.9	542.0	540.9	540.0	540.9	542.0	542.9	543.8	544.2	544.0	543.8
120°	586.7	585.7	584.8	583.8	584.8	585.7	586.7	587.7	588.1	588.1	588.1
122.5°	629.9	629.1	628.4	627.6	628.4	629.1	629.9	630.7	631.2	631.4	631.6
125°	694.1	693.8	693.5	693.3	693.5	693.8	694.1	694.3	694.7	695.1	695.6
127.5°	757.9	757.3	756.9	756.4	756.9	757.3	757.9	758.4	758.7	758.9	759.2
130°	799.9	799.5	798.9	798.4	798.9	799.5	799.9	800.4	800.8	801.0	801.3
132.5°	839.9	839.2	838.6	837.9	838.6	839.2	839.9	840.7	841.0	841.3	841.6
135°	902.1	901.2	900.2	899.2	900.2	901.2	902.1	903.1	903.6	903.6	903.6
137.5°	962.9	961.7	960.5	959.2	960.5	961.7	962.9	964.1	964.6	964.3	964.0
140°	1001.5	1000.2	999.0	997.8	999.0	1000.2	1001.5	1002.7	1003.1	1002.6	1002.0
142.5°	1038.2	1037.1	1035.9	1034.6	1035.9	1037.1	1038.2	1039.4	1039.9	1039.6	1039.3
145°	1092.0	1091.3	1090.5	1089.8	1090.5	1091.3	1092.0	1092.7	1093.1	1093.1	1093.1
147.5°	1141.9	1140.2	1138.6	1136.9	1138.6	1140.2	1141.9	1143.5	1144.1	1143.5	1142.9
150°	1173.4	1172.9	1172.4	1172.0	1172.4	1172.9	1173.4	1173.9	1174.1	1174.1	1174.1
152.5°	1203.5	1202.6	1201.7	1200.9	1201.7	1202.6	1203.5	1204.4	1204.5	1203.9	1203.3
155°	1245.7	1244.4	1243.3	1242.1	1243.3	1244.4	1245.7	1246.9	1247.1	1246.0	1245.1
157.5°	1281.3	1279.7	1278.1	1276.5	1278.1	1279.7	1281.3	1282.9	1283.2	1282.2	1281.2
160°	1303.7	1302.5	1301.3	1300.1	1301.3	1302.5	1303.7	1305.0	1305.0	1304.1	1303.2
162.5°	1324.5	1323.0	1321.6	1320.2	1321.6	1323.0	1324.5	1325.9	1326.1	1324.8	1323.7
165°	1351.6	1350.1	1348.7	1347.2	1348.7	1350.1	1351.6	1353.0	1353.3	1352.3	1351.3
167.5°	1373.2	1371.7	1370.2	1368.7	1370.2	1371.7	1373.2	1374.7	1374.7	1373.3	1371.8
170°	1385.2	1383.5	1381.8	1380.1	1381.8	1383.5	1385.2	1386.9	1387.0	1385.5	1384.0
172.5°	1394.2	1392.7	1391.2	1389.7	1391.2	1392.7	1394.2	1395.7	1395.7	1394.3	1392.8
175°	1403.8	1402.1	1400.3	1398.6	1400.3	1402.1	1403.8	1405.5	1405.6	1404.1	1402.7
177.5°	1408.1	1406.7	1405.3	1403.9	1405.3	1406.7	1408.1	1409.4	1409.5	1408.3	1407.1
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	7.9	7.7	7.2	7.4	6.7	6.5	6.1	5.9	5.8	5.8	5.7
90°	18.8	17.5	15.8	14.1	12.4	10.7	8.9	7.0	5.0	3.0	1.1
92.5°	43.6	42.0	40.0	37.9	35.8	33.6	32.0	30.6	29.2	27.9	26.5
95°	86.1	84.4	81.9	79.5	77.0	74.6	73.1	72.7	72.2	71.6	71.2
97.5°	135.9	134.3	130.9	127.5	124.2	120.8	119.0	118.9	118.7	118.5	118.3
100°	169.8	167.6	164.4	161.3	158.1	155.0	153.4	153.4	153.4	153.4	153.4
102.5°	205.0	202.6	201.0	199.4	197.8	196.2	194.9	194.0	192.9	192.0	191.1
105°	263.3	261.7	260.3	258.8	257.4	255.9	254.6	253.4	252.1	250.9	249.7
107.5°	325.8	325.1	324.0	322.8	321.7	320.6	319.4	318.2	317.0	315.8	314.5
110°	368.7	368.0	367.3	366.6	365.8	365.0	364.1	362.9	361.7	360.4	359.3



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	412.2	411.8	410.9	410.0	409.1	408.1	407.4	406.7	406.0	405.5	404.8
115°	478.4	478.6	478.2	477.7	477.2	476.6	476.0	474.9	474.0	473.1	472.0
117.5°	543.7	543.5	543.0	542.6	542.2	541.7	541.3	540.8	540.5	540.0	539.5
120°	588.1	588.1	588.0	587.7	587.4	587.2	586.4	585.2	584.0	582.8	581.5
122.5°	631.8	632.0	631.3	630.7	630.1	629.4	628.9	628.5	628.0	627.6	627.2
125°	696.1	696.6	696.4	696.1	695.9	695.6	694.7	693.3	691.8	690.4	688.9
127.5°	759.4	759.7	759.4	759.1	758.8	758.6	758.0	757.1	756.3	755.4	754.7
130°	801.5	801.7	801.3	800.8	800.3	799.8	798.9	797.8	796.5	795.3	794.1
132.5°	841.8	842.1	842.2	842.3	842.4	842.4	841.5	839.5	837.5	835.5	833.5
135°	903.6	903.6	903.3	903.1	902.9	902.7	901.8	900.3	898.9	897.4	896.0
137.5°	963.7	963.4	962.9	962.3	961.8	961.3	960.3	958.8	957.4	956.0	954.6
140°	1001.5	1001.1	1000.3	999.7	998.9	998.2	997.2	996.0	994.8	993.5	992.3
142.5°	1039.1	1038.8	1037.8	1036.9	1035.9	1035.1	1034.1	1033.0	1032.1	1031.0	1030.0
145°	1093.1	1093.1	1092.3	1091.7	1090.9	1090.1	1089.3	1088.4	1087.4	1086.4	1085.4
147.5°	1142.3	1141.7	1141.1	1140.6	1140.0	1139.3	1138.8	1138.3	1137.7	1137.2	1136.7
150°	1174.1	1174.1	1173.2	1172.1	1171.2	1170.3	1169.9	1170.2	1170.4	1170.6	1170.8
152.5°	1202.8	1202.2	1201.8	1201.4	1201.0	1200.6	1200.2	1200.0	1199.6	1199.2	1198.9
155°	1244.2	1243.1	1242.9	1242.6	1242.5	1242.2	1242.1	1242.1	1242.1	1242.1	1242.1
157.5°	1280.3	1279.3	1279.0	1278.8	1278.6	1278.3	1278.5	1279.0	1279.5	1280.1	1280.6
160°	1302.1	1301.2	1301.0	1300.7	1300.4	1300.2	1300.4	1301.2	1301.9	1302.7	1303.3
162.5°	1322.5	1321.4	1321.3	1321.3	1321.2	1321.2	1321.4	1321.9	1322.5	1323.0	1323.5
165°	1350.4	1349.3	1349.2	1348.9	1348.7	1348.4	1348.5	1349.1	1349.5	1350.0	1350.5
167.5°	1370.4	1368.9	1368.9	1368.9	1368.9	1368.9	1369.3	1370.4	1371.3	1372.2	1373.3
170°	1382.6	1381.1	1381.1	1381.1	1381.1	1381.1	1381.7	1382.6	1383.6	1384.6	1385.5
172.5°	1391.4	1389.9	1389.9	1389.9	1389.9	1389.9	1390.4	1391.4	1392.3	1393.4	1394.3
175°	1401.2	1399.8	1399.8	1399.8	1399.8	1399.8	1400.2	1401.2	1402.2	1403.2	1404.1
177.5°	1406.0	1404.8	1405.0	1405.2	1405.4	1405.6	1406.1	1406.8	1407.6	1408.4	1409.2
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	6.0	5.8	5.4	5.9	6.3	6.5	6.8	7.0	7.2	7.4	7.6
90°	3.0	5.0	7.0	8.9	10.7	12.4	14.1	15.8	17.5	18.8	20.0
92.5°	27.9	29.2	30.6	32.0	33.6	35.8	37.9	40.0	42.0	43.6	45.2
95°	71.6	72.2	72.7	73.1	74.6	77.0	79.5	81.9	84.4	86.1	87.8
97.5°	118.5	118.7	118.9	119.0	120.8	124.2	127.5	130.9	134.3	135.9	137.5
100°	153.4	153.4	153.4	153.4	155.0	158.1	161.3	164.4	167.6	169.8	171.9
102.5°	192.0	192.9	194.0	194.9	196.2	197.8	199.4	201.0	202.6	205.0	207.4
105°	250.9	252.1	253.4	254.6	255.9	257.4	258.8	260.3	261.7	263.3	264.7
107.5°	315.8	317.0	318.2	319.4	320.6	321.7	322.8	324.0	325.1	325.8	326.5
110°	360.4	361.7	362.9	364.1	365.0	365.8	366.6	367.3	368.0	368.7	369.5



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	405.5	406.0	406.7	407.4	408.1	409.1	410.0	410.9	411.8	412.2	412.6
115°	473.1	474.0	474.9	476.0	476.6	477.2	477.7	478.2	478.6	478.4	478.2
117.5°	540.0	540.5	540.8	541.3	541.7	542.2	542.6	543.0	543.5	543.7	543.8
120°	582.8	584.0	585.2	586.4	587.2	587.4	587.7	588.0	588.1	588.1	588.1
122.5°	627.6	628.0	628.5	628.9	629.4	630.1	630.7	631.3	632.0	631.8	631.6
125°	690.4	691.8	693.3	694.7	695.6	695.9	696.1	696.4	696.6	696.1	695.6
127.5°	755.4	756.3	757.1	758.0	758.6	758.8	759.1	759.4	759.7	759.4	759.2
130°	795.3	796.5	797.8	798.9	799.8	800.3	800.8	801.3	801.7	801.5	801.3
132.5°	835.5	837.5	839.5	841.5	842.4	842.4	842.3	842.2	842.1	841.8	841.6
135°	897.4	898.9	900.3	901.8	902.7	902.9	903.1	903.3	903.6	903.6	903.6
137.5°	956.0	957.4	958.8	960.3	961.3	961.8	962.3	962.9	963.4	963.7	964.0
140°	993.5	994.8	996.0	997.2	998.2	998.9	999.7	1000.3	1001.1	1001.5	1002.0
142.5°	1031.0	1032.1	1033.0	1034.1	1035.1	1035.9	1036.9	1037.8	1038.8	1039.1	1039.3
145°	1086.4	1087.4	1088.4	1089.3	1090.1	1090.9	1091.7	1092.3	1093.1	1093.1	1093.1
147.5°	1137.2	1137.7	1138.3	1138.8	1139.3	1140.0	1140.6	1141.1	1141.7	1142.3	1142.9
150°	1170.6	1170.4	1170.2	1169.9	1170.3	1171.2	1172.1	1173.2	1174.1	1174.1	1174.1
152.5°	1199.2	1199.6	1200.0	1200.2	1200.6	1201.0	1201.4	1201.8	1202.2	1202.8	1203.3
155°	1242.1	1242.1	1242.1	1242.1	1242.2	1242.5	1242.6	1242.9	1243.1	1244.2	1245.1
157.5°	1280.1	1279.5	1279.0	1278.5	1278.3	1278.6	1278.8	1279.0	1279.3	1280.3	1281.2
160°	1302.7	1301.9	1301.2	1300.4	1300.2	1300.4	1300.7	1301.0	1301.2	1302.1	1303.2
162.5°	1323.0	1322.5	1321.9	1321.4	1321.2	1321.2	1321.3	1321.3	1321.4	1322.5	1323.7
165°	1350.0	1349.5	1349.1	1348.5	1348.4	1348.7	1348.9	1349.2	1349.3	1350.4	1351.3
167.5°	1372.2	1371.3	1370.4	1369.3	1368.9	1368.9	1368.9	1368.9	1368.9	1370.4	1371.8
170°	1384.6	1383.6	1382.6	1381.7	1381.1	1381.1	1381.1	1381.1	1381.1	1382.6	1384.0
172.5°	1393.4	1392.3	1391.4	1390.4	1389.9	1389.9	1389.9	1389.9	1389.9	1391.4	1392.8
175°	1403.2	1402.2	1401.2	1400.2	1399.8	1399.8	1399.8	1399.8	1399.8	1401.2	1402.7
177.5°	1408.4	1407.6	1406.8	1406.1	1405.6	1405.4	1405.2	1405.0	1404.8	1406.0	1407.1
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	8.1	8.5	8.3	8.3	8.5	8.8	9.0
90°	21.2	22.4	23.4	24.1	24.8	25.5	26.3
92.5°	46.8	48.4	49.6	50.0	50.6	51.2	51.7
95°	89.4	91.1	92.3	92.7	93.2	93.7	94.2
97.5°	139.1	140.7	141.7	141.9	142.2	142.5	142.8
100°	174.2	176.3	177.7	178.1	178.6	179.2	179.6
102.5°	209.8	212.2	213.7	214.4	215.1	215.7	216.4
105°	266.2	267.6	268.7	269.5	270.1	270.9	271.6
107.5°	327.3	328.0	328.4	328.3	328.3	328.2	328.1
110°	370.2	370.9	371.2	370.9	370.7	370.4	370.2



TEST NUMBER: P333515-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	412.8	413.2	413.1	412.7	412.3	411.8	411.4
115°	477.9	477.7	477.4	477.2	476.9	476.6	476.5
117.5°	544.0	544.2	543.8	542.9	542.0	540.9	540.0
120°	588.1	588.1	587.7	586.7	585.7	584.8	583.8
122.5°	631.4	631.2	630.7	629.9	629.1	628.4	627.6
125°	695.1	694.7	694.3	694.1	693.8	693.5	693.3
127.5°	758.9	758.7	758.4	757.9	757.3	756.9	756.4
130°	801.0	800.8	800.4	799.9	799.5	798.9	798.4
132.5°	841.3	841.0	840.7	839.9	839.2	838.6	837.9
135°	903.6	903.6	903.1	902.1	901.2	900.2	899.2
137.5°	964.3	964.6	964.1	962.9	961.7	960.5	959.2
140°	1002.6	1003.1	1002.7	1001.5	1000.2	999.0	997.8
142.5°	1039.6	1039.9	1039.4	1038.2	1037.1	1035.9	1034.6
145°	1093.1	1093.1	1092.7	1092.0	1091.3	1090.5	1089.8
147.5°	1143.5	1144.1	1143.5	1141.9	1140.2	1138.6	1136.9
150°	1174.1	1174.1	1173.9	1173.4	1172.9	1172.4	1172.0
152.5°	1203.9	1204.5	1204.4	1203.5	1202.6	1201.7	1200.9
155°	1246.0	1247.1	1246.9	1245.7	1244.4	1243.3	1242.1
157.5°	1282.2	1283.2	1282.9	1281.3	1279.7	1278.1	1276.5
160°	1304.1	1305.0	1305.0	1303.7	1302.5	1301.3	1300.1
162.5°	1324.8	1326.1	1325.9	1324.5	1323.0	1321.6	1320.2
165°	1352.3	1353.3	1353.0	1351.6	1350.1	1348.7	1347.2
167.5°	1373.3	1374.7	1374.7	1373.2	1371.7	1370.2	1368.7
170°	1385.5	1387.0	1386.9	1385.2	1383.5	1381.8	1380.1
172.5°	1394.3	1395.7	1395.7	1394.2	1392.7	1391.2	1389.7
175°	1404.1	1405.6	1405.5	1403.8	1402.1	1400.3	1398.6
177.5°	1408.3	1409.5	1409.4	1408.1	1406.7	1405.3	1403.9
180°	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4	1407.4

(END OF REPORT)