

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333516-830

Luminaire Tested: **S125RDIP-S375D1205U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333516-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1205U830-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5451.2 lumens  
Efficiency: N/A  
Efficacy: 129.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 42.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18
3	77	68	61	56	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	14
5	65	54	46	40	57	48	41	37	38	33	30	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	11
7	55	43	36	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	13	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.9	0.9
10°-20°	149.1	2.7
20°-30°	236.4	4.3
30°-40°	285.1	5.2
40°-50°	254.6	4.7
50°-60°	195.2	3.6
60°-70°	126.9	2.3
70°-80°	61.7	1.1
80°-90°	17.7	0.3
90°-100°	393.7	7.2
100°-110°	846.4	15.5
110°-120°	794.4	14.6
120°-130°	643.8	11.8
130°-140°	516.6	9.5
140°-150°	389.9	7.2
150°-160°	274.4	5.0
160°-170°	161.8	3.0
170°-180°	52.6	1.0
0°-30°	436.4	8.0
0°-40°	721.4	13.2
0°-60°	1171.3	21.5
0°-90°	1377.5	25.3
90°-120°	2034.5	37.3
90°-150°	3584.8	65.8
90°-180°	4074.0	74.7
0°-180°	5451.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	25	1	25	1	25	18
95°	257	36	257	36	257	365
105°	1451	124	1451	124	1451	1442
115°	1616	221	1616	221	1616	1579
125°	1274	307	1274	307	1274	1152
135°	1058	359	1058	359	1058	820
145°	834	418	834	418	834	530
155°	700	478	700	478	700	326
165°	613	521	613	521	613	175
175°	551	542	551	542	551	54
180°	543	543	543	543	543	



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	8.9	8.7	8.3	8.3	8.5	8.4	8.0	7.6	7.4	7.2	6.9
90°	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7	18.7	17.5	15.4
92.5°	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1	285.9	353.1	358.8
95°	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4	949.5	970.3	791.8
97.5°	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7	1201.5	1036.2	707.1
100°	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1	1262.7	988.9	630.8
102.5°	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8	1226.0	905.7	573.0
105°	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2	1108.3	794.0	516.9
107.5°	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6	988.4	717.1	493.2
110°	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5	919.9	681.2	486.3



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7	869.1	660.2	486.3
115°	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5	813.7	637.4	489.6
117.5°	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1	780.6	626.2	496.8
120°	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7	762.2	620.9	503.8
122.5°	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0	746.5	616.6	509.9
125°	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6	725.0	611.1	520.2
127.5°	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5	705.3	608.5	531.8
130°	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7	692.2	606.7	538.9
132.5°	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7	681.6	606.7	546.7
135°	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2	669.2	606.7	557.4
137.5°	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2	658.0	608.0	567.3
140°	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0	652.7	608.9	571.7
142.5°	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6	648.4	609.8	574.3
145°	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7	641.8	608.9	577.2
147.5°	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8	635.0	606.1	578.2
150°	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8	629.7	603.4	578.2
152.5°	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1	623.6	599.9	577.4
155°	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9	613.3	593.6	575.0
157.5°	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8	603.7	587.0	572.1
160°	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0	595.8	582.7	569.5
162.5°	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4	588.8	577.4	566.8
165°	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0	578.2	569.5	562.9
167.5°	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3	568.0	561.8	556.8
170°	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3	561.8	557.4	554.2
172.5°	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4	555.7	552.2	550.6
175°	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9	547.6	546.5	546.5
177.5°	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0	544.1	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	6.9	6.4	6.4	5.9	5.3	5.7	5.8	5.7	5.7	5.7	5.8
90°	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1	2.2	4.3	6.6
92.5°	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4	16.2	25.4	39.0
95°	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1	37.2	46.0	58.1
97.5°	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0	61.4	67.5	79.6
100°	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6	78.9	83.2	95.3
102.5°	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1	96.4	99.9	112.8
105°	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8	123.8	129.2	140.2
107.5°	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7	154.0	159.2	168.2
110°	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9	174.2	178.5	188.4





TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1	194.3	197.7	207.6
115°	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2	223.4	226.7	236.6
117.5°	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5	250.8	254.3	264.2
120°	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0	268.3	272.7	282.6
122.5°	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4	285.9	289.4	299.2
125°	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6	308.9	314.3	324.1
127.5°	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8	328.1	335.2	347.6
130°	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2	339.5	348.3	362.5
132.5°	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0	349.1	359.7	375.7
135°	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2	363.6	376.7	394.3
137.5°	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2	380.5	392.8	410.3
140°	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7	391.0	404.2	421.7
142.5°	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9	402.4	414.6	432.2
145°	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4	420.6	431.5	446.9
147.5°	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6	438.9	448.4	462.6
150°	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0	451.2	458.9	473.2
152.5°	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3	462.6	469.4	481.9
155°	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5	477.5	484.1	495.0
157.5°	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0	491.7	497.0	506.4
160°	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6	500.5	504.9	512.6
162.5°	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4	508.4	512.7	519.5
165°	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3	519.2	522.5	527.9
167.5°	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2	528.1	530.1	533.1
170°	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4	533.4	534.4	536.7
172.5°	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0	536.0	537.1	539.2
175°	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2	539.9	541.0	542.2
177.5°	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1	542.3	542.3	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	6.1	6.5	6.6	7.4	7.1	7.7	7.9	7.9	8.2	8.4	8.7
90°	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7	20.8	21.9	24.1
92.5°	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1	140.8	106.0	89.8
95°	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4	620.9	486.3	394.3
97.5°	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7	1056.0	924.8	796.8
100°	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1	1293.5	1180.6	1066.7
102.5°	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8	1438.9	1384.8	1307.7
105°	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2	1521.3	1569.4	1557.4
107.5°	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6	1447.8	1571.6	1628.8
110°	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5	1364.6	1519.0	1612.1



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7	1282.2	1438.4	1548.1
115°	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5	1164.2	1314.2	1433.6
117.5°	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1	1082.5	1211.7	1321.3
120°	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7	1036.0	1156.5	1252.9
122.5°	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0	1002.8	1110.1	1200.3
125°	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6	958.3	1053.6	1132.5
127.5°	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5	915.8	1004.8	1078.6
130°	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7	886.0	971.5	1042.6
132.5°	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7	858.0	935.5	1004.1
135°	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2	814.8	885.0	947.3
137.5°	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2	776.3	834.5	887.6
140°	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0	753.5	803.9	849.9
142.5°	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6	734.2	777.6	817.5
145°	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7	709.6	743.7	773.2
147.5°	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8	689.3	715.4	737.7
150°	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8	678.0	698.7	718.4
152.5°	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1	666.6	685.6	701.0
155°	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9	649.4	664.8	676.8
157.5°	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8	633.2	645.1	654.5
160°	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0	620.9	631.9	639.6
162.5°	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4	610.5	619.6	626.4
165°	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0	594.7	601.2	606.7
167.5°	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3	579.4	584.4	588.3
170°	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3	570.6	573.9	576.1
172.5°	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4	562.7	565.1	566.5
175°	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9	550.9	553.1	553.1
177.5°	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0	545.8	545.8	545.8
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	8.9	8.7	8.9	8.9	8.9	8.7	8.9	8.7	8.4	8.2	7.9
90°	24.1	24.1	25.2	25.2	25.2	24.1	24.1	24.1	21.9	20.8	19.7
92.5°	75.8	73.1	71.6	69.8	71.6	73.1	75.8	89.8	106.0	140.8	194.1
95°	316.5	283.6	274.9	257.4	274.9	283.6	316.5	394.3	486.3	620.9	787.4
97.5°	729.2	667.9	636.1	622.1	636.1	667.9	729.2	796.8	924.8	1056.0	1172.7
100°	991.2	912.3	871.8	854.2	871.8	912.3	991.2	1066.7	1180.6	1293.5	1347.1
102.5°	1226.8	1170.7	1126.7	1113.6	1126.7	1170.7	1226.8	1307.7	1384.8	1438.9	1405.8
105°	1522.3	1486.2	1464.2	1451.1	1464.2	1486.2	1522.3	1557.4	1569.4	1521.3	1371.2
107.5°	1646.5	1646.3	1639.1	1630.3	1639.1	1646.3	1646.5	1628.8	1571.6	1447.8	1247.6
110°	1661.4	1682.2	1689.9	1689.9	1689.9	1682.2	1661.4	1612.1	1519.0	1364.6	1156.5



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1620.2	1656.0	1675.0	1682.9	1675.0	1656.0	1620.2	1548.1	1438.4	1282.2	1084.7
115°	1519.0	1571.6	1602.2	1616.5	1602.2	1571.6	1519.0	1433.6	1314.2	1164.2	994.5
117.5°	1406.7	1461.0	1491.5	1500.2	1491.5	1461.0	1406.7	1321.3	1211.7	1082.5	936.1
120°	1334.0	1386.5	1416.1	1424.8	1416.1	1386.5	1334.0	1252.9	1156.5	1036.0	904.7
122.5°	1272.6	1320.8	1350.4	1358.3	1350.4	1320.8	1272.6	1200.3	1110.1	1002.8	881.0
125°	1193.7	1238.7	1262.7	1273.8	1262.7	1238.7	1193.7	1132.5	1053.6	958.3	846.6
127.5°	1134.2	1173.8	1196.7	1201.5	1196.7	1173.8	1134.2	1078.6	1004.8	915.8	811.5
130°	1097.4	1133.5	1155.5	1162.0	1155.5	1133.5	1097.4	1042.6	971.5	886.0	789.7
132.5°	1058.9	1095.0	1115.1	1122.6	1115.1	1095.0	1058.9	1004.1	935.5	858.0	767.7
135°	995.5	1031.7	1051.4	1058.0	1051.4	1031.7	995.5	947.3	885.0	814.8	739.2
137.5°	930.7	963.6	981.8	988.9	981.8	963.6	930.7	887.6	834.5	776.3	715.2
140°	890.4	918.9	935.3	940.8	935.3	918.9	890.4	849.9	803.9	753.5	702.0
142.5°	851.9	875.9	891.5	896.1	891.5	875.9	851.9	817.5	777.6	734.2	690.6
145°	799.5	818.1	830.2	834.5	830.2	818.1	799.5	773.2	743.7	709.6	675.7
147.5°	758.6	773.5	780.4	782.4	780.4	773.5	758.6	737.7	715.4	689.3	661.8
150°	734.9	748.0	752.4	753.5	752.4	748.0	734.9	718.4	698.7	678.0	653.8
152.5°	714.7	725.2	729.6	730.8	729.6	725.2	714.7	701.0	685.6	666.6	645.1
155°	687.8	695.4	698.7	699.8	698.7	695.4	687.8	676.8	664.8	649.4	631.9
157.5°	663.0	669.4	672.4	672.2	672.4	669.4	663.0	654.5	645.1	633.2	618.8
160°	647.2	652.7	655.0	653.8	655.0	652.7	647.2	639.6	631.9	620.9	610.0
162.5°	632.4	637.0	637.4	637.2	637.4	637.0	632.4	626.4	619.6	610.5	600.4
165°	611.1	613.3	613.3	613.3	613.3	613.3	611.1	606.7	601.2	594.7	587.0
167.5°	590.5	592.5	591.6	591.4	591.6	592.5	590.5	588.3	584.4	579.4	574.3
170°	578.2	579.4	579.4	578.2	579.4	579.4	578.2	576.1	573.9	570.6	567.3
172.5°	566.8	568.8	567.1	566.0	567.1	568.8	566.8	566.5	565.1	562.7	559.4
175°	553.1	554.2	552.0	550.9	552.0	554.2	553.1	553.1	553.1	550.9	550.9
177.5°	545.0	545.8	543.2	543.2	543.2	545.8	545.0	545.8	545.8	545.8	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	7.9	7.7	7.1	7.4	6.6	6.5	6.1	5.8	5.7	5.7	5.7
90°	18.7	17.5	15.4	14.2	12.1	10.9	8.8	6.6	4.3	2.2	1.1
92.5°	285.9	353.1	358.8	250.0	149.6	89.8	57.9	39.0	25.4	16.2	13.4
95°	949.5	970.3	791.8	489.6	248.6	131.4	82.1	58.1	46.0	37.2	36.1
97.5°	1201.5	1036.2	707.1	390.8	214.2	136.7	101.2	79.6	67.5	61.4	60.0
100°	1262.7	988.9	630.8	354.9	212.4	148.9	116.1	95.3	83.2	78.9	76.6
102.5°	1226.0	905.7	573.0	340.0	220.4	163.8	131.9	112.8	99.9	96.4	95.1
105°	1108.3	794.0	516.9	334.0	236.6	188.4	157.7	140.2	129.2	123.8	123.8
107.5°	988.4	717.1	493.2	344.1	260.6	214.0	186.4	168.2	159.2	154.0	151.7
110°	919.9	681.2	486.3	353.7	278.1	233.3	204.8	188.4	178.5	174.2	171.9



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	869.1	660.2	486.3	366.0	294.8	251.7	224.0	207.6	197.7	194.3	192.1
115°	813.7	637.4	489.6	384.4	320.9	280.4	253.0	236.6	226.7	223.4	221.2
117.5°	780.6	626.2	496.8	405.5	347.6	309.2	282.8	264.2	254.3	250.8	247.5
120°	762.2	620.9	503.8	419.4	366.9	328.6	301.1	282.6	272.7	268.3	265.0
122.5°	746.5	616.6	509.9	435.3	385.3	346.9	319.6	299.2	289.4	285.9	283.4
125°	725.0	611.1	520.2	456.7	409.6	373.4	345.0	324.1	314.3	308.9	306.6
127.5°	705.3	608.5	531.8	476.5	433.0	398.2	369.8	347.6	335.2	328.1	324.8
130°	692.2	606.7	538.9	489.6	447.9	414.0	385.5	362.5	348.3	339.5	336.2
132.5°	681.6	606.7	546.7	501.0	461.9	428.0	399.5	375.7	359.7	349.1	345.0
135°	669.2	606.7	557.4	516.9	480.8	446.9	417.3	394.3	376.7	363.6	359.2
137.5°	658.0	608.0	567.3	528.8	494.2	463.3	432.8	410.3	392.8	380.5	377.2
140°	652.7	608.9	571.7	536.7	503.8	472.0	442.4	421.7	404.2	391.0	387.7
142.5°	648.4	609.8	574.3	541.0	509.9	479.9	452.1	432.2	414.6	402.4	399.9
145°	641.8	608.9	577.2	547.6	520.2	491.7	466.6	446.9	431.5	420.6	418.4
147.5°	635.0	606.1	578.2	551.6	526.8	501.8	479.7	462.6	448.4	438.9	437.6
150°	629.7	603.4	578.2	554.2	531.1	507.1	488.4	473.2	458.9	451.2	449.0
152.5°	623.6	599.9	577.4	555.9	535.6	513.2	496.3	481.9	469.4	462.6	461.3
155°	613.3	593.6	575.0	557.4	539.9	521.3	506.0	495.0	484.1	477.5	477.5
157.5°	603.7	587.0	572.1	558.6	543.7	527.6	516.0	506.4	497.0	491.7	492.0
160°	595.8	582.7	569.5	558.6	545.4	531.1	521.3	512.6	504.9	500.5	501.6
162.5°	588.8	577.4	566.8	557.7	547.1	534.7	526.6	519.5	512.7	508.4	509.4
165°	578.2	569.5	562.9	556.4	547.6	538.9	532.3	527.9	522.5	519.2	521.3
167.5°	568.0	561.8	556.8	553.7	547.6	540.4	536.2	533.1	530.1	528.1	529.2
170°	561.8	557.4	554.2	552.0	547.6	542.2	538.9	536.7	534.4	533.4	534.4
172.5°	555.7	552.2	550.6	550.3	546.7	542.2	540.5	539.2	537.1	536.0	538.0
175°	547.6	546.5	546.5	547.6	545.4	542.2	542.2	542.2	541.0	539.9	542.2
177.5°	544.1	543.2	543.2	545.0	544.1	542.3	542.3	543.2	542.3	542.3	544.1
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	5.8	5.7	5.3	5.9	6.4	6.4	6.9	6.9	7.2	7.4	7.6
90°	2.2	4.3	6.6	8.8	10.9	12.1	14.2	15.4	17.5	18.7	19.7
92.5°	16.2	25.4	39.0	57.9	89.8	149.6	250.0	358.8	353.1	285.9	194.1
95°	37.2	46.0	58.1	82.1	131.4	248.6	489.6	791.8	970.3	949.5	787.4
97.5°	61.4	67.5	79.6	101.2	136.7	214.2	390.8	707.1	1036.2	1201.5	1172.7
100°	78.9	83.2	95.3	116.1	148.9	212.4	354.9	630.8	988.9	1262.7	1347.1
102.5°	96.4	99.9	112.8	131.9	163.8	220.4	340.0	573.0	905.7	1226.0	1405.8
105°	123.8	129.2	140.2	157.7	188.4	236.6	334.0	516.9	794.0	1108.3	1371.2
107.5°	154.0	159.2	168.2	186.4	214.0	260.6	344.1	493.2	717.1	988.4	1247.6
110°	174.2	178.5	188.4	204.8	233.3	278.1	353.7	486.3	681.2	919.9	1156.5





TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	194.3	197.7	207.6	224.0	251.7	294.8	366.0	486.3	660.2	869.1	1084.7
115°	223.4	226.7	236.6	253.0	280.4	320.9	384.4	489.6	637.4	813.7	994.5
117.5°	250.8	254.3	264.2	282.8	309.2	347.6	405.5	496.8	626.2	780.6	936.1
120°	268.3	272.7	282.6	301.1	328.6	366.9	419.4	503.8	620.9	762.2	904.7
122.5°	285.9	289.4	299.2	319.6	346.9	385.3	435.3	509.9	616.6	746.5	881.0
125°	308.9	314.3	324.1	345.0	373.4	409.6	456.7	520.2	611.1	725.0	846.6
127.5°	328.1	335.2	347.6	369.8	398.2	433.0	476.5	531.8	608.5	705.3	811.5
130°	339.5	348.3	362.5	385.5	414.0	447.9	489.6	538.9	606.7	692.2	789.7
132.5°	349.1	359.7	375.7	399.5	428.0	461.9	501.0	546.7	606.7	681.6	767.7
135°	363.6	376.7	394.3	417.3	446.9	480.8	516.9	557.4	606.7	669.2	739.2
137.5°	380.5	392.8	410.3	432.8	463.3	494.2	528.8	567.3	608.0	658.0	715.2
140°	391.0	404.2	421.7	442.4	472.0	503.8	536.7	571.7	608.9	652.7	702.0
142.5°	402.4	414.6	432.2	452.1	479.9	509.9	541.0	574.3	609.8	648.4	690.6
145°	420.6	431.5	446.9	466.6	491.7	520.2	547.6	577.2	608.9	641.8	675.7
147.5°	438.9	448.4	462.6	479.7	501.8	526.8	551.6	578.2	606.1	635.0	661.8
150°	451.2	458.9	473.2	488.4	507.1	531.1	554.2	578.2	603.4	629.7	653.8
152.5°	462.6	469.4	481.9	496.3	513.2	535.6	555.9	577.4	599.9	623.6	645.1
155°	477.5	484.1	495.0	506.0	521.3	539.9	557.4	575.0	593.6	613.3	631.9
157.5°	491.7	497.0	506.4	516.0	527.6	543.7	558.6	572.1	587.0	603.7	618.8
160°	500.5	504.9	512.6	521.3	531.1	545.4	558.6	569.5	582.7	595.8	610.0
162.5°	508.4	512.7	519.5	526.6	534.7	547.1	557.7	566.8	577.4	588.8	600.4
165°	519.2	522.5	527.9	532.3	538.9	547.6	556.4	562.9	569.5	578.2	587.0
167.5°	528.1	530.1	533.1	536.2	540.4	547.6	553.7	556.8	561.8	568.0	574.3
170°	533.4	534.4	536.7	538.9	542.2	547.6	552.0	554.2	557.4	561.8	567.3
172.5°	536.0	537.1	539.2	540.5	542.2	546.7	550.3	550.6	552.2	555.7	559.4
175°	539.9	541.0	542.2	542.2	542.2	545.4	547.6	546.5	546.5	547.6	550.9
177.5°	542.3	542.3	543.2	542.3	542.3	544.1	545.0	543.2	543.2	544.1	545.0
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2	543.2



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	8.0	8.4	8.5	8.3	8.3	8.7	8.9
90°	20.8	21.9	24.1	24.1	24.1	25.2	25.2
92.5°	140.8	106.0	89.8	75.8	73.1	71.6	69.8
95°	620.9	486.3	394.3	316.5	283.6	274.9	257.4
97.5°	1056.0	924.8	796.8	729.2	667.9	636.1	622.1
100°	1293.5	1180.6	1066.7	991.2	912.3	871.8	854.2
102.5°	1438.9	1384.8	1307.7	1226.8	1170.7	1126.7	1113.6
105°	1521.3	1569.4	1557.4	1522.3	1486.2	1464.2	1451.1
107.5°	1447.8	1571.6	1628.8	1646.5	1646.3	1639.1	1630.3
110°	1364.6	1519.0	1612.1	1661.4	1682.2	1689.9	1689.9



TEST NUMBER: P333516-830

CATALOG NUMBER: S125RDIP-S375D1205U830-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1282.2	1438.4	1548.1	1620.2	1656.0	1675.0	1682.9
115°	1164.2	1314.2	1433.6	1519.0	1571.6	1602.2	1616.5
117.5°	1082.5	1211.7	1321.3	1406.7	1461.0	1491.5	1500.2
120°	1036.0	1156.5	1252.9	1334.0	1386.5	1416.1	1424.8
122.5°	1002.8	1110.1	1200.3	1272.6	1320.8	1350.4	1358.3
125°	958.3	1053.6	1132.5	1193.7	1238.7	1262.7	1273.8
127.5°	915.8	1004.8	1078.6	1134.2	1173.8	1196.7	1201.5
130°	886.0	971.5	1042.6	1097.4	1133.5	1155.5	1162.0
132.5°	858.0	935.5	1004.1	1058.9	1095.0	1115.1	1122.6
135°	814.8	885.0	947.3	995.5	1031.7	1051.4	1058.0
137.5°	776.3	834.5	887.6	930.7	963.6	981.8	988.9
140°	753.5	803.9	849.9	890.4	918.9	935.3	940.8
142.5°	734.2	777.6	817.5	851.9	875.9	891.5	896.1
145°	709.6	743.7	773.2	799.5	818.1	830.2	834.5
147.5°	689.3	715.4	737.7	758.6	773.5	780.4	782.4
150°	678.0	698.7	718.4	734.9	748.0	752.4	753.5
152.5°	666.6	685.6	701.0	714.7	725.2	729.6	730.8
155°	649.4	664.8	676.8	687.8	695.4	698.7	699.8
157.5°	633.2	645.1	654.5	663.0	669.4	672.4	672.2
160°	620.9	631.9	639.6	647.2	652.7	655.0	653.8
162.5°	610.5	619.6	626.4	632.4	637.0	637.4	637.2
165°	594.7	601.2	606.7	611.1	613.3	613.3	613.3
167.5°	579.4	584.4	588.3	590.5	592.5	591.6	591.4
170°	570.6	573.9	576.1	578.2	579.4	579.4	578.2
172.5°	562.7	565.1	566.5	566.8	568.8	567.1	566.0
175°	550.9	553.1	553.1	553.1	554.2	552.0	550.9
177.5°	545.8	545.8	545.8	545.0	545.8	543.2	543.2
180°	543.2	543.2	543.2	543.2	543.2	543.2	543.2

(END OF REPORT)