

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333496-830

Luminaire Tested: **S125RDIP-S375D590U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333496-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D590U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3603.7 lumens
Efficiency: N/A
Efficacy: 140.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38																				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	40	40	39	33																				
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28																				
3	80	71	64	58	72	64	58	54	53	48	45	42	39	37	32	30	29	24																				
4	73	63	55	49	66	57	51	46	47	42	38	38	34	31	29	27	25	21																				
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18																				
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16																				
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14																				
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13																				
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	12																				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.4
10°-20°	149.1	4.1
20°-30°	236.4	6.6
30°-40°	285.1	7.9
40°-50°	254.6	7.1
50°-60°	195.2	5.4
60°-70°	126.9	3.5
70°-80°	61.7	1.7
80°-90°	16.2	0.5
90°-100°	26.4	0.7
100°-110°	162.5	4.5
110°-120°	294.7	8.2
120°-130°	378.2	10.5
130°-140°	406.7	11.3
140°-150°	381.8	10.6
150°-160°	308.8	8.6
160°-170°	199.7	5.5
170°-180°	68.9	1.9
0°-30°	436.4	12.1
0°-40°	721.4	20.0
0°-60°	1171.3	32.5
0°-90°	1376.0	38.2
90°-120°	483.5	13.4
90°-150°	1650.2	45.8
90°-180°	2228.0	61.8
0°-180°	3603.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	13	1	13	1	13	6
95°	11	31	11	31	11	9
105°	160	158	160	158	160	144
115°	295	297	295	297	295	293
125°	422	422	422	422	422	376
135°	524	526	524	526	524	405
145°	609	610	609	610	609	380
155°	667	672	667	672	667	308
165°	706	709	706	709	706	199
175°	722	726	722	726	722	69
180°	726	726	726	726	726	



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	6.4	6.1	5.9	5.8	5.9	6.2	5.9	5.7	5.5	5.4	5.4
90°	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8	9.2	8.6	7.7
92.5°	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8	9.2	8.6	7.8
95°	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8	9.2	8.6	13.1
97.5°	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7	23.1	26.5	35.4
100°	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0	75.8	93.6	93.1
102.5°	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6	116.0	119.4	119.1
105°	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9	202.8	202.8	202.6
110°	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5	230.9	231.2	231.0



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9	258.4	258.7	258.6
115°	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1	299.6	300.1	299.9
117.5°	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9	339.6	340.2	339.7
120°	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7	364.9	365.1	364.8
122.5°	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2	389.5	389.6	389.5
125°	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0	425.5	425.9	425.9
127.5°	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6	457.9	458.2	458.3
130°	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0	479.3	479.7	479.6
132.5°	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9	499.0	499.1	499.3
135°	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1	528.4	528.6	528.9
137.5°	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3	555.3	555.3	555.5
140°	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1	571.8	571.7	571.7
142.5°	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5	588.4	588.4	588.2
145°	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7	611.5	611.4	611.4
147.5°	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5	631.4	631.2	631.0
150°	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1	643.9	643.7	643.5
152.5°	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3	655.2	654.9	654.6
155°	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8	670.4	670.1	669.8
157.5°	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5	683.2	682.8	682.7
160°	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4	691.0	690.5	690.3
162.5°	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7	698.0	697.4	697.2
165°	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0	707.3	706.6	706.5
167.5°	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1	714.3	713.4	713.2
170°	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8	717.7	716.8	716.7
172.5°	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5	720.7	719.8	719.6
175°	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6	723.7	722.7	722.6
177.5°	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9	725.3	724.5	724.4
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	5.4	5.2	5.3	5.1	4.7	5.4	5.7	5.7	5.6	5.4	5.2
90°	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6	1.5	2.5	3.4
92.5°	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3	7.6	7.0	6.3
95°	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6	30.3	30.0	29.6
97.5°	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0	64.7	65.3	65.9
100°	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8	90.2	90.5	90.9
102.5°	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0	116.5	117.0	117.4
105°	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1	158.5	159.1	159.6
107.5°	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8	201.8	201.8	201.8
110°	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2	230.2	230.2	230.2



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8	257.1	257.4	257.7
115°	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8	297.5	298.0	298.6
117.5°	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3	338.2	338.2	338.2
120°	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1	363.9	363.8	363.7
122.5°	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8	387.3	387.8	388.2
125°	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2	423.0	423.8	424.6
127.5°	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8	456.4	457.0	457.6
130°	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5	477.0	477.7	478.2
132.5°	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1	497.8	498.5	499.2
135°	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5	527.2	527.9	528.6
137.5°	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5	554.1	554.7	555.3
140°	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1	571.4	571.6	571.8
142.5°	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0	587.2	587.3	587.5
145°	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4	610.6	610.9	611.1
147.5°	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7	630.7	630.7	630.7
150°	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.5	643.2	643.0
152.5°	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2	655.6	655.2	654.6
155°	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2	671.5	670.8	670.1
157.5°	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6	684.1	683.7	683.2
160°	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1	692.5	691.7	691.0
162.5°	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0	699.4	698.6	697.9
165°	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3	708.6	707.8	707.2
167.5°	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1	715.5	714.7	714.0
170°	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1	719.3	718.4	717.6
172.5°	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6	721.8	721.0	720.1
175°	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5	724.7	724.0	723.3
177.5°	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7	726.1	725.6	725.0
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	5.2	5.4	5.4	5.9	5.6	5.9	6.0	5.9	6.1	6.2	6.1
90°	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8	10.4	11.0	11.5
92.5°	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8	10.4	11.0	11.4
95°	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8	10.4	11.0	11.3
97.5°	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7	16.3	13.0	11.3
100°	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0	40.2	22.3	13.2
102.5°	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6	109.2	105.9	100.2
105°	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9	202.9	202.9	202.7
110°	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5	230.2	229.8	229.7



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9	257.4	256.9	256.7
115°	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1	298.6	298.1	297.6
117.5°	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9	338.3	337.7	337.2
120°	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7	364.4	364.2	363.7
122.5°	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2	389.0	388.7	388.2
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0	424.4	424.0	423.6
127.5°	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6	457.4	457.1	456.6
130°	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0	478.6	478.2	477.8
132.5°	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9	498.8	498.8	498.4
135°	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1	527.9	527.6	527.2
137.5°	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3	555.4	555.4	555.2
140°	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1	572.3	572.6	572.3
142.5°	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5	588.5	588.6	588.2
145°	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7	611.8	611.9	611.6
147.5°	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5	631.7	631.8	631.4
150°	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1	644.4	644.6	644.3
152.5°	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3	655.6	655.8	655.5
155°	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8	671.1	671.5	671.2
157.5°	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5	683.9	684.3	684.0
160°	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4	691.9	692.4	692.1
162.5°	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7	699.4	700.0	699.8
165°	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0	708.8	709.5	709.4
167.5°	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1	716.0	716.8	716.7
170°	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8	719.7	720.7	720.6
172.5°	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5	722.5	723.3	723.2
175°	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6	725.6	726.6	726.5
177.5°	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9	726.6	727.3	727.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	6.4	6.3	6.3	6.4	6.3	6.3	6.4	6.1	6.2	6.1	5.9
90°	11.9	12.2	12.5	12.9	12.5	12.2	11.9	11.5	11.0	10.4	9.8
92.5°	11.5	11.7	11.9	12.1	11.9	11.7	11.5	11.4	11.0	10.4	9.8
95°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.0	10.4	9.8
97.5°	11.3	11.3	11.3	11.3	11.3	11.3	11.3	11.3	13.0	16.3	19.7
100°	12.7	12.3	11.8	11.3	11.8	12.3	12.7	13.2	22.3	40.2	58.0
102.5°	92.0	83.9	75.8	67.7	75.8	83.9	92.0	100.2	105.9	109.2	112.6
105°	160.0	159.9	159.9	159.7	159.9	159.9	160.0	160.2	160.2	160.2	160.2
107.5°	202.5	202.1	201.7	201.3	201.7	202.1	202.5	202.7	202.9	202.9	202.9
110°	229.8	229.9	230.1	230.2	230.1	229.9	229.8	229.7	229.8	230.2	230.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	256.5	256.3	256.2	256.0	256.2	256.3	256.5	256.7	256.9	257.4	257.9
115°	296.8	296.1	295.4	294.7	295.4	296.1	296.8	297.6	298.1	298.6	299.1
117.5°	337.0	336.6	336.3	336.0	336.3	336.6	337.0	337.2	337.7	338.3	338.9
120°	363.2	362.6	361.9	361.4	361.9	362.6	363.2	363.7	364.2	364.4	364.7
122.5°	387.6	386.8	386.2	385.5	386.2	386.8	387.6	388.2	388.7	389.0	389.2
125°	423.2	422.8	422.5	422.2	422.5	422.8	423.2	423.6	424.0	424.4	425.0
127.5°	455.6	454.8	453.9	453.0	453.9	454.8	455.6	456.6	457.1	457.4	457.6
130°	477.2	476.5	476.0	475.4	476.0	476.5	477.2	477.8	478.2	478.6	479.0
132.5°	497.9	497.2	496.6	496.1	496.6	497.2	497.9	498.4	498.8	498.8	498.9
135°	526.5	525.8	525.0	524.3	525.0	525.8	526.5	527.2	527.6	527.9	528.1
137.5°	554.6	553.9	553.4	552.7	553.4	553.9	554.6	555.2	555.4	555.4	555.3
140°	571.7	570.9	570.2	569.5	570.2	570.9	571.7	572.3	572.6	572.3	572.1
142.5°	587.6	586.8	586.1	585.4	586.1	586.8	587.6	588.2	588.6	588.5	588.5
145°	610.9	610.2	609.4	608.7	609.4	610.2	610.9	611.6	611.9	611.8	611.7
147.5°	630.6	629.7	628.9	628.0	628.9	629.7	630.6	631.4	631.8	631.7	631.5
150°	643.4	642.3	641.4	640.5	641.4	642.3	643.4	644.3	644.6	644.4	644.1
152.5°	654.7	653.8	652.9	652.1	652.9	653.8	654.7	655.5	655.8	655.6	655.3
155°	670.2	669.3	668.4	667.3	668.4	669.3	670.2	671.2	671.5	671.1	670.8
157.5°	683.1	682.0	681.1	680.1	681.1	682.0	683.1	684.0	684.3	683.9	683.5
160°	691.2	690.2	689.3	688.3	689.3	690.2	691.2	692.1	692.4	691.9	691.4
162.5°	698.8	697.8	696.7	695.6	696.7	697.8	698.8	699.8	700.0	699.4	698.7
165°	708.4	707.5	706.5	705.5	706.5	707.5	708.4	709.4	709.5	708.8	708.0
167.5°	715.7	714.5	713.5	712.4	713.5	714.5	715.7	716.7	716.8	716.0	715.1
170°	719.5	718.4	717.4	716.3	717.4	718.4	719.5	720.6	720.7	719.7	718.8
172.5°	722.1	721.0	719.9	718.9	719.9	721.0	722.1	723.2	723.3	722.5	721.5
175°	725.5	724.3	723.3	722.2	723.3	724.3	725.5	726.5	726.6	725.6	724.6
177.5°	726.4	725.7	724.9	724.2	724.9	725.7	726.4	727.2	727.3	726.6	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	6.0	5.9	5.6	5.9	5.4	5.4	5.2	5.2	5.4	5.6	5.7
90°	9.2	8.6	7.7	7.0	6.1	5.3	4.3	3.4	2.5	1.5	0.6
92.5°	9.2	8.6	7.8	7.2	6.4	5.7	5.6	6.3	7.0	7.6	8.3
95°	9.2	8.6	13.1	17.7	22.2	26.8	29.2	29.6	30.0	30.3	30.6
97.5°	23.1	26.5	35.4	44.4	53.4	62.4	66.5	65.9	65.3	64.7	64.0
100°	75.8	93.6	93.1	92.7	92.2	91.6	91.2	90.9	90.5	90.2	89.8
102.5°	116.0	119.4	119.1	118.9	118.5	118.2	117.8	117.4	117.0	116.5	116.0
105°	160.2	160.2	160.2	160.2	160.2	160.2	160.0	159.6	159.1	158.5	158.1
107.5°	202.8	202.8	202.6	202.4	202.1	201.9	201.8	201.8	201.8	201.8	201.8
110°	230.9	231.2	231.0	230.7	230.5	230.3	230.2	230.2	230.2	230.2	230.2



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	258.4	258.7	258.6	258.4	258.4	258.2	258.0	257.7	257.4	257.1	256.8
115°	299.6	300.1	299.9	299.8	299.7	299.6	299.3	298.6	298.0	297.5	296.8
117.5°	339.6	340.2	339.7	339.3	338.8	338.4	338.2	338.2	338.2	338.2	338.3
120°	364.9	365.1	364.8	364.4	364.1	363.7	363.5	363.7	363.8	363.9	364.1
122.5°	389.5	389.6	389.5	389.4	389.2	389.0	388.7	388.2	387.8	387.3	386.8
125°	425.5	425.9	425.9	425.9	425.9	425.9	425.5	424.6	423.8	423.0	422.2
127.5°	457.9	458.2	458.3	458.4	458.4	458.5	458.2	457.6	457.0	456.4	455.8
130°	479.3	479.7	479.6	479.5	479.3	479.2	478.8	478.2	477.7	477.0	476.5
132.5°	499.0	499.1	499.3	499.5	499.8	500.1	499.8	499.2	498.5	497.8	497.1
135°	528.4	528.6	528.9	529.0	529.3	529.6	529.3	528.6	527.9	527.2	526.5
137.5°	555.3	555.3	555.5	555.7	555.9	556.2	555.9	555.3	554.7	554.1	553.5
140°	571.8	571.7	571.7	571.8	572.0	572.1	572.0	571.8	571.6	571.4	571.1
142.5°	588.4	588.4	588.2	588.1	588.0	587.8	587.6	587.5	587.3	587.2	587.0
145°	611.5	611.4	611.4	611.4	611.4	611.4	611.3	611.1	610.9	610.6	610.4
147.5°	631.4	631.2	631.0	630.9	630.7	630.7	630.6	630.7	630.7	630.7	630.7
150°	643.9	643.7	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7
152.5°	655.2	654.9	654.6	654.4	654.1	653.9	654.0	654.6	655.2	655.6	656.2
155°	670.4	670.1	669.8	669.6	669.3	669.1	669.3	670.1	670.8	671.5	672.2
157.5°	683.2	682.8	682.7	682.7	682.7	682.7	682.9	683.2	683.7	684.1	684.6
160°	691.0	690.5	690.3	690.2	690.1	690.0	690.3	691.0	691.7	692.5	693.1
162.5°	698.0	697.4	697.2	697.1	697.0	696.9	697.2	697.9	698.6	699.4	700.0
165°	707.3	706.6	706.5	706.3	706.2	706.2	706.4	707.2	707.8	708.6	709.3
167.5°	714.3	713.4	713.2	713.1	713.0	712.9	713.2	714.0	714.7	715.5	716.1
170°	717.7	716.8	716.7	716.6	716.4	716.3	716.7	717.6	718.4	719.3	720.1
172.5°	720.7	719.8	719.6	719.4	719.2	719.0	719.3	720.1	721.0	721.8	722.6
175°	723.7	722.7	722.6	722.6	722.4	722.3	722.6	723.3	724.0	724.7	725.5
177.5°	725.3	724.5	724.4	724.3	724.2	724.2	724.4	725.0	725.6	726.1	726.7
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	5.7	5.4	4.7	5.1	5.3	5.2	5.4	5.4	5.4	5.5	5.7
90°	1.5	2.5	3.4	4.3	5.3	6.1	7.0	7.7	8.6	9.2	9.8
92.5°	7.6	7.0	6.3	5.6	5.7	6.4	7.2	7.8	8.6	9.2	9.8
95°	30.3	30.0	29.6	29.2	26.8	22.2	17.7	13.1	8.6	9.2	9.8
97.5°	64.7	65.3	65.9	66.5	62.4	53.4	44.4	35.4	26.5	23.1	19.7
100°	90.2	90.5	90.9	91.2	91.6	92.2	92.7	93.1	93.6	75.8	58.0
102.5°	116.5	117.0	117.4	117.8	118.2	118.5	118.9	119.1	119.4	116.0	112.6
105°	158.5	159.1	159.6	160.0	160.2	160.2	160.2	160.2	160.2	160.2	160.2
107.5°	201.8	201.8	201.8	201.8	201.9	202.1	202.4	202.6	202.8	202.8	202.9
110°	230.2	230.2	230.2	230.2	230.3	230.5	230.7	231.0	231.2	230.9	230.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	257.1	257.4	257.7	258.0	258.2	258.4	258.4	258.6	258.7	258.4	257.9
115°	297.5	298.0	298.6	299.3	299.6	299.7	299.8	299.9	300.1	299.6	299.1
117.5°	338.2	338.2	338.2	338.2	338.4	338.8	339.3	339.7	340.2	339.6	338.9
120°	363.9	363.8	363.7	363.5	363.7	364.1	364.4	364.8	365.1	364.9	364.7
122.5°	387.3	387.8	388.2	388.7	389.0	389.2	389.4	389.5	389.6	389.5	389.2
125°	423.0	423.8	424.6	425.5	425.9	425.9	425.9	425.9	425.9	425.5	425.0
127.5°	456.4	457.0	457.6	458.2	458.5	458.4	458.4	458.3	458.2	457.9	457.6
130°	477.0	477.7	478.2	478.8	479.2	479.3	479.5	479.6	479.7	479.3	479.0
132.5°	497.8	498.5	499.2	499.8	500.1	499.8	499.5	499.3	499.1	499.0	498.9
135°	527.2	527.9	528.6	529.3	529.6	529.3	529.0	528.9	528.6	528.4	528.1
137.5°	554.1	554.7	555.3	555.9	556.2	555.9	555.7	555.5	555.3	555.3	555.3
140°	571.4	571.6	571.8	572.0	572.1	572.0	571.8	571.7	571.7	571.8	572.1
142.5°	587.2	587.3	587.5	587.6	587.8	588.0	588.1	588.2	588.4	588.4	588.5
145°	610.6	610.9	611.1	611.3	611.4	611.4	611.4	611.4	611.4	611.5	611.7
147.5°	630.7	630.7	630.7	630.6	630.7	630.7	630.9	631.0	631.2	631.4	631.5
150°	643.5	643.2	643.0	642.7	642.7	643.0	643.2	643.5	643.7	643.9	644.1
152.5°	655.6	655.2	654.6	654.0	653.9	654.1	654.4	654.6	654.9	655.2	655.3
155°	671.5	670.8	670.1	669.3	669.1	669.3	669.6	669.8	670.1	670.4	670.8
157.5°	684.1	683.7	683.2	682.9	682.7	682.7	682.7	682.7	682.8	683.2	683.5
160°	692.5	691.7	691.0	690.3	690.0	690.1	690.2	690.3	690.5	691.0	691.4
162.5°	699.4	698.6	697.9	697.2	696.9	697.0	697.1	697.2	697.4	698.0	698.7
165°	708.6	707.8	707.2	706.4	706.2	706.2	706.3	706.5	706.6	707.3	708.0
167.5°	715.5	714.7	714.0	713.2	712.9	713.0	713.1	713.2	713.4	714.3	715.1
170°	719.3	718.4	717.6	716.7	716.3	716.4	716.6	716.7	716.8	717.7	718.8
172.5°	721.8	721.0	720.1	719.3	719.0	719.2	719.4	719.6	719.8	720.7	721.5
175°	724.7	724.0	723.3	722.6	722.3	722.4	722.6	722.6	722.7	723.7	724.6
177.5°	726.1	725.6	725.0	724.4	724.2	724.2	724.3	724.4	724.5	725.3	725.9
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5	725.5



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	5.9	6.2	5.9	5.8	5.9	6.1	6.4
90°	10.4	11.0	11.5	11.9	12.2	12.5	12.9
92.5°	10.4	11.0	11.4	11.5	11.7	11.9	12.1
95°	10.4	11.0	11.3	11.3	11.3	11.3	11.3
97.5°	16.3	13.0	11.3	11.3	11.3	11.3	11.3
100°	40.2	22.3	13.2	12.7	12.3	11.8	11.3
102.5°	109.2	105.9	100.2	92.0	83.9	75.8	67.7
105°	160.2	160.2	160.2	160.0	159.9	159.9	159.7
107.5°	202.9	202.9	202.7	202.5	202.1	201.7	201.3
110°	230.2	229.8	229.7	229.8	229.9	230.1	230.2



TEST NUMBER: P333496-830

CATALOG NUMBER: S125RDIP-S375D590U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	257.4	256.9	256.7	256.5	256.3	256.2	256.0
115°	298.6	298.1	297.6	296.8	296.1	295.4	294.7
117.5°	338.3	337.7	337.2	337.0	336.6	336.3	336.0
120°	364.4	364.2	363.7	363.2	362.6	361.9	361.4
122.5°	389.0	388.7	388.2	387.6	386.8	386.2	385.5
125°	424.4	424.0	423.6	423.2	422.8	422.5	422.2
127.5°	457.4	457.1	456.6	455.6	454.8	453.9	453.0
130°	478.6	478.2	477.8	477.2	476.5	476.0	475.4
132.5°	498.8	498.8	498.4	497.9	497.2	496.6	496.1
135°	527.9	527.6	527.2	526.5	525.8	525.0	524.3
137.5°	555.4	555.4	555.2	554.6	553.9	553.4	552.7
140°	572.3	572.6	572.3	571.7	570.9	570.2	569.5
142.5°	588.5	588.6	588.2	587.6	586.8	586.1	585.4
145°	611.8	611.9	611.6	610.9	610.2	609.4	608.7
147.5°	631.7	631.8	631.4	630.6	629.7	628.9	628.0
150°	644.4	644.6	644.3	643.4	642.3	641.4	640.5
152.5°	655.6	655.8	655.5	654.7	653.8	652.9	652.1
155°	671.1	671.5	671.2	670.2	669.3	668.4	667.3
157.5°	683.9	684.3	684.0	683.1	682.0	681.1	680.1
160°	691.9	692.4	692.1	691.2	690.2	689.3	688.3
162.5°	699.4	700.0	699.8	698.8	697.8	696.7	695.6
165°	708.8	709.5	709.4	708.4	707.5	706.5	705.5
167.5°	716.0	716.8	716.7	715.7	714.5	713.5	712.4
170°	719.7	720.7	720.6	719.5	718.4	717.4	716.3
172.5°	722.5	723.3	723.2	722.1	721.0	719.9	718.9
175°	725.6	726.6	726.5	725.5	724.3	723.3	722.2
177.5°	726.6	727.3	727.2	726.4	725.7	724.9	724.2
180°	725.5	725.5	725.5	725.5	725.5	725.5	725.5

(END OF REPORT)