

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333504-830

Luminaire Tested: **S125RDIP-S375D810U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333504-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D810U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4117.8 lumens
Efficiency: N/A
Efficacy: 132.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30	24
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	62	54	48	65	56	50	45	45	41	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	36	32	32	28	26	23	21	20	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	19	17	15	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	48	37	29	25	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3427	3427	3427	3427
5°	3942	3431	3030	3431
10°	4522	3413	2674	3413
15°	4884	3379	2376	3379
20°	5386	3338	2194	3338
25°	6233	3284	2037	3284
30°	6783	3227	1933	3227
35°	5722	3162	1837	3162
40°	3995	3043	1755	3043
45°	2964	2883	1675	2883
50°	2364	2716	1607	2716
55°	2005	2509	1545	2509
60°	1732	2324	1447	2324
65°	1543	2123	1244	2123
70°	1358	1945	1135	1945
75°	1173	1684	1065	1684
80°	889	1417	889	1417
85°	741	1112	837	1112



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.9	1.2
10°-20°	149.1	3.6
20°-30°	236.4	5.7
30°-40°	285.1	6.9
40°-50°	254.6	6.2
50°-60°	195.2	4.7
60°-70°	126.9	3.1
70°-80°	61.7	1.5
80°-90°	16.8	0.4
90°-100°	264.9	6.4
100°-110°	569.6	13.8
110°-120°	534.5	13.0
120°-130°	433.2	10.5
130°-140°	347.7	8.4
140°-150°	262.4	6.4
150°-160°	184.7	4.5
160°-170°	108.8	2.6
170°-180°	35.4	0.9
0°-30°	436.4	10.6
0°-40°	721.4	17.5
0°-60°	1171.3	28.4
0°-90°	1376.6	33.4
90°-120°	1369.1	33.2
90°-150°	2412.3	58.6
90°-180°	2741.0	66.6
0°-180°	4117.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	531	531	531	531	531	
5°	608	529	467	529	608	61
15°	730	505	355	505	730	209
25°	875	461	286	461	875	402
35°	726	401	233	401	726	438
45°	324	316	183	316	324	259
55°	178	223	137	223	178	162
65°	101	139	81	139	101	101
75°	47	68	43	68	47	50
85°	10	15	11	15	10	12
90°	17	1	17	1	17	12
95°	173	24	173	24	173	245
105°	976	83	976	83	976	971
115°	1088	149	1088	149	1088	1063
125°	857	206	857	206	857	775
135°	712	242	712	242	712	552
145°	562	282	562	282	562	357
155°	471	321	471	321	471	219
165°	413	351	413	351	413	118
175°	371	365	371	365	371	36
180°	366	366	366	366	366	



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	558.1	557.7	558.5	556.5	556.7	553.7	553.7	551.5	548.5	546.2	545.2
5°	608.0	608.5	607.7	604.4	602.2	598.9	595.2	588.7	583.2	578.0	573.9
7.5°	659.6	659.9	657.0	656.0	650.4	646.5	638.3	629.3	621.5	611.4	603.8
10°	689.6	689.3	686.3	683.8	679.1	673.0	664.9	654.5	644.7	633.8	623.3
12.5°	706.9	706.3	705.4	702.5	698.0	692.7	685.8	675.5	663.5	651.6	639.3
15°	730.5	729.0	726.1	722.4	716.0	709.7	702.2	693.1	681.5	668.0	656.7
17.5°	759.6	759.6	755.3	750.1	741.5	730.4	718.6	703.9	688.2	673.4	661.3
20°	783.6	783.0	778.6	768.5	758.7	744.8	731.3	713.2	694.1	674.7	659.7
22.5°	818.1	816.4	811.9	798.7	783.5	765.5	744.9	722.8	699.6	677.7	657.9
25°	874.7	873.4	864.4	849.1	827.8	800.1	773.2	742.9	709.5	680.6	656.7
27.5°	913.3	911.9	905.2	892.6	872.9	843.8	807.3	766.8	725.2	685.3	650.8
30°	909.5	912.8	911.9	906.0	891.2	865.1	831.3	785.8	736.3	689.6	648.4
32.5°	854.8	857.7	865.3	876.9	877.8	867.3	842.1	800.0	748.9	695.6	646.4
35°	725.7	729.6	744.4	767.7	798.2	823.7	828.9	806.3	760.3	703.0	643.6
37.5°	557.9	579.3	591.8	616.3	662.4	709.3	754.3	770.9	751.4	699.9	638.9
40°	473.9	479.1	501.3	529.0	567.8	616.5	680.8	727.2	728.7	693.1	631.6
42.5°	405.6	412.3	427.4	449.6	482.8	531.5	597.9	659.1	687.4	673.8	622.0
45°	324.5	329.5	340.6	357.6	383.0	423.4	480.4	551.2	607.4	629.4	596.3
47.5°	266.6	269.3	278.9	291.9	310.8	340.1	384.3	445.7	513.1	560.3	555.7
50°	235.3	238.3	245.6	255.4	271.4	296.1	331.5	382.7	452.1	509.8	521.4
52.5°	210.8	213.4	218.0	227.2	240.3	259.4	287.9	334.2	396.7	458.1	484.8
55°	178.1	179.9	183.6	188.8	199.3	213.0	237.6	269.7	320.2	382.0	421.2
57.5°	151.3	152.1	154.5	159.3	166.5	176.5	194.4	221.4	257.7	313.4	356.7
60°	134.1	135.1	138.1	141.4	147.0	156.2	170.1	189.1	223.9	269.8	313.6
62.5°	120.6	121.1	122.4	125.6	130.6	137.7	148.6	164.1	191.8	232.2	273.5
65°	101.0	101.2	101.7	104.3	107.4	112.6	119.8	130.6	151.6	182.1	218.7
67.5°	82.3	82.7	84.2	85.1	88.2	91.0	95.2	103.5	118.3	138.8	167.3
70°	71.9	71.6	73.1	74.3	75.3	78.6	81.4	88.2	97.4	113.0	136.8
72.5°	62.1	61.5	62.2	62.6	64.0	66.3	69.1	73.2	80.3	91.0	109.2
75°	47.0	47.2	47.2	47.7	48.8	49.7	50.5	52.7	56.6	63.8	73.6
77.5°	33.0	32.7	33.6	33.7	34.4	35.3	36.1	36.9	38.5	41.5	46.6
80°	23.9	23.9	24.1	24.8	24.6	25.1	26.1	27.1	28.9	30.7	32.4
82.5°	18.4	18.2	18.4	18.6	18.5	18.9	19.3	19.5	20.3	21.1	22.3
85°	10.0	10.0	10.3	10.3	10.5	10.5	10.7	10.7	10.7	10.9	11.1
87.5°	7.3	7.1	6.7	6.7	6.9	7.0	6.6	6.3	6.1	6.0	5.9
90°	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3	12.5	11.8	10.3
92.5°	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6	192.4	237.6	241.4
95°	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9	638.9	653.0	532.8
97.5°	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2	808.4	697.3	475.8
100°	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4	849.7	665.5	424.5
102.5°	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9	825.0	609.4	385.6
105°	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7	745.8	534.3	347.9
107.5°	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5	665.1	482.6	332.0
110°	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3	619.1	458.4	327.3



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9	584.8	444.2	327.3
115°	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2	547.5	429.0	329.4
117.5°	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0	525.3	421.4	334.3
120°	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7	512.9	417.8	339.0
122.5°	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9	502.3	414.9	343.1
125°	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7	487.9	411.2	350.1
127.5°	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1	474.6	409.4	357.9
130°	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3	465.8	408.3	362.6
132.5°	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6	458.7	408.3	367.9
135°	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5	450.3	408.3	375.1
137.5°	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3	442.8	409.2	381.7
140°	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4	439.2	409.7	384.7
142.5°	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8	436.3	410.4	386.4
145°	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7	431.9	409.7	388.4
147.5°	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3	427.3	407.8	389.1
150°	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0	423.8	406.0	389.1
152.5°	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0	419.6	403.7	388.5
155°	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3	412.7	399.4	386.9
157.5°	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4	406.2	395.0	385.0
160°	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5	401.0	392.1	383.2
162.5°	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0	396.2	388.5	381.4
165°	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0	389.1	383.2	378.8
167.5°	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4	382.2	378.1	374.7
170°	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7	378.1	375.1	372.9
172.5°	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5	373.9	371.6	370.5
175°	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7	368.4	367.8	367.8
177.5°	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7	366.1	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	545.2	543.9	541.7	539.6	537.0	534.7	533.1	531.2	528.8	525.8	523.4
5°	569.3	564.5	558.2	552.7	545.7	540.4	534.7	529.2	523.8	516.8	510.7
7.5°	596.1	586.2	576.6	564.4	553.5	543.7	534.2	524.7	515.4	505.5	496.0
10°	612.5	600.4	587.2	571.9	558.0	544.7	532.5	520.5	507.8	496.8	484.8
12.5°	627.7	612.3	597.1	577.9	561.1	544.9	529.3	514.4	501.0	486.5	473.6
15°	641.6	626.3	609.4	585.9	562.5	542.9	524.6	505.3	488.5	472.4	458.0
17.5°	647.0	630.9	611.2	588.6	563.2	538.5	514.9	493.7	473.9	455.2	439.0
20°	644.9	629.4	609.2	587.6	560.3	534.7	509.2	485.7	463.6	443.8	426.7
22.5°	639.8	623.9	604.3	581.5	555.6	528.4	501.1	476.1	453.1	432.5	413.8
25°	632.3	610.5	590.4	568.2	543.6	516.6	488.5	460.8	436.2	415.3	394.8
27.5°	624.3	597.2	571.7	549.6	523.6	499.5	472.4	444.0	418.2	396.9	375.9
30°	617.2	586.7	558.6	533.6	509.0	486.1	460.4	432.7	406.1	384.2	362.9
32.5°	608.3	575.9	545.1	516.1	492.4	469.8	446.5	420.0	394.2	371.5	349.8
35°	597.2	555.8	522.3	491.5	465.2	443.2	422.3	401.0	375.0	351.5	330.4
37.5°	582.6	535.6	496.8	463.4	435.5	413.5	396.9	377.4	353.7	331.3	311.7
40°	573.6	520.9	478.5	445.4	416.2	392.9	377.4	360.9	339.3	318.2	298.6
42.5°	561.8	507.6	460.1	425.6	396.2	373.7	358.1	343.7	325.6	305.7	284.6
45°	538.6	481.5	431.7	394.6	365.0	343.0	328.4	315.6	301.9	283.5	265.2
47.5°	508.4	454.4	402.2	361.7	332.8	312.4	298.2	288.0	278.2	262.7	245.0
50°	484.2	432.1	381.2	342.0	311.0	291.6	278.3	270.3	261.4	247.2	232.3
52.5°	455.5	409.1	359.2	319.1	289.9	271.7	259.0	250.9	243.6	232.1	217.9
55°	410.6	369.8	324.0	287.7	260.9	242.6	230.5	222.8	218.5	208.7	197.6
57.5°	358.5	329.4	289.1	254.0	230.3	212.3	203.3	196.8	191.9	184.9	177.1
60°	322.3	301.9	265.7	232.3	210.6	193.4	185.3	179.9	175.3	169.5	163.3
62.5°	285.6	270.7	239.2	210.6	190.6	176.2	168.6	163.7	158.4	154.5	148.5
65°	236.3	223.0	201.2	178.8	160.3	148.7	143.3	138.9	135.7	131.3	127.1
67.5°	183.8	178.4	163.3	147.9	134.6	124.3	119.6	116.6	112.7	110.1	107.3
70°	151.6	148.9	138.3	128.1	115.6	108.7	104.3	103.0	98.2	95.6	93.7
72.5°	123.0	121.8	115.6	108.6	99.8	93.7	89.7	88.2	85.1	83.0	81.8
75°	84.3	84.7	83.6	79.1	75.8	71.9	68.4	67.5	65.3	63.6	62.5
77.5°	53.3	55.5	55.6	55.4	54.1	51.7	50.2	49.6	47.5	46.8	46.6
80°	36.6	39.0	41.2	40.9	40.5	39.9	38.7	38.1	37.0	36.4	35.9
82.5°	24.4	26.6	28.5	29.6	29.5	28.8	28.2	27.8	27.6	27.1	27.1
85°	11.5	12.0	12.6	14.1	15.3	15.5	15.3	15.0	14.4	14.6	14.8
87.5°	5.9	5.7	5.7	5.4	4.9	5.5	5.7	5.7	5.6	5.5	5.4
90°	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8	1.5	2.9	4.4
92.5°	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0	10.9	17.1	26.2
95°	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3	25.1	30.9	39.0
97.5°	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3	41.3	45.4	53.5
100°	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6	53.1	56.0	64.1
102.5°	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0	64.8	67.2	75.9
105°	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3	83.3	87.0	94.3
107.5°	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2	103.6	107.2	113.2
110°	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7	117.2	120.1	126.8



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2	130.7	133.1	139.7
115°	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8	150.3	152.6	159.2
117.5°	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5	168.8	171.2	177.8
120°	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3	180.6	183.5	190.1
122.5°	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8	192.4	194.7	201.3
125°	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3	207.8	211.5	218.1
127.5°	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6	220.8	225.6	233.9
130°	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2	228.5	234.3	243.9
132.5°	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1	235.0	242.0	252.8
135°	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8	244.7	253.5	265.3
137.5°	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8	256.0	264.3	276.1
140°	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9	263.1	271.9	283.7
142.5°	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1	270.8	279.0	290.8
145°	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5	283.0	290.4	300.7
147.5°	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5	295.4	301.7	311.3
150°	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2	303.6	308.8	318.4
152.5°	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4	311.3	315.8	324.2
155°	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3	321.3	325.7	333.1
157.5°	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0	330.9	334.4	340.7
160°	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5	336.8	339.8	344.9
162.5°	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8	342.1	345.1	349.6
165°	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8	349.3	351.6	355.2
167.5°	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1	355.3	356.7	358.7
170°	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7	358.9	359.7	361.1
172.5°	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0	360.7	361.4	362.9
175°	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8	363.4	364.1	364.8
177.5°	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1	365.0	365.0	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	521.6	519.2	517.5	514.0	511.5	510.5	508.6	508.0	510.0	508.6	508.4
5°	506.1	499.8	494.8	489.8	484.4	480.9	475.6	474.8	473.4	471.6	471.1
7.5°	487.6	479.3	472.9	464.6	457.4	451.6	445.1	442.0	440.3	437.7	434.3
10°	475.0	465.2	456.5	448.2	439.3	432.1	425.6	420.6	417.3	414.2	412.9
12.5°	462.6	452.6	441.5	431.5	421.5	413.5	406.2	402.9	399.4	395.8	392.8
15°	443.4	430.2	417.9	406.4	397.9	389.2	382.2	377.4	372.0	370.4	364.6
17.5°	423.0	410.0	395.7	383.6	373.7	364.1	356.5	351.0	346.9	341.3	338.7
20°	410.3	394.8	380.9	369.8	358.9	347.6	339.8	335.2	331.3	326.7	324.5
22.5°	396.7	381.6	367.3	354.3	343.3	332.1	326.5	321.8	317.4	313.1	310.2
25°	376.7	361.6	346.5	333.0	321.5	313.4	306.9	301.4	299.1	294.9	291.8
27.5°	357.0	340.8	325.3	311.8	302.7	294.7	289.4	285.1	280.8	277.2	274.5
30°	344.3	327.8	310.8	300.1	290.5	283.0	277.0	272.9	269.7	266.4	264.4
32.5°	331.6	314.5	299.4	287.9	278.9	272.3	266.3	262.2	258.8	255.2	252.9
35°	311.2	293.8	281.6	270.3	261.4	255.2	251.1	245.4	242.6	240.0	237.6
37.5°	292.3	276.1	262.9	253.0	245.2	239.1	233.8	230.7	227.2	224.9	222.9
40°	278.3	263.5	251.6	241.1	235.4	228.7	223.7	219.7	217.2	214.1	211.9
42.5°	265.8	252.0	240.3	231.0	223.9	218.2	213.4	209.4	206.1	204.0	202.2
45°	248.1	234.3	223.0	214.3	207.7	202.4	197.3	195.4	191.0	188.4	187.5
47.5°	229.7	217.4	206.5	198.5	191.8	186.6	181.9	178.0	175.5	173.0	171.5
50°	217.4	205.6	195.4	187.5	181.0	175.3	171.0	168.3	165.0	162.7	161.0
52.5°	205.0	194.1	183.9	176.3	170.7	165.0	160.1	157.6	154.5	153.0	151.7
55°	187.3	175.8	167.0	159.7	153.7	148.5	143.9	141.4	139.4	137.9	137.4
57.5°	167.3	158.2	150.1	143.4	137.2	132.3	128.3	125.8	124.1	123.9	122.5
60°	154.2	145.9	138.6	131.3	126.1	121.5	118.0	115.2	113.5	113.3	112.8
62.5°	141.1	133.2	126.3	120.0	115.3	110.9	107.5	104.4	103.4	102.3	101.3
65°	121.8	114.5	108.9	103.9	98.9	95.2	91.9	89.9	87.6	86.2	83.9
67.5°	102.7	97.2	91.7	87.5	83.5	80.0	77.3	74.4	72.8	71.7	70.0
70°	90.2	85.8	80.4	75.8	72.8	69.9	67.8	64.5	63.3	62.5	61.6
72.5°	78.3	74.5	69.9	66.2	63.2	60.5	58.0	56.5	55.3	54.5	54.0
75°	61.6	58.0	54.0	51.4	49.2	47.0	45.7	44.7	44.2	44.0	43.2
77.5°	45.2	43.3	40.2	38.1	36.7	35.7	34.6	34.0	33.9	33.0	32.7
80°	34.6	33.6	30.9	30.1	28.9	28.1	27.4	26.4	25.3	24.8	24.1
82.5°	25.7	24.7	23.6	22.2	21.3	20.7	20.2	19.7	19.9	19.2	18.9
85°	13.8	12.6	12.2	12.0	11.5	12.0	11.8	11.5	11.3	11.1	11.3
87.5°	5.6	5.8	5.8	6.4	6.0	6.5	6.7	6.7	6.8	7.0	7.1
90°	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3	14.0	14.7	16.2
92.5°	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6	94.8	71.4	60.4
95°	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9	417.8	327.3	265.3
97.5°	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2	710.6	622.3	536.2
100°	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4	870.3	794.5	717.8
102.5°	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9	968.3	931.8	880.0
105°	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7	1023.7	1056.1	1048.0
107.5°	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5	974.3	1057.5	1096.0
110°	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3	918.2	1022.2	1084.8



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9	862.8	967.9	1041.8
115°	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2	783.4	884.4	964.7
117.5°	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0	728.4	815.4	889.1
120°	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7	697.2	778.3	843.1
122.5°	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9	674.8	747.0	807.8
125°	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7	644.9	709.0	762.0
127.5°	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1	616.2	676.1	725.8
130°	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3	596.3	653.7	701.6
132.5°	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6	577.3	629.5	675.6
135°	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5	548.3	595.5	637.4
137.5°	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3	522.4	561.6	597.2
140°	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4	507.0	540.9	571.8
142.5°	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8	494.1	523.2	550.1
145°	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7	477.6	500.4	520.3
147.5°	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3	463.8	481.4	496.4
150°	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0	456.2	470.1	483.4
152.5°	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0	448.6	461.4	471.6
155°	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3	437.1	447.3	455.4
157.5°	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4	426.1	434.0	440.5
160°	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5	417.8	425.3	430.4
162.5°	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0	410.8	417.0	421.5
165°	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0	400.2	404.6	408.3
167.5°	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4	389.8	393.2	395.9
170°	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7	384.0	386.2	387.7
172.5°	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5	378.6	380.3	381.2
175°	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7	370.7	372.2	372.2
177.5°	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7	367.3	367.3	367.3
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.2	506.3	505.8	506.5	505.8	506.3	508.2	508.4	508.6	510.0	508.0
5°	468.9	466.7	467.8	467.4	467.8	466.7	468.9	471.1	471.6	473.4	474.8
7.5°	434.3	431.6	428.8	429.6	428.8	431.6	434.3	434.3	437.7	440.3	442.0
10°	410.1	407.9	406.6	407.7	406.6	407.9	410.1	412.9	414.2	417.3	420.6
12.5°	389.7	388.4	387.3	386.8	387.3	388.4	389.7	392.8	395.8	399.4	402.9
15°	361.9	359.4	358.3	355.4	358.3	359.4	361.9	364.6	370.4	372.0	377.4
17.5°	336.4	335.5	332.7	331.5	332.7	335.5	336.4	338.7	341.3	346.9	351.0
20°	321.2	320.4	317.5	319.2	317.5	320.4	321.2	324.5	326.7	331.3	335.2
22.5°	308.7	306.8	305.9	305.4	305.9	306.8	308.7	310.2	313.1	317.4	321.8
25°	291.0	288.1	287.0	285.8	287.0	288.1	291.0	291.8	294.9	299.1	301.4
27.5°	273.2	271.7	270.3	269.9	270.3	271.7	273.2	274.5	277.2	280.8	285.1
30°	261.7	260.2	259.2	259.2	259.2	260.2	261.7	264.4	266.4	269.7	272.9
32.5°	251.5	250.3	249.2	249.0	249.2	250.3	251.5	252.9	255.2	258.8	262.2
35°	236.5	234.8	234.3	233.0	234.3	234.8	236.5	237.6	240.0	242.6	245.4
37.5°	220.9	219.5	219.5	219.3	219.5	219.5	220.9	222.9	224.9	227.2	230.7
40°	211.0	209.9	209.7	208.2	209.7	209.9	211.0	211.9	214.1	217.2	219.7
42.5°	200.4	199.8	199.1	198.4	199.1	199.8	200.4	202.2	204.0	206.1	209.4
45°	186.0	184.5	184.5	183.4	184.5	184.5	186.0	187.5	188.4	191.0	195.4
47.5°	171.1	169.9	170.0	168.9	170.0	169.9	171.1	171.5	173.0	175.5	178.0
50°	161.2	160.5	160.3	159.9	160.3	160.5	161.2	161.0	162.7	165.0	168.3
52.5°	151.3	150.9	151.7	150.8	151.7	150.9	151.3	151.7	153.0	154.5	157.6
55°	137.9	137.2	138.6	137.2	138.6	137.2	137.9	137.4	137.9	139.4	141.4
57.5°	122.5	121.9	123.1	122.4	123.1	121.9	122.5	122.5	123.9	124.1	125.8
60°	112.4	111.0	111.7	112.0	111.7	111.0	112.4	112.8	113.3	113.5	115.2
62.5°	100.4	99.5	100.1	99.1	100.1	99.5	100.4	101.3	102.3	103.4	104.4
65°	83.4	82.8	81.9	81.4	81.9	82.8	83.4	83.9	86.2	87.6	89.9
67.5°	70.1	68.5	68.4	68.8	68.4	68.5	70.1	70.0	71.7	72.8	74.4
70°	60.3	60.3	60.1	60.1	60.1	60.3	60.3	61.6	62.5	63.3	64.5
72.5°	53.5	53.3	53.0	52.8	53.0	53.3	53.5	54.0	54.5	55.3	56.5
75°	43.2	43.4	42.9	42.7	42.9	43.4	43.2	43.2	44.0	44.2	44.7
77.5°	31.9	30.9	31.4	30.9	31.4	30.9	31.9	32.7	33.0	33.9	34.0
80°	24.1	23.9	24.6	23.9	24.6	23.9	24.1	24.1	24.8	25.3	26.4
82.5°	19.1	18.9	19.2	18.8	19.2	18.9	19.1	18.9	19.2	19.9	19.7
85°	11.5	11.3	11.1	11.3	11.1	11.3	11.5	11.3	11.1	11.3	11.5
87.5°	7.3	7.1	7.3	7.3	7.3	7.1	7.3	7.1	7.0	6.8	6.7
90°	16.2	16.2	17.0	17.0	17.0	16.2	16.2	16.2	14.7	14.0	13.3
92.5°	51.0	49.2	48.2	47.0	48.2	49.2	51.0	60.4	71.4	94.8	130.6
95°	213.0	190.9	185.0	173.1	185.0	190.9	213.0	265.3	327.3	417.8	529.9
97.5°	490.7	449.4	428.0	418.6	428.0	449.4	490.7	536.2	622.3	710.6	789.2
100°	666.9	613.9	586.6	574.9	586.6	613.9	666.9	717.8	794.5	870.3	906.4
102.5°	825.6	787.8	758.2	749.3	758.2	787.8	825.6	880.0	931.8	968.3	945.9
105°	1024.4	1000.0	985.3	976.5	985.3	1000.0	1024.4	1048.0	1056.1	1023.7	922.7
107.5°	1108.0	1107.8	1103.0	1097.0	1103.0	1107.8	1108.0	1096.0	1057.5	974.3	839.5
110°	1117.9	1132.0	1137.2	1137.2	1137.2	1132.0	1117.9	1084.8	1022.2	918.2	778.3



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1090.2	1114.3	1127.1	1132.5	1127.1	1114.3	1090.2	1041.8	967.9	862.8	729.9
115°	1022.2	1057.5	1078.2	1087.8	1078.2	1057.5	1022.2	964.7	884.4	783.4	669.2
117.5°	946.6	983.1	1003.6	1009.5	1003.6	983.1	946.6	889.1	815.4	728.4	630.0
120°	897.6	933.0	952.9	958.8	952.9	933.0	897.6	843.1	778.3	697.2	608.7
122.5°	856.4	888.8	908.7	914.0	908.7	888.8	856.4	807.8	747.0	674.8	592.9
125°	803.3	833.5	849.7	857.1	849.7	833.5	803.3	762.0	709.0	644.9	569.7
127.5°	763.2	789.9	805.2	808.4	805.2	789.9	763.2	725.8	676.1	616.2	546.1
130°	738.5	762.8	777.5	781.9	777.5	762.8	738.5	701.6	653.7	596.3	531.3
132.5°	712.5	736.8	750.4	755.4	750.4	736.8	712.5	675.6	629.5	577.3	516.6
135°	669.9	694.2	707.5	711.9	707.5	694.2	669.9	637.4	595.5	548.3	497.5
137.5°	626.3	648.4	660.6	665.5	660.6	648.4	626.3	597.2	561.6	522.4	481.3
140°	599.2	618.3	629.3	633.0	629.3	618.3	599.2	571.8	540.9	507.0	472.4
142.5°	573.3	589.5	599.9	602.9	599.9	589.5	573.3	550.1	523.2	494.1	464.8
145°	538.0	550.5	558.6	561.6	558.6	550.5	538.0	520.3	500.4	477.6	454.7
147.5°	510.4	520.5	525.2	526.5	525.2	520.5	510.4	496.4	481.4	463.8	445.3
150°	494.6	503.3	506.3	507.0	506.3	503.3	494.6	483.4	470.1	456.2	440.0
152.5°	481.0	488.0	491.0	491.7	491.0	488.0	481.0	471.6	461.4	448.6	434.0
155°	462.8	468.0	470.1	470.9	470.1	468.0	462.8	455.4	447.3	437.1	425.3
157.5°	446.2	450.4	452.5	452.3	452.5	450.4	446.2	440.5	434.0	426.1	416.4
160°	435.5	439.2	440.7	440.0	440.7	439.2	435.5	430.4	425.3	417.8	410.5
162.5°	425.6	428.6	429.0	428.8	429.0	428.6	425.6	421.5	417.0	410.8	404.0
165°	411.2	412.7	412.7	412.7	412.7	412.7	411.2	408.3	404.6	400.2	395.0
167.5°	397.4	398.7	398.1	397.9	398.1	398.7	397.4	395.9	393.2	389.8	386.4
170°	389.1	389.8	389.8	389.1	389.8	389.8	389.1	387.7	386.2	384.0	381.7
172.5°	381.4	382.8	381.6	380.9	381.6	382.8	381.4	381.2	380.3	378.6	376.5
175°	372.2	372.9	371.5	370.7	371.5	372.9	372.2	372.2	372.2	370.7	370.7
177.5°	366.7	367.3	365.5	365.5	365.5	367.3	366.7	367.3	367.3	367.3	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	508.6	510.5	511.5	514.0	517.5	519.2	521.6	523.4	525.8	528.8	531.2
5°	475.6	480.9	484.4	489.8	494.8	499.8	506.1	510.7	516.8	523.8	529.2
7.5°	445.1	451.6	457.4	464.6	472.9	479.3	487.6	496.0	505.5	515.4	524.7
10°	425.6	432.1	439.3	448.2	456.5	465.2	475.0	484.8	496.8	507.8	520.5
12.5°	406.2	413.5	421.5	431.5	441.5	452.6	462.6	473.6	486.5	501.0	514.4
15°	382.2	389.2	397.9	406.4	417.9	430.2	443.4	458.0	472.4	488.5	505.3
17.5°	356.5	364.1	373.7	383.6	395.7	410.0	423.0	439.0	455.2	473.9	493.7
20°	339.8	347.6	358.9	369.8	380.9	394.8	410.3	426.7	443.8	463.6	485.7
22.5°	326.5	332.1	343.3	354.3	367.3	381.6	396.7	413.8	432.5	453.1	476.1
25°	306.9	313.4	321.5	333.0	346.5	361.6	376.7	394.8	415.3	436.2	460.8
27.5°	289.4	294.7	302.7	311.8	325.3	340.8	357.0	375.9	396.9	418.2	444.0
30°	277.0	283.0	290.5	300.1	310.8	327.8	344.3	362.9	384.2	406.1	432.7
32.5°	266.3	272.3	278.9	287.9	299.4	314.5	331.6	349.8	371.5	394.2	420.0
35°	251.1	255.2	261.4	270.3	281.6	293.8	311.2	330.4	351.5	375.0	401.0
37.5°	233.8	239.1	245.2	253.0	262.9	276.1	292.3	311.7	331.3	353.7	377.4
40°	223.7	228.7	235.4	241.1	251.6	263.5	278.3	298.6	318.2	339.3	360.9
42.5°	213.4	218.2	223.9	231.0	240.3	252.0	265.8	284.6	305.7	325.6	343.7
45°	197.3	202.4	207.7	214.3	223.0	234.3	248.1	265.2	283.5	301.9	315.6
47.5°	181.9	186.6	191.8	198.5	206.5	217.4	229.7	245.0	262.7	278.2	288.0
50°	171.0	175.3	181.0	187.5	195.4	205.6	217.4	232.3	247.2	261.4	270.3
52.5°	160.1	165.0	170.7	176.3	183.9	194.1	205.0	217.9	232.1	243.6	250.9
55°	143.9	148.5	153.7	159.7	167.0	175.8	187.3	197.6	208.7	218.5	222.8
57.5°	128.3	132.3	137.2	143.4	150.1	158.2	167.3	177.1	184.9	191.9	196.8
60°	118.0	121.5	126.1	131.3	138.6	145.9	154.2	163.3	169.5	175.3	179.9
62.5°	107.5	110.9	115.3	120.0	126.3	133.2	141.1	148.5	154.5	158.4	163.7
65°	91.9	95.2	98.9	103.9	108.9	114.5	121.8	127.1	131.3	135.7	138.9
67.5°	77.3	80.0	83.5	87.5	91.7	97.2	102.7	107.3	110.1	112.7	116.6
70°	67.8	69.9	72.8	75.8	80.4	85.8	90.2	93.7	95.6	98.2	103.0
72.5°	58.0	60.5	63.2	66.2	69.9	74.5	78.3	81.8	83.0	85.1	88.2
75°	45.7	47.0	49.2	51.4	54.0	58.0	61.6	62.5	63.6	65.3	67.5
77.5°	34.6	35.7	36.7	38.1	40.2	43.3	45.2	46.6	46.8	47.5	49.6
80°	27.4	28.1	28.9	30.1	30.9	33.6	34.6	35.9	36.4	37.0	38.1
82.5°	20.2	20.7	21.3	22.2	23.6	24.7	25.7	27.1	27.1	27.6	27.8
85°	11.8	12.0	11.5	12.0	12.2	12.6	13.8	14.8	14.6	14.4	15.0
87.5°	6.7	6.5	6.0	6.4	5.8	5.8	5.6	5.4	5.5	5.6	5.7
90°	12.5	11.8	10.3	9.6	8.1	7.4	5.9	4.4	2.9	1.5	0.8
92.5°	192.4	237.6	241.4	168.1	100.7	60.4	38.9	26.2	17.1	10.9	9.0
95°	638.9	653.0	532.8	329.4	167.3	88.4	55.2	39.0	30.9	25.1	24.3
97.5°	808.4	697.3	475.8	263.0	144.1	92.0	68.1	53.5	45.4	41.3	40.3
100°	849.7	665.5	424.5	238.7	143.0	100.2	78.1	64.1	56.0	53.1	51.6
102.5°	825.0	609.4	385.6	228.8	148.3	110.3	88.7	75.9	67.2	64.8	64.0
105°	745.8	534.3	347.9	224.8	159.2	126.8	106.1	94.3	87.0	83.3	83.3
107.5°	665.1	482.6	332.0	231.6	175.4	144.0	125.5	113.2	107.2	103.6	102.2
110°	619.1	458.4	327.3	238.1	187.2	156.9	137.8	126.8	120.1	117.2	115.7



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	584.8	444.2	327.3	246.3	198.4	169.4	150.8	139.7	133.1	130.7	129.2
115°	547.5	429.0	329.4	258.6	215.9	188.7	170.2	159.2	152.6	150.3	148.8
117.5°	525.3	421.4	334.3	272.9	233.9	208.1	190.3	177.8	171.2	168.8	166.5
120°	512.9	417.8	339.0	282.3	246.9	221.1	202.6	190.1	183.5	180.6	178.3
122.5°	502.3	414.9	343.1	292.8	259.3	233.5	215.1	201.3	194.7	192.4	190.8
125°	487.9	411.2	350.1	307.3	275.6	251.3	232.1	218.1	211.5	207.8	206.3
127.5°	474.6	409.4	357.9	320.6	291.4	268.0	248.8	233.9	225.6	220.8	218.6
130°	465.8	408.3	362.6	329.4	301.4	278.6	259.4	243.9	234.3	228.5	226.2
132.5°	458.7	408.3	367.9	337.1	310.9	288.0	268.8	252.8	242.0	235.0	232.1
135°	450.3	408.3	375.1	347.9	323.6	300.7	280.8	265.3	253.5	244.7	241.8
137.5°	442.8	409.2	381.7	355.8	332.5	311.7	291.2	276.1	264.3	256.0	253.8
140°	439.2	409.7	384.7	361.1	339.0	317.6	297.7	283.7	271.9	263.1	260.9
142.5°	436.3	410.4	386.4	364.1	343.1	322.9	304.3	290.8	279.0	270.8	269.1
145°	431.9	409.7	388.4	368.4	350.1	330.9	314.0	300.7	290.4	283.0	281.5
147.5°	427.3	407.8	389.1	371.2	354.5	337.7	322.8	311.3	301.7	295.4	294.5
150°	423.8	406.0	389.1	372.9	357.4	341.2	328.7	318.4	308.8	303.6	302.2
152.5°	419.6	403.7	388.5	374.1	360.3	345.3	334.0	324.2	315.8	311.3	310.4
155°	412.7	399.4	386.9	375.1	363.4	350.8	340.4	333.1	325.7	321.3	321.3
157.5°	406.2	395.0	385.0	375.9	365.8	355.1	347.2	340.7	334.4	330.9	331.0
160°	401.0	392.1	383.2	375.9	367.0	357.4	350.8	344.9	339.8	336.8	337.5
162.5°	396.2	388.5	381.4	375.2	368.2	359.8	354.3	349.6	345.1	342.1	342.8
165°	389.1	383.2	378.8	374.4	368.4	362.6	358.2	355.2	351.6	349.3	350.8
167.5°	382.2	378.1	374.7	372.6	368.4	363.6	360.8	358.7	356.7	355.3	356.1
170°	378.1	375.1	372.9	371.5	368.4	364.8	362.6	361.1	359.7	358.9	359.7
172.5°	373.9	371.6	370.5	370.2	367.9	364.8	363.7	362.9	361.4	360.7	362.0
175°	368.4	367.8	367.8	368.4	367.0	364.8	364.8	364.8	364.1	363.4	364.8
177.5°	366.1	365.5	365.5	366.7	366.1	365.0	365.0	365.5	365.0	365.0	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	533.1	534.7	537.0	539.6	541.7	543.9	545.2	545.2	546.2	548.5	551.5
5°	534.7	540.4	545.7	552.7	558.2	564.5	569.3	573.9	578.0	583.2	588.7
7.5°	534.2	543.7	553.5	564.4	576.6	586.2	596.1	603.8	611.4	621.5	629.3
10°	532.5	544.7	558.0	571.9	587.2	600.4	612.5	623.3	633.8	644.7	654.5
12.5°	529.3	544.9	561.1	577.9	597.1	612.3	627.7	639.3	651.6	663.5	675.5
15°	524.6	542.9	562.5	585.9	609.4	626.3	641.6	656.7	668.0	681.5	693.1
17.5°	514.9	538.5	563.2	588.6	611.2	630.9	647.0	661.3	673.4	688.2	703.9
20°	509.2	534.7	560.3	587.6	609.2	629.4	644.9	659.7	674.7	694.1	713.2
22.5°	501.1	528.4	555.6	581.5	604.3	623.9	639.8	657.9	677.7	699.6	722.8
25°	488.5	516.6	543.6	568.2	590.4	610.5	632.3	656.7	680.6	709.5	742.9
27.5°	472.4	499.5	523.6	549.6	571.7	597.2	624.3	650.8	685.3	725.2	766.8
30°	460.4	486.1	509.0	533.6	558.6	586.7	617.2	648.4	689.6	736.3	785.8
32.5°	446.5	469.8	492.4	516.1	545.1	575.9	608.3	646.4	695.6	748.9	800.0
35°	422.3	443.2	465.2	491.5	522.3	555.8	597.2	643.6	703.0	760.3	806.3
37.5°	396.9	413.5	435.5	463.4	496.8	535.6	582.6	638.9	699.9	751.4	770.9
40°	377.4	392.9	416.2	445.4	478.5	520.9	573.6	631.6	693.1	728.7	727.2
42.5°	358.1	373.7	396.2	425.6	460.1	507.6	561.8	622.0	673.8	687.4	659.1
45°	328.4	343.0	365.0	394.6	431.7	481.5	538.6	596.3	629.4	607.4	551.2
47.5°	298.2	312.4	332.8	361.7	402.2	454.4	508.4	555.7	560.3	513.1	445.7
50°	278.3	291.6	311.0	342.0	381.2	432.1	484.2	521.4	509.8	452.1	382.7
52.5°	259.0	271.7	289.9	319.1	359.2	409.1	455.5	484.8	458.1	396.7	334.2
55°	230.5	242.6	260.9	287.7	324.0	369.8	410.6	421.2	382.0	320.2	269.7
57.5°	203.3	212.3	230.3	254.0	289.1	329.4	358.5	356.7	313.4	257.7	221.4
60°	185.3	193.4	210.6	232.3	265.7	301.9	322.3	313.6	269.8	223.9	189.1
62.5°	168.6	176.2	190.6	210.6	239.2	270.7	285.6	273.5	232.2	191.8	164.1
65°	143.3	148.7	160.3	178.8	201.2	223.0	236.3	218.7	182.1	151.6	130.6
67.5°	119.6	124.3	134.6	147.9	163.3	178.4	183.8	167.3	138.8	118.3	103.5
70°	104.3	108.7	115.6	128.1	138.3	148.9	151.6	136.8	113.0	97.4	88.2
72.5°	89.7	93.7	99.8	108.6	115.6	121.8	123.0	109.2	91.0	80.3	73.2
75°	68.4	71.9	75.8	79.1	83.6	84.7	84.3	73.6	63.8	56.6	52.7
77.5°	50.2	51.7	54.1	55.4	55.6	55.5	53.3	46.6	41.5	38.5	36.9
80°	38.7	39.9	40.5	40.9	41.2	39.0	36.6	32.4	30.7	28.9	27.1
82.5°	28.2	28.8	29.5	29.6	28.5	26.6	24.4	22.3	21.1	20.3	19.5
85°	15.3	15.5	15.3	14.1	12.6	12.0	11.5	11.1	10.9	10.7	10.7
87.5°	5.7	5.5	4.9	5.4	5.7	5.7	5.9	5.9	6.0	6.1	6.3
90°	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5	13.3
92.5°	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4	130.6
95°	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9	529.9
97.5°	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4	789.2
100°	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7	906.4
102.5°	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0	945.9
105°	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8	922.7
107.5°	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1	839.5
110°	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1	778.3



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8	729.9
115°	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5	669.2
117.5°	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3	630.0
120°	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9	608.7
122.5°	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3	592.9
125°	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9	569.7
127.5°	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6	546.1
130°	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8	531.3
132.5°	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7	516.6
135°	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3	497.5
137.5°	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8	481.3
140°	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2	472.4
142.5°	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3	464.8
145°	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9	454.7
147.5°	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3	445.3
150°	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8	440.0
152.5°	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6	434.0
155°	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7	425.3
157.5°	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2	416.4
160°	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0	410.5
162.5°	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2	404.0
165°	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1	395.0
167.5°	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2	386.4
170°	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1	381.7
172.5°	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9	376.5
175°	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4	370.7
177.5°	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1	366.7
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	530.6	530.6	530.6	530.6	530.6	530.6	530.6
2.5°	553.7	553.7	556.7	556.5	558.5	557.7	558.1
5°	595.2	598.9	602.2	604.4	607.7	608.5	608.0
7.5°	638.3	646.5	650.4	656.0	657.0	659.9	659.6
10°	664.9	673.0	679.1	683.8	686.3	689.3	689.6
12.5°	685.8	692.7	698.0	702.5	705.4	706.3	706.9
15°	702.2	709.7	716.0	722.4	726.1	729.0	730.5
17.5°	718.6	730.4	741.5	750.1	755.3	759.6	759.6
20°	731.3	744.8	758.7	768.5	778.6	783.0	783.6
22.5°	744.9	765.5	783.5	798.7	811.9	816.4	818.1
25°	773.2	800.1	827.8	849.1	864.4	873.4	874.7
27.5°	807.3	843.8	872.9	892.6	905.2	911.9	913.3
30°	831.3	865.1	891.2	906.0	911.9	912.8	909.5
32.5°	842.1	867.3	877.8	876.9	865.3	857.7	854.8
35°	828.9	823.7	798.2	767.7	744.4	729.6	725.7
37.5°	754.3	709.3	662.4	616.3	591.8	579.3	557.9
40°	680.8	616.5	567.8	529.0	501.3	479.1	473.9
42.5°	597.9	531.5	482.8	449.6	427.4	412.3	405.6
45°	480.4	423.4	383.0	357.6	340.6	329.5	324.5
47.5°	384.3	340.1	310.8	291.9	278.9	269.3	266.6
50°	331.5	296.1	271.4	255.4	245.6	238.3	235.3
52.5°	287.9	259.4	240.3	227.2	218.0	213.4	210.8
55°	237.6	213.0	199.3	188.8	183.6	179.9	178.1
57.5°	194.4	176.5	166.5	159.3	154.5	152.1	151.3
60°	170.1	156.2	147.0	141.4	138.1	135.1	134.1
62.5°	148.6	137.7	130.6	125.6	122.4	121.1	120.6
65°	119.8	112.6	107.4	104.3	101.7	101.2	101.0
67.5°	95.2	91.0	88.2	85.1	84.2	82.7	82.3
70°	81.4	78.6	75.3	74.3	73.1	71.6	71.9
72.5°	69.1	66.3	64.0	62.6	62.2	61.5	62.1
75°	50.5	49.7	48.8	47.7	47.2	47.2	47.0
77.5°	36.1	35.3	34.4	33.7	33.6	32.7	33.0
80°	26.1	25.1	24.6	24.8	24.1	23.9	23.9
82.5°	19.3	18.9	18.5	18.6	18.4	18.2	18.4
85°	10.7	10.5	10.5	10.3	10.3	10.0	10.0
87.5°	6.6	7.0	6.9	6.7	6.7	7.1	7.3
90°	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2



TEST NUMBER: P333504-830

CATALOG NUMBER: S125RDIP-S375D810U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)