

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333540-830

Luminaire Tested: **S125RDIP-S610D1035U830-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333540-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S610D1035U830-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5762.1 lumens
Efficiency: N/A
Efficacy: 129.5 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39																												
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40	34																												
2	87	80	74	70	79	73	68	64	60	57	54	48	46	43	37	35	34	29																												
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25																												
4	73	63	55	49	66	57	51	46	47	43	39	38	35	32	29	27	25	21																												
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19																												
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20	17																												
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15																												
8	53	41	34	28	48	38	31	27	32	26	23	26	22	19	20	18	16	13																												
9	49	37	30	25	45	34	28	24	29	24	20	24	20	17	19	16	14	12																												
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5633	5633	5633	5633
5°	6481	5641	4982	5641
10°	7434	5612	4395	5612
15°	8029	5554	3907	5554
20°	8854	5487	3608	5487
25°	10246	5399	3348	5399
30°	11150	5305	3177	5305
35°	9406	5196	3020	5196
40°	6568	5001	2886	5001
45°	4873	4738	2754	4738
50°	3885	4464	2640	4464
55°	3297	4124	2540	4124
60°	2849	3821	2378	3821
65°	2540	3492	2046	3492
70°	2232	3199	1866	3199
75°	1931	2770	1752	2770
80°	1465	2332	1465	2332
85°	1223	1830	1386	1830



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	1.5
10°-20°	245.1	4.3
20°-30°	388.6	6.7
30°-40°	468.7	8.1
40°-50°	418.5	7.3
50°-60°	321.0	5.6
60°-70°	208.6	3.6
70°-80°	101.4	1.8
80°-90°	26.8	0.5
90°-100°	338.3	5.9
100°-110°	727.2	12.6
110°-120°	682.5	11.8
120°-130°	553.1	9.6
130°-140°	443.9	7.7
140°-150°	334.9	5.8
150°-160°	235.8	4.1
160°-170°	139.0	2.4
170°-180°	45.2	0.8
0°-30°	717.4	12.5
0°-40°	1186.0	20.6
0°-60°	1925.5	33.4
0°-90°	2262.3	39.3
90°-120°	1747.9	30.3
90°-150°	3079.8	53.4
90°-180°	3500.0	60.7
0°-180°	5762.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	872	872	872	872	872	
5°	1000	870	768	870	1000	100
15°	1201	831	584	831	1201	344
25°	1438	758	470	758	1438	660
35°	1193	659	383	659	1193	721
45°	534	519	302	519	534	426
55°	293	366	226	366	293	266
65°	166	228	134	228	166	165
75°	77	111	70	111	77	82
85°	16	25	19	25	16	20
90°	22	1	22	1	22	16
95°	221	31	221	31	221	313
105°	1247	106	1247	106	1247	1239
115°	1389	190	1389	190	1389	1357
125°	1094	263	1094	263	1094	990
135°	909	309	909	309	909	704
145°	717	359	717	359	717	456
155°	601	410	601	410	601	280
165°	527	448	527	448	527	151
175°	473	466	473	466	473	46
180°	467	467	467	467	467	



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	917.5	916.9	918.0	914.8	915.2	910.3	910.3	906.5	901.7	898.0	896.3
5°	999.7	1000.4	998.9	993.5	990.0	984.6	978.5	967.8	958.8	950.3	943.5
7.5°	1084.3	1084.8	1080.1	1078.5	1069.4	1062.8	1049.3	1034.7	1021.7	1005.2	992.7
10°	1133.6	1133.2	1128.2	1124.3	1116.3	1106.4	1093.1	1075.9	1059.8	1041.9	1024.7
12.5°	1162.2	1161.3	1159.7	1154.9	1147.6	1138.7	1127.5	1110.6	1090.7	1071.1	1051.1
15°	1200.9	1198.3	1193.7	1187.6	1177.2	1166.9	1154.3	1139.3	1120.3	1098.2	1079.5
17.5°	1248.7	1248.8	1241.6	1233.2	1219.1	1200.7	1181.4	1157.2	1131.3	1106.9	1087.1
20°	1288.3	1287.1	1280.0	1263.6	1247.5	1224.6	1202.3	1172.6	1141.1	1109.2	1084.5
22.5°	1344.9	1342.2	1334.7	1313.1	1288.1	1258.6	1224.6	1188.4	1150.3	1114.1	1081.7
25°	1437.9	1435.8	1421.1	1396.0	1360.9	1315.4	1271.0	1221.3	1166.5	1118.9	1079.5
27.5°	1501.5	1499.1	1488.3	1467.4	1435.0	1387.2	1327.1	1260.7	1192.2	1126.7	1069.9
30°	1495.2	1500.5	1499.1	1489.5	1465.1	1422.1	1366.7	1291.8	1210.5	1133.6	1065.9
32.5°	1405.2	1410.0	1422.7	1441.6	1443.0	1425.9	1384.4	1315.3	1231.1	1143.6	1062.7
35°	1193.0	1199.5	1223.8	1262.1	1312.2	1354.2	1362.7	1325.5	1249.9	1155.7	1058.0
37.5°	917.2	952.4	972.9	1013.2	1088.9	1166.0	1240.1	1267.4	1235.3	1150.8	1050.4
40°	779.1	787.7	824.3	869.7	933.4	1013.6	1119.3	1195.5	1198.0	1139.3	1038.3
42.5°	666.8	677.7	702.8	739.0	793.6	873.8	982.9	1083.5	1130.1	1107.8	1022.6
45°	533.5	541.7	560.0	587.9	629.8	696.1	789.9	906.3	998.6	1034.7	980.3
47.5°	438.3	442.7	458.5	479.8	510.9	559.1	631.7	732.7	843.6	921.2	913.6
50°	386.7	391.7	403.9	420.0	446.1	486.9	545.0	629.1	743.3	838.2	857.1
52.5°	346.6	350.7	358.4	373.6	395.1	426.5	473.3	549.5	652.2	753.1	797.0
55°	292.8	295.8	301.8	310.4	327.6	350.2	390.6	443.3	526.3	628.0	692.5
57.5°	248.6	250.1	253.9	261.8	273.7	290.2	319.4	364.1	423.7	515.2	586.4
60°	220.6	222.0	227.0	232.3	241.7	256.7	279.7	310.8	368.1	443.7	515.6
62.5°	198.2	199.1	201.2	206.6	214.7	226.4	244.4	269.8	315.4	381.7	449.7
65°	166.2	166.5	167.2	171.5	176.5	185.1	196.9	214.8	249.2	299.4	359.5
67.5°	135.3	135.8	138.4	139.9	145.1	149.6	156.6	170.2	194.4	228.2	274.9
70°	118.2	117.8	120.3	122.1	123.9	129.2	133.9	145.0	160.0	185.9	224.9
72.5°	102.1	101.2	102.3	102.9	105.3	109.0	113.6	120.4	132.0	149.8	179.6
75°	77.4	77.7	77.7	78.4	80.2	81.6	83.0	86.6	93.1	104.9	121.0
77.5°	54.3	53.7	55.2	55.4	56.5	58.1	59.3	60.7	63.3	68.2	76.5
80°	39.4	39.4	39.8	40.8	40.4	41.2	43.0	44.4	47.6	50.5	53.3
82.5°	30.3	30.0	30.3	30.5	30.4	31.1	31.8	32.0	33.3	34.7	36.8
85°	16.5	16.5	16.9	16.9	17.2	17.2	17.5	17.5	17.5	17.9	18.3
87.5°	10.7	10.4	9.9	9.9	10.2	10.4	9.9	9.4	9.2	9.0	9.0
90°	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0	16.0	15.1	13.2
92.5°	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7	245.5	303.3	308.2
95°	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6	815.8	833.7	680.3
97.5°	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6	1032.2	890.3	607.5
100°	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3	1084.9	849.6	542.0
102.5°	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8	1053.3	778.2	492.3
105°	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0	952.3	682.1	444.1
107.5°	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9	849.0	616.1	423.8
110°	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6	790.3	585.2	417.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9	746.7	567.2	417.7
115°	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3	699.1	547.6	420.6
117.5°	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3	670.7	538.0	426.8
120°	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2	654.9	533.5	432.8
122.5°	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9	641.3	529.7	438.1
125°	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4	622.9	525.0	447.0
127.5°	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2	606.0	522.7	456.9
130°	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4	594.7	521.2	463.0
132.5°	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6	585.6	521.2	469.7
135°	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1	574.9	521.2	478.9
137.5°	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4	565.3	522.4	487.4
140°	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1	560.8	523.1	491.2
142.5°	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3	557.0	523.9	493.4
145°	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5	551.4	523.1	495.9
147.5°	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5	545.5	520.7	496.8
150°	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8	541.0	518.4	496.8
152.5°	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2	535.7	515.5	496.1
155°	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9	526.9	510.0	494.0
157.5°	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6	518.6	504.4	491.5
160°	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1	511.9	500.6	489.3
162.5°	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9	505.9	496.1	487.0
165°	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4	496.8	489.3	483.6
167.5°	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4	488.0	482.7	478.3
170°	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4	482.7	478.9	476.1
172.5°	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6	477.4	474.4	473.1
175°	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3	470.4	469.5	469.5
177.5°	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2	467.4	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	896.3	894.3	890.5	887.1	882.8	879.1	876.5	873.4	869.3	864.5	860.4
5°	935.9	928.0	917.7	908.7	897.3	888.3	879.0	870.1	861.1	849.6	839.6
7.5°	979.9	963.7	947.8	927.9	909.8	893.7	878.3	862.6	847.3	831.0	815.3
10°	1006.8	987.1	965.3	940.2	917.3	895.5	875.4	855.7	835.0	816.7	797.0
12.5°	1032.0	1006.6	981.7	950.0	922.5	895.8	870.2	845.7	823.5	799.8	778.6
15°	1054.8	1029.7	1001.8	963.2	924.8	892.6	862.5	830.7	803.1	776.6	753.0
17.5°	1063.6	1037.4	1004.8	967.7	925.9	885.3	846.6	811.6	779.2	748.3	721.7
20°	1060.2	1034.7	1001.5	966.0	921.2	879.0	837.1	798.4	762.2	729.7	701.4
22.5°	1051.9	1025.6	993.4	956.0	913.5	868.6	824.0	782.7	744.8	711.1	680.2
25°	1039.4	1003.6	970.6	934.2	893.7	849.3	803.1	757.6	717.2	682.8	649.1
27.5°	1026.4	981.8	939.9	903.5	860.8	821.2	776.7	730.1	687.5	652.5	618.0
30°	1014.7	964.6	918.4	877.2	836.8	799.2	756.9	711.4	667.8	631.6	596.5
32.5°	1000.1	946.8	896.1	848.6	809.5	772.2	734.0	690.5	648.0	610.7	575.0
35°	981.8	913.7	858.6	808.1	764.8	728.6	694.3	659.1	616.5	577.9	543.2
37.5°	957.7	880.5	816.7	761.7	716.0	679.7	652.6	620.5	581.6	544.6	512.4
40°	943.1	856.5	786.6	732.2	684.2	645.9	620.5	593.2	557.8	523.1	490.9
42.5°	923.6	834.4	756.3	699.6	651.3	614.4	588.7	565.0	535.2	502.5	468.0
45°	885.4	791.6	709.6	648.8	600.1	563.9	539.9	518.8	496.2	466.2	436.1
47.5°	835.8	747.1	661.2	594.7	547.1	513.5	490.2	473.5	457.4	431.9	402.7
50°	796.0	710.4	626.6	562.1	511.3	479.4	457.6	444.3	429.6	406.4	382.0
52.5°	748.9	672.6	590.5	524.6	476.6	446.8	425.7	412.6	400.4	381.4	358.3
55°	675.0	607.9	532.7	473.0	429.0	398.9	378.8	366.3	359.1	343.0	324.7
57.5°	589.5	541.5	475.2	417.5	378.6	348.8	334.2	323.6	315.5	304.1	291.2
60°	529.9	496.2	436.8	382.0	346.2	317.9	304.7	295.8	288.2	278.5	268.5
62.5°	469.5	445.0	393.3	346.2	313.3	289.5	277.2	269.1	260.4	253.9	244.2
65°	388.5	366.6	330.8	294.0	263.5	244.6	235.6	228.5	223.1	215.9	209.1
67.5°	302.2	293.3	268.6	243.2	221.3	204.4	196.7	191.7	185.2	181.0	176.3
70°	249.2	244.9	227.3	210.6	190.1	178.7	171.5	169.4	161.5	157.2	153.9
72.5°	202.3	200.2	190.1	178.4	164.1	154.0	147.4	145.0	140.0	136.6	134.5
75°	138.6	139.3	137.5	130.0	124.6	118.2	112.4	111.0	107.4	104.5	102.7
77.5°	87.7	91.3	91.4	91.0	89.0	85.0	82.7	81.5	78.0	77.0	76.5
80°	60.1	64.1	67.7	67.3	66.6	65.5	63.7	62.7	60.9	59.8	59.1
82.5°	40.1	43.7	46.8	48.7	48.5	47.5	46.3	45.7	45.4	44.6	44.5
85°	18.9	19.7	20.7	23.3	25.1	25.4	25.1	24.7	23.7	24.0	24.3
87.5°	9.0	8.7	8.8	8.4	7.7	8.8	9.2	9.3	9.0	8.8	8.6
90°	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9	1.9	3.8	5.7
92.5°	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5	13.9	21.9	33.5
95°	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0	32.0	39.5	49.9
97.5°	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6	52.7	58.0	68.3
100°	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9	67.8	71.5	81.8
102.5°	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7	82.8	85.8	96.9
105°	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3	106.3	111.0	120.5
107.5°	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4	132.3	136.8	144.5
110°	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7	149.6	153.4	161.8



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0	166.9	169.9	178.4
115°	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1	191.9	194.7	203.2
117.5°	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6	215.5	218.5	227.0
120°	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7	230.5	234.3	242.8
122.5°	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6	245.5	248.5	257.0
125°	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4	265.3	270.0	278.5
127.5°	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1	281.9	287.9	298.7
130°	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9	291.7	299.3	311.4
132.5°	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4	299.9	309.0	322.7
135°	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6	312.4	323.7	338.7
137.5°	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0	326.9	337.4	352.5
140°	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1	335.9	347.2	362.2
142.5°	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7	345.7	356.2	371.3
145°	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4	361.3	370.7	383.9
147.5°	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0	377.1	385.2	397.5
150°	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8	387.7	394.3	406.5
152.5°	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3	397.5	403.3	414.0
155°	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2	410.2	415.8	425.3
157.5°	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6	422.4	427.0	435.1
160°	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9	430.0	433.8	440.4
162.5°	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7	436.8	440.5	446.4
165°	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9	446.0	448.8	453.6
167.5°	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7	453.7	455.4	458.1
170°	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2	458.3	459.2	461.1
172.5°	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2	460.5	461.5	463.3
175°	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7	463.8	464.8	465.7
177.5°	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4	465.9	465.9	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	857.6	853.6	850.7	845.0	840.9	839.2	836.1	835.3	838.4	836.1	835.8
5°	832.1	821.7	813.5	805.2	796.3	790.6	781.9	780.5	778.4	775.1	774.5
7.5°	801.5	788.0	777.4	763.7	752.0	742.4	731.7	726.6	723.8	719.6	714.1
10°	780.9	764.8	750.5	736.9	722.2	710.4	699.6	691.4	686.0	681.0	678.8
12.5°	760.5	744.1	725.9	709.4	693.0	679.7	667.8	662.4	656.5	650.6	645.6
15°	729.0	707.1	687.1	668.1	654.1	639.8	628.4	620.5	611.5	609.1	599.4
17.5°	695.5	674.0	650.5	630.6	614.4	598.6	586.1	577.1	570.3	561.1	556.7
20°	674.6	649.1	626.2	607.9	590.0	571.5	558.6	551.0	544.6	537.1	533.5
22.5°	652.2	627.4	603.9	582.5	564.3	545.9	536.8	529.0	521.7	514.7	510.0
25°	619.4	594.4	569.7	547.4	528.5	515.2	504.4	495.5	491.6	484.7	479.8
27.5°	587.0	560.3	534.7	512.6	497.7	484.6	475.8	468.7	461.6	455.6	451.3
30°	566.1	538.9	511.0	493.4	477.6	465.1	455.4	448.7	443.3	437.9	434.7
32.5°	545.2	517.1	492.3	473.3	458.5	447.6	437.7	431.1	425.5	419.5	415.8
35°	511.6	483.0	463.0	444.3	429.6	419.6	412.8	403.5	398.9	394.5	390.6
37.5°	480.5	453.8	432.2	415.8	403.1	393.1	384.4	379.3	373.6	369.8	366.5
40°	457.6	433.2	413.6	396.3	387.0	376.0	367.7	361.3	356.9	351.9	348.4
42.5°	437.0	414.3	395.2	379.8	368.2	358.7	350.8	344.4	338.9	335.4	332.3
45°	407.8	385.2	366.6	352.3	341.6	332.6	324.4	321.1	314.0	309.7	308.3
47.5°	377.7	357.5	339.5	326.3	315.3	306.8	299.1	292.6	288.6	284.4	282.1
50°	357.3	338.0	321.1	308.3	297.6	288.2	281.1	276.7	271.4	267.5	264.6
52.5°	337.0	319.1	302.3	289.9	280.6	271.4	263.3	259.0	253.9	251.4	249.4
55°	307.9	289.0	274.7	262.4	252.8	244.2	236.7	232.3	229.1	226.7	225.9
57.5°	274.9	260.0	246.7	235.6	225.6	217.5	210.9	206.9	204.1	203.7	201.5
60°	253.4	239.9	227.7	215.9	207.3	199.8	194.1	189.5	186.5	186.2	185.5
62.5°	232.1	219.0	207.6	197.3	189.5	182.3	176.9	171.6	169.9	168.1	166.5
65°	200.1	188.3	179.0	170.8	162.6	156.5	151.1	147.9	143.9	141.8	137.9
67.5°	168.8	159.7	150.7	143.8	137.3	131.6	127.1	122.3	119.7	117.9	115.1
70°	148.3	141.1	132.1	124.6	119.6	114.9	111.3	105.9	104.2	102.7	101.3
72.5°	128.8	122.4	114.9	108.9	103.9	99.4	95.3	92.8	91.0	89.5	88.7
75°	101.3	95.2	88.8	84.5	81.0	77.4	75.2	73.4	72.7	72.3	70.9
77.5°	74.4	71.2	66.0	62.6	60.2	58.8	56.8	55.9	55.9	54.3	53.8
80°	56.9	55.1	50.8	49.4	47.6	46.2	45.1	43.4	41.6	40.8	39.8
82.5°	42.3	40.5	38.8	36.5	35.1	34.1	33.1	32.4	32.6	31.7	31.1
85°	22.5	20.7	20.1	19.7	18.9	19.7	19.3	18.9	18.7	18.3	18.7
87.5°	8.7	9.0	9.0	9.9	9.2	9.9	10.1	10.0	10.2	10.4	10.5
90°	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0	17.9	18.9	20.7
92.5°	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7	121.0	91.0	77.2
95°	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6	533.5	417.7	338.7
97.5°	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6	907.2	794.5	684.6
100°	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3	1111.3	1014.3	916.4
102.5°	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8	1236.1	1189.7	1123.4
105°	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0	1306.9	1348.3	1337.9
107.5°	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9	1243.9	1350.2	1399.3
110°	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6	1172.3	1305.0	1385.1



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9	1101.6	1235.8	1330.1
115°	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3	1000.2	1129.1	1231.6
117.5°	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3	930.0	1041.0	1135.1
120°	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2	890.1	993.6	1076.4
122.5°	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9	861.5	953.7	1031.2
125°	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4	823.3	905.1	972.9
127.5°	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2	786.8	863.2	926.6
130°	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4	761.2	834.6	895.8
132.5°	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6	737.1	803.7	862.6
135°	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1	700.0	760.3	813.9
137.5°	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4	666.9	717.0	762.5
140°	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1	647.3	690.6	730.2
142.5°	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3	630.7	668.1	702.3
145°	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5	609.7	638.9	664.3
147.5°	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5	592.2	614.6	633.8
150°	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8	582.4	600.3	617.3
152.5°	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2	572.6	589.0	602.2
155°	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9	558.0	571.2	581.5
157.5°	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6	544.0	554.2	562.3
160°	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1	533.5	542.9	549.5
162.5°	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9	524.4	532.3	538.2
165°	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4	511.0	516.6	521.2
167.5°	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4	497.8	502.1	505.5
170°	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4	490.2	493.0	494.9
172.5°	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6	483.4	485.5	486.6
175°	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3	473.3	475.1	475.1
177.5°	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2	468.9	468.9	468.9
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	835.6	832.4	831.5	832.6	831.5	832.4	835.6	835.8	836.1	838.4	835.3
5°	770.9	767.3	769.1	768.4	769.1	767.3	770.9	774.5	775.1	778.4	780.5
7.5°	714.0	709.5	704.8	706.3	704.8	709.5	714.0	714.1	719.6	723.8	726.6
10°	674.2	670.6	668.5	670.2	668.5	670.6	674.2	678.8	681.0	686.0	691.4
12.5°	640.6	638.6	636.7	635.9	636.7	638.6	640.6	645.6	650.6	656.5	662.4
15°	595.0	590.8	589.0	584.4	589.0	590.8	595.0	599.4	609.1	611.5	620.5
17.5°	553.0	551.6	547.0	545.0	547.0	551.6	553.0	556.7	561.1	570.3	577.1
20°	528.1	526.7	522.1	524.9	522.1	526.7	528.1	533.5	537.1	544.6	551.0
22.5°	507.5	504.4	502.8	502.0	502.8	504.4	507.5	510.0	514.7	521.7	529.0
25°	478.3	473.7	471.9	469.8	471.9	473.7	478.3	479.8	484.7	491.6	495.5
27.5°	449.3	446.8	444.4	443.8	444.4	446.8	449.3	451.3	455.6	461.6	468.7
30°	430.4	427.8	426.0	426.0	426.0	427.8	430.4	434.7	437.9	443.3	448.7
32.5°	413.5	411.5	409.7	409.4	409.7	411.5	413.5	415.8	419.5	425.5	431.1
35°	388.8	386.0	385.2	383.1	385.2	386.0	388.8	390.6	394.5	398.9	403.5
37.5°	363.3	360.9	360.8	360.6	360.8	360.9	363.3	366.5	369.8	373.6	379.3
40°	346.9	345.2	344.8	342.3	344.8	345.2	346.9	348.4	351.9	356.9	361.3
42.5°	329.5	328.6	327.3	326.2	327.3	328.6	329.5	332.3	335.4	338.9	344.4
45°	305.8	303.3	303.3	301.5	303.3	303.3	305.8	308.3	309.7	314.0	321.1
47.5°	281.3	279.4	279.6	277.7	279.6	279.4	281.3	282.1	284.4	288.6	292.6
50°	264.9	263.9	263.5	262.8	263.5	263.9	264.9	264.6	267.5	271.4	276.7
52.5°	248.6	248.2	249.5	247.9	249.5	248.2	248.6	249.4	251.4	253.9	259.0
55°	226.7	225.6	227.7	225.6	227.7	225.6	226.7	225.9	226.7	229.1	232.3
57.5°	201.3	200.4	202.3	201.2	202.3	200.4	201.3	201.5	203.7	204.1	206.9
60°	184.7	182.6	183.7	184.1	183.7	182.6	184.7	185.5	186.2	186.5	189.5
62.5°	164.9	163.7	164.5	162.9	164.5	163.7	164.9	166.5	168.1	169.9	171.6
65°	137.1	136.1	134.6	133.9	134.6	136.1	137.1	137.9	141.8	143.9	147.9
67.5°	115.2	112.6	112.5	113.1	112.5	112.6	115.2	115.1	117.9	119.7	122.3
70°	99.2	99.2	98.8	98.8	98.8	99.2	99.2	101.3	102.7	104.2	105.9
72.5°	88.0	87.8	87.1	86.8	87.1	87.8	88.0	88.7	89.5	91.0	92.8
75°	70.9	71.3	70.5	70.2	70.5	71.3	70.9	70.9	72.3	72.7	73.4
77.5°	52.3	50.8	51.7	50.8	51.7	50.8	52.3	53.8	54.3	55.9	55.9
80°	39.8	39.4	40.4	39.4	40.4	39.4	39.8	39.8	40.8	41.6	43.4
82.5°	31.5	31.1	31.6	30.8	31.6	31.1	31.5	31.1	31.7	32.6	32.4
85°	18.9	18.7	18.3	18.7	18.3	18.7	18.9	18.7	18.3	18.7	18.9
87.5°	10.7	10.5	10.7	10.7	10.7	10.5	10.7	10.5	10.4	10.2	10.0
90°	20.7	20.7	21.7	21.7	21.7	20.7	20.7	20.7	18.9	17.9	17.0
92.5°	65.1	62.9	61.5	60.0	61.5	62.9	65.1	77.2	91.0	121.0	166.7
95°	271.9	243.7	236.2	221.1	236.2	243.7	271.9	338.7	417.7	533.5	676.6
97.5°	626.5	573.7	546.5	534.4	546.5	573.7	626.5	684.6	794.5	907.2	1007.6
100°	851.5	783.8	748.9	734.0	748.9	783.8	851.5	916.4	1014.3	1111.3	1157.3
102.5°	1054.0	1005.9	968.0	956.7	968.0	1005.9	1054.0	1123.4	1189.7	1236.1	1207.8
105°	1307.9	1276.9	1258.0	1246.7	1258.0	1276.9	1307.9	1337.9	1348.3	1306.9	1178.0
107.5°	1414.6	1414.4	1408.2	1400.6	1408.2	1414.4	1414.6	1399.3	1350.2	1243.9	1071.9
110°	1427.4	1445.2	1451.8	1451.8	1451.8	1445.2	1427.4	1385.1	1305.0	1172.3	993.6



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1391.9	1422.7	1439.1	1445.8	1439.1	1422.7	1391.9	1330.1	1235.8	1101.6	931.9
115°	1305.0	1350.2	1376.6	1388.8	1376.6	1350.2	1305.0	1231.6	1129.1	1000.2	854.3
117.5°	1208.5	1255.2	1281.3	1288.8	1281.3	1255.2	1208.5	1135.1	1041.0	930.0	804.3
120°	1146.0	1191.2	1216.6	1224.2	1216.6	1191.2	1146.0	1076.4	993.6	890.1	777.2
122.5°	1093.3	1134.7	1160.2	1167.0	1160.2	1134.7	1093.3	1031.2	953.7	861.5	756.9
125°	1025.6	1064.1	1084.9	1094.3	1084.9	1064.1	1025.6	972.9	905.1	823.3	727.4
127.5°	974.4	1008.4	1028.0	1032.2	1028.0	1008.4	974.4	926.6	863.2	786.8	697.2
130°	942.8	973.8	992.7	998.3	992.7	973.8	942.8	895.8	834.6	761.2	678.4
132.5°	909.6	940.8	958.0	964.4	958.0	940.8	909.6	862.6	803.7	737.1	659.6
135°	855.3	886.4	903.2	908.9	903.2	886.4	855.3	813.9	760.3	700.0	635.1
137.5°	799.6	827.8	843.5	849.6	843.5	827.8	799.6	762.5	717.0	666.9	614.4
140°	765.0	789.5	803.5	808.2	803.5	789.5	765.0	730.2	690.6	647.3	603.1
142.5°	731.9	752.5	765.9	769.9	765.9	752.5	731.9	702.3	668.1	630.7	593.3
145°	686.8	702.9	713.2	717.0	713.2	702.9	686.8	664.3	638.9	609.7	580.5
147.5°	651.7	664.5	670.5	672.2	670.5	664.5	651.7	633.8	614.6	592.2	568.5
150°	631.3	642.6	646.4	647.3	646.4	642.6	631.3	617.3	600.3	582.4	561.8
152.5°	614.1	623.1	626.8	627.7	626.8	623.1	614.1	602.2	589.0	572.6	554.2
155°	590.9	597.5	600.3	601.2	600.3	597.5	590.9	581.5	571.2	558.0	542.9
157.5°	569.7	575.0	577.7	577.5	577.7	575.0	569.7	562.3	554.2	544.0	531.6
160°	556.1	560.8	562.7	561.8	562.7	560.8	556.1	549.5	542.9	533.5	524.1
162.5°	543.3	547.2	547.6	547.4	547.6	547.2	543.3	538.2	532.3	524.4	515.9
165°	525.0	526.9	526.9	526.9	526.9	526.9	525.0	521.2	516.6	511.0	504.4
167.5°	507.4	509.1	508.3	508.1	508.3	509.1	507.4	505.5	502.1	497.8	493.4
170°	496.8	497.8	497.8	496.8	497.8	497.8	496.8	494.9	493.0	490.2	487.4
172.5°	487.0	488.7	487.2	486.3	487.2	488.7	487.0	486.6	485.5	483.4	480.6
175°	475.1	476.1	474.2	473.3	474.2	476.1	475.1	475.1	475.1	473.3	473.3
177.5°	468.2	468.9	466.7	466.7	466.7	468.9	468.2	468.9	468.9	468.9	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	836.1	839.2	840.9	845.0	850.7	853.6	857.6	860.4	864.5	869.3	873.4
5°	781.9	790.6	796.3	805.2	813.5	821.7	832.1	839.6	849.6	861.1	870.1
7.5°	731.7	742.4	752.0	763.7	777.4	788.0	801.5	815.3	831.0	847.3	862.6
10°	699.6	710.4	722.2	736.9	750.5	764.8	780.9	797.0	816.7	835.0	855.7
12.5°	667.8	679.7	693.0	709.4	725.9	744.1	760.5	778.6	799.8	823.5	845.7
15°	628.4	639.8	654.1	668.1	687.1	707.1	729.0	753.0	776.6	803.1	830.7
17.5°	586.1	598.6	614.4	630.6	650.5	674.0	695.5	721.7	748.3	779.2	811.6
20°	558.6	571.5	590.0	607.9	626.2	649.1	674.6	701.4	729.7	762.2	798.4
22.5°	536.8	545.9	564.3	582.5	603.9	627.4	652.2	680.2	711.1	744.8	782.7
25°	504.4	515.2	528.5	547.4	569.7	594.4	619.4	649.1	682.8	717.2	757.6
27.5°	475.8	484.6	497.7	512.6	534.7	560.3	587.0	618.0	652.5	687.5	730.1
30°	455.4	465.1	477.6	493.4	511.0	538.9	566.1	596.5	631.6	667.8	711.4
32.5°	437.7	447.6	458.5	473.3	492.3	517.1	545.2	575.0	610.7	648.0	690.5
35°	412.8	419.6	429.6	444.3	463.0	483.0	511.6	543.2	577.9	616.5	659.1
37.5°	384.4	393.1	403.1	415.8	432.2	453.8	480.5	512.4	544.6	581.6	620.5
40°	367.7	376.0	387.0	396.3	413.6	433.2	457.6	490.9	523.1	557.8	593.2
42.5°	350.8	358.7	368.2	379.8	395.2	414.3	437.0	468.0	502.5	535.2	565.0
45°	324.4	332.6	341.6	352.3	366.6	385.2	407.8	436.1	466.2	496.2	518.8
47.5°	299.1	306.8	315.3	326.3	339.5	357.5	377.7	402.7	431.9	457.4	473.5
50°	281.1	288.2	297.6	308.3	321.1	338.0	357.3	382.0	406.4	429.6	444.3
52.5°	263.3	271.4	280.6	289.9	302.3	319.1	337.0	358.3	381.4	400.4	412.6
55°	236.7	244.2	252.8	262.4	274.7	289.0	307.9	324.7	343.0	359.1	366.3
57.5°	210.9	217.5	225.6	235.6	246.7	260.0	274.9	291.2	304.1	315.5	323.6
60°	194.1	199.8	207.3	215.9	227.7	239.9	253.4	268.5	278.5	288.2	295.8
62.5°	176.9	182.3	189.5	197.3	207.6	219.0	232.1	244.2	253.9	260.4	269.1
65°	151.1	156.5	162.6	170.8	179.0	188.3	200.1	209.1	215.9	223.1	228.5
67.5°	127.1	131.6	137.3	143.8	150.7	159.7	168.8	176.3	181.0	185.2	191.7
70°	111.3	114.9	119.6	124.6	132.1	141.1	148.3	153.9	157.2	161.5	169.4
72.5°	95.3	99.4	103.9	108.9	114.9	122.4	128.8	134.5	136.6	140.0	145.0
75°	75.2	77.4	81.0	84.5	88.8	95.2	101.3	102.7	104.5	107.4	111.0
77.5°	56.8	58.8	60.2	62.6	66.0	71.2	74.4	76.5	77.0	78.0	81.5
80°	45.1	46.2	47.6	49.4	50.8	55.1	56.9	59.1	59.8	60.9	62.7
82.5°	33.1	34.1	35.1	36.5	38.8	40.5	42.3	44.5	44.6	45.4	45.7
85°	19.3	19.7	18.9	19.7	20.1	20.7	22.5	24.3	24.0	23.7	24.7
87.5°	10.1	9.9	9.2	9.9	9.0	9.0	8.7	8.6	8.8	9.0	9.3
90°	16.0	15.1	13.2	12.3	10.4	9.4	7.5	5.7	3.8	1.9	0.9
92.5°	245.5	303.3	308.2	214.7	128.6	77.2	49.7	33.5	21.9	13.9	11.5
95°	815.8	833.7	680.3	420.6	213.6	112.9	70.6	49.9	39.5	32.0	31.0
97.5°	1032.2	890.3	607.5	335.7	184.1	117.4	86.9	68.3	58.0	52.7	51.6
100°	1084.9	849.6	542.0	304.8	182.6	128.0	99.7	81.8	71.5	67.8	65.9
102.5°	1053.3	778.2	492.3	292.1	189.4	140.7	113.3	96.9	85.8	82.8	81.7
105°	952.3	682.1	444.1	287.0	203.2	161.8	135.5	120.5	111.0	106.3	106.3
107.5°	849.0	616.1	423.8	295.7	223.9	183.9	160.1	144.5	136.8	132.3	130.4
110°	790.3	585.2	417.7	303.9	239.0	200.4	176.0	161.8	153.4	149.6	147.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	746.7	567.2	417.7	314.4	253.3	216.2	192.5	178.4	169.9	166.9	165.0
115°	699.1	547.6	420.6	330.3	275.7	240.9	217.4	203.2	194.7	191.9	190.1
117.5°	670.7	538.0	426.8	348.4	298.7	265.7	243.0	227.0	218.5	215.5	212.6
120°	654.9	533.5	432.8	360.3	315.2	282.3	258.7	242.8	234.3	230.5	227.7
122.5°	641.3	529.7	438.1	373.9	331.0	298.1	274.6	257.0	248.5	245.5	243.6
125°	622.9	525.0	447.0	392.4	351.9	320.8	296.4	278.5	270.0	265.3	263.4
127.5°	606.0	522.7	456.9	409.3	372.0	342.1	317.6	298.7	287.9	281.9	279.1
130°	594.7	521.2	463.0	420.6	384.8	355.6	331.2	311.4	299.3	291.7	288.9
132.5°	585.6	521.2	469.7	430.4	396.9	367.7	343.3	322.7	309.0	299.9	296.4
135°	574.9	521.2	478.9	444.1	413.0	383.9	358.4	338.7	323.7	312.4	308.6
137.5°	565.3	522.4	487.4	454.3	424.5	398.0	371.8	352.5	337.4	326.9	324.0
140°	560.8	523.1	491.2	461.1	432.8	405.6	380.1	362.2	347.2	335.9	333.1
142.5°	557.0	523.9	493.4	464.8	438.1	412.3	388.4	371.3	356.2	345.7	343.7
145°	551.4	523.1	495.9	470.4	447.0	422.4	400.9	383.9	370.7	361.3	359.4
147.5°	545.5	520.7	496.8	473.8	452.6	431.1	412.1	397.5	385.2	377.1	376.0
150°	541.0	518.4	496.8	476.1	456.4	435.6	419.6	406.5	394.3	387.7	385.8
152.5°	535.7	515.5	496.1	477.6	460.1	440.9	426.4	414.0	403.3	397.5	396.3
155°	526.9	510.0	494.0	478.9	463.8	447.9	434.7	425.3	415.8	410.2	410.2
157.5°	518.6	504.4	491.5	479.8	467.0	453.4	443.4	435.1	427.0	422.4	422.6
160°	511.9	500.6	489.3	479.8	468.5	456.4	447.9	440.4	433.8	430.0	430.9
162.5°	505.9	496.1	487.0	479.1	470.0	459.4	452.4	446.4	440.5	436.8	437.7
165°	496.8	489.3	483.6	478.0	470.4	463.0	457.3	453.6	448.8	446.0	447.9
167.5°	488.0	482.7	478.3	475.7	470.4	464.2	460.7	458.1	455.4	453.7	454.7
170°	482.7	478.9	476.1	474.2	470.4	465.7	463.0	461.1	459.2	458.3	459.2
172.5°	477.4	474.4	473.1	472.7	469.7	465.7	464.4	463.3	461.5	460.5	462.2
175°	470.4	469.5	469.5	470.4	468.5	465.7	465.7	465.7	464.8	463.8	465.7
177.5°	467.4	466.7	466.7	468.2	467.4	465.9	465.9	466.7	465.9	465.9	467.4
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	876.5	879.1	882.8	887.1	890.5	894.3	896.3	896.3	898.0	901.7	906.5
5°	879.0	888.3	897.3	908.7	917.7	928.0	935.9	943.5	950.3	958.8	967.8
7.5°	878.3	893.7	909.8	927.9	947.8	963.7	979.9	992.7	1005.2	1021.7	1034.7
10°	875.4	895.5	917.3	940.2	965.3	987.1	1006.8	1024.7	1041.9	1059.8	1075.9
12.5°	870.2	895.8	922.5	950.0	981.7	1006.6	1032.0	1051.1	1071.1	1090.7	1110.6
15°	862.5	892.6	924.8	963.2	1001.8	1029.7	1054.8	1079.5	1098.2	1120.3	1139.3
17.5°	846.6	885.3	925.9	967.7	1004.8	1037.4	1063.6	1087.1	1106.9	1131.3	1157.2
20°	837.1	879.0	921.2	966.0	1001.5	1034.7	1060.2	1084.5	1109.2	1141.1	1172.6
22.5°	824.0	868.6	913.5	956.0	993.4	1025.6	1051.9	1081.7	1114.1	1150.3	1188.4
25°	803.1	849.3	893.7	934.2	970.6	1003.6	1039.4	1079.5	1118.9	1166.5	1221.3
27.5°	776.7	821.2	860.8	903.5	939.9	981.8	1026.4	1069.9	1126.7	1192.2	1260.7
30°	756.9	799.2	836.8	877.2	918.4	964.6	1014.7	1065.9	1133.6	1210.5	1291.8
32.5°	734.0	772.2	809.5	848.6	896.1	946.8	1000.1	1062.7	1143.6	1231.1	1315.3
35°	694.3	728.6	764.8	808.1	858.6	913.7	981.8	1058.0	1155.7	1249.9	1325.5
37.5°	652.6	679.7	716.0	761.7	816.7	880.5	957.7	1050.4	1150.8	1235.3	1267.4
40°	620.5	645.9	684.2	732.2	786.6	856.5	943.1	1038.3	1139.3	1198.0	1195.5
42.5°	588.7	614.4	651.3	699.6	756.3	834.4	923.6	1022.6	1107.8	1130.1	1083.5
45°	539.9	563.9	600.1	648.8	709.6	791.6	885.4	980.3	1034.7	998.6	906.3
47.5°	490.2	513.5	547.1	594.7	661.2	747.1	835.8	913.6	921.2	843.6	732.7
50°	457.6	479.4	511.3	562.1	626.6	710.4	796.0	857.1	838.2	743.3	629.1
52.5°	425.7	446.8	476.6	524.6	590.5	672.6	748.9	797.0	753.1	652.2	549.5
55°	378.8	398.9	429.0	473.0	532.7	607.9	675.0	692.5	628.0	526.3	443.3
57.5°	334.2	348.8	378.6	417.5	475.2	541.5	589.5	586.4	515.2	423.7	364.1
60°	304.7	317.9	346.2	382.0	436.8	496.2	529.9	515.6	443.7	368.1	310.8
62.5°	277.2	289.5	313.3	346.2	393.3	445.0	469.5	449.7	381.7	315.4	269.8
65°	235.6	244.6	263.5	294.0	330.8	366.6	388.5	359.5	299.4	249.2	214.8
67.5°	196.7	204.4	221.3	243.2	268.6	293.3	302.2	274.9	228.2	194.4	170.2
70°	171.5	178.7	190.1	210.6	227.3	244.9	249.2	224.9	185.9	160.0	145.0
72.5°	147.4	154.0	164.1	178.4	190.1	200.2	202.3	179.6	149.8	132.0	120.4
75°	112.4	118.2	124.6	130.0	137.5	139.3	138.6	121.0	104.9	93.1	86.6
77.5°	82.7	85.0	89.0	91.0	91.4	91.3	87.7	76.5	68.2	63.3	60.7
80°	63.7	65.5	66.6	67.3	67.7	64.1	60.1	53.3	50.5	47.6	44.4
82.5°	46.3	47.5	48.5	48.7	46.8	43.7	40.1	36.8	34.7	33.3	32.0
85°	25.1	25.4	25.1	23.3	20.7	19.7	18.9	18.3	17.9	17.5	17.5
87.5°	9.2	8.8	7.7	8.4	8.8	8.7	9.0	9.0	9.0	9.2	9.4
90°	1.9	3.8	5.7	7.5	9.4	10.4	12.3	13.2	15.1	16.0	17.0
92.5°	13.9	21.9	33.5	49.7	77.2	128.6	214.7	308.2	303.3	245.5	166.7
95°	32.0	39.5	49.9	70.6	112.9	213.6	420.6	680.3	833.7	815.8	676.6
97.5°	52.7	58.0	68.3	86.9	117.4	184.1	335.7	607.5	890.3	1032.2	1007.6
100°	67.8	71.5	81.8	99.7	128.0	182.6	304.8	542.0	849.6	1084.9	1157.3
102.5°	82.8	85.8	96.9	113.3	140.7	189.4	292.1	492.3	778.2	1053.3	1207.8
105°	106.3	111.0	120.5	135.5	161.8	203.2	287.0	444.1	682.1	952.3	1178.0
107.5°	132.3	136.8	144.5	160.1	183.9	223.9	295.7	423.8	616.1	849.0	1071.9
110°	149.6	153.4	161.8	176.0	200.4	239.0	303.9	417.7	585.2	790.3	993.6



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	166.9	169.9	178.4	192.5	216.2	253.3	314.4	417.7	567.2	746.7	931.9
115°	191.9	194.7	203.2	217.4	240.9	275.7	330.3	420.6	547.6	699.1	854.3
117.5°	215.5	218.5	227.0	243.0	265.7	298.7	348.4	426.8	538.0	670.7	804.3
120°	230.5	234.3	242.8	258.7	282.3	315.2	360.3	432.8	533.5	654.9	777.2
122.5°	245.5	248.5	257.0	274.6	298.1	331.0	373.9	438.1	529.7	641.3	756.9
125°	265.3	270.0	278.5	296.4	320.8	351.9	392.4	447.0	525.0	622.9	727.4
127.5°	281.9	287.9	298.7	317.6	342.1	372.0	409.3	456.9	522.7	606.0	697.2
130°	291.7	299.3	311.4	331.2	355.6	384.8	420.6	463.0	521.2	594.7	678.4
132.5°	299.9	309.0	322.7	343.3	367.7	396.9	430.4	469.7	521.2	585.6	659.6
135°	312.4	323.7	338.7	358.4	383.9	413.0	444.1	478.9	521.2	574.9	635.1
137.5°	326.9	337.4	352.5	371.8	398.0	424.5	454.3	487.4	522.4	565.3	614.4
140°	335.9	347.2	362.2	380.1	405.6	432.8	461.1	491.2	523.1	560.8	603.1
142.5°	345.7	356.2	371.3	388.4	412.3	438.1	464.8	493.4	523.9	557.0	593.3
145°	361.3	370.7	383.9	400.9	422.4	447.0	470.4	495.9	523.1	551.4	580.5
147.5°	377.1	385.2	397.5	412.1	431.1	452.6	473.8	496.8	520.7	545.5	568.5
150°	387.7	394.3	406.5	419.6	435.6	456.4	476.1	496.8	518.4	541.0	561.8
152.5°	397.5	403.3	414.0	426.4	440.9	460.1	477.6	496.1	515.5	535.7	554.2
155°	410.2	415.8	425.3	434.7	447.9	463.8	478.9	494.0	510.0	526.9	542.9
157.5°	422.4	427.0	435.1	443.4	453.4	467.0	479.8	491.5	504.4	518.6	531.6
160°	430.0	433.8	440.4	447.9	456.4	468.5	479.8	489.3	500.6	511.9	524.1
162.5°	436.8	440.5	446.4	452.4	459.4	470.0	479.1	487.0	496.1	505.9	515.9
165°	446.0	448.8	453.6	457.3	463.0	470.4	478.0	483.6	489.3	496.8	504.4
167.5°	453.7	455.4	458.1	460.7	464.2	470.4	475.7	478.3	482.7	488.0	493.4
170°	458.3	459.2	461.1	463.0	465.7	470.4	474.2	476.1	478.9	482.7	487.4
172.5°	460.5	461.5	463.3	464.4	465.7	469.7	472.7	473.1	474.4	477.4	480.6
175°	463.8	464.8	465.7	465.7	465.7	468.5	470.4	469.5	469.5	470.4	473.3
177.5°	465.9	465.9	466.7	465.9	465.9	467.4	468.2	466.7	466.7	467.4	468.2
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7	466.7



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	872.2	872.2	872.2	872.2	872.2	872.2	872.2
2.5°	910.3	910.3	915.2	914.8	918.0	916.9	917.5
5°	978.5	984.6	990.0	993.5	998.9	1000.4	999.7
7.5°	1049.3	1062.8	1069.4	1078.5	1080.1	1084.8	1084.3
10°	1093.1	1106.4	1116.3	1124.3	1128.2	1133.2	1133.6
12.5°	1127.5	1138.7	1147.6	1154.9	1159.7	1161.3	1162.2
15°	1154.3	1166.9	1177.2	1187.6	1193.7	1198.3	1200.9
17.5°	1181.4	1200.7	1219.1	1233.2	1241.6	1248.8	1248.7
20°	1202.3	1224.6	1247.5	1263.6	1280.0	1287.1	1288.3
22.5°	1224.6	1258.6	1288.1	1313.1	1334.7	1342.2	1344.9
25°	1271.0	1315.4	1360.9	1396.0	1421.1	1435.8	1437.9
27.5°	1327.1	1387.2	1435.0	1467.4	1488.3	1499.1	1501.5
30°	1366.7	1422.1	1465.1	1489.5	1499.1	1500.5	1495.2
32.5°	1384.4	1425.9	1443.0	1441.6	1422.7	1410.0	1405.2
35°	1362.7	1354.2	1312.2	1262.1	1223.8	1199.5	1193.0
37.5°	1240.1	1166.0	1088.9	1013.2	972.9	952.4	917.2
40°	1119.3	1013.6	933.4	869.7	824.3	787.7	779.1
42.5°	982.9	873.8	793.6	739.0	702.8	677.7	666.8
45°	789.9	696.1	629.8	587.9	560.0	541.7	533.5
47.5°	631.7	559.1	510.9	479.8	458.5	442.7	438.3
50°	545.0	486.9	446.1	420.0	403.9	391.7	386.7
52.5°	473.3	426.5	395.1	373.6	358.4	350.7	346.6
55°	390.6	350.2	327.6	310.4	301.8	295.8	292.8
57.5°	319.4	290.2	273.7	261.8	253.9	250.1	248.6
60°	279.7	256.7	241.7	232.3	227.0	222.0	220.6
62.5°	244.4	226.4	214.7	206.6	201.2	199.1	198.2
65°	196.9	185.1	176.5	171.5	167.2	166.5	166.2
67.5°	156.6	149.6	145.1	139.9	138.4	135.8	135.3
70°	133.9	129.2	123.9	122.1	120.3	117.8	118.2
72.5°	113.6	109.0	105.3	102.9	102.3	101.2	102.1
75°	83.0	81.6	80.2	78.4	77.7	77.7	77.4
77.5°	59.3	58.1	56.5	55.4	55.2	53.7	54.3
80°	43.0	41.2	40.4	40.8	39.8	39.4	39.4
82.5°	31.8	31.1	30.4	30.5	30.3	30.0	30.3
85°	17.5	17.2	17.2	16.9	16.9	16.5	16.5
87.5°	9.9	10.4	10.2	9.9	9.9	10.4	10.7
90°	17.9	18.9	20.7	20.7	20.7	21.7	21.7
92.5°	121.0	91.0	77.2	65.1	62.9	61.5	60.0
95°	533.5	417.7	338.7	271.9	243.7	236.2	221.1
97.5°	907.2	794.5	684.6	626.5	573.7	546.5	534.4
100°	1111.3	1014.3	916.4	851.5	783.8	748.9	734.0
102.5°	1236.1	1189.7	1123.4	1054.0	1005.9	968.0	956.7
105°	1306.9	1348.3	1337.9	1307.9	1276.9	1258.0	1246.7
107.5°	1243.9	1350.2	1399.3	1414.6	1414.4	1408.2	1400.6
110°	1172.3	1305.0	1385.1	1427.4	1445.2	1451.8	1451.8



TEST NUMBER: P333540-830

CATALOG NUMBER: S125RDIP-S610D1035U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1101.6	1235.8	1330.1	1391.9	1422.7	1439.1	1445.8
115°	1000.2	1129.1	1231.6	1305.0	1350.2	1376.6	1388.8
117.5°	930.0	1041.0	1135.1	1208.5	1255.2	1281.3	1288.8
120°	890.1	993.6	1076.4	1146.0	1191.2	1216.6	1224.2
122.5°	861.5	953.7	1031.2	1093.3	1134.7	1160.2	1167.0
125°	823.3	905.1	972.9	1025.6	1064.1	1084.9	1094.3
127.5°	786.8	863.2	926.6	974.4	1008.4	1028.0	1032.2
130°	761.2	834.6	895.8	942.8	973.8	992.7	998.3
132.5°	737.1	803.7	862.6	909.6	940.8	958.0	964.4
135°	700.0	760.3	813.9	855.3	886.4	903.2	908.9
137.5°	666.9	717.0	762.5	799.6	827.8	843.5	849.6
140°	647.3	690.6	730.2	765.0	789.5	803.5	808.2
142.5°	630.7	668.1	702.3	731.9	752.5	765.9	769.9
145°	609.7	638.9	664.3	686.8	702.9	713.2	717.0
147.5°	592.2	614.6	633.8	651.7	664.5	670.5	672.2
150°	582.4	600.3	617.3	631.3	642.6	646.4	647.3
152.5°	572.6	589.0	602.2	614.1	623.1	626.8	627.7
155°	558.0	571.2	581.5	590.9	597.5	600.3	601.2
157.5°	544.0	554.2	562.3	569.7	575.0	577.7	577.5
160°	533.5	542.9	549.5	556.1	560.8	562.7	561.8
162.5°	524.4	532.3	538.2	543.3	547.2	547.6	547.4
165°	511.0	516.6	521.2	525.0	526.9	526.9	526.9
167.5°	497.8	502.1	505.5	507.4	509.1	508.3	508.1
170°	490.2	493.0	494.9	496.8	497.8	497.8	496.8
172.5°	483.4	485.5	486.6	487.0	488.7	487.2	486.3
175°	473.3	475.1	475.1	475.1	476.1	474.2	473.3
177.5°	468.9	468.9	468.9	468.2	468.9	466.7	466.7
180°	466.7	466.7	466.7	466.7	466.7	466.7	466.7

(END OF REPORT)