

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333567-830

Luminaire Tested: **S125RDIP-S850D810U830-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333567-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S850D810U830-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5805.1 lumens  
Efficiency: N/A  
Efficacy: 126.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333567-830

CATALOG NUMBER: S125RDIP-S850D810U830-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333567-830

CATALOG NUMBER: S125RDIP-S850D810U830-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	28	24
6	64	52	44	38	59	48	41	36	42	36	32	36	32	28	30	27	24	22
7	59	47	39	33	55	44	37	32	38	32	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8371	8371	8371
5°	8390	8294	8345
10°	8326	8217	8217
15°	8227	8050	7985
20°	8100	7818	7724
25°	7953	7590	7422
30°	7767	7322	7088
35°	7579	7046	6714
40°	7403	6759	6347
45°	7188	6437	5945
50°	6973	6089	5528
55°	6723	5754	5082
60°	6473	5349	4602
65°	6178	4876	4053
70°	5840	4288	3493
75°	5375	3616	2907
80°	4731	2838	2440
85°	3987	2319	2179



TEST NUMBER: P333567-830

CATALOG NUMBER: S125RDIP-S850D810U830-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.9	2.1
10°-20°	340.6	5.9
20°-30°	493.9	8.5
30°-40°	562.9	9.7
40°-50°	548.6	9.5
50°-60°	461.8	8.0
60°-70°	323.7	5.6
70°-80°	166.4	2.9
80°-90°	44.1	0.8
90°-100°	264.9	4.6
100°-110°	569.6	9.8
110°-120°	534.5	9.2
120°-130°	433.2	7.5
130°-140°	347.7	6.0
140°-150°	262.4	4.5
150°-160°	184.7	3.2
160°-170°	108.8	1.9
170°-180°	35.4	0.6
0°-30°	956.3	16.5
0°-40°	1519.2	26.2
0°-60°	2529.7	43.6
0°-90°	3063.9	52.8
90°-120°	1369.1	23.6
90°-150°	2412.3	41.6
90°-180°	2741.0	47.2
0°-180°	5805.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1296	1296	1296	1296	1296	
5°	1294	1290	1279	1289	1287	123
15°	1230	1224	1204	1203	1194	347
25°	1116	1100	1065	1052	1042	513
35°	961	937	894	866	852	602
45°	787	757	705	667	651	607
55°	597	564	511	468	451	534
65°	404	370	319	281	265	400
75°	215	185	145	124	116	228
85°	54	37	31	30	29	60
90°	1	7	12	15	17	4
95°	24	72	653	296	173	26
105°	83	116	534	1052	976	88
115°	149	179	429	925	1088	146
125°	206	242	411	736	857	183
135°	242	291	408	616	712	188
145°	282	322	410	510	562	176
155°	321	346	399	451	471	148
165°	351	360	383	406	413	99
175°	365	365	368	372	371	35
180°	366	366	366	366	366	



TEST NUMBER: P333567-830

CATALOG NUMBER: S125RDIP-S850D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1298.4	1297.9	1297.3	1296.8	1296.3	1295.1	1293.5	1291.7	1290.0	1288.2	1290.0
5°	1294.1	1293.3	1292.3	1291.5	1290.6	1289.0	1286.6	1284.2	1281.8	1279.4	1281.6
7.5°	1281.4	1280.5	1279.7	1278.8	1278.1	1276.2	1273.4	1270.5	1267.6	1264.7	1266.2
10°	1269.6	1268.9	1268.3	1267.6	1267.0	1265.2	1262.2	1259.0	1256.0	1253.0	1253.6
12.5°	1256.3	1255.5	1254.6	1253.9	1253.0	1250.6	1246.4	1242.4	1238.3	1234.2	1234.6
15°	1230.5	1229.2	1227.9	1226.5	1225.2	1222.3	1217.8	1213.1	1208.6	1204.0	1203.8
17.5°	1201.3	1199.3	1197.3	1195.3	1193.3	1189.4	1183.6	1177.9	1172.1	1166.4	1165.4
20°	1178.6	1176.4	1174.2	1172.1	1169.9	1165.3	1158.4	1151.4	1144.4	1137.5	1136.4
22.5°	1153.5	1151.3	1149.1	1147.0	1144.8	1140.1	1132.7	1125.5	1118.1	1110.9	1108.7
25°	1116.0	1112.7	1109.4	1106.2	1102.9	1097.2	1089.2	1081.1	1073.1	1065.1	1062.2
27.5°	1072.9	1068.9	1065.0	1061.0	1057.1	1050.7	1042.2	1033.5	1024.9	1016.2	1012.3
30°	1041.5	1037.4	1033.3	1029.2	1025.0	1018.3	1009.3	1000.1	991.0	981.8	976.9
32.5°	1011.0	1006.2	1001.4	996.6	991.6	984.6	975.3	966.0	956.7	947.3	941.9
35°	961.3	956.0	950.8	945.6	940.4	932.8	923.1	913.3	903.5	893.7	887.4
37.5°	912.5	906.2	899.8	893.4	887.1	878.9	868.8	858.7	848.6	838.5	830.9
40°	878.1	871.6	865.0	858.5	852.0	843.5	833.0	822.6	812.2	801.7	793.4
42.5°	842.1	835.4	828.7	821.9	815.2	806.5	795.7	784.9	774.1	763.4	755.4
45°	787.0	780.7	774.4	768.1	761.8	752.6	740.6	728.8	716.8	704.8	696.1
47.5°	730.1	723.4	716.7	710.1	703.4	694.1	682.0	670.0	657.9	645.8	636.9
50°	694.0	686.8	679.7	672.5	665.3	655.5	643.1	630.7	618.3	606.0	596.8
52.5°	654.9	647.5	640.2	632.8	625.5	616.0	604.3	592.6	580.8	569.1	559.3
55°	597.1	590.1	583.2	576.3	569.3	559.7	547.5	535.4	523.2	511.0	501.1
57.5°	538.8	531.3	523.9	516.4	509.1	499.5	487.7	475.9	464.2	452.4	442.9
60°	501.1	493.6	486.0	478.3	470.7	461.1	449.3	437.5	425.8	414.1	404.5
62.5°	461.3	454.0	446.8	439.4	432.2	422.6	410.7	398.8	386.8	374.9	366.1
65°	404.3	396.9	389.5	382.1	374.7	365.2	353.7	342.1	330.6	319.1	310.4
67.5°	347.7	340.3	332.9	325.6	318.1	308.9	297.8	286.8	275.8	264.7	256.7
70°	309.3	301.9	294.5	287.1	279.7	270.6	259.8	248.8	238.0	227.1	220.4
72.5°	271.7	264.5	257.3	250.1	242.9	234.1	223.9	213.8	203.6	193.4	187.2
75°	215.4	208.9	202.3	195.8	189.3	181.4	172.3	163.2	154.0	144.9	140.1
77.5°	159.4	154.1	148.9	143.7	138.5	132.2	124.9	117.6	110.3	103.0	99.6
80°	127.2	122.1	116.8	111.6	106.4	100.8	94.6	88.5	82.5	76.3	74.4
82.5°	96.0	91.2	86.5	81.8	77.1	72.7	68.5	64.4	60.1	56.0	55.0
85°	53.8	50.0	46.0	42.1	38.2	35.6	34.6	33.5	32.4	31.3	31.1
87.5°	18.2	17.1	16.2	15.3	14.3	13.9	13.9	14.0	13.9	14.1	14.2
90°	0.8	1.5	2.9	4.4	5.9	7.4	8.1	9.6	10.3	11.8	12.5
92.5°	9.0	10.9	17.1	26.2	38.9	60.4	100.7	168.1	241.4	237.6	192.4
95°	24.3	25.1	30.9	39.0	55.2	88.4	167.3	329.4	532.8	653.0	638.9
97.5°	40.3	41.3	45.4	53.5	68.1	92.0	144.1	263.0	475.8	697.3	808.4
100°	51.6	53.1	56.0	64.1	78.1	100.2	143.0	238.7	424.5	665.5	849.7
102.5°	64.0	64.8	67.2	75.9	88.7	110.3	148.3	228.8	385.6	609.4	825.0
105°	83.3	83.3	87.0	94.3	106.1	126.8	159.2	224.8	347.9	534.3	745.8
107.5°	102.2	103.6	107.2	113.2	125.5	144.0	175.4	231.6	332.0	482.6	665.1
110°	115.7	117.2	120.1	126.8	137.8	156.9	187.2	238.1	327.3	458.4	619.1



TEST NUMBER: P333567-830

CATALOG NUMBER: S125RDIP-S850D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	129.2	130.7	133.1	139.7	150.8	169.4	198.4	246.3	327.3	444.2	584.8
115°	148.8	150.3	152.6	159.2	170.2	188.7	215.9	258.6	329.4	429.0	547.5
117.5°	166.5	168.8	171.2	177.8	190.3	208.1	233.9	272.9	334.3	421.4	525.3
120°	178.3	180.6	183.5	190.1	202.6	221.1	246.9	282.3	339.0	417.8	512.9
122.5°	190.8	192.4	194.7	201.3	215.1	233.5	259.3	292.8	343.1	414.9	502.3
125°	206.3	207.8	211.5	218.1	232.1	251.3	275.6	307.3	350.1	411.2	487.9
127.5°	218.6	220.8	225.6	233.9	248.8	268.0	291.4	320.6	357.9	409.4	474.6
130°	226.2	228.5	234.3	243.9	259.4	278.6	301.4	329.4	362.6	408.3	465.8
132.5°	232.1	235.0	242.0	252.8	268.8	288.0	310.9	337.1	367.9	408.3	458.7
135°	241.8	244.7	253.5	265.3	280.8	300.7	323.6	347.9	375.1	408.3	450.3
137.5°	253.8	256.0	264.3	276.1	291.2	311.7	332.5	355.8	381.7	409.2	442.8
140°	260.9	263.1	271.9	283.7	297.7	317.6	339.0	361.1	384.7	409.7	439.2
142.5°	269.1	270.8	279.0	290.8	304.3	322.9	343.1	364.1	386.4	410.4	436.3
145°	281.5	283.0	290.4	300.7	314.0	330.9	350.1	368.4	388.4	409.7	431.9
147.5°	294.5	295.4	301.7	311.3	322.8	337.7	354.5	371.2	389.1	407.8	427.3
150°	302.2	303.6	308.8	318.4	328.7	341.2	357.4	372.9	389.1	406.0	423.8
152.5°	310.4	311.3	315.8	324.2	334.0	345.3	360.3	374.1	388.5	403.7	419.6
155°	321.3	321.3	325.7	333.1	340.4	350.8	363.4	375.1	386.9	399.4	412.7
157.5°	331.0	330.9	334.4	340.7	347.2	355.1	365.8	375.9	385.0	395.0	406.2
160°	337.5	336.8	339.8	344.9	350.8	357.4	367.0	375.9	383.2	392.1	401.0
162.5°	342.8	342.1	345.1	349.6	354.3	359.8	368.2	375.2	381.4	388.5	396.2
165°	350.8	349.3	351.6	355.2	358.2	362.6	368.4	374.4	378.8	383.2	389.1
167.5°	356.1	355.3	356.7	358.7	360.8	363.6	368.4	372.6	374.7	378.1	382.2
170°	359.7	358.9	359.7	361.1	362.6	364.8	368.4	371.5	372.9	375.1	378.1
172.5°	362.0	360.7	361.4	362.9	363.7	364.8	367.9	370.2	370.5	371.6	373.9
175°	364.8	363.4	364.1	364.8	364.8	364.8	367.0	368.4	367.8	367.8	368.4
177.5°	366.1	365.0	365.0	365.5	365.0	365.0	366.1	366.7	365.5	365.5	366.1
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5



TEST NUMBER: P333567-830

CATALOG NUMBER: S125RDIP-S850D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1291.7	1293.5	1295.1	1296.0	1295.8	1295.6	1295.4	1295.2
5°	1283.7	1285.9	1288.1	1289.0	1288.5	1288.1	1287.7	1287.2
7.5°	1267.8	1269.3	1270.8	1271.3	1270.8	1270.4	1269.9	1269.4
10°	1254.2	1254.9	1255.6	1255.6	1254.9	1254.2	1253.6	1253.0
12.5°	1235.1	1235.6	1236.1	1235.9	1234.8	1233.8	1232.8	1231.8
15°	1203.6	1203.3	1203.2	1202.1	1200.1	1198.2	1196.2	1194.2
17.5°	1164.2	1163.2	1162.1	1160.7	1159.1	1157.5	1155.9	1154.3
20°	1135.3	1134.2	1133.1	1131.6	1129.6	1127.7	1125.7	1123.8
22.5°	1106.5	1104.5	1102.3	1100.4	1098.8	1097.2	1095.6	1094.0
25°	1059.4	1056.6	1053.8	1051.1	1048.7	1046.3	1044.0	1041.5
27.5°	1008.3	1004.4	1000.4	997.3	995.0	992.7	990.4	988.1
30°	971.9	966.9	961.8	958.4	956.4	954.4	952.4	950.5
32.5°	936.3	930.8	925.3	921.2	918.8	916.3	913.8	911.3
35°	881.1	874.8	868.5	863.8	860.7	857.7	854.7	851.6
37.5°	823.4	815.8	808.2	803.0	800.0	797.0	794.1	791.2
40°	785.1	776.9	768.6	763.2	760.6	758.0	755.4	752.8
42.5°	747.5	739.6	731.7	725.8	722.0	718.1	714.3	710.5
45°	687.4	678.7	670.0	664.0	660.7	657.5	654.2	650.9
47.5°	627.9	619.0	610.0	603.7	600.1	596.5	592.9	589.3
50°	587.7	578.5	569.4	563.2	560.0	556.7	553.4	550.2
52.5°	549.5	539.6	529.8	523.2	520.0	516.7	513.5	510.2
55°	491.4	481.6	471.8	465.1	461.8	458.3	454.8	451.3
57.5°	433.3	423.8	414.2	407.8	404.7	401.6	398.6	395.5
60°	394.9	385.3	375.8	369.4	366.1	362.9	359.6	356.3
62.5°	357.1	348.3	339.4	333.4	330.1	326.8	323.6	320.3
65°	301.7	293.0	284.3	278.3	275.0	271.8	268.5	265.2
67.5°	248.7	240.8	232.8	227.5	225.0	222.3	219.7	217.2
70°	213.6	206.9	200.1	195.5	192.8	190.2	187.7	185.0
72.5°	181.0	174.7	168.5	164.6	162.8	161.1	159.4	157.6
75°	135.3	130.5	125.7	122.6	121.0	119.5	118.0	116.5
77.5°	96.2	92.9	89.5	87.4	86.2	85.1	84.0	82.8
80°	72.5	70.5	68.5	67.3	66.9	66.4	66.0	65.6
82.5°	54.2	53.3	52.3	51.7	51.5	51.3	51.0	50.7
85°	30.9	30.6	30.4	30.3	30.0	29.8	29.6	29.4
87.5°	14.4	14.5	14.7	14.9	14.7	14.5	14.5	14.3
90°	13.3	14.0	14.7	16.2	16.2	16.2	17.0	17.0
92.5°	130.6	94.8	71.4	60.4	51.0	49.2	48.2	47.0
95°	529.9	417.8	327.3	265.3	213.0	190.9	185.0	173.1
97.5°	789.2	710.6	622.3	536.2	490.7	449.4	428.0	418.6
100°	906.4	870.3	794.5	717.8	666.9	613.9	586.6	574.9
102.5°	945.9	968.3	931.8	880.0	825.6	787.8	758.2	749.3
105°	922.7	1023.7	1056.1	1048.0	1024.4	1000.0	985.3	976.5
107.5°	839.5	974.3	1057.5	1096.0	1108.0	1107.8	1103.0	1097.0
110°	778.3	918.2	1022.2	1084.8	1117.9	1132.0	1137.2	1137.2





TEST NUMBER: P333567-830

CATALOG NUMBER: S125RDIP-S850D810U830-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	729.9	862.8	967.9	1041.8	1090.2	1114.3	1127.1	1132.5
115°	669.2	783.4	884.4	964.7	1022.2	1057.5	1078.2	1087.8
117.5°	630.0	728.4	815.4	889.1	946.6	983.1	1003.6	1009.5
120°	608.7	697.2	778.3	843.1	897.6	933.0	952.9	958.8
122.5°	592.9	674.8	747.0	807.8	856.4	888.8	908.7	914.0
125°	569.7	644.9	709.0	762.0	803.3	833.5	849.7	857.1
127.5°	546.1	616.2	676.1	725.8	763.2	789.9	805.2	808.4
130°	531.3	596.3	653.7	701.6	738.5	762.8	777.5	781.9
132.5°	516.6	577.3	629.5	675.6	712.5	736.8	750.4	755.4
135°	497.5	548.3	595.5	637.4	669.9	694.2	707.5	711.9
137.5°	481.3	522.4	561.6	597.2	626.3	648.4	660.6	665.5
140°	472.4	507.0	540.9	571.8	599.2	618.3	629.3	633.0
142.5°	464.8	494.1	523.2	550.1	573.3	589.5	599.9	602.9
145°	454.7	477.6	500.4	520.3	538.0	550.5	558.6	561.6
147.5°	445.3	463.8	481.4	496.4	510.4	520.5	525.2	526.5
150°	440.0	456.2	470.1	483.4	494.6	503.3	506.3	507.0
152.5°	434.0	448.6	461.4	471.6	481.0	488.0	491.0	491.7
155°	425.3	437.1	447.3	455.4	462.8	468.0	470.1	470.9
157.5°	416.4	426.1	434.0	440.5	446.2	450.4	452.5	452.3
160°	410.5	417.8	425.3	430.4	435.5	439.2	440.7	440.0
162.5°	404.0	410.8	417.0	421.5	425.6	428.6	429.0	428.8
165°	395.0	400.2	404.6	408.3	411.2	412.7	412.7	412.7
167.5°	386.4	389.8	393.2	395.9	397.4	398.7	398.1	397.9
170°	381.7	384.0	386.2	387.7	389.1	389.8	389.8	389.1
172.5°	376.5	378.6	380.3	381.2	381.4	382.8	381.6	380.9
175°	370.7	370.7	372.2	372.2	372.2	372.9	371.5	370.7
177.5°	366.7	367.3	367.3	367.3	366.7	367.3	365.5	365.5
180°	365.5	365.5	365.5	365.5	365.5	365.5	365.5	365.5

(END OF REPORT)