

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333283-930

Luminaire Tested: **S125DIP-S1090D1035U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333283-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S1090D1035U930-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6994.6 lumens  
Efficiency: N/A  
Efficacy: 115.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333283-930  
CATALOG NUMBER: S125DIP-S1090D1035U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333283-930

CATALOG NUMBER: S125DIP-S1090D1035U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52				
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	43				
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36				
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31				
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26				
5	68	57	49	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	25	47	36	29	24	31	25	22	27	22	19	22	19	17	14				
10	47	35	28	23	44	33	26	22	29	23	19	25	20	17	21	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333283-930

CATALOG NUMBER: S125DIP-S1090D1035U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.2	1.9
10°-20°	370.5	5.3
20°-30°	547.1	7.8
30°-40°	638.4	9.1
40°-50°	641.2	9.2
50°-60°	562.8	8.0
60°-70°	419.4	6.0
70°-80°	239.8	3.4
80°-90°	72.0	1.0
90°-100°	39.9	0.6
100°-110°	245.9	3.5
110°-120°	446.1	6.4
120°-130°	572.5	8.2
130°-140°	615.7	8.8
140°-150°	578.0	8.3
150°-160°	467.5	6.7
160°-170°	302.4	4.3
170°-180°	104.3	1.5
0°-30°	1048.8	15.0
0°-40°	1687.2	24.1
0°-60°	2891.2	41.3
0°-90°	3622.4	51.8
90°-120°	731.9	10.5
90°-150°	2498.1	35.7
90°-180°	3372.0	48.2
0°-180°	6994.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	1	7	13	17	20	5
95°	46	42	13	17	17	59
105°	239	242	243	243	242	254
115°	449	453	454	451	446	445
125°	639	644	645	642	639	571
135°	797	802	800	798	794	614
145°	924	926	926	926	922	578
155°	1018	1013	1014	1016	1010	469
165°	1074	1069	1070	1074	1068	303
175°	1098	1094	1094	1100	1093	105
180°	1098	1098	1098	1098	1098	



TEST NUMBER: P333283-930

CATALOG NUMBER: S125DIP-S1090D1035U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	24.0	24.2	24.5	24.8	25.1	25.3	25.4	25.4	25.4	25.5	25.7
90°	0.8	2.3	3.7	5.1	6.6	8.0	9.2	10.5	11.7	13.0	13.9
92.5°	12.6	11.5	10.5	9.5	8.5	8.6	9.6	10.8	11.9	13.0	13.9
95°	46.4	45.8	45.3	44.8	44.3	40.5	33.7	26.7	19.9	13.0	13.9
97.5°	96.9	97.8	98.8	99.8	100.8	94.5	80.9	67.3	53.6	40.0	35.0
100°	135.9	136.5	137.1	137.5	138.1	138.8	139.5	140.2	140.9	141.6	114.7
102.5°	175.7	176.3	177.1	177.7	178.4	179.0	179.4	179.9	180.3	180.8	175.6
105°	239.3	240.0	240.8	241.5	242.2	242.6	242.6	242.6	242.6	242.6	242.6
107.5°	305.4	305.4	305.4	305.4	305.4	305.6	306.0	306.3	306.7	307.0	307.1
110°	348.4	348.4	348.4	348.4	348.4	348.6	348.9	349.4	349.7	350.0	349.5



TEST NUMBER: P333283-930

CATALOG NUMBER: S125DIP-S1090D1035U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	388.8	389.2	389.6	390.1	390.5	390.9	391.1	391.3	391.5	391.8	391.0
115°	449.4	450.3	451.2	452.1	453.0	453.6	453.7	453.9	454.0	454.2	453.6
117.5°	512.0	512.0	511.9	511.9	511.9	512.3	512.9	513.6	514.3	514.9	514.0
120°	551.1	550.9	550.7	550.6	550.4	550.6	551.1	551.6	552.2	552.8	552.4
122.5°	585.6	586.3	587.0	587.7	588.4	588.8	589.1	589.4	589.6	589.9	589.5
125°	639.0	640.3	641.6	642.9	644.1	644.7	644.7	644.7	644.7	644.7	644.0
127.5°	690.0	690.9	691.8	692.7	693.6	694.0	693.9	693.8	693.7	693.6	693.2
130°	721.2	722.2	723.1	724.0	724.9	725.4	725.6	725.8	725.9	726.1	725.6
132.5°	752.5	753.6	754.6	755.6	756.7	757.0	756.6	756.3	755.9	755.5	755.3
135°	797.0	798.0	799.2	800.2	801.3	801.7	801.3	801.0	800.5	800.2	799.8
137.5°	837.8	838.8	839.7	840.7	841.6	841.9	841.6	841.2	840.9	840.6	840.7
140°	864.5	864.9	865.3	865.6	865.9	866.1	865.8	865.7	865.5	865.4	865.7
142.5°	888.6	888.8	889.1	889.2	889.5	889.7	890.0	890.2	890.5	890.7	890.8
145°	924.0	924.3	924.6	925.0	925.4	925.6	925.6	925.6	925.6	925.6	925.8
147.5°	954.9	954.8	954.7	954.6	954.6	954.6	954.9	955.1	955.3	955.5	955.8
150°	974.4	974.0	973.7	973.3	973.0	973.0	973.3	973.7	974.0	974.4	974.8
152.5°	993.3	992.5	991.7	990.9	990.1	989.9	990.3	990.6	991.0	991.3	991.7
155°	1017.6	1016.5	1015.4	1014.3	1013.3	1012.8	1013.3	1013.6	1013.9	1014.3	1014.9
157.5°	1036.2	1035.6	1035.0	1034.4	1033.7	1033.4	1033.4	1033.5	1033.5	1033.6	1034.1
160°	1049.3	1048.2	1047.2	1046.0	1045.0	1044.5	1044.7	1044.9	1045.1	1045.2	1045.9
162.5°	1059.7	1058.7	1057.5	1056.5	1055.4	1054.9	1055.1	1055.3	1055.5	1055.6	1056.7
165°	1073.7	1072.6	1071.5	1070.5	1069.4	1068.9	1069.1	1069.3	1069.5	1069.7	1070.7
167.5°	1084.2	1083.0	1081.9	1080.8	1079.7	1079.2	1079.4	1079.5	1079.7	1079.9	1081.2
170°	1090.0	1088.8	1087.4	1086.2	1084.9	1084.4	1084.6	1084.8	1084.9	1085.2	1086.5
172.5°	1093.9	1092.7	1091.4	1090.1	1088.8	1088.4	1088.7	1089.0	1089.3	1089.6	1091.0
175°	1098.1	1097.1	1096.0	1094.9	1093.8	1093.4	1093.6	1093.7	1093.9	1094.1	1095.5
177.5°	1100.1	1099.3	1098.4	1097.5	1096.7	1096.3	1096.4	1096.6	1096.7	1096.8	1097.9
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1



TEST NUMBER: P333283-930

CATALOG NUMBER: S125DIP-S1090D1035U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	25.8	26.0	26.3	26.2	25.9	25.6	25.4	25.0
90°	14.8	15.7	16.6	17.4	17.9	18.4	19.0	19.6
92.5°	14.8	15.7	16.6	17.2	17.4	17.7	18.0	18.3
95°	14.8	15.7	16.6	17.1	17.1	17.1	17.1	17.1
97.5°	29.8	24.8	19.6	17.1	17.1	17.1	17.1	17.1
100°	87.7	60.8	33.8	20.0	19.2	18.5	17.9	17.1
102.5°	170.5	165.4	160.3	151.6	139.3	127.0	114.7	102.4
105°	242.6	242.6	242.6	242.5	242.3	242.1	242.0	241.7
107.5°	307.1	307.2	307.2	307.0	306.4	305.9	305.3	304.8
110°	348.9	348.4	347.9	347.7	347.9	348.1	348.2	348.4





TEST NUMBER: P333283-930

CATALOG NUMBER: S125DIP-S1090D1035U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	390.4	389.6	389.0	388.5	388.2	388.0	387.8	387.5
115°	452.8	452.1	451.3	450.5	449.4	448.3	447.2	446.1
117.5°	513.1	512.2	511.2	510.5	510.1	509.6	509.1	508.6
120°	552.0	551.6	551.3	550.7	549.8	548.9	548.0	547.1
122.5°	589.1	588.8	588.4	587.7	586.7	585.6	584.6	583.5
125°	643.3	642.5	641.8	641.2	640.7	640.1	639.6	639.0
127.5°	692.8	692.4	691.9	691.1	689.7	688.4	687.1	685.7
130°	725.0	724.5	724.0	723.3	722.4	721.5	720.6	719.6
132.5°	755.2	755.1	755.0	754.5	753.6	752.7	751.8	750.9
135°	799.5	799.2	798.7	798.0	797.0	795.9	794.8	793.7
137.5°	840.7	840.8	840.9	840.4	839.5	838.5	837.6	836.7
140°	866.1	866.4	866.7	866.4	865.4	864.2	863.2	862.1
142.5°	890.9	891.0	891.0	890.6	889.4	888.4	887.3	886.1
145°	925.9	926.1	926.3	925.9	924.8	923.7	922.6	921.5
147.5°	955.9	956.2	956.4	955.9	954.6	953.2	951.9	950.6
150°	975.2	975.5	975.8	975.3	973.9	972.4	970.9	969.6
152.5°	992.1	992.5	992.8	992.3	991.0	989.7	988.4	987.1
155°	1015.4	1015.9	1016.5	1016.0	1014.6	1013.1	1011.7	1010.2
157.5°	1034.7	1035.3	1035.8	1035.4	1034.0	1032.5	1031.0	1029.6
160°	1046.7	1047.4	1048.1	1047.7	1046.4	1044.9	1043.4	1042.0
162.5°	1057.7	1058.7	1059.7	1059.4	1057.9	1056.2	1054.7	1053.0
165°	1071.8	1072.9	1074.0	1073.8	1072.4	1070.9	1069.5	1068.0
167.5°	1082.6	1083.9	1085.2	1085.0	1083.4	1081.7	1080.1	1078.5
170°	1088.0	1089.5	1091.0	1090.8	1089.2	1087.6	1086.0	1084.3
172.5°	1092.3	1093.6	1094.9	1094.7	1093.1	1091.4	1089.8	1088.3
175°	1097.0	1098.5	1099.8	1099.8	1098.1	1096.5	1094.9	1093.2
177.5°	1098.9	1099.9	1100.9	1100.8	1099.7	1098.5	1097.4	1096.2
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1

(END OF REPORT)