

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333297-930

Luminaire Tested: **S125DIP-S1270D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333297-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S1270D365U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5297.8 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80
1	105	100	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68
2	96	88	82	77	91	85	79	74	78	73	69	72	68	65	66	63	61	57
3	88	78	70	64	83	75	68	62	69	63	59	64	59	55	59	55	52	49
4	80	69	61	55	77	67	59	53	62	55	50	57	52	48	53	48	45	42
5	74	62	53	47	71	60	52	46	55	49	44	51	46	42	47	43	39	37
6	68	56	47	41	65	54	46	40	50	43	38	46	41	37	43	38	35	32
7	63	51	42	36	60	49	41	36	45	39	34	42	37	32	39	35	31	29
8	59	46	38	32	56	45	37	32	42	35	30	39	33	29	36	31	28	26
9	55	42	34	29	53	41	34	29	38	32	27	36	30	26	33	29	25	23
10	51	39	31	26	49	38	31	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9671	9671	9671	9671
5°	11199	9703	8496	9703
10°	13029	9653	7444	9653
15°	14422	9582	6867	9582
20°	16144	9470	6403	9470
25°	18912	9344	6178	9344
30°	20427	9219	5982	9219
35°	16796	8984	5852	8984
40°	11938	8658	5712	8658
45°	9171	8219	5630	8219
50°	7829	7675	5620	7675
55°	6971	7142	5668	7142
60°	6288	6559	5813	6559
65°	5809	5974	5963	5974
70°	5280	5365	6048	5365
75°	4664	4726	5996	4726
80°	3924	3853	5482	3853
85°	3105	2779	4431	2779



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.7
10°-20°	429.2	8.1
20°-30°	696.9	13.2
30°-40°	850.1	16.0
40°-50°	773.3	14.6
50°-60°	616.0	11.6
60°-70°	429.0	8.1
70°-80°	228.8	4.3
80°-90°	58.5	1.1
90°-100°	103.6	2.0
100°-110°	222.7	4.2
110°-120°	209.0	3.9
120°-130°	169.4	3.2
130°-140°	135.9	2.6
140°-150°	102.6	1.9
150°-160°	72.2	1.4
160°-170°	42.6	0.8
170°-180°	13.8	0.3
0°-30°	1270.2	24.0
0°-40°	2120.3	40.0
0°-60°	3509.7	66.2
0°-90°	4226.0	79.8
90°-120°	535.3	10.1
90°-150°	943.1	17.8
90°-180°	1072.0	20.2
0°-180°	5297.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1727	1497	1310	1497	1727	174
15°	2157	1433	1027	1433	2157	617
25°	2654	1311	867	1311	2654	1212
35°	2130	1140	742	1140	2130	1304
45°	1004	900	616	900	1004	804
55°	619	634	503	634	619	558
65°	380	391	390	391	380	377
75°	187	189	240	189	187	201
85°	42	38	60	38	42	49
90°	7	0	7	0	7	6
95°	68	10	68	10	68	96
105°	382	32	382	32	382	380
115°	425	58	425	58	425	416
125°	335	81	335	81	335	303
135°	278	94	278	94	278	216
145°	220	110	220	110	220	140
155°	184	126	184	126	184	86
165°	161	137	161	137	161	46
175°	145	143	145	143	145	14
180°	143	143	143	143	143	



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1583.8	1581.8	1579.7	1575.6	1578.7	1570.0	1565.9	1558.9	1550.2	1547.2	1543.6
5°	1727.4	1730.6	1733.7	1720.4	1721.7	1712.8	1692.5	1675.9	1662.6	1645.4	1633.4
7.5°	1900.3	1892.8	1892.1	1883.5	1868.7	1856.7	1835.3	1808.1	1781.8	1751.8	1727.0
10°	1986.7	1987.4	1981.7	1971.5	1955.6	1944.2	1916.2	1889.5	1857.1	1818.9	1791.6
12.5°	2051.8	2054.5	2047.2	2033.5	2025.7	2000.1	1978.2	1946.4	1907.9	1877.4	1835.8
15°	2157.0	2150.0	2145.0	2127.8	2114.5	2087.7	2052.8	2019.7	1977.8	1939.0	1900.3
17.5°	2258.5	2264.1	2254.5	2238.9	2197.5	2166.3	2119.5	2074.1	2021.9	1969.9	1923.7
20°	2349.0	2354.1	2339.4	2312.1	2262.5	2231.4	2169.8	2111.3	2050.9	1984.2	1933.3
22.5°	2461.9	2457.8	2438.1	2396.5	2353.5	2296.0	2229.3	2158.0	2082.4	2007.0	1939.4
25°	2654.0	2627.3	2615.2	2563.8	2507.2	2422.7	2331.2	2226.9	2132.9	2033.1	1946.7
27.5°	2760.5	2752.1	2738.7	2702.9	2643.4	2552.9	2445.1	2318.1	2185.4	2059.4	1946.3
30°	2739.2	2740.5	2741.8	2730.3	2692.2	2624.1	2516.7	2380.1	2222.5	2080.8	1949.9
32.5°	2550.1	2573.2	2595.3	2621.5	2632.2	2619.1	2551.8	2428.5	2266.2	2105.2	1947.8
35°	2130.4	2137.3	2209.1	2280.3	2376.9	2451.9	2502.2	2447.4	2310.8	2125.9	1945.4
37.5°	1661.1	1695.4	1745.1	1825.5	1965.0	2089.8	2250.3	2324.2	2280.1	2132.7	1941.0
40°	1416.0	1447.8	1480.2	1562.2	1679.8	1831.0	2013.4	2169.1	2205.3	2111.3	1925.7
42.5°	1226.9	1252.1	1288.0	1349.6	1447.9	1581.8	1756.2	1959.7	2084.8	2049.3	1893.7
45°	1004.1	1020.0	1048.0	1097.0	1168.2	1273.0	1426.8	1649.3	1843.1	1907.2	1817.6
47.5°	859.5	859.4	881.1	914.9	966.3	1055.4	1169.1	1343.5	1550.5	1703.6	1696.6
50°	779.2	776.0	793.1	822.4	863.1	922.2	1030.9	1170.0	1369.0	1542.5	1590.7
52.5°	710.0	710.4	721.0	742.6	776.7	827.1	908.3	1033.8	1203.7	1381.8	1472.8
55°	619.1	616.4	628.5	643.2	668.0	701.0	759.5	855.4	993.4	1168.7	1286.9
57.5°	535.7	542.7	547.5	557.7	578.2	600.3	649.6	720.1	829.5	980.0	1105.0
60°	486.8	493.8	497.7	507.8	524.3	543.4	581.6	638.7	730.9	860.5	984.5
62.5°	443.1	448.6	449.8	459.0	472.5	491.1	521.1	569.1	641.9	755.3	876.7
65°	380.1	380.1	382.6	392.2	398.5	415.0	437.9	472.9	531.3	619.6	723.3
67.5°	319.3	322.4	321.7	325.9	331.7	344.6	361.0	389.9	433.2	497.7	580.5
70°	279.6	282.2	281.5	284.7	291.1	299.4	312.7	340.0	371.1	426.5	497.7
72.5°	244.0	245.1	243.4	247.6	251.4	258.7	273.5	288.1	317.2	363.9	422.4
75°	186.9	188.1	189.4	191.9	195.8	199.6	207.2	221.8	240.8	275.8	313.3
77.5°	140.1	137.6	140.7	140.3	142.5	145.4	152.1	159.9	175.5	197.6	226.7
80°	105.5	106.2	106.2	106.8	110.0	111.9	117.6	123.3	135.3	151.9	172.3
82.5°	77.0	78.7	77.7	78.8	81.4	82.8	86.0	90.7	97.8	110.7	125.5
85°	41.9	38.8	40.0	41.3	41.3	41.9	44.5	46.4	50.2	55.3	61.0
87.5°	13.5	14.5	15.0	15.0	15.5	15.4	17.4	17.3	18.8	20.2	22.2
90°	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2	4.9	4.6	4.0
92.5°	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0	75.2	92.9	94.4
95°	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2	249.8	255.3	208.3
97.5°	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5	316.1	272.6	186.1
100°	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4	332.2	260.2	166.0
102.5°	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8	322.5	238.3	150.7
105°	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8	291.6	208.9	136.0
107.5°	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2	260.0	188.7	129.8
110°	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3	242.1	179.2	127.9



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4	228.7	173.7	127.9
115°	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6	214.1	167.7	128.8
117.5°	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3	205.4	164.8	130.7
120°	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0	200.6	163.4	132.6
122.5°	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8	196.4	162.2	134.1
125°	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7	190.8	160.8	136.9
127.5°	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5	185.6	160.1	139.9
130°	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7	182.1	159.6	141.8
132.5°	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9	179.4	159.6	143.8
135°	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5	176.0	159.6	146.7
137.5°	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2	173.1	160.0	149.3
140°	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7	171.7	160.2	150.4
142.5°	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7	170.6	160.5	151.1
145°	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8	168.8	160.2	151.8
147.5°	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1	167.1	159.5	152.1
150°	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0	165.7	158.7	152.1
152.5°	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7	164.0	157.8	151.9
155°	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2	161.3	156.2	151.2
157.5°	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8	158.8	154.4	150.5
160°	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5	156.8	153.3	149.9
162.5°	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9	154.9	151.9	149.1
165°	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4	152.1	149.9	148.1
167.5°	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1	149.4	147.8	146.5
170°	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3	147.8	146.7	145.8
172.5°	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2	146.2	145.3	144.9
175°	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0	144.1	143.8	143.8
177.5°	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4	143.2	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1540.6	1537.0	1532.9	1525.8	1517.2	1512.6	1505.5	1500.9	1491.8	1484.1	1476.0
5°	1618.7	1602.2	1587.0	1567.2	1545.6	1531.6	1515.2	1496.7	1477.6	1457.9	1436.3
7.5°	1699.7	1670.5	1638.7	1604.5	1571.1	1540.3	1510.9	1482.1	1455.1	1422.6	1395.1
10°	1754.1	1717.3	1677.8	1631.4	1586.3	1546.9	1506.8	1471.9	1436.3	1398.2	1364.5
12.5°	1808.5	1759.4	1703.7	1652.8	1598.6	1550.9	1503.8	1459.2	1414.5	1372.2	1333.0
15°	1846.9	1803.7	1752.2	1679.8	1618.7	1553.3	1491.0	1433.1	1379.2	1332.1	1282.5
17.5°	1872.2	1816.5	1761.2	1691.7	1611.8	1538.6	1467.9	1401.7	1340.8	1281.2	1233.5
20°	1876.7	1819.6	1761.7	1693.7	1611.8	1527.9	1457.3	1377.9	1312.4	1250.8	1192.3
22.5°	1875.3	1810.4	1747.5	1677.5	1597.5	1520.2	1434.9	1354.0	1282.9	1222.3	1161.2
25°	1860.8	1791.6	1712.8	1642.3	1563.4	1481.5	1395.1	1311.2	1238.7	1169.4	1109.1
27.5°	1848.9	1759.1	1669.8	1587.6	1511.5	1436.3	1353.6	1267.6	1187.3	1117.1	1060.2
30°	1834.2	1735.7	1635.2	1549.5	1471.3	1398.2	1320.1	1236.2	1152.3	1083.6	1022.6
32.5°	1821.0	1706.2	1600.2	1506.8	1424.0	1352.9	1280.8	1201.0	1118.7	1049.0	988.0
35°	1795.5	1662.6	1541.2	1435.7	1347.4	1274.2	1213.9	1139.5	1063.9	996.5	938.1
37.5°	1763.0	1605.4	1475.1	1364.5	1267.6	1190.7	1134.4	1077.3	1004.8	939.9	887.0
40°	1737.6	1564.7	1426.8	1313.7	1213.2	1133.2	1081.1	1027.0	966.7	906.3	850.4
42.5°	1705.5	1528.1	1378.0	1256.2	1156.8	1078.8	1024.1	978.2	925.0	868.7	816.8
45°	1646.7	1461.8	1299.0	1168.2	1067.7	990.8	934.3	899.9	859.9	806.5	762.6
47.5°	1560.2	1382.0	1213.7	1078.6	975.0	903.8	850.8	817.8	789.6	749.9	710.1
50°	1483.4	1322.6	1152.3	1018.1	914.5	842.7	793.8	763.9	739.8	709.2	675.6
52.5°	1397.4	1247.8	1091.8	959.2	856.6	785.8	737.8	711.6	691.5	669.6	636.4
55°	1260.9	1133.8	988.9	863.1	768.3	699.1	657.1	634.3	617.8	601.2	580.9
57.5°	1110.5	1011.1	882.8	767.8	680.5	617.5	578.4	556.1	543.2	534.8	522.8
60°	1004.8	919.7	809.0	704.2	619.1	563.1	525.0	507.8	497.0	490.0	481.1
62.5°	906.7	836.7	734.3	638.6	564.1	511.2	477.2	460.5	450.2	446.8	439.4
65°	762.0	708.0	623.5	544.0	480.5	435.4	406.8	390.9	384.5	380.7	381.3
67.5°	619.5	586.6	518.7	450.9	400.2	362.4	339.5	327.3	324.2	319.0	318.9
70°	532.6	507.8	450.6	391.5	346.3	317.2	296.8	284.1	280.9	278.3	277.8
72.5°	455.8	434.1	384.5	337.1	296.5	270.8	254.1	246.5	241.2	239.7	239.6
75°	342.6	330.5	291.1	253.6	225.6	207.8	196.4	189.4	185.6	184.9	185.6
77.5°	243.5	233.0	208.0	181.4	163.7	150.3	140.6	138.2	133.9	134.0	133.3
80°	183.0	176.0	160.1	139.2	124.6	113.2	108.0	103.6	102.3	100.4	102.3
82.5°	132.7	125.2	114.4	101.0	88.9	82.1	77.0	75.7	74.8	73.9	74.4
85°	65.5	66.1	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.2	36.9
87.5°	23.2	22.0	19.9	18.3	15.6	13.9	13.4	13.8	12.3	11.9	12.6
90°	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3	0.6	1.1	1.7
92.5°	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5	4.2	6.7	10.3
95°	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5	9.8	12.1	15.2
97.5°	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8	16.1	17.8	21.0
100°	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1	20.7	21.9	25.0
102.5°	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0	25.4	26.3	29.7
105°	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5	32.5	34.0	36.9
107.5°	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9	40.5	41.9	44.3
110°	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2	45.8	47.0	49.6



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5	51.1	52.0	54.6
115°	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2	58.8	59.7	62.2
117.5°	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1	66.0	66.9	69.5
120°	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7	70.6	71.7	74.4
122.5°	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6	75.2	76.1	78.8
125°	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7	81.3	82.7	85.3
127.5°	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4	86.3	88.1	91.5
130°	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5	89.4	91.6	95.4
132.5°	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7	91.9	94.7	98.8
135°	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5	95.6	99.1	103.7
137.5°	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2	100.1	103.3	107.9
140°	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0	102.9	106.3	111.0
142.5°	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3	105.8	109.1	113.7
145°	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1	110.6	113.5	117.6
147.5°	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1	115.4	118.0	121.7
150°	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1	118.7	120.7	124.5
152.5°	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4	121.7	123.5	126.8
155°	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6	125.6	127.3	130.2
157.5°	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5	129.4	130.8	133.2
160°	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0	131.7	132.8	134.9
162.5°	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0	133.8	134.9	136.7
165°	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1	136.6	137.5	138.8
167.5°	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3	138.9	139.5	140.2
170°	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6	140.3	140.6	141.2
172.5°	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5	141.0	141.3	141.9
175°	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6	142.0	142.4	142.6
177.5°	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2	142.7	142.7	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1471.4	1465.8	1461.3	1451.1	1445.4	1437.9	1431.7	1438.4	1431.3	1434.3	1429.7
5°	1425.6	1407.7	1395.1	1376.6	1360.7	1346.1	1335.3	1333.3	1328.3	1325.8	1318.1
7.5°	1370.4	1348.1	1326.2	1302.1	1281.7	1261.0	1247.8	1236.9	1229.6	1220.1	1213.7
10°	1337.8	1308.0	1282.5	1253.3	1227.8	1205.7	1187.8	1178.9	1170.7	1158.6	1154.1
12.5°	1297.6	1266.7	1235.7	1204.5	1180.1	1155.3	1140.0	1126.6	1120.9	1107.3	1105.9
15°	1249.4	1203.1	1172.6	1140.8	1107.1	1086.8	1074.1	1059.5	1053.1	1043.6	1036.6
17.5°	1192.0	1150.6	1112.5	1079.5	1050.7	1033.6	1017.7	1007.7	996.8	990.6	979.1
20°	1150.3	1110.9	1072.8	1037.9	1015.6	995.9	983.2	973.6	962.2	959.0	947.6
22.5°	1115.2	1071.8	1035.2	1005.8	981.5	959.3	945.6	939.1	931.2	921.5	919.1
25°	1058.2	1013.1	981.9	952.7	931.1	910.8	901.2	892.9	885.3	878.3	875.8
27.5°	1008.9	968.6	931.6	905.1	886.3	867.8	859.4	849.4	843.8	838.1	831.3
30°	974.3	932.9	900.6	875.1	854.8	838.3	829.4	822.4	817.3	812.2	808.5
32.5°	938.7	900.4	869.0	844.2	823.8	811.3	803.5	798.5	792.9	786.8	782.0
35°	891.7	849.7	819.2	797.6	781.7	772.2	763.3	758.8	752.5	752.5	747.4
37.5°	838.7	802.4	775.5	755.8	741.5	733.0	723.4	720.3	716.2	713.5	711.8
40°	807.1	773.5	748.0	728.3	713.1	706.0	698.5	693.4	690.8	687.6	686.4
42.5°	774.6	742.4	718.0	699.9	686.6	680.7	673.5	670.0	664.9	660.7	660.0
45°	725.1	694.0	671.8	657.1	645.7	638.7	634.3	626.6	624.1	619.1	618.4
47.5°	678.2	648.4	626.6	614.6	604.5	598.8	591.8	584.2	581.3	578.7	578.5
50°	643.2	615.9	595.5	584.1	574.5	566.3	559.3	554.2	552.3	552.3	553.6
52.5°	607.6	584.3	567.0	553.0	544.0	535.2	528.8	525.7	522.8	525.9	528.2
55°	555.5	532.0	519.3	505.9	497.0	486.8	483.6	482.4	480.5	485.6	488.1
57.5°	500.3	483.8	468.9	455.7	447.7	441.8	437.5	436.8	440.3	442.7	450.9
60°	465.2	446.1	432.8	422.7	413.1	409.3	408.1	406.8	409.3	416.3	427.1
62.5°	426.6	411.1	396.7	389.1	382.0	375.8	375.4	376.3	381.3	389.3	400.1
65°	369.9	356.5	347.0	338.1	332.4	328.6	329.9	332.4	338.1	348.9	361.0
67.5°	312.3	303.1	294.6	287.4	281.9	281.9	283.2	287.0	293.8	306.2	317.2
70°	275.2	265.1	258.0	254.9	250.4	247.9	251.7	258.0	263.7	275.2	284.7
72.5°	238.1	229.4	224.0	221.8	219.9	217.8	219.2	226.0	233.7	245.2	256.2
75°	183.0	179.9	176.0	173.5	171.6	172.8	174.1	180.5	186.9	198.9	211.7
77.5°	133.6	130.3	128.0	127.3	126.4	126.9	130.5	135.3	141.5	150.3	159.9
80°	101.0	99.8	98.5	97.8	97.8	98.5	103.6	106.8	112.5	120.7	128.4
82.5°	73.6	72.8	72.6	72.5	73.0	73.1	76.1	80.3	85.0	91.2	97.8
85°	38.8	37.5	39.4	40.0	38.8	40.7	41.9	44.5	46.4	49.6	52.7
87.5°	13.2	14.3	13.9	14.5	14.5	15.7	15.2	17.3	18.3	19.5	19.1
90°	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2	5.5	5.8	6.4
92.5°	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0	37.0	27.9	23.6
95°	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2	163.4	127.9	103.7
97.5°	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5	277.9	243.3	209.6
100°	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4	340.3	310.6	280.6
102.5°	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8	378.5	364.4	344.1
105°	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8	400.2	412.9	409.8
107.5°	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2	380.9	413.4	428.5
110°	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3	359.1	399.7	424.1



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4	337.4	378.5	407.3
115°	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6	306.3	345.8	377.2
117.5°	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3	284.8	318.8	347.6
120°	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0	272.6	304.3	329.6
122.5°	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8	263.8	292.0	315.8
125°	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7	252.1	277.2	297.9
127.5°	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5	240.9	264.3	283.7
130°	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7	233.1	255.6	274.3
132.5°	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9	225.8	246.1	264.2
135°	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5	214.3	232.8	249.2
137.5°	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2	204.2	219.6	233.5
140°	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7	198.2	211.5	223.6
142.5°	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7	193.1	204.6	215.1
145°	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8	186.7	195.7	203.4
147.5°	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1	181.3	188.3	194.1
150°	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0	178.4	183.8	189.0
152.5°	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7	175.4	180.3	184.4
155°	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2	170.9	174.9	178.1
157.5°	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8	166.6	169.7	172.2
160°	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5	163.4	166.2	168.3
162.5°	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9	160.6	163.1	164.9
165°	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4	156.5	158.2	159.6
167.5°	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1	152.5	153.8	154.8
170°	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3	150.1	151.0	151.6
172.5°	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2	148.1	148.7	149.0
175°	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0	145.0	145.5	145.5
177.5°	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4	143.6	143.6	143.6
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1426.7	1430.2	1427.2	1431.3	1427.2	1430.2	1426.7	1429.7	1434.3	1431.3	1438.4
5°	1314.9	1309.2	1313.0	1310.5	1313.0	1309.2	1314.9	1318.1	1325.8	1328.3	1333.3
7.5°	1211.7	1206.2	1200.0	1197.1	1200.0	1206.2	1211.7	1213.7	1220.1	1229.6	1236.9
10°	1147.1	1140.2	1139.5	1135.1	1139.5	1140.2	1147.1	1154.1	1158.6	1170.7	1178.9
12.5°	1099.8	1093.4	1086.1	1084.3	1086.1	1093.4	1099.8	1105.9	1107.3	1120.9	1126.6
15°	1032.7	1027.7	1023.2	1027.0	1023.2	1027.7	1032.7	1036.6	1043.6	1053.1	1059.5
17.5°	977.0	972.7	972.0	967.3	972.0	972.7	977.0	979.1	990.6	996.8	1007.7
20°	941.9	938.7	940.0	931.7	940.0	938.7	941.9	947.6	959.0	962.2	973.6
22.5°	914.0	907.7	906.9	905.3	906.9	907.7	914.0	919.1	921.5	931.2	939.1
25°	870.1	866.9	863.7	866.9	863.7	866.9	870.1	875.8	878.3	885.3	892.9
27.5°	831.8	828.0	827.1	827.4	827.1	828.0	831.8	831.3	838.1	843.8	849.4
30°	808.5	802.1	802.7	802.1	802.7	802.1	808.5	808.5	812.2	817.3	822.4
32.5°	783.0	778.7	777.8	776.7	777.8	778.7	783.0	782.0	786.8	792.9	798.5
35°	745.5	745.5	742.3	742.3	742.3	745.5	745.5	747.4	752.5	752.5	758.8
37.5°	710.3	709.6	707.8	708.0	707.8	709.6	710.3	711.8	713.5	716.2	720.3
40°	683.9	683.2	681.3	677.5	681.3	683.2	683.9	686.4	687.6	690.8	693.4
42.5°	658.4	656.2	655.3	654.1	655.3	656.2	658.4	660.0	660.7	664.9	670.0
45°	618.4	618.4	617.1	616.4	617.1	618.4	618.4	618.4	619.1	624.1	626.6
47.5°	579.5	580.7	583.0	582.7	583.0	580.7	579.5	578.5	578.7	581.3	584.2
50°	556.1	556.8	558.6	559.3	558.6	556.8	556.1	553.6	552.3	552.3	554.2
52.5°	530.2	533.9	536.3	535.9	536.3	533.9	530.2	528.2	525.9	522.8	525.7
55°	493.8	498.2	502.7	503.4	502.7	498.2	493.8	488.1	485.6	480.5	482.4
57.5°	457.9	464.1	468.8	470.3	468.8	464.1	457.9	450.9	442.7	440.3	436.8
60°	433.4	441.7	447.4	450.0	447.4	441.7	433.4	427.1	416.3	409.3	406.8
62.5°	410.0	419.3	425.0	425.6	425.0	419.3	410.0	400.1	389.3	381.3	376.3
65°	371.8	381.3	386.4	390.2	386.4	381.3	371.8	361.0	348.9	338.1	332.4
67.5°	330.6	340.1	345.8	348.8	345.8	340.1	330.6	317.2	306.2	293.8	287.0
70°	300.6	310.1	317.8	320.3	317.8	310.1	300.6	284.7	275.2	263.7	258.0
72.5°	271.1	279.6	285.8	288.8	285.8	279.6	271.1	256.2	245.2	233.7	226.0
75°	219.9	231.3	237.1	240.3	237.1	231.3	219.9	211.7	198.9	186.9	180.5
77.5°	169.6	180.0	183.4	185.1	183.4	180.0	169.6	159.9	150.3	141.5	135.3
80°	136.0	142.4	146.8	147.4	146.8	142.4	136.0	128.4	120.7	112.5	106.8
82.5°	104.5	109.8	111.2	112.8	111.2	109.8	104.5	97.8	91.2	85.0	80.3
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.7	49.6	46.4	44.5
87.5°	20.1	19.6	19.6	20.6	19.6	19.6	20.1	19.1	19.5	18.3	17.3
90°	6.4	6.4	6.6	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2
92.5°	20.0	19.2	18.8	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0
95°	83.2	74.6	72.3	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2
97.5°	191.8	175.7	167.4	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5
100°	260.7	240.0	229.3	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4
102.5°	322.8	308.0	296.4	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8
105°	400.5	391.0	385.2	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8
107.5°	433.2	433.2	431.2	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2
110°	437.1	442.5	444.6	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	426.2	435.7	440.7	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4
115°	399.7	413.4	421.5	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6
117.5°	370.1	384.4	392.4	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3
120°	351.0	364.8	372.6	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0
122.5°	334.8	347.5	355.3	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8
125°	314.1	325.9	332.2	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7
127.5°	298.4	308.8	314.8	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5
130°	288.7	298.2	304.0	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7
132.5°	278.6	288.0	293.3	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9
135°	262.0	271.4	276.6	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5
137.5°	244.8	253.5	258.3	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2
140°	234.2	241.7	246.1	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7
142.5°	224.1	230.5	234.6	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7
145°	210.3	215.2	218.4	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8
147.5°	199.6	203.5	205.3	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1
150°	193.3	196.8	198.0	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0
152.5°	188.0	190.8	191.9	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7
155°	180.9	183.0	183.8	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2
157.5°	174.5	176.1	176.9	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8
160°	170.3	171.7	172.3	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5
162.5°	166.4	167.5	167.7	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9
165°	160.8	161.3	161.3	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4
167.5°	155.4	155.9	155.6	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1
170°	152.1	152.5	152.5	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3
172.5°	149.1	149.7	149.2	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2
175°	145.5	145.8	145.2	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0
177.5°	143.4	143.6	142.9	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1431.7	1437.9	1445.4	1451.1	1461.3	1465.8	1471.4	1476.0	1484.1	1491.8	1500.9
5°	1335.3	1346.1	1360.7	1376.6	1395.1	1407.7	1425.6	1436.3	1457.9	1477.6	1496.7
7.5°	1247.8	1261.0	1281.7	1302.1	1326.2	1348.1	1370.4	1395.1	1422.6	1455.1	1482.1
10°	1187.8	1205.7	1227.8	1253.3	1282.5	1308.0	1337.8	1364.5	1398.2	1436.3	1471.9
12.5°	1140.0	1155.3	1180.1	1204.5	1235.7	1266.7	1297.6	1333.0	1372.2	1414.5	1459.2
15°	1074.1	1086.8	1107.1	1140.8	1172.6	1203.1	1249.4	1282.5	1332.1	1379.2	1433.1
17.5°	1017.7	1033.6	1050.7	1079.5	1112.5	1150.6	1192.0	1233.5	1281.2	1340.8	1401.7
20°	983.2	995.9	1015.6	1037.9	1072.8	1110.9	1150.3	1192.3	1250.8	1312.4	1377.9
22.5°	945.6	959.3	981.5	1005.8	1035.2	1071.8	1115.2	1161.2	1222.3	1282.9	1354.0
25°	901.2	910.8	931.1	952.7	981.9	1013.1	1058.2	1109.1	1169.4	1238.7	1311.2
27.5°	859.4	867.8	886.3	905.1	931.6	968.6	1008.9	1060.2	1117.1	1187.3	1267.6
30°	829.4	838.3	854.8	875.1	900.6	932.9	974.3	1022.6	1083.6	1152.3	1236.2
32.5°	803.5	811.3	823.8	844.2	869.0	900.4	938.7	988.0	1049.0	1118.7	1201.0
35°	763.3	772.2	781.7	797.6	819.2	849.7	891.7	938.1	996.5	1063.9	1139.5
37.5°	723.4	733.0	741.5	755.8	775.5	802.4	838.7	887.0	939.9	1004.8	1077.3
40°	698.5	706.0	713.1	728.3	748.0	773.5	807.1	850.4	906.3	966.7	1027.0
42.5°	673.5	680.7	686.6	699.9	718.0	742.4	774.6	816.8	868.7	925.0	978.2
45°	634.3	638.7	645.7	657.1	671.8	694.0	725.1	762.6	806.5	859.9	899.9
47.5°	591.8	598.8	604.5	614.6	626.6	648.4	678.2	710.1	749.9	789.6	817.8
50°	559.3	566.3	574.5	584.1	595.5	615.9	643.2	675.6	709.2	739.8	763.9
52.5°	528.8	535.2	544.0	553.0	567.0	584.3	607.6	636.4	669.6	691.5	711.6
55°	483.6	486.8	497.0	505.9	519.3	532.0	555.5	580.9	601.2	617.8	634.3
57.5°	437.5	441.8	447.7	455.7	468.9	483.8	500.3	522.8	534.8	543.2	556.1
60°	408.1	409.3	413.1	422.7	432.8	446.1	465.2	481.1	490.0	497.0	507.8
62.5°	375.4	375.8	382.0	389.1	396.7	411.1	426.6	439.4	446.8	450.2	460.5
65°	329.9	328.6	332.4	338.1	347.0	356.5	369.9	381.3	380.7	384.5	390.9
67.5°	283.2	281.9	281.9	287.4	294.6	303.1	312.3	318.9	319.0	324.2	327.3
70°	251.7	247.9	250.4	254.9	258.0	265.1	275.2	277.8	278.3	280.9	284.1
72.5°	219.2	217.8	219.9	221.8	224.0	229.4	238.1	239.6	239.7	241.2	246.5
75°	174.1	172.8	171.6	173.5	176.0	179.9	183.0	185.6	184.9	185.6	189.4
77.5°	130.5	126.9	126.4	127.3	128.0	130.3	133.6	133.3	134.0	133.9	138.2
80°	103.6	98.5	97.8	97.8	98.5	99.8	101.0	102.3	100.4	102.3	103.6
82.5°	76.1	73.1	73.0	72.5	72.6	72.8	73.6	74.4	73.9	74.8	75.7
85°	41.9	40.7	38.8	40.0	39.4	37.5	38.8	36.9	36.2	36.9	37.5
87.5°	15.2	15.7	14.5	14.5	13.9	14.3	13.2	12.6	11.9	12.3	13.8
90°	4.9	4.6	4.0	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3
92.5°	75.2	92.9	94.4	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5
95°	249.8	255.3	208.3	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5
97.5°	316.1	272.6	186.1	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8
100°	332.2	260.2	166.0	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1
102.5°	322.5	238.3	150.7	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0
105°	291.6	208.9	136.0	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5
107.5°	260.0	188.7	129.8	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9
110°	242.1	179.2	127.9	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	228.7	173.7	127.9	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5
115°	214.1	167.7	128.8	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2
117.5°	205.4	164.8	130.7	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1
120°	200.6	163.4	132.6	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7
122.5°	196.4	162.2	134.1	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6
125°	190.8	160.8	136.9	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7
127.5°	185.6	160.1	139.9	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4
130°	182.1	159.6	141.8	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5
132.5°	179.4	159.6	143.8	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7
135°	176.0	159.6	146.7	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5
137.5°	173.1	160.0	149.3	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2
140°	171.7	160.2	150.4	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0
142.5°	170.6	160.5	151.1	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3
145°	168.8	160.2	151.8	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1
147.5°	167.1	159.5	152.1	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1
150°	165.7	158.7	152.1	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1
152.5°	164.0	157.8	151.9	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4
155°	161.3	156.2	151.2	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6
157.5°	158.8	154.4	150.5	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5
160°	156.8	153.3	149.9	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0
162.5°	154.9	151.9	149.1	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0
165°	152.1	149.9	148.1	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1
167.5°	149.4	147.8	146.5	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3
170°	147.8	146.7	145.8	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6
172.5°	146.2	145.3	144.9	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5
175°	144.1	143.8	143.8	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6
177.5°	143.2	142.9	142.9	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1505.5	1512.6	1517.2	1525.8	1532.9	1537.0	1540.6	1543.6	1547.2	1550.2	1558.9
5°	1515.2	1531.6	1545.6	1567.2	1587.0	1602.2	1618.7	1633.4	1645.4	1662.6	1675.9
7.5°	1510.9	1540.3	1571.1	1604.5	1638.7	1670.5	1699.7	1727.0	1751.8	1781.8	1808.1
10°	1506.8	1546.9	1586.3	1631.4	1677.8	1717.3	1754.1	1791.6	1818.9	1857.1	1889.5
12.5°	1503.8	1550.9	1598.6	1652.8	1703.7	1759.4	1808.5	1835.8	1877.4	1907.9	1946.4
15°	1491.0	1553.3	1618.7	1679.8	1752.2	1803.7	1846.9	1900.3	1939.0	1977.8	2019.7
17.5°	1467.9	1538.6	1611.8	1691.7	1761.2	1816.5	1872.2	1923.7	1969.9	2021.9	2074.1
20°	1457.3	1527.9	1611.8	1693.7	1761.7	1819.6	1876.7	1933.3	1984.2	2050.9	2111.3
22.5°	1434.9	1520.2	1597.5	1677.5	1747.5	1810.4	1875.3	1939.4	2007.0	2082.4	2158.0
25°	1395.1	1481.5	1563.4	1642.3	1712.8	1791.6	1860.8	1946.7	2033.1	2132.9	2226.9
27.5°	1353.6	1436.3	1511.5	1587.6	1669.8	1759.1	1848.9	1946.3	2059.4	2185.4	2318.1
30°	1320.1	1398.2	1471.3	1549.5	1635.2	1735.7	1834.2	1949.9	2080.8	2222.5	2380.1
32.5°	1280.8	1352.9	1424.0	1506.8	1600.2	1706.2	1821.0	1947.8	2105.2	2266.2	2428.5
35°	1213.9	1274.2	1347.4	1435.7	1541.2	1662.6	1795.5	1945.4	2125.9	2310.8	2447.4
37.5°	1134.4	1190.7	1267.6	1364.5	1475.1	1605.4	1763.0	1941.0	2132.7	2280.1	2324.2
40°	1081.1	1133.2	1213.2	1313.7	1426.8	1564.7	1737.6	1925.7	2111.3	2205.3	2169.1
42.5°	1024.1	1078.8	1156.8	1256.2	1378.0	1528.1	1705.5	1893.7	2049.3	2084.8	1959.7
45°	934.3	990.8	1067.7	1168.2	1299.0	1461.8	1646.7	1817.6	1907.2	1843.1	1649.3
47.5°	850.8	903.8	975.0	1078.6	1213.7	1382.0	1560.2	1696.6	1703.6	1550.5	1343.5
50°	793.8	842.7	914.5	1018.1	1152.3	1322.6	1483.4	1590.7	1542.5	1369.0	1170.0
52.5°	737.8	785.8	856.6	959.2	1091.8	1247.8	1397.4	1472.8	1381.8	1203.7	1033.8
55°	657.1	699.1	768.3	863.1	988.9	1133.8	1260.9	1286.9	1168.7	993.4	855.4
57.5°	578.4	617.5	680.5	767.8	882.8	1011.1	1110.5	1105.0	980.0	829.5	720.1
60°	525.0	563.1	619.1	704.2	809.0	919.7	1004.8	984.5	860.5	730.9	638.7
62.5°	477.2	511.2	564.1	638.6	734.3	836.7	906.7	876.7	755.3	641.9	569.1
65°	406.8	435.4	480.5	544.0	623.5	708.0	762.0	723.3	619.6	531.3	472.9
67.5°	339.5	362.4	400.2	450.9	518.7	586.6	619.5	580.5	497.7	433.2	389.9
70°	296.8	317.2	346.3	391.5	450.6	507.8	532.6	497.7	426.5	371.1	340.0
72.5°	254.1	270.8	296.5	337.1	384.5	434.1	455.8	422.4	363.9	317.2	288.1
75°	196.4	207.8	225.6	253.6	291.1	330.5	342.6	313.3	275.8	240.8	221.8
77.5°	140.6	150.3	163.7	181.4	208.0	233.0	243.5	226.7	197.6	175.5	159.9
80°	108.0	113.2	124.6	139.2	160.1	176.0	183.0	172.3	151.9	135.3	123.3
82.5°	77.0	82.1	88.9	101.0	114.4	125.2	132.7	125.5	110.7	97.8	90.7
85°	37.5	40.7	44.5	49.6	59.8	66.1	65.5	61.0	55.3	50.2	46.4
87.5°	13.4	13.9	15.6	18.3	19.9	22.0	23.2	22.2	20.2	18.8	17.3
90°	0.6	1.1	1.7	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2
92.5°	4.2	6.7	10.3	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0
95°	9.8	12.1	15.2	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2
97.5°	16.1	17.8	21.0	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5
100°	20.7	21.9	25.0	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4
102.5°	25.4	26.3	29.7	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8
105°	32.5	34.0	36.9	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8
107.5°	40.5	41.9	44.3	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2
110°	45.8	47.0	49.6	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.0	54.6	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4
115°	58.8	59.7	62.2	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6
117.5°	66.0	66.9	69.5	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3
120°	70.6	71.7	74.4	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0
122.5°	75.2	76.1	78.8	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8
125°	81.3	82.7	85.3	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7
127.5°	86.3	88.1	91.5	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5
130°	89.4	91.6	95.4	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7
132.5°	91.9	94.7	98.8	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9
135°	95.6	99.1	103.7	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5
137.5°	100.1	103.3	107.9	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2
140°	102.9	106.3	111.0	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7
142.5°	105.8	109.1	113.7	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7
145°	110.6	113.5	117.6	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8
147.5°	115.4	118.0	121.7	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1
150°	118.7	120.7	124.5	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0
152.5°	121.7	123.5	126.8	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7
155°	125.6	127.3	130.2	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2
157.5°	129.4	130.8	133.2	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8
160°	131.7	132.8	134.9	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5
162.5°	133.8	134.9	136.7	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9
165°	136.6	137.5	138.8	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4
167.5°	138.9	139.5	140.2	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1
170°	140.3	140.6	141.2	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3
172.5°	141.0	141.3	141.9	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2
175°	142.0	142.4	142.6	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0
177.5°	142.7	142.7	142.9	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1565.9	1570.0	1578.7	1575.6	1579.7	1581.8	1583.8
5°	1692.5	1712.8	1721.7	1720.4	1733.7	1730.6	1727.4
7.5°	1835.3	1856.7	1868.7	1883.5	1892.1	1892.8	1900.3
10°	1916.2	1944.2	1955.6	1971.5	1981.7	1987.4	1986.7
12.5°	1978.2	2000.1	2025.7	2033.5	2047.2	2054.5	2051.8
15°	2052.8	2087.7	2114.5	2127.8	2145.0	2150.0	2157.0
17.5°	2119.5	2166.3	2197.5	2238.9	2254.5	2264.1	2258.5
20°	2169.8	2231.4	2262.5	2312.1	2339.4	2354.1	2349.0
22.5°	2229.3	2296.0	2353.5	2396.5	2438.1	2457.8	2461.9
25°	2331.2	2422.7	2507.2	2563.8	2615.2	2627.3	2654.0
27.5°	2445.1	2552.9	2643.4	2702.9	2738.7	2752.1	2760.5
30°	2516.7	2624.1	2692.2	2730.3	2741.8	2740.5	2739.2
32.5°	2551.8	2619.1	2632.2	2621.5	2595.3	2573.2	2550.1
35°	2502.2	2451.9	2376.9	2280.3	2209.1	2137.3	2130.4
37.5°	2250.3	2089.8	1965.0	1825.5	1745.1	1695.4	1661.1
40°	2013.4	1831.0	1679.8	1562.2	1480.2	1447.8	1416.0
42.5°	1756.2	1581.8	1447.9	1349.6	1288.0	1252.1	1226.9
45°	1426.8	1273.0	1168.2	1097.0	1048.0	1020.0	1004.1
47.5°	1169.1	1055.4	966.3	914.9	881.1	859.4	859.5
50°	1030.9	922.2	863.1	822.4	793.1	776.0	779.2
52.5°	908.3	827.1	776.7	742.6	721.0	710.4	710.0
55°	759.5	701.0	668.0	643.2	628.5	616.4	619.1
57.5°	649.6	600.3	578.2	557.7	547.5	542.7	535.7
60°	581.6	543.4	524.3	507.8	497.7	493.8	486.8
62.5°	521.1	491.1	472.5	459.0	449.8	448.6	443.1
65°	437.9	415.0	398.5	392.2	382.6	380.1	380.1
67.5°	361.0	344.6	331.7	325.9	321.7	322.4	319.3
70°	312.7	299.4	291.1	284.7	281.5	282.2	279.6
72.5°	273.5	258.7	251.4	247.6	243.4	245.1	244.0
75°	207.2	199.6	195.8	191.9	189.4	188.1	186.9
77.5°	152.1	145.4	142.5	140.3	140.7	137.6	140.1
80°	117.6	111.9	110.0	106.8	106.2	106.2	105.5
82.5°	86.0	82.8	81.4	78.8	77.7	78.7	77.0
85°	44.5	41.9	41.3	41.3	40.0	38.8	41.9
87.5°	17.4	15.4	15.5	15.0	15.0	14.5	13.5
90°	5.5	5.8	6.4	6.4	6.4	6.6	6.6
92.5°	37.0	27.9	23.6	20.0	19.2	18.8	18.3
95°	163.4	127.9	103.7	83.2	74.6	72.3	67.8
97.5°	277.9	243.3	209.6	191.8	175.7	167.4	163.6
100°	340.3	310.6	280.6	260.7	240.0	229.3	224.8
102.5°	378.5	364.4	344.1	322.8	308.0	296.4	293.0
105°	400.2	412.9	409.8	400.5	391.0	385.2	381.8
107.5°	380.9	413.4	428.5	433.2	433.2	431.2	428.9
110°	359.1	399.7	424.1	437.1	442.5	444.6	444.6



TEST NUMBER: P333297-930

CATALOG NUMBER: S125DIP-S1270D365U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	337.4	378.5	407.3	426.2	435.7	440.7	442.8
115°	306.3	345.8	377.2	399.7	413.4	421.5	425.3
117.5°	284.8	318.8	347.6	370.1	384.4	392.4	394.7
120°	272.6	304.3	329.6	351.0	364.8	372.6	374.9
122.5°	263.8	292.0	315.8	334.8	347.5	355.3	357.3
125°	252.1	277.2	297.9	314.1	325.9	332.2	335.1
127.5°	240.9	264.3	283.7	298.4	308.8	314.8	316.1
130°	233.1	255.6	274.3	288.7	298.2	304.0	305.7
132.5°	225.8	246.1	264.2	278.6	288.0	293.3	295.3
135°	214.3	232.8	249.2	262.0	271.4	276.6	278.3
137.5°	204.2	219.6	233.5	244.8	253.5	258.3	260.2
140°	198.2	211.5	223.6	234.2	241.7	246.1	247.5
142.5°	193.1	204.6	215.1	224.1	230.5	234.6	235.8
145°	186.7	195.7	203.4	210.3	215.2	218.4	219.6
147.5°	181.3	188.3	194.1	199.6	203.5	205.3	205.9
150°	178.4	183.8	189.0	193.3	196.8	198.0	198.2
152.5°	175.4	180.3	184.4	188.0	190.8	191.9	192.2
155°	170.9	174.9	178.1	180.9	183.0	183.8	184.1
157.5°	166.6	169.7	172.2	174.5	176.1	176.9	176.8
160°	163.4	166.2	168.3	170.3	171.7	172.3	172.0
162.5°	160.6	163.1	164.9	166.4	167.5	167.7	167.6
165°	156.5	158.2	159.6	160.8	161.3	161.3	161.3
167.5°	152.5	153.8	154.8	155.4	155.9	155.6	155.6
170°	150.1	151.0	151.6	152.1	152.5	152.5	152.1
172.5°	148.1	148.7	149.0	149.1	149.7	149.2	148.9
175°	145.0	145.5	145.5	145.5	145.8	145.2	145.0
177.5°	143.6	143.6	143.6	143.4	143.6	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9

(END OF REPORT)