

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333144-930

Luminaire Tested: **S125DIP-S375D1035U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333144-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D1035U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4282.0 lumens  
Efficiency: N/A  
Efficacy: 114.8 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	32	25
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	47	36	28	24	42	32	26	22	26	21	18	20	17	14	15	12	11	8
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2866	2866	2866	2866
5°	3319	2877	2519	2877
10°	3862	2861	2207	2861
15°	4275	2841	2035	2841
20°	4786	2808	1898	2808
25°	5606	2770	1831	2770
30°	6055	2732	1773	2732
35°	4978	2663	1735	2663
40°	3538	2566	1693	2566
45°	2719	2437	1669	2437
50°	2321	2275	1666	2275
55°	2066	2117	1680	2117
60°	1864	1944	1723	1944
65°	1722	1771	1768	1771
70°	1565	1590	1794	1590
75°	1382	1402	1777	1402
80°	1164	1142	1625	1142
85°	926	823	1312	823



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	1.0
10°-20°	127.2	3.0
20°-30°	206.6	4.8
30°-40°	252.0	5.9
40°-50°	229.2	5.4
50°-60°	182.6	4.3
60°-70°	127.2	3.0
70°-80°	67.8	1.6
80°-90°	19.4	0.5
90°-100°	292.6	6.8
100°-110°	629.0	14.7
110°-120°	590.3	13.8
120°-130°	478.4	11.2
130°-140°	383.9	9.0
140°-150°	289.7	6.8
150°-160°	203.9	4.8
160°-170°	120.2	2.8
170°-180°	39.1	0.9
0°-30°	376.5	8.8
0°-40°	628.5	14.7
0°-60°	1040.3	24.3
0°-90°	1254.7	29.3
90°-120°	1512.0	35.3
90°-150°	2664.1	62.2
90°-180°	3027.0	70.7
0°-180°	4282.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	512	444	388	444	512	52
15°	639	425	304	425	639	183
25°	787	389	257	389	787	359
35°	631	338	220	338	631	386
45°	298	267	183	267	298	238
55°	184	188	149	188	184	165
65°	113	116	116	116	113	112
75°	55	56	71	56	55	60
85°	12	11	18	11	12	15
90°	19	1	19	1	19	13
95°	191	27	191	27	191	271
105°	1078	92	1078	92	1078	1072
115°	1201	164	1201	164	1201	1174
125°	947	228	947	228	947	856
135°	786	267	786	267	786	609
145°	620	311	620	311	620	394
155°	520	355	520	355	520	242
165°	456	387	456	387	456	130
175°	409	403	409	403	409	40
180°	404	404	404	404	404	



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	469.4	468.9	468.2	467.1	468.0	465.4	464.2	462.1	459.5	458.6	457.5
5°	512.0	513.0	514.0	510.0	510.4	507.7	501.7	496.8	492.8	487.7	484.1
7.5°	563.3	561.1	560.8	558.3	553.9	550.3	544.0	536.0	528.2	519.3	511.9
10°	588.9	589.1	587.4	584.4	579.7	576.3	568.0	560.1	550.5	539.2	531.1
12.5°	608.2	609.0	606.8	602.8	600.5	592.9	586.4	577.0	565.6	556.5	544.2
15°	639.4	637.3	635.9	630.7	626.8	618.9	608.5	598.7	586.3	574.8	563.3
17.5°	669.4	671.2	668.3	663.7	651.3	642.1	628.3	614.8	599.3	583.9	570.2
20°	696.3	697.8	693.5	685.3	670.7	661.5	643.2	625.8	608.0	588.2	573.1
22.5°	729.8	728.6	722.7	710.4	697.7	680.6	660.8	639.7	617.3	594.9	574.9
25°	786.7	778.8	775.2	759.9	743.2	718.1	691.0	660.1	632.3	602.7	577.1
27.5°	818.3	815.8	811.8	801.2	783.6	756.8	724.8	687.1	647.8	610.5	576.9
30°	812.0	812.4	812.7	809.3	798.0	777.9	746.0	705.6	658.8	616.8	578.0
32.5°	755.9	762.7	769.3	777.1	780.2	776.3	756.4	719.8	671.7	624.0	577.4
35°	631.4	633.6	654.8	676.0	704.6	726.8	741.7	725.5	685.0	630.1	576.7
37.5°	492.4	502.6	517.3	541.1	582.4	619.5	667.1	688.9	675.9	632.2	575.4
40°	419.7	429.2	438.8	463.1	497.9	542.7	596.8	642.9	653.7	625.8	570.8
42.5°	363.7	371.1	381.8	400.1	429.2	468.9	520.6	580.9	618.0	607.5	561.3
45°	297.7	302.4	310.6	325.1	346.3	377.3	422.9	488.9	546.3	565.3	538.8
47.5°	254.8	254.8	261.2	271.2	286.4	312.8	346.6	398.2	459.6	505.0	502.9
50°	231.0	230.0	235.1	243.8	255.8	273.4	305.6	346.8	405.8	457.2	471.6
52.5°	210.4	210.6	213.7	220.1	230.2	245.2	269.2	306.5	356.8	409.6	436.6
55°	183.5	182.7	186.3	190.6	198.0	207.8	225.1	253.6	294.5	346.4	381.5
57.5°	158.7	160.9	162.2	165.3	171.4	178.0	192.6	213.4	245.9	290.5	327.5
60°	144.3	146.3	147.5	150.5	155.4	161.1	172.4	189.3	216.6	255.1	291.8
62.5°	131.3	133.0	133.4	136.1	140.1	145.5	154.4	168.7	190.3	223.9	259.8
65°	112.7	112.7	113.4	116.3	118.1	123.0	129.8	140.1	157.5	183.7	214.4
67.5°	94.7	95.6	95.4	96.6	98.3	102.2	107.0	115.5	128.4	147.5	172.1
70°	82.9	83.6	83.5	84.4	86.3	88.7	92.7	100.8	110.0	126.4	147.5
72.5°	72.3	72.6	72.2	73.4	74.5	76.6	81.1	85.4	94.0	107.9	125.2
75°	55.4	55.8	56.2	56.9	58.0	59.2	61.4	65.7	71.4	81.8	92.9
77.5°	41.5	40.8	41.7	41.6	42.2	43.1	45.1	47.4	52.0	58.6	67.2
80°	31.3	31.5	31.5	31.6	32.6	33.2	34.8	36.5	40.1	45.0	51.0
82.5°	22.8	23.3	23.0	23.4	24.1	24.5	25.5	26.9	28.9	32.9	37.2
85°	12.5	11.5	11.9	12.2	12.2	12.5	13.2	13.8	14.9	16.4	18.1
87.5°	7.3	7.7	7.7	7.7	7.8	7.5	7.9	7.7	8.1	8.3	8.6
90°	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7	13.9	13.0	11.4
92.5°	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2	212.4	262.4	266.6
95°	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2	705.6	721.1	588.5
97.5°	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6	892.8	770.1	525.5
100°	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1	938.4	734.9	468.8
102.5°	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7	911.1	673.1	425.8
105°	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0	823.7	590.0	384.2
107.5°	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2	734.4	533.0	366.6
110°	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5	683.6	506.2	361.3



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1	645.9	490.6	361.3
115°	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0	604.7	473.7	363.8
117.5°	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7	580.2	465.4	369.2
120°	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3	566.5	461.5	374.4
122.5°	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7	554.7	458.2	379.0
125°	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2	538.8	454.1	386.6
127.5°	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1	524.2	452.2	395.3
130°	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9	514.4	450.9	400.5
132.5°	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5	506.5	450.9	406.3
135°	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3	497.3	450.9	414.3
137.5°	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5	489.0	451.8	421.6
140°	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7	485.1	452.5	424.9
142.5°	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2	481.8	453.1	426.8
145°	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1	477.0	452.5	428.9
147.5°	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8	471.9	450.4	429.7
150°	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9	468.0	448.4	429.7
152.5°	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4	463.4	445.9	429.1
155°	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6	455.8	441.2	427.3
157.5°	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8	448.6	436.3	425.2
160°	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3	442.8	433.0	423.2
162.5°	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2	437.6	429.1	421.3
165°	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3	429.7	423.2	418.3
167.5°	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8	422.1	417.5	413.8
170°	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6	417.5	414.3	411.8
172.5°	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7	412.9	410.3	409.2
175°	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4	406.9	406.1	406.1
177.5°	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0	404.3	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	456.6	455.6	454.4	452.2	449.7	448.3	446.3	444.9	442.2	439.9	437.5
5°	479.8	474.9	470.4	464.6	458.2	454.0	449.1	443.7	438.0	432.2	425.7
7.5°	503.9	495.1	485.8	475.6	465.7	456.6	447.8	439.4	431.4	421.7	413.5
10°	519.9	509.0	497.3	483.6	470.2	458.5	446.7	436.3	425.7	414.5	404.5
12.5°	536.1	521.5	505.0	489.9	473.9	459.7	445.8	432.5	419.3	406.8	395.1
15°	547.5	534.7	519.4	497.9	479.8	460.4	442.0	424.9	408.8	394.8	380.2
17.5°	555.0	538.4	522.0	501.5	477.8	456.1	435.1	415.5	397.5	379.8	365.7
20°	556.3	539.3	522.2	502.1	477.8	452.9	431.9	408.5	389.1	370.7	353.4
22.5°	555.9	536.6	518.0	497.3	473.5	450.6	425.3	401.4	380.3	362.3	344.2
25°	551.6	531.1	507.7	486.8	463.4	439.1	413.5	388.7	367.2	346.7	328.7
27.5°	548.0	521.5	495.0	470.6	448.0	425.7	401.2	375.8	352.0	331.2	314.3
30°	543.7	514.5	484.7	459.3	436.1	414.5	391.3	366.4	341.5	321.2	303.1
32.5°	539.8	505.7	474.3	446.6	422.1	401.0	379.7	356.0	331.6	311.0	292.9
35°	532.2	492.8	456.8	425.6	399.4	377.7	359.8	337.8	315.4	295.4	278.1
37.5°	522.6	475.9	437.2	404.5	375.8	352.9	336.3	319.4	297.8	278.6	262.9
40°	515.0	463.8	422.9	389.4	359.6	335.9	320.4	304.4	286.6	268.6	252.1
42.5°	505.6	453.0	408.5	372.3	342.9	319.8	303.5	290.0	274.2	257.5	242.1
45°	488.1	433.3	385.1	346.3	316.5	293.7	277.0	266.8	254.9	239.0	226.1
47.5°	462.4	409.7	359.8	319.8	289.0	267.9	252.2	242.4	234.1	222.3	210.5
50°	439.7	392.1	341.5	301.8	271.1	249.8	235.3	226.4	219.3	210.3	200.2
52.5°	414.3	369.9	323.6	284.3	253.9	232.9	218.7	210.9	205.0	198.5	188.7
55°	373.7	336.1	293.1	255.8	227.8	207.2	194.8	188.0	183.1	178.2	172.2
57.5°	329.2	299.7	261.7	227.6	201.7	183.0	171.5	164.9	161.0	158.5	155.0
60°	297.8	272.6	239.9	208.7	183.5	166.9	155.6	150.5	147.3	145.3	142.6
62.5°	268.7	248.0	217.7	189.3	167.2	151.6	141.5	136.5	133.5	132.4	130.3
65°	225.9	209.9	184.8	161.3	142.4	129.1	120.6	115.9	114.0	112.8	113.0
67.5°	183.6	173.9	153.8	133.7	118.6	107.5	100.6	97.0	96.0	94.6	94.6
70°	157.8	150.5	133.5	116.0	102.6	94.0	88.0	84.2	83.2	82.5	82.3
72.5°	135.1	128.7	114.0	100.0	87.9	80.3	75.3	73.1	71.5	71.1	71.0
75°	101.5	98.0	86.3	75.2	66.9	61.6	58.2	56.2	55.0	54.8	55.0
77.5°	72.2	69.1	61.6	53.7	48.5	44.5	41.7	40.9	39.7	39.7	39.5
80°	54.2	52.2	47.5	41.3	36.9	33.5	32.0	30.7	30.3	29.8	30.3
82.5°	39.3	37.1	33.9	29.9	26.3	24.4	22.8	22.4	22.2	21.9	22.0
85°	19.4	19.6	17.7	14.7	13.2	12.1	11.1	11.1	10.9	10.8	10.9
87.5°	8.7	8.2	7.3	6.6	5.5	4.7	4.2	4.2	3.9	4.2	4.6
90°	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8	1.6	3.3	4.9
92.5°	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9	12.1	18.9	28.9
95°	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8	27.6	34.2	43.1
97.5°	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6	45.6	50.1	59.1
100°	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0	58.6	61.9	70.8
102.5°	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7	71.6	74.2	83.8
105°	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0	92.0	96.0	104.2
107.5°	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8	114.5	118.3	125.0
110°	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8	129.4	132.6	140.0





TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8	144.4	147.0	154.3
115°	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4	166.0	168.4	175.8
117.5°	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9	186.4	189.0	196.3
120°	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0	199.4	202.7	210.0
122.5°	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7	212.4	215.0	222.3
125°	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9	229.5	233.6	240.9
127.5°	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4	243.9	249.1	258.4
130°	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9	252.3	258.9	269.4
132.5°	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4	259.4	267.3	279.2
135°	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9	270.2	280.0	293.0
137.5°	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3	282.7	291.9	304.9
140°	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1	290.6	300.4	313.3
142.5°	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3	299.1	308.1	321.1
145°	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9	312.5	320.7	332.1
147.5°	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2	326.2	333.2	343.8
150°	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7	335.3	341.0	351.6
152.5°	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8	343.8	348.9	358.1
155°	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8	354.8	359.7	367.9
157.5°	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6	365.4	369.3	376.3
160°	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8	371.9	375.2	380.9
162.5°	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6	377.8	381.1	386.1
165°	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4	385.8	388.2	392.3
167.5°	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3	392.5	394.0	396.2
170°	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2	396.4	397.2	398.8
172.5°	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8	398.4	399.2	400.7
175°	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8	401.2	402.0	402.8
177.5°	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3	403.0	403.0	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	436.2	434.5	433.2	430.2	428.4	426.2	424.4	426.4	424.3	425.2	423.8
5°	422.6	417.3	413.5	408.1	403.3	399.0	395.8	395.3	393.7	393.0	390.7
7.5°	406.2	399.6	393.1	386.0	379.9	373.8	369.9	366.6	364.5	361.7	359.7
10°	396.6	387.7	380.2	371.5	363.9	357.3	352.1	349.4	347.0	343.4	342.1
12.5°	384.7	375.5	366.3	357.0	349.8	342.4	337.9	333.9	332.2	328.2	327.8
15°	370.4	356.6	347.6	338.2	328.2	322.1	318.4	314.1	312.2	309.3	307.3
17.5°	353.4	341.0	329.8	320.0	311.4	306.4	301.7	298.7	295.5	293.6	290.2
20°	341.0	329.3	318.0	307.6	301.0	295.2	291.5	288.6	285.2	284.3	280.9
22.5°	330.6	317.7	306.9	298.2	291.0	284.4	280.3	278.3	276.1	273.1	272.5
25°	313.6	300.3	291.1	282.4	276.0	269.9	267.2	264.7	262.4	260.3	259.6
27.5°	299.1	287.1	276.1	268.3	262.7	257.2	254.8	251.8	250.1	248.4	246.4
30°	288.8	276.5	266.9	259.4	253.4	248.5	245.8	243.8	242.3	240.8	239.6
32.5°	278.3	266.9	257.6	250.2	244.2	240.5	238.1	236.7	235.1	233.3	231.8
35°	264.3	251.8	242.8	236.4	231.7	228.9	226.2	224.9	223.1	223.1	221.5
37.5°	248.6	237.8	229.8	224.0	219.8	217.3	214.4	213.5	212.3	211.5	211.0
40°	239.3	229.3	221.8	215.9	211.4	209.3	207.0	205.5	204.8	203.8	203.5
42.5°	229.6	220.0	212.9	207.5	203.5	201.8	199.7	198.6	197.1	195.8	195.6
45°	214.9	205.7	199.1	194.8	191.4	189.3	188.0	185.7	185.0	183.5	183.3
47.5°	201.1	192.2	185.7	182.1	179.2	177.5	175.5	173.2	172.3	171.5	171.5
50°	190.6	182.5	176.5	173.2	170.3	167.9	165.8	164.3	163.7	163.7	164.1
52.5°	180.1	173.2	168.1	164.0	161.3	158.7	156.7	155.8	155.0	155.9	156.5
55°	164.7	157.7	153.9	149.9	147.3	144.3	143.3	143.0	142.4	143.9	144.7
57.5°	148.3	143.4	139.0	135.1	132.7	130.9	129.7	129.5	130.5	131.3	133.7
60°	137.9	132.2	128.3	125.3	122.5	121.3	120.9	120.6	121.3	123.4	126.6
62.5°	126.5	121.9	117.6	115.4	113.2	111.4	111.3	111.5	113.0	115.4	118.6
65°	109.7	105.7	102.9	100.2	98.5	97.4	97.8	98.5	100.2	103.5	107.0
67.5°	92.5	89.8	87.3	85.2	83.6	83.6	84.0	85.1	87.1	90.7	94.0
70°	81.6	78.6	76.5	75.6	74.2	73.5	74.6	76.5	78.2	81.6	84.4
72.5°	70.6	68.0	66.4	65.7	65.1	64.6	65.0	67.0	69.3	72.6	76.0
75°	54.2	53.3	52.2	51.4	50.9	51.3	51.6	53.5	55.4	58.9	62.7
77.5°	39.6	38.6	37.9	37.7	37.4	37.7	38.7	40.1	41.9	44.5	47.4
80°	29.9	29.6	29.2	29.0	29.0	29.2	30.7	31.6	33.3	35.8	38.1
82.5°	21.9	21.6	21.5	21.4	21.6	21.7	22.6	23.8	25.2	27.1	29.0
85°	11.5	11.1	11.7	11.9	11.5	12.1	12.5	13.2	13.8	14.7	15.7
87.5°	5.1	5.7	5.7	6.2	6.4	7.0	7.0	7.7	8.2	8.6	8.9
90°	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7	15.5	16.3	17.9
92.5°	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2	104.7	78.8	66.8
95°	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2	461.5	361.3	293.0
97.5°	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6	784.7	687.2	592.2
100°	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1	961.2	877.3	792.7
102.5°	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7	1069.3	1029.1	971.8
105°	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0	1130.5	1166.3	1157.3
107.5°	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2	1076.0	1167.9	1210.4
110°	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5	1014.1	1128.9	1198.1



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1	952.9	1068.9	1150.6
115°	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0	865.2	976.6	1065.4
117.5°	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7	804.5	900.5	981.9
120°	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3	770.0	859.5	931.1
122.5°	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7	745.2	824.9	892.0
125°	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2	712.2	782.9	841.6
127.5°	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1	680.6	746.7	801.5
130°	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9	658.4	721.9	774.9
132.5°	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5	637.6	695.2	746.2
135°	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3	605.5	657.6	704.0
137.5°	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5	576.9	620.2	659.6
140°	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7	559.9	597.4	631.6
142.5°	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2	545.6	577.9	607.5
145°	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1	527.4	552.6	574.6
147.5°	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8	512.3	531.7	548.2
150°	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9	503.8	519.3	533.9
152.5°	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4	495.3	509.5	520.9
155°	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6	482.7	494.1	503.0
157.5°	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8	470.6	479.4	486.4
160°	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3	461.5	469.6	475.3
162.5°	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2	453.6	460.5	465.5
165°	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3	442.0	446.9	450.9
167.5°	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8	430.6	434.3	437.2
170°	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6	424.0	426.5	428.1
172.5°	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7	418.2	420.0	420.9
175°	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4	409.4	411.0	411.0
177.5°	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0	405.6	405.6	405.6
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	422.9	424.0	423.1	424.3	423.1	424.0	422.9	423.8	425.2	424.3	426.4
5°	389.8	388.1	389.2	388.5	389.2	388.1	389.8	390.7	393.0	393.7	395.3
7.5°	359.2	357.6	355.7	354.8	355.7	357.6	359.2	359.7	361.7	364.5	366.6
10°	340.1	337.9	337.8	336.5	337.8	337.9	340.1	342.1	343.4	347.0	349.4
12.5°	326.0	324.1	322.0	321.4	322.0	324.1	326.0	327.8	328.2	332.2	333.9
15°	306.1	304.6	303.3	304.4	303.3	304.6	306.1	307.3	309.3	312.2	314.1
17.5°	289.6	288.4	288.1	286.7	288.1	288.4	289.6	290.2	293.6	295.5	298.7
20°	279.2	278.3	278.7	276.1	278.7	278.3	279.2	280.9	284.3	285.2	288.6
22.5°	270.9	269.0	268.8	268.3	268.8	269.0	270.9	272.5	273.1	276.1	278.3
25°	257.9	257.0	256.0	257.0	256.0	257.0	257.9	259.6	260.3	262.4	264.7
27.5°	246.5	245.4	245.2	245.3	245.2	245.4	246.5	246.4	248.4	250.1	251.8
30°	239.6	237.7	237.9	237.7	237.9	237.7	239.6	239.6	240.8	242.3	243.8
32.5°	232.1	230.8	230.6	230.2	230.6	230.8	232.1	231.8	233.3	235.1	236.7
35°	220.9	220.9	220.0	220.0	220.0	220.9	220.9	221.5	223.1	223.1	224.9
37.5°	210.5	210.3	209.8	209.9	209.8	210.3	210.5	211.0	211.5	212.3	213.5
40°	202.7	202.5	201.9	200.8	201.9	202.5	202.7	203.5	203.8	204.8	205.5
42.5°	195.2	194.5	194.3	193.9	194.3	194.5	195.2	195.6	195.8	197.1	198.6
45°	183.3	183.3	183.0	182.7	183.0	183.3	183.3	183.3	183.5	185.0	185.7
47.5°	171.8	172.1	172.8	172.7	172.8	172.1	171.8	171.5	171.5	172.3	173.2
50°	164.9	165.0	165.6	165.8	165.6	165.0	164.9	164.1	163.7	163.7	164.3
52.5°	157.2	158.2	159.0	158.8	159.0	158.2	157.2	156.5	155.9	155.0	155.8
55°	146.3	147.7	149.0	149.2	149.0	147.7	146.3	144.7	143.9	142.4	143.0
57.5°	135.7	137.5	138.9	139.4	138.9	137.5	135.7	133.7	131.3	130.5	129.5
60°	128.5	130.9	132.6	133.4	132.6	130.9	128.5	126.6	123.4	121.3	120.6
62.5°	121.6	124.3	126.0	126.1	126.0	124.3	121.6	118.6	115.4	113.0	111.5
65°	110.2	113.0	114.5	115.7	114.5	113.0	110.2	107.0	103.5	100.2	98.5
67.5°	98.0	100.9	102.5	103.4	102.5	100.9	98.0	94.0	90.7	87.1	85.1
70°	89.1	92.0	94.2	95.0	94.2	92.0	89.1	84.4	81.6	78.2	76.5
72.5°	80.4	82.9	84.7	85.6	84.7	82.9	80.4	76.0	72.6	69.3	67.0
75°	65.1	68.6	70.3	71.2	70.3	68.6	65.1	62.7	58.9	55.4	53.5
77.5°	50.2	53.3	54.4	54.9	54.4	53.3	50.2	47.4	44.5	41.9	40.1
80°	40.3	42.2	43.5	43.7	43.5	42.2	40.3	38.1	35.8	33.3	31.6
82.5°	31.0	32.5	32.9	33.4	32.9	32.5	31.0	29.0	27.1	25.2	23.8
85°	17.0	17.7	17.9	17.7	17.9	17.7	17.0	15.7	14.7	13.8	13.2
87.5°	9.1	9.0	9.1	9.5	9.1	9.0	9.1	8.9	8.6	8.2	7.7
90°	17.9	17.9	18.8	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7
92.5°	56.3	54.4	53.2	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2
95°	235.2	210.8	204.3	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2
97.5°	541.9	496.3	472.7	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6
100°	736.5	678.0	647.8	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1
102.5°	911.7	870.1	837.3	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7
105°	1131.3	1104.5	1088.2	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0
107.5°	1223.6	1223.4	1218.1	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2
110°	1234.7	1250.1	1255.8	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1204.0	1230.6	1244.8	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1
115°	1128.9	1167.9	1190.7	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0
117.5°	1045.4	1085.7	1108.3	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7
120°	991.3	1030.4	1052.4	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3
122.5°	945.7	981.5	1003.6	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7
125°	887.1	920.5	938.4	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2
127.5°	842.9	872.3	889.2	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1
130°	815.5	842.4	858.7	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9
132.5°	786.8	813.8	828.7	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5
135°	739.8	766.7	781.3	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3
137.5°	691.6	716.1	729.6	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5
140°	661.7	682.9	695.0	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7
142.5°	633.1	650.9	662.5	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2
145°	594.1	608.0	616.9	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1
147.5°	563.7	574.8	580.0	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8
150°	546.1	555.9	559.1	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9
152.5°	531.2	539.0	542.2	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4
155°	511.1	516.8	519.3	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6
157.5°	492.8	497.4	499.7	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8
160°	481.0	485.1	486.7	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3
162.5°	469.9	473.4	473.7	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2
165°	454.1	455.8	455.8	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3
167.5°	438.9	440.3	439.7	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8
170°	429.7	430.6	430.6	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6
172.5°	421.3	422.7	421.4	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7
175°	411.0	411.8	410.2	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4
177.5°	405.0	405.6	403.7	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	424.4	426.2	428.4	430.2	433.2	434.5	436.2	437.5	439.9	442.2	444.9
5°	395.8	399.0	403.3	408.1	413.5	417.3	422.6	425.7	432.2	438.0	443.7
7.5°	369.9	373.8	379.9	386.0	393.1	399.6	406.2	413.5	421.7	431.4	439.4
10°	352.1	357.3	363.9	371.5	380.2	387.7	396.6	404.5	414.5	425.7	436.3
12.5°	337.9	342.4	349.8	357.0	366.3	375.5	384.7	395.1	406.8	419.3	432.5
15°	318.4	322.1	328.2	338.2	347.6	356.6	370.4	380.2	394.8	408.8	424.9
17.5°	301.7	306.4	311.4	320.0	329.8	341.0	353.4	365.7	379.8	397.5	415.5
20°	291.5	295.2	301.0	307.6	318.0	329.3	341.0	353.4	370.7	389.1	408.5
22.5°	280.3	284.4	291.0	298.2	306.9	317.7	330.6	344.2	362.3	380.3	401.4
25°	267.2	269.9	276.0	282.4	291.1	300.3	313.6	328.7	346.7	367.2	388.7
27.5°	254.8	257.2	262.7	268.3	276.1	287.1	299.1	314.3	331.2	352.0	375.8
30°	245.8	248.5	253.4	259.4	266.9	276.5	288.8	303.1	321.2	341.5	366.4
32.5°	238.1	240.5	244.2	250.2	257.6	266.9	278.3	292.9	311.0	331.6	356.0
35°	226.2	228.9	231.7	236.4	242.8	251.8	264.3	278.1	295.4	315.4	337.8
37.5°	214.4	217.3	219.8	224.0	229.8	237.8	248.6	262.9	278.6	297.8	319.4
40°	207.0	209.3	211.4	215.9	221.8	229.3	239.3	252.1	268.6	286.6	304.4
42.5°	199.7	201.8	203.5	207.5	212.9	220.0	229.6	242.1	257.5	274.2	290.0
45°	188.0	189.3	191.4	194.8	199.1	205.7	214.9	226.1	239.0	254.9	266.8
47.5°	175.5	177.5	179.2	182.1	185.7	192.2	201.1	210.5	222.3	234.1	242.4
50°	165.8	167.9	170.3	173.2	176.5	182.5	190.6	200.2	210.3	219.3	226.4
52.5°	156.7	158.7	161.3	164.0	168.1	173.2	180.1	188.7	198.5	205.0	210.9
55°	143.3	144.3	147.3	149.9	153.9	157.7	164.7	172.2	178.2	183.1	188.0
57.5°	129.7	130.9	132.7	135.1	139.0	143.4	148.3	155.0	158.5	161.0	164.9
60°	120.9	121.3	122.5	125.3	128.3	132.2	137.9	142.6	145.3	147.3	150.5
62.5°	111.3	111.4	113.2	115.4	117.6	121.9	126.5	130.3	132.4	133.5	136.5
65°	97.8	97.4	98.5	100.2	102.9	105.7	109.7	113.0	112.8	114.0	115.9
67.5°	84.0	83.6	83.6	85.2	87.3	89.8	92.5	94.6	94.6	96.0	97.0
70°	74.6	73.5	74.2	75.6	76.5	78.6	81.6	82.3	82.5	83.2	84.2
72.5°	65.0	64.6	65.1	65.7	66.4	68.0	70.6	71.0	71.1	71.5	73.1
75°	51.6	51.3	50.9	51.4	52.2	53.3	54.2	55.0	54.8	55.0	56.2
77.5°	38.7	37.7	37.4	37.7	37.9	38.6	39.6	39.5	39.7	39.7	40.9
80°	30.7	29.2	29.0	29.0	29.2	29.6	29.9	30.3	29.8	30.3	30.7
82.5°	22.6	21.7	21.6	21.4	21.5	21.6	21.9	22.0	21.9	22.2	22.4
85°	12.5	12.1	11.5	11.9	11.7	11.1	11.5	10.9	10.8	10.9	11.1
87.5°	7.0	7.0	6.4	6.2	5.7	5.7	5.1	4.6	4.2	3.9	4.2
90°	13.9	13.0	11.4	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8
92.5°	212.4	262.4	266.6	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9
95°	705.6	721.1	588.5	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8
97.5°	892.8	770.1	525.5	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6
100°	938.4	734.9	468.8	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0
102.5°	911.1	673.1	425.8	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7
105°	823.7	590.0	384.2	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0
107.5°	734.4	533.0	366.6	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8
110°	683.6	506.2	361.3	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.9	490.6	361.3	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8
115°	604.7	473.7	363.8	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4
117.5°	580.2	465.4	369.2	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9
120°	566.5	461.5	374.4	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0
122.5°	554.7	458.2	379.0	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7
125°	538.8	454.1	386.6	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9
127.5°	524.2	452.2	395.3	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4
130°	514.4	450.9	400.5	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9
132.5°	506.5	450.9	406.3	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4
135°	497.3	450.9	414.3	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9
137.5°	489.0	451.8	421.6	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3
140°	485.1	452.5	424.9	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1
142.5°	481.8	453.1	426.8	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3
145°	477.0	452.5	428.9	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9
147.5°	471.9	450.4	429.7	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2
150°	468.0	448.4	429.7	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7
152.5°	463.4	445.9	429.1	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8
155°	455.8	441.2	427.3	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8
157.5°	448.6	436.3	425.2	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6
160°	442.8	433.0	423.2	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8
162.5°	437.6	429.1	421.3	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6
165°	429.7	423.2	418.3	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4
167.5°	422.1	417.5	413.8	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3
170°	417.5	414.3	411.8	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2
172.5°	412.9	410.3	409.2	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8
175°	406.9	406.1	406.1	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8
177.5°	404.3	403.7	403.7	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	446.3	448.3	449.7	452.2	454.4	455.6	456.6	457.5	458.6	459.5	462.1
5°	449.1	454.0	458.2	464.6	470.4	474.9	479.8	484.1	487.7	492.8	496.8
7.5°	447.8	456.6	465.7	475.6	485.8	495.1	503.9	511.9	519.3	528.2	536.0
10°	446.7	458.5	470.2	483.6	497.3	509.0	519.9	531.1	539.2	550.5	560.1
12.5°	445.8	459.7	473.9	489.9	505.0	521.5	536.1	544.2	556.5	565.6	577.0
15°	442.0	460.4	479.8	497.9	519.4	534.7	547.5	563.3	574.8	586.3	598.7
17.5°	435.1	456.1	477.8	501.5	522.0	538.4	555.0	570.2	583.9	599.3	614.8
20°	431.9	452.9	477.8	502.1	522.2	539.3	556.3	573.1	588.2	608.0	625.8
22.5°	425.3	450.6	473.5	497.3	518.0	536.6	555.9	574.9	594.9	617.3	639.7
25°	413.5	439.1	463.4	486.8	507.7	531.1	551.6	577.1	602.7	632.3	660.1
27.5°	401.2	425.7	448.0	470.6	495.0	521.5	548.0	576.9	610.5	647.8	687.1
30°	391.3	414.5	436.1	459.3	484.7	514.5	543.7	578.0	616.8	658.8	705.6
32.5°	379.7	401.0	422.1	446.6	474.3	505.7	539.8	577.4	624.0	671.7	719.8
35°	359.8	377.7	399.4	425.6	456.8	492.8	532.2	576.7	630.1	685.0	725.5
37.5°	336.3	352.9	375.8	404.5	437.2	475.9	522.6	575.4	632.2	675.9	688.9
40°	320.4	335.9	359.6	389.4	422.9	463.8	515.0	570.8	625.8	653.7	642.9
42.5°	303.5	319.8	342.9	372.3	408.5	453.0	505.6	561.3	607.5	618.0	580.9
45°	277.0	293.7	316.5	346.3	385.1	433.3	488.1	538.8	565.3	546.3	488.9
47.5°	252.2	267.9	289.0	319.8	359.8	409.7	462.4	502.9	505.0	459.6	398.2
50°	235.3	249.8	271.1	301.8	341.5	392.1	439.7	471.6	457.2	405.8	346.8
52.5°	218.7	232.9	253.9	284.3	323.6	369.9	414.3	436.6	409.6	356.8	306.5
55°	194.8	207.2	227.8	255.8	293.1	336.1	373.7	381.5	346.4	294.5	253.6
57.5°	171.5	183.0	201.7	227.6	261.7	299.7	329.2	327.5	290.5	245.9	213.4
60°	155.6	166.9	183.5	208.7	239.9	272.6	297.8	291.8	255.1	216.6	189.3
62.5°	141.5	151.6	167.2	189.3	217.7	248.0	268.7	259.8	223.9	190.3	168.7
65°	120.6	129.1	142.4	161.3	184.8	209.9	225.9	214.4	183.7	157.5	140.1
67.5°	100.6	107.5	118.6	133.7	153.8	173.9	183.6	172.1	147.5	128.4	115.5
70°	88.0	94.0	102.6	116.0	133.5	150.5	157.8	147.5	126.4	110.0	100.8
72.5°	75.3	80.3	87.9	100.0	114.0	128.7	135.1	125.2	107.9	94.0	85.4
75°	58.2	61.6	66.9	75.2	86.3	98.0	101.5	92.9	81.8	71.4	65.7
77.5°	41.7	44.5	48.5	53.7	61.6	69.1	72.2	67.2	58.6	52.0	47.4
80°	32.0	33.5	36.9	41.3	47.5	52.2	54.2	51.0	45.0	40.1	36.5
82.5°	22.8	24.4	26.3	29.9	33.9	37.1	39.3	37.2	32.9	28.9	26.9
85°	11.1	12.1	13.2	14.7	17.7	19.6	19.4	18.1	16.4	14.9	13.8
87.5°	4.2	4.7	5.5	6.6	7.3	8.2	8.7	8.6	8.3	8.1	7.7
90°	1.6	3.3	4.9	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7
92.5°	12.1	18.9	28.9	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2
95°	27.6	34.2	43.1	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2
97.5°	45.6	50.1	59.1	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6
100°	58.6	61.9	70.8	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1
102.5°	71.6	74.2	83.8	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7
105°	92.0	96.0	104.2	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0
107.5°	114.5	118.3	125.0	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2
110°	129.4	132.6	140.0	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5





TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	147.0	154.3	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1
115°	166.0	168.4	175.8	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0
117.5°	186.4	189.0	196.3	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7
120°	199.4	202.7	210.0	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3
122.5°	212.4	215.0	222.3	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7
125°	229.5	233.6	240.9	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2
127.5°	243.9	249.1	258.4	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1
130°	252.3	258.9	269.4	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9
132.5°	259.4	267.3	279.2	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5
135°	270.2	280.0	293.0	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3
137.5°	282.7	291.9	304.9	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5
140°	290.6	300.4	313.3	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7
142.5°	299.1	308.1	321.1	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2
145°	312.5	320.7	332.1	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1
147.5°	326.2	333.2	343.8	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8
150°	335.3	341.0	351.6	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9
152.5°	343.8	348.9	358.1	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4
155°	354.8	359.7	367.9	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6
157.5°	365.4	369.3	376.3	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8
160°	371.9	375.2	380.9	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3
162.5°	377.8	381.1	386.1	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2
165°	385.8	388.2	392.3	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3
167.5°	392.5	394.0	396.2	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8
170°	396.4	397.2	398.8	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6
172.5°	398.4	399.2	400.7	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7
175°	401.2	402.0	402.8	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4
177.5°	403.0	403.0	403.7	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	464.2	465.4	468.0	467.1	468.2	468.9	469.4
5°	501.7	507.7	510.4	510.0	514.0	513.0	512.0
7.5°	544.0	550.3	553.9	558.3	560.8	561.1	563.3
10°	568.0	576.3	579.7	584.4	587.4	589.1	588.9
12.5°	586.4	592.9	600.5	602.8	606.8	609.0	608.2
15°	608.5	618.9	626.8	630.7	635.9	637.3	639.4
17.5°	628.3	642.1	651.3	663.7	668.3	671.2	669.4
20°	643.2	661.5	670.7	685.3	693.5	697.8	696.3
22.5°	660.8	680.6	697.7	710.4	722.7	728.6	729.8
25°	691.0	718.1	743.2	759.9	775.2	778.8	786.7
27.5°	724.8	756.8	783.6	801.2	811.8	815.8	818.3
30°	746.0	777.9	798.0	809.3	812.7	812.4	812.0
32.5°	756.4	776.3	780.2	777.1	769.3	762.7	755.9
35°	741.7	726.8	704.6	676.0	654.8	633.6	631.4
37.5°	667.1	619.5	582.4	541.1	517.3	502.6	492.4
40°	596.8	542.7	497.9	463.1	438.8	429.2	419.7
42.5°	520.6	468.9	429.2	400.1	381.8	371.1	363.7
45°	422.9	377.3	346.3	325.1	310.6	302.4	297.7
47.5°	346.6	312.8	286.4	271.2	261.2	254.8	254.8
50°	305.6	273.4	255.8	243.8	235.1	230.0	231.0
52.5°	269.2	245.2	230.2	220.1	213.7	210.6	210.4
55°	225.1	207.8	198.0	190.6	186.3	182.7	183.5
57.5°	192.6	178.0	171.4	165.3	162.2	160.9	158.7
60°	172.4	161.1	155.4	150.5	147.5	146.3	144.3
62.5°	154.4	145.5	140.1	136.1	133.4	133.0	131.3
65°	129.8	123.0	118.1	116.3	113.4	112.7	112.7
67.5°	107.0	102.2	98.3	96.6	95.4	95.6	94.7
70°	92.7	88.7	86.3	84.4	83.5	83.6	82.9
72.5°	81.1	76.6	74.5	73.4	72.2	72.6	72.3
75°	61.4	59.2	58.0	56.9	56.2	55.8	55.4
77.5°	45.1	43.1	42.2	41.6	41.7	40.8	41.5
80°	34.8	33.2	32.6	31.6	31.5	31.5	31.3
82.5°	25.5	24.5	24.1	23.4	23.0	23.3	22.8
85°	13.2	12.5	12.2	12.2	11.9	11.5	12.5
87.5°	7.9	7.5	7.8	7.7	7.7	7.7	7.3
90°	15.5	16.3	17.9	17.9	17.9	18.8	18.8
92.5°	104.7	78.8	66.8	56.3	54.4	53.2	51.9
95°	461.5	361.3	293.0	235.2	210.8	204.3	191.3
97.5°	784.7	687.2	592.2	541.9	496.3	472.7	462.3
100°	961.2	877.3	792.7	736.5	678.0	647.8	634.9
102.5°	1069.3	1029.1	971.8	911.7	870.1	837.3	827.5
105°	1130.5	1166.3	1157.3	1131.3	1104.5	1088.2	1078.4
107.5°	1076.0	1167.9	1210.4	1223.6	1223.4	1218.1	1211.5
110°	1014.1	1128.9	1198.1	1234.7	1250.1	1255.8	1255.8



TEST NUMBER: P333144-930

CATALOG NUMBER: S125DIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	952.9	1068.9	1150.6	1204.0	1230.6	1244.8	1250.6
115°	865.2	976.6	1065.4	1128.9	1167.9	1190.7	1201.3
117.5°	804.5	900.5	981.9	1045.4	1085.7	1108.3	1114.8
120°	770.0	859.5	931.1	991.3	1030.4	1052.4	1058.9
122.5°	745.2	824.9	892.0	945.7	981.5	1003.6	1009.4
125°	712.2	782.9	841.6	887.1	920.5	938.4	946.6
127.5°	680.6	746.7	801.5	842.9	872.3	889.2	892.8
130°	658.4	721.9	774.9	815.5	842.4	858.7	863.6
132.5°	637.6	695.2	746.2	786.8	813.8	828.7	834.2
135°	605.5	657.6	704.0	739.8	766.7	781.3	786.2
137.5°	576.9	620.2	659.6	691.6	716.1	729.6	734.9
140°	559.9	597.4	631.6	661.7	682.9	695.0	699.1
142.5°	545.6	577.9	607.5	633.1	650.9	662.5	665.9
145°	527.4	552.6	574.6	594.1	608.0	616.9	620.2
147.5°	512.3	531.7	548.2	563.7	574.8	580.0	581.5
150°	503.8	519.3	533.9	546.1	555.9	559.1	559.9
152.5°	495.3	509.5	520.9	531.2	539.0	542.2	543.0
155°	482.7	494.1	503.0	511.1	516.8	519.3	520.1
157.5°	470.6	479.4	486.4	492.8	497.4	499.7	499.5
160°	461.5	469.6	475.3	481.0	485.1	486.7	485.9
162.5°	453.6	460.5	465.5	469.9	473.4	473.7	473.5
165°	442.0	446.9	450.9	454.1	455.8	455.8	455.8
167.5°	430.6	434.3	437.2	438.9	440.3	439.7	439.5
170°	424.0	426.5	428.1	429.7	430.6	430.6	429.7
172.5°	418.2	420.0	420.9	421.3	422.7	421.4	420.6
175°	409.4	411.0	411.0	411.0	411.8	410.2	409.4
177.5°	405.6	405.6	405.6	405.0	405.6	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7

(END OF REPORT)