

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333153-930

Luminaire Tested: **S125DIP-S375D1205U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333153-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S375D1205U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4778.8 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	88	85	81	82	79	76	73	61	59	58	45	44	43	30	30	29	22
2	84	77	71	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	63	54	47	43	42	38	34	31	28	26	21	20	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2866	2866	2866	2866
5°	3319	2877	2519	2877
10°	3862	2861	2207	2861
15°	4275	2841	2035	2841
20°	4786	2808	1898	2808
25°	5606	2770	1831	2770
30°	6055	2732	1773	2732
35°	4978	2663	1735	2663
40°	3538	2566	1693	2566
45°	2719	2437	1669	2437
50°	2321	2275	1666	2275
55°	2066	2117	1680	2117
60°	1864	1944	1723	1944
65°	1722	1771	1768	1771
70°	1565	1590	1794	1590
75°	1382	1402	1777	1402
80°	1164	1142	1625	1142
85°	926	823	1312	823



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	0.9
10°-20°	127.2	2.7
20°-30°	206.6	4.3
30°-40°	252.0	5.3
40°-50°	229.2	4.8
50°-60°	182.6	3.8
60°-70°	127.2	2.7
70°-80°	67.8	1.4
80°-90°	19.7	0.4
90°-100°	340.6	7.1
100°-110°	732.2	15.3
110°-120°	687.1	14.4
120°-130°	556.9	11.7
130°-140°	446.9	9.4
140°-150°	337.2	7.1
150°-160°	237.4	5.0
160°-170°	139.9	2.9
170°-180°	45.5	1.0
0°-30°	376.5	7.9
0°-40°	628.5	13.2
0°-60°	1040.3	21.8
0°-90°	1255.1	26.3
90°-120°	1759.9	36.8
90°-150°	3100.9	64.9
90°-180°	3524.0	73.7
0°-180°	4778.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	512	444	388	444	512	52
15°	639	425	304	425	639	183
25°	787	389	257	389	787	359
35°	631	338	220	338	631	386
45°	298	267	183	267	298	238
55°	184	188	149	188	184	165
65°	113	116	116	116	113	112
75°	55	56	71	56	55	60
85°	12	11	18	11	12	15
90°	22	1	22	1	22	15
95°	223	31	223	31	223	315
105°	1255	107	1255	107	1255	1248
115°	1398	191	1398	191	1398	1366
125°	1102	265	1102	265	1102	997
135°	915	311	915	311	915	709
145°	722	362	722	362	722	459
155°	605	413	605	413	605	282
165°	530	451	530	451	530	152
175°	476	469	476	469	476	46
180°	470	470	470	470	470	



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	469.4	468.9	468.2	467.1	468.0	465.4	464.2	462.1	459.5	458.6	457.5
5°	512.0	513.0	514.0	510.0	510.4	507.7	501.7	496.8	492.8	487.7	484.1
7.5°	563.3	561.1	560.8	558.3	553.9	550.3	544.0	536.0	528.2	519.3	511.9
10°	588.9	589.1	587.4	584.4	579.7	576.3	568.0	560.1	550.5	539.2	531.1
12.5°	608.2	609.0	606.8	602.8	600.5	592.9	586.4	577.0	565.6	556.5	544.2
15°	639.4	637.3	635.9	630.7	626.8	618.9	608.5	598.7	586.3	574.8	563.3
17.5°	669.4	671.2	668.3	663.7	651.3	642.1	628.3	614.8	599.3	583.9	570.2
20°	696.3	697.8	693.5	685.3	670.7	661.5	643.2	625.8	608.0	588.2	573.1
22.5°	729.8	728.6	722.7	710.4	697.7	680.6	660.8	639.7	617.3	594.9	574.9
25°	786.7	778.8	775.2	759.9	743.2	718.1	691.0	660.1	632.3	602.7	577.1
27.5°	818.3	815.8	811.8	801.2	783.6	756.8	724.8	687.1	647.8	610.5	576.9
30°	812.0	812.4	812.7	809.3	798.0	777.9	746.0	705.6	658.8	616.8	578.0
32.5°	755.9	762.7	769.3	777.1	780.2	776.3	756.4	719.8	671.7	624.0	577.4
35°	631.4	633.6	654.8	676.0	704.6	726.8	741.7	725.5	685.0	630.1	576.7
37.5°	492.4	502.6	517.3	541.1	582.4	619.5	667.1	688.9	675.9	632.2	575.4
40°	419.7	429.2	438.8	463.1	497.9	542.7	596.8	642.9	653.7	625.8	570.8
42.5°	363.7	371.1	381.8	400.1	429.2	468.9	520.6	580.9	618.0	607.5	561.3
45°	297.7	302.4	310.6	325.1	346.3	377.3	422.9	488.9	546.3	565.3	538.8
47.5°	254.8	254.8	261.2	271.2	286.4	312.8	346.6	398.2	459.6	505.0	502.9
50°	231.0	230.0	235.1	243.8	255.8	273.4	305.6	346.8	405.8	457.2	471.6
52.5°	210.4	210.6	213.7	220.1	230.2	245.2	269.2	306.5	356.8	409.6	436.6
55°	183.5	182.7	186.3	190.6	198.0	207.8	225.1	253.6	294.5	346.4	381.5
57.5°	158.7	160.9	162.2	165.3	171.4	178.0	192.6	213.4	245.9	290.5	327.5
60°	144.3	146.3	147.5	150.5	155.4	161.1	172.4	189.3	216.6	255.1	291.8
62.5°	131.3	133.0	133.4	136.1	140.1	145.5	154.4	168.7	190.3	223.9	259.8
65°	112.7	112.7	113.4	116.3	118.1	123.0	129.8	140.1	157.5	183.7	214.4
67.5°	94.7	95.6	95.4	96.6	98.3	102.2	107.0	115.5	128.4	147.5	172.1
70°	82.9	83.6	83.5	84.4	86.3	88.7	92.7	100.8	110.0	126.4	147.5
72.5°	72.3	72.6	72.2	73.4	74.5	76.6	81.1	85.4	94.0	107.9	125.2
75°	55.4	55.8	56.2	56.9	58.0	59.2	61.4	65.7	71.4	81.8	92.9
77.5°	41.5	40.8	41.7	41.6	42.2	43.1	45.1	47.4	52.0	58.6	67.2
80°	31.3	31.5	31.5	31.6	32.6	33.2	34.8	36.5	40.1	45.0	51.0
82.5°	22.8	23.3	23.0	23.4	24.1	24.5	25.5	26.9	28.9	32.9	37.2
85°	12.5	11.5	11.9	12.2	12.2	12.5	13.2	13.8	14.9	16.4	18.1
87.5°	8.0	8.3	8.2	8.2	8.4	8.0	8.4	8.2	8.5	8.7	9.0
90°	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0	16.1	15.2	13.3
92.5°	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9	247.3	305.4	310.4
95°	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1	821.3	839.4	684.9
97.5°	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4	1039.3	896.3	611.6
100°	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2	1092.3	855.4	545.7
102.5°	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0	1060.5	783.4	495.6
105°	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1	958.7	686.8	447.1
107.5°	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2	854.9	620.3	426.6
110°	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4	795.7	589.2	420.6



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2	751.8	571.0	420.6
115°	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2	703.8	551.4	423.5
117.5°	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8	675.2	541.7	429.7
120°	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5	659.3	537.1	435.8
122.5°	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1	645.7	533.4	441.1
125°	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3	627.1	528.6	450.0
127.5°	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0	610.1	526.4	460.0
130°	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1	598.8	524.8	466.1
132.5°	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1	589.6	524.8	472.9
135°	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4	578.9	524.8	482.2
137.5°	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6	569.2	525.9	490.7
140°	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2	564.6	526.7	494.5
142.5°	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4	560.8	527.5	496.8
145°	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5	555.1	526.7	499.3
147.5°	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4	549.3	524.2	500.2
150°	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6	544.7	522.0	500.2
152.5°	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0	539.4	518.9	499.5
155°	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6	530.5	513.5	497.3
157.5°	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2	522.2	507.8	494.9
160°	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7	515.4	504.0	492.6
162.5°	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3	509.3	499.5	490.3
165°	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8	500.2	492.6	486.9
167.5°	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8	491.3	486.0	481.6
170°	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7	486.0	482.2	479.4
172.5°	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9	480.7	477.7	476.3
175°	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5	473.7	472.7	472.7
177.5°	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4	470.7	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	456.6	455.6	454.4	452.2	449.7	448.3	446.3	444.9	442.2	439.9	437.5
5°	479.8	474.9	470.4	464.6	458.2	454.0	449.1	443.7	438.0	432.2	425.7
7.5°	503.9	495.1	485.8	475.6	465.7	456.6	447.8	439.4	431.4	421.7	413.5
10°	519.9	509.0	497.3	483.6	470.2	458.5	446.7	436.3	425.7	414.5	404.5
12.5°	536.1	521.5	505.0	489.9	473.9	459.7	445.8	432.5	419.3	406.8	395.1
15°	547.5	534.7	519.4	497.9	479.8	460.4	442.0	424.9	408.8	394.8	380.2
17.5°	555.0	538.4	522.0	501.5	477.8	456.1	435.1	415.5	397.5	379.8	365.7
20°	556.3	539.3	522.2	502.1	477.8	452.9	431.9	408.5	389.1	370.7	353.4
22.5°	555.9	536.6	518.0	497.3	473.5	450.6	425.3	401.4	380.3	362.3	344.2
25°	551.6	531.1	507.7	486.8	463.4	439.1	413.5	388.7	367.2	346.7	328.7
27.5°	548.0	521.5	495.0	470.6	448.0	425.7	401.2	375.8	352.0	331.2	314.3
30°	543.7	514.5	484.7	459.3	436.1	414.5	391.3	366.4	341.5	321.2	303.1
32.5°	539.8	505.7	474.3	446.6	422.1	401.0	379.7	356.0	331.6	311.0	292.9
35°	532.2	492.8	456.8	425.6	399.4	377.7	359.8	337.8	315.4	295.4	278.1
37.5°	522.6	475.9	437.2	404.5	375.8	352.9	336.3	319.4	297.8	278.6	262.9
40°	515.0	463.8	422.9	389.4	359.6	335.9	320.4	304.4	286.6	268.6	252.1
42.5°	505.6	453.0	408.5	372.3	342.9	319.8	303.5	290.0	274.2	257.5	242.1
45°	488.1	433.3	385.1	346.3	316.5	293.7	277.0	266.8	254.9	239.0	226.1
47.5°	462.4	409.7	359.8	319.8	289.0	267.9	252.2	242.4	234.1	222.3	210.5
50°	439.7	392.1	341.5	301.8	271.1	249.8	235.3	226.4	219.3	210.3	200.2
52.5°	414.3	369.9	323.6	284.3	253.9	232.9	218.7	210.9	205.0	198.5	188.7
55°	373.7	336.1	293.1	255.8	227.8	207.2	194.8	188.0	183.1	178.2	172.2
57.5°	329.2	299.7	261.7	227.6	201.7	183.0	171.5	164.9	161.0	158.5	155.0
60°	297.8	272.6	239.9	208.7	183.5	166.9	155.6	150.5	147.3	145.3	142.6
62.5°	268.7	248.0	217.7	189.3	167.2	151.6	141.5	136.5	133.5	132.4	130.3
65°	225.9	209.9	184.8	161.3	142.4	129.1	120.6	115.9	114.0	112.8	113.0
67.5°	183.6	173.9	153.8	133.7	118.6	107.5	100.6	97.0	96.0	94.6	94.6
70°	157.8	150.5	133.5	116.0	102.6	94.0	88.0	84.2	83.2	82.5	82.3
72.5°	135.1	128.7	114.0	100.0	87.9	80.3	75.3	73.1	71.5	71.1	71.0
75°	101.5	98.0	86.3	75.2	66.9	61.6	58.2	56.2	55.0	54.8	55.0
77.5°	72.2	69.1	61.6	53.7	48.5	44.5	41.7	40.9	39.7	39.7	39.5
80°	54.2	52.2	47.5	41.3	36.9	33.5	32.0	30.7	30.3	29.8	30.3
82.5°	39.3	37.1	33.9	29.9	26.3	24.4	22.8	22.4	22.2	21.9	22.0
85°	19.4	19.6	17.7	14.7	13.2	12.1	11.1	11.1	10.9	10.8	10.9
87.5°	9.1	8.4	7.6	6.8	5.6	4.8	4.3	4.2	4.0	4.2	4.7
90°	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0	1.9	3.8	5.7
92.5°	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6	14.0	22.0	33.8
95°	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2	32.2	39.8	50.2
97.5°	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9	53.1	58.4	68.8
100°	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3	68.2	72.0	82.4
102.5°	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3	83.4	86.4	97.6
105°	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0	107.0	111.8	121.2
107.5°	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3	133.2	137.7	145.5
110°	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7	150.7	154.4	163.0



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2	168.0	171.0	179.6
115°	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4	193.2	196.1	204.6
117.5°	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1	217.0	220.0	228.5
120°	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3	232.1	235.9	244.4
122.5°	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2	247.3	250.3	258.8
125°	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2	267.2	271.9	280.4
127.5°	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0	283.8	289.9	300.7
130°	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8	293.7	301.3	313.6
132.5°	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4	302.0	311.1	325.0
135°	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7	314.5	325.9	341.0
137.5°	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3	329.1	339.7	354.9
140°	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3	338.2	349.6	364.8
142.5°	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9	348.1	358.7	373.8
145°	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9	363.8	373.2	386.5
147.5°	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5	379.7	387.8	400.1
150°	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4	390.3	397.0	409.3
152.5°	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0	400.1	406.0	416.9
155°	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0	413.0	418.7	428.2
157.5°	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6	425.3	429.9	438.1
160°	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9	432.9	436.8	443.4
162.5°	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7	439.8	443.5	449.4
165°	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9	449.1	451.9	456.6
167.5°	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8	456.8	458.5	461.1
170°	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3	461.4	462.3	464.2
172.5°	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4	463.7	464.6	466.4
175°	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0	467.0	468.0	469.0
177.5°	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7	469.1	469.1	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	436.2	434.5	433.2	430.2	428.4	426.2	424.4	426.4	424.3	425.2	423.8
5°	422.6	417.3	413.5	408.1	403.3	399.0	395.8	395.3	393.7	393.0	390.7
7.5°	406.2	399.6	393.1	386.0	379.9	373.8	369.9	366.6	364.5	361.7	359.7
10°	396.6	387.7	380.2	371.5	363.9	357.3	352.1	349.4	347.0	343.4	342.1
12.5°	384.7	375.5	366.3	357.0	349.8	342.4	337.9	333.9	332.2	328.2	327.8
15°	370.4	356.6	347.6	338.2	328.2	322.1	318.4	314.1	312.2	309.3	307.3
17.5°	353.4	341.0	329.8	320.0	311.4	306.4	301.7	298.7	295.5	293.6	290.2
20°	341.0	329.3	318.0	307.6	301.0	295.2	291.5	288.6	285.2	284.3	280.9
22.5°	330.6	317.7	306.9	298.2	291.0	284.4	280.3	278.3	276.1	273.1	272.5
25°	313.6	300.3	291.1	282.4	276.0	269.9	267.2	264.7	262.4	260.3	259.6
27.5°	299.1	287.1	276.1	268.3	262.7	257.2	254.8	251.8	250.1	248.4	246.4
30°	288.8	276.5	266.9	259.4	253.4	248.5	245.8	243.8	242.3	240.8	239.6
32.5°	278.3	266.9	257.6	250.2	244.2	240.5	238.1	236.7	235.1	233.3	231.8
35°	264.3	251.8	242.8	236.4	231.7	228.9	226.2	224.9	223.1	223.1	221.5
37.5°	248.6	237.8	229.8	224.0	219.8	217.3	214.4	213.5	212.3	211.5	211.0
40°	239.3	229.3	221.8	215.9	211.4	209.3	207.0	205.5	204.8	203.8	203.5
42.5°	229.6	220.0	212.9	207.5	203.5	201.8	199.7	198.6	197.1	195.8	195.6
45°	214.9	205.7	199.1	194.8	191.4	189.3	188.0	185.7	185.0	183.5	183.3
47.5°	201.1	192.2	185.7	182.1	179.2	177.5	175.5	173.2	172.3	171.5	171.5
50°	190.6	182.5	176.5	173.2	170.3	167.9	165.8	164.3	163.7	163.7	164.1
52.5°	180.1	173.2	168.1	164.0	161.3	158.7	156.7	155.8	155.0	155.9	156.5
55°	164.7	157.7	153.9	149.9	147.3	144.3	143.3	143.0	142.4	143.9	144.7
57.5°	148.3	143.4	139.0	135.1	132.7	130.9	129.7	129.5	130.5	131.3	133.7
60°	137.9	132.2	128.3	125.3	122.5	121.3	120.9	120.6	121.3	123.4	126.6
62.5°	126.5	121.9	117.6	115.4	113.2	111.4	111.3	111.5	113.0	115.4	118.6
65°	109.7	105.7	102.9	100.2	98.5	97.4	97.8	98.5	100.2	103.5	107.0
67.5°	92.5	89.8	87.3	85.2	83.6	83.6	84.0	85.1	87.1	90.7	94.0
70°	81.6	78.6	76.5	75.6	74.2	73.5	74.6	76.5	78.2	81.6	84.4
72.5°	70.6	68.0	66.4	65.7	65.1	64.6	65.0	67.0	69.3	72.6	76.0
75°	54.2	53.3	52.2	51.4	50.9	51.3	51.6	53.5	55.4	58.9	62.7
77.5°	39.6	38.6	37.9	37.7	37.4	37.7	38.7	40.1	41.9	44.5	47.4
80°	29.9	29.6	29.2	29.0	29.0	29.2	30.7	31.6	33.3	35.8	38.1
82.5°	21.9	21.6	21.5	21.4	21.6	21.7	22.6	23.8	25.2	27.1	29.0
85°	11.5	11.1	11.7	11.9	11.5	12.1	12.5	13.2	13.8	14.7	15.7
87.5°	5.3	6.0	6.0	6.5	6.7	7.4	7.4	8.2	8.7	9.2	9.5
90°	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0	18.0	18.9	20.9
92.5°	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9	121.8	91.7	77.7
95°	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1	537.1	420.6	341.0
97.5°	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4	913.5	800.0	689.3
100°	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2	1118.8	1021.2	922.7
102.5°	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0	1244.6	1197.8	1131.1
105°	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1	1315.9	1357.6	1347.1
107.5°	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2	1252.4	1359.4	1408.9
110°	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4	1180.4	1313.9	1394.5



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2	1109.1	1244.2	1339.1
115°	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2	1007.1	1136.8	1240.1
117.5°	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8	936.4	1048.1	1142.9
120°	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5	896.2	1000.4	1083.8
122.5°	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1	867.4	960.3	1038.3
125°	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3	828.9	911.3	979.6
127.5°	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0	792.1	869.1	932.9
130°	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1	766.4	840.3	901.9
132.5°	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1	742.2	809.2	868.5
135°	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4	704.8	765.5	819.5
137.5°	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6	671.5	721.9	767.8
140°	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2	651.8	695.4	735.2
142.5°	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4	635.1	672.6	707.1
145°	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5	613.8	643.3	668.8
147.5°	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4	596.2	618.8	638.1
150°	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6	586.4	604.4	621.4
152.5°	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0	576.6	593.0	606.3
155°	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6	561.7	575.0	585.5
157.5°	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2	547.7	558.0	566.1
160°	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7	537.1	546.6	553.3
162.5°	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3	528.1	536.0	541.8
165°	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8	514.4	520.1	524.8
167.5°	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8	501.2	505.5	508.9
170°	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7	493.6	496.4	498.3
172.5°	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9	486.7	488.9	490.0
175°	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5	476.5	478.4	478.4
177.5°	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4	472.1	472.1	472.1
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	422.9	424.0	423.1	424.3	423.1	424.0	422.9	423.8	425.2	424.3	426.4
5°	389.8	388.1	389.2	388.5	389.2	388.1	389.8	390.7	393.0	393.7	395.3
7.5°	359.2	357.6	355.7	354.8	355.7	357.6	359.2	359.7	361.7	364.5	366.6
10°	340.1	337.9	337.8	336.5	337.8	337.9	340.1	342.1	343.4	347.0	349.4
12.5°	326.0	324.1	322.0	321.4	322.0	324.1	326.0	327.8	328.2	332.2	333.9
15°	306.1	304.6	303.3	304.4	303.3	304.6	306.1	307.3	309.3	312.2	314.1
17.5°	289.6	288.4	288.1	286.7	288.1	288.4	289.6	290.2	293.6	295.5	298.7
20°	279.2	278.3	278.7	276.1	278.7	278.3	279.2	280.9	284.3	285.2	288.6
22.5°	270.9	269.0	268.8	268.3	268.8	269.0	270.9	272.5	273.1	276.1	278.3
25°	257.9	257.0	256.0	257.0	256.0	257.0	257.9	259.6	260.3	262.4	264.7
27.5°	246.5	245.4	245.2	245.3	245.2	245.4	246.5	246.4	248.4	250.1	251.8
30°	239.6	237.7	237.9	237.7	237.9	237.7	239.6	239.6	240.8	242.3	243.8
32.5°	232.1	230.8	230.6	230.2	230.6	230.8	232.1	231.8	233.3	235.1	236.7
35°	220.9	220.9	220.0	220.0	220.0	220.9	220.9	221.5	223.1	223.1	224.9
37.5°	210.5	210.3	209.8	209.9	209.8	210.3	210.5	211.0	211.5	212.3	213.5
40°	202.7	202.5	201.9	200.8	201.9	202.5	202.7	203.5	203.8	204.8	205.5
42.5°	195.2	194.5	194.3	193.9	194.3	194.5	195.2	195.6	195.8	197.1	198.6
45°	183.3	183.3	183.0	182.7	183.0	183.3	183.3	183.3	183.5	185.0	185.7
47.5°	171.8	172.1	172.8	172.7	172.8	172.1	171.8	171.5	171.5	172.3	173.2
50°	164.9	165.0	165.6	165.8	165.6	165.0	164.9	164.1	163.7	163.7	164.3
52.5°	157.2	158.2	159.0	158.8	159.0	158.2	157.2	156.5	155.9	155.0	155.8
55°	146.3	147.7	149.0	149.2	149.0	147.7	146.3	144.7	143.9	142.4	143.0
57.5°	135.7	137.5	138.9	139.4	138.9	137.5	135.7	133.7	131.3	130.5	129.5
60°	128.5	130.9	132.6	133.4	132.6	130.9	128.5	126.6	123.4	121.3	120.6
62.5°	121.6	124.3	126.0	126.1	126.0	124.3	121.6	118.6	115.4	113.0	111.5
65°	110.2	113.0	114.5	115.7	114.5	113.0	110.2	107.0	103.5	100.2	98.5
67.5°	98.0	100.9	102.5	103.4	102.5	100.9	98.0	94.0	90.7	87.1	85.1
70°	89.1	92.0	94.2	95.0	94.2	92.0	89.1	84.4	81.6	78.2	76.5
72.5°	80.4	82.9	84.7	85.6	84.7	82.9	80.4	76.0	72.6	69.3	67.0
75°	65.1	68.6	70.3	71.2	70.3	68.6	65.1	62.7	58.9	55.4	53.5
77.5°	50.2	53.3	54.4	54.9	54.4	53.3	50.2	47.4	44.5	41.9	40.1
80°	40.3	42.2	43.5	43.7	43.5	42.2	40.3	38.1	35.8	33.3	31.6
82.5°	31.0	32.5	32.9	33.4	32.9	32.5	31.0	29.0	27.1	25.2	23.8
85°	17.0	17.7	17.9	17.7	17.9	17.7	17.0	15.7	14.7	13.8	13.2
87.5°	9.8	9.6	9.8	10.1	9.8	9.6	9.8	9.5	9.2	8.7	8.2
90°	20.9	20.9	21.8	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0
92.5°	65.6	63.3	62.0	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9
95°	273.8	245.3	237.8	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1
97.5°	630.7	577.7	550.2	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4
100°	857.4	789.1	754.1	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2
102.5°	1061.2	1012.7	974.6	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0
105°	1316.8	1285.6	1266.6	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1
107.5°	1424.2	1424.1	1417.8	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2
110°	1437.1	1455.1	1461.8	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1401.5	1432.4	1448.9	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2
115°	1313.9	1359.4	1385.9	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2
117.5°	1216.8	1263.8	1290.1	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8
120°	1153.9	1199.3	1224.9	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5
122.5°	1100.8	1142.5	1168.1	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1
125°	1032.6	1071.5	1092.3	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3
127.5°	981.0	1015.4	1035.1	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0
130°	949.3	980.5	999.5	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1
132.5°	915.9	947.1	964.6	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1
135°	861.1	892.4	909.5	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4
137.5°	805.0	833.5	849.2	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6
140°	770.2	794.8	809.0	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2
142.5°	736.9	757.7	771.1	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4
145°	691.5	707.7	718.1	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5
147.5°	656.2	669.0	675.1	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4
150°	635.7	647.0	650.9	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6
152.5°	618.2	627.3	631.1	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0
155°	594.9	601.5	604.4	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6
157.5°	573.5	579.0	581.6	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2
160°	559.9	564.6	566.6	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7
162.5°	547.0	551.0	551.4	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3
165°	528.6	530.5	530.5	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8
167.5°	510.8	512.5	511.8	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8
170°	500.2	501.2	501.2	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7
172.5°	490.3	492.0	490.6	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9
175°	478.4	479.4	477.4	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5
177.5°	471.4	472.1	469.9	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	424.4	426.2	428.4	430.2	433.2	434.5	436.2	437.5	439.9	442.2	444.9
5°	395.8	399.0	403.3	408.1	413.5	417.3	422.6	425.7	432.2	438.0	443.7
7.5°	369.9	373.8	379.9	386.0	393.1	399.6	406.2	413.5	421.7	431.4	439.4
10°	352.1	357.3	363.9	371.5	380.2	387.7	396.6	404.5	414.5	425.7	436.3
12.5°	337.9	342.4	349.8	357.0	366.3	375.5	384.7	395.1	406.8	419.3	432.5
15°	318.4	322.1	328.2	338.2	347.6	356.6	370.4	380.2	394.8	408.8	424.9
17.5°	301.7	306.4	311.4	320.0	329.8	341.0	353.4	365.7	379.8	397.5	415.5
20°	291.5	295.2	301.0	307.6	318.0	329.3	341.0	353.4	370.7	389.1	408.5
22.5°	280.3	284.4	291.0	298.2	306.9	317.7	330.6	344.2	362.3	380.3	401.4
25°	267.2	269.9	276.0	282.4	291.1	300.3	313.6	328.7	346.7	367.2	388.7
27.5°	254.8	257.2	262.7	268.3	276.1	287.1	299.1	314.3	331.2	352.0	375.8
30°	245.8	248.5	253.4	259.4	266.9	276.5	288.8	303.1	321.2	341.5	366.4
32.5°	238.1	240.5	244.2	250.2	257.6	266.9	278.3	292.9	311.0	331.6	356.0
35°	226.2	228.9	231.7	236.4	242.8	251.8	264.3	278.1	295.4	315.4	337.8
37.5°	214.4	217.3	219.8	224.0	229.8	237.8	248.6	262.9	278.6	297.8	319.4
40°	207.0	209.3	211.4	215.9	221.8	229.3	239.3	252.1	268.6	286.6	304.4
42.5°	199.7	201.8	203.5	207.5	212.9	220.0	229.6	242.1	257.5	274.2	290.0
45°	188.0	189.3	191.4	194.8	199.1	205.7	214.9	226.1	239.0	254.9	266.8
47.5°	175.5	177.5	179.2	182.1	185.7	192.2	201.1	210.5	222.3	234.1	242.4
50°	165.8	167.9	170.3	173.2	176.5	182.5	190.6	200.2	210.3	219.3	226.4
52.5°	156.7	158.7	161.3	164.0	168.1	173.2	180.1	188.7	198.5	205.0	210.9
55°	143.3	144.3	147.3	149.9	153.9	157.7	164.7	172.2	178.2	183.1	188.0
57.5°	129.7	130.9	132.7	135.1	139.0	143.4	148.3	155.0	158.5	161.0	164.9
60°	120.9	121.3	122.5	125.3	128.3	132.2	137.9	142.6	145.3	147.3	150.5
62.5°	111.3	111.4	113.2	115.4	117.6	121.9	126.5	130.3	132.4	133.5	136.5
65°	97.8	97.4	98.5	100.2	102.9	105.7	109.7	113.0	112.8	114.0	115.9
67.5°	84.0	83.6	83.6	85.2	87.3	89.8	92.5	94.6	94.6	96.0	97.0
70°	74.6	73.5	74.2	75.6	76.5	78.6	81.6	82.3	82.5	83.2	84.2
72.5°	65.0	64.6	65.1	65.7	66.4	68.0	70.6	71.0	71.1	71.5	73.1
75°	51.6	51.3	50.9	51.4	52.2	53.3	54.2	55.0	54.8	55.0	56.2
77.5°	38.7	37.7	37.4	37.7	37.9	38.6	39.6	39.5	39.7	39.7	40.9
80°	30.7	29.2	29.0	29.0	29.2	29.6	29.9	30.3	29.8	30.3	30.7
82.5°	22.6	21.7	21.6	21.4	21.5	21.6	21.9	22.0	21.9	22.2	22.4
85°	12.5	12.1	11.5	11.9	11.7	11.1	11.5	10.9	10.8	10.9	11.1
87.5°	7.4	7.4	6.7	6.5	6.0	6.0	5.3	4.7	4.2	4.0	4.2
90°	16.1	15.2	13.3	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0
92.5°	247.3	305.4	310.4	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6
95°	821.3	839.4	684.9	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2
97.5°	1039.3	896.3	611.6	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9
100°	1092.3	855.4	545.7	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3
102.5°	1060.5	783.4	495.6	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3
105°	958.7	686.8	447.1	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0
107.5°	854.9	620.3	426.6	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3
110°	795.7	589.2	420.6	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	751.8	571.0	420.6	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2
115°	703.8	551.4	423.5	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4
117.5°	675.2	541.7	429.7	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1
120°	659.3	537.1	435.8	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3
122.5°	645.7	533.4	441.1	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2
125°	627.1	528.6	450.0	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2
127.5°	610.1	526.4	460.0	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0
130°	598.8	524.8	466.1	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8
132.5°	589.6	524.8	472.9	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4
135°	578.9	524.8	482.2	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7
137.5°	569.2	525.9	490.7	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3
140°	564.6	526.7	494.5	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3
142.5°	560.8	527.5	496.8	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9
145°	555.1	526.7	499.3	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9
147.5°	549.3	524.2	500.2	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5
150°	544.7	522.0	500.2	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4
152.5°	539.4	518.9	499.5	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0
155°	530.5	513.5	497.3	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0
157.5°	522.2	507.8	494.9	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6
160°	515.4	504.0	492.6	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9
162.5°	509.3	499.5	490.3	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7
165°	500.2	492.6	486.9	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9
167.5°	491.3	486.0	481.6	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8
170°	486.0	482.2	479.4	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3
172.5°	480.7	477.7	476.3	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4
175°	473.7	472.7	472.7	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0
177.5°	470.7	469.9	469.9	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	446.3	448.3	449.7	452.2	454.4	455.6	456.6	457.5	458.6	459.5	462.1
5°	449.1	454.0	458.2	464.6	470.4	474.9	479.8	484.1	487.7	492.8	496.8
7.5°	447.8	456.6	465.7	475.6	485.8	495.1	503.9	511.9	519.3	528.2	536.0
10°	446.7	458.5	470.2	483.6	497.3	509.0	519.9	531.1	539.2	550.5	560.1
12.5°	445.8	459.7	473.9	489.9	505.0	521.5	536.1	544.2	556.5	565.6	577.0
15°	442.0	460.4	479.8	497.9	519.4	534.7	547.5	563.3	574.8	586.3	598.7
17.5°	435.1	456.1	477.8	501.5	522.0	538.4	555.0	570.2	583.9	599.3	614.8
20°	431.9	452.9	477.8	502.1	522.2	539.3	556.3	573.1	588.2	608.0	625.8
22.5°	425.3	450.6	473.5	497.3	518.0	536.6	555.9	574.9	594.9	617.3	639.7
25°	413.5	439.1	463.4	486.8	507.7	531.1	551.6	577.1	602.7	632.3	660.1
27.5°	401.2	425.7	448.0	470.6	495.0	521.5	548.0	576.9	610.5	647.8	687.1
30°	391.3	414.5	436.1	459.3	484.7	514.5	543.7	578.0	616.8	658.8	705.6
32.5°	379.7	401.0	422.1	446.6	474.3	505.7	539.8	577.4	624.0	671.7	719.8
35°	359.8	377.7	399.4	425.6	456.8	492.8	532.2	576.7	630.1	685.0	725.5
37.5°	336.3	352.9	375.8	404.5	437.2	475.9	522.6	575.4	632.2	675.9	688.9
40°	320.4	335.9	359.6	389.4	422.9	463.8	515.0	570.8	625.8	653.7	642.9
42.5°	303.5	319.8	342.9	372.3	408.5	453.0	505.6	561.3	607.5	618.0	580.9
45°	277.0	293.7	316.5	346.3	385.1	433.3	488.1	538.8	565.3	546.3	488.9
47.5°	252.2	267.9	289.0	319.8	359.8	409.7	462.4	502.9	505.0	459.6	398.2
50°	235.3	249.8	271.1	301.8	341.5	392.1	439.7	471.6	457.2	405.8	346.8
52.5°	218.7	232.9	253.9	284.3	323.6	369.9	414.3	436.6	409.6	356.8	306.5
55°	194.8	207.2	227.8	255.8	293.1	336.1	373.7	381.5	346.4	294.5	253.6
57.5°	171.5	183.0	201.7	227.6	261.7	299.7	329.2	327.5	290.5	245.9	213.4
60°	155.6	166.9	183.5	208.7	239.9	272.6	297.8	291.8	255.1	216.6	189.3
62.5°	141.5	151.6	167.2	189.3	217.7	248.0	268.7	259.8	223.9	190.3	168.7
65°	120.6	129.1	142.4	161.3	184.8	209.9	225.9	214.4	183.7	157.5	140.1
67.5°	100.6	107.5	118.6	133.7	153.8	173.9	183.6	172.1	147.5	128.4	115.5
70°	88.0	94.0	102.6	116.0	133.5	150.5	157.8	147.5	126.4	110.0	100.8
72.5°	75.3	80.3	87.9	100.0	114.0	128.7	135.1	125.2	107.9	94.0	85.4
75°	58.2	61.6	66.9	75.2	86.3	98.0	101.5	92.9	81.8	71.4	65.7
77.5°	41.7	44.5	48.5	53.7	61.6	69.1	72.2	67.2	58.6	52.0	47.4
80°	32.0	33.5	36.9	41.3	47.5	52.2	54.2	51.0	45.0	40.1	36.5
82.5°	22.8	24.4	26.3	29.9	33.9	37.1	39.3	37.2	32.9	28.9	26.9
85°	11.1	12.1	13.2	14.7	17.7	19.6	19.4	18.1	16.4	14.9	13.8
87.5°	4.3	4.8	5.6	6.8	7.6	8.4	9.1	9.0	8.7	8.5	8.2
90°	1.9	3.8	5.7	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0
92.5°	14.0	22.0	33.8	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9
95°	32.2	39.8	50.2	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1
97.5°	53.1	58.4	68.8	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4
100°	68.2	72.0	82.4	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2
102.5°	83.4	86.4	97.6	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0
105°	107.0	111.8	121.2	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1
107.5°	133.2	137.7	145.5	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2
110°	150.7	154.4	163.0	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.0	171.0	179.6	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2
115°	193.2	196.1	204.6	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2
117.5°	217.0	220.0	228.5	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8
120°	232.1	235.9	244.4	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5
122.5°	247.3	250.3	258.8	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1
125°	267.2	271.9	280.4	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3
127.5°	283.8	289.9	300.7	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0
130°	293.7	301.3	313.6	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1
132.5°	302.0	311.1	325.0	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1
135°	314.5	325.9	341.0	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4
137.5°	329.1	339.7	354.9	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6
140°	338.2	349.6	364.8	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2
142.5°	348.1	358.7	373.8	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4
145°	363.8	373.2	386.5	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5
147.5°	379.7	387.8	400.1	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4
150°	390.3	397.0	409.3	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6
152.5°	400.1	406.0	416.9	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0
155°	413.0	418.7	428.2	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6
157.5°	425.3	429.9	438.1	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2
160°	432.9	436.8	443.4	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7
162.5°	439.8	443.5	449.4	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3
165°	449.1	451.9	456.6	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8
167.5°	456.8	458.5	461.1	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8
170°	461.4	462.3	464.2	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7
172.5°	463.7	464.6	466.4	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9
175°	467.0	468.0	469.0	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5
177.5°	469.1	469.1	469.9	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	464.2	465.4	468.0	467.1	468.2	468.9	469.4
5°	501.7	507.7	510.4	510.0	514.0	513.0	512.0
7.5°	544.0	550.3	553.9	558.3	560.8	561.1	563.3
10°	568.0	576.3	579.7	584.4	587.4	589.1	588.9
12.5°	586.4	592.9	600.5	602.8	606.8	609.0	608.2
15°	608.5	618.9	626.8	630.7	635.9	637.3	639.4
17.5°	628.3	642.1	651.3	663.7	668.3	671.2	669.4
20°	643.2	661.5	670.7	685.3	693.5	697.8	696.3
22.5°	660.8	680.6	697.7	710.4	722.7	728.6	729.8
25°	691.0	718.1	743.2	759.9	775.2	778.8	786.7
27.5°	724.8	756.8	783.6	801.2	811.8	815.8	818.3
30°	746.0	777.9	798.0	809.3	812.7	812.4	812.0
32.5°	756.4	776.3	780.2	777.1	769.3	762.7	755.9
35°	741.7	726.8	704.6	676.0	654.8	633.6	631.4
37.5°	667.1	619.5	582.4	541.1	517.3	502.6	492.4
40°	596.8	542.7	497.9	463.1	438.8	429.2	419.7
42.5°	520.6	468.9	429.2	400.1	381.8	371.1	363.7
45°	422.9	377.3	346.3	325.1	310.6	302.4	297.7
47.5°	346.6	312.8	286.4	271.2	261.2	254.8	254.8
50°	305.6	273.4	255.8	243.8	235.1	230.0	231.0
52.5°	269.2	245.2	230.2	220.1	213.7	210.6	210.4
55°	225.1	207.8	198.0	190.6	186.3	182.7	183.5
57.5°	192.6	178.0	171.4	165.3	162.2	160.9	158.7
60°	172.4	161.1	155.4	150.5	147.5	146.3	144.3
62.5°	154.4	145.5	140.1	136.1	133.4	133.0	131.3
65°	129.8	123.0	118.1	116.3	113.4	112.7	112.7
67.5°	107.0	102.2	98.3	96.6	95.4	95.6	94.7
70°	92.7	88.7	86.3	84.4	83.5	83.6	82.9
72.5°	81.1	76.6	74.5	73.4	72.2	72.6	72.3
75°	61.4	59.2	58.0	56.9	56.2	55.8	55.4
77.5°	45.1	43.1	42.2	41.6	41.7	40.8	41.5
80°	34.8	33.2	32.6	31.6	31.5	31.5	31.3
82.5°	25.5	24.5	24.1	23.4	23.0	23.3	22.8
85°	13.2	12.5	12.2	12.2	11.9	11.5	12.5
87.5°	8.4	8.0	8.4	8.2	8.2	8.3	8.0
90°	18.0	18.9	20.9	20.9	20.9	21.8	21.8
92.5°	121.8	91.7	77.7	65.6	63.3	62.0	60.4
95°	537.1	420.6	341.0	273.8	245.3	237.8	222.7
97.5°	913.5	800.0	689.3	630.7	577.7	550.2	538.1
100°	1118.8	1021.2	922.7	857.4	789.1	754.1	738.9
102.5°	1244.6	1197.8	1131.1	1061.2	1012.7	974.6	963.3
105°	1315.9	1357.6	1347.1	1316.8	1285.6	1266.6	1255.2
107.5°	1252.4	1359.4	1408.9	1424.2	1424.1	1417.8	1410.2
110°	1180.4	1313.9	1394.5	1437.1	1455.1	1461.8	1461.8



TEST NUMBER: P333153-930

CATALOG NUMBER: S125DIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1109.1	1244.2	1339.1	1401.5	1432.4	1448.9	1455.7
115°	1007.1	1136.8	1240.1	1313.9	1359.4	1385.9	1398.2
117.5°	936.4	1048.1	1142.9	1216.8	1263.8	1290.1	1297.6
120°	896.2	1000.4	1083.8	1153.9	1199.3	1224.9	1232.5
122.5°	867.4	960.3	1038.3	1100.8	1142.5	1168.1	1174.9
125°	828.9	911.3	979.6	1032.6	1071.5	1092.3	1101.8
127.5°	792.1	869.1	932.9	981.0	1015.4	1035.1	1039.3
130°	766.4	840.3	901.9	949.3	980.5	999.5	1005.1
132.5°	742.2	809.2	868.5	915.9	947.1	964.6	971.0
135°	704.8	765.5	819.5	861.1	892.4	909.5	915.2
137.5°	671.5	721.9	767.8	805.0	833.5	849.2	855.4
140°	651.8	695.4	735.2	770.2	794.8	809.0	813.8
142.5°	635.1	672.6	707.1	736.9	757.7	771.1	775.1
145°	613.8	643.3	668.8	691.5	707.7	718.1	721.9
147.5°	596.2	618.8	638.1	656.2	669.0	675.1	676.8
150°	586.4	604.4	621.4	635.7	647.0	650.9	651.8
152.5°	576.6	593.0	606.3	618.2	627.3	631.1	632.1
155°	561.7	575.0	585.5	594.9	601.5	604.4	605.4
157.5°	547.7	558.0	566.1	573.5	579.0	581.6	581.5
160°	537.1	546.6	553.3	559.9	564.6	566.6	565.6
162.5°	528.1	536.0	541.8	547.0	551.0	551.4	551.1
165°	514.4	520.1	524.8	528.6	530.5	530.5	530.5
167.5°	501.2	505.5	508.9	510.8	512.5	511.8	511.6
170°	493.6	496.4	498.3	500.2	501.2	501.2	500.2
172.5°	486.7	488.9	490.0	490.3	492.0	490.6	489.6
175°	476.5	478.4	478.4	478.4	479.4	477.4	476.5
177.5°	472.1	472.1	472.1	471.4	472.1	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9

(END OF REPORT)