

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333117-930

Luminaire Tested: **S125DIP-S375D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333117-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIP-S375D365U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2325.0 lumens  
Efficiency: N/A  
Efficacy: 114.5 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	51	70	60	53	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	25	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	37	30	25	32	26	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2866	2866	2866	2866
5°	3319	2877	2519	2877
10°	3862	2861	2207	2861
15°	4275	2841	2035	2841
20°	4786	2808	1898	2808
25°	5606	2770	1831	2770
30°	6055	2732	1773	2732
35°	4978	2663	1735	2663
40°	3538	2566	1693	2566
45°	2719	2437	1669	2437
50°	2321	2275	1666	2275
55°	2066	2117	1680	2117
60°	1864	1944	1723	1944
65°	1722	1771	1768	1771
70°	1565	1590	1794	1590
75°	1382	1402	1777	1402
80°	1164	1142	1625	1142
85°	926	823	1312	823



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.7	1.8
10°-20°	127.2	5.5
20°-30°	206.6	8.9
30°-40°	252.0	10.8
40°-50°	229.2	9.9
50°-60°	182.6	7.9
60°-70°	127.2	5.5
70°-80°	67.8	2.9
80°-90°	17.9	0.8
90°-100°	103.6	4.5
100°-110°	222.7	9.6
110°-120°	209.0	9.0
120°-130°	169.4	7.3
130°-140°	135.9	5.8
140°-150°	102.6	4.4
150°-160°	72.2	3.1
160°-170°	42.6	1.8
170°-180°	13.8	0.6
0°-30°	376.5	16.2
0°-40°	628.5	27.0
0°-60°	1040.3	44.7
0°-90°	1253.2	53.9
90°-120°	535.3	23.0
90°-150°	943.1	40.6
90°-180°	1072.0	46.1
0°-180°	2325.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	444	444	444	444	444	
5°	512	444	388	444	512	52
15°	639	425	304	425	639	183
25°	787	389	257	389	787	359
35°	631	338	220	338	631	386
45°	298	267	183	267	298	238
55°	184	188	149	188	184	165
65°	113	116	116	116	113	112
75°	55	56	71	56	55	60
85°	12	11	18	11	12	15
90°	7	0	7	0	7	5
95°	68	10	68	10	68	96
105°	382	32	382	32	382	380
115°	425	58	425	58	425	416
125°	335	81	335	81	335	303
135°	278	94	278	94	278	216
145°	220	110	220	110	220	140
155°	184	126	184	126	184	86
165°	161	137	161	137	161	46
175°	145	143	145	143	145	14
180°	143	143	143	143	143	



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	469.4	468.9	468.2	467.1	468.0	465.4	464.2	462.1	459.5	458.6	457.5
5°	512.0	513.0	514.0	510.0	510.4	507.7	501.7	496.8	492.8	487.7	484.1
7.5°	563.3	561.1	560.8	558.3	553.9	550.3	544.0	536.0	528.2	519.3	511.9
10°	588.9	589.1	587.4	584.4	579.7	576.3	568.0	560.1	550.5	539.2	531.1
12.5°	608.2	609.0	606.8	602.8	600.5	592.9	586.4	577.0	565.6	556.5	544.2
15°	639.4	637.3	635.9	630.7	626.8	618.9	608.5	598.7	586.3	574.8	563.3
17.5°	669.4	671.2	668.3	663.7	651.3	642.1	628.3	614.8	599.3	583.9	570.2
20°	696.3	697.8	693.5	685.3	670.7	661.5	643.2	625.8	608.0	588.2	573.1
22.5°	729.8	728.6	722.7	710.4	697.7	680.6	660.8	639.7	617.3	594.9	574.9
25°	786.7	778.8	775.2	759.9	743.2	718.1	691.0	660.1	632.3	602.7	577.1
27.5°	818.3	815.8	811.8	801.2	783.6	756.8	724.8	687.1	647.8	610.5	576.9
30°	812.0	812.4	812.7	809.3	798.0	777.9	746.0	705.6	658.8	616.8	578.0
32.5°	755.9	762.7	769.3	777.1	780.2	776.3	756.4	719.8	671.7	624.0	577.4
35°	631.4	633.6	654.8	676.0	704.6	726.8	741.7	725.5	685.0	630.1	576.7
37.5°	492.4	502.6	517.3	541.1	582.4	619.5	667.1	688.9	675.9	632.2	575.4
40°	419.7	429.2	438.8	463.1	497.9	542.7	596.8	642.9	653.7	625.8	570.8
42.5°	363.7	371.1	381.8	400.1	429.2	468.9	520.6	580.9	618.0	607.5	561.3
45°	297.7	302.4	310.6	325.1	346.3	377.3	422.9	488.9	546.3	565.3	538.8
47.5°	254.8	254.8	261.2	271.2	286.4	312.8	346.6	398.2	459.6	505.0	502.9
50°	231.0	230.0	235.1	243.8	255.8	273.4	305.6	346.8	405.8	457.2	471.6
52.5°	210.4	210.6	213.7	220.1	230.2	245.2	269.2	306.5	356.8	409.6	436.6
55°	183.5	182.7	186.3	190.6	198.0	207.8	225.1	253.6	294.5	346.4	381.5
57.5°	158.7	160.9	162.2	165.3	171.4	178.0	192.6	213.4	245.9	290.5	327.5
60°	144.3	146.3	147.5	150.5	155.4	161.1	172.4	189.3	216.6	255.1	291.8
62.5°	131.3	133.0	133.4	136.1	140.1	145.5	154.4	168.7	190.3	223.9	259.8
65°	112.7	112.7	113.4	116.3	118.1	123.0	129.8	140.1	157.5	183.7	214.4
67.5°	94.7	95.6	95.4	96.6	98.3	102.2	107.0	115.5	128.4	147.5	172.1
70°	82.9	83.6	83.5	84.4	86.3	88.7	92.7	100.8	110.0	126.4	147.5
72.5°	72.3	72.6	72.2	73.4	74.5	76.6	81.1	85.4	94.0	107.9	125.2
75°	55.4	55.8	56.2	56.9	58.0	59.2	61.4	65.7	71.4	81.8	92.9
77.5°	41.5	40.8	41.7	41.6	42.2	43.1	45.1	47.4	52.0	58.6	67.2
80°	31.3	31.5	31.5	31.6	32.6	33.2	34.8	36.5	40.1	45.0	51.0
82.5°	22.8	23.3	23.0	23.4	24.1	24.5	25.5	26.9	28.9	32.9	37.2
85°	12.5	11.5	11.9	12.2	12.2	12.5	13.2	13.8	14.9	16.4	18.1
87.5°	5.0	5.2	5.3	5.3	5.5	5.4	6.0	5.9	6.3	6.7	7.2
90°	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2	4.9	4.6	4.0
92.5°	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0	75.2	92.9	94.4
95°	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2	249.8	255.3	208.3
97.5°	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5	316.1	272.6	186.1
100°	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4	332.2	260.2	166.0
102.5°	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8	322.5	238.3	150.7
105°	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8	291.6	208.9	136.0
107.5°	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2	260.0	188.7	129.8
110°	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3	242.1	179.2	127.9



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4	228.7	173.7	127.9
115°	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6	214.1	167.7	128.8
117.5°	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3	205.4	164.8	130.7
120°	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0	200.6	163.4	132.6
122.5°	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8	196.4	162.2	134.1
125°	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7	190.8	160.8	136.9
127.5°	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5	185.6	160.1	139.9
130°	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7	182.1	159.6	141.8
132.5°	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9	179.4	159.6	143.8
135°	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5	176.0	159.6	146.7
137.5°	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2	173.1	160.0	149.3
140°	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7	171.7	160.2	150.4
142.5°	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7	170.6	160.5	151.1
145°	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8	168.8	160.2	151.8
147.5°	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1	167.1	159.5	152.1
150°	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0	165.7	158.7	152.1
152.5°	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7	164.0	157.8	151.9
155°	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2	161.3	156.2	151.2
157.5°	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8	158.8	154.4	150.5
160°	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5	156.8	153.3	149.9
162.5°	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9	154.9	151.9	149.1
165°	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4	152.1	149.9	148.1
167.5°	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1	149.4	147.8	146.5
170°	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3	147.8	146.7	145.8
172.5°	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2	146.2	145.3	144.9
175°	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0	144.1	143.8	143.8
177.5°	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4	143.2	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	456.6	455.6	454.4	452.2	449.7	448.3	446.3	444.9	442.2	439.9	437.5
5°	479.8	474.9	470.4	464.6	458.2	454.0	449.1	443.7	438.0	432.2	425.7
7.5°	503.9	495.1	485.8	475.6	465.7	456.6	447.8	439.4	431.4	421.7	413.5
10°	519.9	509.0	497.3	483.6	470.2	458.5	446.7	436.3	425.7	414.5	404.5
12.5°	536.1	521.5	505.0	489.9	473.9	459.7	445.8	432.5	419.3	406.8	395.1
15°	547.5	534.7	519.4	497.9	479.8	460.4	442.0	424.9	408.8	394.8	380.2
17.5°	555.0	538.4	522.0	501.5	477.8	456.1	435.1	415.5	397.5	379.8	365.7
20°	556.3	539.3	522.2	502.1	477.8	452.9	431.9	408.5	389.1	370.7	353.4
22.5°	555.9	536.6	518.0	497.3	473.5	450.6	425.3	401.4	380.3	362.3	344.2
25°	551.6	531.1	507.7	486.8	463.4	439.1	413.5	388.7	367.2	346.7	328.7
27.5°	548.0	521.5	495.0	470.6	448.0	425.7	401.2	375.8	352.0	331.2	314.3
30°	543.7	514.5	484.7	459.3	436.1	414.5	391.3	366.4	341.5	321.2	303.1
32.5°	539.8	505.7	474.3	446.6	422.1	401.0	379.7	356.0	331.6	311.0	292.9
35°	532.2	492.8	456.8	425.6	399.4	377.7	359.8	337.8	315.4	295.4	278.1
37.5°	522.6	475.9	437.2	404.5	375.8	352.9	336.3	319.4	297.8	278.6	262.9
40°	515.0	463.8	422.9	389.4	359.6	335.9	320.4	304.4	286.6	268.6	252.1
42.5°	505.6	453.0	408.5	372.3	342.9	319.8	303.5	290.0	274.2	257.5	242.1
45°	488.1	433.3	385.1	346.3	316.5	293.7	277.0	266.8	254.9	239.0	226.1
47.5°	462.4	409.7	359.8	319.8	289.0	267.9	252.2	242.4	234.1	222.3	210.5
50°	439.7	392.1	341.5	301.8	271.1	249.8	235.3	226.4	219.3	210.3	200.2
52.5°	414.3	369.9	323.6	284.3	253.9	232.9	218.7	210.9	205.0	198.5	188.7
55°	373.7	336.1	293.1	255.8	227.8	207.2	194.8	188.0	183.1	178.2	172.2
57.5°	329.2	299.7	261.7	227.6	201.7	183.0	171.5	164.9	161.0	158.5	155.0
60°	297.8	272.6	239.9	208.7	183.5	166.9	155.6	150.5	147.3	145.3	142.6
62.5°	268.7	248.0	217.7	189.3	167.2	151.6	141.5	136.5	133.5	132.4	130.3
65°	225.9	209.9	184.8	161.3	142.4	129.1	120.6	115.9	114.0	112.8	113.0
67.5°	183.6	173.9	153.8	133.7	118.6	107.5	100.6	97.0	96.0	94.6	94.6
70°	157.8	150.5	133.5	116.0	102.6	94.0	88.0	84.2	83.2	82.5	82.3
72.5°	135.1	128.7	114.0	100.0	87.9	80.3	75.3	73.1	71.5	71.1	71.0
75°	101.5	98.0	86.3	75.2	66.9	61.6	58.2	56.2	55.0	54.8	55.0
77.5°	72.2	69.1	61.6	53.7	48.5	44.5	41.7	40.9	39.7	39.7	39.5
80°	54.2	52.2	47.5	41.3	36.9	33.5	32.0	30.7	30.3	29.8	30.3
82.5°	39.3	37.1	33.9	29.9	26.3	24.4	22.8	22.4	22.2	21.9	22.0
85°	19.4	19.6	17.7	14.7	13.2	12.1	11.1	11.1	10.9	10.8	10.9
87.5°	7.4	6.9	6.3	5.7	4.9	4.3	4.0	4.2	3.8	3.7	4.0
90°	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3	0.6	1.1	1.7
92.5°	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5	4.2	6.7	10.3
95°	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5	9.8	12.1	15.2
97.5°	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8	16.1	17.8	21.0
100°	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1	20.7	21.9	25.0
102.5°	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0	25.4	26.3	29.7
105°	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5	32.5	34.0	36.9
107.5°	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9	40.5	41.9	44.3
110°	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2	45.8	47.0	49.6





TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5	51.1	52.0	54.6
115°	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2	58.8	59.7	62.2
117.5°	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1	66.0	66.9	69.5
120°	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7	70.6	71.7	74.4
122.5°	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6	75.2	76.1	78.8
125°	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7	81.3	82.7	85.3
127.5°	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4	86.3	88.1	91.5
130°	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5	89.4	91.6	95.4
132.5°	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7	91.9	94.7	98.8
135°	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5	95.6	99.1	103.7
137.5°	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2	100.1	103.3	107.9
140°	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0	102.9	106.3	111.0
142.5°	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3	105.8	109.1	113.7
145°	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1	110.6	113.5	117.6
147.5°	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1	115.4	118.0	121.7
150°	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1	118.7	120.7	124.5
152.5°	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4	121.7	123.5	126.8
155°	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6	125.6	127.3	130.2
157.5°	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5	129.4	130.8	133.2
160°	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0	131.7	132.8	134.9
162.5°	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0	133.8	134.9	136.7
165°	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1	136.6	137.5	138.8
167.5°	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3	138.9	139.5	140.2
170°	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6	140.3	140.6	141.2
172.5°	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5	141.0	141.3	141.9
175°	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6	142.0	142.4	142.6
177.5°	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2	142.7	142.7	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	436.2	434.5	433.2	430.2	428.4	426.2	424.4	426.4	424.3	425.2	423.8
5°	422.6	417.3	413.5	408.1	403.3	399.0	395.8	395.3	393.7	393.0	390.7
7.5°	406.2	399.6	393.1	386.0	379.9	373.8	369.9	366.6	364.5	361.7	359.7
10°	396.6	387.7	380.2	371.5	363.9	357.3	352.1	349.4	347.0	343.4	342.1
12.5°	384.7	375.5	366.3	357.0	349.8	342.4	337.9	333.9	332.2	328.2	327.8
15°	370.4	356.6	347.6	338.2	328.2	322.1	318.4	314.1	312.2	309.3	307.3
17.5°	353.4	341.0	329.8	320.0	311.4	306.4	301.7	298.7	295.5	293.6	290.2
20°	341.0	329.3	318.0	307.6	301.0	295.2	291.5	288.6	285.2	284.3	280.9
22.5°	330.6	317.7	306.9	298.2	291.0	284.4	280.3	278.3	276.1	273.1	272.5
25°	313.6	300.3	291.1	282.4	276.0	269.9	267.2	264.7	262.4	260.3	259.6
27.5°	299.1	287.1	276.1	268.3	262.7	257.2	254.8	251.8	250.1	248.4	246.4
30°	288.8	276.5	266.9	259.4	253.4	248.5	245.8	243.8	242.3	240.8	239.6
32.5°	278.3	266.9	257.6	250.2	244.2	240.5	238.1	236.7	235.1	233.3	231.8
35°	264.3	251.8	242.8	236.4	231.7	228.9	226.2	224.9	223.1	223.1	221.5
37.5°	248.6	237.8	229.8	224.0	219.8	217.3	214.4	213.5	212.3	211.5	211.0
40°	239.3	229.3	221.8	215.9	211.4	209.3	207.0	205.5	204.8	203.8	203.5
42.5°	229.6	220.0	212.9	207.5	203.5	201.8	199.7	198.6	197.1	195.8	195.6
45°	214.9	205.7	199.1	194.8	191.4	189.3	188.0	185.7	185.0	183.5	183.3
47.5°	201.1	192.2	185.7	182.1	179.2	177.5	175.5	173.2	172.3	171.5	171.5
50°	190.6	182.5	176.5	173.2	170.3	167.9	165.8	164.3	163.7	163.7	164.1
52.5°	180.1	173.2	168.1	164.0	161.3	158.7	156.7	155.8	155.0	155.9	156.5
55°	164.7	157.7	153.9	149.9	147.3	144.3	143.3	143.0	142.4	143.9	144.7
57.5°	148.3	143.4	139.0	135.1	132.7	130.9	129.7	129.5	130.5	131.3	133.7
60°	137.9	132.2	128.3	125.3	122.5	121.3	120.9	120.6	121.3	123.4	126.6
62.5°	126.5	121.9	117.6	115.4	113.2	111.4	111.3	111.5	113.0	115.4	118.6
65°	109.7	105.7	102.9	100.2	98.5	97.4	97.8	98.5	100.2	103.5	107.0
67.5°	92.5	89.8	87.3	85.2	83.6	83.6	84.0	85.1	87.1	90.7	94.0
70°	81.6	78.6	76.5	75.6	74.2	73.5	74.6	76.5	78.2	81.6	84.4
72.5°	70.6	68.0	66.4	65.7	65.1	64.6	65.0	67.0	69.3	72.6	76.0
75°	54.2	53.3	52.2	51.4	50.9	51.3	51.6	53.5	55.4	58.9	62.7
77.5°	39.6	38.6	37.9	37.7	37.4	37.7	38.7	40.1	41.9	44.5	47.4
80°	29.9	29.6	29.2	29.0	29.0	29.2	30.7	31.6	33.3	35.8	38.1
82.5°	21.9	21.6	21.5	21.4	21.6	21.7	22.6	23.8	25.2	27.1	29.0
85°	11.5	11.1	11.7	11.9	11.5	12.1	12.5	13.2	13.8	14.7	15.7
87.5°	4.2	4.6	4.6	4.8	4.9	5.3	5.2	5.9	6.2	6.6	6.5
90°	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2	5.5	5.8	6.4
92.5°	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0	37.0	27.9	23.6
95°	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2	163.4	127.9	103.7
97.5°	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5	277.9	243.3	209.6
100°	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4	340.3	310.6	280.6
102.5°	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8	378.5	364.4	344.1
105°	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8	400.2	412.9	409.8
107.5°	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2	380.9	413.4	428.5
110°	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3	359.1	399.7	424.1



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4	337.4	378.5	407.3
115°	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6	306.3	345.8	377.2
117.5°	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3	284.8	318.8	347.6
120°	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0	272.6	304.3	329.6
122.5°	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8	263.8	292.0	315.8
125°	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7	252.1	277.2	297.9
127.5°	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5	240.9	264.3	283.7
130°	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7	233.1	255.6	274.3
132.5°	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9	225.8	246.1	264.2
135°	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5	214.3	232.8	249.2
137.5°	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2	204.2	219.6	233.5
140°	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7	198.2	211.5	223.6
142.5°	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7	193.1	204.6	215.1
145°	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8	186.7	195.7	203.4
147.5°	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1	181.3	188.3	194.1
150°	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0	178.4	183.8	189.0
152.5°	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7	175.4	180.3	184.4
155°	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2	170.9	174.9	178.1
157.5°	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8	166.6	169.7	172.2
160°	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5	163.4	166.2	168.3
162.5°	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9	160.6	163.1	164.9
165°	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4	156.5	158.2	159.6
167.5°	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1	152.5	153.8	154.8
170°	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3	150.1	151.0	151.6
172.5°	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2	148.1	148.7	149.0
175°	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0	145.0	145.5	145.5
177.5°	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4	143.6	143.6	143.6
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	422.9	424.0	423.1	424.3	423.1	424.0	422.9	423.8	425.2	424.3	426.4
5°	389.8	388.1	389.2	388.5	389.2	388.1	389.8	390.7	393.0	393.7	395.3
7.5°	359.2	357.6	355.7	354.8	355.7	357.6	359.2	359.7	361.7	364.5	366.6
10°	340.1	337.9	337.8	336.5	337.8	337.9	340.1	342.1	343.4	347.0	349.4
12.5°	326.0	324.1	322.0	321.4	322.0	324.1	326.0	327.8	328.2	332.2	333.9
15°	306.1	304.6	303.3	304.4	303.3	304.6	306.1	307.3	309.3	312.2	314.1
17.5°	289.6	288.4	288.1	286.7	288.1	288.4	289.6	290.2	293.6	295.5	298.7
20°	279.2	278.3	278.7	276.1	278.7	278.3	279.2	280.9	284.3	285.2	288.6
22.5°	270.9	269.0	268.8	268.3	268.8	269.0	270.9	272.5	273.1	276.1	278.3
25°	257.9	257.0	256.0	257.0	256.0	257.0	257.9	259.6	260.3	262.4	264.7
27.5°	246.5	245.4	245.2	245.3	245.2	245.4	246.5	246.4	248.4	250.1	251.8
30°	239.6	237.7	237.9	237.7	237.9	237.7	239.6	239.6	240.8	242.3	243.8
32.5°	232.1	230.8	230.6	230.2	230.6	230.8	232.1	231.8	233.3	235.1	236.7
35°	220.9	220.9	220.0	220.0	220.0	220.9	220.9	221.5	223.1	223.1	224.9
37.5°	210.5	210.3	209.8	209.9	209.8	210.3	210.5	211.0	211.5	212.3	213.5
40°	202.7	202.5	201.9	200.8	201.9	202.5	202.7	203.5	203.8	204.8	205.5
42.5°	195.2	194.5	194.3	193.9	194.3	194.5	195.2	195.6	195.8	197.1	198.6
45°	183.3	183.3	183.0	182.7	183.0	183.3	183.3	183.3	183.5	185.0	185.7
47.5°	171.8	172.1	172.8	172.7	172.8	172.1	171.8	171.5	171.5	172.3	173.2
50°	164.9	165.0	165.6	165.8	165.6	165.0	164.9	164.1	163.7	163.7	164.3
52.5°	157.2	158.2	159.0	158.8	159.0	158.2	157.2	156.5	155.9	155.0	155.8
55°	146.3	147.7	149.0	149.2	149.0	147.7	146.3	144.7	143.9	142.4	143.0
57.5°	135.7	137.5	138.9	139.4	138.9	137.5	135.7	133.7	131.3	130.5	129.5
60°	128.5	130.9	132.6	133.4	132.6	130.9	128.5	126.6	123.4	121.3	120.6
62.5°	121.6	124.3	126.0	126.1	126.0	124.3	121.6	118.6	115.4	113.0	111.5
65°	110.2	113.0	114.5	115.7	114.5	113.0	110.2	107.0	103.5	100.2	98.5
67.5°	98.0	100.9	102.5	103.4	102.5	100.9	98.0	94.0	90.7	87.1	85.1
70°	89.1	92.0	94.2	95.0	94.2	92.0	89.1	84.4	81.6	78.2	76.5
72.5°	80.4	82.9	84.7	85.6	84.7	82.9	80.4	76.0	72.6	69.3	67.0
75°	65.1	68.6	70.3	71.2	70.3	68.6	65.1	62.7	58.9	55.4	53.5
77.5°	50.2	53.3	54.4	54.9	54.4	53.3	50.2	47.4	44.5	41.9	40.1
80°	40.3	42.2	43.5	43.7	43.5	42.2	40.3	38.1	35.8	33.3	31.6
82.5°	31.0	32.5	32.9	33.4	32.9	32.5	31.0	29.0	27.1	25.2	23.8
85°	17.0	17.7	17.9	17.7	17.9	17.7	17.0	15.7	14.7	13.8	13.2
87.5°	6.8	6.7	6.8	7.1	6.8	6.7	6.8	6.5	6.6	6.2	5.9
90°	6.4	6.4	6.6	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2
92.5°	20.0	19.2	18.8	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0
95°	83.2	74.6	72.3	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2
97.5°	191.8	175.7	167.4	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5
100°	260.7	240.0	229.3	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4
102.5°	322.8	308.0	296.4	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8
105°	400.5	391.0	385.2	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8
107.5°	433.2	433.2	431.2	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2
110°	437.1	442.5	444.6	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	426.2	435.7	440.7	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4
115°	399.7	413.4	421.5	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6
117.5°	370.1	384.4	392.4	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3
120°	351.0	364.8	372.6	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0
122.5°	334.8	347.5	355.3	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8
125°	314.1	325.9	332.2	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7
127.5°	298.4	308.8	314.8	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5
130°	288.7	298.2	304.0	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7
132.5°	278.6	288.0	293.3	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9
135°	262.0	271.4	276.6	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5
137.5°	244.8	253.5	258.3	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2
140°	234.2	241.7	246.1	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7
142.5°	224.1	230.5	234.6	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7
145°	210.3	215.2	218.4	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8
147.5°	199.6	203.5	205.3	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1
150°	193.3	196.8	198.0	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0
152.5°	188.0	190.8	191.9	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7
155°	180.9	183.0	183.8	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2
157.5°	174.5	176.1	176.9	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8
160°	170.3	171.7	172.3	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5
162.5°	166.4	167.5	167.7	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9
165°	160.8	161.3	161.3	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4
167.5°	155.4	155.9	155.6	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1
170°	152.1	152.5	152.5	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3
172.5°	149.1	149.7	149.2	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2
175°	145.5	145.8	145.2	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0
177.5°	143.4	143.6	142.9	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	424.4	426.2	428.4	430.2	433.2	434.5	436.2	437.5	439.9	442.2	444.9
5°	395.8	399.0	403.3	408.1	413.5	417.3	422.6	425.7	432.2	438.0	443.7
7.5°	369.9	373.8	379.9	386.0	393.1	399.6	406.2	413.5	421.7	431.4	439.4
10°	352.1	357.3	363.9	371.5	380.2	387.7	396.6	404.5	414.5	425.7	436.3
12.5°	337.9	342.4	349.8	357.0	366.3	375.5	384.7	395.1	406.8	419.3	432.5
15°	318.4	322.1	328.2	338.2	347.6	356.6	370.4	380.2	394.8	408.8	424.9
17.5°	301.7	306.4	311.4	320.0	329.8	341.0	353.4	365.7	379.8	397.5	415.5
20°	291.5	295.2	301.0	307.6	318.0	329.3	341.0	353.4	370.7	389.1	408.5
22.5°	280.3	284.4	291.0	298.2	306.9	317.7	330.6	344.2	362.3	380.3	401.4
25°	267.2	269.9	276.0	282.4	291.1	300.3	313.6	328.7	346.7	367.2	388.7
27.5°	254.8	257.2	262.7	268.3	276.1	287.1	299.1	314.3	331.2	352.0	375.8
30°	245.8	248.5	253.4	259.4	266.9	276.5	288.8	303.1	321.2	341.5	366.4
32.5°	238.1	240.5	244.2	250.2	257.6	266.9	278.3	292.9	311.0	331.6	356.0
35°	226.2	228.9	231.7	236.4	242.8	251.8	264.3	278.1	295.4	315.4	337.8
37.5°	214.4	217.3	219.8	224.0	229.8	237.8	248.6	262.9	278.6	297.8	319.4
40°	207.0	209.3	211.4	215.9	221.8	229.3	239.3	252.1	268.6	286.6	304.4
42.5°	199.7	201.8	203.5	207.5	212.9	220.0	229.6	242.1	257.5	274.2	290.0
45°	188.0	189.3	191.4	194.8	199.1	205.7	214.9	226.1	239.0	254.9	266.8
47.5°	175.5	177.5	179.2	182.1	185.7	192.2	201.1	210.5	222.3	234.1	242.4
50°	165.8	167.9	170.3	173.2	176.5	182.5	190.6	200.2	210.3	219.3	226.4
52.5°	156.7	158.7	161.3	164.0	168.1	173.2	180.1	188.7	198.5	205.0	210.9
55°	143.3	144.3	147.3	149.9	153.9	157.7	164.7	172.2	178.2	183.1	188.0
57.5°	129.7	130.9	132.7	135.1	139.0	143.4	148.3	155.0	158.5	161.0	164.9
60°	120.9	121.3	122.5	125.3	128.3	132.2	137.9	142.6	145.3	147.3	150.5
62.5°	111.3	111.4	113.2	115.4	117.6	121.9	126.5	130.3	132.4	133.5	136.5
65°	97.8	97.4	98.5	100.2	102.9	105.7	109.7	113.0	112.8	114.0	115.9
67.5°	84.0	83.6	83.6	85.2	87.3	89.8	92.5	94.6	94.6	96.0	97.0
70°	74.6	73.5	74.2	75.6	76.5	78.6	81.6	82.3	82.5	83.2	84.2
72.5°	65.0	64.6	65.1	65.7	66.4	68.0	70.6	71.0	71.1	71.5	73.1
75°	51.6	51.3	50.9	51.4	52.2	53.3	54.2	55.0	54.8	55.0	56.2
77.5°	38.7	37.7	37.4	37.7	37.9	38.6	39.6	39.5	39.7	39.7	40.9
80°	30.7	29.2	29.0	29.0	29.2	29.6	29.9	30.3	29.8	30.3	30.7
82.5°	22.6	21.7	21.6	21.4	21.5	21.6	21.9	22.0	21.9	22.2	22.4
85°	12.5	12.1	11.5	11.9	11.7	11.1	11.5	10.9	10.8	10.9	11.1
87.5°	5.2	5.3	4.9	4.8	4.6	4.6	4.2	4.0	3.7	3.8	4.2
90°	4.9	4.6	4.0	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3
92.5°	75.2	92.9	94.4	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5
95°	249.8	255.3	208.3	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5
97.5°	316.1	272.6	186.1	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8
100°	332.2	260.2	166.0	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1
102.5°	322.5	238.3	150.7	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0
105°	291.6	208.9	136.0	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5
107.5°	260.0	188.7	129.8	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9
110°	242.1	179.2	127.9	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	228.7	173.7	127.9	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5
115°	214.1	167.7	128.8	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2
117.5°	205.4	164.8	130.7	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1
120°	200.6	163.4	132.6	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7
122.5°	196.4	162.2	134.1	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6
125°	190.8	160.8	136.9	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7
127.5°	185.6	160.1	139.9	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4
130°	182.1	159.6	141.8	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5
132.5°	179.4	159.6	143.8	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7
135°	176.0	159.6	146.7	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5
137.5°	173.1	160.0	149.3	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2
140°	171.7	160.2	150.4	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0
142.5°	170.6	160.5	151.1	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3
145°	168.8	160.2	151.8	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1
147.5°	167.1	159.5	152.1	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1
150°	165.7	158.7	152.1	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1
152.5°	164.0	157.8	151.9	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4
155°	161.3	156.2	151.2	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6
157.5°	158.8	154.4	150.5	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5
160°	156.8	153.3	149.9	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0
162.5°	154.9	151.9	149.1	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0
165°	152.1	149.9	148.1	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1
167.5°	149.4	147.8	146.5	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3
170°	147.8	146.7	145.8	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6
172.5°	146.2	145.3	144.9	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5
175°	144.1	143.8	143.8	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6
177.5°	143.2	142.9	142.9	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	446.3	448.3	449.7	452.2	454.4	455.6	456.6	457.5	458.6	459.5	462.1
5°	449.1	454.0	458.2	464.6	470.4	474.9	479.8	484.1	487.7	492.8	496.8
7.5°	447.8	456.6	465.7	475.6	485.8	495.1	503.9	511.9	519.3	528.2	536.0
10°	446.7	458.5	470.2	483.6	497.3	509.0	519.9	531.1	539.2	550.5	560.1
12.5°	445.8	459.7	473.9	489.9	505.0	521.5	536.1	544.2	556.5	565.6	577.0
15°	442.0	460.4	479.8	497.9	519.4	534.7	547.5	563.3	574.8	586.3	598.7
17.5°	435.1	456.1	477.8	501.5	522.0	538.4	555.0	570.2	583.9	599.3	614.8
20°	431.9	452.9	477.8	502.1	522.2	539.3	556.3	573.1	588.2	608.0	625.8
22.5°	425.3	450.6	473.5	497.3	518.0	536.6	555.9	574.9	594.9	617.3	639.7
25°	413.5	439.1	463.4	486.8	507.7	531.1	551.6	577.1	602.7	632.3	660.1
27.5°	401.2	425.7	448.0	470.6	495.0	521.5	548.0	576.9	610.5	647.8	687.1
30°	391.3	414.5	436.1	459.3	484.7	514.5	543.7	578.0	616.8	658.8	705.6
32.5°	379.7	401.0	422.1	446.6	474.3	505.7	539.8	577.4	624.0	671.7	719.8
35°	359.8	377.7	399.4	425.6	456.8	492.8	532.2	576.7	630.1	685.0	725.5
37.5°	336.3	352.9	375.8	404.5	437.2	475.9	522.6	575.4	632.2	675.9	688.9
40°	320.4	335.9	359.6	389.4	422.9	463.8	515.0	570.8	625.8	653.7	642.9
42.5°	303.5	319.8	342.9	372.3	408.5	453.0	505.6	561.3	607.5	618.0	580.9
45°	277.0	293.7	316.5	346.3	385.1	433.3	488.1	538.8	565.3	546.3	488.9
47.5°	252.2	267.9	289.0	319.8	359.8	409.7	462.4	502.9	505.0	459.6	398.2
50°	235.3	249.8	271.1	301.8	341.5	392.1	439.7	471.6	457.2	405.8	346.8
52.5°	218.7	232.9	253.9	284.3	323.6	369.9	414.3	436.6	409.6	356.8	306.5
55°	194.8	207.2	227.8	255.8	293.1	336.1	373.7	381.5	346.4	294.5	253.6
57.5°	171.5	183.0	201.7	227.6	261.7	299.7	329.2	327.5	290.5	245.9	213.4
60°	155.6	166.9	183.5	208.7	239.9	272.6	297.8	291.8	255.1	216.6	189.3
62.5°	141.5	151.6	167.2	189.3	217.7	248.0	268.7	259.8	223.9	190.3	168.7
65°	120.6	129.1	142.4	161.3	184.8	209.9	225.9	214.4	183.7	157.5	140.1
67.5°	100.6	107.5	118.6	133.7	153.8	173.9	183.6	172.1	147.5	128.4	115.5
70°	88.0	94.0	102.6	116.0	133.5	150.5	157.8	147.5	126.4	110.0	100.8
72.5°	75.3	80.3	87.9	100.0	114.0	128.7	135.1	125.2	107.9	94.0	85.4
75°	58.2	61.6	66.9	75.2	86.3	98.0	101.5	92.9	81.8	71.4	65.7
77.5°	41.7	44.5	48.5	53.7	61.6	69.1	72.2	67.2	58.6	52.0	47.4
80°	32.0	33.5	36.9	41.3	47.5	52.2	54.2	51.0	45.0	40.1	36.5
82.5°	22.8	24.4	26.3	29.9	33.9	37.1	39.3	37.2	32.9	28.9	26.9
85°	11.1	12.1	13.2	14.7	17.7	19.6	19.4	18.1	16.4	14.9	13.8
87.5°	4.0	4.3	4.9	5.7	6.3	6.9	7.4	7.2	6.7	6.3	5.9
90°	0.6	1.1	1.7	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2
92.5°	4.2	6.7	10.3	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0
95°	9.8	12.1	15.2	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2
97.5°	16.1	17.8	21.0	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5
100°	20.7	21.9	25.0	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4
102.5°	25.4	26.3	29.7	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8
105°	32.5	34.0	36.9	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8
107.5°	40.5	41.9	44.3	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2
110°	45.8	47.0	49.6	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3





TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.0	54.6	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4
115°	58.8	59.7	62.2	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6
117.5°	66.0	66.9	69.5	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3
120°	70.6	71.7	74.4	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0
122.5°	75.2	76.1	78.8	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8
125°	81.3	82.7	85.3	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7
127.5°	86.3	88.1	91.5	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5
130°	89.4	91.6	95.4	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7
132.5°	91.9	94.7	98.8	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9
135°	95.6	99.1	103.7	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5
137.5°	100.1	103.3	107.9	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2
140°	102.9	106.3	111.0	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7
142.5°	105.8	109.1	113.7	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7
145°	110.6	113.5	117.6	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8
147.5°	115.4	118.0	121.7	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1
150°	118.7	120.7	124.5	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0
152.5°	121.7	123.5	126.8	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7
155°	125.6	127.3	130.2	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2
157.5°	129.4	130.8	133.2	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8
160°	131.7	132.8	134.9	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5
162.5°	133.8	134.9	136.7	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9
165°	136.6	137.5	138.8	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4
167.5°	138.9	139.5	140.2	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1
170°	140.3	140.6	141.2	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3
172.5°	141.0	141.3	141.9	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2
175°	142.0	142.4	142.6	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0
177.5°	142.7	142.7	142.9	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	443.8	443.8	443.8	443.8	443.8	443.8	443.8
2.5°	464.2	465.4	468.0	467.1	468.2	468.9	469.4
5°	501.7	507.7	510.4	510.0	514.0	513.0	512.0
7.5°	544.0	550.3	553.9	558.3	560.8	561.1	563.3
10°	568.0	576.3	579.7	584.4	587.4	589.1	588.9
12.5°	586.4	592.9	600.5	602.8	606.8	609.0	608.2
15°	608.5	618.9	626.8	630.7	635.9	637.3	639.4
17.5°	628.3	642.1	651.3	663.7	668.3	671.2	669.4
20°	643.2	661.5	670.7	685.3	693.5	697.8	696.3
22.5°	660.8	680.6	697.7	710.4	722.7	728.6	729.8
25°	691.0	718.1	743.2	759.9	775.2	778.8	786.7
27.5°	724.8	756.8	783.6	801.2	811.8	815.8	818.3
30°	746.0	777.9	798.0	809.3	812.7	812.4	812.0
32.5°	756.4	776.3	780.2	777.1	769.3	762.7	755.9
35°	741.7	726.8	704.6	676.0	654.8	633.6	631.4
37.5°	667.1	619.5	582.4	541.1	517.3	502.6	492.4
40°	596.8	542.7	497.9	463.1	438.8	429.2	419.7
42.5°	520.6	468.9	429.2	400.1	381.8	371.1	363.7
45°	422.9	377.3	346.3	325.1	310.6	302.4	297.7
47.5°	346.6	312.8	286.4	271.2	261.2	254.8	254.8
50°	305.6	273.4	255.8	243.8	235.1	230.0	231.0
52.5°	269.2	245.2	230.2	220.1	213.7	210.6	210.4
55°	225.1	207.8	198.0	190.6	186.3	182.7	183.5
57.5°	192.6	178.0	171.4	165.3	162.2	160.9	158.7
60°	172.4	161.1	155.4	150.5	147.5	146.3	144.3
62.5°	154.4	145.5	140.1	136.1	133.4	133.0	131.3
65°	129.8	123.0	118.1	116.3	113.4	112.7	112.7
67.5°	107.0	102.2	98.3	96.6	95.4	95.6	94.7
70°	92.7	88.7	86.3	84.4	83.5	83.6	82.9
72.5°	81.1	76.6	74.5	73.4	72.2	72.6	72.3
75°	61.4	59.2	58.0	56.9	56.2	55.8	55.4
77.5°	45.1	43.1	42.2	41.6	41.7	40.8	41.5
80°	34.8	33.2	32.6	31.6	31.5	31.5	31.3
82.5°	25.5	24.5	24.1	23.4	23.0	23.3	22.8
85°	13.2	12.5	12.2	12.2	11.9	11.5	12.5
87.5°	6.0	5.4	5.5	5.3	5.3	5.2	5.0
90°	5.5	5.8	6.4	6.4	6.4	6.6	6.6
92.5°	37.0	27.9	23.6	20.0	19.2	18.8	18.3
95°	163.4	127.9	103.7	83.2	74.6	72.3	67.8
97.5°	277.9	243.3	209.6	191.8	175.7	167.4	163.6
100°	340.3	310.6	280.6	260.7	240.0	229.3	224.8
102.5°	378.5	364.4	344.1	322.8	308.0	296.4	293.0
105°	400.2	412.9	409.8	400.5	391.0	385.2	381.8
107.5°	380.9	413.4	428.5	433.2	433.2	431.2	428.9
110°	359.1	399.7	424.1	437.1	442.5	444.6	444.6



TEST NUMBER: P333117-930

CATALOG NUMBER: S125DIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	337.4	378.5	407.3	426.2	435.7	440.7	442.8
115°	306.3	345.8	377.2	399.7	413.4	421.5	425.3
117.5°	284.8	318.8	347.6	370.1	384.4	392.4	394.7
120°	272.6	304.3	329.6	351.0	364.8	372.6	374.9
122.5°	263.8	292.0	315.8	334.8	347.5	355.3	357.3
125°	252.1	277.2	297.9	314.1	325.9	332.2	335.1
127.5°	240.9	264.3	283.7	298.4	308.8	314.8	316.1
130°	233.1	255.6	274.3	288.7	298.2	304.0	305.7
132.5°	225.8	246.1	264.2	278.6	288.0	293.3	295.3
135°	214.3	232.8	249.2	262.0	271.4	276.6	278.3
137.5°	204.2	219.6	233.5	244.8	253.5	258.3	260.2
140°	198.2	211.5	223.6	234.2	241.7	246.1	247.5
142.5°	193.1	204.6	215.1	224.1	230.5	234.6	235.8
145°	186.7	195.7	203.4	210.3	215.2	218.4	219.6
147.5°	181.3	188.3	194.1	199.6	203.5	205.3	205.9
150°	178.4	183.8	189.0	193.3	196.8	198.0	198.2
152.5°	175.4	180.3	184.4	188.0	190.8	191.9	192.2
155°	170.9	174.9	178.1	180.9	183.0	183.8	184.1
157.5°	166.6	169.7	172.2	174.5	176.1	176.9	176.8
160°	163.4	166.2	168.3	170.3	171.7	172.3	172.0
162.5°	160.6	163.1	164.9	166.4	167.5	167.7	167.6
165°	156.5	158.2	159.6	160.8	161.3	161.3	161.3
167.5°	152.5	153.8	154.8	155.4	155.9	155.6	155.6
170°	150.1	151.0	151.6	152.1	152.5	152.5	152.1
172.5°	148.1	148.7	149.0	149.1	149.7	149.2	148.9
175°	145.0	145.5	145.5	145.5	145.8	145.2	145.0
177.5°	143.6	143.6	143.6	143.4	143.6	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9

(END OF REPORT)