

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333179-930

Luminaire Tested: **S125DIP-S610D810U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333179-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S610D810U930-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4346.8 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46				40	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4713	4713	4713	4713
5°	5457	4729	4140	4729
10°	6349	4704	3628	4704
15°	7029	4670	3346	4670
20°	7867	4615	3120	4615
25°	9217	4554	3011	4554
30°	9955	4492	2915	4492
35°	8185	4378	2852	4378
40°	5818	4220	2783	4220
45°	4469	4005	2744	4005
50°	3815	3741	2739	3741
55°	3397	3480	2762	3480
60°	3065	3196	2833	3196
65°	2830	2911	2905	2911
70°	2572	2613	2948	2613
75°	2273	2303	2922	2303
80°	1912	1878	2670	1878
85°	1519	1356	2156	1356



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	1.6
10°-20°	209.2	4.8
20°-30°	339.6	7.8
30°-40°	414.3	9.5
40°-50°	376.9	8.7
50°-60°	300.2	6.9
60°-70°	209.1	4.8
70°-80°	111.5	2.6
80°-90°	29.9	0.7
90°-100°	54.9	1.3
100°-110°	162.0	3.7
110°-120°	274.4	6.3
120°-130°	361.2	8.3
130°-140°	404.7	9.3
140°-150°	396.7	9.1
150°-160°	333.1	7.7
160°-170°	221.5	5.1
170°-180°	77.5	1.8
0°-30°	619.0	14.2
0°-40°	1033.3	23.8
0°-60°	1710.3	39.3
0°-90°	2060.8	47.4
90°-120°	491.4	11.3
90°-150°	1653.9	38.0
90°-180°	2286.0	52.6
0°-180°	4346.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	730	730	730	730	730	
5°	842	729	639	729	842	85
15°	1051	698	500	698	1051	301
25°	1293	639	422	639	1293	591
35°	1038	555	362	555	1038	635
45°	489	438	300	438	489	392
55°	302	309	245	309	302	272
65°	185	190	190	190	185	184
75°	91	92	117	92	91	98
85°	20	18	29	18	20	24
90°	15	1	15	1	15	10
95°	55	41	55	41	55	56
105°	158	145	158	145	158	168
115°	277	275	277	275	277	274
125°	404	401	404	401	404	360
135°	523	522	523	522	523	404
145°	634	632	634	632	634	396
155°	723	723	723	723	723	333
165°	784	786	784	786	784	221
175°	814	817	814	817	814	77
180°	819	819	819	819	819	



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7
2.5°	771.8	770.8	769.8	767.8	769.3	765.1	763.1	759.7	755.5	754.0	752.2
5°	841.8	843.3	844.9	838.4	839.0	834.7	824.8	816.7	810.2	801.8	796.0
7.5°	926.0	922.3	922.1	917.9	910.6	904.8	894.4	881.1	868.3	853.7	841.6
10°	968.2	968.5	965.7	960.7	953.0	947.4	933.8	920.8	905.0	886.4	873.1
12.5°	999.9	1001.2	997.7	991.0	987.2	974.7	964.0	948.5	929.8	914.9	894.6
15°	1051.2	1047.7	1045.3	1036.9	1030.4	1017.4	1000.4	984.2	963.8	944.9	926.0
17.5°	1100.6	1103.3	1098.7	1091.0	1070.9	1055.6	1032.8	1010.8	985.3	960.0	937.4
20°	1144.7	1147.2	1140.0	1126.7	1102.6	1087.4	1057.4	1028.8	999.5	966.9	942.2
22.5°	1199.7	1197.8	1188.1	1167.8	1147.0	1118.8	1086.4	1051.7	1014.8	978.0	945.1
25°	1293.4	1280.3	1274.5	1249.4	1221.8	1180.6	1136.0	1085.2	1039.4	990.8	948.7
27.5°	1345.2	1341.2	1334.6	1317.1	1288.2	1244.1	1191.6	1129.7	1064.9	1003.6	948.4
30°	1334.9	1335.5	1336.1	1330.5	1312.0	1278.8	1226.5	1159.8	1083.0	1014.0	950.2
32.5°	1242.7	1253.9	1264.8	1277.5	1282.7	1276.4	1243.6	1183.4	1104.4	1025.9	949.2
35°	1038.1	1041.5	1076.6	1111.3	1158.3	1194.9	1219.4	1192.7	1126.1	1036.0	948.0
37.5°	809.4	826.2	850.4	889.7	957.6	1018.4	1096.7	1132.6	1111.1	1039.3	945.8
40°	690.1	705.6	721.3	761.2	818.6	892.3	981.1	1057.0	1074.7	1028.8	938.4
42.5°	597.9	610.2	627.7	657.7	705.6	770.9	855.8	955.0	1015.9	998.7	922.8
45°	489.3	497.1	510.7	534.6	569.2	620.4	695.3	803.7	898.1	929.4	885.7
47.5°	418.8	418.8	429.4	445.9	470.9	514.3	569.7	654.7	755.5	830.2	826.7
50°	379.7	378.1	386.5	400.8	420.6	449.4	502.4	570.2	667.2	751.7	775.2
52.5°	346.0	346.2	351.3	361.8	378.5	403.1	442.6	503.8	586.6	673.4	717.7
55°	301.7	300.4	306.3	313.4	325.5	341.6	370.1	416.9	484.0	569.6	627.1
57.5°	261.1	264.4	266.8	271.7	281.8	292.5	316.6	350.9	404.2	477.6	538.5
60°	237.3	240.7	242.5	247.4	255.5	264.8	283.4	311.3	356.2	419.4	479.7
62.5°	215.9	218.6	219.2	223.6	230.2	239.3	253.9	277.3	312.8	368.0	427.2
65°	185.2	185.2	186.5	191.1	194.2	202.3	213.4	230.4	258.9	302.0	352.5
67.5°	155.6	157.1	156.8	158.8	161.7	168.0	175.9	190.0	211.1	242.5	282.9
70°	136.2	137.5	137.2	138.8	141.9	145.9	152.4	165.7	180.8	207.8	242.5
72.5°	119.0	119.4	118.6	120.7	122.5	126.0	133.3	140.4	154.6	177.3	205.9
75°	91.1	91.6	92.3	93.5	95.4	97.3	100.9	108.1	117.4	134.4	152.7
77.5°	68.2	67.1	68.6	68.4	69.5	70.8	74.1	77.9	85.5	96.3	110.5
80°	51.4	51.7	51.7	52.0	53.6	54.5	57.3	60.1	66.0	74.0	83.9
82.5°	37.5	38.3	37.8	38.4	39.7	40.4	41.9	44.2	47.6	54.0	61.1
85°	20.5	18.9	19.5	20.1	20.1	20.5	21.7	22.6	24.5	26.9	29.8
87.5°	9.0	9.5	9.6	9.5	9.6	9.5	10.4	10.3	10.8	11.5	12.2
90°	15.3	14.8	14.4	14.0	13.6	13.0	12.3	11.6	10.9	10.2	9.2
92.5°	30.1	29.8	29.4	29.2	28.9	28.2	27.3	26.3	25.4	24.5	23.2
95°	54.8	54.5	54.3	54.0	53.7	53.1	52.1	51.0	50.1	49.1	47.7
97.5°	83.2	83.0	82.8	82.6	82.4	81.9	81.0	80.1	79.1	78.2	76.2
100°	104.5	104.3	104.0	103.7	103.5	102.6	101.3	100.1	98.8	97.5	95.7
102.5°	126.0	125.6	125.1	124.8	124.4	123.5	122.1	120.7	119.4	118.0	117.0
105°	158.1	157.7	157.3	156.9	156.4	155.8	154.9	154.1	153.2	152.4	151.5
107.5°	191.0	191.0	191.0	191.1	191.1	190.9	190.5	190.0	189.6	189.2	188.6
110°	215.5	215.6	215.7	215.9	216.1	215.9	215.5	215.1	214.7	214.2	213.8



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	239.5	239.7	239.9	240.2	240.5	240.5	240.3	240.1	239.9	239.7	239.2
115°	277.4	277.4	277.6	277.8	277.9	278.0	278.2	278.3	278.4	278.6	278.3
117.5°	314.3	314.9	315.4	316.0	316.6	316.8	316.7	316.6	316.4	316.3	316.1
120°	339.8	340.4	341.0	341.5	342.1	342.3	342.3	342.3	342.3	342.3	342.2
122.5°	365.3	365.7	366.2	366.6	367.1	367.4	367.5	367.6	367.7	367.9	367.5
125°	403.6	403.7	403.8	404.0	404.1	404.3	404.6	404.9	405.2	405.4	405.3
127.5°	440.3	440.6	440.8	441.2	441.4	441.6	441.7	441.9	442.1	442.2	442.1
130°	464.7	465.0	465.3	465.6	465.9	466.1	466.3	466.4	466.5	466.7	466.4
132.5°	487.7	488.1	488.5	488.9	489.3	489.6	489.7	489.8	490.0	490.2	490.2
135°	523.4	524.0	524.6	525.1	525.7	525.9	525.9	525.9	525.9	525.9	525.8
137.5°	558.3	559.1	559.8	560.4	561.2	561.4	561.3	561.1	560.9	560.8	560.4
140°	580.8	581.5	582.2	582.9	583.6	583.8	583.5	583.3	583.0	582.7	582.3
142.5°	602.2	602.9	603.6	604.3	605.0	605.3	605.1	605.0	604.8	604.6	604.1
145°	634.3	634.8	635.2	635.6	636.0	636.3	636.3	636.3	636.3	636.3	635.9
147.5°	661.8	662.8	663.7	664.6	665.6	665.9	665.6	665.2	664.9	664.6	664.2
150°	682.2	682.4	682.7	683.0	683.3	683.5	683.5	683.5	683.5	683.5	682.9
152.5°	699.0	699.5	700.0	700.5	701.0	701.1	700.7	700.4	700.1	699.8	699.5
155°	722.9	723.7	724.4	725.0	725.8	725.9	725.3	724.7	724.1	723.6	723.4
157.5°	743.0	743.9	744.9	745.8	746.7	746.9	746.3	745.8	745.2	744.6	744.4
160°	756.8	757.4	758.1	758.9	759.6	759.6	759.0	758.6	758.0	757.4	757.2
162.5°	768.5	769.3	770.1	770.9	771.8	771.8	771.2	770.5	769.8	769.2	769.1
165°	784.2	785.0	785.9	786.7	787.6	787.7	787.2	786.6	786.0	785.5	785.3
167.5°	796.6	797.5	798.4	799.3	800.1	800.2	799.3	798.5	797.6	796.8	796.8
170°	803.3	804.3	805.3	806.2	807.2	807.3	806.5	805.6	804.8	803.9	803.9
172.5°	808.9	809.8	810.7	811.5	812.4	812.4	811.5	810.7	809.8	809.0	809.0
175°	814.2	815.1	816.1	817.1	818.1	818.2	817.3	816.4	815.6	814.7	814.7
177.5°	817.2	818.0	818.8	819.5	820.4	820.4	819.7	819.0	818.4	817.7	817.8
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7
2.5°	750.7	749.0	747.1	743.6	739.3	737.1	733.7	731.4	726.9	723.3	719.3
5°	788.8	780.8	773.4	763.8	753.3	746.4	738.3	729.4	720.1	710.5	699.9
7.5°	828.3	814.1	798.6	781.9	765.6	750.6	736.3	722.3	709.1	693.2	679.8
10°	854.8	836.8	817.7	795.0	773.1	753.8	734.3	717.3	699.9	681.3	665.0
12.5°	881.3	857.4	830.3	805.4	779.0	755.9	732.9	711.1	689.3	668.7	649.6
15°	900.0	879.0	853.9	818.6	788.8	756.9	726.6	698.4	672.1	649.1	625.0
17.5°	912.3	885.3	858.3	824.4	785.5	749.7	715.3	683.1	653.5	624.4	601.1
20°	914.6	886.7	858.5	825.4	785.5	744.5	710.2	671.5	639.5	609.5	581.0
22.5°	913.9	882.2	851.6	817.4	778.5	740.9	699.3	659.8	625.2	595.7	565.9
25°	906.9	873.1	834.7	800.3	761.9	721.9	679.8	639.0	603.6	569.9	540.5
27.5°	901.0	857.2	813.8	773.6	736.5	699.9	659.7	617.8	578.6	544.4	516.7
30°	893.8	845.8	796.9	755.0	717.0	681.3	643.3	602.4	561.5	528.1	498.3
32.5°	887.4	831.4	779.8	734.3	694.0	659.3	624.2	585.3	545.2	511.2	481.5
35°	875.0	810.2	751.1	699.6	656.6	621.0	591.6	555.3	518.4	485.6	457.1
37.5°	859.2	782.4	718.8	665.0	617.8	580.2	552.9	525.1	489.7	458.0	432.3
40°	846.8	762.5	695.3	640.2	591.3	552.2	526.8	500.5	471.1	441.6	414.4
42.5°	831.1	744.7	671.5	612.2	563.8	525.7	499.0	476.7	450.8	423.3	398.0
45°	802.5	712.3	633.1	569.2	520.3	482.8	455.3	438.5	419.1	393.1	371.7
47.5°	760.3	673.5	591.5	525.6	475.2	440.4	414.6	398.5	384.8	365.5	346.1
50°	722.8	644.5	561.5	496.2	445.6	410.7	386.9	372.3	360.5	345.6	329.2
52.5°	681.0	608.1	532.1	467.4	417.4	382.9	359.5	346.7	337.0	326.3	310.1
55°	614.5	552.5	481.9	420.6	374.5	340.7	320.2	309.1	301.0	293.0	283.1
57.5°	541.2	492.8	430.2	374.1	331.7	300.9	281.8	271.0	264.7	260.6	254.8
60°	489.7	448.2	394.3	343.2	301.7	274.4	255.8	247.4	242.2	238.8	234.5
62.5°	441.8	407.7	357.8	311.2	274.9	249.2	232.5	224.5	219.4	217.8	214.1
65°	371.4	345.0	303.9	265.1	234.2	212.1	198.2	190.5	187.4	185.5	185.8
67.5°	301.9	285.8	252.8	219.8	195.0	176.6	165.4	159.5	157.9	155.5	155.4
70°	259.5	247.4	219.6	190.8	168.8	154.6	144.6	138.4	136.9	135.7	135.3
72.5°	222.1	211.6	187.4	164.3	144.6	132.0	123.8	120.1	117.6	116.8	116.8
75°	167.0	161.0	141.9	123.6	110.0	101.3	95.7	92.3	90.4	90.1	90.4
77.5°	118.7	113.6	101.3	88.4	79.8	73.2	68.5	67.3	65.2	65.3	65.0
80°	89.2	85.8	78.0	67.8	60.7	55.1	52.7	50.5	49.9	48.9	49.9
82.5°	64.7	61.0	55.8	49.2	43.4	40.0	37.5	36.9	36.4	36.0	36.2
85°	31.9	32.2	29.1	24.1	21.7	19.8	18.3	18.3	17.9	17.7	17.9
87.5°	12.6	11.8	10.7	9.7	8.2	7.3	6.8	6.8	6.3	6.3	6.8
90°	8.2	7.3	6.2	5.1	4.1	2.9	1.8	0.7	1.8	2.9	4.1
92.5°	22.0	20.8	19.6	18.6	17.8	17.0	16.2	15.4	16.2	17.0	17.8
95°	46.2	44.8	43.5	42.6	42.3	42.0	41.7	41.4	41.7	42.0	42.3
97.5°	74.3	72.3	70.4	69.3	69.2	69.1	69.0	68.9	69.0	69.1	69.2
100°	93.8	92.0	90.2	89.3	89.3	89.3	89.3	89.3	89.3	89.3	89.3
102.5°	116.1	115.1	114.2	113.5	112.9	112.3	111.8	111.2	111.8	112.3	112.9
105°	150.7	149.9	149.0	148.2	147.5	146.8	146.1	145.4	146.1	146.8	147.5
107.5°	187.9	187.3	186.6	186.0	185.2	184.5	183.8	183.1	183.8	184.5	185.2
110°	213.4	213.0	212.5	212.0	211.2	210.5	209.9	209.1	209.9	210.5	211.2



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	238.6	238.1	237.6	237.1	236.8	236.4	236.0	235.6	236.0	236.4	236.8
115°	278.0	277.8	277.4	277.0	276.5	275.9	275.3	274.8	275.3	275.9	276.5
117.5°	315.8	315.6	315.4	315.0	314.8	314.5	314.3	314.1	314.3	314.5	314.8
120°	342.1	341.9	341.8	341.4	340.6	340.0	339.2	338.5	339.2	340.0	340.6
122.5°	367.1	366.7	366.4	366.1	365.8	365.6	365.3	365.0	365.3	365.6	365.8
125°	405.2	405.0	404.9	404.4	403.6	402.7	401.9	401.0	401.9	402.7	403.6
127.5°	441.8	441.6	441.5	441.2	440.7	440.2	439.8	439.3	439.8	440.2	440.7
130°	466.1	465.8	465.5	465.0	464.3	463.7	462.9	462.2	462.9	463.7	464.3
132.5°	490.2	490.3	490.3	489.8	488.6	487.5	486.3	485.2	486.3	487.5	488.6
135°	525.7	525.5	525.4	524.9	524.1	523.2	522.4	521.5	522.4	523.2	524.1
137.5°	560.1	559.9	559.5	559.0	558.2	557.3	556.5	555.7	556.5	557.3	558.2
140°	581.9	581.4	581.0	580.4	579.8	579.0	578.3	577.6	578.3	579.0	579.8
142.5°	603.6	603.0	602.5	601.9	601.3	600.7	600.1	599.6	600.1	600.7	601.3
145°	635.4	635.0	634.5	634.1	633.5	632.9	632.3	631.8	632.3	632.9	633.5
147.5°	663.9	663.6	663.2	662.8	662.6	662.3	661.9	661.6	661.9	662.3	662.6
150°	682.3	681.8	681.2	680.9	681.1	681.3	681.3	681.5	681.3	681.3	681.1
152.5°	699.3	699.0	698.9	698.6	698.5	698.2	698.1	697.8	698.1	698.2	698.5
155°	723.3	723.2	723.0	722.9	722.9	722.9	722.9	722.9	722.9	722.9	722.9
157.5°	744.4	744.2	744.0	744.1	744.4	744.8	745.1	745.4	745.1	744.8	744.4
160°	757.1	756.9	756.8	756.9	757.4	757.8	758.2	758.6	758.2	757.8	757.4
162.5°	769.1	769.0	769.0	769.2	769.5	769.7	770.1	770.4	770.1	769.7	769.5
165°	785.1	785.0	784.9	785.0	785.2	785.5	785.8	786.1	785.8	785.5	785.2
167.5°	796.8	796.8	796.8	797.0	797.6	798.2	798.7	799.3	798.7	798.2	797.6
170°	803.9	803.9	803.9	804.2	804.8	805.4	805.9	806.5	805.9	805.4	804.8
172.5°	809.0	809.0	809.0	809.3	809.8	810.4	811.0	811.5	811.0	810.4	809.8
175°	814.7	814.7	814.7	815.1	815.6	816.2	816.8	817.3	816.8	816.2	815.6
177.5°	817.9	818.1	818.2	818.4	818.9	819.4	819.8	820.3	819.8	819.4	818.9
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7
2.5°	717.1	714.3	712.1	707.1	704.4	700.7	697.7	700.9	697.5	699.0	696.8
5°	694.7	686.0	679.8	670.8	663.1	656.0	650.7	649.8	647.3	646.0	642.4
7.5°	667.8	657.0	646.3	634.5	624.6	614.6	608.1	602.8	599.2	594.6	591.4
10°	651.9	637.4	625.0	610.7	598.3	587.5	578.9	574.5	570.5	564.6	562.5
12.5°	632.3	617.3	602.2	586.9	575.1	563.0	555.5	549.0	546.3	539.6	538.9
15°	608.9	586.3	571.4	556.0	539.5	529.6	523.4	516.3	513.2	508.6	505.2
17.5°	580.9	560.7	542.1	526.1	512.0	503.7	495.9	491.1	485.8	482.7	477.1
20°	560.6	541.4	522.8	505.7	494.9	485.3	479.2	474.5	468.9	467.3	461.8
22.5°	543.5	522.3	504.4	490.2	478.3	467.5	460.8	457.6	453.8	449.0	447.9
25°	515.7	493.7	478.5	464.2	453.7	443.8	439.2	435.1	431.5	428.0	426.8
27.5°	491.6	472.0	454.0	441.1	431.9	422.9	418.8	413.9	411.2	408.5	405.1
30°	474.8	454.7	438.9	426.5	416.5	408.5	404.1	400.8	398.3	395.8	394.0
32.5°	457.5	438.8	423.5	411.4	401.5	395.4	391.5	389.1	386.4	383.4	381.1
35°	434.6	414.1	399.3	388.7	380.9	376.3	371.9	369.8	366.7	366.7	364.2
37.5°	408.7	391.0	377.9	368.3	361.3	357.2	352.5	351.1	349.0	347.7	346.9
40°	393.3	376.9	364.5	354.9	347.5	344.1	340.4	337.9	336.6	335.1	334.5
42.5°	377.5	361.8	349.9	341.0	334.6	331.7	328.2	326.5	324.0	322.0	321.6
45°	353.4	338.2	327.3	320.2	314.7	311.3	309.1	305.4	304.1	301.7	301.3
47.5°	330.5	315.9	305.3	299.5	294.6	291.8	288.4	284.7	283.2	282.0	281.9
50°	313.4	300.1	290.2	284.6	280.0	276.0	272.6	270.1	269.1	269.1	269.8
52.5°	296.1	284.8	276.3	269.5	265.1	260.8	257.7	256.2	254.8	256.2	257.4
55°	270.7	259.3	253.1	246.5	242.2	237.3	235.7	235.1	234.2	236.6	237.8
57.5°	243.8	235.8	228.5	222.1	218.2	215.3	213.2	212.9	214.6	215.7	219.8
60°	226.7	217.4	210.9	205.9	201.3	199.4	198.9	198.2	199.4	202.8	208.1
62.5°	207.9	200.3	193.3	189.6	186.2	183.1	183.0	183.4	185.8	189.7	195.0
65°	180.3	173.7	169.1	164.8	162.0	160.1	160.8	162.0	164.8	170.1	175.9
67.5°	152.2	147.7	143.6	140.1	137.4	137.4	138.0	139.9	143.2	149.2	154.6
70°	134.1	129.1	125.7	124.2	122.1	120.8	122.6	125.7	128.5	134.1	138.8
72.5°	116.0	111.8	109.2	108.1	107.1	106.2	106.8	110.1	113.9	119.5	124.9
75°	89.2	87.6	85.8	84.5	83.6	84.2	84.9	88.0	91.1	96.9	103.1
77.5°	65.1	63.5	62.4	62.0	61.6	61.9	63.6	65.9	69.0	73.2	77.9
80°	49.2	48.6	48.0	47.7	47.7	48.0	50.5	52.0	54.8	58.9	62.5
82.5°	35.9	35.5	35.4	35.3	35.5	35.6	37.1	39.1	41.4	44.5	47.7
85°	18.9	18.3	19.2	19.5	18.9	19.8	20.5	21.7	22.6	24.1	25.7
87.5°	7.3	7.9	7.9	8.3	8.6	9.2	9.1	10.3	10.9	11.5	11.4
90°	5.1	6.2	7.3	8.2	9.2	10.2	10.9	11.6	12.3	13.0	13.6
92.5°	18.6	19.6	20.8	22.0	23.2	24.5	25.4	26.3	27.3	28.2	28.9
95°	42.6	43.5	44.8	46.2	47.7	49.1	50.1	51.0	52.1	53.1	53.7
97.5°	69.3	70.4	72.3	74.3	76.2	78.2	79.1	80.1	81.0	81.9	82.4
100°	89.3	90.2	92.0	93.8	95.7	97.5	98.8	100.1	101.3	102.6	103.5
102.5°	113.5	114.2	115.1	116.1	117.0	118.0	119.4	120.7	122.1	123.5	124.4
105°	148.2	149.0	149.9	150.7	151.5	152.4	153.2	154.1	154.9	155.8	156.4
107.5°	186.0	186.6	187.3	187.9	188.6	189.2	189.6	190.0	190.5	190.9	191.1
110°	212.0	212.5	213.0	213.4	213.8	214.2	214.7	215.1	215.5	215.9	216.1



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	237.1	237.6	238.1	238.6	239.2	239.7	239.9	240.1	240.3	240.5	240.5
115°	277.0	277.4	277.8	278.0	278.3	278.6	278.4	278.3	278.2	278.0	277.9
117.5°	315.0	315.4	315.6	315.8	316.1	316.3	316.4	316.6	316.7	316.8	316.6
120°	341.4	341.8	341.9	342.1	342.2	342.3	342.3	342.3	342.3	342.3	342.1
122.5°	366.1	366.4	366.7	367.1	367.5	367.9	367.7	367.6	367.5	367.4	367.1
125°	404.4	404.9	405.0	405.2	405.3	405.4	405.2	404.9	404.6	404.3	404.1
127.5°	441.2	441.5	441.6	441.8	442.1	442.2	442.1	441.9	441.7	441.6	441.4
130°	465.0	465.5	465.8	466.1	466.4	466.7	466.5	466.4	466.3	466.1	465.9
132.5°	489.8	490.3	490.3	490.2	490.2	490.2	490.0	489.8	489.7	489.6	489.3
135°	524.9	525.4	525.5	525.7	525.8	525.9	525.9	525.9	525.9	525.9	525.7
137.5°	559.0	559.5	559.9	560.1	560.4	560.8	560.9	561.1	561.3	561.4	561.2
140°	580.4	581.0	581.4	581.9	582.3	582.7	583.0	583.3	583.5	583.8	583.6
142.5°	601.9	602.5	603.0	603.6	604.1	604.6	604.8	605.0	605.1	605.3	605.0
145°	634.1	634.5	635.0	635.4	635.9	636.3	636.3	636.3	636.3	636.3	636.0
147.5°	662.8	663.2	663.6	663.9	664.2	664.6	664.9	665.2	665.6	665.9	665.6
150°	680.9	681.2	681.8	682.3	682.9	683.5	683.5	683.5	683.5	683.5	683.3
152.5°	698.6	698.9	699.0	699.3	699.5	699.8	700.1	700.4	700.7	701.1	701.0
155°	722.9	723.0	723.2	723.3	723.4	723.6	724.1	724.7	725.3	725.9	725.8
157.5°	744.1	744.0	744.2	744.4	744.4	744.6	745.2	745.8	746.3	746.9	746.7
160°	756.9	756.8	756.9	757.1	757.2	757.4	758.0	758.6	759.0	759.6	759.6
162.5°	769.2	769.0	769.0	769.1	769.1	769.2	769.8	770.5	771.2	771.8	771.8
165°	785.0	784.9	785.0	785.1	785.3	785.5	786.0	786.6	787.2	787.7	787.6
167.5°	797.0	796.8	796.8	796.8	796.8	796.8	797.6	798.5	799.3	800.2	800.1
170°	804.2	803.9	803.9	803.9	803.9	803.9	804.8	805.6	806.5	807.3	807.2
172.5°	809.3	809.0	809.0	809.0	809.0	809.0	809.8	810.7	811.5	812.4	812.4
175°	815.1	814.7	814.7	814.7	814.7	814.7	815.6	816.4	817.3	818.2	818.1
177.5°	818.4	818.2	818.1	817.9	817.8	817.7	818.4	819.0	819.7	820.4	820.4
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7
2.5°	695.2	697.0	695.5	697.5	695.5	697.0	695.2	696.8	699.0	697.5	700.9
5°	640.8	638.0	639.8	638.6	639.8	638.0	640.8	642.4	646.0	647.3	649.8
7.5°	590.5	587.8	584.8	583.3	584.8	587.8	590.5	591.4	594.6	599.2	602.8
10°	559.1	555.6	555.3	553.2	555.3	555.6	559.1	562.5	564.6	570.5	574.5
12.5°	536.0	532.8	529.3	528.4	529.3	532.8	536.0	538.9	539.6	546.3	549.0
15°	503.3	500.8	498.6	500.5	498.6	500.8	503.3	505.2	508.6	513.2	516.3
17.5°	476.1	474.0	473.7	471.4	473.7	474.0	476.1	477.1	482.7	485.8	491.1
20°	459.0	457.5	458.0	454.0	458.0	457.5	459.0	461.8	467.3	468.9	474.5
22.5°	445.4	442.3	442.0	441.2	442.0	442.3	445.4	447.9	449.0	453.8	457.6
25°	424.0	422.5	420.9	422.5	420.9	422.5	424.0	426.8	428.0	431.5	435.1
27.5°	405.4	403.5	403.1	403.2	403.1	403.5	405.4	405.1	408.5	411.2	413.9
30°	394.0	390.9	391.2	390.9	391.2	390.9	394.0	394.0	395.8	398.3	400.8
32.5°	381.6	379.4	379.0	378.5	379.0	379.4	381.6	381.1	383.4	386.4	389.1
35°	363.3	363.3	361.7	361.7	361.7	363.3	363.3	364.2	366.7	366.7	369.8
37.5°	346.1	345.8	344.9	345.0	344.9	345.8	346.1	346.9	347.7	349.0	351.1
40°	333.2	333.0	332.0	330.1	332.0	333.0	333.2	334.5	335.1	336.6	337.9
42.5°	320.9	319.8	319.4	318.8	319.4	319.8	320.9	321.6	322.0	324.0	326.5
45°	301.3	301.3	300.8	300.4	300.8	301.3	301.3	301.3	301.7	304.1	305.4
47.5°	282.4	283.0	284.1	284.0	284.1	283.0	282.4	281.9	282.0	283.2	284.7
50°	271.0	271.3	272.2	272.6	272.2	271.3	271.0	269.8	269.1	269.1	270.1
52.5°	258.4	260.2	261.3	261.1	261.3	260.2	258.4	257.4	256.2	254.8	256.2
55°	240.7	242.8	245.0	245.3	245.0	242.8	240.7	237.8	236.6	234.2	235.1
57.5°	223.1	226.2	228.4	229.2	228.4	226.2	223.1	219.8	215.7	214.6	212.9
60°	211.2	215.2	218.0	219.3	218.0	215.2	211.2	208.1	202.8	199.4	198.2
62.5°	199.8	204.3	207.2	207.4	207.2	204.3	199.8	195.0	189.7	185.8	183.4
65°	181.2	185.8	188.3	190.1	188.3	185.8	181.2	175.9	170.1	164.8	162.0
67.5°	161.1	165.8	168.5	170.0	168.5	165.8	161.1	154.6	149.2	143.2	139.9
70°	146.5	151.2	154.8	156.1	154.8	151.2	146.5	138.8	134.1	128.5	125.7
72.5°	132.2	136.2	139.3	140.7	139.3	136.2	132.2	124.9	119.5	113.9	110.1
75°	107.1	112.8	115.5	117.1	115.5	112.8	107.1	103.1	96.9	91.1	88.0
77.5°	82.7	87.7	89.4	90.2	89.4	87.7	82.7	77.9	73.2	69.0	65.9
80°	66.3	69.4	71.6	71.8	71.6	69.4	66.3	62.5	58.9	54.8	52.0
82.5°	51.0	53.5	54.2	55.0	54.2	53.5	51.0	47.7	44.5	41.4	39.1
85°	27.9	29.1	29.4	29.1	29.4	29.1	27.9	25.7	24.1	22.6	21.7
87.5°	12.0	11.8	11.9	12.5	11.9	11.8	12.0	11.4	11.5	10.9	10.3
90°	14.0	14.4	14.8	15.3	14.8	14.4	14.0	13.6	13.0	12.3	11.6
92.5°	29.2	29.4	29.8	30.1	29.8	29.4	29.2	28.9	28.2	27.3	26.3
95°	54.0	54.3	54.5	54.8	54.5	54.3	54.0	53.7	53.1	52.1	51.0
97.5°	82.6	82.8	83.0	83.2	83.0	82.8	82.6	82.4	81.9	81.0	80.1
100°	103.7	104.0	104.3	104.5	104.3	104.0	103.7	103.5	102.6	101.3	100.1
102.5°	124.8	125.1	125.6	126.0	125.6	125.1	124.8	124.4	123.5	122.1	120.7
105°	156.9	157.3	157.7	158.1	157.7	157.3	156.9	156.4	155.8	154.9	154.1
107.5°	191.1	191.0	191.0	191.0	191.0	191.0	191.1	191.1	190.9	190.5	190.0
110°	215.9	215.7	215.6	215.5	215.6	215.7	215.9	216.1	215.9	215.5	215.1



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	240.2	239.9	239.7	239.5	239.7	239.9	240.2	240.5	240.5	240.3	240.1
115°	277.8	277.6	277.4	277.4	277.4	277.6	277.8	277.9	278.0	278.2	278.3
117.5°	316.0	315.4	314.9	314.3	314.9	315.4	316.0	316.6	316.8	316.7	316.6
120°	341.5	341.0	340.4	339.8	340.4	341.0	341.5	342.1	342.3	342.3	342.3
122.5°	366.6	366.2	365.7	365.3	365.7	366.2	366.6	367.1	367.4	367.5	367.6
125°	404.0	403.8	403.7	403.6	403.7	403.8	404.0	404.1	404.3	404.6	404.9
127.5°	441.2	440.8	440.6	440.3	440.6	440.8	441.2	441.4	441.6	441.7	441.9
130°	465.6	465.3	465.0	464.7	465.0	465.3	465.6	465.9	466.1	466.3	466.4
132.5°	488.9	488.5	488.1	487.7	488.1	488.5	488.9	489.3	489.6	489.7	489.8
135°	525.1	524.6	524.0	523.4	524.0	524.6	525.1	525.7	525.9	525.9	525.9
137.5°	560.4	559.8	559.1	558.3	559.1	559.8	560.4	561.2	561.4	561.3	561.1
140°	582.9	582.2	581.5	580.8	581.5	582.2	582.9	583.6	583.8	583.5	583.3
142.5°	604.3	603.6	602.9	602.2	602.9	603.6	604.3	605.0	605.3	605.1	605.0
145°	635.6	635.2	634.8	634.3	634.8	635.2	635.6	636.0	636.3	636.3	636.3
147.5°	664.6	663.7	662.8	661.8	662.8	663.7	664.6	665.6	665.9	665.6	665.2
150°	683.0	682.7	682.4	682.2	682.4	682.7	683.0	683.3	683.5	683.5	683.5
152.5°	700.5	700.0	699.5	699.0	699.5	700.0	700.5	701.0	701.1	700.7	700.4
155°	725.0	724.4	723.7	722.9	723.7	724.4	725.0	725.8	725.9	725.3	724.7
157.5°	745.8	744.9	743.9	743.0	743.9	744.9	745.8	746.7	746.9	746.3	745.8
160°	758.9	758.1	757.4	756.8	757.4	758.1	758.9	759.6	759.6	759.0	758.6
162.5°	770.9	770.1	769.3	768.5	769.3	770.1	770.9	771.8	771.8	771.2	770.5
165°	786.7	785.9	785.0	784.2	785.0	785.9	786.7	787.6	787.7	787.2	786.6
167.5°	799.3	798.4	797.5	796.6	797.5	798.4	799.3	800.1	800.2	799.3	798.5
170°	806.2	805.3	804.3	803.3	804.3	805.3	806.2	807.2	807.3	806.5	805.6
172.5°	811.5	810.7	809.8	808.9	809.8	810.7	811.5	812.4	812.4	811.5	810.7
175°	817.1	816.1	815.1	814.2	815.1	816.1	817.1	818.1	818.2	817.3	816.4
177.5°	819.5	818.8	818.0	817.2	818.0	818.8	819.5	820.4	820.4	819.7	819.0
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7
2.5°	697.7	700.7	704.4	707.1	712.1	714.3	717.1	719.3	723.3	726.9	731.4
5°	650.7	656.0	663.1	670.8	679.8	686.0	694.7	699.9	710.5	720.1	729.4
7.5°	608.1	614.6	624.6	634.5	646.3	657.0	667.8	679.8	693.2	709.1	722.3
10°	578.9	587.5	598.3	610.7	625.0	637.4	651.9	665.0	681.3	699.9	717.3
12.5°	555.5	563.0	575.1	586.9	602.2	617.3	632.3	649.6	668.7	689.3	711.1
15°	523.4	529.6	539.5	556.0	571.4	586.3	608.9	625.0	649.1	672.1	698.4
17.5°	495.9	503.7	512.0	526.1	542.1	560.7	580.9	601.1	624.4	653.5	683.1
20°	479.2	485.3	494.9	505.7	522.8	541.4	560.6	581.0	609.5	639.5	671.5
22.5°	460.8	467.5	478.3	490.2	504.4	522.3	543.5	565.9	595.7	625.2	659.8
25°	439.2	443.8	453.7	464.2	478.5	493.7	515.7	540.5	569.9	603.6	639.0
27.5°	418.8	422.9	431.9	441.1	454.0	472.0	491.6	516.7	544.4	578.6	617.8
30°	404.1	408.5	416.5	426.5	438.9	454.7	474.8	498.3	528.1	561.5	602.4
32.5°	391.5	395.4	401.5	411.4	423.5	438.8	457.5	481.5	511.2	545.2	585.3
35°	371.9	376.3	380.9	388.7	399.3	414.1	434.6	457.1	485.6	518.4	555.3
37.5°	352.5	357.2	361.3	368.3	377.9	391.0	408.7	432.3	458.0	489.7	525.1
40°	340.4	344.1	347.5	354.9	364.5	376.9	393.3	414.4	441.6	471.1	500.5
42.5°	328.2	331.7	334.6	341.0	349.9	361.8	377.5	398.0	423.3	450.8	476.7
45°	309.1	311.3	314.7	320.2	327.3	338.2	353.4	371.7	393.1	419.1	438.5
47.5°	288.4	291.8	294.6	299.5	305.3	315.9	330.5	346.1	365.5	384.8	398.5
50°	272.6	276.0	280.0	284.6	290.2	300.1	313.4	329.2	345.6	360.5	372.3
52.5°	257.7	260.8	265.1	269.5	276.3	284.8	296.1	310.1	326.3	337.0	346.7
55°	235.7	237.3	242.2	246.5	253.1	259.3	270.7	283.1	293.0	301.0	309.1
57.5°	213.2	215.3	218.2	222.1	228.5	235.8	243.8	254.8	260.6	264.7	271.0
60°	198.9	199.4	201.3	205.9	210.9	217.4	226.7	234.5	238.8	242.2	247.4
62.5°	183.0	183.1	186.2	189.6	193.3	200.3	207.9	214.1	217.8	219.4	224.5
65°	160.8	160.1	162.0	164.8	169.1	173.7	180.3	185.8	185.5	187.4	190.5
67.5°	138.0	137.4	137.4	140.1	143.6	147.7	152.2	155.4	155.5	157.9	159.5
70°	122.6	120.8	122.1	124.2	125.7	129.1	134.1	135.3	135.7	136.9	138.4
72.5°	106.8	106.2	107.1	108.1	109.2	111.8	116.0	116.8	116.8	117.6	120.1
75°	84.9	84.2	83.6	84.5	85.8	87.6	89.2	90.4	90.1	90.4	92.3
77.5°	63.6	61.9	61.6	62.0	62.4	63.5	65.1	65.0	65.3	65.2	67.3
80°	50.5	48.0	47.7	47.7	48.0	48.6	49.2	49.9	48.9	49.9	50.5
82.5°	37.1	35.6	35.5	35.3	35.4	35.5	35.9	36.2	36.0	36.4	36.9
85°	20.5	19.8	18.9	19.5	19.2	18.3	18.9	17.9	17.7	17.9	18.3
87.5°	9.1	9.2	8.6	8.3	7.9	7.9	7.3	6.8	6.3	6.3	6.8
90°	10.9	10.2	9.2	8.2	7.3	6.2	5.1	4.1	2.9	1.8	0.7
92.5°	25.4	24.5	23.2	22.0	20.8	19.6	18.6	17.8	17.0	16.2	15.4
95°	50.1	49.1	47.7	46.2	44.8	43.5	42.6	42.3	42.0	41.7	41.4
97.5°	79.1	78.2	76.2	74.3	72.3	70.4	69.3	69.2	69.1	69.0	68.9
100°	98.8	97.5	95.7	93.8	92.0	90.2	89.3	89.3	89.3	89.3	89.3
102.5°	119.4	118.0	117.0	116.1	115.1	114.2	113.5	112.9	112.3	111.8	111.2
105°	153.2	152.4	151.5	150.7	149.9	149.0	148.2	147.5	146.8	146.1	145.4
107.5°	189.6	189.2	188.6	187.9	187.3	186.6	186.0	185.2	184.5	183.8	183.1
110°	214.7	214.2	213.8	213.4	213.0	212.5	212.0	211.2	210.5	209.9	209.1



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	239.9	239.7	239.2	238.6	238.1	237.6	237.1	236.8	236.4	236.0	235.6
115°	278.4	278.6	278.3	278.0	277.8	277.4	277.0	276.5	275.9	275.3	274.8
117.5°	316.4	316.3	316.1	315.8	315.6	315.4	315.0	314.8	314.5	314.3	314.1
120°	342.3	342.3	342.2	342.1	341.9	341.8	341.4	340.6	340.0	339.2	338.5
122.5°	367.7	367.9	367.5	367.1	366.7	366.4	366.1	365.8	365.6	365.3	365.0
125°	405.2	405.4	405.3	405.2	405.0	404.9	404.4	403.6	402.7	401.9	401.0
127.5°	442.1	442.2	442.1	441.8	441.6	441.5	441.2	440.7	440.2	439.8	439.3
130°	466.5	466.7	466.4	466.1	465.8	465.5	465.0	464.3	463.7	462.9	462.2
132.5°	490.0	490.2	490.2	490.2	490.3	490.3	489.8	488.6	487.5	486.3	485.2
135°	525.9	525.9	525.8	525.7	525.5	525.4	524.9	524.1	523.2	522.4	521.5
137.5°	560.9	560.8	560.4	560.1	559.9	559.5	559.0	558.2	557.3	556.5	555.7
140°	583.0	582.7	582.3	581.9	581.4	581.0	580.4	579.8	579.0	578.3	577.6
142.5°	604.8	604.6	604.1	603.6	603.0	602.5	601.9	601.3	600.7	600.1	599.6
145°	636.3	636.3	635.9	635.4	635.0	634.5	634.1	633.5	632.9	632.3	631.8
147.5°	664.9	664.6	664.2	663.9	663.6	663.2	662.8	662.6	662.3	661.9	661.6
150°	683.5	683.5	682.9	682.3	681.8	681.2	680.9	681.1	681.3	681.3	681.5
152.5°	700.1	699.8	699.5	699.3	699.0	698.9	698.6	698.5	698.2	698.1	697.8
155°	724.1	723.6	723.4	723.3	723.2	723.0	722.9	722.9	722.9	722.9	722.9
157.5°	745.2	744.6	744.4	744.4	744.2	744.0	744.1	744.4	744.8	745.1	745.4
160°	758.0	757.4	757.2	757.1	756.9	756.8	756.9	757.4	757.8	758.2	758.6
162.5°	769.8	769.2	769.1	769.1	769.0	769.0	769.2	769.5	769.7	770.1	770.4
165°	786.0	785.5	785.3	785.1	785.0	784.9	785.0	785.2	785.5	785.8	786.1
167.5°	797.6	796.8	796.8	796.8	796.8	796.8	797.0	797.6	798.2	798.7	799.3
170°	804.8	803.9	803.9	803.9	803.9	803.9	804.2	804.8	805.4	805.9	806.5
172.5°	809.8	809.0	809.0	809.0	809.0	809.0	809.3	809.8	810.4	811.0	811.5
175°	815.6	814.7	814.7	814.7	814.7	814.7	815.1	815.6	816.2	816.8	817.3
177.5°	818.4	817.7	817.8	817.9	818.1	818.2	818.4	818.9	819.4	819.8	820.3
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7	729.7
2.5°	733.7	737.1	739.3	743.6	747.1	749.0	750.7	752.2	754.0	755.5	759.7
5°	738.3	746.4	753.3	763.8	773.4	780.8	788.8	796.0	801.8	810.2	816.7
7.5°	736.3	750.6	765.6	781.9	798.6	814.1	828.3	841.6	853.7	868.3	881.1
10°	734.3	753.8	773.1	795.0	817.7	836.8	854.8	873.1	886.4	905.0	920.8
12.5°	732.9	755.9	779.0	805.4	830.3	857.4	881.3	894.6	914.9	929.8	948.5
15°	726.6	756.9	788.8	818.6	853.9	879.0	900.0	926.0	944.9	963.8	984.2
17.5°	715.3	749.7	785.5	824.4	858.3	885.3	912.3	937.4	960.0	985.3	1010.8
20°	710.2	744.5	785.5	825.4	858.5	886.7	914.6	942.2	966.9	999.5	1028.8
22.5°	699.3	740.9	778.5	817.4	851.6	882.2	913.9	945.1	978.0	1014.8	1051.7
25°	679.8	721.9	761.9	800.3	834.7	873.1	906.9	948.7	990.8	1039.4	1085.2
27.5°	659.7	699.9	736.5	773.6	813.8	857.2	901.0	948.4	1003.6	1064.9	1129.7
30°	643.3	681.3	717.0	755.0	796.9	845.8	893.8	950.2	1014.0	1083.0	1159.8
32.5°	624.2	659.3	694.0	734.3	779.8	831.4	887.4	949.2	1025.9	1104.4	1183.4
35°	591.6	621.0	656.6	699.6	751.1	810.2	875.0	948.0	1036.0	1126.1	1192.7
37.5°	552.9	580.2	617.8	665.0	718.8	782.4	859.2	945.8	1039.3	1111.1	1132.6
40°	526.8	552.2	591.3	640.2	695.3	762.5	846.8	938.4	1028.8	1074.7	1057.0
42.5°	499.0	525.7	563.8	612.2	671.5	744.7	831.1	922.8	998.7	1015.9	955.0
45°	455.3	482.8	520.3	569.2	633.1	712.3	802.5	885.7	929.4	898.1	803.7
47.5°	414.6	440.4	475.2	525.6	591.5	673.5	760.3	826.7	830.2	755.5	654.7
50°	386.9	410.7	445.6	496.2	561.5	644.5	722.8	775.2	751.7	667.2	570.2
52.5°	359.5	382.9	417.4	467.4	532.1	608.1	681.0	717.7	673.4	586.6	503.8
55°	320.2	340.7	374.5	420.6	481.9	552.5	614.5	627.1	569.6	484.0	416.9
57.5°	281.8	300.9	331.7	374.1	430.2	492.8	541.2	538.5	477.6	404.2	350.9
60°	255.8	274.4	301.7	343.2	394.3	448.2	489.7	479.7	419.4	356.2	311.3
62.5°	232.5	249.2	274.9	311.2	357.8	407.7	441.8	427.2	368.0	312.8	277.3
65°	198.2	212.1	234.2	265.1	303.9	345.0	371.4	352.5	302.0	258.9	230.4
67.5°	165.4	176.6	195.0	219.8	252.8	285.8	301.9	282.9	242.5	211.1	190.0
70°	144.6	154.6	168.8	190.8	219.6	247.4	259.5	242.5	207.8	180.8	165.7
72.5°	123.8	132.0	144.6	164.3	187.4	211.6	222.1	205.9	177.3	154.6	140.4
75°	95.7	101.3	110.0	123.6	141.9	161.0	167.0	152.7	134.4	117.4	108.1
77.5°	68.5	73.2	79.8	88.4	101.3	113.6	118.7	110.5	96.3	85.5	77.9
80°	52.7	55.1	60.7	67.8	78.0	85.8	89.2	83.9	74.0	66.0	60.1
82.5°	37.5	40.0	43.4	49.2	55.8	61.0	64.7	61.1	54.0	47.6	44.2
85°	18.3	19.8	21.7	24.1	29.1	32.2	31.9	29.8	26.9	24.5	22.6
87.5°	6.8	7.3	8.2	9.7	10.7	11.8	12.6	12.2	11.5	10.8	10.3
90°	1.8	2.9	4.1	5.1	6.2	7.3	8.2	9.2	10.2	10.9	11.6
92.5°	16.2	17.0	17.8	18.6	19.6	20.8	22.0	23.2	24.5	25.4	26.3
95°	41.7	42.0	42.3	42.6	43.5	44.8	46.2	47.7	49.1	50.1	51.0
97.5°	69.0	69.1	69.2	69.3	70.4	72.3	74.3	76.2	78.2	79.1	80.1
100°	89.3	89.3	89.3	89.3	90.2	92.0	93.8	95.7	97.5	98.8	100.1
102.5°	111.8	112.3	112.9	113.5	114.2	115.1	116.1	117.0	118.0	119.4	120.7
105°	146.1	146.8	147.5	148.2	149.0	149.9	150.7	151.5	152.4	153.2	154.1
107.5°	183.8	184.5	185.2	186.0	186.6	187.3	187.9	188.6	189.2	189.6	190.0
110°	209.9	210.5	211.2	212.0	212.5	213.0	213.4	213.8	214.2	214.7	215.1



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	236.0	236.4	236.8	237.1	237.6	238.1	238.6	239.2	239.7	239.9	240.1
115°	275.3	275.9	276.5	277.0	277.4	277.8	278.0	278.3	278.6	278.4	278.3
117.5°	314.3	314.5	314.8	315.0	315.4	315.6	315.8	316.1	316.3	316.4	316.6
120°	339.2	340.0	340.6	341.4	341.8	341.9	342.1	342.2	342.3	342.3	342.3
122.5°	365.3	365.6	365.8	366.1	366.4	366.7	367.1	367.5	367.9	367.7	367.6
125°	401.9	402.7	403.6	404.4	404.9	405.0	405.2	405.3	405.4	405.2	404.9
127.5°	439.8	440.2	440.7	441.2	441.5	441.6	441.8	442.1	442.2	442.1	441.9
130°	462.9	463.7	464.3	465.0	465.5	465.8	466.1	466.4	466.7	466.5	466.4
132.5°	486.3	487.5	488.6	489.8	490.3	490.3	490.2	490.2	490.2	490.0	489.8
135°	522.4	523.2	524.1	524.9	525.4	525.5	525.7	525.8	525.9	525.9	525.9
137.5°	556.5	557.3	558.2	559.0	559.5	559.9	560.1	560.4	560.8	560.9	561.1
140°	578.3	579.0	579.8	580.4	581.0	581.4	581.9	582.3	582.7	583.0	583.3
142.5°	600.1	600.7	601.3	601.9	602.5	603.0	603.6	604.1	604.6	604.8	605.0
145°	632.3	632.9	633.5	634.1	634.5	635.0	635.4	635.9	636.3	636.3	636.3
147.5°	661.9	662.3	662.6	662.8	663.2	663.6	663.9	664.2	664.6	664.9	665.2
150°	681.3	681.3	681.1	680.9	681.2	681.8	682.3	682.9	683.5	683.5	683.5
152.5°	698.1	698.2	698.5	698.6	698.9	699.0	699.3	699.5	699.8	700.1	700.4
155°	722.9	722.9	722.9	722.9	723.0	723.2	723.3	723.4	723.6	724.1	724.7
157.5°	745.1	744.8	744.4	744.1	744.0	744.2	744.4	744.4	744.6	745.2	745.8
160°	758.2	757.8	757.4	756.9	756.8	756.9	757.1	757.2	757.4	758.0	758.6
162.5°	770.1	769.7	769.5	769.2	769.0	769.0	769.1	769.1	769.2	769.8	770.5
165°	785.8	785.5	785.2	785.0	784.9	785.0	785.1	785.3	785.5	786.0	786.6
167.5°	798.7	798.2	797.6	797.0	796.8	796.8	796.8	796.8	796.8	797.6	798.5
170°	805.9	805.4	804.8	804.2	803.9	803.9	803.9	803.9	803.9	804.8	805.6
172.5°	811.0	810.4	809.8	809.3	809.0	809.0	809.0	809.0	809.0	809.8	810.7
175°	816.8	816.2	815.6	815.1	814.7	814.7	814.7	814.7	814.7	815.6	816.4
177.5°	819.8	819.4	818.9	818.4	818.2	818.1	817.9	817.8	817.7	818.4	819.0
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2	819.2



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	729.7	729.7	729.7	729.7	729.7	729.7	729.7
2.5°	763.1	765.1	769.3	767.8	769.8	770.8	771.8
5°	824.8	834.7	839.0	838.4	844.9	843.3	841.8
7.5°	894.4	904.8	910.6	917.9	922.1	922.3	926.0
10°	933.8	947.4	953.0	960.7	965.7	968.5	968.2
12.5°	964.0	974.7	987.2	991.0	997.7	1001.2	999.9
15°	1000.4	1017.4	1030.4	1036.9	1045.3	1047.7	1051.2
17.5°	1032.8	1055.6	1070.9	1091.0	1098.7	1103.3	1100.6
20°	1057.4	1087.4	1102.6	1126.7	1140.0	1147.2	1144.7
22.5°	1086.4	1118.8	1147.0	1167.8	1188.1	1197.8	1199.7
25°	1136.0	1180.6	1221.8	1249.4	1274.5	1280.3	1293.4
27.5°	1191.6	1244.1	1288.2	1317.1	1334.6	1341.2	1345.2
30°	1226.5	1278.8	1312.0	1330.5	1336.1	1335.5	1334.9
32.5°	1243.6	1276.4	1282.7	1277.5	1264.8	1253.9	1242.7
35°	1219.4	1194.9	1158.3	1111.3	1076.6	1041.5	1038.1
37.5°	1096.7	1018.4	957.6	889.7	850.4	826.2	809.4
40°	981.1	892.3	818.6	761.2	721.3	705.6	690.1
42.5°	855.8	770.9	705.6	657.7	627.7	610.2	597.9
45°	695.3	620.4	569.2	534.6	510.7	497.1	489.3
47.5°	569.7	514.3	470.9	445.9	429.4	418.8	418.8
50°	502.4	449.4	420.6	400.8	386.5	378.1	379.7
52.5°	442.6	403.1	378.5	361.8	351.3	346.2	346.0
55°	370.1	341.6	325.5	313.4	306.3	300.4	301.7
57.5°	316.6	292.5	281.8	271.7	266.8	264.4	261.1
60°	283.4	264.8	255.5	247.4	242.5	240.7	237.3
62.5°	253.9	239.3	230.2	223.6	219.2	218.6	215.9
65°	213.4	202.3	194.2	191.1	186.5	185.2	185.2
67.5°	175.9	168.0	161.7	158.8	156.8	157.1	155.6
70°	152.4	145.9	141.9	138.8	137.2	137.5	136.2
72.5°	133.3	126.0	122.5	120.7	118.6	119.4	119.0
75°	100.9	97.3	95.4	93.5	92.3	91.6	91.1
77.5°	74.1	70.8	69.5	68.4	68.6	67.1	68.2
80°	57.3	54.5	53.6	52.0	51.7	51.7	51.4
82.5°	41.9	40.4	39.7	38.4	37.8	38.3	37.5
85°	21.7	20.5	20.1	20.1	19.5	18.9	20.5
87.5°	10.4	9.5	9.6	9.5	9.6	9.5	9.0
90°	12.3	13.0	13.6	14.0	14.4	14.8	15.3
92.5°	27.3	28.2	28.9	29.2	29.4	29.8	30.1
95°	52.1	53.1	53.7	54.0	54.3	54.5	54.8
97.5°	81.0	81.9	82.4	82.6	82.8	83.0	83.2
100°	101.3	102.6	103.5	103.7	104.0	104.3	104.5
102.5°	122.1	123.5	124.4	124.8	125.1	125.6	126.0
105°	154.9	155.8	156.4	156.9	157.3	157.7	158.1
107.5°	190.5	190.9	191.1	191.1	191.0	191.0	191.0
110°	215.5	215.9	216.1	215.9	215.7	215.6	215.5



TEST NUMBER: P333179-930

CATALOG NUMBER: S125DIP-S610D810U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	240.3	240.5	240.5	240.2	239.9	239.7	239.5
115°	278.2	278.0	277.9	277.8	277.6	277.4	277.4
117.5°	316.7	316.8	316.6	316.0	315.4	314.9	314.3
120°	342.3	342.3	342.1	341.5	341.0	340.4	339.8
122.5°	367.5	367.4	367.1	366.6	366.2	365.7	365.3
125°	404.6	404.3	404.1	404.0	403.8	403.7	403.6
127.5°	441.7	441.6	441.4	441.2	440.8	440.6	440.3
130°	466.3	466.1	465.9	465.6	465.3	465.0	464.7
132.5°	489.7	489.6	489.3	488.9	488.5	488.1	487.7
135°	525.9	525.9	525.7	525.1	524.6	524.0	523.4
137.5°	561.3	561.4	561.2	560.4	559.8	559.1	558.3
140°	583.5	583.8	583.6	582.9	582.2	581.5	580.8
142.5°	605.1	605.3	605.0	604.3	603.6	602.9	602.2
145°	636.3	636.3	636.0	635.6	635.2	634.8	634.3
147.5°	665.6	665.9	665.6	664.6	663.7	662.8	661.8
150°	683.5	683.5	683.3	683.0	682.7	682.4	682.2
152.5°	700.7	701.1	701.0	700.5	700.0	699.5	699.0
155°	725.3	725.9	725.8	725.0	724.4	723.7	722.9
157.5°	746.3	746.9	746.7	745.8	744.9	743.9	743.0
160°	759.0	759.6	759.6	758.9	758.1	757.4	756.8
162.5°	771.2	771.8	771.8	770.9	770.1	769.3	768.5
165°	787.2	787.7	787.6	786.7	785.9	785.0	784.2
167.5°	799.3	800.2	800.1	799.3	798.4	797.5	796.6
170°	806.5	807.3	807.2	806.2	805.3	804.3	803.3
172.5°	811.5	812.4	812.4	811.5	810.7	809.8	808.9
175°	817.3	818.2	818.1	817.1	816.1	815.1	814.2
177.5°	819.7	820.4	820.4	819.5	818.8	818.0	817.2
180°	819.2	819.2	819.2	819.2	819.2	819.2	819.2

(END OF REPORT)