

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333225-930

Luminaire Tested: **S125DIP-S850D810U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333225-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIP-S850D810U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5187.4 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	67	66	63	59	57	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	43	42	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20	17
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6442	6442	6442	6442
5°	7459	6463	5659	6463
10°	8679	6430	4958	6430
15°	9607	6383	4574	6383
20°	10754	6308	4265	6308
25°	12598	6223	4115	6223
30°	13607	6141	3985	6141
35°	11188	5984	3899	5984
40°	7952	5767	3805	5767
45°	6109	5476	3751	5476
50°	5215	5112	3743	5112
55°	4644	4757	3775	4757
60°	4188	4370	3871	4370
65°	3869	3978	3972	3978
70°	3518	3573	4030	3573
75°	3107	3147	3992	3147
80°	2615	2566	3652	2566
85°	2075	1845	2949	1845



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	1.9
10°-20°	285.9	5.5
20°-30°	464.2	8.9
30°-40°	566.3	10.9
40°-50°	515.1	9.9
50°-60°	410.3	7.9
60°-70°	285.8	5.5
70°-80°	152.4	2.9
80°-90°	40.2	0.8
90°-100°	229.2	4.4
100°-110°	492.7	9.5
110°-120°	462.4	8.9
120°-130°	374.7	7.2
130°-140°	300.7	5.8
140°-150°	226.9	4.4
150°-160°	159.7	3.1
160°-170°	94.2	1.8
170°-180°	30.6	0.6
0°-30°	846.1	16.3
0°-40°	1412.4	27.2
0°-60°	2337.8	45.1
0°-90°	2816.3	54.3
90°-120°	1184.3	22.8
90°-150°	2086.6	40.2
90°-180°	2371.0	45.7
0°-180°	5187.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1151	997	873	997	1151	116
15°	1437	955	684	955	1437	411
25°	1768	873	578	873	1768	807
35°	1419	759	494	759	1419	868
45°	669	600	411	600	669	535
55°	412	422	335	422	412	371
65°	253	260	260	260	253	251
75°	124	126	160	126	124	134
85°	28	25	40	25	28	33
90°	15	1	15	1	15	11
95°	150	21	150	21	150	212
105°	845	72	845	72	845	840
115°	941	129	941	129	941	919
125°	741	178	741	178	741	671
135°	616	209	616	209	616	477
145°	486	244	486	244	486	309
155°	407	278	407	278	407	190
165°	357	304	357	304	357	102
175°	321	316	321	316	321	31
180°	316	316	316	316	316	



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1055.0	1053.6	1052.3	1049.5	1051.6	1045.9	1043.1	1038.4	1032.7	1030.6	1028.3
5°	1150.6	1152.8	1154.9	1146.0	1146.9	1140.9	1127.4	1116.4	1107.5	1096.1	1088.0
7.5°	1265.8	1260.8	1260.4	1254.7	1244.7	1236.8	1222.5	1204.4	1186.9	1166.9	1150.4
10°	1323.4	1323.8	1320.0	1313.2	1302.7	1295.0	1276.4	1258.6	1237.1	1211.6	1193.4
12.5°	1366.8	1368.5	1363.7	1354.5	1349.4	1332.3	1317.7	1296.6	1270.9	1250.6	1222.9
15°	1436.9	1432.2	1428.8	1417.4	1408.5	1390.7	1367.4	1345.4	1317.4	1291.6	1265.8
17.5°	1504.4	1508.1	1501.8	1491.3	1463.8	1443.0	1411.8	1381.6	1346.9	1312.2	1281.4
20°	1564.7	1568.1	1558.4	1540.2	1507.2	1486.4	1445.3	1406.4	1366.1	1321.7	1287.8
22.5°	1639.9	1637.2	1624.1	1596.4	1567.7	1529.4	1484.9	1437.5	1387.2	1336.9	1291.9
25°	1767.9	1750.1	1742.1	1707.8	1670.1	1613.8	1552.8	1483.4	1420.7	1354.3	1296.7
27.5°	1838.8	1833.3	1824.3	1800.4	1760.8	1700.6	1628.7	1544.1	1455.7	1371.8	1296.5
30°	1824.6	1825.5	1826.4	1818.7	1793.3	1748.0	1676.5	1585.4	1480.4	1386.0	1298.9
32.5°	1698.7	1714.1	1728.8	1746.2	1753.3	1744.7	1699.8	1617.6	1509.6	1402.3	1297.5
35°	1419.0	1423.8	1471.5	1519.0	1583.3	1633.3	1666.7	1630.4	1539.3	1416.1	1295.8
37.5°	1106.4	1129.4	1162.5	1216.0	1308.9	1392.0	1499.0	1548.2	1518.8	1420.6	1292.9
40°	943.2	964.4	985.9	1040.6	1118.9	1219.7	1341.2	1444.9	1469.0	1406.4	1282.7
42.5°	817.3	834.0	857.9	899.0	964.5	1053.7	1169.8	1305.4	1388.8	1365.1	1261.4
45°	668.9	679.5	698.1	730.7	778.1	848.0	950.4	1098.6	1227.7	1270.5	1210.8
47.5°	572.5	572.4	586.9	609.4	643.7	703.0	778.8	894.9	1032.8	1134.8	1130.1
50°	519.0	516.9	528.3	547.8	574.9	614.2	686.6	779.3	911.9	1027.4	1059.6
52.5°	473.0	473.2	480.2	494.6	517.3	551.0	605.0	688.6	801.8	920.5	981.0
55°	412.4	410.7	418.7	428.4	444.9	466.9	505.9	569.8	661.7	778.5	857.3
57.5°	356.8	361.4	364.7	371.5	385.1	399.9	432.8	479.6	552.5	652.8	736.1
60°	324.2	329.0	331.5	338.3	349.3	362.0	387.3	425.5	486.8	573.2	655.7
62.5°	295.1	298.8	299.6	305.7	314.7	327.1	347.1	379.0	427.5	503.1	584.0
65°	253.2	253.2	254.9	261.2	265.5	276.5	291.7	315.0	353.9	412.8	481.8
67.5°	212.7	214.7	214.3	217.1	221.0	229.5	240.4	259.7	288.5	331.5	386.7
70°	186.3	187.9	187.5	189.6	193.9	199.4	208.3	226.5	247.2	284.1	331.5
72.5°	162.6	163.2	162.2	164.9	167.5	172.3	182.2	191.9	211.3	242.4	281.4
75°	124.5	125.3	126.1	127.8	130.4	132.9	138.0	147.7	160.5	183.8	208.7
77.5°	93.3	91.7	93.8	93.5	94.9	96.9	101.3	106.5	116.9	131.7	151.0
80°	70.3	70.7	70.7	71.1	73.2	74.5	78.4	82.1	90.2	101.2	114.7
82.5°	51.3	52.4	51.8	52.5	54.3	55.2	57.3	60.4	65.1	73.8	83.6
85°	28.0	25.8	26.7	27.6	27.6	28.0	29.6	30.9	33.4	36.9	40.6
87.5°	11.1	11.7	12.0	12.0	12.3	12.1	13.3	13.1	14.0	14.9	16.0
90°	14.7	14.7	14.0	14.0	14.0	12.7	12.1	11.5	10.8	10.2	8.9
92.5°	40.7	41.7	42.6	44.1	52.3	61.7	82.0	113.0	166.4	205.5	208.8
95°	149.8	160.0	165.1	184.3	229.5	283.1	361.4	458.4	552.7	564.8	460.9
97.5°	362.1	370.2	388.7	424.4	463.8	538.3	614.7	682.7	699.3	603.2	411.6
100°	497.3	507.4	531.0	576.9	620.9	687.2	752.8	784.1	735.0	575.7	367.2
102.5°	648.2	655.8	681.4	714.1	761.2	806.0	837.6	818.2	713.6	527.2	333.5
105°	844.7	852.3	865.0	886.1	906.5	913.5	885.5	798.1	645.1	462.2	300.9
107.5°	948.9	954.1	958.2	958.4	948.0	914.8	842.8	726.2	575.3	417.4	287.1
110°	983.7	983.7	979.2	967.0	938.3	884.2	794.3	673.2	535.5	396.5	283.1



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	979.6	974.9	963.8	943.1	901.2	837.2	746.3	631.4	505.9	384.3	283.1
115°	940.9	932.6	914.8	884.2	834.5	765.0	677.7	578.9	473.6	371.0	284.9
117.5°	873.2	868.1	850.4	818.8	769.1	705.3	630.1	544.9	454.4	364.5	289.2
120°	829.3	824.3	807.1	776.4	729.3	673.2	603.1	526.5	443.7	361.4	293.3
122.5°	790.6	786.0	768.8	740.8	698.7	646.1	583.7	512.8	434.5	358.9	296.8
125°	741.4	735.0	721.0	694.9	659.2	613.3	557.8	492.8	422.0	355.7	302.8
127.5°	699.3	696.5	683.2	660.1	627.8	584.8	533.0	472.4	410.5	354.2	309.6
130°	676.4	672.5	659.8	638.8	606.9	565.4	515.8	459.6	402.9	353.2	313.6
132.5°	653.4	649.1	637.3	616.3	584.4	544.5	499.4	446.9	396.8	353.2	318.2
135°	615.8	612.0	600.5	579.4	551.4	515.1	474.3	430.3	389.5	353.2	324.5
137.5°	575.7	571.4	560.8	541.8	516.6	485.8	451.8	416.3	383.0	353.9	330.2
140°	547.6	544.4	534.8	518.3	494.6	467.9	438.5	408.6	379.9	354.4	332.7
142.5°	521.5	518.9	509.9	495.9	475.8	452.6	427.4	402.0	377.4	355.0	334.3
145°	485.8	483.2	476.2	465.4	450.0	432.8	413.1	393.3	373.6	354.4	336.0
147.5°	455.4	454.3	450.2	441.5	429.4	416.4	401.2	385.1	369.6	352.8	336.6
150°	438.5	438.0	435.4	427.8	418.2	406.7	394.6	380.6	366.6	351.2	336.6
152.5°	425.3	424.7	422.2	416.0	408.0	399.1	388.0	375.4	363.0	349.2	336.1
155°	407.3	406.7	404.8	400.3	394.0	386.9	378.1	367.9	357.0	345.5	334.7
157.5°	391.3	391.4	389.6	386.0	381.0	375.4	368.6	360.2	351.4	341.7	333.0
160°	380.6	381.2	379.9	376.7	372.3	367.9	361.4	355.1	346.8	339.2	331.5
162.5°	370.9	371.0	370.7	368.1	364.6	360.7	355.3	349.4	342.7	336.1	330.0
165°	357.0	357.0	357.0	355.7	353.2	350.0	346.2	341.7	336.6	331.5	327.7
167.5°	344.2	344.4	344.9	343.7	342.4	340.1	337.2	334.3	330.6	327.0	324.1
170°	336.6	337.2	337.2	336.6	335.3	334.0	332.2	330.2	327.0	324.5	322.5
172.5°	329.5	330.1	331.1	330.0	329.7	329.0	327.5	325.6	323.4	321.4	320.5
175°	320.7	321.3	322.5	322.0	322.0	322.0	320.7	320.7	318.7	318.1	318.1
177.5°	316.2	316.2	317.7	317.2	317.7	317.7	317.7	317.2	316.7	316.2	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1026.2	1023.9	1021.1	1016.4	1010.6	1007.5	1002.8	999.8	993.7	988.6	983.2
5°	1078.2	1067.2	1057.1	1044.0	1029.6	1020.3	1009.3	996.9	984.3	971.2	956.8
7.5°	1132.2	1112.7	1091.5	1068.8	1046.5	1026.1	1006.5	987.2	969.3	947.6	929.3
10°	1168.4	1143.9	1117.6	1086.7	1056.7	1030.5	1003.8	980.5	956.8	931.4	908.9
12.5°	1204.7	1172.0	1134.9	1101.0	1064.8	1033.1	1001.8	972.0	942.2	914.1	887.9
15°	1230.3	1201.4	1167.2	1118.9	1078.2	1034.7	993.2	954.6	918.7	887.4	854.4
17.5°	1247.1	1210.0	1173.2	1126.9	1073.6	1024.8	977.9	933.8	893.2	853.5	821.7
20°	1250.2	1212.0	1173.5	1128.2	1073.6	1017.7	970.8	917.8	874.2	833.2	794.2
22.5°	1249.1	1206.0	1164.0	1117.4	1064.1	1012.7	955.9	901.9	854.6	814.2	773.6
25°	1239.6	1193.4	1140.9	1094.0	1041.5	986.8	929.3	873.3	825.1	778.9	738.7
27.5°	1231.6	1171.7	1112.3	1057.5	1006.8	956.8	901.6	844.4	790.9	744.1	706.2
30°	1221.8	1156.2	1089.2	1032.1	980.1	931.4	879.3	823.5	767.5	721.8	681.2
32.5°	1213.0	1136.5	1065.9	1003.7	948.5	901.2	853.2	800.1	745.2	698.8	658.1
35°	1196.0	1107.5	1026.6	956.3	897.5	848.8	808.6	759.0	708.7	663.8	624.8
37.5°	1174.4	1069.3	982.6	908.9	844.4	793.1	755.7	717.6	669.3	626.1	590.8
40°	1157.4	1042.3	950.4	875.1	808.2	754.8	720.2	684.1	643.9	603.7	566.5
42.5°	1136.1	1017.9	917.9	836.8	770.5	718.6	682.2	651.6	616.1	578.6	544.0
45°	1096.9	973.7	865.4	778.1	711.2	660.0	622.3	599.5	572.8	537.2	508.0
47.5°	1039.3	920.6	808.5	718.5	649.5	602.0	566.7	544.8	525.9	499.5	473.0
50°	988.1	881.0	767.5	678.2	609.2	561.3	528.8	508.8	492.8	472.5	450.0
52.5°	930.8	831.2	727.2	639.0	570.6	523.4	491.5	474.0	460.6	446.1	424.0
55°	839.9	755.3	658.8	574.9	511.8	465.7	437.7	422.5	411.5	400.5	386.9
57.5°	739.7	673.5	588.0	511.4	453.3	411.3	385.2	370.4	361.9	356.2	348.2
60°	669.3	612.6	538.9	469.0	412.4	375.1	349.7	338.3	331.1	326.4	320.5
62.5°	604.0	557.4	489.1	425.3	375.8	340.6	317.9	306.8	299.9	297.6	292.7
65°	507.6	471.7	415.3	362.4	320.1	290.0	270.9	260.3	256.1	253.6	254.0
67.5°	412.7	390.8	345.5	300.4	266.6	241.4	226.2	218.0	215.9	212.5	212.5
70°	354.7	338.3	300.2	260.8	230.7	211.2	197.7	189.2	187.1	185.4	185.0
72.5°	303.6	289.2	256.1	224.5	197.5	180.4	169.3	164.2	160.7	159.7	159.6
75°	228.2	220.1	193.9	168.9	150.3	138.4	130.9	126.1	123.6	123.2	123.6
77.5°	162.2	155.2	138.5	120.8	109.1	100.1	93.7	92.0	89.2	89.3	88.8
80°	121.9	117.2	106.7	92.7	83.0	75.3	72.0	69.0	68.2	66.9	68.2
82.5°	88.4	83.4	76.2	67.3	59.3	54.7	51.3	50.4	49.9	49.2	49.6
85°	43.6	44.0	39.8	33.0	29.6	27.1	24.9	24.9	24.5	24.1	24.5
87.5°	16.6	15.7	14.1	12.9	10.9	9.6	9.0	9.3	8.4	8.3	8.9
90°	8.3	7.0	6.4	5.1	3.8	2.5	1.3	0.7	1.3	2.5	3.8
92.5°	145.4	87.1	52.3	33.7	22.7	14.8	9.5	7.7	9.5	14.8	22.7
95°	284.9	144.7	76.5	47.8	33.8	26.7	21.7	21.0	21.7	26.7	33.8
97.5°	227.5	124.7	79.6	58.9	46.3	39.3	35.7	34.9	35.7	39.3	46.3
100°	206.5	123.7	86.7	67.6	55.4	48.4	45.9	44.6	45.9	48.4	55.4
102.5°	197.9	128.2	95.4	76.7	65.6	58.1	56.1	55.4	56.1	58.1	65.6
105°	194.4	137.7	109.7	91.8	81.6	75.3	72.1	72.1	72.1	75.3	81.6
107.5°	200.3	151.7	124.6	108.5	97.9	92.7	89.6	88.4	89.6	92.7	97.9
110°	205.9	161.9	135.7	119.2	109.7	103.9	101.3	100.1	101.3	103.9	109.7



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	213.0	171.6	146.5	130.4	120.8	115.1	113.1	111.8	113.1	115.1	120.8
115°	223.7	186.8	163.2	147.2	137.7	132.0	130.0	128.7	130.0	132.0	137.7
117.5°	236.0	202.4	180.0	164.6	153.8	148.1	146.0	144.1	146.0	148.1	153.8
120°	244.2	213.5	191.3	175.3	164.4	158.7	156.2	154.3	156.2	158.7	164.4
122.5°	253.3	224.3	201.9	186.1	174.1	168.4	166.4	165.0	166.4	168.4	174.1
125°	265.8	238.4	217.4	200.8	188.7	183.0	179.8	178.5	179.8	183.0	188.7
127.5°	277.3	252.1	231.8	215.2	202.4	195.1	191.0	189.1	191.0	195.1	202.4
130°	284.9	260.7	241.0	224.4	211.0	202.7	197.6	195.7	197.6	202.7	211.0
132.5°	291.6	268.9	249.2	232.5	218.7	209.4	203.3	200.8	203.3	209.4	218.7
135°	300.9	279.9	260.1	242.9	229.5	219.3	211.7	209.1	211.7	219.3	229.5
137.5°	307.8	287.6	269.6	251.9	238.8	228.6	221.4	219.6	221.4	228.6	238.8
140°	312.3	293.3	274.8	257.6	245.4	235.2	227.6	225.7	227.6	235.2	245.4
142.5°	315.0	296.8	279.3	263.2	251.5	241.3	234.2	232.8	234.2	241.3	251.5
145°	318.7	302.8	286.3	271.6	260.1	251.2	244.8	243.5	244.8	251.2	260.1
147.5°	321.1	306.6	292.1	279.2	269.3	261.0	255.5	254.7	255.5	261.0	269.3
150°	322.5	309.2	295.1	284.3	275.4	267.1	262.6	261.4	262.6	267.1	275.4
152.5°	323.6	311.7	298.7	288.9	280.5	273.2	269.3	268.5	269.3	273.2	280.5
155°	324.5	314.3	303.5	294.5	288.1	281.8	277.9	277.9	277.9	281.8	288.1
157.5°	325.1	316.4	307.1	300.4	294.7	289.3	286.3	286.3	286.3	289.3	294.7
160°	325.1	317.5	309.2	303.5	298.3	293.9	291.3	292.0	291.3	293.9	298.3
162.5°	324.6	318.5	311.2	306.5	302.4	298.5	296.0	296.5	296.0	298.5	302.4
165°	323.8	318.7	313.6	309.8	307.3	304.1	302.1	303.5	302.1	304.1	307.3
167.5°	322.3	318.7	314.5	312.1	310.3	308.5	307.4	308.0	307.4	308.5	310.3
170°	321.3	318.7	315.5	313.6	312.3	311.1	310.5	311.1	310.5	311.1	312.3
172.5°	320.2	318.2	315.5	314.6	313.9	312.6	312.0	313.2	312.0	312.6	313.9
175°	318.7	317.5	315.5	315.5	315.5	315.0	314.3	315.5	314.3	315.0	315.5
177.5°	317.2	316.7	315.7	315.7	316.2	315.7	315.7	316.7	315.7	315.7	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	980.2	976.4	973.4	966.6	962.9	957.8	953.7	958.1	953.4	955.4	952.4
5°	949.6	937.8	929.3	917.0	906.4	896.7	889.5	888.2	884.8	883.1	878.0
7.5°	912.8	898.0	883.5	867.4	853.8	840.0	831.2	823.9	819.1	812.8	808.5
10°	891.1	871.2	854.4	834.9	817.9	803.1	791.2	785.3	779.8	771.8	768.8
12.5°	864.4	843.8	823.1	802.3	786.1	769.6	759.4	750.4	746.7	737.5	736.6
15°	832.3	801.4	781.1	759.9	737.4	723.9	715.4	705.7	701.5	695.1	690.5
17.5°	794.0	766.5	741.0	719.1	699.9	688.4	677.9	671.2	664.0	659.8	652.2
20°	766.3	740.0	714.6	691.3	676.5	663.4	654.9	648.6	641.0	638.9	631.2
22.5°	742.9	714.0	689.6	670.0	653.8	639.0	629.8	625.6	620.3	613.8	612.2
25°	704.9	674.8	654.1	634.6	620.2	606.7	600.3	594.8	589.7	585.1	583.3
27.5°	672.1	645.1	620.5	602.9	590.4	578.0	572.4	565.7	562.1	558.3	553.8
30°	649.0	621.5	599.9	582.9	569.4	558.4	552.4	547.8	544.5	541.0	538.5
32.5°	625.3	599.8	578.9	562.3	548.8	540.5	535.2	531.9	528.2	524.1	520.9
35°	593.9	566.0	545.7	531.3	520.7	514.4	508.4	505.5	501.2	501.2	497.8
37.5°	558.6	534.5	516.6	503.4	494.0	488.3	481.8	479.8	477.1	475.3	474.2
40°	537.7	515.2	498.3	485.2	475.0	470.3	465.3	461.9	460.2	458.0	457.2
42.5°	516.0	494.6	478.3	466.2	457.4	453.4	448.7	446.3	442.9	440.1	439.6
45°	483.1	462.3	447.5	437.7	430.2	425.5	422.5	417.4	415.7	412.4	411.9
47.5°	451.8	431.9	417.4	409.4	402.7	398.8	394.2	389.1	387.2	385.5	385.3
50°	428.4	410.3	396.6	389.1	382.7	377.2	372.5	369.2	367.9	367.9	368.8
52.5°	404.7	389.2	377.7	368.4	362.4	356.5	352.2	350.2	348.2	350.3	351.8
55°	370.0	354.3	345.8	337.0	331.1	324.2	322.2	321.3	320.1	323.4	325.1
57.5°	333.3	322.3	312.3	303.5	298.2	294.3	291.5	290.9	293.3	294.9	300.4
60°	309.9	297.2	288.3	281.5	275.2	272.6	271.8	270.9	272.6	277.3	284.5
62.5°	284.1	273.9	264.2	259.2	254.5	250.3	250.1	250.6	254.0	259.3	266.5
65°	246.4	237.5	231.1	225.2	221.4	218.9	219.7	221.4	225.2	232.4	240.4
67.5°	208.1	201.9	196.2	191.4	187.8	187.8	188.7	191.2	195.7	204.0	211.3
70°	183.3	176.5	171.9	169.7	166.8	165.1	167.6	171.9	175.7	183.3	189.6
72.5°	158.6	152.9	149.2	147.7	146.5	145.1	145.9	150.5	155.7	163.3	170.7
75°	121.9	119.8	117.2	115.6	114.3	115.1	116.0	120.3	124.5	132.5	141.0
77.5°	88.9	86.7	85.3	84.9	84.1	84.5	87.0	90.1	94.2	100.1	106.5
80°	67.3	66.4	65.6	65.2	65.2	65.6	69.0	71.1	74.9	80.5	85.5
82.5°	49.0	48.5	48.3	48.3	48.6	48.7	50.7	53.5	56.7	60.8	65.2
85°	25.8	24.9	26.3	26.7	25.8	27.1	28.0	29.6	30.9	33.0	35.1
87.5°	9.5	10.4	10.2	10.8	10.9	11.8	11.7	13.1	13.9	14.8	14.7
90°	5.1	6.4	7.0	8.3	8.9	10.2	10.8	11.5	12.1	12.7	14.0
92.5°	33.7	52.3	87.1	145.4	208.8	205.5	166.4	113.0	82.0	61.7	52.3
95°	47.8	76.5	144.7	284.9	460.9	564.8	552.7	458.4	361.4	283.1	229.5
97.5°	58.9	79.6	124.7	227.5	411.6	603.2	699.3	682.7	614.7	538.3	463.8
100°	67.6	86.7	123.7	206.5	367.2	575.7	735.0	784.1	752.8	687.2	620.9
102.5°	76.7	95.4	128.2	197.9	333.5	527.2	713.6	818.2	837.6	806.0	761.2
105°	91.8	109.7	137.7	194.4	300.9	462.2	645.1	798.1	885.5	913.5	906.5
107.5°	108.5	124.6	151.7	200.3	287.1	417.4	575.3	726.2	842.8	914.8	948.0
110°	119.2	135.7	161.9	205.9	283.1	396.5	535.5	673.2	794.3	884.2	938.3



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	130.4	146.5	171.6	213.0	283.1	384.3	505.9	631.4	746.3	837.2	901.2
115°	147.2	163.2	186.8	223.7	284.9	371.0	473.6	578.9	677.7	765.0	834.5
117.5°	164.6	180.0	202.4	236.0	289.2	364.5	454.4	544.9	630.1	705.3	769.1
120°	175.3	191.3	213.5	244.2	293.3	361.4	443.7	526.5	603.1	673.2	729.3
122.5°	186.1	201.9	224.3	253.3	296.8	358.9	434.5	512.8	583.7	646.1	698.7
125°	200.8	217.4	238.4	265.8	302.8	355.7	422.0	492.8	557.8	613.3	659.2
127.5°	215.2	231.8	252.1	277.3	309.6	354.2	410.5	472.4	533.0	584.8	627.8
130°	224.4	241.0	260.7	284.9	313.6	353.2	402.9	459.6	515.8	565.4	606.9
132.5°	232.5	249.2	268.9	291.6	318.2	353.2	396.8	446.9	499.4	544.5	584.4
135°	242.9	260.1	279.9	300.9	324.5	353.2	389.5	430.3	474.3	515.1	551.4
137.5°	251.9	269.6	287.6	307.8	330.2	353.9	383.0	416.3	451.8	485.8	516.6
140°	257.6	274.8	293.3	312.3	332.7	354.4	379.9	408.6	438.5	467.9	494.6
142.5°	263.2	279.3	296.8	315.0	334.3	355.0	377.4	402.0	427.4	452.6	475.8
145°	271.6	286.3	302.8	318.7	336.0	354.4	373.6	393.3	413.1	432.8	450.0
147.5°	279.2	292.1	306.6	321.1	336.6	352.8	369.6	385.1	401.2	416.4	429.4
150°	284.3	295.1	309.2	322.5	336.6	351.2	366.6	380.6	394.6	406.7	418.2
152.5°	288.9	298.7	311.7	323.6	336.1	349.2	363.0	375.4	388.0	399.1	408.0
155°	294.5	303.5	314.3	324.5	334.7	345.5	357.0	367.9	378.1	386.9	394.0
157.5°	300.4	307.1	316.4	325.1	333.0	341.7	351.4	360.2	368.6	375.4	381.0
160°	303.5	309.2	317.5	325.1	331.5	339.2	346.8	355.1	361.4	367.9	372.3
162.5°	306.5	311.2	318.5	324.6	330.0	336.1	342.7	349.4	355.3	360.7	364.6
165°	309.8	313.6	318.7	323.8	327.7	331.5	336.6	341.7	346.2	350.0	353.2
167.5°	312.1	314.5	318.7	322.3	324.1	327.0	330.6	334.3	337.2	340.1	342.4
170°	313.6	315.5	318.7	321.3	322.5	324.5	327.0	330.2	332.2	334.0	335.3
172.5°	314.6	315.5	318.2	320.2	320.5	321.4	323.4	325.6	327.5	329.0	329.7
175°	315.5	315.5	317.5	318.7	318.1	318.1	318.7	320.7	320.7	322.0	322.0
177.5°	315.7	315.7	316.7	317.2	316.2	316.2	316.7	317.2	317.7	317.7	317.7
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	950.3	952.7	950.6	953.4	950.6	952.7	950.3	952.4	955.4	953.4	958.1
5°	875.9	872.1	874.7	872.9	874.7	872.1	875.9	878.0	883.1	884.8	888.2
7.5°	807.1	803.5	799.4	797.4	799.4	803.5	807.1	808.5	812.8	819.1	823.9
10°	764.2	759.5	759.0	756.1	759.0	759.5	764.2	768.8	771.8	779.8	785.3
12.5°	732.6	728.3	723.5	722.3	723.5	728.3	732.6	736.6	737.5	746.7	750.4
15°	687.9	684.5	681.6	684.1	681.6	684.5	687.9	690.5	695.1	701.5	705.7
17.5°	650.8	648.0	647.4	644.3	647.4	648.0	650.8	652.2	659.8	664.0	671.2
20°	627.4	625.3	626.1	620.6	626.1	625.3	627.4	631.2	638.9	641.0	648.6
22.5°	608.8	604.6	604.1	603.0	604.1	604.6	608.8	612.2	613.8	620.3	625.6
25°	579.6	577.5	575.4	577.5	575.4	577.5	579.6	583.3	585.1	589.7	594.8
27.5°	554.1	551.5	551.0	551.2	551.0	551.5	554.1	553.8	558.3	562.1	565.7
30°	538.5	534.3	534.7	534.3	534.7	534.3	538.5	538.5	541.0	544.5	547.8
32.5°	521.5	518.7	518.1	517.3	518.1	518.7	521.5	520.9	524.1	528.2	531.9
35°	496.6	496.6	494.5	494.5	494.5	496.6	496.6	497.8	501.2	501.2	505.5
37.5°	473.1	472.7	471.4	471.7	471.4	472.7	473.1	474.2	475.3	477.1	479.8
40°	455.5	455.1	453.8	451.3	453.8	455.1	455.5	457.2	458.0	460.2	461.9
42.5°	438.5	437.2	436.6	435.7	436.6	437.2	438.5	439.6	440.1	442.9	446.3
45°	411.9	411.9	411.1	410.7	411.1	411.9	411.9	411.9	412.4	415.7	417.4
47.5°	386.0	386.8	388.4	388.2	388.4	386.8	386.0	385.3	385.5	387.2	389.1
50°	370.4	370.9	372.1	372.5	372.1	370.9	370.4	368.8	367.9	367.9	369.2
52.5°	353.2	355.6	357.2	356.9	357.2	355.6	353.2	351.8	350.3	348.2	350.2
55°	329.0	331.9	334.8	335.3	334.8	331.9	329.0	325.1	323.4	320.1	321.3
57.5°	305.0	309.2	312.3	313.2	312.3	309.2	305.0	300.4	294.9	293.3	290.9
60°	288.7	294.2	298.1	299.7	298.1	294.2	288.7	284.5	277.3	272.6	270.9
62.5°	273.1	279.3	283.2	283.5	283.2	279.3	273.1	266.5	259.3	254.0	250.6
65°	247.7	254.0	257.4	259.9	257.4	254.0	247.7	240.4	232.4	225.2	221.4
67.5°	220.2	226.6	230.3	232.4	230.3	226.6	220.2	211.3	204.0	195.7	191.2
70°	200.2	206.6	211.7	213.4	211.7	206.6	200.2	189.6	183.3	175.7	171.9
72.5°	180.6	186.3	190.4	192.3	190.4	186.3	180.6	170.7	163.3	155.7	150.5
75°	146.5	154.1	157.9	160.0	157.9	154.1	146.5	141.0	132.5	124.5	120.3
77.5°	112.9	119.9	122.2	123.3	122.2	119.9	112.9	106.5	100.1	94.2	90.1
80°	90.6	94.8	97.8	98.2	97.8	94.8	90.6	85.5	80.5	74.9	71.1
82.5°	69.6	73.1	74.1	75.2	74.1	73.1	69.6	65.2	60.8	56.7	53.5
85°	38.1	39.8	40.2	39.8	40.2	39.8	38.1	35.1	33.0	30.9	29.6
87.5°	15.3	15.0	15.2	15.8	15.2	15.0	15.3	14.7	14.8	13.9	13.1
90°	14.0	14.0	14.7	14.7	14.7	14.0	14.0	14.0	12.7	12.1	11.5
92.5°	44.1	42.6	41.7	40.7	41.7	42.6	44.1	52.3	61.7	82.0	113.0
95°	184.3	165.1	160.0	149.8	160.0	165.1	184.3	229.5	283.1	361.4	458.4
97.5°	424.4	388.7	370.2	362.1	370.2	388.7	424.4	463.8	538.3	614.7	682.7
100°	576.9	531.0	507.4	497.3	507.4	531.0	576.9	620.9	687.2	752.8	784.1
102.5°	714.1	681.4	655.8	648.2	655.8	681.4	714.1	761.2	806.0	837.6	818.2
105°	886.1	865.0	852.3	844.7	852.3	865.0	886.1	906.5	913.5	885.5	798.1
107.5°	958.4	958.2	954.1	948.9	954.1	958.2	958.4	948.0	914.8	842.8	726.2
110°	967.0	979.2	983.7	983.7	983.7	979.2	967.0	938.3	884.2	794.3	673.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	943.1	963.8	974.9	979.6	974.9	963.8	943.1	901.2	837.2	746.3	631.4
115°	884.2	914.8	932.6	940.9	932.6	914.8	884.2	834.5	765.0	677.7	578.9
117.5°	818.8	850.4	868.1	873.2	868.1	850.4	818.8	769.1	705.3	630.1	544.9
120°	776.4	807.1	824.3	829.3	824.3	807.1	776.4	729.3	673.2	603.1	526.5
122.5°	740.8	768.8	786.0	790.6	786.0	768.8	740.8	698.7	646.1	583.7	512.8
125°	694.9	721.0	735.0	741.4	735.0	721.0	694.9	659.2	613.3	557.8	492.8
127.5°	660.1	683.2	696.5	699.3	696.5	683.2	660.1	627.8	584.8	533.0	472.4
130°	638.8	659.8	672.5	676.4	672.5	659.8	638.8	606.9	565.4	515.8	459.6
132.5°	616.3	637.3	649.1	653.4	649.1	637.3	616.3	584.4	544.5	499.4	446.9
135°	579.4	600.5	612.0	615.8	612.0	600.5	579.4	551.4	515.1	474.3	430.3
137.5°	541.8	560.8	571.4	575.7	571.4	560.8	541.8	516.6	485.8	451.8	416.3
140°	518.3	534.8	544.4	547.6	544.4	534.8	518.3	494.6	467.9	438.5	408.6
142.5°	495.9	509.9	518.9	521.5	518.9	509.9	495.9	475.8	452.6	427.4	402.0
145°	465.4	476.2	483.2	485.8	483.2	476.2	465.4	450.0	432.8	413.1	393.3
147.5°	441.5	450.2	454.3	455.4	454.3	450.2	441.5	429.4	416.4	401.2	385.1
150°	427.8	435.4	438.0	438.5	438.0	435.4	427.8	418.2	406.7	394.6	380.6
152.5°	416.0	422.2	424.7	425.3	424.7	422.2	416.0	408.0	399.1	388.0	375.4
155°	400.3	404.8	406.7	407.3	406.7	404.8	400.3	394.0	386.9	378.1	367.9
157.5°	386.0	389.6	391.4	391.3	391.4	389.6	386.0	381.0	375.4	368.6	360.2
160°	376.7	379.9	381.2	380.6	381.2	379.9	376.7	372.3	367.9	361.4	355.1
162.5°	368.1	370.7	371.0	370.9	371.0	370.7	368.1	364.6	360.7	355.3	349.4
165°	355.7	357.0	357.0	357.0	357.0	357.0	355.7	353.2	350.0	346.2	341.7
167.5°	343.7	344.9	344.4	344.2	344.4	344.9	343.7	342.4	340.1	337.2	334.3
170°	336.6	337.2	337.2	336.6	337.2	337.2	336.6	335.3	334.0	332.2	330.2
172.5°	330.0	331.1	330.1	329.5	330.1	331.1	330.0	329.7	329.0	327.5	325.6
175°	322.0	322.5	321.3	320.7	321.3	322.5	322.0	322.0	322.0	320.7	320.7
177.5°	317.2	317.7	316.2	316.2	316.2	317.7	317.2	317.7	317.7	317.7	317.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	953.7	957.8	962.9	966.6	973.4	976.4	980.2	983.2	988.6	993.7	999.8
5°	889.5	896.7	906.4	917.0	929.3	937.8	949.6	956.8	971.2	984.3	996.9
7.5°	831.2	840.0	853.8	867.4	883.5	898.0	912.8	929.3	947.6	969.3	987.2
10°	791.2	803.1	817.9	834.9	854.4	871.2	891.1	908.9	931.4	956.8	980.5
12.5°	759.4	769.6	786.1	802.3	823.1	843.8	864.4	887.9	914.1	942.2	972.0
15°	715.4	723.9	737.4	759.9	781.1	801.4	832.3	854.4	887.4	918.7	954.6
17.5°	677.9	688.4	699.9	719.1	741.0	766.5	794.0	821.7	853.5	893.2	933.8
20°	654.9	663.4	676.5	691.3	714.6	740.0	766.3	794.2	833.2	874.2	917.8
22.5°	629.8	639.0	653.8	670.0	689.6	714.0	742.9	773.6	814.2	854.6	901.9
25°	600.3	606.7	620.2	634.6	654.1	674.8	704.9	738.7	778.9	825.1	873.3
27.5°	572.4	578.0	590.4	602.9	620.5	645.1	672.1	706.2	744.1	790.9	844.4
30°	552.4	558.4	569.4	582.9	599.9	621.5	649.0	681.2	721.8	767.5	823.5
32.5°	535.2	540.5	548.8	562.3	578.9	599.8	625.3	658.1	698.8	745.2	800.1
35°	508.4	514.4	520.7	531.3	545.7	566.0	593.9	624.8	663.8	708.7	759.0
37.5°	481.8	488.3	494.0	503.4	516.6	534.5	558.6	590.8	626.1	669.3	717.6
40°	465.3	470.3	475.0	485.2	498.3	515.2	537.7	566.5	603.7	643.9	684.1
42.5°	448.7	453.4	457.4	466.2	478.3	494.6	516.0	544.0	578.6	616.1	651.6
45°	422.5	425.5	430.2	437.7	447.5	462.3	483.1	508.0	537.2	572.8	599.5
47.5°	394.2	398.8	402.7	409.4	417.4	431.9	451.8	473.0	499.5	525.9	544.8
50°	372.5	377.2	382.7	389.1	396.6	410.3	428.4	450.0	472.5	492.8	508.8
52.5°	352.2	356.5	362.4	368.4	377.7	389.2	404.7	424.0	446.1	460.6	474.0
55°	322.2	324.2	331.1	337.0	345.8	354.3	370.0	386.9	400.5	411.5	422.5
57.5°	291.5	294.3	298.2	303.5	312.3	322.3	333.3	348.2	356.2	361.9	370.4
60°	271.8	272.6	275.2	281.5	288.3	297.2	309.9	320.5	326.4	331.1	338.3
62.5°	250.1	250.3	254.5	259.2	264.2	273.9	284.1	292.7	297.6	299.9	306.8
65°	219.7	218.9	221.4	225.2	231.1	237.5	246.4	254.0	253.6	256.1	260.3
67.5°	188.7	187.8	187.8	191.4	196.2	201.9	208.1	212.5	212.5	215.9	218.0
70°	167.6	165.1	166.8	169.7	171.9	176.5	183.3	185.0	185.4	187.1	189.2
72.5°	145.9	145.1	146.5	147.7	149.2	152.9	158.6	159.6	159.7	160.7	164.2
75°	116.0	115.1	114.3	115.6	117.2	119.8	121.9	123.6	123.2	123.6	126.1
77.5°	87.0	84.5	84.1	84.9	85.3	86.7	88.9	88.8	89.3	89.2	92.0
80°	69.0	65.6	65.2	65.2	65.6	66.4	67.3	68.2	66.9	68.2	69.0
82.5°	50.7	48.7	48.6	48.3	48.3	48.5	49.0	49.6	49.2	49.9	50.4
85°	28.0	27.1	25.8	26.7	26.3	24.9	25.8	24.5	24.1	24.5	24.9
87.5°	11.7	11.8	10.9	10.8	10.2	10.4	9.5	8.9	8.3	8.4	9.3
90°	10.8	10.2	8.9	8.3	7.0	6.4	5.1	3.8	2.5	1.3	0.7
92.5°	166.4	205.5	208.8	145.4	87.1	52.3	33.7	22.7	14.8	9.5	7.7
95°	552.7	564.8	460.9	284.9	144.7	76.5	47.8	33.8	26.7	21.7	21.0
97.5°	699.3	603.2	411.6	227.5	124.7	79.6	58.9	46.3	39.3	35.7	34.9
100°	735.0	575.7	367.2	206.5	123.7	86.7	67.6	55.4	48.4	45.9	44.6
102.5°	713.6	527.2	333.5	197.9	128.2	95.4	76.7	65.6	58.1	56.1	55.4
105°	645.1	462.2	300.9	194.4	137.7	109.7	91.8	81.6	75.3	72.1	72.1
107.5°	575.3	417.4	287.1	200.3	151.7	124.6	108.5	97.9	92.7	89.6	88.4
110°	535.5	396.5	283.1	205.9	161.9	135.7	119.2	109.7	103.9	101.3	100.1



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	505.9	384.3	283.1	213.0	171.6	146.5	130.4	120.8	115.1	113.1	111.8
115°	473.6	371.0	284.9	223.7	186.8	163.2	147.2	137.7	132.0	130.0	128.7
117.5°	454.4	364.5	289.2	236.0	202.4	180.0	164.6	153.8	148.1	146.0	144.1
120°	443.7	361.4	293.3	244.2	213.5	191.3	175.3	164.4	158.7	156.2	154.3
122.5°	434.5	358.9	296.8	253.3	224.3	201.9	186.1	174.1	168.4	166.4	165.0
125°	422.0	355.7	302.8	265.8	238.4	217.4	200.8	188.7	183.0	179.8	178.5
127.5°	410.5	354.2	309.6	277.3	252.1	231.8	215.2	202.4	195.1	191.0	189.1
130°	402.9	353.2	313.6	284.9	260.7	241.0	224.4	211.0	202.7	197.6	195.7
132.5°	396.8	353.2	318.2	291.6	268.9	249.2	232.5	218.7	209.4	203.3	200.8
135°	389.5	353.2	324.5	300.9	279.9	260.1	242.9	229.5	219.3	211.7	209.1
137.5°	383.0	353.9	330.2	307.8	287.6	269.6	251.9	238.8	228.6	221.4	219.6
140°	379.9	354.4	332.7	312.3	293.3	274.8	257.6	245.4	235.2	227.6	225.7
142.5°	377.4	355.0	334.3	315.0	296.8	279.3	263.2	251.5	241.3	234.2	232.8
145°	373.6	354.4	336.0	318.7	302.8	286.3	271.6	260.1	251.2	244.8	243.5
147.5°	369.6	352.8	336.6	321.1	306.6	292.1	279.2	269.3	261.0	255.5	254.7
150°	366.6	351.2	336.6	322.5	309.2	295.1	284.3	275.4	267.1	262.6	261.4
152.5°	363.0	349.2	336.1	323.6	311.7	298.7	288.9	280.5	273.2	269.3	268.5
155°	357.0	345.5	334.7	324.5	314.3	303.5	294.5	288.1	281.8	277.9	277.9
157.5°	351.4	341.7	333.0	325.1	316.4	307.1	300.4	294.7	289.3	286.3	286.3
160°	346.8	339.2	331.5	325.1	317.5	309.2	303.5	298.3	293.9	291.3	292.0
162.5°	342.7	336.1	330.0	324.6	318.5	311.2	306.5	302.4	298.5	296.0	296.5
165°	336.6	331.5	327.7	323.8	318.7	313.6	309.8	307.3	304.1	302.1	303.5
167.5°	330.6	327.0	324.1	322.3	318.7	314.5	312.1	310.3	308.5	307.4	308.0
170°	327.0	324.5	322.5	321.3	318.7	315.5	313.6	312.3	311.1	310.5	311.1
172.5°	323.4	321.4	320.5	320.2	318.2	315.5	314.6	313.9	312.6	312.0	313.2
175°	318.7	318.1	318.1	318.7	317.5	315.5	315.5	315.5	315.0	314.3	315.5
177.5°	316.7	316.2	316.2	317.2	316.7	315.7	315.7	316.2	315.7	315.7	316.7
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1002.8	1007.5	1010.6	1016.4	1021.1	1023.9	1026.2	1028.3	1030.6	1032.7	1038.4
5°	1009.3	1020.3	1029.6	1044.0	1057.1	1067.2	1078.2	1088.0	1096.1	1107.5	1116.4
7.5°	1006.5	1026.1	1046.5	1068.8	1091.5	1112.7	1132.2	1150.4	1166.9	1186.9	1204.4
10°	1003.8	1030.5	1056.7	1086.7	1117.6	1143.9	1168.4	1193.4	1211.6	1237.1	1258.6
12.5°	1001.8	1033.1	1064.8	1101.0	1134.9	1172.0	1204.7	1222.9	1250.6	1270.9	1296.6
15°	993.2	1034.7	1078.2	1118.9	1167.2	1201.4	1230.3	1265.8	1291.6	1317.4	1345.4
17.5°	977.9	1024.8	1073.6	1126.9	1173.2	1210.0	1247.1	1281.4	1312.2	1346.9	1381.6
20°	970.8	1017.7	1073.6	1128.2	1173.5	1212.0	1250.2	1287.8	1321.7	1366.1	1406.4
22.5°	955.9	1012.7	1064.1	1117.4	1164.0	1206.0	1249.1	1291.9	1336.9	1387.2	1437.5
25°	929.3	986.8	1041.5	1094.0	1140.9	1193.4	1239.6	1296.7	1354.3	1420.7	1483.4
27.5°	901.6	956.8	1006.8	1057.5	1112.3	1171.7	1231.6	1296.5	1371.8	1455.7	1544.1
30°	879.3	931.4	980.1	1032.1	1089.2	1156.2	1221.8	1298.9	1386.0	1480.4	1585.4
32.5°	853.2	901.2	948.5	1003.7	1065.9	1136.5	1213.0	1297.5	1402.3	1509.6	1617.6
35°	808.6	848.8	897.5	956.3	1026.6	1107.5	1196.0	1295.8	1416.1	1539.3	1630.4
37.5°	755.7	793.1	844.4	908.9	982.6	1069.3	1174.4	1292.9	1420.6	1518.8	1548.2
40°	720.2	754.8	808.2	875.1	950.4	1042.3	1157.4	1282.7	1406.4	1469.0	1444.9
42.5°	682.2	718.6	770.5	836.8	917.9	1017.9	1136.1	1261.4	1365.1	1388.8	1305.4
45°	622.3	660.0	711.2	778.1	865.4	973.7	1096.9	1210.8	1270.5	1227.7	1098.6
47.5°	566.7	602.0	649.5	718.5	808.5	920.6	1039.3	1130.1	1134.8	1032.8	894.9
50°	528.8	561.3	609.2	678.2	767.5	881.0	988.1	1059.6	1027.4	911.9	779.3
52.5°	491.5	523.4	570.6	639.0	727.2	831.2	930.8	981.0	920.5	801.8	688.6
55°	437.7	465.7	511.8	574.9	658.8	755.3	839.9	857.3	778.5	661.7	569.8
57.5°	385.2	411.3	453.3	511.4	588.0	673.5	739.7	736.1	652.8	552.5	479.6
60°	349.7	375.1	412.4	469.0	538.9	612.6	669.3	655.7	573.2	486.8	425.5
62.5°	317.9	340.6	375.8	425.3	489.1	557.4	604.0	584.0	503.1	427.5	379.0
65°	270.9	290.0	320.1	362.4	415.3	471.7	507.6	481.8	412.8	353.9	315.0
67.5°	226.2	241.4	266.6	300.4	345.5	390.8	412.7	386.7	331.5	288.5	259.7
70°	197.7	211.2	230.7	260.8	300.2	338.3	354.7	331.5	284.1	247.2	226.5
72.5°	169.3	180.4	197.5	224.5	256.1	289.2	303.6	281.4	242.4	211.3	191.9
75°	130.9	138.4	150.3	168.9	193.9	220.1	228.2	208.7	183.8	160.5	147.7
77.5°	93.7	100.1	109.1	120.8	138.5	155.2	162.2	151.0	131.7	116.9	106.5
80°	72.0	75.3	83.0	92.7	106.7	117.2	121.9	114.7	101.2	90.2	82.1
82.5°	51.3	54.7	59.3	67.3	76.2	83.4	88.4	83.6	73.8	65.1	60.4
85°	24.9	27.1	29.6	33.0	39.8	44.0	43.6	40.6	36.9	33.4	30.9
87.5°	9.0	9.6	10.9	12.9	14.1	15.7	16.6	16.0	14.9	14.0	13.1
90°	1.3	2.5	3.8	5.1	6.4	7.0	8.3	8.9	10.2	10.8	11.5
92.5°	9.5	14.8	22.7	33.7	52.3	87.1	145.4	208.8	205.5	166.4	113.0
95°	21.7	26.7	33.8	47.8	76.5	144.7	284.9	460.9	564.8	552.7	458.4
97.5°	35.7	39.3	46.3	58.9	79.6	124.7	227.5	411.6	603.2	699.3	682.7
100°	45.9	48.4	55.4	67.6	86.7	123.7	206.5	367.2	575.7	735.0	784.1
102.5°	56.1	58.1	65.6	76.7	95.4	128.2	197.9	333.5	527.2	713.6	818.2
105°	72.1	75.3	81.6	91.8	109.7	137.7	194.4	300.9	462.2	645.1	798.1
107.5°	89.6	92.7	97.9	108.5	124.6	151.7	200.3	287.1	417.4	575.3	726.2
110°	101.3	103.9	109.7	119.2	135.7	161.9	205.9	283.1	396.5	535.5	673.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	113.1	115.1	120.8	130.4	146.5	171.6	213.0	283.1	384.3	505.9	631.4
115°	130.0	132.0	137.7	147.2	163.2	186.8	223.7	284.9	371.0	473.6	578.9
117.5°	146.0	148.1	153.8	164.6	180.0	202.4	236.0	289.2	364.5	454.4	544.9
120°	156.2	158.7	164.4	175.3	191.3	213.5	244.2	293.3	361.4	443.7	526.5
122.5°	166.4	168.4	174.1	186.1	201.9	224.3	253.3	296.8	358.9	434.5	512.8
125°	179.8	183.0	188.7	200.8	217.4	238.4	265.8	302.8	355.7	422.0	492.8
127.5°	191.0	195.1	202.4	215.2	231.8	252.1	277.3	309.6	354.2	410.5	472.4
130°	197.6	202.7	211.0	224.4	241.0	260.7	284.9	313.6	353.2	402.9	459.6
132.5°	203.3	209.4	218.7	232.5	249.2	268.9	291.6	318.2	353.2	396.8	446.9
135°	211.7	219.3	229.5	242.9	260.1	279.9	300.9	324.5	353.2	389.5	430.3
137.5°	221.4	228.6	238.8	251.9	269.6	287.6	307.8	330.2	353.9	383.0	416.3
140°	227.6	235.2	245.4	257.6	274.8	293.3	312.3	332.7	354.4	379.9	408.6
142.5°	234.2	241.3	251.5	263.2	279.3	296.8	315.0	334.3	355.0	377.4	402.0
145°	244.8	251.2	260.1	271.6	286.3	302.8	318.7	336.0	354.4	373.6	393.3
147.5°	255.5	261.0	269.3	279.2	292.1	306.6	321.1	336.6	352.8	369.6	385.1
150°	262.6	267.1	275.4	284.3	295.1	309.2	322.5	336.6	351.2	366.6	380.6
152.5°	269.3	273.2	280.5	288.9	298.7	311.7	323.6	336.1	349.2	363.0	375.4
155°	277.9	281.8	288.1	294.5	303.5	314.3	324.5	334.7	345.5	357.0	367.9
157.5°	286.3	289.3	294.7	300.4	307.1	316.4	325.1	333.0	341.7	351.4	360.2
160°	291.3	293.9	298.3	303.5	309.2	317.5	325.1	331.5	339.2	346.8	355.1
162.5°	296.0	298.5	302.4	306.5	311.2	318.5	324.6	330.0	336.1	342.7	349.4
165°	302.1	304.1	307.3	309.8	313.6	318.7	323.8	327.7	331.5	336.6	341.7
167.5°	307.4	308.5	310.3	312.1	314.5	318.7	322.3	324.1	327.0	330.6	334.3
170°	310.5	311.1	312.3	313.6	315.5	318.7	321.3	322.5	324.5	327.0	330.2
172.5°	312.0	312.6	313.9	314.6	315.5	318.2	320.2	320.5	321.4	323.4	325.6
175°	314.3	315.0	315.5	315.5	315.5	317.5	318.7	318.1	318.1	318.7	320.7
177.5°	315.7	315.7	316.2	315.7	315.7	316.7	317.2	316.2	316.2	316.7	317.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1043.1	1045.9	1051.6	1049.5	1052.3	1053.6	1055.0
5°	1127.4	1140.9	1146.9	1146.0	1154.9	1152.8	1150.6
7.5°	1222.5	1236.8	1244.7	1254.7	1260.4	1260.8	1265.8
10°	1276.4	1295.0	1302.7	1313.2	1320.0	1323.8	1323.4
12.5°	1317.7	1332.3	1349.4	1354.5	1363.7	1368.5	1366.8
15°	1367.4	1390.7	1408.5	1417.4	1428.8	1432.2	1436.9
17.5°	1411.8	1443.0	1463.8	1491.3	1501.8	1508.1	1504.4
20°	1445.3	1486.4	1507.2	1540.2	1558.4	1568.1	1564.7
22.5°	1484.9	1529.4	1567.7	1596.4	1624.1	1637.2	1639.9
25°	1552.8	1613.8	1670.1	1707.8	1742.1	1750.1	1767.9
27.5°	1628.7	1700.6	1760.8	1800.4	1824.3	1833.3	1838.8
30°	1676.5	1748.0	1793.3	1818.7	1826.4	1825.5	1824.6
32.5°	1699.8	1744.7	1753.3	1746.2	1728.8	1714.1	1698.7
35°	1666.7	1633.3	1583.3	1519.0	1471.5	1423.8	1419.0
37.5°	1499.0	1392.0	1308.9	1216.0	1162.5	1129.4	1106.4
40°	1341.2	1219.7	1118.9	1040.6	985.9	964.4	943.2
42.5°	1169.8	1053.7	964.5	899.0	857.9	834.0	817.3
45°	950.4	848.0	778.1	730.7	698.1	679.5	668.9
47.5°	778.8	703.0	643.7	609.4	586.9	572.4	572.5
50°	686.6	614.2	574.9	547.8	528.3	516.9	519.0
52.5°	605.0	551.0	517.3	494.6	480.2	473.2	473.0
55°	505.9	466.9	444.9	428.4	418.7	410.7	412.4
57.5°	432.8	399.9	385.1	371.5	364.7	361.4	356.8
60°	387.3	362.0	349.3	338.3	331.5	329.0	324.2
62.5°	347.1	327.1	314.7	305.7	299.6	298.8	295.1
65°	291.7	276.5	265.5	261.2	254.9	253.2	253.2
67.5°	240.4	229.5	221.0	217.1	214.3	214.7	212.7
70°	208.3	199.4	193.9	189.6	187.5	187.9	186.3
72.5°	182.2	172.3	167.5	164.9	162.2	163.2	162.6
75°	138.0	132.9	130.4	127.8	126.1	125.3	124.5
77.5°	101.3	96.9	94.9	93.5	93.8	91.7	93.3
80°	78.4	74.5	73.2	71.1	70.7	70.7	70.3
82.5°	57.3	55.2	54.3	52.5	51.8	52.4	51.3
85°	29.6	28.0	27.6	27.6	26.7	25.8	28.0
87.5°	13.3	12.1	12.3	12.0	12.0	11.7	11.1
90°	12.1	12.7	14.0	14.0	14.0	14.7	14.7
92.5°	82.0	61.7	52.3	44.1	42.6	41.7	40.7
95°	361.4	283.1	229.5	184.3	165.1	160.0	149.8
97.5°	614.7	538.3	463.8	424.4	388.7	370.2	362.1
100°	752.8	687.2	620.9	576.9	531.0	507.4	497.3
102.5°	837.6	806.0	761.2	714.1	681.4	655.8	648.2
105°	885.5	913.5	906.5	886.1	865.0	852.3	844.7
107.5°	842.8	914.8	948.0	958.4	958.2	954.1	948.9
110°	794.3	884.2	938.3	967.0	979.2	983.7	983.7



TEST NUMBER: P333225-930

CATALOG NUMBER: S125DIP-S850D810U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	746.3	837.2	901.2	943.1	963.8	974.9	979.6
115°	677.7	765.0	834.5	884.2	914.8	932.6	940.9
117.5°	630.1	705.3	769.1	818.8	850.4	868.1	873.2
120°	603.1	673.2	729.3	776.4	807.1	824.3	829.3
122.5°	583.7	646.1	698.7	740.8	768.8	786.0	790.6
125°	557.8	613.3	659.2	694.9	721.0	735.0	741.4
127.5°	533.0	584.8	627.8	660.1	683.2	696.5	699.3
130°	515.8	565.4	606.9	638.8	659.8	672.5	676.4
132.5°	499.4	544.5	584.4	616.3	637.3	649.1	653.4
135°	474.3	515.1	551.4	579.4	600.5	612.0	615.8
137.5°	451.8	485.8	516.6	541.8	560.8	571.4	575.7
140°	438.5	467.9	494.6	518.3	534.8	544.4	547.6
142.5°	427.4	452.6	475.8	495.9	509.9	518.9	521.5
145°	413.1	432.8	450.0	465.4	476.2	483.2	485.8
147.5°	401.2	416.4	429.4	441.5	450.2	454.3	455.4
150°	394.6	406.7	418.2	427.8	435.4	438.0	438.5
152.5°	388.0	399.1	408.0	416.0	422.2	424.7	425.3
155°	378.1	386.9	394.0	400.3	404.8	406.7	407.3
157.5°	368.6	375.4	381.0	386.0	389.6	391.4	391.3
160°	361.4	367.9	372.3	376.7	379.9	381.2	380.6
162.5°	355.3	360.7	364.6	368.1	370.7	371.0	370.9
165°	346.2	350.0	353.2	355.7	357.0	357.0	357.0
167.5°	337.2	340.1	342.4	343.7	344.9	344.4	344.2
170°	332.2	334.0	335.3	336.6	337.2	337.2	336.6
172.5°	327.5	329.0	329.7	330.0	331.1	330.1	329.5
175°	320.7	322.0	322.0	322.0	322.5	321.3	320.7
177.5°	317.7	317.7	317.7	317.2	317.7	316.2	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2

(END OF REPORT)