

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333603-930

Luminaire Tested: **S125RDIP-S1090D1035U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333603-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6472.2 lumens  
Efficiency: N/A  
Efficacy: 107.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333603-930

CATALOG NUMBER: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P333603-930

CATALOG NUMBER: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43	38
3	82	73	66	60	76	68	62	56	58	54	50	50	46	43	41	39	37	33
4	75	65	57	51	70	60	53	48	52	47	42	44	40	37	37	34	32	28
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28	25
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	32	26	47	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9412	9412	9412
5°	9433	9326	9383
10°	9362	9239	9239
15°	9250	9052	8978
20°	9108	8790	8685
25°	8941	8533	8345
30°	8733	8232	7970
35°	8521	7923	7550
40°	8323	7599	7136
45°	8082	7238	6685
50°	7840	6845	6215
55°	7560	6469	5713
60°	7279	6013	5174
65°	6946	5483	4557
70°	6567	4823	3928
75°	6041	4065	3266
80°	5322	3195	2741
85°	4483	2608	2445



TEST NUMBER: P333603-930

CATALOG NUMBER: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.0	2.1
10°-20°	382.9	5.9
20°-30°	555.3	8.6
30°-40°	632.9	9.8
40°-50°	616.9	9.5
50°-60°	519.3	8.0
60°-70°	364.0	5.6
70°-80°	187.1	2.9
80°-90°	49.5	0.8
90°-100°	292.6	4.5
100°-110°	629.0	9.7
110°-120°	590.3	9.1
120°-130°	478.4	7.4
130°-140°	383.9	5.9
140°-150°	289.7	4.5
150°-160°	203.9	3.2
160°-170°	120.2	1.9
170°-180°	39.1	0.6
0°-30°	1075.3	16.6
0°-40°	1708.1	26.4
0°-60°	2844.3	43.9
0°-90°	3444.9	53.2
90°-120°	1512.0	23.4
90°-150°	2664.1	41.2
90°-180°	3027.0	46.8
0°-180°	6472.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1457	1457	1457	1457	1457	
5°	1455	1450	1438	1449	1447	138
15°	1384	1376	1354	1352	1343	390
25°	1255	1237	1198	1183	1171	577
35°	1081	1053	1005	974	958	676
45°	885	851	792	750	732	682
55°	671	635	574	527	507	600
65°	454	416	359	316	298	450
75°	242	208	163	140	131	256
85°	60	42	35	34	33	68
90°	1	7	13	17	19	4
95°	27	79	721	327	191	29
105°	92	129	590	1162	1078	97
115°	164	198	474	1021	1201	162
125°	228	267	454	812	947	202
135°	267	321	451	681	786	207
145°	311	356	452	564	620	195
155°	355	382	441	499	520	163
165°	387	398	423	449	456	109
175°	403	403	406	411	409	38
180°	404	404	404	404	404	



TEST NUMBER: P333603-930

CATALOG NUMBER: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1459.9	1459.3	1458.7	1458.1	1457.5	1456.3	1454.3	1452.4	1450.4	1448.5	1450.4
5°	1455.1	1454.1	1453.1	1452.1	1451.2	1449.3	1446.6	1443.9	1441.2	1438.5	1441.0
7.5°	1440.7	1439.8	1438.8	1437.9	1437.0	1434.9	1431.7	1428.5	1425.2	1422.0	1423.8
10°	1427.5	1426.8	1426.0	1425.3	1424.6	1422.5	1419.1	1415.7	1412.3	1408.8	1409.6
12.5°	1412.5	1411.6	1410.7	1409.7	1408.8	1406.1	1401.5	1396.9	1392.3	1387.6	1388.2
15°	1383.5	1382.0	1380.5	1379.1	1377.6	1374.4	1369.2	1364.1	1358.9	1353.8	1353.6
17.5°	1350.7	1348.4	1346.2	1343.9	1341.7	1337.3	1330.9	1324.5	1317.9	1311.5	1310.3
20°	1325.2	1322.7	1320.3	1317.8	1315.4	1310.3	1302.4	1294.6	1286.8	1279.0	1277.7
22.5°	1297.0	1294.5	1292.1	1289.6	1287.2	1281.9	1273.7	1265.4	1257.2	1249.0	1246.6
25°	1254.7	1251.1	1247.4	1243.7	1240.1	1233.7	1224.7	1215.6	1206.6	1197.5	1194.3
27.5°	1206.3	1201.8	1197.3	1192.9	1188.5	1181.5	1171.7	1162.0	1152.3	1142.6	1138.2
30°	1171.1	1166.4	1161.8	1157.2	1152.5	1145.0	1134.7	1124.5	1114.2	1103.9	1098.3
32.5°	1136.7	1131.3	1125.8	1120.5	1115.0	1107.1	1096.6	1086.1	1075.6	1065.2	1059.0
35°	1080.8	1075.0	1069.1	1063.2	1057.4	1048.9	1037.9	1026.9	1015.9	1004.9	997.8
37.5°	1026.0	1018.9	1011.7	1004.6	997.4	988.2	976.8	965.5	954.1	942.8	934.3
40°	987.2	979.9	972.6	965.2	957.9	948.4	936.6	924.9	913.1	901.4	892.1
42.5°	946.7	939.2	931.7	924.1	916.6	906.8	894.6	882.6	870.4	858.3	849.4
45°	884.9	877.8	870.7	863.6	856.6	846.3	832.8	819.4	805.9	792.5	782.7
47.5°	820.8	813.3	805.8	798.4	790.9	780.4	766.9	753.3	739.7	726.2	716.1
50°	780.3	772.3	764.2	756.1	748.0	737.0	723.1	709.1	695.2	681.3	671.0
52.5°	736.3	728.1	719.7	711.5	703.3	692.5	679.4	666.2	653.1	639.9	628.8
55°	671.4	663.6	655.7	647.9	640.1	629.3	615.6	601.9	588.2	574.5	563.5
57.5°	605.8	597.5	589.1	580.7	572.3	561.6	548.4	535.2	522.0	508.7	498.0
60°	563.5	555.0	546.4	537.9	529.3	518.4	505.2	492.0	478.7	465.5	454.8
62.5°	518.6	510.5	502.3	494.1	485.9	475.2	461.8	448.3	435.0	421.5	411.6
65°	454.5	446.2	437.9	429.6	421.3	410.7	397.7	384.7	371.8	358.8	349.0
67.5°	390.9	382.6	374.3	366.0	357.7	347.3	334.8	322.5	310.1	297.6	288.7
70°	347.8	339.5	331.2	322.9	314.5	304.3	292.0	279.8	267.6	255.4	247.8
72.5°	305.6	297.4	289.3	281.2	273.0	263.3	251.8	240.4	228.9	217.5	210.5
75°	242.1	234.8	227.5	220.1	212.8	204.0	193.7	183.4	173.2	162.9	157.5
77.5°	179.2	173.3	167.5	161.6	155.7	148.6	140.5	132.2	124.0	115.8	112.0
80°	143.1	137.2	131.3	125.5	119.6	113.2	106.4	99.5	92.7	85.9	83.6
82.5°	107.9	102.6	97.3	92.0	86.7	81.8	77.0	72.3	67.7	62.9	62.0
85°	60.5	56.1	51.7	47.3	42.9	40.1	38.9	37.7	36.4	35.2	35.0
87.5°	20.4	19.2	18.2	17.1	16.1	15.7	15.6	15.7	15.7	15.8	16.0
90°	0.8	1.6	3.3	4.9	6.5	8.2	9.0	10.6	11.4	13.0	13.9
92.5°	9.9	12.1	18.9	28.9	43.0	66.8	111.2	185.7	266.6	262.4	212.4
95°	26.8	27.6	34.2	43.1	61.1	97.7	184.7	363.8	588.5	721.1	705.6
97.5°	44.6	45.6	50.1	59.1	75.2	101.6	159.2	290.4	525.5	770.1	892.8
100°	57.0	58.6	61.9	70.8	86.3	110.7	157.9	263.7	468.8	734.9	938.4
102.5°	70.7	71.6	74.2	83.8	98.0	121.7	163.8	252.7	425.8	673.1	911.1
105°	92.0	92.0	96.0	104.2	117.2	140.0	175.8	248.3	384.2	590.0	823.7
107.5°	112.8	114.5	118.3	125.0	138.5	159.1	193.7	255.8	366.6	533.0	734.4
110°	127.8	129.4	132.6	140.0	152.2	173.3	206.8	262.9	361.3	506.2	683.6



TEST NUMBER: P333603-930

CATALOG NUMBER: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	142.8	144.4	147.0	154.3	166.5	187.0	219.1	272.0	361.3	490.6	645.9
115°	164.4	166.0	168.4	175.8	188.0	208.4	238.5	285.7	363.8	473.7	604.7
117.5°	183.9	186.4	189.0	196.3	210.2	229.8	258.4	301.3	369.2	465.4	580.2
120°	197.0	199.4	202.7	210.0	223.8	244.2	272.6	311.7	374.4	461.5	566.5
122.5°	210.7	212.4	215.0	222.3	237.5	257.9	286.3	323.4	379.0	458.2	554.7
125°	227.9	229.5	233.6	240.9	256.4	277.5	304.4	339.4	386.6	454.1	538.8
127.5°	241.4	243.9	249.1	258.4	274.8	296.0	321.8	354.0	395.3	452.2	524.2
130°	249.9	252.3	258.9	269.4	286.5	307.6	332.9	363.8	400.5	450.9	514.4
132.5°	256.4	259.4	267.3	279.2	296.9	318.0	343.3	372.3	406.3	450.9	506.5
135°	266.9	270.2	280.0	293.0	310.1	332.1	357.3	384.2	414.3	450.9	497.3
137.5°	280.3	282.7	291.9	304.9	321.6	344.3	367.2	393.0	421.6	451.8	489.0
140°	288.1	290.6	300.4	313.3	328.8	350.8	374.4	398.8	424.9	452.5	485.1
142.5°	297.3	299.1	308.1	321.1	336.0	356.6	379.0	402.0	426.8	453.1	481.8
145°	310.9	312.5	320.7	332.1	346.7	365.4	386.6	406.9	428.9	452.5	477.0
147.5°	325.2	326.2	333.2	343.8	356.4	372.9	391.5	409.9	429.7	450.4	471.9
150°	333.7	335.3	341.0	351.6	363.0	376.8	394.8	411.8	429.7	448.4	468.0
152.5°	342.8	343.8	348.9	358.1	368.8	381.4	398.0	413.1	429.1	445.9	463.4
155°	354.8	354.8	359.7	367.9	376.0	387.4	401.2	414.3	427.3	441.2	455.8
157.5°	365.6	365.4	369.3	376.3	383.5	392.2	404.0	415.1	425.2	436.3	448.6
160°	372.8	371.9	375.2	380.9	387.4	394.8	405.3	415.1	423.2	433.0	442.8
162.5°	378.6	377.8	381.1	386.1	391.3	397.4	406.6	414.4	421.3	429.1	437.6
165°	387.4	385.8	388.2	392.3	395.6	400.5	406.9	413.4	418.3	423.2	429.7
167.5°	393.3	392.5	394.0	396.2	398.5	401.5	406.9	411.5	413.8	417.5	422.1
170°	397.2	396.4	397.2	398.8	400.5	402.8	406.9	410.2	411.8	414.3	417.5
172.5°	399.8	398.4	399.2	400.7	401.7	402.8	406.3	408.9	409.2	410.3	412.9
175°	402.8	401.2	402.0	402.8	402.8	402.8	405.3	406.9	406.1	406.1	406.9
177.5°	404.3	403.0	403.0	403.7	403.0	403.0	404.3	405.0	403.7	403.7	404.3
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333603-930

CATALOG NUMBER: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3	1457.3
2.5°	1452.4	1454.3	1456.3	1457.1	1456.9	1456.8	1456.5	1456.4
5°	1443.4	1445.9	1448.3	1449.3	1448.8	1448.3	1447.8	1447.3
7.5°	1425.5	1427.2	1428.9	1429.5	1428.9	1428.4	1427.8	1427.3
10°	1410.3	1411.0	1411.8	1411.8	1411.0	1410.3	1409.6	1408.8
12.5°	1388.8	1389.3	1389.8	1389.5	1388.4	1387.3	1386.2	1385.0
15°	1353.3	1353.1	1352.8	1351.6	1349.4	1347.2	1345.0	1342.8
17.5°	1309.0	1307.8	1306.6	1305.1	1303.3	1301.5	1299.7	1297.9
20°	1276.5	1275.3	1274.1	1272.4	1270.2	1268.0	1265.8	1263.6
22.5°	1244.2	1241.8	1239.4	1237.3	1235.5	1233.7	1231.8	1230.0
25°	1191.2	1188.0	1184.8	1181.9	1179.2	1176.5	1173.8	1171.1
27.5°	1133.8	1129.4	1124.9	1121.4	1118.8	1116.1	1113.5	1111.0
30°	1092.7	1087.0	1081.4	1077.5	1075.3	1073.1	1070.9	1068.7
32.5°	1052.8	1046.5	1040.3	1035.8	1033.1	1030.3	1027.4	1024.7
35°	990.7	983.6	976.5	971.3	967.8	964.4	961.0	957.6
37.5°	925.8	917.3	908.7	902.9	899.5	896.2	892.8	889.5
40°	882.8	873.5	864.2	858.1	855.2	852.2	849.3	846.4
42.5°	840.5	831.5	822.6	816.0	811.7	807.5	803.2	798.8
45°	772.9	763.1	753.3	746.6	742.9	739.2	735.6	731.9
47.5°	706.0	695.9	685.9	678.8	674.7	670.7	666.7	662.6
50°	660.7	650.4	640.2	633.2	629.6	625.9	622.2	618.6
52.5°	617.8	606.7	595.7	588.3	584.7	581.0	577.3	573.6
55°	552.5	541.5	530.5	523.0	519.1	515.2	511.3	507.4
57.5°	487.2	476.5	465.7	458.5	455.1	451.6	448.1	444.7
60°	444.0	433.3	422.5	415.3	411.6	408.0	404.3	400.6
62.5°	401.6	391.6	381.6	374.8	371.1	367.5	363.8	360.1
65°	339.2	329.5	319.7	312.9	309.2	305.6	301.9	298.2
67.5°	279.7	270.8	261.8	255.8	252.9	250.0	247.0	244.1
70°	240.2	232.6	225.0	219.7	216.8	213.9	210.9	208.0
72.5°	203.5	196.5	189.5	185.0	183.0	181.1	179.1	177.2
75°	152.1	146.8	141.4	137.8	136.1	134.4	132.6	130.9
77.5°	108.3	104.5	100.7	98.2	96.9	95.6	94.4	93.1
80°	81.4	79.2	77.0	75.7	75.2	74.7	74.2	73.7
82.5°	60.9	59.8	58.9	58.2	57.9	57.6	57.3	57.0
85°	34.7	34.5	34.2	34.0	33.8	33.5	33.3	33.0
87.5°	16.1	16.3	16.5	16.7	16.5	16.3	16.3	16.1
90°	14.7	15.5	16.3	17.9	17.9	17.9	18.8	18.8
92.5°	144.2	104.7	78.8	66.8	56.3	54.4	53.2	51.9
95°	585.2	461.5	361.3	293.0	235.2	210.8	204.3	191.3
97.5°	871.6	784.7	687.2	592.2	541.9	496.3	472.7	462.3
100°	1001.1	961.2	877.3	792.7	736.5	678.0	647.8	634.9
102.5°	1044.7	1069.3	1029.1	971.8	911.7	870.1	837.3	827.5
105°	1019.0	1130.5	1166.3	1157.3	1131.3	1104.5	1088.2	1078.4
107.5°	927.2	1076.0	1167.9	1210.4	1223.6	1223.4	1218.1	1211.5
110°	859.5	1014.1	1128.9	1198.1	1234.7	1250.1	1255.8	1255.8





TEST NUMBER: P333603-930

CATALOG NUMBER: S125RDIP-S1090D1035U930-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	806.1	952.9	1068.9	1150.6	1204.0	1230.6	1244.8	1250.6
115°	739.0	865.2	976.6	1065.4	1128.9	1167.9	1190.7	1201.3
117.5°	695.7	804.5	900.5	981.9	1045.4	1085.7	1108.3	1114.8
120°	672.3	770.0	859.5	931.1	991.3	1030.4	1052.4	1058.9
122.5°	654.7	745.2	824.9	892.0	945.7	981.5	1003.6	1009.4
125°	629.2	712.2	782.9	841.6	887.1	920.5	938.4	946.6
127.5°	603.1	680.6	746.7	801.5	842.9	872.3	889.2	892.8
130°	586.9	658.4	721.9	774.9	815.5	842.4	858.7	863.6
132.5°	570.5	637.6	695.2	746.2	786.8	813.8	828.7	834.2
135°	549.3	605.5	657.6	704.0	739.8	766.7	781.3	786.2
137.5°	531.5	576.9	620.2	659.6	691.6	716.1	729.6	734.9
140°	521.7	559.9	597.4	631.6	661.7	682.9	695.0	699.1
142.5°	513.2	545.6	577.9	607.5	633.1	650.9	662.5	665.9
145°	502.1	527.4	552.6	574.6	594.1	608.0	616.9	620.2
147.5°	491.8	512.3	531.7	548.2	563.7	574.8	580.0	581.5
150°	485.9	503.8	519.3	533.9	546.1	555.9	559.1	559.9
152.5°	479.4	495.3	509.5	520.9	531.2	539.0	542.2	543.0
155°	469.6	482.7	494.1	503.0	511.1	516.8	519.3	520.1
157.5°	459.8	470.6	479.4	486.4	492.8	497.4	499.7	499.5
160°	453.3	461.5	469.6	475.3	481.0	485.1	486.7	485.9
162.5°	446.2	453.6	460.5	465.5	469.9	473.4	473.7	473.5
165°	436.3	442.0	446.9	450.9	454.1	455.8	455.8	455.8
167.5°	426.8	430.6	434.3	437.2	438.9	440.3	439.7	439.5
170°	421.6	424.0	426.5	428.1	429.7	430.6	430.6	429.7
172.5°	415.7	418.2	420.0	420.9	421.3	422.7	421.4	420.6
175°	409.4	409.4	411.0	411.0	411.0	411.8	410.2	409.4
177.5°	405.0	405.6	405.6	405.6	405.0	405.6	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7

(END OF REPORT)