

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333606-930

Luminaire Tested: **S125RDIP-S1090D1205U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333606-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6999.3 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	44	43	41	36
3	82	73	66	60	75	68	61	56	58	53	49	48	45	42	40	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	19
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8657	8657	8657	8657
5°	9961	8669	7656	8669
10°	11425	8625	6755	8625
15°	12341	8536	6005	8536
20°	13608	8434	5544	8434
25°	15748	8298	5144	8298
30°	17137	8154	4883	8154
35°	14456	7987	4642	7987
40°	10095	7687	4435	7687
45°	7489	7283	4232	7283
50°	5971	6861	4058	6861
55°	5068	6339	3904	6339
60°	4379	5871	3653	5871
65°	3903	5365	3145	5365
70°	3429	4913	2868	4913
75°	2967	4257	2692	4257
80°	2250	3582	2250	3582
85°	1875	2816	2119	2816



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	1.8
10°-20°	376.7	5.4
20°-30°	597.3	8.5
30°-40°	720.3	10.3
40°-50°	643.2	9.2
50°-60°	493.3	7.0
60°-70°	320.6	4.6
70°-80°	155.9	2.2
80°-90°	39.8	0.6
90°-100°	340.6	4.9
100°-110°	732.2	10.5
110°-120°	687.1	9.8
120°-130°	556.9	8.0
130°-140°	446.9	6.4
140°-150°	337.2	4.8
150°-160°	237.4	3.4
160°-170°	139.9	2.0
170°-180°	45.5	0.7
0°-30°	1102.6	15.8
0°-40°	1822.8	26.0
0°-60°	2959.4	42.3
0°-90°	3475.6	49.7
90°-120°	1759.9	25.1
90°-150°	3100.9	44.3
90°-180°	3524.0	50.3
0°-180°	6999.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1340	1340	1340	1340	1340	
5°	1536	1337	1181	1337	1536	154
15°	1846	1277	898	1277	1846	529
25°	2210	1164	722	1164	2210	1015
35°	1834	1013	589	1013	1834	1108
45°	820	797	463	797	820	654
55°	450	563	347	563	450	408
65°	255	351	206	351	255	254
75°	119	171	108	171	119	127
85°	25	38	29	38	25	30
90°	22	1	22	1	22	16
95°	223	31	223	31	223	315
105°	1255	107	1255	107	1255	1248
115°	1398	191	1398	191	1398	1366
125°	1102	265	1102	265	1102	997
135°	915	311	915	311	915	709
145°	722	362	722	362	722	459
155°	605	413	605	413	605	282
165°	530	451	530	451	530	152
175°	476	469	476	469	476	46
180°	470	470	470	470	470	



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1410.1	1409.2	1411.0	1406.1	1406.6	1399.1	1399.1	1393.3	1385.8	1380.1	1377.4
5°	1536.4	1537.5	1535.3	1527.1	1521.5	1513.3	1503.9	1487.4	1473.7	1460.4	1450.0
7.5°	1666.5	1667.2	1659.9	1657.4	1643.6	1633.5	1612.7	1590.2	1570.3	1545.0	1525.6
10°	1742.2	1741.6	1733.9	1727.9	1715.8	1700.4	1680.0	1653.6	1628.8	1601.3	1574.9
12.5°	1786.2	1784.8	1782.3	1775.0	1763.7	1750.1	1732.8	1706.8	1676.3	1646.3	1615.4
15°	1845.7	1841.8	1834.7	1825.3	1809.3	1793.3	1774.1	1751.0	1721.8	1687.7	1659.1
17.5°	1919.1	1919.3	1908.3	1895.2	1873.6	1845.4	1815.7	1778.4	1738.8	1701.3	1670.8
20°	1979.9	1978.2	1967.2	1942.0	1917.2	1882.0	1847.9	1802.1	1753.7	1704.8	1666.8
22.5°	2067.1	2062.8	2051.3	2018.1	1979.7	1934.4	1882.2	1826.4	1767.8	1712.2	1662.4
25°	2210.0	2206.6	2184.0	2145.5	2091.7	2021.7	1953.5	1877.0	1792.8	1719.6	1659.1
27.5°	2307.6	2304.0	2287.3	2255.3	2205.5	2132.0	2039.6	1937.4	1832.3	1731.6	1644.4
30°	2298.0	2306.2	2304.0	2289.2	2251.8	2185.7	2100.5	1985.4	1860.5	1742.2	1638.2
32.5°	2159.7	2167.1	2186.5	2215.7	2217.9	2191.4	2127.7	2021.5	1892.2	1757.6	1633.4
35°	1833.5	1843.5	1880.9	1939.8	2016.8	2081.1	2094.3	2037.1	1921.0	1776.3	1626.1
37.5°	1409.6	1463.7	1495.3	1557.2	1673.6	1792.0	1905.9	1947.9	1898.4	1768.6	1614.3
40°	1197.4	1210.6	1266.7	1336.6	1434.6	1557.9	1720.2	1837.4	1841.3	1751.0	1595.8
42.5°	1024.8	1041.5	1080.1	1135.9	1219.8	1343.0	1510.7	1665.2	1736.9	1702.6	1571.6
45°	819.9	832.6	860.6	903.6	967.9	1069.8	1213.9	1392.8	1534.7	1590.3	1506.7
47.5°	673.5	680.4	704.8	737.5	785.1	859.3	970.9	1126.2	1296.5	1415.8	1404.1
50°	594.3	602.0	620.7	645.5	685.7	748.4	837.6	966.9	1142.4	1288.2	1317.4
52.5°	532.6	539.1	550.7	574.1	607.3	655.5	727.5	844.5	1002.4	1157.5	1224.9
55°	450.1	454.5	463.9	477.1	503.5	538.2	600.4	681.3	808.9	965.2	1064.2
57.5°	382.1	384.3	390.3	402.5	420.8	446.1	491.0	559.5	651.1	791.8	901.2
60°	339.0	341.2	348.9	357.1	371.5	394.5	429.7	477.6	565.7	681.8	792.4
62.5°	304.6	306.0	309.2	317.5	330.0	347.9	375.6	414.7	484.7	586.7	691.1
65°	255.4	255.8	257.0	263.6	271.3	284.5	302.6	330.2	383.0	460.1	552.4
67.5°	208.0	208.8	212.6	214.9	223.0	229.9	240.6	261.6	298.8	350.7	422.7
70°	181.6	181.1	184.9	187.7	190.4	198.7	205.8	222.9	246.0	285.6	345.6
72.5°	156.9	155.5	157.2	158.2	161.8	167.4	174.6	185.0	202.8	230.2	276.1
75°	118.9	119.4	119.4	120.5	123.3	125.5	127.7	133.1	143.1	161.3	186.0
77.5°	83.4	82.5	84.9	85.2	86.8	89.3	91.2	93.4	97.4	104.8	117.6
80°	60.5	60.5	61.1	62.7	62.2	63.3	66.0	68.2	73.2	77.6	82.0
82.5°	46.5	46.0	46.6	46.9	46.8	47.9	48.8	49.3	51.2	53.4	56.4
85°	25.3	25.3	25.8	25.8	26.4	26.4	27.0	27.0	27.0	27.5	28.0
87.5°	14.0	13.6	13.0	13.0	13.5	13.9	13.3	12.6	12.5	12.3	12.3
90°	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0	16.1	15.2	13.3
92.5°	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9	247.3	305.4	310.4
95°	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1	821.3	839.4	684.9
97.5°	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4	1039.3	896.3	611.6
100°	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2	1092.3	855.4	545.7
102.5°	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0	1060.5	783.4	495.6
105°	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1	958.7	686.8	447.1
107.5°	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2	854.9	620.3	426.6
110°	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4	795.7	589.2	420.6



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2	751.8	571.0	420.6
115°	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2	703.8	551.4	423.5
117.5°	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8	675.2	541.7	429.7
120°	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5	659.3	537.1	435.8
122.5°	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1	645.7	533.4	441.1
125°	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3	627.1	528.6	450.0
127.5°	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0	610.1	526.4	460.0
130°	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1	598.8	524.8	466.1
132.5°	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1	589.6	524.8	472.9
135°	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4	578.9	524.8	482.2
137.5°	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6	569.2	525.9	490.7
140°	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2	564.6	526.7	494.5
142.5°	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4	560.8	527.5	496.8
145°	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5	555.1	526.7	499.3
147.5°	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4	549.3	524.2	500.2
150°	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6	544.7	522.0	500.2
152.5°	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0	539.4	518.9	499.5
155°	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6	530.5	513.5	497.3
157.5°	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2	522.2	507.8	494.9
160°	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7	515.4	504.0	492.6
162.5°	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3	509.3	499.5	490.3
165°	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8	500.2	492.6	486.9
167.5°	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8	491.3	486.0	481.6
170°	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7	486.0	482.2	479.4
172.5°	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9	480.7	477.7	476.3
175°	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5	473.7	472.7	472.7
177.5°	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4	470.7	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1377.4	1374.4	1368.6	1363.3	1356.7	1351.0	1347.1	1342.2	1336.1	1328.6	1322.4
5°	1438.4	1426.3	1410.4	1396.6	1379.0	1365.2	1351.0	1337.2	1323.4	1305.8	1290.4
7.5°	1506.0	1481.0	1456.7	1426.1	1398.4	1373.6	1349.8	1325.8	1302.2	1277.2	1253.1
10°	1547.4	1517.1	1483.5	1445.0	1409.8	1376.2	1345.4	1315.2	1283.3	1255.2	1224.9
12.5°	1586.2	1547.0	1508.6	1460.0	1417.7	1376.7	1337.5	1299.8	1265.7	1229.2	1196.8
15°	1621.1	1582.6	1539.7	1480.3	1421.4	1371.8	1325.6	1276.7	1234.3	1193.5	1157.2
17.5°	1634.7	1594.2	1544.4	1487.3	1422.9	1360.7	1301.1	1247.4	1197.5	1150.1	1109.2
20°	1629.4	1590.3	1539.1	1484.7	1415.8	1351.0	1286.5	1227.1	1171.6	1121.4	1078.0
22.5°	1616.6	1576.2	1526.8	1469.3	1403.9	1335.1	1266.3	1202.9	1144.7	1092.8	1045.5
25°	1597.5	1542.5	1491.8	1435.7	1373.5	1305.3	1234.3	1164.4	1102.2	1049.4	997.7
27.5°	1577.5	1508.9	1444.5	1388.7	1323.0	1262.1	1193.7	1122.0	1056.6	1002.8	949.7
30°	1559.5	1482.5	1411.4	1348.2	1286.0	1228.2	1163.3	1093.4	1026.3	970.7	916.8
32.5°	1537.0	1455.1	1377.1	1304.2	1244.1	1186.8	1128.0	1061.3	995.9	938.6	883.8
35°	1508.9	1404.4	1319.6	1241.9	1175.4	1119.8	1067.0	1013.1	947.6	888.2	834.8
37.5°	1471.9	1353.2	1255.2	1170.7	1100.4	1044.6	1002.9	953.7	893.9	837.0	787.4
40°	1449.4	1316.3	1208.9	1125.4	1051.6	992.7	953.7	911.8	857.4	804.0	754.4
42.5°	1419.5	1282.4	1162.3	1075.1	1000.9	944.3	904.7	868.2	822.6	772.3	719.2
45°	1360.8	1216.7	1090.6	997.1	922.3	866.7	829.8	797.4	762.7	716.5	670.3
47.5°	1284.4	1148.1	1016.3	914.1	840.8	789.2	753.4	727.8	703.0	663.7	618.8
50°	1223.3	1091.8	963.0	864.0	785.8	736.8	703.3	682.9	660.3	624.6	587.2
52.5°	1151.0	1033.6	907.5	806.2	732.5	686.6	654.4	634.1	615.5	586.3	550.6
55°	1037.3	934.4	818.8	726.9	659.3	613.0	582.2	563.0	552.0	527.2	499.1
57.5°	906.0	832.3	730.3	641.7	581.9	536.2	513.6	497.3	484.8	467.3	447.5
60°	814.4	762.7	671.3	587.2	532.1	488.6	468.3	454.5	443.0	428.1	412.7
62.5°	721.5	683.9	604.5	532.1	481.5	445.1	426.0	413.6	400.3	390.3	375.3
65°	597.0	563.5	508.4	451.8	405.0	375.9	362.1	351.1	342.8	331.8	321.4
67.5°	464.5	450.8	412.8	373.7	340.1	314.2	302.3	294.6	284.7	278.1	270.9
70°	383.0	376.4	349.4	323.6	292.2	274.6	263.6	260.2	248.2	241.6	236.6
72.5°	310.8	307.7	292.2	274.3	252.2	236.8	226.6	222.9	215.2	209.9	206.7
75°	213.0	214.1	211.3	199.7	191.5	181.6	172.8	170.6	165.1	160.7	157.9
77.5°	134.7	140.3	140.6	140.0	136.7	130.6	127.0	125.4	119.9	118.3	117.6
80°	92.5	98.5	104.0	103.5	102.3	100.7	97.9	96.3	93.5	91.9	90.8
82.5°	61.6	67.3	71.8	74.8	74.6	73.0	71.1	70.4	69.8	68.6	68.3
85°	29.2	30.2	31.9	35.8	38.5	39.1	38.5	38.0	36.3	36.9	37.4
87.5°	12.6	12.2	12.5	12.1	11.3	13.0	14.0	14.3	13.6	13.0	12.6
90°	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0	1.9	3.8	5.7
92.5°	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6	14.0	22.0	33.8
95°	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2	32.2	39.8	50.2
97.5°	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9	53.1	58.4	68.8
100°	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3	68.2	72.0	82.4
102.5°	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3	83.4	86.4	97.6
105°	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0	107.0	111.8	121.2
107.5°	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3	133.2	137.7	145.5
110°	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7	150.7	154.4	163.0



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2	168.0	171.0	179.6
115°	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4	193.2	196.1	204.6
117.5°	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1	217.0	220.0	228.5
120°	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3	232.1	235.9	244.4
122.5°	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2	247.3	250.3	258.8
125°	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2	267.2	271.9	280.4
127.5°	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0	283.8	289.9	300.7
130°	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8	293.7	301.3	313.6
132.5°	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4	302.0	311.1	325.0
135°	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7	314.5	325.9	341.0
137.5°	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3	329.1	339.7	354.9
140°	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3	338.2	349.6	364.8
142.5°	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9	348.1	358.7	373.8
145°	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9	363.8	373.2	386.5
147.5°	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5	379.7	387.8	400.1
150°	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4	390.3	397.0	409.3
152.5°	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0	400.1	406.0	416.9
155°	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0	413.0	418.7	428.2
157.5°	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6	425.3	429.9	438.1
160°	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9	432.9	436.8	443.4
162.5°	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7	439.8	443.5	449.4
165°	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9	449.1	451.9	456.6
167.5°	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8	456.8	458.5	461.1
170°	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3	461.4	462.3	464.2
172.5°	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4	463.7	464.6	466.4
175°	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0	467.0	468.0	469.0
177.5°	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7	469.1	469.1	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1318.0	1311.9	1307.5	1298.7	1292.5	1289.9	1285.0	1283.7	1288.5	1285.0	1284.6
5°	1278.9	1262.9	1250.3	1237.5	1223.8	1215.0	1201.8	1199.6	1196.3	1191.3	1190.3
7.5°	1231.8	1211.0	1194.7	1173.9	1155.7	1141.1	1124.5	1116.7	1112.5	1106.0	1097.5
10°	1200.1	1175.4	1153.4	1132.5	1109.9	1091.8	1075.2	1062.6	1054.3	1046.6	1043.3
12.5°	1168.9	1143.7	1115.5	1090.2	1065.0	1044.6	1026.4	1018.1	1009.0	1000.0	992.3
15°	1120.4	1086.8	1056.0	1026.8	1005.3	983.3	965.7	953.7	939.9	936.0	921.2
17.5°	1068.9	1035.9	999.9	969.1	944.3	920.1	900.7	887.0	876.6	862.4	855.6
20°	1036.7	997.7	962.5	934.4	906.9	878.2	858.4	846.9	837.0	825.4	819.9
22.5°	1002.4	964.2	928.1	895.2	867.2	839.1	825.0	813.0	801.8	791.1	783.8
25°	951.9	913.5	875.5	841.4	812.2	791.8	775.3	761.6	755.5	745.1	737.4
27.5°	902.1	861.2	821.8	787.7	764.9	744.8	731.2	720.3	709.4	700.3	693.6
30°	870.0	828.2	785.2	758.3	734.1	714.8	699.9	689.5	681.3	673.0	668.1
32.5°	837.9	794.8	756.6	727.5	704.6	687.9	672.6	662.7	654.0	644.8	639.0
35°	786.4	742.3	711.5	682.9	660.3	644.9	634.5	620.2	613.0	606.4	600.4
37.5°	738.5	697.6	664.2	639.1	619.5	604.2	590.7	582.9	574.1	568.2	563.1
40°	703.3	665.9	635.6	609.2	594.8	577.8	565.2	555.2	548.6	541.0	535.4
42.5°	671.6	636.7	607.4	583.6	565.8	551.4	539.2	529.3	520.9	515.4	510.8
45°	626.8	592.1	563.5	541.4	525.0	511.2	498.6	493.6	482.6	476.0	473.8
47.5°	580.4	549.4	521.8	501.5	484.6	471.6	459.7	449.6	443.5	437.0	433.5
50°	549.2	519.4	493.6	473.8	457.3	443.0	431.9	425.3	417.1	411.1	406.7
52.5°	518.0	490.4	464.6	445.6	431.3	417.0	404.7	398.1	390.3	386.4	383.4
55°	473.3	444.1	422.1	403.3	388.5	375.3	363.7	357.1	352.2	348.3	347.2
57.5°	422.7	399.5	379.0	362.2	346.7	334.4	324.2	318.0	313.6	313.0	309.7
60°	389.6	368.7	350.0	331.8	318.6	307.0	298.2	291.1	286.7	286.2	285.0
62.5°	356.6	336.6	319.2	303.2	291.3	280.2	271.8	263.8	261.1	258.4	256.0
65°	307.6	289.4	275.2	262.4	249.8	240.4	232.2	227.3	221.2	217.9	211.9
67.5°	259.5	245.4	231.7	221.0	211.1	202.2	195.3	188.0	183.9	181.2	176.8
70°	227.8	216.8	203.1	191.5	183.8	176.7	171.1	162.9	160.1	157.9	155.7
72.5°	197.9	188.2	176.7	167.3	159.6	152.9	146.5	142.6	139.9	137.7	136.4
75°	155.7	146.3	136.5	129.9	124.3	118.9	115.5	112.8	111.7	111.1	108.9
77.5°	114.4	109.4	101.5	96.2	92.5	90.3	87.4	85.9	85.9	83.4	82.7
80°	87.5	84.7	78.1	75.9	73.2	71.0	69.3	66.6	63.8	62.7	61.1
82.5°	65.1	62.3	59.7	56.1	53.8	52.5	50.9	49.8	50.2	48.7	47.9
85°	34.7	31.9	30.8	30.2	29.2	30.2	29.7	29.2	28.6	28.0	28.6
87.5°	12.6	12.9	12.6	13.9	12.8	13.6	13.8	13.5	13.7	13.9	13.9
90°	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0	18.0	18.9	20.9
92.5°	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9	121.8	91.7	77.7
95°	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1	537.1	420.6	341.0
97.5°	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4	913.5	800.0	689.3
100°	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2	1118.8	1021.2	922.7
102.5°	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0	1244.6	1197.8	1131.1
105°	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1	1315.9	1357.6	1347.1
107.5°	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2	1252.4	1359.4	1408.9
110°	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4	1180.4	1313.9	1394.5



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2	1109.1	1244.2	1339.1
115°	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2	1007.1	1136.8	1240.1
117.5°	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8	936.4	1048.1	1142.9
120°	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5	896.2	1000.4	1083.8
122.5°	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1	867.4	960.3	1038.3
125°	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3	828.9	911.3	979.6
127.5°	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0	792.1	869.1	932.9
130°	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1	766.4	840.3	901.9
132.5°	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1	742.2	809.2	868.5
135°	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4	704.8	765.5	819.5
137.5°	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6	671.5	721.9	767.8
140°	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2	651.8	695.4	735.2
142.5°	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4	635.1	672.6	707.1
145°	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5	613.8	643.3	668.8
147.5°	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4	596.2	618.8	638.1
150°	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6	586.4	604.4	621.4
152.5°	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0	576.6	593.0	606.3
155°	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6	561.7	575.0	585.5
157.5°	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2	547.7	558.0	566.1
160°	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7	537.1	546.6	553.3
162.5°	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3	528.1	536.0	541.8
165°	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8	514.4	520.1	524.8
167.5°	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8	501.2	505.5	508.9
170°	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7	493.6	496.4	498.3
172.5°	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9	486.7	488.9	490.0
175°	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5	476.5	478.4	478.4
177.5°	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4	472.1	472.1	472.1
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1284.1	1279.3	1278.0	1279.7	1278.0	1279.3	1284.1	1284.6	1285.0	1288.5	1283.7
5°	1184.8	1179.2	1182.0	1180.9	1182.0	1179.2	1184.8	1190.3	1191.3	1196.3	1199.6
7.5°	1097.4	1090.5	1083.3	1085.6	1083.3	1090.5	1097.4	1097.5	1106.0	1112.5	1116.7
10°	1036.2	1030.7	1027.4	1030.1	1027.4	1030.7	1036.2	1043.3	1046.6	1054.3	1062.6
12.5°	984.6	981.4	978.5	977.3	978.5	981.4	984.6	992.3	1000.0	1009.0	1018.1
15°	914.6	908.0	905.2	898.1	905.2	908.0	914.6	921.2	936.0	939.9	953.7
17.5°	849.9	847.7	840.6	837.6	840.6	847.7	849.9	855.6	862.4	876.6	887.0
20°	811.6	809.4	802.3	806.7	802.3	809.4	811.6	819.9	825.4	837.0	846.9
22.5°	780.0	775.1	772.8	771.5	772.8	775.1	780.0	783.8	791.1	801.8	813.0
25°	735.2	728.0	725.3	721.9	725.3	728.0	735.2	737.4	745.1	755.5	761.6
27.5°	690.5	686.6	683.0	682.2	683.0	686.6	690.5	693.6	700.3	709.4	720.3
30°	661.5	657.6	654.8	654.8	654.8	657.6	661.5	668.1	673.0	681.3	689.5
32.5°	635.4	632.5	629.7	629.3	629.7	632.5	635.4	639.0	644.8	654.0	662.7
35°	597.6	593.2	592.1	588.8	592.1	593.2	597.6	600.4	606.4	613.0	620.2
37.5°	558.3	554.6	554.6	554.2	554.6	554.6	558.3	563.1	568.2	574.1	582.9
40°	533.2	530.4	529.9	526.0	529.9	530.4	533.2	535.4	541.0	548.6	555.2
42.5°	506.4	504.9	503.0	501.4	503.0	504.9	506.4	510.8	515.4	520.9	529.3
45°	469.9	466.1	466.1	463.3	466.1	466.1	469.9	473.8	476.0	482.6	493.6
47.5°	432.3	429.3	429.7	426.8	429.7	429.3	432.3	433.5	437.0	443.5	449.6
50°	407.2	405.5	405.0	403.9	405.0	405.5	407.2	406.7	411.1	417.1	425.3
52.5°	382.1	381.3	383.4	381.0	383.4	381.3	382.1	383.4	386.4	390.3	398.1
55°	348.3	346.7	350.0	346.7	350.0	346.7	348.3	347.2	348.3	352.2	357.1
57.5°	309.5	307.9	310.9	309.2	310.9	307.9	309.5	309.7	313.0	313.6	318.0
60°	284.0	280.6	282.3	282.8	282.3	280.6	284.0	285.0	286.2	286.7	291.1
62.5°	253.6	251.6	252.8	250.3	252.8	251.6	253.6	256.0	258.4	261.1	263.8
65°	210.8	209.1	206.9	205.8	206.9	209.1	210.8	211.9	217.9	221.2	227.3
67.5°	177.1	173.1	173.0	173.9	173.0	173.1	177.1	176.8	181.2	183.9	188.0
70°	152.5	152.5	151.9	151.9	151.9	152.5	152.5	155.7	157.9	160.1	162.9
72.5°	135.3	134.9	133.8	133.4	133.8	134.9	135.3	136.4	137.7	139.9	142.6
75°	108.9	109.5	108.4	107.9	108.4	109.5	108.9	108.9	111.1	111.7	112.8
77.5°	80.5	78.1	79.3	78.1	79.3	78.1	80.5	82.7	83.4	85.9	85.9
80°	61.1	60.5	62.2	60.5	62.2	60.5	61.1	61.1	62.7	63.8	66.6
82.5°	48.3	47.8	48.5	47.3	48.5	47.8	48.3	47.9	48.7	50.2	49.8
85°	29.2	28.6	28.0	28.6	28.0	28.6	29.2	28.6	28.0	28.6	29.2
87.5°	14.3	13.9	14.0	14.0	14.0	13.9	14.3	13.9	13.9	13.7	13.5
90°	20.9	20.9	21.8	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0
92.5°	65.6	63.3	62.0	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9
95°	273.8	245.3	237.8	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1
97.5°	630.7	577.7	550.2	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4
100°	857.4	789.1	754.1	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2
102.5°	1061.2	1012.7	974.6	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0
105°	1316.8	1285.6	1266.6	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1
107.5°	1424.2	1424.1	1417.8	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2
110°	1437.1	1455.1	1461.8	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1401.5	1432.4	1448.9	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2
115°	1313.9	1359.4	1385.9	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2
117.5°	1216.8	1263.8	1290.1	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8
120°	1153.9	1199.3	1224.9	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5
122.5°	1100.8	1142.5	1168.1	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1
125°	1032.6	1071.5	1092.3	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3
127.5°	981.0	1015.4	1035.1	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0
130°	949.3	980.5	999.5	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1
132.5°	915.9	947.1	964.6	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1
135°	861.1	892.4	909.5	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4
137.5°	805.0	833.5	849.2	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6
140°	770.2	794.8	809.0	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2
142.5°	736.9	757.7	771.1	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4
145°	691.5	707.7	718.1	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5
147.5°	656.2	669.0	675.1	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4
150°	635.7	647.0	650.9	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6
152.5°	618.2	627.3	631.1	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0
155°	594.9	601.5	604.4	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6
157.5°	573.5	579.0	581.6	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2
160°	559.9	564.6	566.6	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7
162.5°	547.0	551.0	551.4	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3
165°	528.6	530.5	530.5	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8
167.5°	510.8	512.5	511.8	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8
170°	500.2	501.2	501.2	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7
172.5°	490.3	492.0	490.6	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9
175°	478.4	479.4	477.4	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5
177.5°	471.4	472.1	469.9	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1285.0	1289.9	1292.5	1298.7	1307.5	1311.9	1318.0	1322.4	1328.6	1336.1	1342.2
5°	1201.8	1215.0	1223.8	1237.5	1250.3	1262.9	1278.9	1290.4	1305.8	1323.4	1337.2
7.5°	1124.5	1141.1	1155.7	1173.9	1194.7	1211.0	1231.8	1253.1	1277.2	1302.2	1325.8
10°	1075.2	1091.8	1109.9	1132.5	1153.4	1175.4	1200.1	1224.9	1255.2	1283.3	1315.2
12.5°	1026.4	1044.6	1065.0	1090.2	1115.5	1143.7	1168.9	1196.8	1229.2	1265.7	1299.8
15°	965.7	983.3	1005.3	1026.8	1056.0	1086.8	1120.4	1157.2	1193.5	1234.3	1276.7
17.5°	900.7	920.1	944.3	969.1	999.9	1035.9	1068.9	1109.2	1150.1	1197.5	1247.4
20°	858.4	878.2	906.9	934.4	962.5	997.7	1036.7	1078.0	1121.4	1171.6	1227.1
22.5°	825.0	839.1	867.2	895.2	928.1	964.2	1002.4	1045.5	1092.8	1144.7	1202.9
25°	775.3	791.8	812.2	841.4	875.5	913.5	951.9	997.7	1049.4	1102.2	1164.4
27.5°	731.2	744.8	764.9	787.7	821.8	861.2	902.1	949.7	1002.8	1056.6	1122.0
30°	699.9	714.8	734.1	758.3	785.2	828.2	870.0	916.8	970.7	1026.3	1093.4
32.5°	672.6	687.9	704.6	727.5	756.6	794.8	837.9	883.8	938.6	995.9	1061.3
35°	634.5	644.9	660.3	682.9	711.5	742.3	786.4	834.8	888.2	947.6	1013.1
37.5°	590.7	604.2	619.5	639.1	664.2	697.6	738.5	787.4	837.0	893.9	953.7
40°	565.2	577.8	594.8	609.2	635.6	665.9	703.3	754.4	804.0	857.4	911.8
42.5°	539.2	551.4	565.8	583.6	607.4	636.7	671.6	719.2	772.3	822.6	868.2
45°	498.6	511.2	525.0	541.4	563.5	592.1	626.8	670.3	716.5	762.7	797.4
47.5°	459.7	471.6	484.6	501.5	521.8	549.4	580.4	618.8	663.7	703.0	727.8
50°	431.9	443.0	457.3	473.8	493.6	519.4	549.2	587.2	624.6	660.3	682.9
52.5°	404.7	417.0	431.3	445.6	464.6	490.4	518.0	550.6	586.3	615.5	634.1
55°	363.7	375.3	388.5	403.3	422.1	444.1	473.3	499.1	527.2	552.0	563.0
57.5°	324.2	334.4	346.7	362.2	379.0	399.5	422.7	447.5	467.3	484.8	497.3
60°	298.2	307.0	318.6	331.8	350.0	368.7	389.6	412.7	428.1	443.0	454.5
62.5°	271.8	280.2	291.3	303.2	319.2	336.6	356.6	375.3	390.3	400.3	413.6
65°	232.2	240.4	249.8	262.4	275.2	289.4	307.6	321.4	331.8	342.8	351.1
67.5°	195.3	202.2	211.1	221.0	231.7	245.4	259.5	270.9	278.1	284.7	294.6
70°	171.1	176.7	183.8	191.5	203.1	216.8	227.8	236.6	241.6	248.2	260.2
72.5°	146.5	152.9	159.6	167.3	176.7	188.2	197.9	206.7	209.9	215.2	222.9
75°	115.5	118.9	124.3	129.9	136.5	146.3	155.7	157.9	160.7	165.1	170.6
77.5°	87.4	90.3	92.5	96.2	101.5	109.4	114.4	117.6	118.3	119.9	125.4
80°	69.3	71.0	73.2	75.9	78.1	84.7	87.5	90.8	91.9	93.5	96.3
82.5°	50.9	52.5	53.8	56.1	59.7	62.3	65.1	68.3	68.6	69.8	70.4
85°	29.7	30.2	29.2	30.2	30.8	31.9	34.7	37.4	36.9	36.3	38.0
87.5°	13.8	13.6	12.8	13.9	12.6	12.9	12.6	12.6	13.0	13.6	14.3
90°	16.1	15.2	13.3	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0
92.5°	247.3	305.4	310.4	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6
95°	821.3	839.4	684.9	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2
97.5°	1039.3	896.3	611.6	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9
100°	1092.3	855.4	545.7	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3
102.5°	1060.5	783.4	495.6	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3
105°	958.7	686.8	447.1	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0
107.5°	854.9	620.3	426.6	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3
110°	795.7	589.2	420.6	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	751.8	571.0	420.6	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2
115°	703.8	551.4	423.5	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4
117.5°	675.2	541.7	429.7	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1
120°	659.3	537.1	435.8	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3
122.5°	645.7	533.4	441.1	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2
125°	627.1	528.6	450.0	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2
127.5°	610.1	526.4	460.0	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0
130°	598.8	524.8	466.1	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8
132.5°	589.6	524.8	472.9	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4
135°	578.9	524.8	482.2	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7
137.5°	569.2	525.9	490.7	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3
140°	564.6	526.7	494.5	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3
142.5°	560.8	527.5	496.8	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9
145°	555.1	526.7	499.3	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9
147.5°	549.3	524.2	500.2	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5
150°	544.7	522.0	500.2	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4
152.5°	539.4	518.9	499.5	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0
155°	530.5	513.5	497.3	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0
157.5°	522.2	507.8	494.9	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6
160°	515.4	504.0	492.6	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9
162.5°	509.3	499.5	490.3	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7
165°	500.2	492.6	486.9	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9
167.5°	491.3	486.0	481.6	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8
170°	486.0	482.2	479.4	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3
172.5°	480.7	477.7	476.3	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4
175°	473.7	472.7	472.7	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0
177.5°	470.7	469.9	469.9	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1347.1	1351.0	1356.7	1363.3	1368.6	1374.4	1377.4	1377.4	1380.1	1385.8	1393.3
5°	1351.0	1365.2	1379.0	1396.6	1410.4	1426.3	1438.4	1450.0	1460.4	1473.7	1487.4
7.5°	1349.8	1373.6	1398.4	1426.1	1456.7	1481.0	1506.0	1525.6	1545.0	1570.3	1590.2
10°	1345.4	1376.2	1409.8	1445.0	1483.5	1517.1	1547.4	1574.9	1601.3	1628.8	1653.6
12.5°	1337.5	1376.7	1417.7	1460.0	1508.6	1547.0	1586.2	1615.4	1646.3	1676.3	1706.8
15°	1325.6	1371.8	1421.4	1480.3	1539.7	1582.6	1621.1	1659.1	1687.7	1721.8	1751.0
17.5°	1301.1	1360.7	1422.9	1487.3	1544.4	1594.2	1634.7	1670.8	1701.3	1738.8	1778.4
20°	1286.5	1351.0	1415.8	1484.7	1539.1	1590.3	1629.4	1666.8	1704.8	1753.7	1802.1
22.5°	1266.3	1335.1	1403.9	1469.3	1526.8	1576.2	1616.6	1662.4	1712.2	1767.8	1826.4
25°	1234.3	1305.3	1373.5	1435.7	1491.8	1542.5	1597.5	1659.1	1719.6	1792.8	1877.0
27.5°	1193.7	1262.1	1323.0	1388.7	1444.5	1508.9	1577.5	1644.4	1731.6	1832.3	1937.4
30°	1163.3	1228.2	1286.0	1348.2	1411.4	1482.5	1559.5	1638.2	1742.2	1860.5	1985.4
32.5°	1128.0	1186.8	1244.1	1304.2	1377.1	1455.1	1537.0	1633.4	1757.6	1892.2	2021.5
35°	1067.0	1119.8	1175.4	1241.9	1319.6	1404.4	1508.9	1626.1	1776.3	1921.0	2037.1
37.5°	1002.9	1044.6	1100.4	1170.7	1255.2	1353.2	1471.9	1614.3	1768.6	1898.4	1947.9
40°	953.7	992.7	1051.6	1125.4	1208.9	1316.3	1449.4	1595.8	1751.0	1841.3	1837.4
42.5°	904.7	944.3	1000.9	1075.1	1162.3	1282.4	1419.5	1571.6	1702.6	1736.9	1665.2
45°	829.8	866.7	922.3	997.1	1090.6	1216.7	1360.8	1506.7	1590.3	1534.7	1392.8
47.5°	753.4	789.2	840.8	914.1	1016.3	1148.1	1284.4	1404.1	1415.8	1296.5	1126.2
50°	703.3	736.8	785.8	864.0	963.0	1091.8	1223.3	1317.4	1288.2	1142.4	966.9
52.5°	654.4	686.6	732.5	806.2	907.5	1033.6	1151.0	1224.9	1157.5	1002.4	844.5
55°	582.2	613.0	659.3	726.9	818.8	934.4	1037.3	1064.2	965.2	808.9	681.3
57.5°	513.6	536.2	581.9	641.7	730.3	832.3	906.0	901.2	791.8	651.1	559.5
60°	468.3	488.6	532.1	587.2	671.3	762.7	814.4	792.4	681.8	565.7	477.6
62.5°	426.0	445.1	481.5	532.1	604.5	683.9	721.5	691.1	586.7	484.7	414.7
65°	362.1	375.9	405.0	451.8	508.4	563.5	597.0	552.4	460.1	383.0	330.2
67.5°	302.3	314.2	340.1	373.7	412.8	450.8	464.5	422.7	350.7	298.8	261.6
70°	263.6	274.6	292.2	323.6	349.4	376.4	383.0	345.6	285.6	246.0	222.9
72.5°	226.6	236.8	252.2	274.3	292.2	307.7	310.8	276.1	230.2	202.8	185.0
75°	172.8	181.6	191.5	199.7	211.3	214.1	213.0	186.0	161.3	143.1	133.1
77.5°	127.0	130.6	136.7	140.0	140.6	140.3	134.7	117.6	104.8	97.4	93.4
80°	97.9	100.7	102.3	103.5	104.0	98.5	92.5	82.0	77.6	73.2	68.2
82.5°	71.1	73.0	74.6	74.8	71.8	67.3	61.6	56.4	53.4	51.2	49.3
85°	38.5	39.1	38.5	35.8	31.9	30.2	29.2	28.0	27.5	27.0	27.0
87.5°	14.0	13.0	11.3	12.1	12.5	12.2	12.6	12.3	12.3	12.5	12.6
90°	1.9	3.8	5.7	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0
92.5°	14.0	22.0	33.8	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9
95°	32.2	39.8	50.2	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1
97.5°	53.1	58.4	68.8	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4
100°	68.2	72.0	82.4	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2
102.5°	83.4	86.4	97.6	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0
105°	107.0	111.8	121.2	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1
107.5°	133.2	137.7	145.5	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2
110°	150.7	154.4	163.0	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.0	171.0	179.6	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2
115°	193.2	196.1	204.6	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2
117.5°	217.0	220.0	228.5	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8
120°	232.1	235.9	244.4	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5
122.5°	247.3	250.3	258.8	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1
125°	267.2	271.9	280.4	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3
127.5°	283.8	289.9	300.7	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0
130°	293.7	301.3	313.6	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1
132.5°	302.0	311.1	325.0	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1
135°	314.5	325.9	341.0	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4
137.5°	329.1	339.7	354.9	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6
140°	338.2	349.6	364.8	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2
142.5°	348.1	358.7	373.8	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4
145°	363.8	373.2	386.5	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5
147.5°	379.7	387.8	400.1	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4
150°	390.3	397.0	409.3	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6
152.5°	400.1	406.0	416.9	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0
155°	413.0	418.7	428.2	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6
157.5°	425.3	429.9	438.1	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2
160°	432.9	436.8	443.4	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7
162.5°	439.8	443.5	449.4	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3
165°	449.1	451.9	456.6	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8
167.5°	456.8	458.5	461.1	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8
170°	461.4	462.3	464.2	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7
172.5°	463.7	464.6	466.4	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9
175°	467.0	468.0	469.0	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5
177.5°	469.1	469.1	469.9	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1399.1	1399.1	1406.6	1406.1	1411.0	1409.2	1410.1
5°	1503.9	1513.3	1521.5	1527.1	1535.3	1537.5	1536.4
7.5°	1612.7	1633.5	1643.6	1657.4	1659.9	1667.2	1666.5
10°	1680.0	1700.4	1715.8	1727.9	1733.9	1741.6	1742.2
12.5°	1732.8	1750.1	1763.7	1775.0	1782.3	1784.8	1786.2
15°	1774.1	1793.3	1809.3	1825.3	1834.7	1841.8	1845.7
17.5°	1815.7	1845.4	1873.6	1895.2	1908.3	1919.3	1919.1
20°	1847.9	1882.0	1917.2	1942.0	1967.2	1978.2	1979.9
22.5°	1882.2	1934.4	1979.7	2018.1	2051.3	2062.8	2067.1
25°	1953.5	2021.7	2091.7	2145.5	2184.0	2206.6	2210.0
27.5°	2039.6	2132.0	2205.5	2255.3	2287.3	2304.0	2307.6
30°	2100.5	2185.7	2251.8	2289.2	2304.0	2306.2	2298.0
32.5°	2127.7	2191.4	2217.9	2215.7	2186.5	2167.1	2159.7
35°	2094.3	2081.1	2016.8	1939.8	1880.9	1843.5	1833.5
37.5°	1905.9	1792.0	1673.6	1557.2	1495.3	1463.7	1409.6
40°	1720.2	1557.9	1434.6	1336.6	1266.7	1210.6	1197.4
42.5°	1510.7	1343.0	1219.8	1135.9	1080.1	1041.5	1024.8
45°	1213.9	1069.8	967.9	903.6	860.6	832.6	819.9
47.5°	970.9	859.3	785.1	737.5	704.8	680.4	673.5
50°	837.6	748.4	685.7	645.5	620.7	602.0	594.3
52.5°	727.5	655.5	607.3	574.1	550.7	539.1	532.6
55°	600.4	538.2	503.5	477.1	463.9	454.5	450.1
57.5°	491.0	446.1	420.8	402.5	390.3	384.3	382.1
60°	429.7	394.5	371.5	357.1	348.9	341.2	339.0
62.5°	375.6	347.9	330.0	317.5	309.2	306.0	304.6
65°	302.6	284.5	271.3	263.6	257.0	255.8	255.4
67.5°	240.6	229.9	223.0	214.9	212.6	208.8	208.0
70°	205.8	198.7	190.4	187.7	184.9	181.1	181.6
72.5°	174.6	167.4	161.8	158.2	157.2	155.5	156.9
75°	127.7	125.5	123.3	120.5	119.4	119.4	118.9
77.5°	91.2	89.3	86.8	85.2	84.9	82.5	83.4
80°	66.0	63.3	62.2	62.7	61.1	60.5	60.5
82.5°	48.8	47.9	46.8	46.9	46.6	46.0	46.5
85°	27.0	26.4	26.4	25.8	25.8	25.3	25.3
87.5°	13.3	13.9	13.5	13.0	13.0	13.6	14.0
90°	18.0	18.9	20.9	20.9	20.9	21.8	21.8
92.5°	121.8	91.7	77.7	65.6	63.3	62.0	60.4
95°	537.1	420.6	341.0	273.8	245.3	237.8	222.7
97.5°	913.5	800.0	689.3	630.7	577.7	550.2	538.1
100°	1118.8	1021.2	922.7	857.4	789.1	754.1	738.9
102.5°	1244.6	1197.8	1131.1	1061.2	1012.7	974.6	963.3
105°	1315.9	1357.6	1347.1	1316.8	1285.6	1266.6	1255.2
107.5°	1252.4	1359.4	1408.9	1424.2	1424.1	1417.8	1410.2
110°	1180.4	1313.9	1394.5	1437.1	1455.1	1461.8	1461.8



TEST NUMBER: P333606-930

CATALOG NUMBER: S125RDIP-S1090D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1109.1	1244.2	1339.1	1401.5	1432.4	1448.9	1455.7
115°	1007.1	1136.8	1240.1	1313.9	1359.4	1385.9	1398.2
117.5°	936.4	1048.1	1142.9	1216.8	1263.8	1290.1	1297.6
120°	896.2	1000.4	1083.8	1153.9	1199.3	1224.9	1232.5
122.5°	867.4	960.3	1038.3	1100.8	1142.5	1168.1	1174.9
125°	828.9	911.3	979.6	1032.6	1071.5	1092.3	1101.8
127.5°	792.1	869.1	932.9	981.0	1015.4	1035.1	1039.3
130°	766.4	840.3	901.9	949.3	980.5	999.5	1005.1
132.5°	742.2	809.2	868.5	915.9	947.1	964.6	971.0
135°	704.8	765.5	819.5	861.1	892.4	909.5	915.2
137.5°	671.5	721.9	767.8	805.0	833.5	849.2	855.4
140°	651.8	695.4	735.2	770.2	794.8	809.0	813.8
142.5°	635.1	672.6	707.1	736.9	757.7	771.1	775.1
145°	613.8	643.3	668.8	691.5	707.7	718.1	721.9
147.5°	596.2	618.8	638.1	656.2	669.0	675.1	676.8
150°	586.4	604.4	621.4	635.7	647.0	650.9	651.8
152.5°	576.6	593.0	606.3	618.2	627.3	631.1	632.1
155°	561.7	575.0	585.5	594.9	601.5	604.4	605.4
157.5°	547.7	558.0	566.1	573.5	579.0	581.6	581.5
160°	537.1	546.6	553.3	559.9	564.6	566.6	565.6
162.5°	528.1	536.0	541.8	547.0	551.0	551.4	551.1
165°	514.4	520.1	524.8	528.6	530.5	530.5	530.5
167.5°	501.2	505.5	508.9	510.8	512.5	511.8	511.6
170°	493.6	496.4	498.3	500.2	501.2	501.2	500.2
172.5°	486.7	488.9	490.0	490.3	492.0	490.6	489.6
175°	476.5	478.4	478.4	478.4	479.4	477.4	476.5
177.5°	472.1	472.1	472.1	471.4	472.1	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9

(END OF REPORT)