

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333588-930

Luminaire Tested: **S125RDIP-S1090D590U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333588-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1090D590U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5204.1 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	80	75	88	81	76	72	73	69	65	65	61	59	57	55	53	49
3	86	76	69	63	80	72	66	60	65	59	55	58	54	50	51	48	45	42
4	79	68	60	54	74	64	57	52	58	52	48	52	47	43	46	42	39	36
5	72	61	53	47	68	58	50	45	52	46	41	47	42	38	42	38	35	32
6	67	55	46	41	63	52	45	39	47	41	36	42	37	33	38	34	31	28
7	62	50	41	36	58	47	40	35	43	37	32	38	33	30	35	30	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8657	8657	8657	8657
5°	9961	8669	7656	8669
10°	11425	8625	6755	8625
15°	12341	8536	6005	8536
20°	13608	8434	5544	8434
25°	15748	8298	5144	8298
30°	17137	8154	4883	8154
35°	14456	7987	4642	7987
40°	10095	7687	4435	7687
45°	7489	7283	4232	7283
50°	5971	6861	4058	6861
55°	5068	6339	3904	6339
60°	4379	5871	3653	5871
65°	3903	5365	3145	5365
70°	3429	4913	2868	4913
75°	2967	4257	2692	4257
80°	2250	3582	2250	3582
85°	1875	2816	2119	2816



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	2.5
10°-20°	376.7	7.2
20°-30°	597.3	11.5
30°-40°	720.3	13.8
40°-50°	643.2	12.4
50°-60°	493.3	9.5
60°-70°	320.6	6.2
70°-80°	155.9	3.0
80°-90°	38.5	0.7
90°-100°	167.2	3.2
100°-110°	359.4	6.9
110°-120°	337.3	6.5
120°-130°	273.4	5.3
130°-140°	219.4	4.2
140°-150°	165.6	3.2
150°-160°	116.5	2.2
160°-170°	68.7	1.3
170°-180°	22.3	0.4
0°-30°	1102.6	21.2
0°-40°	1822.8	35.0
0°-60°	2959.4	56.9
0°-90°	3474.3	66.8
90°-120°	864.0	16.6
90°-150°	1522.3	29.3
90°-180°	1730.0	33.2
0°-180°	5204.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1340	1340	1340	1340	1340	
5°	1536	1337	1181	1337	1536	154
15°	1846	1277	898	1277	1846	529
25°	2210	1164	722	1164	2210	1015
35°	1834	1013	589	1013	1834	1108
45°	820	797	463	797	820	654
55°	450	563	347	563	450	408
65°	255	351	206	351	255	254
75°	119	171	108	171	119	127
85°	25	38	29	38	25	29
90°	11	0	11	0	11	9
95°	109	15	109	15	109	155
105°	616	53	616	53	616	613
115°	686	94	686	94	686	671
125°	541	130	541	130	541	489
135°	449	152	449	152	449	348
145°	354	178	354	178	354	225
155°	297	203	297	203	297	139
165°	260	221	260	221	260	74
175°	234	230	234	230	234	23
180°	231	231	231	231	231	



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1410.1	1409.2	1411.0	1406.1	1406.6	1399.1	1399.1	1393.3	1385.8	1380.1	1377.4
5°	1536.4	1537.5	1535.3	1527.1	1521.5	1513.3	1503.9	1487.4	1473.7	1460.4	1450.0
7.5°	1666.5	1667.2	1659.9	1657.4	1643.6	1633.5	1612.7	1590.2	1570.3	1545.0	1525.6
10°	1742.2	1741.6	1733.9	1727.9	1715.8	1700.4	1680.0	1653.6	1628.8	1601.3	1574.9
12.5°	1786.2	1784.8	1782.3	1775.0	1763.7	1750.1	1732.8	1706.8	1676.3	1646.3	1615.4
15°	1845.7	1841.8	1834.7	1825.3	1809.3	1793.3	1774.1	1751.0	1721.8	1687.7	1659.1
17.5°	1919.1	1919.3	1908.3	1895.2	1873.6	1845.4	1815.7	1778.4	1738.8	1701.3	1670.8
20°	1979.9	1978.2	1967.2	1942.0	1917.2	1882.0	1847.9	1802.1	1753.7	1704.8	1666.8
22.5°	2067.1	2062.8	2051.3	2018.1	1979.7	1934.4	1882.2	1826.4	1767.8	1712.2	1662.4
25°	2210.0	2206.6	2184.0	2145.5	2091.7	2021.7	1953.5	1877.0	1792.8	1719.6	1659.1
27.5°	2307.6	2304.0	2287.3	2255.3	2205.5	2132.0	2039.6	1937.4	1832.3	1731.6	1644.4
30°	2298.0	2306.2	2304.0	2289.2	2251.8	2185.7	2100.5	1985.4	1860.5	1742.2	1638.2
32.5°	2159.7	2167.1	2186.5	2215.7	2217.9	2191.4	2127.7	2021.5	1892.2	1757.6	1633.4
35°	1833.5	1843.5	1880.9	1939.8	2016.8	2081.1	2094.3	2037.1	1921.0	1776.3	1626.1
37.5°	1409.6	1463.7	1495.3	1557.2	1673.6	1792.0	1905.9	1947.9	1898.4	1768.6	1614.3
40°	1197.4	1210.6	1266.7	1336.6	1434.6	1557.9	1720.2	1837.4	1841.3	1751.0	1595.8
42.5°	1024.8	1041.5	1080.1	1135.9	1219.8	1343.0	1510.7	1665.2	1736.9	1702.6	1571.6
45°	819.9	832.6	860.6	903.6	967.9	1069.8	1213.9	1392.8	1534.7	1590.3	1506.7
47.5°	673.5	680.4	704.8	737.5	785.1	859.3	970.9	1126.2	1296.5	1415.8	1404.1
50°	594.3	602.0	620.7	645.5	685.7	748.4	837.6	966.9	1142.4	1288.2	1317.4
52.5°	532.6	539.1	550.7	574.1	607.3	655.5	727.5	844.5	1002.4	1157.5	1224.9
55°	450.1	454.5	463.9	477.1	503.5	538.2	600.4	681.3	808.9	965.2	1064.2
57.5°	382.1	384.3	390.3	402.5	420.8	446.1	491.0	559.5	651.1	791.8	901.2
60°	339.0	341.2	348.9	357.1	371.5	394.5	429.7	477.6	565.7	681.8	792.4
62.5°	304.6	306.0	309.2	317.5	330.0	347.9	375.6	414.7	484.7	586.7	691.1
65°	255.4	255.8	257.0	263.6	271.3	284.5	302.6	330.2	383.0	460.1	552.4
67.5°	208.0	208.8	212.6	214.9	223.0	229.9	240.6	261.6	298.8	350.7	422.7
70°	181.6	181.1	184.9	187.7	190.4	198.7	205.8	222.9	246.0	285.6	345.6
72.5°	156.9	155.5	157.2	158.2	161.8	167.4	174.6	185.0	202.8	230.2	276.1
75°	118.9	119.4	119.4	120.5	123.3	125.5	127.7	133.1	143.1	161.3	186.0
77.5°	83.4	82.5	84.9	85.2	86.8	89.3	91.2	93.4	97.4	104.8	117.6
80°	60.5	60.5	61.1	62.7	62.2	63.3	66.0	68.2	73.2	77.6	82.0
82.5°	46.5	46.0	46.6	46.9	46.8	47.9	48.8	49.3	51.2	53.4	56.4
85°	25.3	25.3	25.8	25.8	26.4	26.4	27.0	27.0	27.0	27.5	28.0
87.5°	11.8	11.4	10.8	10.8	11.3	12.0	11.4	10.9	10.8	10.8	11.0
90°	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4	7.9	7.4	6.5
92.5°	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4	121.4	149.9	152.4
95°	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4	403.2	412.1	336.2
97.5°	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0	510.2	440.0	300.3
100°	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0	536.2	420.0	267.9
102.5°	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0	520.6	384.6	243.3
105°	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3	470.7	337.2	219.5
107.5°	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8	419.7	304.5	209.5
110°	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1	390.7	289.3	206.5



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6	369.1	280.4	206.5
115°	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2	345.5	270.7	207.9
117.5°	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5	331.5	266.0	210.9
120°	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2	323.7	263.7	213.9
122.5°	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1	317.0	261.9	216.5
125°	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5	307.9	259.5	220.9
127.5°	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6	299.5	258.4	225.8
130°	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3	293.9	257.6	228.9
132.5°	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0	289.4	257.6	232.2
135°	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9	284.1	257.6	236.7
137.5°	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7	279.4	258.2	240.9
140°	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1	277.2	258.6	242.8
142.5°	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3	275.3	258.9	243.9
145°	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0	272.6	258.6	245.1
147.5°	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0	269.6	257.4	245.6
150°	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6	267.4	256.2	245.6
152.5°	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9	264.8	254.8	245.2
155°	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3	260.4	252.1	244.2
157.5°	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8	256.3	249.2	243.0
160°	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0	253.0	247.4	241.8
162.5°	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9	250.1	245.2	240.8
165°	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2	245.6	241.8	239.0
167.5°	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9	241.2	238.6	236.4
170°	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9	238.6	236.7	235.3
172.5°	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6	235.9	234.5	233.8
175°	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9	232.5	232.0	232.0
177.5°	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4	231.1	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1377.4	1374.4	1368.6	1363.3	1356.7	1351.0	1347.1	1342.2	1336.1	1328.6	1322.4
5°	1438.4	1426.3	1410.4	1396.6	1379.0	1365.2	1351.0	1337.2	1323.4	1305.8	1290.4
7.5°	1506.0	1481.0	1456.7	1426.1	1398.4	1373.6	1349.8	1325.8	1302.2	1277.2	1253.1
10°	1547.4	1517.1	1483.5	1445.0	1409.8	1376.2	1345.4	1315.2	1283.3	1255.2	1224.9
12.5°	1586.2	1547.0	1508.6	1460.0	1417.7	1376.7	1337.5	1299.8	1265.7	1229.2	1196.8
15°	1621.1	1582.6	1539.7	1480.3	1421.4	1371.8	1325.6	1276.7	1234.3	1193.5	1157.2
17.5°	1634.7	1594.2	1544.4	1487.3	1422.9	1360.7	1301.1	1247.4	1197.5	1150.1	1109.2
20°	1629.4	1590.3	1539.1	1484.7	1415.8	1351.0	1286.5	1227.1	1171.6	1121.4	1078.0
22.5°	1616.6	1576.2	1526.8	1469.3	1403.9	1335.1	1266.3	1202.9	1144.7	1092.8	1045.5
25°	1597.5	1542.5	1491.8	1435.7	1373.5	1305.3	1234.3	1164.4	1102.2	1049.4	997.7
27.5°	1577.5	1508.9	1444.5	1388.7	1323.0	1262.1	1193.7	1122.0	1056.6	1002.8	949.7
30°	1559.5	1482.5	1411.4	1348.2	1286.0	1228.2	1163.3	1093.4	1026.3	970.7	916.8
32.5°	1537.0	1455.1	1377.1	1304.2	1244.1	1186.8	1128.0	1061.3	995.9	938.6	883.8
35°	1508.9	1404.4	1319.6	1241.9	1175.4	1119.8	1067.0	1013.1	947.6	888.2	834.8
37.5°	1471.9	1353.2	1255.2	1170.7	1100.4	1044.6	1002.9	953.7	893.9	837.0	787.4
40°	1449.4	1316.3	1208.9	1125.4	1051.6	992.7	953.7	911.8	857.4	804.0	754.4
42.5°	1419.5	1282.4	1162.3	1075.1	1000.9	944.3	904.7	868.2	822.6	772.3	719.2
45°	1360.8	1216.7	1090.6	997.1	922.3	866.7	829.8	797.4	762.7	716.5	670.3
47.5°	1284.4	1148.1	1016.3	914.1	840.8	789.2	753.4	727.8	703.0	663.7	618.8
50°	1223.3	1091.8	963.0	864.0	785.8	736.8	703.3	682.9	660.3	624.6	587.2
52.5°	1151.0	1033.6	907.5	806.2	732.5	686.6	654.4	634.1	615.5	586.3	550.6
55°	1037.3	934.4	818.8	726.9	659.3	613.0	582.2	563.0	552.0	527.2	499.1
57.5°	906.0	832.3	730.3	641.7	581.9	536.2	513.6	497.3	484.8	467.3	447.5
60°	814.4	762.7	671.3	587.2	532.1	488.6	468.3	454.5	443.0	428.1	412.7
62.5°	721.5	683.9	604.5	532.1	481.5	445.1	426.0	413.6	400.3	390.3	375.3
65°	597.0	563.5	508.4	451.8	405.0	375.9	362.1	351.1	342.8	331.8	321.4
67.5°	464.5	450.8	412.8	373.7	340.1	314.2	302.3	294.6	284.7	278.1	270.9
70°	383.0	376.4	349.4	323.6	292.2	274.6	263.6	260.2	248.2	241.6	236.6
72.5°	310.8	307.7	292.2	274.3	252.2	236.8	226.6	222.9	215.2	209.9	206.7
75°	213.0	214.1	211.3	199.7	191.5	181.6	172.8	170.6	165.1	160.7	157.9
77.5°	134.7	140.3	140.6	140.0	136.7	130.6	127.0	125.4	119.9	118.3	117.6
80°	92.5	98.5	104.0	103.5	102.3	100.7	97.9	96.3	93.5	91.9	90.8
82.5°	61.6	67.3	71.8	74.8	74.6	73.0	71.1	70.4	69.8	68.6	68.3
85°	29.2	30.2	31.9	35.8	38.5	39.1	38.5	38.0	36.3	36.9	37.4
87.5°	11.3	11.2	11.5	11.3	10.7	12.7	13.9	14.2	13.4	12.7	12.0
90°	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5	0.9	1.9	2.8
92.5°	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7	6.8	10.8	16.6
95°	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3	15.8	19.6	24.6
97.5°	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5	26.0	28.6	33.8
100°	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5	33.5	35.4	40.4
102.5°	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4	40.9	42.4	47.9
105°	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6	52.6	54.9	59.5
107.5°	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5	65.4	67.6	71.4
110°	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1	73.9	75.8	80.0



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6	82.5	84.0	88.2
115°	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9	94.9	96.3	100.4
117.5°	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1	106.5	108.0	112.2
120°	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5	114.0	115.8	120.0
122.5°	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3	121.4	122.9	127.0
125°	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2	131.2	133.5	137.6
127.5°	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9	139.3	142.4	147.7
130°	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8	144.1	147.9	153.9
132.5°	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5	148.3	152.7	159.6
135°	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5	154.4	160.0	167.5
137.5°	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2	161.6	166.8	174.2
140°	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6	166.0	171.6	179.0
142.5°	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8	170.9	176.1	183.5
145°	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7	178.6	183.2	189.7
147.5°	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8	186.4	190.4	196.4
150°	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7	191.6	194.9	200.9
152.5°	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9	196.4	199.3	204.6
155°	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8	202.8	205.5	210.2
157.5°	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9	208.8	211.1	215.1
160°	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0	212.5	214.4	217.7
162.5°	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4	215.9	217.8	220.6
165°	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4	220.5	221.8	224.1
167.5°	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7	224.3	225.1	226.4
170°	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0	226.5	227.0	227.9
172.5°	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4	227.6	228.0	229.0
175°	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2	229.3	229.8	230.2
177.5°	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1	230.3	230.3	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1318.0	1311.9	1307.5	1298.7	1292.5	1289.9	1285.0	1283.7	1288.5	1285.0	1284.6
5°	1278.9	1262.9	1250.3	1237.5	1223.8	1215.0	1201.8	1199.6	1196.3	1191.3	1190.3
7.5°	1231.8	1211.0	1194.7	1173.9	1155.7	1141.1	1124.5	1116.7	1112.5	1106.0	1097.5
10°	1200.1	1175.4	1153.4	1132.5	1109.9	1091.8	1075.2	1062.6	1054.3	1046.6	1043.3
12.5°	1168.9	1143.7	1115.5	1090.2	1065.0	1044.6	1026.4	1018.1	1009.0	1000.0	992.3
15°	1120.4	1086.8	1056.0	1026.8	1005.3	983.3	965.7	953.7	939.9	936.0	921.2
17.5°	1068.9	1035.9	999.9	969.1	944.3	920.1	900.7	887.0	876.6	862.4	855.6
20°	1036.7	997.7	962.5	934.4	906.9	878.2	858.4	846.9	837.0	825.4	819.9
22.5°	1002.4	964.2	928.1	895.2	867.2	839.1	825.0	813.0	801.8	791.1	783.8
25°	951.9	913.5	875.5	841.4	812.2	791.8	775.3	761.6	755.5	745.1	737.4
27.5°	902.1	861.2	821.8	787.7	764.9	744.8	731.2	720.3	709.4	700.3	693.6
30°	870.0	828.2	785.2	758.3	734.1	714.8	699.9	689.5	681.3	673.0	668.1
32.5°	837.9	794.8	756.6	727.5	704.6	687.9	672.6	662.7	654.0	644.8	639.0
35°	786.4	742.3	711.5	682.9	660.3	644.9	634.5	620.2	613.0	606.4	600.4
37.5°	738.5	697.6	664.2	639.1	619.5	604.2	590.7	582.9	574.1	568.2	563.1
40°	703.3	665.9	635.6	609.2	594.8	577.8	565.2	555.2	548.6	541.0	535.4
42.5°	671.6	636.7	607.4	583.6	565.8	551.4	539.2	529.3	520.9	515.4	510.8
45°	626.8	592.1	563.5	541.4	525.0	511.2	498.6	493.6	482.6	476.0	473.8
47.5°	580.4	549.4	521.8	501.5	484.6	471.6	459.7	449.6	443.5	437.0	433.5
50°	549.2	519.4	493.6	473.8	457.3	443.0	431.9	425.3	417.1	411.1	406.7
52.5°	518.0	490.4	464.6	445.6	431.3	417.0	404.7	398.1	390.3	386.4	383.4
55°	473.3	444.1	422.1	403.3	388.5	375.3	363.7	357.1	352.2	348.3	347.2
57.5°	422.7	399.5	379.0	362.2	346.7	334.4	324.2	318.0	313.6	313.0	309.7
60°	389.6	368.7	350.0	331.8	318.6	307.0	298.2	291.1	286.7	286.2	285.0
62.5°	356.6	336.6	319.2	303.2	291.3	280.2	271.8	263.8	261.1	258.4	256.0
65°	307.6	289.4	275.2	262.4	249.8	240.4	232.2	227.3	221.2	217.9	211.9
67.5°	259.5	245.4	231.7	221.0	211.1	202.2	195.3	188.0	183.9	181.2	176.8
70°	227.8	216.8	203.1	191.5	183.8	176.7	171.1	162.9	160.1	157.9	155.7
72.5°	197.9	188.2	176.7	167.3	159.6	152.9	146.5	142.6	139.9	137.7	136.4
75°	155.7	146.3	136.5	129.9	124.3	118.9	115.5	112.8	111.7	111.1	108.9
77.5°	114.4	109.4	101.5	96.2	92.5	90.3	87.4	85.9	85.9	83.4	82.7
80°	87.5	84.7	78.1	75.9	73.2	71.0	69.3	66.6	63.8	62.7	61.1
82.5°	65.1	62.3	59.7	56.1	53.8	52.5	50.9	49.8	50.2	48.7	47.9
85°	34.7	31.9	30.8	30.2	29.2	30.2	29.7	29.2	28.6	28.0	28.6
87.5°	11.7	11.9	11.6	12.6	11.4	12.1	12.1	11.8	11.9	12.0	11.7
90°	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4	8.8	9.3	10.2
92.5°	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4	59.8	45.0	38.2
95°	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4	263.7	206.5	167.5
97.5°	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0	448.4	392.7	338.3
100°	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0	549.3	501.3	453.0
102.5°	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0	611.0	588.0	555.3
105°	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3	646.0	666.4	661.3
107.5°	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8	614.8	667.4	691.6
110°	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1	579.5	645.1	684.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6	544.5	610.8	657.5
115°	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2	494.4	558.1	608.8
117.5°	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5	459.7	514.5	561.1
120°	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2	439.9	491.1	532.1
122.5°	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1	425.8	471.4	509.7
125°	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5	406.9	447.4	480.9
127.5°	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6	388.9	426.6	458.0
130°	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3	376.3	412.5	442.7
132.5°	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0	364.4	397.3	426.4
135°	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9	346.0	375.8	402.3
137.5°	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7	329.6	354.4	376.9
140°	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1	320.0	341.4	360.9
142.5°	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3	311.8	330.2	347.2
145°	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0	301.3	315.8	328.3
147.5°	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0	292.7	303.8	313.2
150°	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6	287.9	296.7	305.1
152.5°	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9	283.1	291.1	297.7
155°	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3	275.8	282.3	287.4
157.5°	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8	268.9	273.9	277.9
160°	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0	263.7	268.3	271.6
162.5°	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9	259.3	263.1	266.0
165°	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2	252.5	255.4	257.6
167.5°	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9	246.1	248.2	249.8
170°	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9	242.3	243.7	244.6
172.5°	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6	239.0	239.9	240.5
175°	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9	233.9	234.9	234.9
177.5°	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4	231.8	231.8	231.8
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1284.1	1279.3	1278.0	1279.7	1278.0	1279.3	1284.1	1284.6	1285.0	1288.5	1283.7
5°	1184.8	1179.2	1182.0	1180.9	1182.0	1179.2	1184.8	1190.3	1191.3	1196.3	1199.6
7.5°	1097.4	1090.5	1083.3	1085.6	1083.3	1090.5	1097.4	1097.5	1106.0	1112.5	1116.7
10°	1036.2	1030.7	1027.4	1030.1	1027.4	1030.7	1036.2	1043.3	1046.6	1054.3	1062.6
12.5°	984.6	981.4	978.5	977.3	978.5	981.4	984.6	992.3	1000.0	1009.0	1018.1
15°	914.6	908.0	905.2	898.1	905.2	908.0	914.6	921.2	936.0	939.9	953.7
17.5°	849.9	847.7	840.6	837.6	840.6	847.7	849.9	855.6	862.4	876.6	887.0
20°	811.6	809.4	802.3	806.7	802.3	809.4	811.6	819.9	825.4	837.0	846.9
22.5°	780.0	775.1	772.8	771.5	772.8	775.1	780.0	783.8	791.1	801.8	813.0
25°	735.2	728.0	725.3	721.9	725.3	728.0	735.2	737.4	745.1	755.5	761.6
27.5°	690.5	686.6	683.0	682.2	683.0	686.6	690.5	693.6	700.3	709.4	720.3
30°	661.5	657.6	654.8	654.8	654.8	657.6	661.5	668.1	673.0	681.3	689.5
32.5°	635.4	632.5	629.7	629.3	629.7	632.5	635.4	639.0	644.8	654.0	662.7
35°	597.6	593.2	592.1	588.8	592.1	593.2	597.6	600.4	606.4	613.0	620.2
37.5°	558.3	554.6	554.6	554.2	554.6	554.6	558.3	563.1	568.2	574.1	582.9
40°	533.2	530.4	529.9	526.0	529.9	530.4	533.2	535.4	541.0	548.6	555.2
42.5°	506.4	504.9	503.0	501.4	503.0	504.9	506.4	510.8	515.4	520.9	529.3
45°	469.9	466.1	466.1	463.3	466.1	466.1	469.9	473.8	476.0	482.6	493.6
47.5°	432.3	429.3	429.7	426.8	429.7	429.3	432.3	433.5	437.0	443.5	449.6
50°	407.2	405.5	405.0	403.9	405.0	405.5	407.2	406.7	411.1	417.1	425.3
52.5°	382.1	381.3	383.4	381.0	383.4	381.3	382.1	383.4	386.4	390.3	398.1
55°	348.3	346.7	350.0	346.7	350.0	346.7	348.3	347.2	348.3	352.2	357.1
57.5°	309.5	307.9	310.9	309.2	310.9	307.9	309.5	309.7	313.0	313.6	318.0
60°	284.0	280.6	282.3	282.8	282.3	280.6	284.0	285.0	286.2	286.7	291.1
62.5°	253.6	251.6	252.8	250.3	252.8	251.6	253.6	256.0	258.4	261.1	263.8
65°	210.8	209.1	206.9	205.8	206.9	209.1	210.8	211.9	217.9	221.2	227.3
67.5°	177.1	173.1	173.0	173.9	173.0	173.1	177.1	176.8	181.2	183.9	188.0
70°	152.5	152.5	151.9	151.9	151.9	152.5	152.5	155.7	157.9	160.1	162.9
72.5°	135.3	134.9	133.8	133.4	133.8	134.9	135.3	136.4	137.7	139.9	142.6
75°	108.9	109.5	108.4	107.9	108.4	109.5	108.9	108.9	111.1	111.7	112.8
77.5°	80.5	78.1	79.3	78.1	79.3	78.1	80.5	82.7	83.4	85.9	85.9
80°	61.1	60.5	62.2	60.5	62.2	60.5	61.1	61.1	62.7	63.8	66.6
82.5°	48.3	47.8	48.5	47.3	48.5	47.8	48.3	47.9	48.7	50.2	49.8
85°	29.2	28.6	28.0	28.6	28.0	28.6	29.2	28.6	28.0	28.6	29.2
87.5°	12.1	11.7	11.8	11.8	11.8	11.7	12.1	11.7	12.0	11.9	11.8
90°	10.2	10.2	10.7	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4
92.5°	32.2	31.1	30.4	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4
95°	134.4	120.4	116.8	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4
97.5°	309.7	283.6	270.1	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0
100°	420.9	387.4	370.2	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0
102.5°	521.0	497.2	478.5	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0
105°	646.5	631.1	621.8	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3
107.5°	699.2	699.1	696.0	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8
110°	705.5	714.4	717.6	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	688.0	703.2	711.3	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6
115°	645.1	667.4	680.4	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2
117.5°	597.4	620.4	633.3	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5
120°	566.5	588.8	601.4	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2
122.5°	540.4	560.8	573.4	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1
125°	507.0	526.0	536.2	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5
127.5°	481.6	498.5	508.1	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6
130°	466.0	481.4	490.6	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3
132.5°	449.6	465.0	473.5	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0
135°	422.7	438.1	446.5	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9
137.5°	395.2	409.2	416.9	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7
140°	378.1	390.2	397.1	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1
142.5°	361.7	371.9	378.5	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3
145°	339.5	347.4	352.5	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0
147.5°	322.1	328.4	331.4	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0
150°	312.1	317.6	319.5	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6
152.5°	303.5	307.9	309.8	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9
155°	292.0	295.3	296.7	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3
157.5°	281.5	284.2	285.5	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8
160°	274.8	277.2	278.1	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0
162.5°	268.6	270.5	270.7	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9
165°	259.5	260.4	260.4	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2
167.5°	250.8	251.6	251.2	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9
170°	245.6	246.1	246.1	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9
172.5°	240.8	241.6	240.8	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6
175°	234.9	235.3	234.4	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9
177.5°	231.4	231.8	230.6	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1285.0	1289.9	1292.5	1298.7	1307.5	1311.9	1318.0	1322.4	1328.6	1336.1	1342.2
5°	1201.8	1215.0	1223.8	1237.5	1250.3	1262.9	1278.9	1290.4	1305.8	1323.4	1337.2
7.5°	1124.5	1141.1	1155.7	1173.9	1194.7	1211.0	1231.8	1253.1	1277.2	1302.2	1325.8
10°	1075.2	1091.8	1109.9	1132.5	1153.4	1175.4	1200.1	1224.9	1255.2	1283.3	1315.2
12.5°	1026.4	1044.6	1065.0	1090.2	1115.5	1143.7	1168.9	1196.8	1229.2	1265.7	1299.8
15°	965.7	983.3	1005.3	1026.8	1056.0	1086.8	1120.4	1157.2	1193.5	1234.3	1276.7
17.5°	900.7	920.1	944.3	969.1	999.9	1035.9	1068.9	1109.2	1150.1	1197.5	1247.4
20°	858.4	878.2	906.9	934.4	962.5	997.7	1036.7	1078.0	1121.4	1171.6	1227.1
22.5°	825.0	839.1	867.2	895.2	928.1	964.2	1002.4	1045.5	1092.8	1144.7	1202.9
25°	775.3	791.8	812.2	841.4	875.5	913.5	951.9	997.7	1049.4	1102.2	1164.4
27.5°	731.2	744.8	764.9	787.7	821.8	861.2	902.1	949.7	1002.8	1056.6	1122.0
30°	699.9	714.8	734.1	758.3	785.2	828.2	870.0	916.8	970.7	1026.3	1093.4
32.5°	672.6	687.9	704.6	727.5	756.6	794.8	837.9	883.8	938.6	995.9	1061.3
35°	634.5	644.9	660.3	682.9	711.5	742.3	786.4	834.8	888.2	947.6	1013.1
37.5°	590.7	604.2	619.5	639.1	664.2	697.6	738.5	787.4	837.0	893.9	953.7
40°	565.2	577.8	594.8	609.2	635.6	665.9	703.3	754.4	804.0	857.4	911.8
42.5°	539.2	551.4	565.8	583.6	607.4	636.7	671.6	719.2	772.3	822.6	868.2
45°	498.6	511.2	525.0	541.4	563.5	592.1	626.8	670.3	716.5	762.7	797.4
47.5°	459.7	471.6	484.6	501.5	521.8	549.4	580.4	618.8	663.7	703.0	727.8
50°	431.9	443.0	457.3	473.8	493.6	519.4	549.2	587.2	624.6	660.3	682.9
52.5°	404.7	417.0	431.3	445.6	464.6	490.4	518.0	550.6	586.3	615.5	634.1
55°	363.7	375.3	388.5	403.3	422.1	444.1	473.3	499.1	527.2	552.0	563.0
57.5°	324.2	334.4	346.7	362.2	379.0	399.5	422.7	447.5	467.3	484.8	497.3
60°	298.2	307.0	318.6	331.8	350.0	368.7	389.6	412.7	428.1	443.0	454.5
62.5°	271.8	280.2	291.3	303.2	319.2	336.6	356.6	375.3	390.3	400.3	413.6
65°	232.2	240.4	249.8	262.4	275.2	289.4	307.6	321.4	331.8	342.8	351.1
67.5°	195.3	202.2	211.1	221.0	231.7	245.4	259.5	270.9	278.1	284.7	294.6
70°	171.1	176.7	183.8	191.5	203.1	216.8	227.8	236.6	241.6	248.2	260.2
72.5°	146.5	152.9	159.6	167.3	176.7	188.2	197.9	206.7	209.9	215.2	222.9
75°	115.5	118.9	124.3	129.9	136.5	146.3	155.7	157.9	160.7	165.1	170.6
77.5°	87.4	90.3	92.5	96.2	101.5	109.4	114.4	117.6	118.3	119.9	125.4
80°	69.3	71.0	73.2	75.9	78.1	84.7	87.5	90.8	91.9	93.5	96.3
82.5°	50.9	52.5	53.8	56.1	59.7	62.3	65.1	68.3	68.6	69.8	70.4
85°	29.7	30.2	29.2	30.2	30.8	31.9	34.7	37.4	36.9	36.3	38.0
87.5°	12.1	12.1	11.4	12.6	11.6	11.9	11.7	12.0	12.7	13.4	14.2
90°	7.9	7.4	6.5	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5
92.5°	121.4	149.9	152.4	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7
95°	403.2	412.1	336.2	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3
97.5°	510.2	440.0	300.3	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5
100°	536.2	420.0	267.9	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5
102.5°	520.6	384.6	243.3	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4
105°	470.7	337.2	219.5	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6
107.5°	419.7	304.5	209.5	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5
110°	390.7	289.3	206.5	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	369.1	280.4	206.5	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6
115°	345.5	270.7	207.9	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9
117.5°	331.5	266.0	210.9	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1
120°	323.7	263.7	213.9	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5
122.5°	317.0	261.9	216.5	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3
125°	307.9	259.5	220.9	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2
127.5°	299.5	258.4	225.8	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9
130°	293.9	257.6	228.9	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8
132.5°	289.4	257.6	232.2	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5
135°	284.1	257.6	236.7	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5
137.5°	279.4	258.2	240.9	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2
140°	277.2	258.6	242.8	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6
142.5°	275.3	258.9	243.9	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8
145°	272.6	258.6	245.1	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7
147.5°	269.6	257.4	245.6	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8
150°	267.4	256.2	245.6	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7
152.5°	264.8	254.8	245.2	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9
155°	260.4	252.1	244.2	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8
157.5°	256.3	249.2	243.0	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9
160°	253.0	247.4	241.8	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0
162.5°	250.1	245.2	240.8	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4
165°	245.6	241.8	239.0	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4
167.5°	241.2	238.6	236.4	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7
170°	238.6	236.7	235.3	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0
172.5°	235.9	234.5	233.8	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4
175°	232.5	232.0	232.0	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2
177.5°	231.1	230.6	230.6	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1347.1	1351.0	1356.7	1363.3	1368.6	1374.4	1377.4	1377.4	1380.1	1385.8	1393.3
5°	1351.0	1365.2	1379.0	1396.6	1410.4	1426.3	1438.4	1450.0	1460.4	1473.7	1487.4
7.5°	1349.8	1373.6	1398.4	1426.1	1456.7	1481.0	1506.0	1525.6	1545.0	1570.3	1590.2
10°	1345.4	1376.2	1409.8	1445.0	1483.5	1517.1	1547.4	1574.9	1601.3	1628.8	1653.6
12.5°	1337.5	1376.7	1417.7	1460.0	1508.6	1547.0	1586.2	1615.4	1646.3	1676.3	1706.8
15°	1325.6	1371.8	1421.4	1480.3	1539.7	1582.6	1621.1	1659.1	1687.7	1721.8	1751.0
17.5°	1301.1	1360.7	1422.9	1487.3	1544.4	1594.2	1634.7	1670.8	1701.3	1738.8	1778.4
20°	1286.5	1351.0	1415.8	1484.7	1539.1	1590.3	1629.4	1666.8	1704.8	1753.7	1802.1
22.5°	1266.3	1335.1	1403.9	1469.3	1526.8	1576.2	1616.6	1662.4	1712.2	1767.8	1826.4
25°	1234.3	1305.3	1373.5	1435.7	1491.8	1542.5	1597.5	1659.1	1719.6	1792.8	1877.0
27.5°	1193.7	1262.1	1323.0	1388.7	1444.5	1508.9	1577.5	1644.4	1731.6	1832.3	1937.4
30°	1163.3	1228.2	1286.0	1348.2	1411.4	1482.5	1559.5	1638.2	1742.2	1860.5	1985.4
32.5°	1128.0	1186.8	1244.1	1304.2	1377.1	1455.1	1537.0	1633.4	1757.6	1892.2	2021.5
35°	1067.0	1119.8	1175.4	1241.9	1319.6	1404.4	1508.9	1626.1	1776.3	1921.0	2037.1
37.5°	1002.9	1044.6	1100.4	1170.7	1255.2	1353.2	1471.9	1614.3	1768.6	1898.4	1947.9
40°	953.7	992.7	1051.6	1125.4	1208.9	1316.3	1449.4	1595.8	1751.0	1841.3	1837.4
42.5°	904.7	944.3	1000.9	1075.1	1162.3	1282.4	1419.5	1571.6	1702.6	1736.9	1665.2
45°	829.8	866.7	922.3	997.1	1090.6	1216.7	1360.8	1506.7	1590.3	1534.7	1392.8
47.5°	753.4	789.2	840.8	914.1	1016.3	1148.1	1284.4	1404.1	1415.8	1296.5	1126.2
50°	703.3	736.8	785.8	864.0	963.0	1091.8	1223.3	1317.4	1288.2	1142.4	966.9
52.5°	654.4	686.6	732.5	806.2	907.5	1033.6	1151.0	1224.9	1157.5	1002.4	844.5
55°	582.2	613.0	659.3	726.9	818.8	934.4	1037.3	1064.2	965.2	808.9	681.3
57.5°	513.6	536.2	581.9	641.7	730.3	832.3	906.0	901.2	791.8	651.1	559.5
60°	468.3	488.6	532.1	587.2	671.3	762.7	814.4	792.4	681.8	565.7	477.6
62.5°	426.0	445.1	481.5	532.1	604.5	683.9	721.5	691.1	586.7	484.7	414.7
65°	362.1	375.9	405.0	451.8	508.4	563.5	597.0	552.4	460.1	383.0	330.2
67.5°	302.3	314.2	340.1	373.7	412.8	450.8	464.5	422.7	350.7	298.8	261.6
70°	263.6	274.6	292.2	323.6	349.4	376.4	383.0	345.6	285.6	246.0	222.9
72.5°	226.6	236.8	252.2	274.3	292.2	307.7	310.8	276.1	230.2	202.8	185.0
75°	172.8	181.6	191.5	199.7	211.3	214.1	213.0	186.0	161.3	143.1	133.1
77.5°	127.0	130.6	136.7	140.0	140.6	140.3	134.7	117.6	104.8	97.4	93.4
80°	97.9	100.7	102.3	103.5	104.0	98.5	92.5	82.0	77.6	73.2	68.2
82.5°	71.1	73.0	74.6	74.8	71.8	67.3	61.6	56.4	53.4	51.2	49.3
85°	38.5	39.1	38.5	35.8	31.9	30.2	29.2	28.0	27.5	27.0	27.0
87.5°	13.9	12.7	10.7	11.3	11.5	11.2	11.3	11.0	10.8	10.8	10.9
90°	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4
92.5°	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4
95°	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4
97.5°	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0
100°	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0
102.5°	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0
105°	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3
107.5°	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8
110°	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6
115°	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2
117.5°	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5
120°	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2
122.5°	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1
125°	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5
127.5°	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6
130°	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3
132.5°	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0
135°	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9
137.5°	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7
140°	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1
142.5°	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3
145°	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0
147.5°	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0
150°	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6
152.5°	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9
155°	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3
157.5°	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8
160°	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0
162.5°	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9
165°	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2
167.5°	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9
170°	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9
172.5°	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6
175°	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9
177.5°	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1399.1	1399.1	1406.6	1406.1	1411.0	1409.2	1410.1
5°	1503.9	1513.3	1521.5	1527.1	1535.3	1537.5	1536.4
7.5°	1612.7	1633.5	1643.6	1657.4	1659.9	1667.2	1666.5
10°	1680.0	1700.4	1715.8	1727.9	1733.9	1741.6	1742.2
12.5°	1732.8	1750.1	1763.7	1775.0	1782.3	1784.8	1786.2
15°	1774.1	1793.3	1809.3	1825.3	1834.7	1841.8	1845.7
17.5°	1815.7	1845.4	1873.6	1895.2	1908.3	1919.3	1919.1
20°	1847.9	1882.0	1917.2	1942.0	1967.2	1978.2	1979.9
22.5°	1882.2	1934.4	1979.7	2018.1	2051.3	2062.8	2067.1
25°	1953.5	2021.7	2091.7	2145.5	2184.0	2206.6	2210.0
27.5°	2039.6	2132.0	2205.5	2255.3	2287.3	2304.0	2307.6
30°	2100.5	2185.7	2251.8	2289.2	2304.0	2306.2	2298.0
32.5°	2127.7	2191.4	2217.9	2215.7	2186.5	2167.1	2159.7
35°	2094.3	2081.1	2016.8	1939.8	1880.9	1843.5	1833.5
37.5°	1905.9	1792.0	1673.6	1557.2	1495.3	1463.7	1409.6
40°	1720.2	1557.9	1434.6	1336.6	1266.7	1210.6	1197.4
42.5°	1510.7	1343.0	1219.8	1135.9	1080.1	1041.5	1024.8
45°	1213.9	1069.8	967.9	903.6	860.6	832.6	819.9
47.5°	970.9	859.3	785.1	737.5	704.8	680.4	673.5
50°	837.6	748.4	685.7	645.5	620.7	602.0	594.3
52.5°	727.5	655.5	607.3	574.1	550.7	539.1	532.6
55°	600.4	538.2	503.5	477.1	463.9	454.5	450.1
57.5°	491.0	446.1	420.8	402.5	390.3	384.3	382.1
60°	429.7	394.5	371.5	357.1	348.9	341.2	339.0
62.5°	375.6	347.9	330.0	317.5	309.2	306.0	304.6
65°	302.6	284.5	271.3	263.6	257.0	255.8	255.4
67.5°	240.6	229.9	223.0	214.9	212.6	208.8	208.0
70°	205.8	198.7	190.4	187.7	184.9	181.1	181.6
72.5°	174.6	167.4	161.8	158.2	157.2	155.5	156.9
75°	127.7	125.5	123.3	120.5	119.4	119.4	118.9
77.5°	91.2	89.3	86.8	85.2	84.9	82.5	83.4
80°	66.0	63.3	62.2	62.7	61.1	60.5	60.5
82.5°	48.8	47.9	46.8	46.9	46.6	46.0	46.5
85°	27.0	26.4	26.4	25.8	25.8	25.3	25.3
87.5°	11.4	12.0	11.3	10.8	10.8	11.4	11.8
90°	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333588-930

CATALOG NUMBER: S125RDIP-S1090D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)