

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333630-930

Luminaire Tested: **S125RDIP-S1270D1035U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333630-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7040.6 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	96	92	89	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	73	85	79	73	69	68	64	61	59	56	53	50	48	46	42
3	84	74	67	61	78	70	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	58	52	71	62	55	50	54	49	44	47	43	39	40	37	34	31
5	70	59	51	45	65	55	48	43	49	43	39	42	38	34	36	33	30	27
6	65	53	45	39	60	50	43	37	44	38	34	38	34	30	33	29	27	24
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	34	29	36	31	27	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	2.1
10°-20°	435.1	6.2
20°-30°	689.8	9.8
30°-40°	831.9	11.8
40°-50°	742.9	10.6
50°-60°	569.7	8.1
60°-70°	370.2	5.3
70°-80°	180.0	2.6
80°-90°	45.2	0.6
90°-100°	292.6	4.2
100°-110°	629.0	8.9
110°-120°	590.3	8.4
120°-130°	478.4	6.8
130°-140°	383.9	5.5
140°-150°	289.7	4.1
150°-160°	203.9	2.9
160°-170°	120.2	1.7
170°-180°	39.1	0.6
0°-30°	1273.4	18.1
0°-40°	2105.3	29.9
0°-60°	3417.9	48.5
0°-90°	4013.3	57.0
90°-120°	1512.0	21.5
90°-150°	2664.1	37.8
90°-180°	3027.0	43.0
0°-180°	7040.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	19	1	19	1	19	14
95°	191	27	191	27	191	271
105°	1078	92	1078	92	1078	1072
115°	1201	164	1201	164	1201	1174
125°	947	228	947	228	947	856
135°	786	267	786	267	786	609
145°	620	311	620	311	620	394
155°	520	355	520	355	520	242
165°	456	387	456	387	456	130
175°	409	403	409	403	409	40
180°	404	404	404	404	404	



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	14.9	14.4	13.8	13.8	14.3	14.9	14.3	13.6	13.5	13.3	13.5
90°	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7	13.9	13.0	11.4
92.5°	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2	212.4	262.4	266.6
95°	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2	705.6	721.1	588.5
97.5°	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6	892.8	770.1	525.5
100°	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1	938.4	734.9	468.8
102.5°	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7	911.1	673.1	425.8
105°	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0	823.7	590.0	384.2
107.5°	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2	734.4	533.0	366.6
110°	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5	683.6	506.2	361.3



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1	645.9	490.6	361.3
115°	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0	604.7	473.7	363.8
117.5°	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7	580.2	465.4	369.2
120°	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3	566.5	461.5	374.4
122.5°	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7	554.7	458.2	379.0
125°	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2	538.8	454.1	386.6
127.5°	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1	524.2	452.2	395.3
130°	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9	514.4	450.9	400.5
132.5°	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5	506.5	450.9	406.3
135°	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3	497.3	450.9	414.3
137.5°	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5	489.0	451.8	421.6
140°	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7	485.1	452.5	424.9
142.5°	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2	481.8	453.1	426.8
145°	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1	477.0	452.5	428.9
147.5°	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8	471.9	450.4	429.7
150°	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9	468.0	448.4	429.7
152.5°	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4	463.4	445.9	429.1
155°	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6	455.8	441.2	427.3
157.5°	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8	448.6	436.3	425.2
160°	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3	442.8	433.0	423.2
162.5°	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2	437.6	429.1	421.3
165°	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3	429.7	423.2	418.3
167.5°	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8	422.1	417.5	413.8
170°	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6	417.5	414.3	411.8
172.5°	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7	412.9	410.3	409.2
175°	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4	406.9	406.1	406.1
177.5°	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0	404.3	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	13.8	13.5	13.9	13.5	12.6	14.9	16.1	16.5	15.6	14.9	14.2
90°	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8	1.6	3.3	4.9
92.5°	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9	12.1	18.9	28.9
95°	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8	27.6	34.2	43.1
97.5°	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6	45.6	50.1	59.1
100°	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0	58.6	61.9	70.8
102.5°	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7	71.6	74.2	83.8
105°	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0	92.0	96.0	104.2
107.5°	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8	114.5	118.3	125.0
110°	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8	129.4	132.6	140.0



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8	144.4	147.0	154.3
115°	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4	166.0	168.4	175.8
117.5°	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9	186.4	189.0	196.3
120°	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0	199.4	202.7	210.0
122.5°	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7	212.4	215.0	222.3
125°	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9	229.5	233.6	240.9
127.5°	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4	243.9	249.1	258.4
130°	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9	252.3	258.9	269.4
132.5°	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4	259.4	267.3	279.2
135°	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9	270.2	280.0	293.0
137.5°	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3	282.7	291.9	304.9
140°	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1	290.6	300.4	313.3
142.5°	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3	299.1	308.1	321.1
145°	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9	312.5	320.7	332.1
147.5°	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2	326.2	333.2	343.8
150°	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7	335.3	341.0	351.6
152.5°	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8	343.8	348.9	358.1
155°	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8	354.8	359.7	367.9
157.5°	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6	365.4	369.3	376.3
160°	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8	371.9	375.2	380.9
162.5°	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6	377.8	381.1	386.1
165°	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4	385.8	388.2	392.3
167.5°	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3	392.5	394.0	396.2
170°	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2	396.4	397.2	398.8
172.5°	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8	398.4	399.2	400.7
175°	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8	401.2	402.0	402.8
177.5°	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3	403.0	403.0	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	14.0	14.3	14.0	15.3	13.9	14.8	15.0	14.6	14.8	14.9	14.8
90°	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7	15.5	16.3	17.9
92.5°	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2	104.7	78.8	66.8
95°	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2	461.5	361.3	293.0
97.5°	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6	784.7	687.2	592.2
100°	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1	961.2	877.3	792.7
102.5°	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7	1069.3	1029.1	971.8
105°	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0	1130.5	1166.3	1157.3
107.5°	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2	1076.0	1167.9	1210.4
110°	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5	1014.1	1128.9	1198.1



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1	952.9	1068.9	1150.6
115°	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0	865.2	976.6	1065.4
117.5°	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7	804.5	900.5	981.9
120°	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3	770.0	859.5	931.1
122.5°	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7	745.2	824.9	892.0
125°	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2	712.2	782.9	841.6
127.5°	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1	680.6	746.7	801.5
130°	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9	658.4	721.9	774.9
132.5°	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5	637.6	695.2	746.2
135°	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3	605.5	657.6	704.0
137.5°	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5	576.9	620.2	659.6
140°	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7	559.9	597.4	631.6
142.5°	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2	545.6	577.9	607.5
145°	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1	527.4	552.6	574.6
147.5°	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8	512.3	531.7	548.2
150°	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9	503.8	519.3	533.9
152.5°	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4	495.3	509.5	520.9
155°	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6	482.7	494.1	503.0
157.5°	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8	470.6	479.4	486.4
160°	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3	461.5	469.6	475.3
162.5°	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2	453.6	460.5	465.5
165°	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3	442.0	446.9	450.9
167.5°	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8	430.6	434.3	437.2
170°	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6	424.0	426.5	428.1
172.5°	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7	418.2	420.0	420.9
175°	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4	409.4	411.0	411.0
177.5°	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0	405.6	405.6	405.6
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	15.2	14.8	14.9	14.9	14.9	14.8	15.2	14.8	14.9	14.8	14.6
90°	17.9	17.9	18.8	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7
92.5°	56.3	54.4	53.2	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2
95°	235.2	210.8	204.3	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2
97.5°	541.9	496.3	472.7	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6
100°	736.5	678.0	647.8	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1
102.5°	911.7	870.1	837.3	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7
105°	1131.3	1104.5	1088.2	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0
107.5°	1223.6	1223.4	1218.1	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2
110°	1234.7	1250.1	1255.8	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1204.0	1230.6	1244.8	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1
115°	1128.9	1167.9	1190.7	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0
117.5°	1045.4	1085.7	1108.3	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7
120°	991.3	1030.4	1052.4	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3
122.5°	945.7	981.5	1003.6	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7
125°	887.1	920.5	938.4	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2
127.5°	842.9	872.3	889.2	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1
130°	815.5	842.4	858.7	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9
132.5°	786.8	813.8	828.7	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5
135°	739.8	766.7	781.3	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3
137.5°	691.6	716.1	729.6	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5
140°	661.7	682.9	695.0	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7
142.5°	633.1	650.9	662.5	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2
145°	594.1	608.0	616.9	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1
147.5°	563.7	574.8	580.0	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8
150°	546.1	555.9	559.1	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9
152.5°	531.2	539.0	542.2	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4
155°	511.1	516.8	519.3	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6
157.5°	492.8	497.4	499.7	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8
160°	481.0	485.1	486.7	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3
162.5°	469.9	473.4	473.7	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2
165°	454.1	455.8	455.8	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3
167.5°	438.9	440.3	439.7	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8
170°	429.7	430.6	430.6	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6
172.5°	421.3	422.7	421.4	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7
175°	411.0	411.8	410.2	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4
177.5°	405.0	405.6	403.7	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	15.0	14.8	13.9	15.3	14.0	14.3	14.0	14.2	14.9	15.6	16.5
90°	13.9	13.0	11.4	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8
92.5°	212.4	262.4	266.6	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9
95°	705.6	721.1	588.5	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8
97.5°	892.8	770.1	525.5	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6
100°	938.4	734.9	468.8	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0
102.5°	911.1	673.1	425.8	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7
105°	823.7	590.0	384.2	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0
107.5°	734.4	533.0	366.6	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8
110°	683.6	506.2	361.3	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.9	490.6	361.3	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8
115°	604.7	473.7	363.8	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4
117.5°	580.2	465.4	369.2	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9
120°	566.5	461.5	374.4	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0
122.5°	554.7	458.2	379.0	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7
125°	538.8	454.1	386.6	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9
127.5°	524.2	452.2	395.3	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4
130°	514.4	450.9	400.5	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9
132.5°	506.5	450.9	406.3	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4
135°	497.3	450.9	414.3	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9
137.5°	489.0	451.8	421.6	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3
140°	485.1	452.5	424.9	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1
142.5°	481.8	453.1	426.8	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3
145°	477.0	452.5	428.9	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9
147.5°	471.9	450.4	429.7	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2
150°	468.0	448.4	429.7	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7
152.5°	463.4	445.9	429.1	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8
155°	455.8	441.2	427.3	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8
157.5°	448.6	436.3	425.2	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6
160°	442.8	433.0	423.2	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8
162.5°	437.6	429.1	421.3	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6
165°	429.7	423.2	418.3	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4
167.5°	422.1	417.5	413.8	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3
170°	417.5	414.3	411.8	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2
172.5°	412.9	410.3	409.2	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8
175°	406.9	406.1	406.1	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8
177.5°	404.3	403.7	403.7	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.1	14.9	12.6	13.5	13.9	13.5	13.8	13.5	13.3	13.5	13.6
90°	1.6	3.3	4.9	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7
92.5°	12.1	18.9	28.9	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2
95°	27.6	34.2	43.1	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2
97.5°	45.6	50.1	59.1	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6
100°	58.6	61.9	70.8	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1
102.5°	71.6	74.2	83.8	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7
105°	92.0	96.0	104.2	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0
107.5°	114.5	118.3	125.0	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2
110°	129.4	132.6	140.0	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	147.0	154.3	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1
115°	166.0	168.4	175.8	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0
117.5°	186.4	189.0	196.3	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7
120°	199.4	202.7	210.0	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3
122.5°	212.4	215.0	222.3	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7
125°	229.5	233.6	240.9	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2
127.5°	243.9	249.1	258.4	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1
130°	252.3	258.9	269.4	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9
132.5°	259.4	267.3	279.2	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5
135°	270.2	280.0	293.0	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3
137.5°	282.7	291.9	304.9	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5
140°	290.6	300.4	313.3	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7
142.5°	299.1	308.1	321.1	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2
145°	312.5	320.7	332.1	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1
147.5°	326.2	333.2	343.8	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8
150°	335.3	341.0	351.6	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9
152.5°	343.8	348.9	358.1	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4
155°	354.8	359.7	367.9	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6
157.5°	365.4	369.3	376.3	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8
160°	371.9	375.2	380.9	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3
162.5°	377.8	381.1	386.1	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2
165°	385.8	388.2	392.3	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3
167.5°	392.5	394.0	396.2	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8
170°	396.4	397.2	398.8	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6
172.5°	398.4	399.2	400.7	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7
175°	401.2	402.0	402.8	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4
177.5°	403.0	403.0	403.7	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	14.3	14.9	14.3	13.8	13.8	14.4	14.9
90°	15.5	16.3	17.9	17.9	17.9	18.8	18.8
92.5°	104.7	78.8	66.8	56.3	54.4	53.2	51.9
95°	461.5	361.3	293.0	235.2	210.8	204.3	191.3
97.5°	784.7	687.2	592.2	541.9	496.3	472.7	462.3
100°	961.2	877.3	792.7	736.5	678.0	647.8	634.9
102.5°	1069.3	1029.1	971.8	911.7	870.1	837.3	827.5
105°	1130.5	1166.3	1157.3	1131.3	1104.5	1088.2	1078.4
107.5°	1076.0	1167.9	1210.4	1223.6	1223.4	1218.1	1211.5
110°	1014.1	1128.9	1198.1	1234.7	1250.1	1255.8	1255.8



TEST NUMBER: P333630-930

CATALOG NUMBER: S125RDIP-S1270D1035U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	952.9	1068.9	1150.6	1204.0	1230.6	1244.8	1250.6
115°	865.2	976.6	1065.4	1128.9	1167.9	1190.7	1201.3
117.5°	804.5	900.5	981.9	1045.4	1085.7	1108.3	1114.8
120°	770.0	859.5	931.1	991.3	1030.4	1052.4	1058.9
122.5°	745.2	824.9	892.0	945.7	981.5	1003.6	1009.4
125°	712.2	782.9	841.6	887.1	920.5	938.4	946.6
127.5°	680.6	746.7	801.5	842.9	872.3	889.2	892.8
130°	658.4	721.9	774.9	815.5	842.4	858.7	863.6
132.5°	637.6	695.2	746.2	786.8	813.8	828.7	834.2
135°	605.5	657.6	704.0	739.8	766.7	781.3	786.2
137.5°	576.9	620.2	659.6	691.6	716.1	729.6	734.9
140°	559.9	597.4	631.6	661.7	682.9	695.0	699.1
142.5°	545.6	577.9	607.5	633.1	650.9	662.5	665.9
145°	527.4	552.6	574.6	594.1	608.0	616.9	620.2
147.5°	512.3	531.7	548.2	563.7	574.8	580.0	581.5
150°	503.8	519.3	533.9	546.1	555.9	559.1	559.9
152.5°	495.3	509.5	520.9	531.2	539.0	542.2	543.0
155°	482.7	494.1	503.0	511.1	516.8	519.3	520.1
157.5°	470.6	479.4	486.4	492.8	497.4	499.7	499.5
160°	461.5	469.6	475.3	481.0	485.1	486.7	485.9
162.5°	453.6	460.5	465.5	469.9	473.4	473.7	473.5
165°	442.0	446.9	450.9	454.1	455.8	455.8	455.8
167.5°	430.6	434.3	437.2	438.9	440.3	439.7	439.5
170°	424.0	426.5	428.1	429.7	430.6	430.6	429.7
172.5°	418.2	420.0	420.9	421.3	422.7	421.4	420.6
175°	409.4	411.0	411.0	411.0	411.8	410.2	409.4
177.5°	405.6	405.6	405.6	405.0	405.6	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7

(END OF REPORT)