

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333635-930

Luminaire Tested: **S125RDIP-S1270D1205U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333635-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1205 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7410.9 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60	54
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	40
3	83	74	67	61	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	30
5	70	58	51	45	65	55	48	42	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	32	39	33	29	34	29	26	29	25	23	20
8	55	43	36	30	51	41	34	29	36	30	26	31	26	23	27	23	20	18
9	52	40	32	27	48	37	30	26	33	27	23	28	24	21	24	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	2.0
10°-20°	435.1	5.9
20°-30°	689.8	9.3
30°-40°	831.9	11.2
40°-50°	742.9	10.0
50°-60°	569.7	7.7
60°-70°	370.2	5.0
70°-80°	180.0	2.4
80°-90°	45.6	0.6
90°-100°	81.5	1.1
100°-110°	240.8	3.2
110°-120°	407.8	5.5
120°-130°	536.7	7.2
130°-140°	601.4	8.1
140°-150°	589.4	8.0
150°-160°	495.1	6.7
160°-170°	329.1	4.4
170°-180°	115.2	1.6
0°-30°	1273.4	17.2
0°-40°	2105.3	28.4
0°-60°	3417.9	46.1
0°-90°	4013.7	54.2
90°-120°	730.2	9.9
90°-150°	2457.8	33.2
90°-180°	3397.0	45.8
0°-180°	7410.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	23	1	23	1	23	14
95°	81	62	81	62	81	83
105°	235	216	235	216	235	249
115°	412	408	412	408	412	408
125°	600	596	600	596	600	535
135°	778	775	778	775	778	600
145°	943	939	943	939	943	588
155°	1074	1074	1074	1074	1074	494
165°	1165	1168	1165	1168	1165	328
175°	1210	1215	1210	1215	1210	115
180°	1217	1217	1217	1217	1217	



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	15.7	15.1	14.4	14.3	14.8	15.6	14.8	14.1	13.9	13.7	13.9
90°	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3	16.2	15.2	13.7
92.5°	44.7	44.3	43.8	43.3	42.9	41.9	40.5	39.1	37.7	36.4	34.6
95°	81.4	81.0	80.6	80.2	79.8	78.8	77.4	75.9	74.4	73.0	70.8
97.5°	123.5	123.3	123.0	122.8	122.5	121.7	120.3	119.0	117.6	116.2	113.2
100°	155.4	155.0	154.5	154.1	153.7	152.5	150.7	148.7	146.8	145.0	142.2
102.5°	187.2	186.6	186.1	185.5	184.8	183.5	181.5	179.4	177.3	175.3	173.9
105°	235.0	234.3	233.7	233.1	232.4	231.5	230.2	228.9	227.7	226.4	225.2
107.5°	283.8	283.9	284.0	284.0	284.1	283.7	283.1	282.4	281.8	281.2	280.2
110°	320.2	320.4	320.7	320.8	321.1	320.8	320.2	319.6	318.9	318.3	317.7



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	355.9	356.2	356.6	357.0	357.3	357.4	357.1	356.9	356.5	356.2	355.4
115°	412.1	412.3	412.5	412.8	412.9	413.2	413.4	413.6	413.8	414.0	413.6
117.5°	467.1	467.9	468.8	469.6	470.4	470.8	470.6	470.4	470.3	470.1	469.7
120°	505.0	505.8	506.6	507.5	508.3	508.7	508.7	508.7	508.7	508.7	508.6
122.5°	542.9	543.6	544.2	544.9	545.6	546.0	546.2	546.3	546.5	546.7	546.1
125°	599.7	599.9	600.1	600.4	600.5	600.9	601.3	601.7	602.1	602.6	602.3
127.5°	654.3	654.7	655.1	655.6	656.0	656.3	656.5	656.7	656.9	657.1	656.9
130°	690.6	691.0	691.5	691.9	692.4	692.7	692.8	693.1	693.3	693.5	693.1
132.5°	724.8	725.4	725.9	726.5	727.2	727.5	727.7	728.0	728.1	728.4	728.5
135°	777.8	778.7	779.5	780.3	781.2	781.6	781.6	781.6	781.6	781.6	781.4
137.5°	829.7	830.8	831.8	832.9	834.0	834.4	834.1	833.9	833.6	833.3	832.9
140°	863.1	864.1	865.2	866.3	867.3	867.6	867.2	866.7	866.3	865.9	865.3
142.5°	895.0	896.0	897.1	898.1	899.1	899.5	899.3	899.0	898.8	898.5	897.7
145°	942.6	943.3	944.0	944.6	945.2	945.5	945.5	945.5	945.5	945.5	944.9
147.5°	983.4	984.9	986.3	987.7	989.1	989.6	989.1	988.6	988.1	987.6	987.1
150°	1013.7	1014.2	1014.6	1015.0	1015.5	1015.6	1015.6	1015.6	1015.6	1015.6	1014.8
152.5°	1038.8	1039.5	1040.2	1041.1	1041.8	1041.9	1041.4	1040.9	1040.4	1039.9	1039.6
155°	1074.4	1075.5	1076.4	1077.5	1078.6	1078.7	1077.8	1077.0	1076.2	1075.3	1075.1
157.5°	1104.2	1105.5	1106.9	1108.3	1109.7	1109.9	1109.1	1108.2	1107.4	1106.6	1106.4
160°	1124.6	1125.6	1126.7	1127.7	1128.8	1128.9	1128.0	1127.2	1126.3	1125.5	1125.4
162.5°	1142.0	1143.2	1144.4	1145.7	1146.9	1147.0	1146.0	1145.0	1143.9	1143.0	1142.9
165°	1165.3	1166.6	1167.8	1169.1	1170.4	1170.6	1169.7	1168.9	1168.1	1167.2	1167.0
167.5°	1183.9	1185.2	1186.5	1187.8	1189.1	1189.1	1187.9	1186.6	1185.4	1184.1	1184.1
170°	1193.8	1195.2	1196.7	1198.2	1199.6	1199.7	1198.5	1197.2	1196.0	1194.7	1194.7
172.5°	1202.1	1203.4	1204.7	1206.0	1207.3	1207.3	1206.1	1204.8	1203.5	1202.2	1202.2
175°	1209.8	1211.3	1212.8	1214.3	1215.8	1215.9	1214.6	1213.3	1212.0	1210.8	1210.8
177.5°	1214.4	1215.6	1216.8	1218.0	1219.1	1219.2	1218.2	1217.2	1216.2	1215.1	1215.3
180°	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	14.1	13.9	14.0	13.8	12.9	15.1	16.3	16.5	15.8	15.1	14.4
90°	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0	2.6	4.3	6.0
92.5°	32.8	31.0	29.1	27.6	26.5	25.3	24.1	22.9	24.1	25.3	26.5
95°	68.7	66.6	64.5	63.3	62.9	62.5	62.0	61.6	62.0	62.5	62.9
97.5°	110.3	107.5	104.5	103.0	102.8	102.6	102.5	102.3	102.5	102.6	102.8
100°	139.5	136.7	134.0	132.6	132.6	132.6	132.6	132.6	132.6	132.6	132.6
102.5°	172.5	171.1	169.7	168.6	167.8	166.9	166.1	165.3	166.1	166.9	167.8
105°	223.9	222.7	221.4	220.2	219.2	218.1	217.0	216.0	217.0	218.1	219.2
107.5°	279.2	278.3	277.3	276.3	275.2	274.2	273.1	272.1	273.1	274.2	275.2
110°	317.1	316.4	315.8	315.0	313.9	312.8	311.8	310.8	311.8	312.8	313.9





TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	354.7	353.8	353.0	352.4	351.8	351.2	350.7	350.2	350.7	351.2	351.8
115°	413.2	412.8	412.3	411.7	410.8	410.0	409.2	408.3	409.2	410.0	410.8
117.5°	469.4	469.0	468.6	468.2	467.8	467.5	467.1	466.7	467.1	467.5	467.8
120°	508.3	508.1	507.9	507.3	506.2	505.2	504.1	503.0	504.1	505.2	506.2
122.5°	545.6	545.0	544.5	544.0	543.6	543.2	542.9	542.5	542.9	543.2	543.6
125°	602.1	601.9	601.7	601.0	599.7	598.4	597.2	595.9	597.2	598.4	599.7
127.5°	656.6	656.4	656.2	655.7	654.9	654.2	653.5	652.8	653.5	654.2	654.9
130°	692.7	692.3	691.9	691.0	690.1	689.0	687.9	686.9	687.9	689.0	690.1
132.5°	728.6	728.6	728.7	727.9	726.2	724.5	722.7	721.0	722.7	724.5	726.2
135°	781.2	781.0	780.8	780.1	778.8	777.6	776.2	775.0	776.2	777.6	778.8
137.5°	832.4	831.9	831.5	830.6	829.4	828.2	827.0	825.7	827.0	828.2	829.4
140°	864.7	864.1	863.4	862.6	861.5	860.5	859.4	858.3	859.4	860.5	861.5
142.5°	896.9	896.1	895.4	894.5	893.6	892.8	891.9	891.0	891.9	892.8	893.6
145°	944.3	943.6	943.0	942.2	941.4	940.6	939.7	938.9	939.7	940.6	941.4
147.5°	986.6	986.1	985.5	985.0	984.6	984.1	983.7	983.3	983.7	984.1	984.6
150°	1013.9	1013.1	1012.3	1011.9	1012.2	1012.4	1012.6	1012.8	1012.6	1012.4	1012.2
152.5°	1039.2	1038.9	1038.5	1038.2	1038.0	1037.6	1037.3	1037.1	1037.3	1037.6	1038.0
155°	1074.9	1074.7	1074.5	1074.4	1074.4	1074.4	1074.4	1074.4	1074.4	1074.4	1074.4
157.5°	1106.2	1106.0	1105.7	1105.9	1106.4	1106.8	1107.3	1107.7	1107.3	1106.8	1106.4
160°	1125.1	1124.9	1124.7	1124.9	1125.5	1126.2	1126.8	1127.4	1126.8	1126.2	1125.5
162.5°	1142.9	1142.8	1142.8	1143.0	1143.5	1143.9	1144.4	1144.8	1144.4	1143.9	1143.5
165°	1166.8	1166.6	1166.4	1166.4	1166.9	1167.3	1167.8	1168.2	1167.8	1167.3	1166.9
167.5°	1184.1	1184.1	1184.1	1184.5	1185.4	1186.2	1187.0	1187.9	1187.0	1186.2	1185.4
170°	1194.7	1194.7	1194.7	1195.1	1196.0	1196.8	1197.7	1198.5	1197.7	1196.8	1196.0
172.5°	1202.2	1202.2	1202.2	1202.7	1203.5	1204.4	1205.3	1206.1	1205.3	1204.4	1203.5
175°	1210.8	1210.8	1210.8	1211.2	1212.0	1212.9	1213.7	1214.6	1213.7	1212.9	1212.0
177.5°	1215.5	1215.7	1215.9	1216.3	1216.9	1217.6	1218.3	1219.0	1218.3	1217.6	1216.9
180°	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	14.3	14.6	14.3	15.7	14.4	15.2	15.4	15.2	15.3	15.6	15.2
90°	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3	18.3	19.4	20.2
92.5°	27.6	29.1	31.0	32.8	34.6	36.4	37.7	39.1	40.5	41.9	42.9
95°	63.3	64.5	66.6	68.7	70.8	73.0	74.4	75.9	77.4	78.8	79.8
97.5°	103.0	104.5	107.5	110.3	113.2	116.2	117.6	119.0	120.3	121.7	122.5
100°	132.6	134.0	136.7	139.5	142.2	145.0	146.8	148.7	150.7	152.5	153.7
102.5°	168.6	169.7	171.1	172.5	173.9	175.3	177.3	179.4	181.5	183.5	184.8
105°	220.2	221.4	222.7	223.9	225.2	226.4	227.7	228.9	230.2	231.5	232.4
107.5°	276.3	277.3	278.3	279.2	280.2	281.2	281.8	282.4	283.1	283.7	284.1
110°	315.0	315.8	316.4	317.1	317.7	318.3	318.9	319.6	320.2	320.8	321.1



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	352.4	353.0	353.8	354.7	355.4	356.2	356.5	356.9	357.1	357.4	357.3
115°	411.7	412.3	412.8	413.2	413.6	414.0	413.8	413.6	413.4	413.2	412.9
117.5°	468.2	468.6	469.0	469.4	469.7	470.1	470.3	470.4	470.6	470.8	470.4
120°	507.3	507.9	508.1	508.3	508.6	508.7	508.7	508.7	508.7	508.7	508.3
122.5°	544.0	544.5	545.0	545.6	546.1	546.7	546.5	546.3	546.2	546.0	545.6
125°	601.0	601.7	601.9	602.1	602.3	602.6	602.1	601.7	601.3	600.9	600.5
127.5°	655.7	656.2	656.4	656.6	656.9	657.1	656.9	656.7	656.5	656.3	656.0
130°	691.0	691.9	692.3	692.7	693.1	693.5	693.3	693.1	692.8	692.7	692.4
132.5°	727.9	728.7	728.6	728.6	728.5	728.4	728.1	728.0	727.7	727.5	727.2
135°	780.1	780.8	781.0	781.2	781.4	781.6	781.6	781.6	781.6	781.6	781.2
137.5°	830.6	831.5	831.9	832.4	832.9	833.3	833.6	833.9	834.1	834.4	834.0
140°	862.6	863.4	864.1	864.7	865.3	865.9	866.3	866.7	867.2	867.6	867.3
142.5°	894.5	895.4	896.1	896.9	897.7	898.5	898.8	899.0	899.3	899.5	899.1
145°	942.2	943.0	943.6	944.3	944.9	945.5	945.5	945.5	945.5	945.5	945.2
147.5°	985.0	985.5	986.1	986.6	987.1	987.6	988.1	988.6	989.1	989.6	989.1
150°	1011.9	1012.3	1013.1	1013.9	1014.8	1015.6	1015.6	1015.6	1015.6	1015.6	1015.5
152.5°	1038.2	1038.5	1038.9	1039.2	1039.6	1039.9	1040.4	1040.9	1041.4	1041.9	1041.8
155°	1074.4	1074.5	1074.7	1074.9	1075.1	1075.3	1076.2	1077.0	1077.8	1078.7	1078.6
157.5°	1105.9	1105.7	1106.0	1106.2	1106.4	1106.6	1107.4	1108.2	1109.1	1109.9	1109.7
160°	1124.9	1124.7	1124.9	1125.1	1125.4	1125.5	1126.3	1127.2	1128.0	1128.9	1128.8
162.5°	1143.0	1142.8	1142.8	1142.9	1142.9	1143.0	1143.9	1145.0	1146.0	1147.0	1146.9
165°	1166.4	1166.4	1166.6	1166.8	1167.0	1167.2	1168.1	1168.9	1169.7	1170.6	1170.4
167.5°	1184.5	1184.1	1184.1	1184.1	1184.1	1184.1	1185.4	1186.6	1187.9	1189.1	1189.1
170°	1195.1	1194.7	1194.7	1194.7	1194.7	1194.7	1196.0	1197.2	1198.5	1199.7	1199.6
172.5°	1202.7	1202.2	1202.2	1202.2	1202.2	1202.2	1203.5	1204.8	1206.1	1207.3	1207.3
175°	1211.2	1210.8	1210.8	1210.8	1210.8	1210.8	1212.0	1213.3	1214.6	1215.9	1215.8
177.5°	1216.3	1215.9	1215.7	1215.5	1215.3	1215.1	1216.2	1217.2	1218.2	1219.2	1219.1
180°	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	15.9	15.5	15.6	15.7	15.6	15.5	15.9	15.2	15.6	15.3	15.2
90°	20.9	21.4	22.1	22.7	22.1	21.4	20.9	20.2	19.4	18.3	17.3
92.5°	43.3	43.8	44.3	44.7	44.3	43.8	43.3	42.9	41.9	40.5	39.1
95°	80.2	80.6	81.0	81.4	81.0	80.6	80.2	79.8	78.8	77.4	75.9
97.5°	122.8	123.0	123.3	123.5	123.3	123.0	122.8	122.5	121.7	120.3	119.0
100°	154.1	154.5	155.0	155.4	155.0	154.5	154.1	153.7	152.5	150.7	148.7
102.5°	185.5	186.1	186.6	187.2	186.6	186.1	185.5	184.8	183.5	181.5	179.4
105°	233.1	233.7	234.3	235.0	234.3	233.7	233.1	232.4	231.5	230.2	228.9
107.5°	284.0	284.0	283.9	283.8	283.9	284.0	284.0	284.1	283.7	283.1	282.4
110°	320.8	320.7	320.4	320.2	320.4	320.7	320.8	321.1	320.8	320.2	319.6



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	357.0	356.6	356.2	355.9	356.2	356.6	357.0	357.3	357.4	357.1	356.9
115°	412.8	412.5	412.3	412.1	412.3	412.5	412.8	412.9	413.2	413.4	413.6
117.5°	469.6	468.8	467.9	467.1	467.9	468.8	469.6	470.4	470.8	470.6	470.4
120°	507.5	506.6	505.8	505.0	505.8	506.6	507.5	508.3	508.7	508.7	508.7
122.5°	544.9	544.2	543.6	542.9	543.6	544.2	544.9	545.6	546.0	546.2	546.3
125°	600.4	600.1	599.9	599.7	599.9	600.1	600.4	600.5	600.9	601.3	601.7
127.5°	655.6	655.1	654.7	654.3	654.7	655.1	655.6	656.0	656.3	656.5	656.7
130°	691.9	691.5	691.0	690.6	691.0	691.5	691.9	692.4	692.7	692.8	693.1
132.5°	726.5	725.9	725.4	724.8	725.4	725.9	726.5	727.2	727.5	727.7	728.0
135°	780.3	779.5	778.7	777.8	778.7	779.5	780.3	781.2	781.6	781.6	781.6
137.5°	832.9	831.8	830.8	829.7	830.8	831.8	832.9	834.0	834.4	834.1	833.9
140°	866.3	865.2	864.1	863.1	864.1	865.2	866.3	867.3	867.6	867.2	866.7
142.5°	898.1	897.1	896.0	895.0	896.0	897.1	898.1	899.1	899.5	899.3	899.0
145°	944.6	944.0	943.3	942.6	943.3	944.0	944.6	945.2	945.5	945.5	945.5
147.5°	987.7	986.3	984.9	983.4	984.9	986.3	987.7	989.1	989.6	989.1	988.6
150°	1015.0	1014.6	1014.2	1013.7	1014.2	1014.6	1015.0	1015.5	1015.6	1015.6	1015.6
152.5°	1041.1	1040.2	1039.5	1038.8	1039.5	1040.2	1041.1	1041.8	1041.9	1041.4	1040.9
155°	1077.5	1076.4	1075.5	1074.4	1075.5	1076.4	1077.5	1078.6	1078.7	1077.8	1077.0
157.5°	1108.3	1106.9	1105.5	1104.2	1105.5	1106.9	1108.3	1109.7	1109.9	1109.1	1108.2
160°	1127.7	1126.7	1125.6	1124.6	1125.6	1126.7	1127.7	1128.8	1128.9	1128.0	1127.2
162.5°	1145.7	1144.4	1143.2	1142.0	1143.2	1144.4	1145.7	1146.9	1147.0	1146.0	1145.0
165°	1169.1	1167.8	1166.6	1165.3	1166.6	1167.8	1169.1	1170.4	1170.6	1169.7	1168.9
167.5°	1187.8	1186.5	1185.2	1183.9	1185.2	1186.5	1187.8	1189.1	1189.1	1187.9	1186.6
170°	1198.2	1196.7	1195.2	1193.8	1195.2	1196.7	1198.2	1199.6	1199.7	1198.5	1197.2
172.5°	1206.0	1204.7	1203.4	1202.1	1203.4	1204.7	1206.0	1207.3	1207.3	1206.1	1204.8
175°	1214.3	1212.8	1211.3	1209.8	1211.3	1212.8	1214.3	1215.8	1215.9	1214.6	1213.3
177.5°	1218.0	1216.8	1215.6	1214.4	1215.6	1216.8	1218.0	1219.1	1219.2	1218.2	1217.2
180°	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	15.4	15.2	14.4	15.7	14.3	14.6	14.3	14.4	15.1	15.8	16.5
90°	16.2	15.2	13.7	12.2	10.8	9.3	7.7	6.0	4.3	2.6	1.0
92.5°	37.7	36.4	34.6	32.8	31.0	29.1	27.6	26.5	25.3	24.1	22.9
95°	74.4	73.0	70.8	68.7	66.6	64.5	63.3	62.9	62.5	62.0	61.6
97.5°	117.6	116.2	113.2	110.3	107.5	104.5	103.0	102.8	102.6	102.5	102.3
100°	146.8	145.0	142.2	139.5	136.7	134.0	132.6	132.6	132.6	132.6	132.6
102.5°	177.3	175.3	173.9	172.5	171.1	169.7	168.6	167.8	166.9	166.1	165.3
105°	227.7	226.4	225.2	223.9	222.7	221.4	220.2	219.2	218.1	217.0	216.0
107.5°	281.8	281.2	280.2	279.2	278.3	277.3	276.3	275.2	274.2	273.1	272.1
110°	318.9	318.3	317.7	317.1	316.4	315.8	315.0	313.9	312.8	311.8	310.8



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	356.5	356.2	355.4	354.7	353.8	353.0	352.4	351.8	351.2	350.7	350.2
115°	413.8	414.0	413.6	413.2	412.8	412.3	411.7	410.8	410.0	409.2	408.3
117.5°	470.3	470.1	469.7	469.4	469.0	468.6	468.2	467.8	467.5	467.1	466.7
120°	508.7	508.7	508.6	508.3	508.1	507.9	507.3	506.2	505.2	504.1	503.0
122.5°	546.5	546.7	546.1	545.6	545.0	544.5	544.0	543.6	543.2	542.9	542.5
125°	602.1	602.6	602.3	602.1	601.9	601.7	601.0	599.7	598.4	597.2	595.9
127.5°	656.9	657.1	656.9	656.6	656.4	656.2	655.7	654.9	654.2	653.5	652.8
130°	693.3	693.5	693.1	692.7	692.3	691.9	691.0	690.1	689.0	687.9	686.9
132.5°	728.1	728.4	728.5	728.6	728.6	728.7	727.9	726.2	724.5	722.7	721.0
135°	781.6	781.6	781.4	781.2	781.0	780.8	780.1	778.8	777.6	776.2	775.0
137.5°	833.6	833.3	832.9	832.4	831.9	831.5	830.6	829.4	828.2	827.0	825.7
140°	866.3	865.9	865.3	864.7	864.1	863.4	862.6	861.5	860.5	859.4	858.3
142.5°	898.8	898.5	897.7	896.9	896.1	895.4	894.5	893.6	892.8	891.9	891.0
145°	945.5	945.5	944.9	944.3	943.6	943.0	942.2	941.4	940.6	939.7	938.9
147.5°	988.1	987.6	987.1	986.6	986.1	985.5	985.0	984.6	984.1	983.7	983.3
150°	1015.6	1015.6	1014.8	1013.9	1013.1	1012.3	1011.9	1012.2	1012.4	1012.6	1012.8
152.5°	1040.4	1039.9	1039.6	1039.2	1038.9	1038.5	1038.2	1038.0	1037.6	1037.3	1037.1
155°	1076.2	1075.3	1075.1	1074.9	1074.7	1074.5	1074.4	1074.4	1074.4	1074.4	1074.4
157.5°	1107.4	1106.6	1106.4	1106.2	1106.0	1105.7	1105.9	1106.4	1106.8	1107.3	1107.7
160°	1126.3	1125.5	1125.4	1125.1	1124.9	1124.7	1124.9	1125.5	1126.2	1126.8	1127.4
162.5°	1143.9	1143.0	1142.9	1142.9	1142.8	1142.8	1143.0	1143.5	1143.9	1144.4	1144.8
165°	1168.1	1167.2	1167.0	1166.8	1166.6	1166.4	1166.4	1166.9	1167.3	1167.8	1168.2
167.5°	1185.4	1184.1	1184.1	1184.1	1184.1	1184.1	1184.5	1185.4	1186.2	1187.0	1187.9
170°	1196.0	1194.7	1194.7	1194.7	1194.7	1194.7	1195.1	1196.0	1196.8	1197.7	1198.5
172.5°	1203.5	1202.2	1202.2	1202.2	1202.2	1202.2	1202.7	1203.5	1204.4	1205.3	1206.1
175°	1212.0	1210.8	1210.8	1210.8	1210.8	1210.8	1211.2	1212.0	1212.9	1213.7	1214.6
177.5°	1216.2	1215.1	1215.3	1215.5	1215.7	1215.9	1216.3	1216.9	1217.6	1218.3	1219.0
180°	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.3	15.1	12.9	13.8	14.0	13.9	14.1	13.9	13.7	13.9	14.1
90°	2.6	4.3	6.0	7.7	9.3	10.8	12.2	13.7	15.2	16.2	17.3
92.5°	24.1	25.3	26.5	27.6	29.1	31.0	32.8	34.6	36.4	37.7	39.1
95°	62.0	62.5	62.9	63.3	64.5	66.6	68.7	70.8	73.0	74.4	75.9
97.5°	102.5	102.6	102.8	103.0	104.5	107.5	110.3	113.2	116.2	117.6	119.0
100°	132.6	132.6	132.6	132.6	134.0	136.7	139.5	142.2	145.0	146.8	148.7
102.5°	166.1	166.9	167.8	168.6	169.7	171.1	172.5	173.9	175.3	177.3	179.4
105°	217.0	218.1	219.2	220.2	221.4	222.7	223.9	225.2	226.4	227.7	228.9
107.5°	273.1	274.2	275.2	276.3	277.3	278.3	279.2	280.2	281.2	281.8	282.4
110°	311.8	312.8	313.9	315.0	315.8	316.4	317.1	317.7	318.3	318.9	319.6





TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	350.7	351.2	351.8	352.4	353.0	353.8	354.7	355.4	356.2	356.5	356.9
115°	409.2	410.0	410.8	411.7	412.3	412.8	413.2	413.6	414.0	413.8	413.6
117.5°	467.1	467.5	467.8	468.2	468.6	469.0	469.4	469.7	470.1	470.3	470.4
120°	504.1	505.2	506.2	507.3	507.9	508.1	508.3	508.6	508.7	508.7	508.7
122.5°	542.9	543.2	543.6	544.0	544.5	545.0	545.6	546.1	546.7	546.5	546.3
125°	597.2	598.4	599.7	601.0	601.7	601.9	602.1	602.3	602.6	602.1	601.7
127.5°	653.5	654.2	654.9	655.7	656.2	656.4	656.6	656.9	657.1	656.9	656.7
130°	687.9	689.0	690.1	691.0	691.9	692.3	692.7	693.1	693.5	693.3	693.1
132.5°	722.7	724.5	726.2	727.9	728.7	728.6	728.6	728.5	728.4	728.1	728.0
135°	776.2	777.6	778.8	780.1	780.8	781.0	781.2	781.4	781.6	781.6	781.6
137.5°	827.0	828.2	829.4	830.6	831.5	831.9	832.4	832.9	833.3	833.6	833.9
140°	859.4	860.5	861.5	862.6	863.4	864.1	864.7	865.3	865.9	866.3	866.7
142.5°	891.9	892.8	893.6	894.5	895.4	896.1	896.9	897.7	898.5	898.8	899.0
145°	939.7	940.6	941.4	942.2	943.0	943.6	944.3	944.9	945.5	945.5	945.5
147.5°	983.7	984.1	984.6	985.0	985.5	986.1	986.6	987.1	987.6	988.1	988.6
150°	1012.6	1012.4	1012.2	1011.9	1012.3	1013.1	1013.9	1014.8	1015.6	1015.6	1015.6
152.5°	1037.3	1037.6	1038.0	1038.2	1038.5	1038.9	1039.2	1039.6	1039.9	1040.4	1040.9
155°	1074.4	1074.4	1074.4	1074.4	1074.5	1074.7	1074.9	1075.1	1075.3	1076.2	1077.0
157.5°	1107.3	1106.8	1106.4	1105.9	1105.7	1106.0	1106.2	1106.4	1106.6	1107.4	1108.2
160°	1126.8	1126.2	1125.5	1124.9	1124.7	1124.9	1125.1	1125.4	1125.5	1126.3	1127.2
162.5°	1144.4	1143.9	1143.5	1143.0	1142.8	1142.8	1142.9	1142.9	1143.0	1143.9	1145.0
165°	1167.8	1167.3	1166.9	1166.4	1166.4	1166.6	1166.8	1167.0	1167.2	1168.1	1168.9
167.5°	1187.0	1186.2	1185.4	1184.5	1184.1	1184.1	1184.1	1184.1	1184.1	1185.4	1186.6
170°	1197.7	1196.8	1196.0	1195.1	1194.7	1194.7	1194.7	1194.7	1194.7	1196.0	1197.2
172.5°	1205.3	1204.4	1203.5	1202.7	1202.2	1202.2	1202.2	1202.2	1202.2	1203.5	1204.8
175°	1213.7	1212.9	1212.0	1211.2	1210.8	1210.8	1210.8	1210.8	1210.8	1212.0	1213.3
177.5°	1218.3	1217.6	1216.9	1216.3	1215.9	1215.7	1215.5	1215.3	1215.1	1216.2	1217.2
180°	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	14.8	15.6	14.8	14.3	14.4	15.1	15.7
90°	18.3	19.4	20.2	20.9	21.4	22.1	22.7
92.5°	40.5	41.9	42.9	43.3	43.8	44.3	44.7
95°	77.4	78.8	79.8	80.2	80.6	81.0	81.4
97.5°	120.3	121.7	122.5	122.8	123.0	123.3	123.5
100°	150.7	152.5	153.7	154.1	154.5	155.0	155.4
102.5°	181.5	183.5	184.8	185.5	186.1	186.6	187.2
105°	230.2	231.5	232.4	233.1	233.7	234.3	235.0
107.5°	283.1	283.7	284.1	284.0	284.0	283.9	283.8
110°	320.2	320.8	321.1	320.8	320.7	320.4	320.2



TEST NUMBER: P333635-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	357.1	357.4	357.3	357.0	356.6	356.2	355.9
115°	413.4	413.2	412.9	412.8	412.5	412.3	412.1
117.5°	470.6	470.8	470.4	469.6	468.8	467.9	467.1
120°	508.7	508.7	508.3	507.5	506.6	505.8	505.0
122.5°	546.2	546.0	545.6	544.9	544.2	543.6	542.9
125°	601.3	600.9	600.5	600.4	600.1	599.9	599.7
127.5°	656.5	656.3	656.0	655.6	655.1	654.7	654.3
130°	692.8	692.7	692.4	691.9	691.5	691.0	690.6
132.5°	727.7	727.5	727.2	726.5	725.9	725.4	724.8
135°	781.6	781.6	781.2	780.3	779.5	778.7	777.8
137.5°	834.1	834.4	834.0	832.9	831.8	830.8	829.7
140°	867.2	867.6	867.3	866.3	865.2	864.1	863.1
142.5°	899.3	899.5	899.1	898.1	897.1	896.0	895.0
145°	945.5	945.5	945.2	944.6	944.0	943.3	942.6
147.5°	989.1	989.6	989.1	987.7	986.3	984.9	983.4
150°	1015.6	1015.6	1015.5	1015.0	1014.6	1014.2	1013.7
152.5°	1041.4	1041.9	1041.8	1041.1	1040.2	1039.5	1038.8
155°	1077.8	1078.7	1078.6	1077.5	1076.4	1075.5	1074.4
157.5°	1109.1	1109.9	1109.7	1108.3	1106.9	1105.5	1104.2
160°	1128.0	1128.9	1128.8	1127.7	1126.7	1125.6	1124.6
162.5°	1146.0	1147.0	1146.9	1145.7	1144.4	1143.2	1142.0
165°	1169.7	1170.6	1170.4	1169.1	1167.8	1166.6	1165.3
167.5°	1187.9	1189.1	1189.1	1187.8	1186.5	1185.2	1183.9
170°	1198.5	1199.7	1199.6	1198.2	1196.7	1195.2	1193.8
172.5°	1206.1	1207.3	1207.3	1206.0	1204.7	1203.4	1202.1
175°	1214.6	1215.9	1215.8	1214.3	1212.8	1211.3	1209.8
177.5°	1218.2	1219.2	1219.1	1218.0	1216.8	1215.6	1214.4
180°	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4	1217.4

(END OF REPORT)