

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333636-930

Luminaire Tested: **S125RDIP-S1270D1205U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333636-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7537.4 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	67	63	59	56	54	51	47	45	43	39
3	83	74	66	61	76	69	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	55	47	42	47	42	37	41	36	33	34	31	29	25
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.5	2.0
10°-20°	435.1	5.8
20°-30°	689.8	9.2
30°-40°	831.9	11.0
40°-50°	742.9	9.9
50°-60°	569.7	7.6
60°-70°	370.2	4.9
70°-80°	180.0	2.4
80°-90°	45.6	0.6
90°-100°	340.6	4.5
100°-110°	732.2	9.7
110°-120°	687.1	9.1
120°-130°	556.9	7.4
130°-140°	446.9	5.9
140°-150°	337.2	4.5
150°-160°	237.4	3.1
160°-170°	139.9	1.9
170°-180°	45.5	0.6
0°-30°	1273.4	16.9
0°-40°	2105.3	27.9
0°-60°	3417.9	45.3
0°-90°	4013.7	53.3
90°-120°	1759.9	23.3
90°-150°	3100.9	41.1
90°-180°	3524.0	46.8
0°-180°	7537.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	22	1	22	1	22	16
95°	223	31	223	31	223	315
105°	1255	107	1255	107	1255	1248
115°	1398	191	1398	191	1398	1366
125°	1102	265	1102	265	1102	997
135°	915	311	915	311	915	709
145°	722	362	722	362	722	459
155°	605	413	605	413	605	282
165°	530	451	530	451	530	152
175°	476	469	476	469	476	46
180°	470	470	470	470	470	



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	15.6	15.0	14.3	14.3	14.8	15.5	14.8	14.1	13.9	13.7	13.9
90°	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0	16.1	15.2	13.3
92.5°	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9	247.3	305.4	310.4
95°	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1	821.3	839.4	684.9
97.5°	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4	1039.3	896.3	611.6
100°	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2	1092.3	855.4	545.7
102.5°	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0	1060.5	783.4	495.6
105°	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1	958.7	686.8	447.1
107.5°	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2	854.9	620.3	426.6
110°	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4	795.7	589.2	420.6



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2	751.8	571.0	420.6
115°	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2	703.8	551.4	423.5
117.5°	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8	675.2	541.7	429.7
120°	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5	659.3	537.1	435.8
122.5°	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1	645.7	533.4	441.1
125°	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3	627.1	528.6	450.0
127.5°	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0	610.1	526.4	460.0
130°	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1	598.8	524.8	466.1
132.5°	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1	589.6	524.8	472.9
135°	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4	578.9	524.8	482.2
137.5°	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6	569.2	525.9	490.7
140°	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2	564.6	526.7	494.5
142.5°	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4	560.8	527.5	496.8
145°	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5	555.1	526.7	499.3
147.5°	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4	549.3	524.2	500.2
150°	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6	544.7	522.0	500.2
152.5°	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0	539.4	518.9	499.5
155°	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6	530.5	513.5	497.3
157.5°	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2	522.2	507.8	494.9
160°	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7	515.4	504.0	492.6
162.5°	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3	509.3	499.5	490.3
165°	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8	500.2	492.6	486.9
167.5°	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8	491.3	486.0	481.6
170°	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7	486.0	482.2	479.4
172.5°	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9	480.7	477.7	476.3
175°	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5	473.7	472.7	472.7
177.5°	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4	470.7	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	14.2	13.8	14.1	13.7	12.8	15.0	16.1	16.5	15.7	15.0	14.3
90°	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0	1.9	3.8	5.7
92.5°	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6	14.0	22.0	33.8
95°	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2	32.2	39.8	50.2
97.5°	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9	53.1	58.4	68.8
100°	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3	68.2	72.0	82.4
102.5°	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3	83.4	86.4	97.6
105°	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0	107.0	111.8	121.2
107.5°	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3	133.2	137.7	145.5
110°	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7	150.7	154.4	163.0



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2	168.0	171.0	179.6
115°	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4	193.2	196.1	204.6
117.5°	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1	217.0	220.0	228.5
120°	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3	232.1	235.9	244.4
122.5°	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2	247.3	250.3	258.8
125°	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2	267.2	271.9	280.4
127.5°	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0	283.8	289.9	300.7
130°	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8	293.7	301.3	313.6
132.5°	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4	302.0	311.1	325.0
135°	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7	314.5	325.9	341.0
137.5°	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3	329.1	339.7	354.9
140°	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3	338.2	349.6	364.8
142.5°	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9	348.1	358.7	373.8
145°	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9	363.8	373.2	386.5
147.5°	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5	379.7	387.8	400.1
150°	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4	390.3	397.0	409.3
152.5°	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0	400.1	406.0	416.9
155°	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0	413.0	418.7	428.2
157.5°	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6	425.3	429.9	438.1
160°	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9	432.9	436.8	443.4
162.5°	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7	439.8	443.5	449.4
165°	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9	449.1	451.9	456.6
167.5°	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8	456.8	458.5	461.1
170°	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3	461.4	462.3	464.2
172.5°	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4	463.7	464.6	466.4
175°	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0	467.0	468.0	469.0
177.5°	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7	469.1	469.1	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	14.2	14.6	14.3	15.7	14.3	15.2	15.4	15.1	15.3	15.5	15.3
90°	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0	18.0	18.9	20.9
92.5°	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9	121.8	91.7	77.7
95°	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1	537.1	420.6	341.0
97.5°	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4	913.5	800.0	689.3
100°	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2	1118.8	1021.2	922.7
102.5°	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0	1244.6	1197.8	1131.1
105°	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1	1315.9	1357.6	1347.1
107.5°	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2	1252.4	1359.4	1408.9
110°	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4	1180.4	1313.9	1394.5



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2	1109.1	1244.2	1339.1
115°	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2	1007.1	1136.8	1240.1
117.5°	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8	936.4	1048.1	1142.9
120°	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5	896.2	1000.4	1083.8
122.5°	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1	867.4	960.3	1038.3
125°	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3	828.9	911.3	979.6
127.5°	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0	792.1	869.1	932.9
130°	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1	766.4	840.3	901.9
132.5°	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1	742.2	809.2	868.5
135°	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4	704.8	765.5	819.5
137.5°	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6	671.5	721.9	767.8
140°	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2	651.8	695.4	735.2
142.5°	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4	635.1	672.6	707.1
145°	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5	613.8	643.3	668.8
147.5°	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4	596.2	618.8	638.1
150°	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6	586.4	604.4	621.4
152.5°	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0	576.6	593.0	606.3
155°	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6	561.7	575.0	585.5
157.5°	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2	547.7	558.0	566.1
160°	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7	537.1	546.6	553.3
162.5°	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3	528.1	536.0	541.8
165°	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8	514.4	520.1	524.8
167.5°	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8	501.2	505.5	508.9
170°	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7	493.6	496.4	498.3
172.5°	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9	486.7	488.9	490.0
175°	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5	476.5	478.4	478.4
177.5°	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4	472.1	472.1	472.1
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	15.9	15.3	15.6	15.6	15.6	15.3	15.9	15.3	15.5	15.3	15.1
90°	20.9	20.9	21.8	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0
92.5°	65.6	63.3	62.0	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9
95°	273.8	245.3	237.8	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1
97.5°	630.7	577.7	550.2	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4
100°	857.4	789.1	754.1	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2
102.5°	1061.2	1012.7	974.6	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0
105°	1316.8	1285.6	1266.6	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1
107.5°	1424.2	1424.1	1417.8	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2
110°	1437.1	1455.1	1461.8	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1401.5	1432.4	1448.9	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2
115°	1313.9	1359.4	1385.9	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2
117.5°	1216.8	1263.8	1290.1	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8
120°	1153.9	1199.3	1224.9	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5
122.5°	1100.8	1142.5	1168.1	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1
125°	1032.6	1071.5	1092.3	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3
127.5°	981.0	1015.4	1035.1	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0
130°	949.3	980.5	999.5	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1
132.5°	915.9	947.1	964.6	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1
135°	861.1	892.4	909.5	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4
137.5°	805.0	833.5	849.2	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6
140°	770.2	794.8	809.0	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2
142.5°	736.9	757.7	771.1	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4
145°	691.5	707.7	718.1	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5
147.5°	656.2	669.0	675.1	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4
150°	635.7	647.0	650.9	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6
152.5°	618.2	627.3	631.1	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0
155°	594.9	601.5	604.4	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6
157.5°	573.5	579.0	581.6	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2
160°	559.9	564.6	566.6	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7
162.5°	547.0	551.0	551.4	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3
165°	528.6	530.5	530.5	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8
167.5°	510.8	512.5	511.8	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8
170°	500.2	501.2	501.2	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7
172.5°	490.3	492.0	490.6	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9
175°	478.4	479.4	477.4	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5
177.5°	471.4	472.1	469.9	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	15.4	15.2	14.3	15.7	14.3	14.6	14.2	14.3	15.0	15.7	16.5
90°	16.1	15.2	13.3	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0
92.5°	247.3	305.4	310.4	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6
95°	821.3	839.4	684.9	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2
97.5°	1039.3	896.3	611.6	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9
100°	1092.3	855.4	545.7	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3
102.5°	1060.5	783.4	495.6	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3
105°	958.7	686.8	447.1	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0
107.5°	854.9	620.3	426.6	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3
110°	795.7	589.2	420.6	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	751.8	571.0	420.6	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2
115°	703.8	551.4	423.5	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4
117.5°	675.2	541.7	429.7	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1
120°	659.3	537.1	435.8	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3
122.5°	645.7	533.4	441.1	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2
125°	627.1	528.6	450.0	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2
127.5°	610.1	526.4	460.0	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0
130°	598.8	524.8	466.1	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8
132.5°	589.6	524.8	472.9	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4
135°	578.9	524.8	482.2	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7
137.5°	569.2	525.9	490.7	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3
140°	564.6	526.7	494.5	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3
142.5°	560.8	527.5	496.8	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9
145°	555.1	526.7	499.3	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9
147.5°	549.3	524.2	500.2	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5
150°	544.7	522.0	500.2	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4
152.5°	539.4	518.9	499.5	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0
155°	530.5	513.5	497.3	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0
157.5°	522.2	507.8	494.9	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6
160°	515.4	504.0	492.6	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9
162.5°	509.3	499.5	490.3	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7
165°	500.2	492.6	486.9	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9
167.5°	491.3	486.0	481.6	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8
170°	486.0	482.2	479.4	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3
172.5°	480.7	477.7	476.3	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4
175°	473.7	472.7	472.7	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0
177.5°	470.7	469.9	469.9	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.1	15.0	12.8	13.7	14.1	13.8	14.2	13.9	13.7	13.9	14.1
90°	1.9	3.8	5.7	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0
92.5°	14.0	22.0	33.8	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9
95°	32.2	39.8	50.2	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1
97.5°	53.1	58.4	68.8	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4
100°	68.2	72.0	82.4	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2
102.5°	83.4	86.4	97.6	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0
105°	107.0	111.8	121.2	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1
107.5°	133.2	137.7	145.5	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2
110°	150.7	154.4	163.0	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.0	171.0	179.6	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2
115°	193.2	196.1	204.6	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2
117.5°	217.0	220.0	228.5	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8
120°	232.1	235.9	244.4	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5
122.5°	247.3	250.3	258.8	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1
125°	267.2	271.9	280.4	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3
127.5°	283.8	289.9	300.7	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0
130°	293.7	301.3	313.6	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1
132.5°	302.0	311.1	325.0	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1
135°	314.5	325.9	341.0	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4
137.5°	329.1	339.7	354.9	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6
140°	338.2	349.6	364.8	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2
142.5°	348.1	358.7	373.8	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4
145°	363.8	373.2	386.5	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5
147.5°	379.7	387.8	400.1	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4
150°	390.3	397.0	409.3	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6
152.5°	400.1	406.0	416.9	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0
155°	413.0	418.7	428.2	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6
157.5°	425.3	429.9	438.1	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2
160°	432.9	436.8	443.4	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7
162.5°	439.8	443.5	449.4	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3
165°	449.1	451.9	456.6	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8
167.5°	456.8	458.5	461.1	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8
170°	461.4	462.3	464.2	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7
172.5°	463.7	464.6	466.4	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9
175°	467.0	468.0	469.0	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5
177.5°	469.1	469.1	469.9	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	14.8	15.5	14.8	14.3	14.3	15.0	15.6
90°	18.0	18.9	20.9	20.9	20.9	21.8	21.8
92.5°	121.8	91.7	77.7	65.6	63.3	62.0	60.4
95°	537.1	420.6	341.0	273.8	245.3	237.8	222.7
97.5°	913.5	800.0	689.3	630.7	577.7	550.2	538.1
100°	1118.8	1021.2	922.7	857.4	789.1	754.1	738.9
102.5°	1244.6	1197.8	1131.1	1061.2	1012.7	974.6	963.3
105°	1315.9	1357.6	1347.1	1316.8	1285.6	1266.6	1255.2
107.5°	1252.4	1359.4	1408.9	1424.2	1424.1	1417.8	1410.2
110°	1180.4	1313.9	1394.5	1437.1	1455.1	1461.8	1461.8



TEST NUMBER: P333636-930

CATALOG NUMBER: S125RDIP-S1270D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1109.1	1244.2	1339.1	1401.5	1432.4	1448.9	1455.7
115°	1007.1	1136.8	1240.1	1313.9	1359.4	1385.9	1398.2
117.5°	936.4	1048.1	1142.9	1216.8	1263.8	1290.1	1297.6
120°	896.2	1000.4	1083.8	1153.9	1199.3	1224.9	1232.5
122.5°	867.4	960.3	1038.3	1100.8	1142.5	1168.1	1174.9
125°	828.9	911.3	979.6	1032.6	1071.5	1092.3	1101.8
127.5°	792.1	869.1	932.9	981.0	1015.4	1035.1	1039.3
130°	766.4	840.3	901.9	949.3	980.5	999.5	1005.1
132.5°	742.2	809.2	868.5	915.9	947.1	964.6	971.0
135°	704.8	765.5	819.5	861.1	892.4	909.5	915.2
137.5°	671.5	721.9	767.8	805.0	833.5	849.2	855.4
140°	651.8	695.4	735.2	770.2	794.8	809.0	813.8
142.5°	635.1	672.6	707.1	736.9	757.7	771.1	775.1
145°	613.8	643.3	668.8	691.5	707.7	718.1	721.9
147.5°	596.2	618.8	638.1	656.2	669.0	675.1	676.8
150°	586.4	604.4	621.4	635.7	647.0	650.9	651.8
152.5°	576.6	593.0	606.3	618.2	627.3	631.1	632.1
155°	561.7	575.0	585.5	594.9	601.5	604.4	605.4
157.5°	547.7	558.0	566.1	573.5	579.0	581.6	581.5
160°	537.1	546.6	553.3	559.9	564.6	566.6	565.6
162.5°	528.1	536.0	541.8	547.0	551.0	551.4	551.1
165°	514.4	520.1	524.8	528.6	530.5	530.5	530.5
167.5°	501.2	505.5	508.9	510.8	512.5	511.8	511.6
170°	493.6	496.4	498.3	500.2	501.2	501.2	500.2
172.5°	486.7	488.9	490.0	490.3	492.0	490.6	489.6
175°	476.5	478.4	478.4	478.4	479.4	477.4	476.5
177.5°	472.1	472.1	472.1	471.4	472.1	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9

(END OF REPORT)