

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333615-930

Luminaire Tested: **S125RDIP-S1270D365U930-4F0-1E-UDD-F4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333615-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S1270D365U930-4F0-1E-UDD-F4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5048.5 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 49.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333615-930

CATALOG NUMBER: S125RDIP-S1270D365U930-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P333615-930

CATALOG NUMBER: S125RDIP-S1270D365U930-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	109	109	109	109	99	99	99	91	91	91	83	83	83	79
1	105	100	96	93	100	96	92	89	88	85	83	80	78	76	74	72	71	67
2	96	88	82	76	91	84	79	74	77	73	69	71	67	64	65	62	60	57
3	87	78	70	64	83	75	68	62	69	63	58	63	59	55	58	54	51	48
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	48	45	42
5	74	62	53	47	70	60	52	46	55	49	44	51	46	41	47	43	39	36
6	68	56	47	41	65	54	46	40	50	43	38	46	41	36	43	38	35	32
7	63	51	42	37	60	49	41	36	45	39	34	42	37	32	39	34	31	29
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	31	28	26
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	33	29	25	23
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10869	10869	10869
5°	10895	10771	10836
10°	10812	10670	10670
15°	10683	10454	10369
20°	10519	10152	10030
25°	10326	9855	9638
30°	10086	9508	9205
35°	9842	9150	8719
40°	9613	8777	8241
45°	9334	8360	7721
50°	9055	7905	7178
55°	8731	7472	6598
60°	8407	6945	5977
65°	8023	6333	5265
70°	7585	5569	4538
75°	6977	4694	3773
80°	6148	3686	3169
85°	5187	3016	2831



TEST NUMBER: P333615-930

CATALOG NUMBER: S125RDIP-S1270D365U930-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.3	3.1
10°-20°	442.3	8.8
20°-30°	641.3	12.7
30°-40°	730.9	14.5
40°-50°	712.5	14.1
50°-60°	599.7	11.9
60°-70°	420.4	8.3
70°-80°	216.1	4.3
80°-90°	55.4	1.1
90°-100°	103.6	2.1
100°-110°	222.7	4.4
110°-120°	209.0	4.1
120°-130°	169.4	3.4
130°-140°	135.9	2.7
140°-150°	102.6	2.0
150°-160°	72.2	1.4
160°-170°	42.6	0.8
170°-180°	13.8	0.3
0°-30°	1241.9	24.6
0°-40°	1972.8	39.1
0°-60°	3284.9	65.1
0°-90°	3976.8	78.8
90°-120°	535.3	10.6
90°-150°	943.1	18.7
90°-180°	1072.0	21.2
0°-180°	5048.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1683	1683	1683	1683	1683	
5°	1680	1675	1661	1673	1672	159
15°	1598	1589	1564	1562	1551	450
25°	1449	1428	1383	1367	1352	666
35°	1248	1216	1161	1125	1106	781
45°	1022	983	915	866	845	788
55°	775	733	664	608	586	693
65°	525	480	414	365	344	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	0	3	5	6	7	4
95°	10	28	255	116	68	10
105°	32	46	209	411	382	34
115°	58	70	168	362	425	57
125°	81	94	161	288	335	72
135°	94	114	160	241	278	73
145°	110	126	160	200	220	69
155°	126	135	156	176	184	58
165°	137	141	150	159	161	39
175°	143	143	144	146	145	14
180°	143	143	143	143	143	



TEST NUMBER: P333615-930

CATALOG NUMBER: S125RDIP-S1270D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1686.0	1685.4	1684.7	1684.0	1683.3	1681.9	1679.6	1677.3	1675.1	1672.8	1675.1
5°	1680.5	1679.4	1678.2	1677.1	1675.9	1673.8	1670.7	1667.6	1664.5	1661.4	1664.2
7.5°	1663.9	1662.9	1661.8	1660.7	1659.6	1657.3	1653.5	1649.8	1646.1	1642.3	1644.3
10°	1648.7	1647.8	1647.0	1646.2	1645.3	1642.9	1638.9	1635.0	1631.0	1627.1	1627.9
12.5°	1631.4	1630.4	1629.2	1628.2	1627.1	1623.9	1618.6	1613.3	1607.9	1602.6	1603.3
15°	1597.8	1596.1	1594.5	1592.8	1591.1	1587.2	1581.3	1575.4	1569.5	1563.5	1563.3
17.5°	1559.9	1557.4	1554.8	1552.2	1549.6	1544.5	1537.1	1529.6	1522.2	1514.7	1513.3
20°	1530.5	1527.6	1524.8	1522.0	1519.1	1513.2	1504.2	1495.2	1486.1	1477.1	1475.7
22.5°	1497.9	1495.1	1492.2	1489.5	1486.6	1480.5	1471.0	1461.5	1452.0	1442.5	1439.7
25°	1449.1	1444.9	1440.6	1436.4	1432.2	1424.8	1414.4	1403.9	1393.4	1383.0	1379.3
27.5°	1393.2	1388.0	1382.9	1377.8	1372.6	1364.5	1353.2	1342.1	1330.9	1319.7	1314.6
30°	1352.5	1347.1	1341.7	1336.4	1331.1	1322.4	1310.5	1298.7	1286.8	1275.0	1268.4
32.5°	1312.9	1306.6	1300.3	1294.0	1287.8	1278.6	1266.5	1254.4	1242.3	1230.2	1223.0
35°	1248.3	1241.5	1234.7	1227.9	1221.2	1211.4	1198.7	1186.0	1173.3	1160.6	1152.3
37.5°	1185.0	1176.7	1168.5	1160.3	1151.9	1141.3	1128.2	1115.1	1102.0	1088.8	1079.0
40°	1140.2	1131.7	1123.2	1114.8	1106.4	1095.3	1081.7	1068.2	1054.6	1041.1	1030.4
42.5°	1093.5	1084.8	1076.0	1067.3	1058.7	1047.3	1033.3	1019.3	1005.3	991.2	981.0
45°	1022.0	1013.8	1005.6	997.4	989.2	977.4	961.8	946.3	930.7	915.3	903.9
47.5°	948.0	939.4	930.7	922.1	913.5	901.3	885.7	870.0	854.4	838.7	827.0
50°	901.2	891.9	882.6	873.3	864.0	851.3	835.1	819.0	802.9	786.8	774.9
52.5°	850.4	840.8	831.3	821.7	812.2	799.8	784.6	769.5	754.2	739.1	726.3
55°	775.4	766.4	757.3	748.3	739.2	726.8	711.0	695.2	679.4	663.6	650.9
57.5°	699.6	690.0	680.3	670.7	661.0	648.6	633.3	618.0	602.8	587.5	575.1
60°	650.9	640.9	631.0	621.2	611.3	598.7	583.4	568.2	552.9	537.7	525.3
62.5°	599.0	589.5	580.1	570.6	561.3	548.8	533.3	517.8	502.3	486.8	475.3
65°	525.0	515.4	505.8	496.2	486.6	474.3	459.3	444.3	429.3	414.4	403.1
67.5°	451.5	441.9	432.3	422.7	413.1	401.1	386.8	372.4	358.1	343.7	333.4
70°	401.7	392.1	382.5	372.8	363.3	351.4	337.3	323.2	309.0	294.9	286.2
72.5°	352.9	343.5	334.1	324.7	315.4	304.0	290.8	277.6	264.4	251.2	243.1
75°	279.6	271.2	262.7	254.2	245.7	235.6	223.7	211.9	200.0	188.1	181.9
77.5°	206.9	200.2	193.4	186.6	179.9	171.7	162.2	152.7	143.2	133.7	129.4
80°	165.3	158.5	151.7	144.9	138.1	130.8	122.9	115.0	107.0	99.1	96.6
82.5°	124.6	118.5	112.3	106.2	100.2	94.4	88.9	83.6	78.1	72.7	71.5
85°	70.0	64.8	59.8	54.6	49.6	46.3	44.9	43.5	42.1	40.7	40.4
87.5°	23.5	21.9	20.5	19.0	17.5	16.7	16.6	16.5	16.3	16.1	16.2
90°	0.3	0.6	1.1	1.7	2.3	2.9	3.2	3.8	4.0	4.6	4.9
92.5°	3.5	4.2	6.7	10.3	15.2	23.6	39.4	65.7	94.4	92.9	75.2
95°	9.5	9.8	12.1	15.2	21.6	34.6	65.4	128.8	208.3	255.3	249.8
97.5°	15.8	16.1	17.8	21.0	26.7	36.0	56.3	102.8	186.1	272.6	316.1
100°	20.1	20.7	21.9	25.0	30.6	39.2	55.9	93.4	166.0	260.2	332.2
102.5°	25.0	25.4	26.3	29.7	34.7	43.1	58.0	89.4	150.7	238.3	322.5
105°	32.5	32.5	34.0	36.9	41.5	49.6	62.2	87.9	136.0	208.9	291.6
107.5°	39.9	40.5	41.9	44.3	49.1	56.3	68.6	90.5	129.8	188.7	260.0
110°	45.2	45.8	47.0	49.6	53.9	61.4	73.2	93.1	127.9	179.2	242.1



TEST NUMBER: P333615-930

CATALOG NUMBER: S125RDIP-S1270D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	50.5	51.1	52.0	54.6	58.9	66.2	77.5	96.3	127.9	173.7	228.7
115°	58.2	58.8	59.7	62.2	66.5	73.8	84.5	101.1	128.8	167.7	214.1
117.5°	65.1	66.0	66.9	69.5	74.4	81.4	91.5	106.6	130.7	164.8	205.4
120°	69.7	70.6	71.7	74.4	79.2	86.4	96.5	110.4	132.6	163.4	200.6
122.5°	74.6	75.2	76.1	78.8	84.1	91.3	101.3	114.5	134.1	162.2	196.4
125°	80.7	81.3	82.7	85.3	90.7	98.2	107.8	120.2	136.9	160.8	190.8
127.5°	85.4	86.3	88.1	91.5	97.3	104.8	113.9	125.3	139.9	160.1	185.6
130°	88.5	89.4	91.6	95.4	101.4	108.9	117.8	128.8	141.8	159.6	182.1
132.5°	90.7	91.9	94.7	98.8	105.1	112.6	121.6	131.8	143.8	159.6	179.4
135°	94.5	95.6	99.1	103.7	109.8	117.6	126.5	136.0	146.7	159.6	176.0
137.5°	99.2	100.1	103.3	107.9	113.9	121.9	130.0	139.1	149.3	160.0	173.1
140°	102.0	102.9	106.3	111.0	116.4	124.2	132.6	141.2	150.4	160.2	171.7
142.5°	105.3	105.8	109.1	113.7	119.0	126.3	134.1	142.4	151.1	160.5	170.6
145°	110.1	110.6	113.5	117.6	122.8	129.4	136.9	144.1	151.8	160.2	168.8
147.5°	115.1	115.4	118.0	121.7	126.2	132.0	138.6	145.1	152.1	159.5	167.1
150°	118.1	118.7	120.7	124.5	128.5	133.4	139.7	145.8	152.1	158.7	165.7
152.5°	121.4	121.7	123.5	126.8	130.6	135.0	140.9	146.3	151.9	157.8	164.0
155°	125.6	125.6	127.3	130.2	133.1	137.1	142.0	146.7	151.2	156.2	161.3
157.5°	129.5	129.4	130.8	133.2	135.7	138.8	143.0	146.9	150.5	154.4	158.8
160°	132.0	131.7	132.8	134.9	137.1	139.7	143.5	146.9	149.9	153.3	156.8
162.5°	134.0	133.8	134.9	136.7	138.5	140.6	144.0	146.8	149.1	151.9	154.9
165°	137.1	136.6	137.5	138.8	140.1	141.8	144.1	146.3	148.1	149.9	152.1
167.5°	139.3	138.9	139.5	140.2	141.0	142.2	144.1	145.7	146.5	147.8	149.4
170°	140.6	140.3	140.6	141.2	141.8	142.6	144.1	145.2	145.8	146.7	147.8
172.5°	141.5	141.0	141.3	141.9	142.2	142.6	143.8	144.8	144.9	145.3	146.2
175°	142.6	142.0	142.4	142.6	142.6	142.6	143.5	144.1	143.8	143.8	144.1
177.5°	143.2	142.7	142.7	142.9	142.7	142.7	143.2	143.4	142.9	142.9	143.2
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333615-930

CATALOG NUMBER: S125RDIP-S1270D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1677.3	1679.6	1681.9	1682.9	1682.7	1682.5	1682.2	1682.0
5°	1667.0	1669.9	1672.7	1673.8	1673.2	1672.7	1672.1	1671.5
7.5°	1646.3	1648.3	1650.2	1650.9	1650.2	1649.7	1649.0	1648.5
10°	1628.7	1629.6	1630.4	1630.4	1629.6	1628.7	1627.9	1627.1
12.5°	1603.9	1604.5	1605.2	1604.8	1603.5	1602.2	1600.9	1599.6
15°	1562.9	1562.7	1562.4	1561.0	1558.4	1555.9	1553.3	1550.8
17.5°	1511.9	1510.4	1509.0	1507.3	1505.2	1503.1	1501.0	1498.9
20°	1474.2	1472.8	1471.5	1469.4	1466.9	1464.4	1461.8	1459.3
22.5°	1437.0	1434.2	1431.4	1429.0	1426.9	1424.8	1422.7	1420.7
25°	1375.7	1372.0	1368.3	1364.9	1361.8	1358.7	1355.6	1352.5
27.5°	1309.5	1304.3	1299.2	1295.1	1292.1	1289.1	1286.1	1283.1
30°	1262.0	1255.5	1249.0	1244.5	1241.9	1239.3	1236.8	1234.3
32.5°	1215.9	1208.7	1201.5	1196.3	1193.1	1189.8	1186.7	1183.4
35°	1144.2	1136.0	1127.8	1121.7	1117.8	1113.8	1109.9	1105.9
37.5°	1069.2	1059.4	1049.5	1042.7	1038.9	1035.0	1031.2	1027.4
40°	1019.6	1008.9	998.2	991.1	987.7	984.3	980.9	977.5
42.5°	970.7	960.4	950.1	942.5	937.5	932.5	927.6	922.6
45°	892.6	881.3	870.0	862.3	858.0	853.8	849.5	845.3
47.5°	815.5	803.8	792.1	784.0	779.3	774.6	769.9	765.2
50°	763.1	751.2	739.4	731.3	727.1	722.8	718.6	714.4
52.5°	713.5	700.7	687.9	679.5	675.2	671.0	666.8	662.5
55°	638.1	625.4	612.7	604.1	599.6	595.0	590.5	586.0
57.5°	562.6	550.2	537.8	529.6	525.5	521.5	517.6	513.6
60°	512.8	500.4	488.0	479.6	475.4	471.2	466.9	462.7
62.5°	463.8	452.2	440.8	432.8	428.6	424.4	420.1	415.9
65°	391.8	380.5	369.2	361.4	357.2	352.9	348.7	344.5
67.5°	323.0	312.7	302.4	295.5	292.1	288.7	285.4	281.9
70°	277.4	268.6	259.9	253.8	250.4	247.0	243.6	240.3
72.5°	235.1	227.0	218.8	213.7	211.4	209.2	206.9	204.6
75°	175.7	169.5	163.3	159.1	157.2	155.2	153.3	151.2
77.5°	125.0	120.7	116.3	113.4	111.9	110.5	109.0	107.5
80°	94.1	91.6	88.9	87.4	86.8	86.3	85.8	85.2
82.5°	70.4	69.1	68.0	67.2	66.9	66.5	66.2	65.9
85°	40.1	39.9	39.5	39.3	39.0	38.7	38.4	38.2
87.5°	16.3	16.4	16.4	16.4	16.1	16.0	15.8	15.6
90°	5.2	5.5	5.8	6.4	6.4	6.4	6.6	6.6
92.5°	51.0	37.0	27.9	23.6	20.0	19.2	18.8	18.3
95°	207.2	163.4	127.9	103.7	83.2	74.6	72.3	67.8
97.5°	308.5	277.9	243.3	209.6	191.8	175.7	167.4	163.6
100°	354.4	340.3	310.6	280.6	260.7	240.0	229.3	224.8
102.5°	369.8	378.5	364.4	344.1	322.8	308.0	296.4	293.0
105°	360.8	400.2	412.9	409.8	400.5	391.0	385.2	381.8
107.5°	328.2	380.9	413.4	428.5	433.2	433.2	431.2	428.9
110°	304.3	359.1	399.7	424.1	437.1	442.5	444.6	444.6



TEST NUMBER: P333615-930

CATALOG NUMBER: S125RDIP-S1270D365U930-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	285.4	337.4	378.5	407.3	426.2	435.7	440.7	442.8
115°	261.6	306.3	345.8	377.2	399.7	413.4	421.5	425.3
117.5°	246.3	284.8	318.8	347.6	370.1	384.4	392.4	394.7
120°	238.0	272.6	304.3	329.6	351.0	364.8	372.6	374.9
122.5°	231.8	263.8	292.0	315.8	334.8	347.5	355.3	357.3
125°	222.7	252.1	277.2	297.9	314.1	325.9	332.2	335.1
127.5°	213.5	240.9	264.3	283.7	298.4	308.8	314.8	316.1
130°	207.7	233.1	255.6	274.3	288.7	298.2	304.0	305.7
132.5°	201.9	225.8	246.1	264.2	278.6	288.0	293.3	295.3
135°	194.5	214.3	232.8	249.2	262.0	271.4	276.6	278.3
137.5°	188.2	204.2	219.6	233.5	244.8	253.5	258.3	260.2
140°	184.7	198.2	211.5	223.6	234.2	241.7	246.1	247.5
142.5°	181.7	193.1	204.6	215.1	224.1	230.5	234.6	235.8
145°	177.8	186.7	195.7	203.4	210.3	215.2	218.4	219.6
147.5°	174.1	181.3	188.3	194.1	199.6	203.5	205.3	205.9
150°	172.0	178.4	183.8	189.0	193.3	196.8	198.0	198.2
152.5°	169.7	175.4	180.3	184.4	188.0	190.8	191.9	192.2
155°	166.2	170.9	174.9	178.1	180.9	183.0	183.8	184.1
157.5°	162.8	166.6	169.7	172.2	174.5	176.1	176.9	176.8
160°	160.5	163.4	166.2	168.3	170.3	171.7	172.3	172.0
162.5°	157.9	160.6	163.1	164.9	166.4	167.5	167.7	167.6
165°	154.4	156.5	158.2	159.6	160.8	161.3	161.3	161.3
167.5°	151.1	152.5	153.8	154.8	155.4	155.9	155.6	155.6
170°	149.3	150.1	151.0	151.6	152.1	152.5	152.5	152.1
172.5°	147.2	148.1	148.7	149.0	149.1	149.7	149.2	148.9
175°	145.0	145.0	145.5	145.5	145.5	145.8	145.2	145.0
177.5°	143.4	143.6	143.6	143.6	143.4	143.6	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9

(END OF REPORT)