

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333618-930

Luminaire Tested: **S125RDIP-S1270D590U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333618-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D590U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5742.2 lumens  
Efficiency: N/A  
Efficacy: 104.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	70	
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	60	
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	57	55	55	55	55	51	
3	86	77	70	64	81	73	66	61	66	61	56	59	55	52	53	50	47	47	47	47	44	
4	79	68	60	54	75	65	58	52	59	53	49	53	48	45	48	44	41	41	41	41	38	
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	36	36	36	33	
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	32	32	32	29	
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	28	28	28	28	26	
8	58	46	38	32	55	44	36	31	40	34	29	36	31	27	33	29	26	26	26	26	23	
9	54	42	34	29	51	40	33	28	37	31	26	34	28	25	31	26	23	23	23	23	21	
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	28	24	21	21	21	21	19	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	2.6
10°-20°	435.1	7.6
20°-30°	689.8	12.0
30°-40°	831.9	14.5
40°-50°	742.9	12.9
50°-60°	569.7	9.9
60°-70°	370.2	6.4
70°-80°	180.0	3.1
80°-90°	44.2	0.8
90°-100°	167.2	2.9
100°-110°	359.4	6.3
110°-120°	337.3	5.9
120°-130°	273.4	4.8
130°-140°	219.4	3.8
140°-150°	165.6	2.9
150°-160°	116.5	2.0
160°-170°	68.7	1.2
170°-180°	22.3	0.4
0°-30°	1273.4	22.2
0°-40°	2105.3	36.7
0°-60°	3417.9	59.5
0°-90°	4012.3	69.9
90°-120°	864.0	15.0
90°-150°	1522.3	26.5
90°-180°	1730.0	30.1
0°-180°	5742.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	11	0	11	0	11	9
95°	109	15	109	15	109	155
105°	616	53	616	53	616	613
115°	686	94	686	94	686	671
125°	541	130	541	130	541	489
135°	449	152	449	152	449	348
145°	354	178	354	178	354	225
155°	297	203	297	203	297	139
165°	260	221	260	221	260	74
175°	234	230	234	230	234	23
180°	231	231	231	231	231	



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	13.3	12.8	12.2	12.2	12.7	13.5	13.0	12.3	12.2	12.1	12.5
90°	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4	7.9	7.4	6.5
92.5°	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4	121.4	149.9	152.4
95°	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4	403.2	412.1	336.2
97.5°	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0	510.2	440.0	300.3
100°	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0	536.2	420.0	267.9
102.5°	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0	520.6	384.6	243.3
105°	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3	470.7	337.2	219.5
107.5°	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8	419.7	304.5	209.5
110°	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1	390.7	289.3	206.5



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6	369.1	280.4	206.5
115°	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2	345.5	270.7	207.9
117.5°	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5	331.5	266.0	210.9
120°	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2	323.7	263.7	213.9
122.5°	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1	317.0	261.9	216.5
125°	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5	307.9	259.5	220.9
127.5°	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6	299.5	258.4	225.8
130°	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3	293.9	257.6	228.9
132.5°	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0	289.4	257.6	232.2
135°	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9	284.1	257.6	236.7
137.5°	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7	279.4	258.2	240.9
140°	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1	277.2	258.6	242.8
142.5°	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3	275.3	258.9	243.9
145°	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0	272.6	258.6	245.1
147.5°	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0	269.6	257.4	245.6
150°	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6	267.4	256.2	245.6
152.5°	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9	264.8	254.8	245.2
155°	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3	260.4	252.1	244.2
157.5°	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8	256.3	249.2	243.0
160°	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0	253.0	247.4	241.8
162.5°	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9	250.1	245.2	240.8
165°	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2	245.6	241.8	239.0
167.5°	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9	241.2	238.6	236.4
170°	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9	238.6	236.7	235.3
172.5°	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6	235.9	234.5	233.8
175°	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9	232.5	232.0	232.0
177.5°	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4	231.1	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	12.9	12.7	13.1	13.0	12.2	14.6	16.0	16.4	15.4	14.6	13.8
90°	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5	0.9	1.9	2.8
92.5°	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7	6.8	10.8	16.6
95°	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3	15.8	19.6	24.6
97.5°	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5	26.0	28.6	33.8
100°	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5	33.5	35.4	40.4
102.5°	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4	40.9	42.4	47.9
105°	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6	52.6	54.9	59.5
107.5°	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5	65.4	67.6	71.4
110°	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1	73.9	75.8	80.0





TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6	82.5	84.0	88.2
115°	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9	94.9	96.3	100.4
117.5°	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1	106.5	108.0	112.2
120°	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5	114.0	115.8	120.0
122.5°	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3	121.4	122.9	127.0
125°	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2	131.2	133.5	137.6
127.5°	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9	139.3	142.4	147.7
130°	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8	144.1	147.9	153.9
132.5°	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5	148.3	152.7	159.6
135°	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5	154.4	160.0	167.5
137.5°	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2	161.6	166.8	174.2
140°	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6	166.0	171.6	179.0
142.5°	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8	170.9	176.1	183.5
145°	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7	178.6	183.2	189.7
147.5°	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8	186.4	190.4	196.4
150°	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7	191.6	194.9	200.9
152.5°	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9	196.4	199.3	204.6
155°	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8	202.8	205.5	210.2
157.5°	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9	208.8	211.1	215.1
160°	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0	212.5	214.4	217.7
162.5°	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4	215.9	217.8	220.6
165°	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4	220.5	221.8	224.1
167.5°	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7	224.3	225.1	226.4
170°	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0	226.5	227.0	227.9
172.5°	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4	227.6	228.0	229.0
175°	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2	229.3	229.8	230.2
177.5°	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1	230.3	230.3	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	13.5	13.6	13.2	14.4	13.0	13.7	13.8	13.4	13.5	13.5	13.2
90°	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4	8.8	9.3	10.2
92.5°	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4	59.8	45.0	38.2
95°	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4	263.7	206.5	167.5
97.5°	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0	448.4	392.7	338.3
100°	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0	549.3	501.3	453.0
102.5°	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0	611.0	588.0	555.3
105°	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3	646.0	666.4	661.3
107.5°	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8	614.8	667.4	691.6
110°	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1	579.5	645.1	684.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6	544.5	610.8	657.5
115°	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2	494.4	558.1	608.8
117.5°	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5	459.7	514.5	561.1
120°	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2	439.9	491.1	532.1
122.5°	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1	425.8	471.4	509.7
125°	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5	406.9	447.4	480.9
127.5°	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6	388.9	426.6	458.0
130°	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3	376.3	412.5	442.7
132.5°	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0	364.4	397.3	426.4
135°	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9	346.0	375.8	402.3
137.5°	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7	329.6	354.4	376.9
140°	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1	320.0	341.4	360.9
142.5°	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3	311.8	330.2	347.2
145°	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0	301.3	315.8	328.3
147.5°	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0	292.7	303.8	313.2
150°	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6	287.9	296.7	305.1
152.5°	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9	283.1	291.1	297.7
155°	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3	275.8	282.3	287.4
157.5°	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8	268.9	273.9	277.9
160°	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0	263.7	268.3	271.6
162.5°	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9	259.3	263.1	266.0
165°	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2	252.5	255.4	257.6
167.5°	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9	246.1	248.2	249.8
170°	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9	242.3	243.7	244.6
172.5°	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6	239.0	239.9	240.5
175°	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9	233.9	234.9	234.9
177.5°	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4	231.8	231.8	231.8
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	13.8	13.2	13.3	13.3	13.3	13.2	13.8	13.2	13.5	13.5	13.4
90°	10.2	10.2	10.7	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4
92.5°	32.2	31.1	30.4	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4
95°	134.4	120.4	116.8	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4
97.5°	309.7	283.6	270.1	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0
100°	420.9	387.4	370.2	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0
102.5°	521.0	497.2	478.5	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0
105°	646.5	631.1	621.8	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3
107.5°	699.2	699.1	696.0	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8
110°	705.5	714.4	717.6	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	688.0	703.2	711.3	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6
115°	645.1	667.4	680.4	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2
117.5°	597.4	620.4	633.3	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5
120°	566.5	588.8	601.4	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2
122.5°	540.4	560.8	573.4	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1
125°	507.0	526.0	536.2	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5
127.5°	481.6	498.5	508.1	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6
130°	466.0	481.4	490.6	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3
132.5°	449.6	465.0	473.5	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0
135°	422.7	438.1	446.5	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9
137.5°	395.2	409.2	416.9	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7
140°	378.1	390.2	397.1	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1
142.5°	361.7	371.9	378.5	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3
145°	339.5	347.4	352.5	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0
147.5°	322.1	328.4	331.4	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0
150°	312.1	317.6	319.5	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6
152.5°	303.5	307.9	309.8	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9
155°	292.0	295.3	296.7	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3
157.5°	281.5	284.2	285.5	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8
160°	274.8	277.2	278.1	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0
162.5°	268.6	270.5	270.7	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9
165°	259.5	260.4	260.4	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2
167.5°	250.8	251.6	251.2	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9
170°	245.6	246.1	246.1	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9
172.5°	240.8	241.6	240.8	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6
175°	234.9	235.3	234.4	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9
177.5°	231.4	231.8	230.6	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	13.8	13.7	13.0	14.4	13.2	13.6	13.5	13.8	14.6	15.4	16.4
90°	7.9	7.4	6.5	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5
92.5°	121.4	149.9	152.4	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7
95°	403.2	412.1	336.2	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3
97.5°	510.2	440.0	300.3	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5
100°	536.2	420.0	267.9	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5
102.5°	520.6	384.6	243.3	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4
105°	470.7	337.2	219.5	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6
107.5°	419.7	304.5	209.5	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5
110°	390.7	289.3	206.5	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	369.1	280.4	206.5	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6
115°	345.5	270.7	207.9	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9
117.5°	331.5	266.0	210.9	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1
120°	323.7	263.7	213.9	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5
122.5°	317.0	261.9	216.5	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3
125°	307.9	259.5	220.9	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2
127.5°	299.5	258.4	225.8	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9
130°	293.9	257.6	228.9	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8
132.5°	289.4	257.6	232.2	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5
135°	284.1	257.6	236.7	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5
137.5°	279.4	258.2	240.9	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2
140°	277.2	258.6	242.8	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6
142.5°	275.3	258.9	243.9	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8
145°	272.6	258.6	245.1	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7
147.5°	269.6	257.4	245.6	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8
150°	267.4	256.2	245.6	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7
152.5°	264.8	254.8	245.2	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9
155°	260.4	252.1	244.2	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8
157.5°	256.3	249.2	243.0	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9
160°	253.0	247.4	241.8	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0
162.5°	250.1	245.2	240.8	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4
165°	245.6	241.8	239.0	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4
167.5°	241.2	238.6	236.4	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7
170°	238.6	236.7	235.3	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0
172.5°	235.9	234.5	233.8	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4
175°	232.5	232.0	232.0	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2
177.5°	231.1	230.6	230.6	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.0	14.6	12.2	13.0	13.1	12.7	12.9	12.5	12.1	12.2	12.3
90°	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4
92.5°	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4
95°	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4
97.5°	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0
100°	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0
102.5°	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0
105°	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3
107.5°	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8
110°	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1





TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6
115°	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2
117.5°	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5
120°	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2
122.5°	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1
125°	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5
127.5°	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6
130°	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3
132.5°	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0
135°	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9
137.5°	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7
140°	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1
142.5°	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3
145°	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0
147.5°	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0
150°	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6
152.5°	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9
155°	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3
157.5°	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8
160°	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0
162.5°	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9
165°	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2
167.5°	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9
170°	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9
172.5°	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6
175°	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9
177.5°	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	13.0	13.5	12.7	12.2	12.2	12.8	13.3
90°	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333618-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)