

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333619-930

Luminaire Tested: **S125RDIP-S1270D590U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333619-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D590U930-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5904.3 lumens  
Efficiency: N/A  
Efficacy: 107.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333619-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333619-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	62	57
2	93	86	79	74	88	81	76	71	72	68	64	64	61	58	57	54	52	49
3	85	76	68	62	80	72	65	60	64	59	54	57	53	50	51	47	45	41
4	78	67	59	53	73	64	56	51	57	51	47	51	46	43	45	42	39	36
5	72	60	52	46	68	57	50	44	51	45	41	46	41	37	41	37	34	31
6	66	54	46	40	62	51	44	38	46	40	36	42	37	33	37	33	30	27
7	61	49	41	35	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20
10	50	38	30	25	47	36	29	25	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10869	10869	10869
5°	10895	10771	10836
10°	10812	10670	10670
15°	10683	10454	10369
20°	10519	10152	10030
25°	10326	9855	9638
30°	10086	9508	9205
35°	9842	9150	8719
40°	9613	8777	8241
45°	9334	8360	7721
50°	9055	7905	7178
55°	8731	7472	6598
60°	8407	6945	5977
65°	8023	6333	5265
70°	7585	5569	4538
75°	6977	4694	3773
80°	6148	3686	3169
85°	5187	3016	2831



TEST NUMBER: P333619-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.3	2.7
10°-20°	442.3	7.5
20°-30°	641.3	10.9
30°-40°	730.9	12.4
40°-50°	712.5	12.1
50°-60°	599.7	10.2
60°-70°	420.4	7.1
70°-80°	216.1	3.7
80°-90°	55.9	0.9
90°-100°	22.8	0.4
100°-110°	140.5	2.4
110°-120°	254.9	4.3
120°-130°	327.1	5.5
130°-140°	351.8	6.0
140°-150°	330.3	5.6
150°-160°	267.1	4.5
160°-170°	172.8	2.9
170°-180°	59.6	1.0
0°-30°	1241.9	21.0
0°-40°	1972.8	33.4
0°-60°	3284.9	55.6
0°-90°	3977.3	67.4
90°-120°	418.2	7.1
90°-150°	1427.4	24.2
90°-180°	1927.0	32.6
0°-180°	5904.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1683	1683	1683	1683	1683	
5°	1680	1675	1661	1673	1672	159
15°	1598	1589	1564	1562	1551	450
25°	1449	1428	1383	1367	1352	666
35°	1248	1216	1161	1125	1106	781
45°	1022	983	915	866	845	788
55°	775	733	664	608	586	693
65°	525	480	414	365	344	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	0	4	7	10	11	4
95°	26	24	7	10	10	34
105°	137	138	139	139	138	145
115°	257	259	260	258	255	254
125°	365	368	368	367	365	326
135°	455	458	457	456	454	351
145°	528	529	529	529	526	330
155°	582	579	580	581	577	268
165°	614	611	611	614	610	173
175°	628	625	625	628	625	60
180°	628	628	628	628	628	



TEST NUMBER: P333619-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1686.0	1685.4	1684.7	1684.0	1683.3	1681.9	1679.6	1677.3	1675.1	1672.8	1675.1
5°	1680.5	1679.4	1678.2	1677.1	1675.9	1673.8	1670.7	1667.6	1664.5	1661.4	1664.2
7.5°	1663.9	1662.9	1661.8	1660.7	1659.6	1657.3	1653.5	1649.8	1646.1	1642.3	1644.3
10°	1648.7	1647.8	1647.0	1646.2	1645.3	1642.9	1638.9	1635.0	1631.0	1627.1	1627.9
12.5°	1631.4	1630.4	1629.2	1628.2	1627.1	1623.9	1618.6	1613.3	1607.9	1602.6	1603.3
15°	1597.8	1596.1	1594.5	1592.8	1591.1	1587.2	1581.3	1575.4	1569.5	1563.5	1563.3
17.5°	1559.9	1557.4	1554.8	1552.2	1549.6	1544.5	1537.1	1529.6	1522.2	1514.7	1513.3
20°	1530.5	1527.6	1524.8	1522.0	1519.1	1513.2	1504.2	1495.2	1486.1	1477.1	1475.7
22.5°	1497.9	1495.1	1492.2	1489.5	1486.6	1480.5	1471.0	1461.5	1452.0	1442.5	1439.7
25°	1449.1	1444.9	1440.6	1436.4	1432.2	1424.8	1414.4	1403.9	1393.4	1383.0	1379.3
27.5°	1393.2	1388.0	1382.9	1377.8	1372.6	1364.5	1353.2	1342.1	1330.9	1319.7	1314.6
30°	1352.5	1347.1	1341.7	1336.4	1331.1	1322.4	1310.5	1298.7	1286.8	1275.0	1268.4
32.5°	1312.9	1306.6	1300.3	1294.0	1287.8	1278.6	1266.5	1254.4	1242.3	1230.2	1223.0
35°	1248.3	1241.5	1234.7	1227.9	1221.2	1211.4	1198.7	1186.0	1173.3	1160.6	1152.3
37.5°	1185.0	1176.7	1168.5	1160.3	1151.9	1141.3	1128.2	1115.1	1102.0	1088.8	1079.0
40°	1140.2	1131.7	1123.2	1114.8	1106.4	1095.3	1081.7	1068.2	1054.6	1041.1	1030.4
42.5°	1093.5	1084.8	1076.0	1067.3	1058.7	1047.3	1033.3	1019.3	1005.3	991.2	981.0
45°	1022.0	1013.8	1005.6	997.4	989.2	977.4	961.8	946.3	930.7	915.3	903.9
47.5°	948.0	939.4	930.7	922.1	913.5	901.3	885.7	870.0	854.4	838.7	827.0
50°	901.2	891.9	882.6	873.3	864.0	851.3	835.1	819.0	802.9	786.8	774.9
52.5°	850.4	840.8	831.3	821.7	812.2	799.8	784.6	769.5	754.2	739.1	726.3
55°	775.4	766.4	757.3	748.3	739.2	726.8	711.0	695.2	679.4	663.6	650.9
57.5°	699.6	690.0	680.3	670.7	661.0	648.6	633.3	618.0	602.8	587.5	575.1
60°	650.9	640.9	631.0	621.2	611.3	598.7	583.4	568.2	552.9	537.7	525.3
62.5°	599.0	589.5	580.1	570.6	561.3	548.8	533.3	517.8	502.3	486.8	475.3
65°	525.0	515.4	505.8	496.2	486.6	474.3	459.3	444.3	429.3	414.4	403.1
67.5°	451.5	441.9	432.3	422.7	413.1	401.1	386.8	372.4	358.1	343.7	333.4
70°	401.7	392.1	382.5	372.8	363.3	351.4	337.3	323.2	309.0	294.9	286.2
72.5°	352.9	343.5	334.1	324.7	315.4	304.0	290.8	277.6	264.4	251.2	243.1
75°	279.6	271.2	262.7	254.2	245.7	235.6	223.7	211.9	200.0	188.1	181.9
77.5°	206.9	200.2	193.4	186.6	179.9	171.7	162.2	152.7	143.2	133.7	129.4
80°	165.3	158.5	151.7	144.9	138.1	130.8	122.9	115.0	107.0	99.1	96.6
82.5°	124.6	118.5	112.3	106.2	100.2	94.4	88.9	83.6	78.1	72.7	71.5
85°	70.0	64.8	59.8	54.6	49.6	46.3	44.9	43.5	42.1	40.7	40.4
87.5°	23.5	22.1	20.6	19.2	17.9	17.0	17.0	16.9	16.8	16.7	16.9
90°	0.5	1.3	2.1	2.9	3.8	4.6	5.3	6.0	6.7	7.4	8.0
92.5°	7.2	6.6	6.0	5.5	4.8	4.9	5.5	6.2	6.8	7.4	8.0
95°	26.5	26.2	25.9	25.6	25.3	23.2	19.2	15.3	11.3	7.4	8.0
97.5°	55.4	55.9	56.5	57.0	57.6	54.0	46.2	38.4	30.7	22.9	20.0
100°	77.7	78.0	78.3	78.6	78.9	79.2	79.7	80.1	80.6	81.0	65.6
102.5°	100.4	100.8	101.2	101.6	101.9	102.2	102.5	102.8	103.1	103.3	100.4
105°	136.7	137.1	137.6	138.0	138.4	138.6	138.6	138.6	138.6	138.6	138.6
107.5°	174.6	174.6	174.6	174.6	174.6	174.6	174.8	175.0	175.3	175.5	175.5
110°	199.1	199.1	199.1	199.1	199.1	199.2	199.4	199.6	199.8	200.0	199.7



TEST NUMBER: P333619-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	222.2	222.4	222.7	222.9	223.1	223.3	223.5	223.6	223.7	223.8	223.5
115°	256.7	257.3	257.8	258.3	258.9	259.2	259.3	259.3	259.4	259.6	259.2
117.5°	292.6	292.5	292.5	292.5	292.5	292.7	293.1	293.5	293.8	294.2	293.8
120°	315.0	314.8	314.7	314.6	314.5	314.6	315.0	315.2	315.5	315.8	315.6
122.5°	334.6	335.0	335.4	335.8	336.2	336.5	336.6	336.8	336.9	337.0	336.9
125°	365.2	365.9	366.6	367.3	368.0	368.4	368.4	368.4	368.4	368.4	368.0
127.5°	394.3	394.8	395.3	395.8	396.3	396.6	396.5	396.5	396.4	396.3	396.1
130°	412.1	412.6	413.2	413.7	414.2	414.5	414.6	414.7	414.8	414.9	414.6
132.5°	430.0	430.6	431.2	431.8	432.4	432.6	432.4	432.1	431.9	431.7	431.6
135°	455.4	456.0	456.6	457.2	457.9	458.1	457.9	457.6	457.5	457.2	457.1
137.5°	478.7	479.3	479.8	480.4	480.9	481.1	480.9	480.7	480.5	480.3	480.4
140°	494.0	494.2	494.4	494.6	494.8	494.9	494.8	494.6	494.6	494.5	494.6
142.5°	507.8	507.9	508.0	508.2	508.3	508.4	508.6	508.7	508.8	509.0	509.0
145°	528.0	528.2	528.4	528.6	528.8	528.9	528.9	528.9	528.9	528.9	529.0
147.5°	545.6	545.6	545.5	545.5	545.4	545.5	545.6	545.8	545.8	546.0	546.2
150°	556.8	556.6	556.4	556.2	556.0	556.0	556.2	556.4	556.6	556.8	557.0
152.5°	567.6	567.1	566.7	566.2	565.7	565.7	565.8	566.1	566.2	566.5	566.7
155°	581.5	580.8	580.2	579.6	578.9	578.8	578.9	579.2	579.4	579.6	579.9
157.5°	592.2	591.7	591.4	591.0	590.7	590.5	590.5	590.5	590.5	590.6	590.9
160°	599.6	599.0	598.3	597.7	597.1	596.9	597.0	597.0	597.1	597.3	597.7
162.5°	605.5	605.0	604.3	603.6	603.1	602.8	602.9	603.0	603.1	603.2	603.8
165°	613.5	612.9	612.3	611.7	611.1	610.8	610.9	611.0	611.1	611.2	611.8
167.5°	619.5	618.9	618.2	617.6	616.9	616.7	616.8	616.9	616.9	617.1	617.8
170°	622.9	622.2	621.4	620.7	620.0	619.6	619.7	619.9	620.0	620.0	620.9
172.5°	625.1	624.4	623.6	622.9	622.2	621.9	622.1	622.3	622.5	622.6	623.4
175°	627.5	626.9	626.2	625.7	625.0	624.8	624.8	625.0	625.1	625.2	626.0
177.5°	628.6	628.1	627.6	627.1	626.6	626.4	626.5	626.6	626.6	626.7	627.4
180°	627.5	627.5	627.5	627.5	627.5	627.5	627.5	627.5	627.5	627.5	627.5



TEST NUMBER: P333619-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1677.3	1679.6	1681.9	1682.9	1682.7	1682.5	1682.2	1682.0
5°	1667.0	1669.9	1672.7	1673.8	1673.2	1672.7	1672.1	1671.5
7.5°	1646.3	1648.3	1650.2	1650.9	1650.2	1649.7	1649.0	1648.5
10°	1628.7	1629.6	1630.4	1630.4	1629.6	1628.7	1627.9	1627.1
12.5°	1603.9	1604.5	1605.2	1604.8	1603.5	1602.2	1600.9	1599.6
15°	1562.9	1562.7	1562.4	1561.0	1558.4	1555.9	1553.3	1550.8
17.5°	1511.9	1510.4	1509.0	1507.3	1505.2	1503.1	1501.0	1498.9
20°	1474.2	1472.8	1471.5	1469.4	1466.9	1464.4	1461.8	1459.3
22.5°	1437.0	1434.2	1431.4	1429.0	1426.9	1424.8	1422.7	1420.7
25°	1375.7	1372.0	1368.3	1364.9	1361.8	1358.7	1355.6	1352.5
27.5°	1309.5	1304.3	1299.2	1295.1	1292.1	1289.1	1286.1	1283.1
30°	1262.0	1255.5	1249.0	1244.5	1241.9	1239.3	1236.8	1234.3
32.5°	1215.9	1208.7	1201.5	1196.3	1193.1	1189.8	1186.7	1183.4
35°	1144.2	1136.0	1127.8	1121.7	1117.8	1113.8	1109.9	1105.9
37.5°	1069.2	1059.4	1049.5	1042.7	1038.9	1035.0	1031.2	1027.4
40°	1019.6	1008.9	998.2	991.1	987.7	984.3	980.9	977.5
42.5°	970.7	960.4	950.1	942.5	937.5	932.5	927.6	922.6
45°	892.6	881.3	870.0	862.3	858.0	853.8	849.5	845.3
47.5°	815.5	803.8	792.1	784.0	779.3	774.6	769.9	765.2
50°	763.1	751.2	739.4	731.3	727.1	722.8	718.6	714.4
52.5°	713.5	700.7	687.9	679.5	675.2	671.0	666.8	662.5
55°	638.1	625.4	612.7	604.1	599.6	595.0	590.5	586.0
57.5°	562.6	550.2	537.8	529.6	525.5	521.5	517.6	513.6
60°	512.8	500.4	488.0	479.6	475.4	471.2	466.9	462.7
62.5°	463.8	452.2	440.8	432.8	428.6	424.4	420.1	415.9
65°	391.8	380.5	369.2	361.4	357.2	352.9	348.7	344.5
67.5°	323.0	312.7	302.4	295.5	292.1	288.7	285.4	281.9
70°	277.4	268.6	259.9	253.8	250.4	247.0	243.6	240.3
72.5°	235.1	227.0	218.8	213.7	211.4	209.2	206.9	204.6
75°	175.7	169.5	163.3	159.1	157.2	155.2	153.3	151.2
77.5°	125.0	120.7	116.3	113.4	111.9	110.5	109.0	107.5
80°	94.1	91.6	88.9	87.4	86.8	86.3	85.8	85.2
82.5°	70.4	69.1	68.0	67.2	66.9	66.5	66.2	65.9
85°	40.1	39.9	39.5	39.3	39.0	38.7	38.4	38.2
87.5°	17.0	17.0	17.1	17.1	17.0	16.8	16.6	16.5
90°	8.5	9.0	9.5	9.9	10.3	10.5	10.8	11.2
92.5°	8.5	9.0	9.5	9.9	9.9	10.1	10.3	10.4
95°	8.5	9.0	9.5	9.8	9.8	9.8	9.8	9.8
97.5°	17.0	14.1	11.3	9.8	9.8	9.8	9.8	9.8
100°	50.1	34.7	19.3	11.4	11.0	10.6	10.2	9.8
102.5°	97.4	94.5	91.6	86.7	79.6	72.6	65.6	58.5
105°	138.6	138.6	138.6	138.6	138.4	138.4	138.3	138.1
107.5°	175.5	175.5	175.5	175.4	175.1	174.8	174.5	174.1
110°	199.4	199.1	198.8	198.7	198.8	198.9	199.0	199.1





TEST NUMBER: P333619-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	223.1	222.7	222.3	222.0	221.8	221.7	221.6	221.4
115°	258.7	258.3	257.9	257.4	256.7	256.2	255.5	254.9
117.5°	293.2	292.6	292.1	291.7	291.5	291.1	290.9	290.7
120°	315.4	315.2	315.0	314.6	314.1	313.6	313.1	312.6
122.5°	336.6	336.5	336.2	335.8	335.3	334.6	334.0	333.5
125°	367.6	367.1	366.7	366.4	366.1	365.7	365.5	365.2
127.5°	395.8	395.7	395.4	394.9	394.1	393.4	392.6	391.8
130°	414.3	414.0	413.7	413.3	412.8	412.2	411.7	411.2
132.5°	431.5	431.5	431.5	431.1	430.6	430.1	429.6	429.1
135°	456.8	456.6	456.4	456.0	455.4	454.8	454.1	453.6
137.5°	480.4	480.5	480.5	480.2	479.7	479.2	478.7	478.1
140°	494.9	495.0	495.3	495.0	494.5	493.8	493.3	492.6
142.5°	509.1	509.1	509.2	508.8	508.3	507.6	507.0	506.4
145°	529.1	529.2	529.3	529.0	528.4	527.8	527.2	526.5
147.5°	546.3	546.4	546.5	546.2	545.4	544.7	544.0	543.2
150°	557.2	557.4	557.6	557.3	556.5	555.6	554.8	554.0
152.5°	566.9	567.1	567.3	567.0	566.3	565.6	564.8	564.0
155°	580.2	580.5	580.8	580.6	579.8	578.9	578.1	577.2
157.5°	591.3	591.6	591.9	591.7	590.8	590.0	589.1	588.3
160°	598.1	598.5	598.9	598.7	597.9	597.0	596.2	595.4
162.5°	604.4	605.0	605.5	605.4	604.5	603.6	602.7	601.7
165°	612.5	613.1	613.7	613.6	612.8	612.0	611.1	610.3
167.5°	618.6	619.3	620.0	620.0	619.1	618.1	617.2	616.2
170°	621.7	622.6	623.4	623.3	622.4	621.4	620.5	619.6
172.5°	624.1	624.9	625.7	625.6	624.6	623.7	622.7	621.8
175°	626.8	627.6	628.5	628.4	627.5	626.6	625.7	624.7
177.5°	627.9	628.5	629.1	629.0	628.4	627.7	627.0	626.4
180°	627.5	627.5	627.5	627.5	627.5	627.5	627.5	627.5

(END OF REPORT)