

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333620-930

Luminaire Tested: **S125RDIP-S1270D590U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333620-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D590U930-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 590 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5645.0 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333620-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333620-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	98	94	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	86	80	75	88	82	76	72	74	69	66	66	63	60	59	57	54	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	49	47	43
4	79	68	60	53	74	64	57	51	58	52	48	53	48	44	47	43	40	37
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	43	39	35	33
6	67	55	46	40	63	52	44	39	47	41	36	43	38	34	39	35	31	29
7	62	49	41	36	59	47	40	34	43	37	32	39	34	30	36	31	28	26
8	58	45	37	32	55	43	36	31	39	33	29	36	31	27	33	28	25	23
9	54	41	34	28	51	40	32	28	36	30	26	33	28	24	30	26	23	21
10	50	38	31	26	48	36	30	25	34	28	24	31	26	22	28	24	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10869	10869	10869
5°	10895	10771	10836
10°	10812	10670	10670
15°	10683	10454	10369
20°	10519	10152	10030
25°	10326	9855	9638
30°	10086	9508	9205
35°	9842	9150	8719
40°	9613	8777	8241
45°	9334	8360	7721
50°	9055	7905	7178
55°	8731	7472	6598
60°	8407	6945	5977
65°	8023	6333	5265
70°	7585	5569	4538
75°	6977	4694	3773
80°	6148	3686	3169
85°	5187	3016	2831



TEST NUMBER: P333620-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.3	2.8
10°-20°	442.3	7.8
20°-30°	641.3	11.4
30°-40°	730.9	12.9
40°-50°	712.5	12.6
50°-60°	599.7	10.6
60°-70°	420.4	7.4
70°-80°	216.1	3.8
80°-90°	55.9	1.0
90°-100°	40.0	0.7
100°-110°	118.2	2.1
110°-120°	200.2	3.5
120°-130°	263.5	4.7
130°-140°	295.3	5.2
140°-150°	289.4	5.1
150°-160°	243.0	4.3
160°-170°	161.6	2.9
170°-180°	56.5	1.0
0°-30°	1241.9	22.0
0°-40°	1972.8	34.9
0°-60°	3284.9	58.2
0°-90°	3977.3	70.5
90°-120°	358.5	6.3
90°-150°	1206.6	21.4
90°-180°	1668.0	29.5
0°-180°	5645.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1683	1683	1683	1683	1683	
5°	1680	1675	1661	1673	1672	159
15°	1598	1589	1564	1562	1551	450
25°	1449	1428	1383	1367	1352	666
35°	1248	1216	1161	1125	1106	781
45°	1022	983	915	866	845	788
55°	775	733	664	608	586	693
65°	525	480	414	365	344	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	0	4	7	10	11	5
95°	30	31	36	39	40	32
105°	106	108	111	114	115	113
115°	200	202	203	203	202	198
125°	292	295	296	295	294	262
135°	380	383	384	384	382	293
145°	461	463	464	464	463	288
155°	527	527	528	530	527	243
165°	574	573	573	575	572	162
175°	596	594	594	597	594	57
180°	598	598	598	598	598	



TEST NUMBER: P333620-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1686.0	1685.4	1684.7	1684.0	1683.3	1681.9	1679.6	1677.3	1675.1	1672.8	1675.1
5°	1680.5	1679.4	1678.2	1677.1	1675.9	1673.8	1670.7	1667.6	1664.5	1661.4	1664.2
7.5°	1663.9	1662.9	1661.8	1660.7	1659.6	1657.3	1653.5	1649.8	1646.1	1642.3	1644.3
10°	1648.7	1647.8	1647.0	1646.2	1645.3	1642.9	1638.9	1635.0	1631.0	1627.1	1627.9
12.5°	1631.4	1630.4	1629.2	1628.2	1627.1	1623.9	1618.6	1613.3	1607.9	1602.6	1603.3
15°	1597.8	1596.1	1594.5	1592.8	1591.1	1587.2	1581.3	1575.4	1569.5	1563.5	1563.3
17.5°	1559.9	1557.4	1554.8	1552.2	1549.6	1544.5	1537.1	1529.6	1522.2	1514.7	1513.3
20°	1530.5	1527.6	1524.8	1522.0	1519.1	1513.2	1504.2	1495.2	1486.1	1477.1	1475.7
22.5°	1497.9	1495.1	1492.2	1489.5	1486.6	1480.5	1471.0	1461.5	1452.0	1442.5	1439.7
25°	1449.1	1444.9	1440.6	1436.4	1432.2	1424.8	1414.4	1403.9	1393.4	1383.0	1379.3
27.5°	1393.2	1388.0	1382.9	1377.8	1372.6	1364.5	1353.2	1342.1	1330.9	1319.7	1314.6
30°	1352.5	1347.1	1341.7	1336.4	1331.1	1322.4	1310.5	1298.7	1286.8	1275.0	1268.4
32.5°	1312.9	1306.6	1300.3	1294.0	1287.8	1278.6	1266.5	1254.4	1242.3	1230.2	1223.0
35°	1248.3	1241.5	1234.7	1227.9	1221.2	1211.4	1198.7	1186.0	1173.3	1160.6	1152.3
37.5°	1185.0	1176.7	1168.5	1160.3	1151.9	1141.3	1128.2	1115.1	1102.0	1088.8	1079.0
40°	1140.2	1131.7	1123.2	1114.8	1106.4	1095.3	1081.7	1068.2	1054.6	1041.1	1030.4
42.5°	1093.5	1084.8	1076.0	1067.3	1058.7	1047.3	1033.3	1019.3	1005.3	991.2	981.0
45°	1022.0	1013.8	1005.6	997.4	989.2	977.4	961.8	946.3	930.7	915.3	903.9
47.5°	948.0	939.4	930.7	922.1	913.5	901.3	885.7	870.0	854.4	838.7	827.0
50°	901.2	891.9	882.6	873.3	864.0	851.3	835.1	819.0	802.9	786.8	774.9
52.5°	850.4	840.8	831.3	821.7	812.2	799.8	784.6	769.5	754.2	739.1	726.3
55°	775.4	766.4	757.3	748.3	739.2	726.8	711.0	695.2	679.4	663.6	650.9
57.5°	699.6	690.0	680.3	670.7	661.0	648.6	633.3	618.0	602.8	587.5	575.1
60°	650.9	640.9	631.0	621.2	611.3	598.7	583.4	568.2	552.9	537.7	525.3
62.5°	599.0	589.5	580.1	570.6	561.3	548.8	533.3	517.8	502.3	486.8	475.3
65°	525.0	515.4	505.8	496.2	486.6	474.3	459.3	444.3	429.3	414.4	403.1
67.5°	451.5	441.9	432.3	422.7	413.1	401.1	386.8	372.4	358.1	343.7	333.4
70°	401.7	392.1	382.5	372.8	363.3	351.4	337.3	323.2	309.0	294.9	286.2
72.5°	352.9	343.5	334.1	324.7	315.4	304.0	290.8	277.6	264.4	251.2	243.1
75°	279.6	271.2	262.7	254.2	245.7	235.6	223.7	211.9	200.0	188.1	181.9
77.5°	206.9	200.2	193.4	186.6	179.9	171.7	162.2	152.7	143.2	133.7	129.4
80°	165.3	158.5	151.7	144.9	138.1	130.8	122.9	115.0	107.0	99.1	96.6
82.5°	124.6	118.5	112.3	106.2	100.2	94.4	88.9	83.6	78.1	72.7	71.5
85°	70.0	64.8	59.8	54.6	49.6	46.3	44.9	43.5	42.1	40.7	40.4
87.5°	23.5	22.1	20.6	19.2	17.9	17.0	17.0	16.9	16.8	16.7	16.9
90°	0.5	1.3	2.1	2.9	3.8	4.6	5.3	6.0	6.7	7.4	8.0
92.5°	11.3	11.8	12.4	13.0	13.5	14.3	15.2	16.1	17.0	17.9	18.5
95°	30.2	30.4	30.7	30.8	31.1	31.7	32.7	33.8	34.8	35.8	36.5
97.5°	50.2	50.3	50.4	50.5	50.5	51.3	52.7	54.1	55.6	57.0	57.7
100°	65.1	65.1	65.1	65.1	65.1	65.8	67.1	68.5	69.8	71.2	72.1
102.5°	81.1	81.5	81.9	82.3	82.8	83.3	84.0	84.7	85.4	86.0	87.1
105°	106.1	106.6	107.0	107.6	108.1	108.7	109.3	109.9	110.6	111.1	111.8
107.5°	133.5	134.1	134.6	135.1	135.7	136.2	136.6	137.1	137.5	138.0	138.4
110°	152.5	153.0	153.6	154.1	154.7	155.1	155.3	155.6	156.0	156.3	156.6



TEST NUMBER: P333620-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.9	172.2	172.4	172.7	173.0	173.3	173.7	174.1	174.5	174.9	175.0
115°	200.5	200.9	201.3	201.7	202.1	202.4	202.6	202.8	203.0	203.3	203.2
117.5°	229.1	229.3	229.5	229.7	229.8	230.1	230.2	230.4	230.6	230.8	230.9
120°	247.0	247.5	248.0	248.5	249.1	249.3	249.5	249.6	249.6	249.7	249.7
122.5°	266.4	266.5	266.7	266.8	267.1	267.3	267.6	267.8	268.1	268.4	268.3
125°	292.5	293.2	293.8	294.4	295.1	295.4	295.5	295.6	295.7	295.8	295.6
127.5°	320.5	320.8	321.1	321.5	321.9	322.1	322.2	322.4	322.5	322.6	322.5
130°	337.2	337.7	338.3	338.8	339.2	339.7	339.8	340.1	340.2	340.5	340.4
132.5°	353.9	354.8	355.6	356.4	357.3	357.8	357.7	357.7	357.6	357.6	357.5
135°	380.4	381.1	381.7	382.3	382.9	383.3	383.4	383.5	383.6	383.7	383.7
137.5°	405.4	406.0	406.6	407.2	407.8	408.2	408.5	408.6	408.9	409.1	409.2
140°	421.3	421.9	422.4	422.9	423.5	423.9	424.2	424.5	424.8	425.1	425.3
142.5°	437.4	437.8	438.2	438.7	439.1	439.5	439.9	440.3	440.8	441.1	441.2
145°	460.9	461.3	461.8	462.2	462.6	462.9	463.3	463.6	463.9	464.1	464.1
147.5°	482.7	482.9	483.1	483.4	483.6	483.8	484.0	484.4	484.6	484.9	485.1
150°	497.2	497.1	497.0	496.9	496.8	496.9	497.3	497.7	498.1	498.6	498.6
152.5°	509.1	509.2	509.4	509.6	509.6	509.8	510.0	510.1	510.3	510.5	510.8
155°	527.4	527.4	527.4	527.4	527.4	527.5	527.6	527.7	527.8	527.9	528.3
157.5°	543.8	543.6	543.3	543.2	542.9	542.8	542.9	543.1	543.2	543.2	543.6
160°	553.5	553.2	552.9	552.5	552.2	552.1	552.2	552.4	552.4	552.5	552.9
162.5°	562.1	561.8	561.6	561.3	561.1	561.0	561.0	561.1	561.1	561.1	561.6
165°	573.5	573.2	573.1	572.8	572.7	572.6	572.7	572.8	572.9	573.0	573.4
167.5°	583.2	582.8	582.3	581.9	581.5	581.3	581.3	581.3	581.3	581.3	581.9
170°	588.3	587.9	587.5	587.1	586.7	586.5	586.5	586.5	586.5	586.5	587.1
172.5°	592.1	591.7	591.3	590.8	590.4	590.2	590.2	590.2	590.2	590.2	590.8
175°	596.2	595.8	595.4	595.0	594.6	594.4	594.4	594.4	594.4	594.4	595.0
177.5°	598.4	598.1	597.8	597.5	597.0	596.9	596.8	596.7	596.6	596.6	597.0
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7



TEST NUMBER: P333620-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1677.3	1679.6	1681.9	1682.9	1682.7	1682.5	1682.2	1682.0
5°	1667.0	1669.9	1672.7	1673.8	1673.2	1672.7	1672.1	1671.5
7.5°	1646.3	1648.3	1650.2	1650.9	1650.2	1649.7	1649.0	1648.5
10°	1628.7	1629.6	1630.4	1630.4	1629.6	1628.7	1627.9	1627.1
12.5°	1603.9	1604.5	1605.2	1604.8	1603.5	1602.2	1600.9	1599.6
15°	1562.9	1562.7	1562.4	1561.0	1558.4	1555.9	1553.3	1550.8
17.5°	1511.9	1510.4	1509.0	1507.3	1505.2	1503.1	1501.0	1498.9
20°	1474.2	1472.8	1471.5	1469.4	1466.9	1464.4	1461.8	1459.3
22.5°	1437.0	1434.2	1431.4	1429.0	1426.9	1424.8	1422.7	1420.7
25°	1375.7	1372.0	1368.3	1364.9	1361.8	1358.7	1355.6	1352.5
27.5°	1309.5	1304.3	1299.2	1295.1	1292.1	1289.1	1286.1	1283.1
30°	1262.0	1255.5	1249.0	1244.5	1241.9	1239.3	1236.8	1234.3
32.5°	1215.9	1208.7	1201.5	1196.3	1193.1	1189.8	1186.7	1183.4
35°	1144.2	1136.0	1127.8	1121.7	1117.8	1113.8	1109.9	1105.9
37.5°	1069.2	1059.4	1049.5	1042.7	1038.9	1035.0	1031.2	1027.4
40°	1019.6	1008.9	998.2	991.1	987.7	984.3	980.9	977.5
42.5°	970.7	960.4	950.1	942.5	937.5	932.5	927.6	922.6
45°	892.6	881.3	870.0	862.3	858.0	853.8	849.5	845.3
47.5°	815.5	803.8	792.1	784.0	779.3	774.6	769.9	765.2
50°	763.1	751.2	739.4	731.3	727.1	722.8	718.6	714.4
52.5°	713.5	700.7	687.9	679.5	675.2	671.0	666.8	662.5
55°	638.1	625.4	612.7	604.1	599.6	595.0	590.5	586.0
57.5°	562.6	550.2	537.8	529.6	525.5	521.5	517.6	513.6
60°	512.8	500.4	488.0	479.6	475.4	471.2	466.9	462.7
62.5°	463.8	452.2	440.8	432.8	428.6	424.4	420.1	415.9
65°	391.8	380.5	369.2	361.4	357.2	352.9	348.7	344.5
67.5°	323.0	312.7	302.4	295.5	292.1	288.7	285.4	281.9
70°	277.4	268.6	259.9	253.8	250.4	247.0	243.6	240.3
72.5°	235.1	227.0	218.8	213.7	211.4	209.2	206.9	204.6
75°	175.7	169.5	163.3	159.1	157.2	155.2	153.3	151.2
77.5°	125.0	120.7	116.3	113.4	111.9	110.5	109.0	107.5
80°	94.1	91.6	88.9	87.4	86.8	86.3	85.8	85.2
82.5°	70.4	69.1	68.0	67.2	66.9	66.5	66.2	65.9
85°	40.1	39.9	39.5	39.3	39.0	38.7	38.4	38.2
87.5°	17.0	17.0	17.1	17.1	17.0	16.8	16.6	16.5
90°	8.5	9.0	9.5	9.9	10.3	10.5	10.8	11.2
92.5°	19.2	19.9	20.6	21.0	21.3	21.5	21.7	21.9
95°	37.3	38.0	38.7	39.1	39.4	39.6	39.8	40.0
97.5°	58.4	59.1	59.8	60.2	60.3	60.4	60.5	60.7
100°	73.1	73.9	74.8	75.4	75.7	75.9	76.1	76.3
102.5°	88.1	89.1	90.1	90.7	91.1	91.3	91.6	91.9
105°	112.4	113.0	113.7	114.1	114.4	114.7	115.0	115.4
107.5°	138.7	139.0	139.3	139.4	139.4	139.4	139.3	139.3
110°	156.9	157.2	157.5	157.6	157.5	157.4	157.3	157.2





TEST NUMBER: P333620-930

CATALOG NUMBER: S125RDIP-S1270D590U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	175.2	175.3	175.5	175.5	175.3	175.0	174.9	174.7
115°	203.0	202.9	202.8	202.8	202.6	202.5	202.4	202.4
117.5°	231.0	231.1	231.1	231.0	230.6	230.2	229.8	229.3
120°	249.7	249.7	249.7	249.6	249.2	248.7	248.3	247.9
122.5°	268.2	268.2	268.1	267.8	267.5	267.2	266.8	266.5
125°	295.4	295.2	295.0	294.8	294.7	294.6	294.5	294.4
127.5°	322.4	322.3	322.2	322.0	321.8	321.6	321.4	321.2
130°	340.2	340.1	340.1	339.9	339.7	339.5	339.2	339.1
132.5°	357.3	357.3	357.2	356.9	356.7	356.4	356.1	355.8
135°	383.7	383.7	383.7	383.5	383.1	382.7	382.3	381.9
137.5°	409.4	409.4	409.6	409.4	408.9	408.4	407.9	407.3
140°	425.5	425.7	425.9	425.7	425.3	424.8	424.2	423.7
142.5°	441.3	441.5	441.6	441.4	440.9	440.3	439.9	439.4
145°	464.1	464.1	464.1	464.0	463.7	463.4	463.1	462.8
147.5°	485.3	485.6	485.8	485.6	484.9	484.2	483.5	482.8
150°	498.6	498.6	498.6	498.5	498.3	498.1	497.9	497.7
152.5°	511.0	511.3	511.5	511.4	511.0	510.7	510.3	510.0
155°	528.7	529.1	529.5	529.5	529.0	528.5	527.9	527.4
157.5°	544.0	544.5	544.9	544.8	544.0	543.4	542.7	542.0
160°	553.3	553.8	554.2	554.2	553.7	553.1	552.6	552.1
162.5°	562.1	562.6	563.1	563.0	562.5	561.8	561.3	560.6
165°	573.8	574.2	574.7	574.5	574.0	573.3	572.7	572.1
167.5°	582.5	583.2	583.8	583.8	583.1	582.4	581.8	581.2
170°	587.7	588.3	589.0	588.9	588.2	587.5	586.8	586.0
172.5°	591.5	592.1	592.7	592.7	592.1	591.4	590.8	590.1
175°	595.7	596.2	596.9	596.8	596.1	595.4	594.7	593.9
177.5°	597.5	598.0	598.5	598.5	597.9	597.4	596.7	596.1
180°	597.7	597.7	597.7	597.7	597.7	597.7	597.7	597.7

(END OF REPORT)