

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333622-930

Luminaire Tested: **S125RDIP-S1270D810U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333622-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U930-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6654.1 lumens  
Efficiency: N/A  
Efficacy: 109.6 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	60
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	58	56	52
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48	44
3	84	75	68	62	79	70	64	59	62	57	53	54	50	47	47	44	42	38
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	42	39	36	33
5	71	60	51	46	66	56	49	44	50	44	39	44	39	36	38	35	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	31	35	31	28	25
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	32	28	25	23
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22	20
9	53	40	33	28	49	38	31	27	34	29	25	30	26	22	27	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	2.2
10°-20°	435.1	6.5
20°-30°	689.8	10.4
30°-40°	831.9	12.5
40°-50°	742.9	11.2
50°-60°	569.7	8.6
60°-70°	370.2	5.6
70°-80°	180.0	2.7
80°-90°	44.8	0.7
90°-100°	31.3	0.5
100°-110°	192.6	2.9
110°-120°	349.4	5.3
120°-130°	448.4	6.7
130°-140°	482.3	7.2
140°-150°	452.7	6.8
150°-160°	366.2	5.5
160°-170°	236.8	3.6
170°-180°	81.7	1.2
0°-30°	1273.4	19.1
0°-40°	2105.3	31.6
0°-60°	3417.9	51.4
0°-90°	4012.8	60.3
90°-120°	573.3	8.6
90°-150°	1956.6	29.4
90°-180°	2641.0	39.7
0°-180°	6654.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	15	1	15	1	15	8
95°	13	36	13	36	13	11
105°	189	187	189	187	189	171
115°	349	352	349	352	349	347
125°	500	500	500	500	500	445
135°	622	624	622	624	622	480
145°	722	724	722	724	722	451
155°	791	797	791	797	791	365
165°	836	841	836	841	836	236
175°	856	860	856	860	856	81
180°	860	860	860	860	860	



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	14.3	13.6	13.0	13.0	13.4	14.3	13.6	13.0	12.9	12.7	13.0
90°	15.3	14.8	14.4	14.0	13.6	13.0	12.3	11.7	10.9	10.2	9.2
92.5°	14.3	14.1	13.9	13.7	13.5	13.0	12.3	11.7	10.9	10.2	9.3
95°	13.4	13.4	13.4	13.4	13.4	13.0	12.3	11.7	10.9	10.2	15.6
97.5°	13.4	13.4	13.4	13.4	13.4	15.4	19.4	23.4	27.4	31.4	42.0
100°	13.4	13.9	14.5	15.1	15.7	26.5	47.6	68.7	89.8	111.0	110.4
102.5°	80.2	89.8	99.5	109.1	118.8	125.6	129.6	133.5	137.5	141.5	141.2
105°	189.4	189.5	189.6	189.8	190.0	190.0	190.0	190.0	190.0	190.0	190.0
107.5°	238.7	239.1	239.5	240.0	240.4	240.6	240.6	240.6	240.5	240.5	240.2
110°	272.9	272.7	272.6	272.5	272.3	272.5	272.9	273.3	273.8	274.2	273.9



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	303.5	303.7	303.9	304.1	304.3	304.7	305.2	305.7	306.3	306.8	306.6
115°	349.4	350.3	351.1	352.0	352.8	353.5	354.1	354.7	355.2	355.8	355.6
117.5°	398.4	398.8	399.1	399.5	399.8	400.4	401.1	401.9	402.6	403.3	402.8
120°	428.4	429.2	429.9	430.6	431.3	431.8	432.1	432.4	432.7	432.9	432.5
122.5°	457.1	457.9	458.7	459.5	460.3	460.9	461.1	461.5	461.7	462.0	461.8
125°	500.5	500.9	501.3	501.8	502.2	502.7	503.3	503.9	504.4	505.0	505.0
127.5°	537.1	538.2	539.2	540.3	541.3	542.0	542.3	542.6	542.9	543.2	543.3
130°	563.6	564.4	565.1	565.7	566.5	567.0	567.4	567.9	568.3	568.8	568.6
132.5°	588.2	588.8	589.5	590.3	590.9	591.3	591.4	591.5	591.6	591.7	592.0
135°	621.7	622.5	623.4	624.2	625.1	625.7	625.9	626.2	626.5	626.8	627.0
137.5°	655.3	656.1	656.8	657.5	658.3	658.6	658.5	658.5	658.4	658.4	658.7
140°	675.2	676.0	676.9	677.8	678.7	678.9	678.7	678.3	678.1	677.8	677.9
142.5°	694.1	695.0	695.8	696.7	697.5	697.9	697.8	697.8	697.7	697.7	697.5
145°	721.8	722.6	723.5	724.3	725.1	725.5	725.4	725.2	725.1	725.0	725.0
147.5°	744.6	745.6	746.7	747.6	748.7	749.1	748.9	748.8	748.6	748.4	748.3
150°	759.4	760.5	761.7	762.8	763.9	764.3	764.1	763.8	763.5	763.2	763.0
152.5°	773.1	774.2	775.2	776.2	777.2	777.6	777.3	777.1	776.7	776.5	776.2
155°	791.2	792.4	793.5	794.7	795.8	796.1	795.7	795.3	794.8	794.4	794.2
157.5°	806.4	807.6	808.7	809.8	811.0	811.3	810.9	810.4	809.9	809.5	809.4
160°	816.1	817.3	818.4	819.5	820.7	820.9	820.4	819.8	819.2	818.6	818.6
162.5°	824.8	826.1	827.3	828.5	829.8	830.0	829.2	828.4	827.6	826.9	826.7
165°	836.5	837.6	838.8	839.9	841.1	841.2	840.3	839.5	838.7	837.8	837.6
167.5°	844.7	846.0	847.3	848.5	849.8	849.9	848.9	847.9	846.9	845.9	845.7
170°	849.3	850.5	851.8	853.1	854.4	854.4	853.3	852.2	851.1	849.9	849.8
172.5°	852.3	853.6	854.9	856.1	857.5	857.6	856.6	855.5	854.5	853.5	853.2
175°	856.3	857.6	858.8	860.1	861.4	861.4	860.3	859.2	858.1	857.0	856.8
177.5°	858.6	859.5	860.4	861.3	862.3	862.3	861.4	860.7	859.9	859.1	859.0
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	13.4	13.1	13.5	13.2	12.5	14.8	16.1	16.4	15.6	14.8	14.0
90°	8.2	7.3	6.2	5.1	4.1	2.9	1.8	0.7	1.8	2.9	4.1
92.5°	8.5	7.6	6.7	6.7	7.4	8.2	9.0	9.8	9.0	8.2	7.4
95°	21.0	26.3	31.7	34.7	35.1	35.5	36.0	36.4	36.0	35.5	35.1
97.5°	52.7	63.3	74.0	78.9	78.2	77.4	76.6	75.9	76.6	77.4	78.2
100°	109.8	109.3	108.7	108.2	107.8	107.3	106.9	106.5	106.9	107.3	107.8
102.5°	140.9	140.6	140.1	139.7	139.2	138.7	138.1	137.6	138.1	138.7	139.2
105°	190.0	190.0	190.0	189.7	189.1	188.6	188.0	187.4	188.0	188.6	189.1
107.5°	239.9	239.6	239.4	239.2	239.2	239.2	239.2	239.2	239.2	239.2	239.2
110°	273.6	273.3	273.0	272.9	272.9	272.9	272.9	272.9	272.9	272.9	272.9





TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	306.5	306.3	306.1	305.9	305.6	305.2	304.8	304.5	304.8	305.2	305.6
115°	355.5	355.4	355.2	354.8	354.1	353.4	352.7	352.0	352.7	353.4	354.1
117.5°	402.3	401.7	401.2	401.0	401.0	401.0	401.0	401.0	401.0	401.0	401.0
120°	432.1	431.6	431.2	431.0	431.2	431.4	431.5	431.6	431.5	431.4	431.2
122.5°	461.6	461.4	461.2	460.8	460.3	459.7	459.3	458.7	459.3	459.7	460.3
125°	505.0	505.0	505.0	504.5	503.5	502.5	501.5	500.5	501.5	502.5	503.5
127.5°	543.4	543.5	543.6	543.2	542.6	541.8	541.1	540.5	541.1	541.8	542.6
130°	568.4	568.3	568.2	567.8	567.0	566.3	565.7	564.9	565.7	566.3	567.0
132.5°	592.3	592.6	593.0	592.7	591.8	591.0	590.2	589.4	590.2	591.0	591.8
135°	627.3	627.6	627.9	627.6	626.8	625.9	625.1	624.2	625.1	625.9	626.8
137.5°	658.9	659.2	659.4	659.2	658.4	657.7	657.0	656.2	657.0	657.7	658.4
140°	678.1	678.2	678.3	678.2	678.0	677.7	677.4	677.1	677.4	677.7	678.0
142.5°	697.2	697.1	696.8	696.7	696.5	696.3	696.2	696.0	696.2	696.3	696.5
145°	725.0	725.0	725.0	724.8	724.6	724.2	724.0	723.7	724.0	724.2	724.6
147.5°	748.0	747.9	747.7	747.7	747.7	747.8	747.9	747.9	747.9	747.8	747.7
150°	762.6	762.4	762.1	762.1	762.4	762.6	763.0	763.2	763.0	762.6	762.4
152.5°	775.9	775.6	775.3	775.5	776.2	776.7	777.4	778.0	777.4	776.7	776.2
155°	793.9	793.6	793.3	793.6	794.4	795.3	796.1	797.0	796.1	795.3	794.4
157.5°	809.4	809.4	809.3	809.6	810.2	810.7	811.1	811.6	811.1	810.7	810.2
160°	818.4	818.2	818.2	818.5	819.3	820.2	821.0	821.9	821.0	820.2	819.3
162.5°	826.6	826.4	826.3	826.6	827.4	828.3	829.2	830.1	829.2	828.3	827.4
165°	837.6	837.4	837.2	837.6	838.5	839.3	840.2	841.0	840.2	839.3	838.5
167.5°	845.5	845.4	845.3	845.6	846.5	847.4	848.3	849.1	848.3	847.4	846.5
170°	849.6	849.5	849.4	849.8	850.8	851.7	852.7	853.8	852.7	851.7	850.8
172.5°	853.0	852.7	852.5	852.8	853.9	854.8	855.8	856.8	855.8	854.8	853.9
175°	856.6	856.5	856.4	856.7	857.6	858.4	859.2	860.1	859.2	858.4	857.6
177.5°	858.8	858.8	858.7	858.9	859.7	860.3	861.0	861.7	861.0	860.3	859.7
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	13.8	13.9	13.6	14.8	13.5	14.3	14.3	14.0	14.2	14.3	13.9
90°	5.1	6.2	7.3	8.2	9.2	10.2	10.9	11.7	12.3	13.0	13.6
92.5°	6.7	6.7	7.6	8.5	9.3	10.2	10.9	11.7	12.3	13.0	13.5
95°	34.7	31.7	26.3	21.0	15.6	10.2	10.9	11.7	12.3	13.0	13.4
97.5°	78.9	74.0	63.3	52.7	42.0	31.4	27.4	23.4	19.4	15.4	13.4
100°	108.2	108.7	109.3	109.8	110.4	111.0	89.8	68.7	47.6	26.5	15.7
102.5°	139.7	140.1	140.6	140.9	141.2	141.5	137.5	133.5	129.6	125.6	118.8
105°	189.7	190.0	190.0	190.0	190.0	190.0	190.0	190.0	190.0	190.0	190.0
107.5°	239.2	239.4	239.6	239.9	240.2	240.5	240.5	240.6	240.6	240.6	240.4
110°	272.9	273.0	273.3	273.6	273.9	274.2	273.8	273.3	272.9	272.5	272.3



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	305.9	306.1	306.3	306.5	306.6	306.8	306.3	305.7	305.2	304.7	304.3
115°	354.8	355.2	355.4	355.5	355.6	355.8	355.2	354.7	354.1	353.5	352.8
117.5°	401.0	401.2	401.7	402.3	402.8	403.3	402.6	401.9	401.1	400.4	399.8
120°	431.0	431.2	431.6	432.1	432.5	432.9	432.7	432.4	432.1	431.8	431.3
122.5°	460.8	461.2	461.4	461.6	461.8	462.0	461.7	461.5	461.1	460.9	460.3
125°	504.5	505.0	505.0	505.0	505.0	505.0	504.4	503.9	503.3	502.7	502.2
127.5°	543.2	543.6	543.5	543.4	543.3	543.2	542.9	542.6	542.3	542.0	541.3
130°	567.8	568.2	568.3	568.4	568.6	568.8	568.3	567.9	567.4	567.0	566.5
132.5°	592.7	593.0	592.6	592.3	592.0	591.7	591.6	591.5	591.4	591.3	590.9
135°	627.6	627.9	627.6	627.3	627.0	626.8	626.5	626.2	625.9	625.7	625.1
137.5°	659.2	659.4	659.2	658.9	658.7	658.4	658.4	658.5	658.5	658.6	658.3
140°	678.2	678.3	678.2	678.1	677.9	677.8	678.1	678.3	678.7	678.9	678.7
142.5°	696.7	696.8	697.1	697.2	697.5	697.7	697.7	697.8	697.8	697.9	697.5
145°	724.8	725.0	725.0	725.0	725.0	725.0	725.1	725.2	725.4	725.5	725.1
147.5°	747.7	747.7	747.9	748.0	748.3	748.4	748.6	748.8	748.9	749.1	748.7
150°	762.1	762.1	762.4	762.6	763.0	763.2	763.5	763.8	764.1	764.3	763.9
152.5°	775.5	775.3	775.6	775.9	776.2	776.5	776.7	777.1	777.3	777.6	777.2
155°	793.6	793.3	793.6	793.9	794.2	794.4	794.8	795.3	795.7	796.1	795.8
157.5°	809.6	809.3	809.4	809.4	809.4	809.5	809.9	810.4	810.9	811.3	811.0
160°	818.5	818.2	818.2	818.4	818.6	818.6	819.2	819.8	820.4	820.9	820.7
162.5°	826.6	826.3	826.4	826.6	826.7	826.9	827.6	828.4	829.2	830.0	829.8
165°	837.6	837.2	837.4	837.6	837.6	837.8	838.7	839.5	840.3	841.2	841.1
167.5°	845.6	845.3	845.4	845.5	845.7	845.9	846.9	847.9	848.9	849.9	849.8
170°	849.8	849.4	849.5	849.6	849.8	849.9	851.1	852.2	853.3	854.4	854.4
172.5°	852.8	852.5	852.7	853.0	853.2	853.5	854.5	855.5	856.6	857.6	857.5
175°	856.7	856.4	856.5	856.6	856.8	857.0	858.1	859.2	860.3	861.4	861.4
177.5°	858.9	858.7	858.8	858.8	859.0	859.1	859.9	860.7	861.4	862.3	862.3
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	14.5	14.1	14.2	14.3	14.2	14.1	14.5	13.9	14.3	14.2	14.0
90°	14.0	14.4	14.8	15.3	14.8	14.4	14.0	13.6	13.0	12.3	11.7
92.5°	13.7	13.9	14.1	14.3	14.1	13.9	13.7	13.5	13.0	12.3	11.7
95°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.0	12.3	11.7
97.5°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	15.4	19.4	23.4
100°	15.1	14.5	13.9	13.4	13.9	14.5	15.1	15.7	26.5	47.6	68.7
102.5°	109.1	99.5	89.8	80.2	89.8	99.5	109.1	118.8	125.6	129.6	133.5
105°	189.8	189.6	189.5	189.4	189.5	189.6	189.8	190.0	190.0	190.0	190.0
107.5°	240.0	239.5	239.1	238.7	239.1	239.5	240.0	240.4	240.6	240.6	240.6
110°	272.5	272.6	272.7	272.9	272.7	272.6	272.5	272.3	272.5	272.9	273.3



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	304.1	303.9	303.7	303.5	303.7	303.9	304.1	304.3	304.7	305.2	305.7
115°	352.0	351.1	350.3	349.4	350.3	351.1	352.0	352.8	353.5	354.1	354.7
117.5°	399.5	399.1	398.8	398.4	398.8	399.1	399.5	399.8	400.4	401.1	401.9
120°	430.6	429.9	429.2	428.4	429.2	429.9	430.6	431.3	431.8	432.1	432.4
122.5°	459.5	458.7	457.9	457.1	457.9	458.7	459.5	460.3	460.9	461.1	461.5
125°	501.8	501.3	500.9	500.5	500.9	501.3	501.8	502.2	502.7	503.3	503.9
127.5°	540.3	539.2	538.2	537.1	538.2	539.2	540.3	541.3	542.0	542.3	542.6
130°	565.7	565.1	564.4	563.6	564.4	565.1	565.7	566.5	567.0	567.4	567.9
132.5°	590.3	589.5	588.8	588.2	588.8	589.5	590.3	590.9	591.3	591.4	591.5
135°	624.2	623.4	622.5	621.7	622.5	623.4	624.2	625.1	625.7	625.9	626.2
137.5°	657.5	656.8	656.1	655.3	656.1	656.8	657.5	658.3	658.6	658.5	658.5
140°	677.8	676.9	676.0	675.2	676.0	676.9	677.8	678.7	678.9	678.7	678.3
142.5°	696.7	695.8	695.0	694.1	695.0	695.8	696.7	697.5	697.9	697.8	697.8
145°	724.3	723.5	722.6	721.8	722.6	723.5	724.3	725.1	725.5	725.4	725.2
147.5°	747.6	746.7	745.6	744.6	745.6	746.7	747.6	748.7	749.1	748.9	748.8
150°	762.8	761.7	760.5	759.4	760.5	761.7	762.8	763.9	764.3	764.1	763.8
152.5°	776.2	775.2	774.2	773.1	774.2	775.2	776.2	777.2	777.6	777.3	777.1
155°	794.7	793.5	792.4	791.2	792.4	793.5	794.7	795.8	796.1	795.7	795.3
157.5°	809.8	808.7	807.6	806.4	807.6	808.7	809.8	811.0	811.3	810.9	810.4
160°	819.5	818.4	817.3	816.1	817.3	818.4	819.5	820.7	820.9	820.4	819.8
162.5°	828.5	827.3	826.1	824.8	826.1	827.3	828.5	829.8	830.0	829.2	828.4
165°	839.9	838.8	837.6	836.5	837.6	838.8	839.9	841.1	841.2	840.3	839.5
167.5°	848.5	847.3	846.0	844.7	846.0	847.3	848.5	849.8	849.9	848.9	847.9
170°	853.1	851.8	850.5	849.3	850.5	851.8	853.1	854.4	854.4	853.3	852.2
172.5°	856.1	854.9	853.6	852.3	853.6	854.9	856.1	857.5	857.6	856.6	855.5
175°	860.1	858.8	857.6	856.3	857.6	858.8	860.1	861.4	861.4	860.3	859.2
177.5°	861.3	860.4	859.5	858.6	859.5	860.4	861.3	862.3	862.3	861.4	860.7
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	14.3	14.3	13.5	14.8	13.6	13.9	13.8	14.0	14.8	15.6	16.4
90°	10.9	10.2	9.2	8.2	7.3	6.2	5.1	4.1	2.9	1.8	0.7
92.5°	10.9	10.2	9.3	8.5	7.6	6.7	6.7	7.4	8.2	9.0	9.8
95°	10.9	10.2	15.6	21.0	26.3	31.7	34.7	35.1	35.5	36.0	36.4
97.5°	27.4	31.4	42.0	52.7	63.3	74.0	78.9	78.2	77.4	76.6	75.9
100°	89.8	111.0	110.4	109.8	109.3	108.7	108.2	107.8	107.3	106.9	106.5
102.5°	137.5	141.5	141.2	140.9	140.6	140.1	139.7	139.2	138.7	138.1	137.6
105°	190.0	190.0	190.0	190.0	190.0	190.0	189.7	189.1	188.6	188.0	187.4
107.5°	240.5	240.5	240.2	239.9	239.6	239.4	239.2	239.2	239.2	239.2	239.2
110°	273.8	274.2	273.9	273.6	273.3	273.0	272.9	272.9	272.9	272.9	272.9



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	306.3	306.8	306.6	306.5	306.3	306.1	305.9	305.6	305.2	304.8	304.5
115°	355.2	355.8	355.6	355.5	355.4	355.2	354.8	354.1	353.4	352.7	352.0
117.5°	402.6	403.3	402.8	402.3	401.7	401.2	401.0	401.0	401.0	401.0	401.0
120°	432.7	432.9	432.5	432.1	431.6	431.2	431.0	431.2	431.4	431.5	431.6
122.5°	461.7	462.0	461.8	461.6	461.4	461.2	460.8	460.3	459.7	459.3	458.7
125°	504.4	505.0	505.0	505.0	505.0	505.0	504.5	503.5	502.5	501.5	500.5
127.5°	542.9	543.2	543.3	543.4	543.5	543.6	543.2	542.6	541.8	541.1	540.5
130°	568.3	568.8	568.6	568.4	568.3	568.2	567.8	567.0	566.3	565.7	564.9
132.5°	591.6	591.7	592.0	592.3	592.6	593.0	592.7	591.8	591.0	590.2	589.4
135°	626.5	626.8	627.0	627.3	627.6	627.9	627.6	626.8	625.9	625.1	624.2
137.5°	658.4	658.4	658.7	658.9	659.2	659.4	659.2	658.4	657.7	657.0	656.2
140°	678.1	677.8	677.9	678.1	678.2	678.3	678.2	678.0	677.7	677.4	677.1
142.5°	697.7	697.7	697.5	697.2	697.1	696.8	696.7	696.5	696.3	696.2	696.0
145°	725.1	725.0	725.0	725.0	725.0	725.0	724.8	724.6	724.2	724.0	723.7
147.5°	748.6	748.4	748.3	748.0	747.9	747.7	747.7	747.7	747.8	747.9	747.9
150°	763.5	763.2	763.0	762.6	762.4	762.1	762.1	762.4	762.6	763.0	763.2
152.5°	776.7	776.5	776.2	775.9	775.6	775.3	775.5	776.2	776.7	777.4	778.0
155°	794.8	794.4	794.2	793.9	793.6	793.3	793.6	794.4	795.3	796.1	797.0
157.5°	809.9	809.5	809.4	809.4	809.4	809.3	809.6	810.2	810.7	811.1	811.6
160°	819.2	818.6	818.6	818.4	818.2	818.2	818.5	819.3	820.2	821.0	821.9
162.5°	827.6	826.9	826.7	826.6	826.4	826.3	826.6	827.4	828.3	829.2	830.1
165°	838.7	837.8	837.6	837.6	837.4	837.2	837.6	838.5	839.3	840.2	841.0
167.5°	846.9	845.9	845.7	845.5	845.4	845.3	845.6	846.5	847.4	848.3	849.1
170°	851.1	849.9	849.8	849.6	849.5	849.4	849.8	850.8	851.7	852.7	853.8
172.5°	854.5	853.5	853.2	853.0	852.7	852.5	852.8	853.9	854.8	855.8	856.8
175°	858.1	857.0	856.8	856.6	856.5	856.4	856.7	857.6	858.4	859.2	860.1
177.5°	859.9	859.1	859.0	858.8	858.8	858.7	858.9	859.7	860.3	861.0	861.7
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.1	14.8	12.5	13.2	13.5	13.1	13.4	13.0	12.7	12.9	13.0
90°	1.8	2.9	4.1	5.1	6.2	7.3	8.2	9.2	10.2	10.9	11.7
92.5°	9.0	8.2	7.4	6.7	6.7	7.6	8.5	9.3	10.2	10.9	11.7
95°	36.0	35.5	35.1	34.7	31.7	26.3	21.0	15.6	10.2	10.9	11.7
97.5°	76.6	77.4	78.2	78.9	74.0	63.3	52.7	42.0	31.4	27.4	23.4
100°	106.9	107.3	107.8	108.2	108.7	109.3	109.8	110.4	111.0	89.8	68.7
102.5°	138.1	138.7	139.2	139.7	140.1	140.6	140.9	141.2	141.5	137.5	133.5
105°	188.0	188.6	189.1	189.7	190.0	190.0	190.0	190.0	190.0	190.0	190.0
107.5°	239.2	239.2	239.2	239.2	239.4	239.6	239.9	240.2	240.5	240.5	240.6
110°	272.9	272.9	272.9	272.9	273.0	273.3	273.6	273.9	274.2	273.8	273.3





TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	304.8	305.2	305.6	305.9	306.1	306.3	306.5	306.6	306.8	306.3	305.7
115°	352.7	353.4	354.1	354.8	355.2	355.4	355.5	355.6	355.8	355.2	354.7
117.5°	401.0	401.0	401.0	401.0	401.2	401.7	402.3	402.8	403.3	402.6	401.9
120°	431.5	431.4	431.2	431.0	431.2	431.6	432.1	432.5	432.9	432.7	432.4
122.5°	459.3	459.7	460.3	460.8	461.2	461.4	461.6	461.8	462.0	461.7	461.5
125°	501.5	502.5	503.5	504.5	505.0	505.0	505.0	505.0	505.0	504.4	503.9
127.5°	541.1	541.8	542.6	543.2	543.6	543.5	543.4	543.3	543.2	542.9	542.6
130°	565.7	566.3	567.0	567.8	568.2	568.3	568.4	568.6	568.8	568.3	567.9
132.5°	590.2	591.0	591.8	592.7	593.0	592.6	592.3	592.0	591.7	591.6	591.5
135°	625.1	625.9	626.8	627.6	627.9	627.6	627.3	627.0	626.8	626.5	626.2
137.5°	657.0	657.7	658.4	659.2	659.4	659.2	658.9	658.7	658.4	658.4	658.5
140°	677.4	677.7	678.0	678.2	678.3	678.2	678.1	677.9	677.8	678.1	678.3
142.5°	696.2	696.3	696.5	696.7	696.8	697.1	697.2	697.5	697.7	697.7	697.8
145°	724.0	724.2	724.6	724.8	725.0	725.0	725.0	725.0	725.0	725.1	725.2
147.5°	747.9	747.8	747.7	747.7	747.7	747.9	748.0	748.3	748.4	748.6	748.8
150°	763.0	762.6	762.4	762.1	762.1	762.4	762.6	763.0	763.2	763.5	763.8
152.5°	777.4	776.7	776.2	775.5	775.3	775.6	775.9	776.2	776.5	776.7	777.1
155°	796.1	795.3	794.4	793.6	793.3	793.6	793.9	794.2	794.4	794.8	795.3
157.5°	811.1	810.7	810.2	809.6	809.3	809.4	809.4	809.4	809.5	809.9	810.4
160°	821.0	820.2	819.3	818.5	818.2	818.2	818.4	818.6	818.6	819.2	819.8
162.5°	829.2	828.3	827.4	826.6	826.3	826.4	826.6	826.7	826.9	827.6	828.4
165°	840.2	839.3	838.5	837.6	837.2	837.4	837.6	837.6	837.8	838.7	839.5
167.5°	848.3	847.4	846.5	845.6	845.3	845.4	845.5	845.7	845.9	846.9	847.9
170°	852.7	851.7	850.8	849.8	849.4	849.5	849.6	849.8	849.9	851.1	852.2
172.5°	855.8	854.8	853.9	852.8	852.5	852.7	853.0	853.2	853.5	854.5	855.5
175°	859.2	858.4	857.6	856.7	856.4	856.5	856.6	856.8	857.0	858.1	859.2
177.5°	861.0	860.3	859.7	858.9	858.7	858.8	858.8	859.0	859.1	859.9	860.7
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1	860.1



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	13.6	14.3	13.4	13.0	13.0	13.6	14.3
90°	12.3	13.0	13.6	14.0	14.4	14.8	15.3
92.5°	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	47.6	26.5	15.7	15.1	14.5	13.9	13.4
102.5°	129.6	125.6	118.8	109.1	99.5	89.8	80.2
105°	190.0	190.0	190.0	189.8	189.6	189.5	189.4
107.5°	240.6	240.6	240.4	240.0	239.5	239.1	238.7
110°	272.9	272.5	272.3	272.5	272.6	272.7	272.9



TEST NUMBER: P333622-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	305.2	304.7	304.3	304.1	303.9	303.7	303.5
115°	354.1	353.5	352.8	352.0	351.1	350.3	349.4
117.5°	401.1	400.4	399.8	399.5	399.1	398.8	398.4
120°	432.1	431.8	431.3	430.6	429.9	429.2	428.4
122.5°	461.1	460.9	460.3	459.5	458.7	457.9	457.1
125°	503.3	502.7	502.2	501.8	501.3	500.9	500.5
127.5°	542.3	542.0	541.3	540.3	539.2	538.2	537.1
130°	567.4	567.0	566.5	565.7	565.1	564.4	563.6
132.5°	591.4	591.3	590.9	590.3	589.5	588.8	588.2
135°	625.9	625.7	625.1	624.2	623.4	622.5	621.7
137.5°	658.5	658.6	658.3	657.5	656.8	656.1	655.3
140°	678.7	678.9	678.7	677.8	676.9	676.0	675.2
142.5°	697.8	697.9	697.5	696.7	695.8	695.0	694.1
145°	725.4	725.5	725.1	724.3	723.5	722.6	721.8
147.5°	748.9	749.1	748.7	747.6	746.7	745.6	744.6
150°	764.1	764.3	763.9	762.8	761.7	760.5	759.4
152.5°	777.3	777.6	777.2	776.2	775.2	774.2	773.1
155°	795.7	796.1	795.8	794.7	793.5	792.4	791.2
157.5°	810.9	811.3	811.0	809.8	808.7	807.6	806.4
160°	820.4	820.9	820.7	819.5	818.4	817.3	816.1
162.5°	829.2	830.0	829.8	828.5	827.3	826.1	824.8
165°	840.3	841.2	841.1	839.9	838.8	837.6	836.5
167.5°	848.9	849.9	849.8	848.5	847.3	846.0	844.7
170°	853.3	854.4	854.4	853.1	851.8	850.5	849.3
172.5°	856.6	857.6	857.5	856.1	854.9	853.6	852.3
175°	860.3	861.4	861.4	860.1	858.8	857.6	856.3
177.5°	861.4	862.3	862.3	861.3	860.4	859.5	858.6
180°	860.1	860.1	860.1	860.1	860.1	860.1	860.1

(END OF REPORT)