

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333624-930

Luminaire Tested: **S125RDIP-S1270D810U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333624-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S1270D810U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6384.0 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 60.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	70	68	67	61	60	58	54
2	93	85	79	74	87	80	75	71	71	67	63	62	59	57	54	52	50	46
3	85	75	68	62	79	71	65	60	63	58	54	55	52	48	48	46	43	40
4	78	67	59	53	73	63	56	51	56	51	46	50	45	42	44	40	37	34
5	72	60	52	46	67	57	49	44	51	45	40	45	40	36	39	36	33	30
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	45	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	2.3
10°-20°	435.1	6.8
20°-30°	689.8	10.8
30°-40°	831.9	13.0
40°-50°	742.9	11.6
50°-60°	569.7	8.9
60°-70°	370.2	5.8
70°-80°	180.0	2.8
80°-90°	44.7	0.7
90°-100°	229.2	3.6
100°-110°	492.7	7.7
110°-120°	462.4	7.2
120°-130°	374.7	5.9
130°-140°	300.7	4.7
140°-150°	226.9	3.6
150°-160°	159.7	2.5
160°-170°	94.2	1.5
170°-180°	30.6	0.5
0°-30°	1273.4	19.9
0°-40°	2105.3	33.0
0°-60°	3417.9	53.5
0°-90°	4012.8	62.9
90°-120°	1184.3	18.6
90°-150°	2086.6	32.7
90°-180°	2371.0	37.1
0°-180°	6384.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	15	1	15	1	15	12
95°	150	21	150	21	150	212
105°	845	72	845	72	845	840
115°	941	129	941	129	941	919
125°	741	178	741	178	741	671
135°	616	209	616	209	616	477
145°	486	244	486	244	486	309
155°	407	278	407	278	407	190
165°	357	304	357	304	357	102
175°	321	316	321	316	321	31
180°	316	316	316	316	316	



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	14.1	13.6	13.0	13.0	13.5	14.3	13.6	13.0	12.9	12.7	13.0
90°	14.7	14.7	14.0	14.0	14.0	12.7	12.1	11.5	10.8	10.2	8.9
92.5°	40.7	41.7	42.6	44.1	52.3	61.7	82.0	113.0	166.4	205.5	208.8
95°	149.8	160.0	165.1	184.3	229.5	283.1	361.4	458.4	552.7	564.8	460.9
97.5°	362.1	370.2	388.7	424.4	463.8	538.3	614.7	682.7	699.3	603.2	411.6
100°	497.3	507.4	531.0	576.9	620.9	687.2	752.8	784.1	735.0	575.7	367.2
102.5°	648.2	655.8	681.4	714.1	761.2	806.0	837.6	818.2	713.6	527.2	333.5
105°	844.7	852.3	865.0	886.1	906.5	913.5	885.5	798.1	645.1	462.2	300.9
107.5°	948.9	954.1	958.2	958.4	948.0	914.8	842.8	726.2	575.3	417.4	287.1
110°	983.7	983.7	979.2	967.0	938.3	884.2	794.3	673.2	535.5	396.5	283.1



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	979.6	974.9	963.8	943.1	901.2	837.2	746.3	631.4	505.9	384.3	283.1
115°	940.9	932.6	914.8	884.2	834.5	765.0	677.7	578.9	473.6	371.0	284.9
117.5°	873.2	868.1	850.4	818.8	769.1	705.3	630.1	544.9	454.4	364.5	289.2
120°	829.3	824.3	807.1	776.4	729.3	673.2	603.1	526.5	443.7	361.4	293.3
122.5°	790.6	786.0	768.8	740.8	698.7	646.1	583.7	512.8	434.5	358.9	296.8
125°	741.4	735.0	721.0	694.9	659.2	613.3	557.8	492.8	422.0	355.7	302.8
127.5°	699.3	696.5	683.2	660.1	627.8	584.8	533.0	472.4	410.5	354.2	309.6
130°	676.4	672.5	659.8	638.8	606.9	565.4	515.8	459.6	402.9	353.2	313.6
132.5°	653.4	649.1	637.3	616.3	584.4	544.5	499.4	446.9	396.8	353.2	318.2
135°	615.8	612.0	600.5	579.4	551.4	515.1	474.3	430.3	389.5	353.2	324.5
137.5°	575.7	571.4	560.8	541.8	516.6	485.8	451.8	416.3	383.0	353.9	330.2
140°	547.6	544.4	534.8	518.3	494.6	467.9	438.5	408.6	379.9	354.4	332.7
142.5°	521.5	518.9	509.9	495.9	475.8	452.6	427.4	402.0	377.4	355.0	334.3
145°	485.8	483.2	476.2	465.4	450.0	432.8	413.1	393.3	373.6	354.4	336.0
147.5°	455.4	454.3	450.2	441.5	429.4	416.4	401.2	385.1	369.6	352.8	336.6
150°	438.5	438.0	435.4	427.8	418.2	406.7	394.6	380.6	366.6	351.2	336.6
152.5°	425.3	424.7	422.2	416.0	408.0	399.1	388.0	375.4	363.0	349.2	336.1
155°	407.3	406.7	404.8	400.3	394.0	386.9	378.1	367.9	357.0	345.5	334.7
157.5°	391.3	391.4	389.6	386.0	381.0	375.4	368.6	360.2	351.4	341.7	333.0
160°	380.6	381.2	379.9	376.7	372.3	367.9	361.4	355.1	346.8	339.2	331.5
162.5°	370.9	371.0	370.7	368.1	364.6	360.7	355.3	349.4	342.7	336.1	330.0
165°	357.0	357.0	357.0	355.7	353.2	350.0	346.2	341.7	336.6	331.5	327.7
167.5°	344.2	344.4	344.9	343.7	342.4	340.1	337.2	334.3	330.6	327.0	324.1
170°	336.6	337.2	337.2	336.6	335.3	334.0	332.2	330.2	327.0	324.5	322.5
172.5°	329.5	330.1	331.1	330.0	329.7	329.0	327.5	325.6	323.4	321.4	320.5
175°	320.7	321.3	322.5	322.0	322.0	322.0	320.7	320.7	318.7	318.1	318.1
177.5°	316.2	316.2	317.7	317.2	317.7	317.7	317.7	317.2	316.7	316.2	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	13.4	13.1	13.5	13.2	12.5	14.8	16.0	16.4	15.5	14.8	14.0
90°	8.3	7.0	6.4	5.1	3.8	2.5	1.3	0.7	1.3	2.5	3.8
92.5°	145.4	87.1	52.3	33.7	22.7	14.8	9.5	7.7	9.5	14.8	22.7
95°	284.9	144.7	76.5	47.8	33.8	26.7	21.7	21.0	21.7	26.7	33.8
97.5°	227.5	124.7	79.6	58.9	46.3	39.3	35.7	34.9	35.7	39.3	46.3
100°	206.5	123.7	86.7	67.6	55.4	48.4	45.9	44.6	45.9	48.4	55.4
102.5°	197.9	128.2	95.4	76.7	65.6	58.1	56.1	55.4	56.1	58.1	65.6
105°	194.4	137.7	109.7	91.8	81.6	75.3	72.1	72.1	72.1	75.3	81.6
107.5°	200.3	151.7	124.6	108.5	97.9	92.7	89.6	88.4	89.6	92.7	97.9
110°	205.9	161.9	135.7	119.2	109.7	103.9	101.3	100.1	101.3	103.9	109.7





TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	213.0	171.6	146.5	130.4	120.8	115.1	113.1	111.8	113.1	115.1	120.8
115°	223.7	186.8	163.2	147.2	137.7	132.0	130.0	128.7	130.0	132.0	137.7
117.5°	236.0	202.4	180.0	164.6	153.8	148.1	146.0	144.1	146.0	148.1	153.8
120°	244.2	213.5	191.3	175.3	164.4	158.7	156.2	154.3	156.2	158.7	164.4
122.5°	253.3	224.3	201.9	186.1	174.1	168.4	166.4	165.0	166.4	168.4	174.1
125°	265.8	238.4	217.4	200.8	188.7	183.0	179.8	178.5	179.8	183.0	188.7
127.5°	277.3	252.1	231.8	215.2	202.4	195.1	191.0	189.1	191.0	195.1	202.4
130°	284.9	260.7	241.0	224.4	211.0	202.7	197.6	195.7	197.6	202.7	211.0
132.5°	291.6	268.9	249.2	232.5	218.7	209.4	203.3	200.8	203.3	209.4	218.7
135°	300.9	279.9	260.1	242.9	229.5	219.3	211.7	209.1	211.7	219.3	229.5
137.5°	307.8	287.6	269.6	251.9	238.8	228.6	221.4	219.6	221.4	228.6	238.8
140°	312.3	293.3	274.8	257.6	245.4	235.2	227.6	225.7	227.6	235.2	245.4
142.5°	315.0	296.8	279.3	263.2	251.5	241.3	234.2	232.8	234.2	241.3	251.5
145°	318.7	302.8	286.3	271.6	260.1	251.2	244.8	243.5	244.8	251.2	260.1
147.5°	321.1	306.6	292.1	279.2	269.3	261.0	255.5	254.7	255.5	261.0	269.3
150°	322.5	309.2	295.1	284.3	275.4	267.1	262.6	261.4	262.6	267.1	275.4
152.5°	323.6	311.7	298.7	288.9	280.5	273.2	269.3	268.5	269.3	273.2	280.5
155°	324.5	314.3	303.5	294.5	288.1	281.8	277.9	277.9	277.9	281.8	288.1
157.5°	325.1	316.4	307.1	300.4	294.7	289.3	286.3	286.3	286.3	289.3	294.7
160°	325.1	317.5	309.2	303.5	298.3	293.9	291.3	292.0	291.3	293.9	298.3
162.5°	324.6	318.5	311.2	306.5	302.4	298.5	296.0	296.5	296.0	298.5	302.4
165°	323.8	318.7	313.6	309.8	307.3	304.1	302.1	303.5	302.1	304.1	307.3
167.5°	322.3	318.7	314.5	312.1	310.3	308.5	307.4	308.0	307.4	308.5	310.3
170°	321.3	318.7	315.5	313.6	312.3	311.1	310.5	311.1	310.5	311.1	312.3
172.5°	320.2	318.2	315.5	314.6	313.9	312.6	312.0	313.2	312.0	312.6	313.9
175°	318.7	317.5	315.5	315.5	315.5	315.0	314.3	315.5	314.3	315.0	315.5
177.5°	317.2	316.7	315.7	315.7	316.2	315.7	315.7	316.7	315.7	315.7	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	13.7	14.0	13.6	14.8	13.5	14.3	14.3	14.0	14.1	14.3	14.0
90°	5.1	6.4	7.0	8.3	8.9	10.2	10.8	11.5	12.1	12.7	14.0
92.5°	33.7	52.3	87.1	145.4	208.8	205.5	166.4	113.0	82.0	61.7	52.3
95°	47.8	76.5	144.7	284.9	460.9	564.8	552.7	458.4	361.4	283.1	229.5
97.5°	58.9	79.6	124.7	227.5	411.6	603.2	699.3	682.7	614.7	538.3	463.8
100°	67.6	86.7	123.7	206.5	367.2	575.7	735.0	784.1	752.8	687.2	620.9
102.5°	76.7	95.4	128.2	197.9	333.5	527.2	713.6	818.2	837.6	806.0	761.2
105°	91.8	109.7	137.7	194.4	300.9	462.2	645.1	798.1	885.5	913.5	906.5
107.5°	108.5	124.6	151.7	200.3	287.1	417.4	575.3	726.2	842.8	914.8	948.0
110°	119.2	135.7	161.9	205.9	283.1	396.5	535.5	673.2	794.3	884.2	938.3



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	130.4	146.5	171.6	213.0	283.1	384.3	505.9	631.4	746.3	837.2	901.2
115°	147.2	163.2	186.8	223.7	284.9	371.0	473.6	578.9	677.7	765.0	834.5
117.5°	164.6	180.0	202.4	236.0	289.2	364.5	454.4	544.9	630.1	705.3	769.1
120°	175.3	191.3	213.5	244.2	293.3	361.4	443.7	526.5	603.1	673.2	729.3
122.5°	186.1	201.9	224.3	253.3	296.8	358.9	434.5	512.8	583.7	646.1	698.7
125°	200.8	217.4	238.4	265.8	302.8	355.7	422.0	492.8	557.8	613.3	659.2
127.5°	215.2	231.8	252.1	277.3	309.6	354.2	410.5	472.4	533.0	584.8	627.8
130°	224.4	241.0	260.7	284.9	313.6	353.2	402.9	459.6	515.8	565.4	606.9
132.5°	232.5	249.2	268.9	291.6	318.2	353.2	396.8	446.9	499.4	544.5	584.4
135°	242.9	260.1	279.9	300.9	324.5	353.2	389.5	430.3	474.3	515.1	551.4
137.5°	251.9	269.6	287.6	307.8	330.2	353.9	383.0	416.3	451.8	485.8	516.6
140°	257.6	274.8	293.3	312.3	332.7	354.4	379.9	408.6	438.5	467.9	494.6
142.5°	263.2	279.3	296.8	315.0	334.3	355.0	377.4	402.0	427.4	452.6	475.8
145°	271.6	286.3	302.8	318.7	336.0	354.4	373.6	393.3	413.1	432.8	450.0
147.5°	279.2	292.1	306.6	321.1	336.6	352.8	369.6	385.1	401.2	416.4	429.4
150°	284.3	295.1	309.2	322.5	336.6	351.2	366.6	380.6	394.6	406.7	418.2
152.5°	288.9	298.7	311.7	323.6	336.1	349.2	363.0	375.4	388.0	399.1	408.0
155°	294.5	303.5	314.3	324.5	334.7	345.5	357.0	367.9	378.1	386.9	394.0
157.5°	300.4	307.1	316.4	325.1	333.0	341.7	351.4	360.2	368.6	375.4	381.0
160°	303.5	309.2	317.5	325.1	331.5	339.2	346.8	355.1	361.4	367.9	372.3
162.5°	306.5	311.2	318.5	324.6	330.0	336.1	342.7	349.4	355.3	360.7	364.6
165°	309.8	313.6	318.7	323.8	327.7	331.5	336.6	341.7	346.2	350.0	353.2
167.5°	312.1	314.5	318.7	322.3	324.1	327.0	330.6	334.3	337.2	340.1	342.4
170°	313.6	315.5	318.7	321.3	322.5	324.5	327.0	330.2	332.2	334.0	335.3
172.5°	314.6	315.5	318.2	320.2	320.5	321.4	323.4	325.6	327.5	329.0	329.7
175°	315.5	315.5	317.5	318.7	318.1	318.1	318.7	320.7	320.7	322.0	322.0
177.5°	315.7	315.7	316.7	317.2	316.2	316.2	316.7	317.2	317.7	317.7	317.7
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	14.5	14.0	14.1	14.1	14.1	14.0	14.5	14.0	14.3	14.1	14.0
90°	14.0	14.0	14.7	14.7	14.7	14.0	14.0	14.0	12.7	12.1	11.5
92.5°	44.1	42.6	41.7	40.7	41.7	42.6	44.1	52.3	61.7	82.0	113.0
95°	184.3	165.1	160.0	149.8	160.0	165.1	184.3	229.5	283.1	361.4	458.4
97.5°	424.4	388.7	370.2	362.1	370.2	388.7	424.4	463.8	538.3	614.7	682.7
100°	576.9	531.0	507.4	497.3	507.4	531.0	576.9	620.9	687.2	752.8	784.1
102.5°	714.1	681.4	655.8	648.2	655.8	681.4	714.1	761.2	806.0	837.6	818.2
105°	886.1	865.0	852.3	844.7	852.3	865.0	886.1	906.5	913.5	885.5	798.1
107.5°	958.4	958.2	954.1	948.9	954.1	958.2	958.4	948.0	914.8	842.8	726.2
110°	967.0	979.2	983.7	983.7	983.7	979.2	967.0	938.3	884.2	794.3	673.2



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	943.1	963.8	974.9	979.6	974.9	963.8	943.1	901.2	837.2	746.3	631.4
115°	884.2	914.8	932.6	940.9	932.6	914.8	884.2	834.5	765.0	677.7	578.9
117.5°	818.8	850.4	868.1	873.2	868.1	850.4	818.8	769.1	705.3	630.1	544.9
120°	776.4	807.1	824.3	829.3	824.3	807.1	776.4	729.3	673.2	603.1	526.5
122.5°	740.8	768.8	786.0	790.6	786.0	768.8	740.8	698.7	646.1	583.7	512.8
125°	694.9	721.0	735.0	741.4	735.0	721.0	694.9	659.2	613.3	557.8	492.8
127.5°	660.1	683.2	696.5	699.3	696.5	683.2	660.1	627.8	584.8	533.0	472.4
130°	638.8	659.8	672.5	676.4	672.5	659.8	638.8	606.9	565.4	515.8	459.6
132.5°	616.3	637.3	649.1	653.4	649.1	637.3	616.3	584.4	544.5	499.4	446.9
135°	579.4	600.5	612.0	615.8	612.0	600.5	579.4	551.4	515.1	474.3	430.3
137.5°	541.8	560.8	571.4	575.7	571.4	560.8	541.8	516.6	485.8	451.8	416.3
140°	518.3	534.8	544.4	547.6	544.4	534.8	518.3	494.6	467.9	438.5	408.6
142.5°	495.9	509.9	518.9	521.5	518.9	509.9	495.9	475.8	452.6	427.4	402.0
145°	465.4	476.2	483.2	485.8	483.2	476.2	465.4	450.0	432.8	413.1	393.3
147.5°	441.5	450.2	454.3	455.4	454.3	450.2	441.5	429.4	416.4	401.2	385.1
150°	427.8	435.4	438.0	438.5	438.0	435.4	427.8	418.2	406.7	394.6	380.6
152.5°	416.0	422.2	424.7	425.3	424.7	422.2	416.0	408.0	399.1	388.0	375.4
155°	400.3	404.8	406.7	407.3	406.7	404.8	400.3	394.0	386.9	378.1	367.9
157.5°	386.0	389.6	391.4	391.3	391.4	389.6	386.0	381.0	375.4	368.6	360.2
160°	376.7	379.9	381.2	380.6	381.2	379.9	376.7	372.3	367.9	361.4	355.1
162.5°	368.1	370.7	371.0	370.9	371.0	370.7	368.1	364.6	360.7	355.3	349.4
165°	355.7	357.0	357.0	357.0	357.0	357.0	355.7	353.2	350.0	346.2	341.7
167.5°	343.7	344.9	344.4	344.2	344.4	344.9	343.7	342.4	340.1	337.2	334.3
170°	336.6	337.2	337.2	336.6	337.2	337.2	336.6	335.3	334.0	332.2	330.2
172.5°	330.0	331.1	330.1	329.5	330.1	331.1	330.0	329.7	329.0	327.5	325.6
175°	322.0	322.5	321.3	320.7	321.3	322.5	322.0	322.0	322.0	320.7	320.7
177.5°	317.2	317.7	316.2	316.2	316.2	317.7	317.2	317.7	317.7	317.7	317.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	14.3	14.3	13.5	14.8	13.6	14.0	13.7	14.0	14.8	15.5	16.4
90°	10.8	10.2	8.9	8.3	7.0	6.4	5.1	3.8	2.5	1.3	0.7
92.5°	166.4	205.5	208.8	145.4	87.1	52.3	33.7	22.7	14.8	9.5	7.7
95°	552.7	564.8	460.9	284.9	144.7	76.5	47.8	33.8	26.7	21.7	21.0
97.5°	699.3	603.2	411.6	227.5	124.7	79.6	58.9	46.3	39.3	35.7	34.9
100°	735.0	575.7	367.2	206.5	123.7	86.7	67.6	55.4	48.4	45.9	44.6
102.5°	713.6	527.2	333.5	197.9	128.2	95.4	76.7	65.6	58.1	56.1	55.4
105°	645.1	462.2	300.9	194.4	137.7	109.7	91.8	81.6	75.3	72.1	72.1
107.5°	575.3	417.4	287.1	200.3	151.7	124.6	108.5	97.9	92.7	89.6	88.4
110°	535.5	396.5	283.1	205.9	161.9	135.7	119.2	109.7	103.9	101.3	100.1



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	505.9	384.3	283.1	213.0	171.6	146.5	130.4	120.8	115.1	113.1	111.8
115°	473.6	371.0	284.9	223.7	186.8	163.2	147.2	137.7	132.0	130.0	128.7
117.5°	454.4	364.5	289.2	236.0	202.4	180.0	164.6	153.8	148.1	146.0	144.1
120°	443.7	361.4	293.3	244.2	213.5	191.3	175.3	164.4	158.7	156.2	154.3
122.5°	434.5	358.9	296.8	253.3	224.3	201.9	186.1	174.1	168.4	166.4	165.0
125°	422.0	355.7	302.8	265.8	238.4	217.4	200.8	188.7	183.0	179.8	178.5
127.5°	410.5	354.2	309.6	277.3	252.1	231.8	215.2	202.4	195.1	191.0	189.1
130°	402.9	353.2	313.6	284.9	260.7	241.0	224.4	211.0	202.7	197.6	195.7
132.5°	396.8	353.2	318.2	291.6	268.9	249.2	232.5	218.7	209.4	203.3	200.8
135°	389.5	353.2	324.5	300.9	279.9	260.1	242.9	229.5	219.3	211.7	209.1
137.5°	383.0	353.9	330.2	307.8	287.6	269.6	251.9	238.8	228.6	221.4	219.6
140°	379.9	354.4	332.7	312.3	293.3	274.8	257.6	245.4	235.2	227.6	225.7
142.5°	377.4	355.0	334.3	315.0	296.8	279.3	263.2	251.5	241.3	234.2	232.8
145°	373.6	354.4	336.0	318.7	302.8	286.3	271.6	260.1	251.2	244.8	243.5
147.5°	369.6	352.8	336.6	321.1	306.6	292.1	279.2	269.3	261.0	255.5	254.7
150°	366.6	351.2	336.6	322.5	309.2	295.1	284.3	275.4	267.1	262.6	261.4
152.5°	363.0	349.2	336.1	323.6	311.7	298.7	288.9	280.5	273.2	269.3	268.5
155°	357.0	345.5	334.7	324.5	314.3	303.5	294.5	288.1	281.8	277.9	277.9
157.5°	351.4	341.7	333.0	325.1	316.4	307.1	300.4	294.7	289.3	286.3	286.3
160°	346.8	339.2	331.5	325.1	317.5	309.2	303.5	298.3	293.9	291.3	292.0
162.5°	342.7	336.1	330.0	324.6	318.5	311.2	306.5	302.4	298.5	296.0	296.5
165°	336.6	331.5	327.7	323.8	318.7	313.6	309.8	307.3	304.1	302.1	303.5
167.5°	330.6	327.0	324.1	322.3	318.7	314.5	312.1	310.3	308.5	307.4	308.0
170°	327.0	324.5	322.5	321.3	318.7	315.5	313.6	312.3	311.1	310.5	311.1
172.5°	323.4	321.4	320.5	320.2	318.2	315.5	314.6	313.9	312.6	312.0	313.2
175°	318.7	318.1	318.1	318.7	317.5	315.5	315.5	315.5	315.0	314.3	315.5
177.5°	316.7	316.2	316.2	317.2	316.7	315.7	315.7	316.2	315.7	315.7	316.7
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.0	14.8	12.5	13.2	13.5	13.1	13.4	13.0	12.7	12.9	13.0
90°	1.3	2.5	3.8	5.1	6.4	7.0	8.3	8.9	10.2	10.8	11.5
92.5°	9.5	14.8	22.7	33.7	52.3	87.1	145.4	208.8	205.5	166.4	113.0
95°	21.7	26.7	33.8	47.8	76.5	144.7	284.9	460.9	564.8	552.7	458.4
97.5°	35.7	39.3	46.3	58.9	79.6	124.7	227.5	411.6	603.2	699.3	682.7
100°	45.9	48.4	55.4	67.6	86.7	123.7	206.5	367.2	575.7	735.0	784.1
102.5°	56.1	58.1	65.6	76.7	95.4	128.2	197.9	333.5	527.2	713.6	818.2
105°	72.1	75.3	81.6	91.8	109.7	137.7	194.4	300.9	462.2	645.1	798.1
107.5°	89.6	92.7	97.9	108.5	124.6	151.7	200.3	287.1	417.4	575.3	726.2
110°	101.3	103.9	109.7	119.2	135.7	161.9	205.9	283.1	396.5	535.5	673.2





TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	113.1	115.1	120.8	130.4	146.5	171.6	213.0	283.1	384.3	505.9	631.4
115°	130.0	132.0	137.7	147.2	163.2	186.8	223.7	284.9	371.0	473.6	578.9
117.5°	146.0	148.1	153.8	164.6	180.0	202.4	236.0	289.2	364.5	454.4	544.9
120°	156.2	158.7	164.4	175.3	191.3	213.5	244.2	293.3	361.4	443.7	526.5
122.5°	166.4	168.4	174.1	186.1	201.9	224.3	253.3	296.8	358.9	434.5	512.8
125°	179.8	183.0	188.7	200.8	217.4	238.4	265.8	302.8	355.7	422.0	492.8
127.5°	191.0	195.1	202.4	215.2	231.8	252.1	277.3	309.6	354.2	410.5	472.4
130°	197.6	202.7	211.0	224.4	241.0	260.7	284.9	313.6	353.2	402.9	459.6
132.5°	203.3	209.4	218.7	232.5	249.2	268.9	291.6	318.2	353.2	396.8	446.9
135°	211.7	219.3	229.5	242.9	260.1	279.9	300.9	324.5	353.2	389.5	430.3
137.5°	221.4	228.6	238.8	251.9	269.6	287.6	307.8	330.2	353.9	383.0	416.3
140°	227.6	235.2	245.4	257.6	274.8	293.3	312.3	332.7	354.4	379.9	408.6
142.5°	234.2	241.3	251.5	263.2	279.3	296.8	315.0	334.3	355.0	377.4	402.0
145°	244.8	251.2	260.1	271.6	286.3	302.8	318.7	336.0	354.4	373.6	393.3
147.5°	255.5	261.0	269.3	279.2	292.1	306.6	321.1	336.6	352.8	369.6	385.1
150°	262.6	267.1	275.4	284.3	295.1	309.2	322.5	336.6	351.2	366.6	380.6
152.5°	269.3	273.2	280.5	288.9	298.7	311.7	323.6	336.1	349.2	363.0	375.4
155°	277.9	281.8	288.1	294.5	303.5	314.3	324.5	334.7	345.5	357.0	367.9
157.5°	286.3	289.3	294.7	300.4	307.1	316.4	325.1	333.0	341.7	351.4	360.2
160°	291.3	293.9	298.3	303.5	309.2	317.5	325.1	331.5	339.2	346.8	355.1
162.5°	296.0	298.5	302.4	306.5	311.2	318.5	324.6	330.0	336.1	342.7	349.4
165°	302.1	304.1	307.3	309.8	313.6	318.7	323.8	327.7	331.5	336.6	341.7
167.5°	307.4	308.5	310.3	312.1	314.5	318.7	322.3	324.1	327.0	330.6	334.3
170°	310.5	311.1	312.3	313.6	315.5	318.7	321.3	322.5	324.5	327.0	330.2
172.5°	312.0	312.6	313.9	314.6	315.5	318.2	320.2	320.5	321.4	323.4	325.6
175°	314.3	315.0	315.5	315.5	315.5	317.5	318.7	318.1	318.1	318.7	320.7
177.5°	315.7	315.7	316.2	315.7	315.7	316.7	317.2	316.2	316.2	316.7	317.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2	316.2



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	13.6	14.3	13.5	13.0	13.0	13.6	14.1
90°	12.1	12.7	14.0	14.0	14.0	14.7	14.7
92.5°	82.0	61.7	52.3	44.1	42.6	41.7	40.7
95°	361.4	283.1	229.5	184.3	165.1	160.0	149.8
97.5°	614.7	538.3	463.8	424.4	388.7	370.2	362.1
100°	752.8	687.2	620.9	576.9	531.0	507.4	497.3
102.5°	837.6	806.0	761.2	714.1	681.4	655.8	648.2
105°	885.5	913.5	906.5	886.1	865.0	852.3	844.7
107.5°	842.8	914.8	948.0	958.4	958.2	954.1	948.9
110°	794.3	884.2	938.3	967.0	979.2	983.7	983.7



TEST NUMBER: P333624-930

CATALOG NUMBER: S125RDIP-S1270D810U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	746.3	837.2	901.2	943.1	963.8	974.9	979.6
115°	677.7	765.0	834.5	884.2	914.8	932.6	940.9
117.5°	630.1	705.3	769.1	818.8	850.4	868.1	873.2
120°	603.1	673.2	729.3	776.4	807.1	824.3	829.3
122.5°	583.7	646.1	698.7	740.8	768.8	786.0	790.6
125°	557.8	613.3	659.2	694.9	721.0	735.0	741.4
127.5°	533.0	584.8	627.8	660.1	683.2	696.5	699.3
130°	515.8	565.4	606.9	638.8	659.8	672.5	676.4
132.5°	499.4	544.5	584.4	616.3	637.3	649.1	653.4
135°	474.3	515.1	551.4	579.4	600.5	612.0	615.8
137.5°	451.8	485.8	516.6	541.8	560.8	571.4	575.7
140°	438.5	467.9	494.6	518.3	534.8	544.4	547.6
142.5°	427.4	452.6	475.8	495.9	509.9	518.9	521.5
145°	413.1	432.8	450.0	465.4	476.2	483.2	485.8
147.5°	401.2	416.4	429.4	441.5	450.2	454.3	455.4
150°	394.6	406.7	418.2	427.8	435.4	438.0	438.5
152.5°	388.0	399.1	408.0	416.0	422.2	424.7	425.3
155°	378.1	386.9	394.0	400.3	404.8	406.7	407.3
157.5°	368.6	375.4	381.0	386.0	389.6	391.4	391.3
160°	361.4	367.9	372.3	376.7	379.9	381.2	380.6
162.5°	355.3	360.7	364.6	368.1	370.7	371.0	370.9
165°	346.2	350.0	353.2	355.7	357.0	357.0	357.0
167.5°	337.2	340.1	342.4	343.7	344.9	344.4	344.2
170°	332.2	334.0	335.3	336.6	337.2	337.2	336.6
172.5°	327.5	329.0	329.7	330.0	331.1	330.1	329.5
175°	320.7	322.0	322.0	322.0	322.5	321.3	320.7
177.5°	317.7	317.7	317.7	317.2	317.7	316.2	316.2
180°	316.2	316.2	316.2	316.2	316.2	316.2	316.2

(END OF REPORT)