

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333508-930

Luminaire Tested: **S125RDIP-S375D1035U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333508-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1035U930-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4563.5 lumens  
Efficiency: N/A  
Efficacy: 122.3 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34	26
1	93	89	85	82	83	79	76	73	62	60	58	45	44	43	30	30	29	22
2	84	78	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	21	16
4	71	60	53	47	63	54	48	43	43	38	35	32	29	26	22	20	19	14
5	65	54	46	40	58	48	42	37	38	33	30	28	25	23	20	18	16	12
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	19	16	14	14	12	10	8
10	44	32	26	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	1.0
10°-20°	129.0	2.8
20°-30°	204.5	4.5
30°-40°	246.6	5.4
40°-50°	220.2	4.8
50°-60°	168.9	3.7
60°-70°	109.7	2.4
70°-80°	53.3	1.2
80°-90°	15.0	0.3
90°-100°	39.9	0.9
100°-110°	245.9	5.4
110°-120°	446.1	9.8
120°-130°	572.5	12.5
130°-140°	615.7	13.5
140°-150°	578.0	12.7
150°-160°	467.5	10.2
160°-170°	302.4	6.6
170°-180°	104.3	2.3
0°-30°	377.5	8.3
0°-40°	624.0	13.7
0°-60°	1013.1	22.2
0°-90°	1191.2	26.1
90°-120°	731.9	16.0
90°-150°	2498.1	54.7
90°-180°	3372.0	73.9
0°-180°	4563.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	10
90°	20	1	20	1	20	9
95°	17	46	17	46	17	14
105°	242	239	242	239	242	219
115°	446	449	446	449	446	443
125°	639	639	639	639	639	568
135°	794	797	794	797	794	613
145°	922	924	922	924	922	576
155°	1010	1018	1010	1018	1010	466
165°	1068	1074	1068	1074	1068	301
175°	1093	1098	1093	1098	1093	104
180°	1098	1098	1098	1098	1098	



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	7.3	6.9	6.7	6.6	6.6	6.8	6.4	6.1	6.0	5.8	5.7
90°	19.6	19.0	18.4	17.9	17.4	16.6	15.7	14.8	13.9	13.0	11.7
92.5°	18.3	18.0	17.7	17.4	17.2	16.6	15.7	14.8	13.9	13.0	11.9
95°	17.1	17.1	17.1	17.1	17.1	16.6	15.7	14.8	13.9	13.0	19.9
97.5°	17.1	17.1	17.1	17.1	17.1	19.6	24.8	29.8	35.0	40.0	53.6
100°	17.1	17.9	18.5	19.2	20.0	33.8	60.8	87.7	114.7	141.6	140.9
102.5°	102.4	114.7	127.0	139.3	151.6	160.3	165.4	170.5	175.6	180.8	180.3
105°	241.7	242.0	242.1	242.3	242.5	242.6	242.6	242.6	242.6	242.6	242.6
107.5°	304.8	305.3	305.9	306.4	307.0	307.2	307.2	307.1	307.1	307.0	306.7
110°	348.4	348.2	348.1	347.9	347.7	347.9	348.4	348.9	349.5	350.0	349.7



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	387.5	387.8	388.0	388.2	388.5	389.0	389.6	390.4	391.0	391.8	391.5
115°	446.1	447.2	448.3	449.4	450.5	451.3	452.1	452.8	453.6	454.2	454.0
117.5°	508.6	509.1	509.6	510.1	510.5	511.2	512.2	513.1	514.0	514.9	514.3
120°	547.1	548.0	548.9	549.8	550.7	551.3	551.6	552.0	552.4	552.8	552.2
122.5°	583.5	584.6	585.6	586.7	587.7	588.4	588.8	589.1	589.5	589.9	589.6
125°	639.0	639.6	640.1	640.7	641.2	641.8	642.5	643.3	644.0	644.7	644.7
127.5°	685.7	687.1	688.4	689.7	691.1	691.9	692.4	692.8	693.2	693.6	693.7
130°	719.6	720.6	721.5	722.4	723.3	724.0	724.5	725.0	725.6	726.1	725.9
132.5°	750.9	751.8	752.7	753.6	754.5	755.0	755.1	755.2	755.3	755.5	755.9
135°	793.7	794.8	795.9	797.0	798.0	798.7	799.2	799.5	799.8	800.2	800.5
137.5°	836.7	837.6	838.5	839.5	840.4	840.9	840.8	840.7	840.7	840.6	840.9
140°	862.1	863.2	864.2	865.4	866.4	866.7	866.4	866.1	865.7	865.4	865.5
142.5°	886.1	887.3	888.4	889.4	890.6	891.0	891.0	890.9	890.8	890.7	890.5
145°	921.5	922.6	923.7	924.8	925.9	926.3	926.1	925.9	925.8	925.6	925.6
147.5°	950.6	951.9	953.2	954.6	955.9	956.4	956.2	955.9	955.8	955.5	955.3
150°	969.6	970.9	972.4	973.9	975.3	975.8	975.5	975.2	974.8	974.4	974.0
152.5°	987.1	988.4	989.7	991.0	992.3	992.8	992.5	992.1	991.7	991.3	991.0
155°	1010.2	1011.7	1013.1	1014.6	1016.0	1016.5	1015.9	1015.4	1014.9	1014.3	1013.9
157.5°	1029.6	1031.0	1032.5	1034.0	1035.4	1035.8	1035.3	1034.7	1034.1	1033.6	1033.5
160°	1042.0	1043.4	1044.9	1046.4	1047.7	1048.1	1047.4	1046.7	1045.9	1045.2	1045.1
162.5°	1053.0	1054.7	1056.2	1057.9	1059.4	1059.7	1058.7	1057.7	1056.7	1055.6	1055.5
165°	1068.0	1069.5	1070.9	1072.4	1073.8	1074.0	1072.9	1071.8	1070.7	1069.7	1069.5
167.5°	1078.5	1080.1	1081.7	1083.4	1085.0	1085.2	1083.9	1082.6	1081.2	1079.9	1079.7
170°	1084.3	1086.0	1087.6	1089.2	1090.8	1091.0	1089.5	1088.0	1086.5	1085.2	1084.9
172.5°	1088.3	1089.8	1091.4	1093.1	1094.7	1094.9	1093.6	1092.3	1091.0	1089.6	1089.3
175°	1093.2	1094.9	1096.5	1098.1	1099.8	1099.8	1098.5	1097.0	1095.5	1094.1	1093.9
177.5°	1096.2	1097.4	1098.5	1099.7	1100.8	1100.9	1099.9	1098.9	1097.9	1096.8	1096.7
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	5.5	5.3	5.2	5.0	4.5	5.0	5.1	5.0	5.0	5.0	5.0
90°	10.5	9.2	8.0	6.6	5.1	3.7	2.3	0.8	2.3	3.7	5.1
92.5°	10.8	9.6	8.6	8.5	9.5	10.5	11.5	12.6	11.5	10.5	9.5
95°	26.7	33.7	40.5	44.3	44.8	45.3	45.8	46.4	45.8	45.3	44.8
97.5°	67.3	80.9	94.5	100.8	99.8	98.8	97.8	96.9	97.8	98.8	99.8
100°	140.2	139.5	138.8	138.1	137.5	137.1	136.5	135.9	136.5	137.1	137.5
102.5°	179.9	179.4	179.0	178.4	177.7	177.1	176.3	175.7	176.3	177.1	177.7
105°	242.6	242.6	242.6	242.2	241.5	240.8	240.0	239.3	240.0	240.8	241.5
107.5°	306.3	306.0	305.6	305.4	305.4	305.4	305.4	305.4	305.4	305.4	305.4
110°	349.4	348.9	348.6	348.4	348.4	348.4	348.4	348.4	348.4	348.4	348.4





TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	391.3	391.1	390.9	390.5	390.1	389.6	389.2	388.8	389.2	389.6	390.1
115°	453.9	453.7	453.6	453.0	452.1	451.2	450.3	449.4	450.3	451.2	452.1
117.5°	513.6	512.9	512.3	511.9	511.9	511.9	512.0	512.0	512.0	511.9	511.9
120°	551.6	551.1	550.6	550.4	550.6	550.7	550.9	551.1	550.9	550.7	550.6
122.5°	589.4	589.1	588.8	588.4	587.7	587.0	586.3	585.6	586.3	587.0	587.7
125°	644.7	644.7	644.7	644.1	642.9	641.6	640.3	639.0	640.3	641.6	642.9
127.5°	693.8	693.9	694.0	693.6	692.7	691.8	690.9	690.0	690.9	691.8	692.7
130°	725.8	725.6	725.4	724.9	724.0	723.1	722.2	721.2	722.2	723.1	724.0
132.5°	756.3	756.6	757.0	756.7	755.6	754.6	753.6	752.5	753.6	754.6	755.6
135°	801.0	801.3	801.7	801.3	800.2	799.2	798.0	797.0	798.0	799.2	800.2
137.5°	841.2	841.6	841.9	841.6	840.7	839.7	838.8	837.8	838.8	839.7	840.7
140°	865.7	865.8	866.1	865.9	865.6	865.3	864.9	864.5	864.9	865.3	865.6
142.5°	890.2	890.0	889.7	889.5	889.2	889.1	888.8	888.6	888.8	889.1	889.2
145°	925.6	925.6	925.6	925.4	925.0	924.6	924.3	924.0	924.3	924.6	925.0
147.5°	955.1	954.9	954.6	954.6	954.6	954.7	954.8	954.9	954.8	954.7	954.6
150°	973.7	973.3	973.0	973.0	973.3	973.7	974.0	974.4	974.0	973.7	973.3
152.5°	990.6	990.3	989.9	990.1	990.9	991.7	992.5	993.3	992.5	991.7	990.9
155°	1013.6	1013.3	1012.8	1013.3	1014.3	1015.4	1016.5	1017.6	1016.5	1015.4	1014.3
157.5°	1033.5	1033.4	1033.4	1033.7	1034.4	1035.0	1035.6	1036.2	1035.6	1035.0	1034.4
160°	1044.9	1044.7	1044.5	1045.0	1046.0	1047.2	1048.2	1049.3	1048.2	1047.2	1046.0
162.5°	1055.3	1055.1	1054.9	1055.4	1056.5	1057.5	1058.7	1059.7	1058.7	1057.5	1056.5
165°	1069.3	1069.1	1068.9	1069.4	1070.5	1071.5	1072.6	1073.7	1072.6	1071.5	1070.5
167.5°	1079.5	1079.4	1079.2	1079.7	1080.8	1081.9	1083.0	1084.2	1083.0	1081.9	1080.8
170°	1084.8	1084.6	1084.4	1084.9	1086.2	1087.4	1088.8	1090.0	1088.8	1087.4	1086.2
172.5°	1089.0	1088.7	1088.4	1088.8	1090.1	1091.4	1092.7	1093.9	1092.7	1091.4	1090.1
175°	1093.7	1093.6	1093.4	1093.8	1094.9	1096.0	1097.1	1098.1	1097.1	1096.0	1094.9
177.5°	1096.6	1096.4	1096.3	1096.7	1097.5	1098.4	1099.3	1100.1	1099.3	1098.4	1097.5
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	5.1	5.4	5.5	6.0	5.8	6.2	6.4	6.4	6.6	6.8	6.8
90°	6.6	8.0	9.2	10.5	11.7	13.0	13.9	14.8	15.7	16.6	17.4
92.5°	8.5	8.6	9.6	10.8	11.9	13.0	13.9	14.8	15.7	16.6	17.2
95°	44.3	40.5	33.7	26.7	19.9	13.0	13.9	14.8	15.7	16.6	17.1
97.5°	100.8	94.5	80.9	67.3	53.6	40.0	35.0	29.8	24.8	19.6	17.1
100°	138.1	138.8	139.5	140.2	140.9	141.6	114.7	87.7	60.8	33.8	20.0
102.5°	178.4	179.0	179.4	179.9	180.3	180.8	175.6	170.5	165.4	160.3	151.6
105°	242.2	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.5
107.5°	305.4	305.6	306.0	306.3	306.7	307.0	307.1	307.1	307.2	307.2	307.0
110°	348.4	348.6	348.9	349.4	349.7	350.0	349.5	348.9	348.4	347.9	347.7



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	390.5	390.9	391.1	391.3	391.5	391.8	391.0	390.4	389.6	389.0	388.5
115°	453.0	453.6	453.7	453.9	454.0	454.2	453.6	452.8	452.1	451.3	450.5
117.5°	511.9	512.3	512.9	513.6	514.3	514.9	514.0	513.1	512.2	511.2	510.5
120°	550.4	550.6	551.1	551.6	552.2	552.8	552.4	552.0	551.6	551.3	550.7
122.5°	588.4	588.8	589.1	589.4	589.6	589.9	589.5	589.1	588.8	588.4	587.7
125°	644.1	644.7	644.7	644.7	644.7	644.7	644.0	643.3	642.5	641.8	641.2
127.5°	693.6	694.0	693.9	693.8	693.7	693.6	693.2	692.8	692.4	691.9	691.1
130°	724.9	725.4	725.6	725.8	725.9	726.1	725.6	725.0	724.5	724.0	723.3
132.5°	756.7	757.0	756.6	756.3	755.9	755.5	755.3	755.2	755.1	755.0	754.5
135°	801.3	801.7	801.3	801.0	800.5	800.2	799.8	799.5	799.2	798.7	798.0
137.5°	841.6	841.9	841.6	841.2	840.9	840.6	840.7	840.7	840.8	840.9	840.4
140°	865.9	866.1	865.8	865.7	865.5	865.4	865.7	866.1	866.4	866.7	866.4
142.5°	889.5	889.7	890.0	890.2	890.5	890.7	890.8	890.9	891.0	891.0	890.6
145°	925.4	925.6	925.6	925.6	925.6	925.6	925.8	925.9	926.1	926.3	925.9
147.5°	954.6	954.6	954.9	955.1	955.3	955.5	955.8	955.9	956.2	956.4	955.9
150°	973.0	973.0	973.3	973.7	974.0	974.4	974.8	975.2	975.5	975.8	975.3
152.5°	990.1	989.9	990.3	990.6	991.0	991.3	991.7	992.1	992.5	992.8	992.3
155°	1013.3	1012.8	1013.3	1013.6	1013.9	1014.3	1014.9	1015.4	1015.9	1016.5	1016.0
157.5°	1033.7	1033.4	1033.4	1033.5	1033.5	1033.6	1034.1	1034.7	1035.3	1035.8	1035.4
160°	1045.0	1044.5	1044.7	1044.9	1045.1	1045.2	1045.9	1046.7	1047.4	1048.1	1047.7
162.5°	1055.4	1054.9	1055.1	1055.3	1055.5	1055.6	1056.7	1057.7	1058.7	1059.7	1059.4
165°	1069.4	1068.9	1069.1	1069.3	1069.5	1069.7	1070.7	1071.8	1072.9	1074.0	1073.8
167.5°	1079.7	1079.2	1079.4	1079.5	1079.7	1079.9	1081.2	1082.6	1083.9	1085.2	1085.0
170°	1084.9	1084.4	1084.6	1084.8	1084.9	1085.2	1086.5	1088.0	1089.5	1091.0	1090.8
172.5°	1088.8	1088.4	1088.7	1089.0	1089.3	1089.6	1091.0	1092.3	1093.6	1094.9	1094.7
175°	1093.8	1093.4	1093.6	1093.7	1093.9	1094.1	1095.5	1097.0	1098.5	1099.8	1099.8
177.5°	1096.7	1096.3	1096.4	1096.6	1096.7	1096.8	1097.9	1098.9	1099.9	1100.9	1100.8
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	7.0	7.0	7.1	7.3	7.1	7.0	7.0	6.8	6.8	6.6	6.4
90°	17.9	18.4	19.0	19.6	19.0	18.4	17.9	17.4	16.6	15.7	14.8
92.5°	17.4	17.7	18.0	18.3	18.0	17.7	17.4	17.2	16.6	15.7	14.8
95°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	16.6	15.7	14.8
97.5°	17.1	17.1	17.1	17.1	17.1	17.1	17.1	17.1	19.6	24.8	29.8
100°	19.2	18.5	17.9	17.1	17.9	18.5	19.2	20.0	33.8	60.8	87.7
102.5°	139.3	127.0	114.7	102.4	114.7	127.0	139.3	151.6	160.3	165.4	170.5
105°	242.3	242.1	242.0	241.7	242.0	242.1	242.3	242.5	242.6	242.6	242.6
107.5°	306.4	305.9	305.3	304.8	305.3	305.9	306.4	307.0	307.2	307.2	307.1
110°	347.9	348.1	348.2	348.4	348.2	348.1	347.9	347.7	347.9	348.4	348.9



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	388.2	388.0	387.8	387.5	387.8	388.0	388.2	388.5	389.0	389.6	390.4
115°	449.4	448.3	447.2	446.1	447.2	448.3	449.4	450.5	451.3	452.1	452.8
117.5°	510.1	509.6	509.1	508.6	509.1	509.6	510.1	510.5	511.2	512.2	513.1
120°	549.8	548.9	548.0	547.1	548.0	548.9	549.8	550.7	551.3	551.6	552.0
122.5°	586.7	585.6	584.6	583.5	584.6	585.6	586.7	587.7	588.4	588.8	589.1
125°	640.7	640.1	639.6	639.0	639.6	640.1	640.7	641.2	641.8	642.5	643.3
127.5°	689.7	688.4	687.1	685.7	687.1	688.4	689.7	691.1	691.9	692.4	692.8
130°	722.4	721.5	720.6	719.6	720.6	721.5	722.4	723.3	724.0	724.5	725.0
132.5°	753.6	752.7	751.8	750.9	751.8	752.7	753.6	754.5	755.0	755.1	755.2
135°	797.0	795.9	794.8	793.7	794.8	795.9	797.0	798.0	798.7	799.2	799.5
137.5°	839.5	838.5	837.6	836.7	837.6	838.5	839.5	840.4	840.9	840.8	840.7
140°	865.4	864.2	863.2	862.1	863.2	864.2	865.4	866.4	866.7	866.4	866.1
142.5°	889.4	888.4	887.3	886.1	887.3	888.4	889.4	890.6	891.0	891.0	890.9
145°	924.8	923.7	922.6	921.5	922.6	923.7	924.8	925.9	926.3	926.1	925.9
147.5°	954.6	953.2	951.9	950.6	951.9	953.2	954.6	955.9	956.4	956.2	955.9
150°	973.9	972.4	970.9	969.6	970.9	972.4	973.9	975.3	975.8	975.5	975.2
152.5°	991.0	989.7	988.4	987.1	988.4	989.7	991.0	992.3	992.8	992.5	992.1
155°	1014.6	1013.1	1011.7	1010.2	1011.7	1013.1	1014.6	1016.0	1016.5	1015.9	1015.4
157.5°	1034.0	1032.5	1031.0	1029.6	1031.0	1032.5	1034.0	1035.4	1035.8	1035.3	1034.7
160°	1046.4	1044.9	1043.4	1042.0	1043.4	1044.9	1046.4	1047.7	1048.1	1047.4	1046.7
162.5°	1057.9	1056.2	1054.7	1053.0	1054.7	1056.2	1057.9	1059.4	1059.7	1058.7	1057.7
165°	1072.4	1070.9	1069.5	1068.0	1069.5	1070.9	1072.4	1073.8	1074.0	1072.9	1071.8
167.5°	1083.4	1081.7	1080.1	1078.5	1080.1	1081.7	1083.4	1085.0	1085.2	1083.9	1082.6
170°	1089.2	1087.6	1086.0	1084.3	1086.0	1087.6	1089.2	1090.8	1091.0	1089.5	1088.0
172.5°	1093.1	1091.4	1089.8	1088.3	1089.8	1091.4	1093.1	1094.7	1094.9	1093.6	1092.3
175°	1098.1	1096.5	1094.9	1093.2	1094.9	1096.5	1098.1	1099.8	1099.8	1098.5	1097.0
177.5°	1099.7	1098.5	1097.4	1096.2	1097.4	1098.5	1099.7	1100.8	1100.9	1099.9	1098.9
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	6.4	6.2	5.8	6.0	5.5	5.4	5.1	5.0	5.0	5.0	5.0
90°	13.9	13.0	11.7	10.5	9.2	8.0	6.6	5.1	3.7	2.3	0.8
92.5°	13.9	13.0	11.9	10.8	9.6	8.6	8.5	9.5	10.5	11.5	12.6
95°	13.9	13.0	19.9	26.7	33.7	40.5	44.3	44.8	45.3	45.8	46.4
97.5°	35.0	40.0	53.6	67.3	80.9	94.5	100.8	99.8	98.8	97.8	96.9
100°	114.7	141.6	140.9	140.2	139.5	138.8	138.1	137.5	137.1	136.5	135.9
102.5°	175.6	180.8	180.3	179.9	179.4	179.0	178.4	177.7	177.1	176.3	175.7
105°	242.6	242.6	242.6	242.6	242.6	242.6	242.2	241.5	240.8	240.0	239.3
107.5°	307.1	307.0	306.7	306.3	306.0	305.6	305.4	305.4	305.4	305.4	305.4
110°	349.5	350.0	349.7	349.4	348.9	348.6	348.4	348.4	348.4	348.4	348.4



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	391.0	391.8	391.5	391.3	391.1	390.9	390.5	390.1	389.6	389.2	388.8
115°	453.6	454.2	454.0	453.9	453.7	453.6	453.0	452.1	451.2	450.3	449.4
117.5°	514.0	514.9	514.3	513.6	512.9	512.3	511.9	511.9	511.9	512.0	512.0
120°	552.4	552.8	552.2	551.6	551.1	550.6	550.4	550.6	550.7	550.9	551.1
122.5°	589.5	589.9	589.6	589.4	589.1	588.8	588.4	587.7	587.0	586.3	585.6
125°	644.0	644.7	644.7	644.7	644.7	644.7	644.1	642.9	641.6	640.3	639.0
127.5°	693.2	693.6	693.7	693.8	693.9	694.0	693.6	692.7	691.8	690.9	690.0
130°	725.6	726.1	725.9	725.8	725.6	725.4	724.9	724.0	723.1	722.2	721.2
132.5°	755.3	755.5	755.9	756.3	756.6	757.0	756.7	755.6	754.6	753.6	752.5
135°	799.8	800.2	800.5	801.0	801.3	801.7	801.3	800.2	799.2	798.0	797.0
137.5°	840.7	840.6	840.9	841.2	841.6	841.9	841.6	840.7	839.7	838.8	837.8
140°	865.7	865.4	865.5	865.7	865.8	866.1	865.9	865.6	865.3	864.9	864.5
142.5°	890.8	890.7	890.5	890.2	890.0	889.7	889.5	889.2	889.1	888.8	888.6
145°	925.8	925.6	925.6	925.6	925.6	925.6	925.4	925.0	924.6	924.3	924.0
147.5°	955.8	955.5	955.3	955.1	954.9	954.6	954.6	954.6	954.7	954.8	954.9
150°	974.8	974.4	974.0	973.7	973.3	973.0	973.0	973.3	973.7	974.0	974.4
152.5°	991.7	991.3	991.0	990.6	990.3	989.9	990.1	990.9	991.7	992.5	993.3
155°	1014.9	1014.3	1013.9	1013.6	1013.3	1012.8	1013.3	1014.3	1015.4	1016.5	1017.6
157.5°	1034.1	1033.6	1033.5	1033.5	1033.4	1033.4	1033.7	1034.4	1035.0	1035.6	1036.2
160°	1045.9	1045.2	1045.1	1044.9	1044.7	1044.5	1045.0	1046.0	1047.2	1048.2	1049.3
162.5°	1056.7	1055.6	1055.5	1055.3	1055.1	1054.9	1055.4	1056.5	1057.5	1058.7	1059.7
165°	1070.7	1069.7	1069.5	1069.3	1069.1	1068.9	1069.4	1070.5	1071.5	1072.6	1073.7
167.5°	1081.2	1079.9	1079.7	1079.5	1079.4	1079.2	1079.7	1080.8	1081.9	1083.0	1084.2
170°	1086.5	1085.2	1084.9	1084.8	1084.6	1084.4	1084.9	1086.2	1087.4	1088.8	1090.0
172.5°	1091.0	1089.6	1089.3	1089.0	1088.7	1088.4	1088.8	1090.1	1091.4	1092.7	1093.9
175°	1095.5	1094.1	1093.9	1093.7	1093.6	1093.4	1093.8	1094.9	1096.0	1097.1	1098.1
177.5°	1097.9	1096.8	1096.7	1096.6	1096.4	1096.3	1096.7	1097.5	1098.4	1099.3	1100.1
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	5.1	5.0	4.5	5.0	5.2	5.3	5.5	5.7	5.8	6.0	6.1
90°	2.3	3.7	5.1	6.6	8.0	9.2	10.5	11.7	13.0	13.9	14.8
92.5°	11.5	10.5	9.5	8.5	8.6	9.6	10.8	11.9	13.0	13.9	14.8
95°	45.8	45.3	44.8	44.3	40.5	33.7	26.7	19.9	13.0	13.9	14.8
97.5°	97.8	98.8	99.8	100.8	94.5	80.9	67.3	53.6	40.0	35.0	29.8
100°	136.5	137.1	137.5	138.1	138.8	139.5	140.2	140.9	141.6	114.7	87.7
102.5°	176.3	177.1	177.7	178.4	179.0	179.4	179.9	180.3	180.8	175.6	170.5
105°	240.0	240.8	241.5	242.2	242.6	242.6	242.6	242.6	242.6	242.6	242.6
107.5°	305.4	305.4	305.4	305.4	305.6	306.0	306.3	306.7	307.0	307.1	307.1
110°	348.4	348.4	348.4	348.4	348.6	348.9	349.4	349.7	350.0	349.5	348.9





TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	389.2	389.6	390.1	390.5	390.9	391.1	391.3	391.5	391.8	391.0	390.4
115°	450.3	451.2	452.1	453.0	453.6	453.7	453.9	454.0	454.2	453.6	452.8
117.5°	512.0	511.9	511.9	511.9	512.3	512.9	513.6	514.3	514.9	514.0	513.1
120°	550.9	550.7	550.6	550.4	550.6	551.1	551.6	552.2	552.8	552.4	552.0
122.5°	586.3	587.0	587.7	588.4	588.8	589.1	589.4	589.6	589.9	589.5	589.1
125°	640.3	641.6	642.9	644.1	644.7	644.7	644.7	644.7	644.7	644.0	643.3
127.5°	690.9	691.8	692.7	693.6	694.0	693.9	693.8	693.7	693.6	693.2	692.8
130°	722.2	723.1	724.0	724.9	725.4	725.6	725.8	725.9	726.1	725.6	725.0
132.5°	753.6	754.6	755.6	756.7	757.0	756.6	756.3	755.9	755.5	755.3	755.2
135°	798.0	799.2	800.2	801.3	801.7	801.3	801.0	800.5	800.2	799.8	799.5
137.5°	838.8	839.7	840.7	841.6	841.9	841.6	841.2	840.9	840.6	840.7	840.7
140°	864.9	865.3	865.6	865.9	866.1	865.8	865.7	865.5	865.4	865.7	866.1
142.5°	888.8	889.1	889.2	889.5	889.7	890.0	890.2	890.5	890.7	890.8	890.9
145°	924.3	924.6	925.0	925.4	925.6	925.6	925.6	925.6	925.6	925.8	925.9
147.5°	954.8	954.7	954.6	954.6	954.6	954.9	955.1	955.3	955.5	955.8	955.9
150°	974.0	973.7	973.3	973.0	973.0	973.3	973.7	974.0	974.4	974.8	975.2
152.5°	992.5	991.7	990.9	990.1	989.9	990.3	990.6	991.0	991.3	991.7	992.1
155°	1016.5	1015.4	1014.3	1013.3	1012.8	1013.3	1013.6	1013.9	1014.3	1014.9	1015.4
157.5°	1035.6	1035.0	1034.4	1033.7	1033.4	1033.4	1033.5	1033.5	1033.6	1034.1	1034.7
160°	1048.2	1047.2	1046.0	1045.0	1044.5	1044.7	1044.9	1045.1	1045.2	1045.9	1046.7
162.5°	1058.7	1057.5	1056.5	1055.4	1054.9	1055.1	1055.3	1055.5	1055.6	1056.7	1057.7
165°	1072.6	1071.5	1070.5	1069.4	1068.9	1069.1	1069.3	1069.5	1069.7	1070.7	1071.8
167.5°	1083.0	1081.9	1080.8	1079.7	1079.2	1079.4	1079.5	1079.7	1079.9	1081.2	1082.6
170°	1088.8	1087.4	1086.2	1084.9	1084.4	1084.6	1084.8	1084.9	1085.2	1086.5	1088.0
172.5°	1092.7	1091.4	1090.1	1088.8	1088.4	1088.7	1089.0	1089.3	1089.6	1091.0	1092.3
175°	1097.1	1096.0	1094.9	1093.8	1093.4	1093.6	1093.7	1093.9	1094.1	1095.5	1097.0
177.5°	1099.3	1098.4	1097.5	1096.7	1096.3	1096.4	1096.6	1096.7	1096.8	1097.9	1098.9
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	6.4	6.8	6.6	6.6	6.7	6.9	7.3
90°	15.7	16.6	17.4	17.9	18.4	19.0	19.6
92.5°	15.7	16.6	17.2	17.4	17.7	18.0	18.3
95°	15.7	16.6	17.1	17.1	17.1	17.1	17.1
97.5°	24.8	19.6	17.1	17.1	17.1	17.1	17.1
100°	60.8	33.8	20.0	19.2	18.5	17.9	17.1
102.5°	165.4	160.3	151.6	139.3	127.0	114.7	102.4
105°	242.6	242.6	242.5	242.3	242.1	242.0	241.7
107.5°	307.2	307.2	307.0	306.4	305.9	305.3	304.8
110°	348.4	347.9	347.7	347.9	348.1	348.2	348.4



TEST NUMBER: P333508-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	389.6	389.0	388.5	388.2	388.0	387.8	387.5
115°	452.1	451.3	450.5	449.4	448.3	447.2	446.1
117.5°	512.2	511.2	510.5	510.1	509.6	509.1	508.6
120°	551.6	551.3	550.7	549.8	548.9	548.0	547.1
122.5°	588.8	588.4	587.7	586.7	585.6	584.6	583.5
125°	642.5	641.8	641.2	640.7	640.1	639.6	639.0
127.5°	692.4	691.9	691.1	689.7	688.4	687.1	685.7
130°	724.5	724.0	723.3	722.4	721.5	720.6	719.6
132.5°	755.1	755.0	754.5	753.6	752.7	751.8	750.9
135°	799.2	798.7	798.0	797.0	795.9	794.8	793.7
137.5°	840.8	840.9	840.4	839.5	838.5	837.6	836.7
140°	866.4	866.7	866.4	865.4	864.2	863.2	862.1
142.5°	891.0	891.0	890.6	889.4	888.4	887.3	886.1
145°	926.1	926.3	925.9	924.8	923.7	922.6	921.5
147.5°	956.2	956.4	955.9	954.6	953.2	951.9	950.6
150°	975.5	975.8	975.3	973.9	972.4	970.9	969.6
152.5°	992.5	992.8	992.3	991.0	989.7	988.4	987.1
155°	1015.9	1016.5	1016.0	1014.6	1013.1	1011.7	1010.2
157.5°	1035.3	1035.8	1035.4	1034.0	1032.5	1031.0	1029.6
160°	1047.4	1048.1	1047.7	1046.4	1044.9	1043.4	1042.0
162.5°	1058.7	1059.7	1059.4	1057.9	1056.2	1054.7	1053.0
165°	1072.9	1074.0	1073.8	1072.4	1070.9	1069.5	1068.0
167.5°	1083.9	1085.2	1085.0	1083.4	1081.7	1080.1	1078.5
170°	1089.5	1091.0	1090.8	1089.2	1087.6	1086.0	1084.3
172.5°	1093.6	1094.9	1094.7	1093.1	1091.4	1089.8	1088.3
175°	1098.5	1099.8	1099.8	1098.1	1096.5	1094.9	1093.2
177.5°	1099.9	1100.9	1100.8	1099.7	1098.5	1097.4	1096.2
180°	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1	1098.1

(END OF REPORT)