

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333510-930

Luminaire Tested: **S125RDIP-S375D1035U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333510-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D1035U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1035 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4218.5 lumens  
Efficiency: N/A  
Efficacy: 113.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 37.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	48	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	13
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	11
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9
9	48	36	29	24	43	33	26	22	26	21	18	20	17	15	14	12	11	9
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	13	11	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	1.0
10°-20°	129.0	3.1
20°-30°	204.5	4.8
30°-40°	246.6	5.8
40°-50°	220.2	5.2
50°-60°	168.9	4.0
60°-70°	109.7	2.6
70°-80°	53.3	1.3
80°-90°	15.0	0.4
90°-100°	292.6	6.9
100°-110°	629.0	14.9
110°-120°	590.3	14.0
120°-130°	478.4	11.3
130°-140°	383.9	9.1
140°-150°	289.7	6.9
150°-160°	203.9	4.8
160°-170°	120.2	2.8
170°-180°	39.1	0.9
0°-30°	377.5	8.9
0°-40°	624.0	14.8
0°-60°	1013.1	24.0
0°-90°	1191.2	28.2
90°-120°	1512.0	35.8
90°-150°	2664.1	63.2
90°-180°	3027.0	71.8
0°-180°	4218.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	10
90°	19	1	19	1	19	13
95°	191	27	191	27	191	271
105°	1078	92	1078	92	1078	1072
115°	1201	164	1201	164	1201	1174
125°	947	228	947	228	947	856
135°	786	267	786	267	786	609
145°	620	311	620	311	620	394
155°	520	355	520	355	520	242
165°	456	387	456	387	456	130
175°	409	403	409	403	409	40
180°	404	404	404	404	404	



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	7.1	6.9	6.6	6.6	6.8	6.7	6.4	6.1	6.0	5.8	5.6
90°	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7	13.9	13.0	11.4
92.5°	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2	212.4	262.4	266.6
95°	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2	705.6	721.1	588.5
97.5°	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6	892.8	770.1	525.5
100°	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1	938.4	734.9	468.8
102.5°	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7	911.1	673.1	425.8
105°	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0	823.7	590.0	384.2
107.5°	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2	734.4	533.0	366.6
110°	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5	683.6	506.2	361.3



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1	645.9	490.6	361.3
115°	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0	604.7	473.7	363.8
117.5°	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7	580.2	465.4	369.2
120°	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3	566.5	461.5	374.4
122.5°	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7	554.7	458.2	379.0
125°	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2	538.8	454.1	386.6
127.5°	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1	524.2	452.2	395.3
130°	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9	514.4	450.9	400.5
132.5°	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5	506.5	450.9	406.3
135°	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3	497.3	450.9	414.3
137.5°	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5	489.0	451.8	421.6
140°	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7	485.1	452.5	424.9
142.5°	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2	481.8	453.1	426.8
145°	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1	477.0	452.5	428.9
147.5°	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8	471.9	450.4	429.7
150°	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9	468.0	448.4	429.7
152.5°	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4	463.4	445.9	429.1
155°	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6	455.8	441.2	427.3
157.5°	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8	448.6	436.3	425.2
160°	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3	442.8	433.0	423.2
162.5°	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2	437.6	429.1	421.3
165°	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3	429.7	423.2	418.3
167.5°	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8	422.1	417.5	413.8
170°	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6	417.5	414.3	411.8
172.5°	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7	412.9	410.3	409.2
175°	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4	406.9	406.1	406.1
177.5°	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0	404.3	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	5.5	5.2	5.2	4.9	4.4	4.9	5.0	5.0	4.8	4.9	4.9
90°	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8	1.6	3.3	4.9
92.5°	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9	12.1	18.9	28.9
95°	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8	27.6	34.2	43.1
97.5°	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6	45.6	50.1	59.1
100°	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0	58.6	61.9	70.8
102.5°	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7	71.6	74.2	83.8
105°	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0	92.0	96.0	104.2
107.5°	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8	114.5	118.3	125.0
110°	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8	129.4	132.6	140.0





TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8	144.4	147.0	154.3
115°	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4	166.0	168.4	175.8
117.5°	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9	186.4	189.0	196.3
120°	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0	199.4	202.7	210.0
122.5°	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7	212.4	215.0	222.3
125°	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9	229.5	233.6	240.9
127.5°	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4	243.9	249.1	258.4
130°	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9	252.3	258.9	269.4
132.5°	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4	259.4	267.3	279.2
135°	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9	270.2	280.0	293.0
137.5°	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3	282.7	291.9	304.9
140°	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1	290.6	300.4	313.3
142.5°	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3	299.1	308.1	321.1
145°	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9	312.5	320.7	332.1
147.5°	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2	326.2	333.2	343.8
150°	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7	335.3	341.0	351.6
152.5°	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8	343.8	348.9	358.1
155°	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8	354.8	359.7	367.9
157.5°	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6	365.4	369.3	376.3
160°	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8	371.9	375.2	380.9
162.5°	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6	377.8	381.1	386.1
165°	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4	385.8	388.2	392.3
167.5°	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3	392.5	394.0	396.2
170°	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2	396.4	397.2	398.8
172.5°	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8	398.4	399.2	400.7
175°	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8	401.2	402.0	402.8
177.5°	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3	403.0	403.0	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	5.1	5.4	5.4	6.0	5.7	6.2	6.4	6.4	6.5	6.7	6.9
90°	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7	15.5	16.3	17.9
92.5°	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2	104.7	78.8	66.8
95°	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2	461.5	361.3	293.0
97.5°	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6	784.7	687.2	592.2
100°	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1	961.2	877.3	792.7
102.5°	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7	1069.3	1029.1	971.8
105°	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0	1130.5	1166.3	1157.3
107.5°	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2	1076.0	1167.9	1210.4
110°	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5	1014.1	1128.9	1198.1



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1	952.9	1068.9	1150.6
115°	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0	865.2	976.6	1065.4
117.5°	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7	804.5	900.5	981.9
120°	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3	770.0	859.5	931.1
122.5°	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7	745.2	824.9	892.0
125°	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2	712.2	782.9	841.6
127.5°	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1	680.6	746.7	801.5
130°	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9	658.4	721.9	774.9
132.5°	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5	637.6	695.2	746.2
135°	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3	605.5	657.6	704.0
137.5°	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5	576.9	620.2	659.6
140°	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7	559.9	597.4	631.6
142.5°	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2	545.6	577.9	607.5
145°	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1	527.4	552.6	574.6
147.5°	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8	512.3	531.7	548.2
150°	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9	503.8	519.3	533.9
152.5°	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4	495.3	509.5	520.9
155°	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6	482.7	494.1	503.0
157.5°	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8	470.6	479.4	486.4
160°	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3	461.5	469.6	475.3
162.5°	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2	453.6	460.5	465.5
165°	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3	442.0	446.9	450.9
167.5°	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8	430.6	434.3	437.2
170°	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6	424.0	426.5	428.1
172.5°	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7	418.2	420.0	420.9
175°	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4	409.4	411.0	411.0
177.5°	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0	405.6	405.6	405.6
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	7.0	6.9	7.1	7.1	7.1	6.9	7.0	6.9	6.7	6.5	6.4
90°	17.9	17.9	18.8	18.8	18.8	17.9	17.9	17.9	16.3	15.5	14.7
92.5°	56.3	54.4	53.2	51.9	53.2	54.4	56.3	66.8	78.8	104.7	144.2
95°	235.2	210.8	204.3	191.3	204.3	210.8	235.2	293.0	361.3	461.5	585.2
97.5°	541.9	496.3	472.7	462.3	472.7	496.3	541.9	592.2	687.2	784.7	871.6
100°	736.5	678.0	647.8	634.9	647.8	678.0	736.5	792.7	877.3	961.2	1001.1
102.5°	911.7	870.1	837.3	827.5	837.3	870.1	911.7	971.8	1029.1	1069.3	1044.7
105°	1131.3	1104.5	1088.2	1078.4	1088.2	1104.5	1131.3	1157.3	1166.3	1130.5	1019.0
107.5°	1223.6	1223.4	1218.1	1211.5	1218.1	1223.4	1223.6	1210.4	1167.9	1076.0	927.2
110°	1234.7	1250.1	1255.8	1255.8	1255.8	1250.1	1234.7	1198.1	1128.9	1014.1	859.5



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1204.0	1230.6	1244.8	1250.6	1244.8	1230.6	1204.0	1150.6	1068.9	952.9	806.1
115°	1128.9	1167.9	1190.7	1201.3	1190.7	1167.9	1128.9	1065.4	976.6	865.2	739.0
117.5°	1045.4	1085.7	1108.3	1114.8	1108.3	1085.7	1045.4	981.9	900.5	804.5	695.7
120°	991.3	1030.4	1052.4	1058.9	1052.4	1030.4	991.3	931.1	859.5	770.0	672.3
122.5°	945.7	981.5	1003.6	1009.4	1003.6	981.5	945.7	892.0	824.9	745.2	654.7
125°	887.1	920.5	938.4	946.6	938.4	920.5	887.1	841.6	782.9	712.2	629.2
127.5°	842.9	872.3	889.2	892.8	889.2	872.3	842.9	801.5	746.7	680.6	603.1
130°	815.5	842.4	858.7	863.6	858.7	842.4	815.5	774.9	721.9	658.4	586.9
132.5°	786.8	813.8	828.7	834.2	828.7	813.8	786.8	746.2	695.2	637.6	570.5
135°	739.8	766.7	781.3	786.2	781.3	766.7	739.8	704.0	657.6	605.5	549.3
137.5°	691.6	716.1	729.6	734.9	729.6	716.1	691.6	659.6	620.2	576.9	531.5
140°	661.7	682.9	695.0	699.1	695.0	682.9	661.7	631.6	597.4	559.9	521.7
142.5°	633.1	650.9	662.5	665.9	662.5	650.9	633.1	607.5	577.9	545.6	513.2
145°	594.1	608.0	616.9	620.2	616.9	608.0	594.1	574.6	552.6	527.4	502.1
147.5°	563.7	574.8	580.0	581.5	580.0	574.8	563.7	548.2	531.7	512.3	491.8
150°	546.1	555.9	559.1	559.9	559.1	555.9	546.1	533.9	519.3	503.8	485.9
152.5°	531.2	539.0	542.2	543.0	542.2	539.0	531.2	520.9	509.5	495.3	479.4
155°	511.1	516.8	519.3	520.1	519.3	516.8	511.1	503.0	494.1	482.7	469.6
157.5°	492.8	497.4	499.7	499.5	499.7	497.4	492.8	486.4	479.4	470.6	459.8
160°	481.0	485.1	486.7	485.9	486.7	485.1	481.0	475.3	469.6	461.5	453.3
162.5°	469.9	473.4	473.7	473.5	473.7	473.4	469.9	465.5	460.5	453.6	446.2
165°	454.1	455.8	455.8	455.8	455.8	455.8	454.1	450.9	446.9	442.0	436.3
167.5°	438.9	440.3	439.7	439.5	439.7	440.3	438.9	437.2	434.3	430.6	426.8
170°	429.7	430.6	430.6	429.7	430.6	430.6	429.7	428.1	426.5	424.0	421.6
172.5°	421.3	422.7	421.4	420.6	421.4	422.7	421.3	420.9	420.0	418.2	415.7
175°	411.0	411.8	410.2	409.4	410.2	411.8	411.0	411.0	411.0	409.4	409.4
177.5°	405.0	405.6	403.7	403.7	403.7	405.6	405.0	405.6	405.6	405.6	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	6.4	6.2	5.7	6.0	5.4	5.4	5.1	4.9	4.9	4.8	5.0
90°	13.9	13.0	11.4	10.6	9.0	8.2	6.5	4.9	3.3	1.6	0.8
92.5°	212.4	262.4	266.6	185.7	111.2	66.8	43.0	28.9	18.9	12.1	9.9
95°	705.6	721.1	588.5	363.8	184.7	97.7	61.1	43.1	34.2	27.6	26.8
97.5°	892.8	770.1	525.5	290.4	159.2	101.6	75.2	59.1	50.1	45.6	44.6
100°	938.4	734.9	468.8	263.7	157.9	110.7	86.3	70.8	61.9	58.6	57.0
102.5°	911.1	673.1	425.8	252.7	163.8	121.7	98.0	83.8	74.2	71.6	70.7
105°	823.7	590.0	384.2	248.3	175.8	140.0	117.2	104.2	96.0	92.0	92.0
107.5°	734.4	533.0	366.6	255.8	193.7	159.1	138.5	125.0	118.3	114.5	112.8
110°	683.6	506.2	361.3	262.9	206.8	173.3	152.2	140.0	132.6	129.4	127.8



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.9	490.6	361.3	272.0	219.1	187.0	166.5	154.3	147.0	144.4	142.8
115°	604.7	473.7	363.8	285.7	238.5	208.4	188.0	175.8	168.4	166.0	164.4
117.5°	580.2	465.4	369.2	301.3	258.4	229.8	210.2	196.3	189.0	186.4	183.9
120°	566.5	461.5	374.4	311.7	272.6	244.2	223.8	210.0	202.7	199.4	197.0
122.5°	554.7	458.2	379.0	323.4	286.3	257.9	237.5	222.3	215.0	212.4	210.7
125°	538.8	454.1	386.6	339.4	304.4	277.5	256.4	240.9	233.6	229.5	227.9
127.5°	524.2	452.2	395.3	354.0	321.8	296.0	274.8	258.4	249.1	243.9	241.4
130°	514.4	450.9	400.5	363.8	332.9	307.6	286.5	269.4	258.9	252.3	249.9
132.5°	506.5	450.9	406.3	372.3	343.3	318.0	296.9	279.2	267.3	259.4	256.4
135°	497.3	450.9	414.3	384.2	357.3	332.1	310.1	293.0	280.0	270.2	266.9
137.5°	489.0	451.8	421.6	393.0	367.2	344.3	321.6	304.9	291.9	282.7	280.3
140°	485.1	452.5	424.9	398.8	374.4	350.8	328.8	313.3	300.4	290.6	288.1
142.5°	481.8	453.1	426.8	402.0	379.0	356.6	336.0	321.1	308.1	299.1	297.3
145°	477.0	452.5	428.9	406.9	386.6	365.4	346.7	332.1	320.7	312.5	310.9
147.5°	471.9	450.4	429.7	409.9	391.5	372.9	356.4	343.8	333.2	326.2	325.2
150°	468.0	448.4	429.7	411.8	394.8	376.8	363.0	351.6	341.0	335.3	333.7
152.5°	463.4	445.9	429.1	413.1	398.0	381.4	368.8	358.1	348.9	343.8	342.8
155°	455.8	441.2	427.3	414.3	401.2	387.4	376.0	367.9	359.7	354.8	354.8
157.5°	448.6	436.3	425.2	415.1	404.0	392.2	383.5	376.3	369.3	365.4	365.6
160°	442.8	433.0	423.2	415.1	405.3	394.8	387.4	380.9	375.2	371.9	372.8
162.5°	437.6	429.1	421.3	414.4	406.6	397.4	391.3	386.1	381.1	377.8	378.6
165°	429.7	423.2	418.3	413.4	406.9	400.5	395.6	392.3	388.2	385.8	387.4
167.5°	422.1	417.5	413.8	411.5	406.9	401.5	398.5	396.2	394.0	392.5	393.3
170°	417.5	414.3	411.8	410.2	406.9	402.8	400.5	398.8	397.2	396.4	397.2
172.5°	412.9	410.3	409.2	408.9	406.3	402.8	401.7	400.7	399.2	398.4	399.8
175°	406.9	406.1	406.1	406.9	405.3	402.8	402.8	402.8	402.0	401.2	402.8
177.5°	404.3	403.7	403.7	405.0	404.3	403.0	403.0	403.7	403.0	403.0	404.3
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	5.0	4.9	4.4	4.9	5.2	5.2	5.5	5.6	5.8	6.0	6.1
90°	1.6	3.3	4.9	6.5	8.2	9.0	10.6	11.4	13.0	13.9	14.7
92.5°	12.1	18.9	28.9	43.0	66.8	111.2	185.7	266.6	262.4	212.4	144.2
95°	27.6	34.2	43.1	61.1	97.7	184.7	363.8	588.5	721.1	705.6	585.2
97.5°	45.6	50.1	59.1	75.2	101.6	159.2	290.4	525.5	770.1	892.8	871.6
100°	58.6	61.9	70.8	86.3	110.7	157.9	263.7	468.8	734.9	938.4	1001.1
102.5°	71.6	74.2	83.8	98.0	121.7	163.8	252.7	425.8	673.1	911.1	1044.7
105°	92.0	96.0	104.2	117.2	140.0	175.8	248.3	384.2	590.0	823.7	1019.0
107.5°	114.5	118.3	125.0	138.5	159.1	193.7	255.8	366.6	533.0	734.4	927.2
110°	129.4	132.6	140.0	152.2	173.3	206.8	262.9	361.3	506.2	683.6	859.5





TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.4	147.0	154.3	166.5	187.0	219.1	272.0	361.3	490.6	645.9	806.1
115°	166.0	168.4	175.8	188.0	208.4	238.5	285.7	363.8	473.7	604.7	739.0
117.5°	186.4	189.0	196.3	210.2	229.8	258.4	301.3	369.2	465.4	580.2	695.7
120°	199.4	202.7	210.0	223.8	244.2	272.6	311.7	374.4	461.5	566.5	672.3
122.5°	212.4	215.0	222.3	237.5	257.9	286.3	323.4	379.0	458.2	554.7	654.7
125°	229.5	233.6	240.9	256.4	277.5	304.4	339.4	386.6	454.1	538.8	629.2
127.5°	243.9	249.1	258.4	274.8	296.0	321.8	354.0	395.3	452.2	524.2	603.1
130°	252.3	258.9	269.4	286.5	307.6	332.9	363.8	400.5	450.9	514.4	586.9
132.5°	259.4	267.3	279.2	296.9	318.0	343.3	372.3	406.3	450.9	506.5	570.5
135°	270.2	280.0	293.0	310.1	332.1	357.3	384.2	414.3	450.9	497.3	549.3
137.5°	282.7	291.9	304.9	321.6	344.3	367.2	393.0	421.6	451.8	489.0	531.5
140°	290.6	300.4	313.3	328.8	350.8	374.4	398.8	424.9	452.5	485.1	521.7
142.5°	299.1	308.1	321.1	336.0	356.6	379.0	402.0	426.8	453.1	481.8	513.2
145°	312.5	320.7	332.1	346.7	365.4	386.6	406.9	428.9	452.5	477.0	502.1
147.5°	326.2	333.2	343.8	356.4	372.9	391.5	409.9	429.7	450.4	471.9	491.8
150°	335.3	341.0	351.6	363.0	376.8	394.8	411.8	429.7	448.4	468.0	485.9
152.5°	343.8	348.9	358.1	368.8	381.4	398.0	413.1	429.1	445.9	463.4	479.4
155°	354.8	359.7	367.9	376.0	387.4	401.2	414.3	427.3	441.2	455.8	469.6
157.5°	365.4	369.3	376.3	383.5	392.2	404.0	415.1	425.2	436.3	448.6	459.8
160°	371.9	375.2	380.9	387.4	394.8	405.3	415.1	423.2	433.0	442.8	453.3
162.5°	377.8	381.1	386.1	391.3	397.4	406.6	414.4	421.3	429.1	437.6	446.2
165°	385.8	388.2	392.3	395.6	400.5	406.9	413.4	418.3	423.2	429.7	436.3
167.5°	392.5	394.0	396.2	398.5	401.5	406.9	411.5	413.8	417.5	422.1	426.8
170°	396.4	397.2	398.8	400.5	402.8	406.9	410.2	411.8	414.3	417.5	421.6
172.5°	398.4	399.2	400.7	401.7	402.8	406.3	408.9	409.2	410.3	412.9	415.7
175°	401.2	402.0	402.8	402.8	402.8	405.3	406.9	406.1	406.1	406.9	409.4
177.5°	403.0	403.0	403.7	403.0	403.0	404.3	405.0	403.7	403.7	404.3	405.0
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	6.4	6.7	6.8	6.6	6.6	6.9	7.1
90°	15.5	16.3	17.9	17.9	17.9	18.8	18.8
92.5°	104.7	78.8	66.8	56.3	54.4	53.2	51.9
95°	461.5	361.3	293.0	235.2	210.8	204.3	191.3
97.5°	784.7	687.2	592.2	541.9	496.3	472.7	462.3
100°	961.2	877.3	792.7	736.5	678.0	647.8	634.9
102.5°	1069.3	1029.1	971.8	911.7	870.1	837.3	827.5
105°	1130.5	1166.3	1157.3	1131.3	1104.5	1088.2	1078.4
107.5°	1076.0	1167.9	1210.4	1223.6	1223.4	1218.1	1211.5
110°	1014.1	1128.9	1198.1	1234.7	1250.1	1255.8	1255.8



TEST NUMBER: P333510-930

CATALOG NUMBER: S125RDIP-S375D1035U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	952.9	1068.9	1150.6	1204.0	1230.6	1244.8	1250.6
115°	865.2	976.6	1065.4	1128.9	1167.9	1190.7	1201.3
117.5°	804.5	900.5	981.9	1045.4	1085.7	1108.3	1114.8
120°	770.0	859.5	931.1	991.3	1030.4	1052.4	1058.9
122.5°	745.2	824.9	892.0	945.7	981.5	1003.6	1009.4
125°	712.2	782.9	841.6	887.1	920.5	938.4	946.6
127.5°	680.6	746.7	801.5	842.9	872.3	889.2	892.8
130°	658.4	721.9	774.9	815.5	842.4	858.7	863.6
132.5°	637.6	695.2	746.2	786.8	813.8	828.7	834.2
135°	605.5	657.6	704.0	739.8	766.7	781.3	786.2
137.5°	576.9	620.2	659.6	691.6	716.1	729.6	734.9
140°	559.9	597.4	631.6	661.7	682.9	695.0	699.1
142.5°	545.6	577.9	607.5	633.1	650.9	662.5	665.9
145°	527.4	552.6	574.6	594.1	608.0	616.9	620.2
147.5°	512.3	531.7	548.2	563.7	574.8	580.0	581.5
150°	503.8	519.3	533.9	546.1	555.9	559.1	559.9
152.5°	495.3	509.5	520.9	531.2	539.0	542.2	543.0
155°	482.7	494.1	503.0	511.1	516.8	519.3	520.1
157.5°	470.6	479.4	486.4	492.8	497.4	499.7	499.5
160°	461.5	469.6	475.3	481.0	485.1	486.7	485.9
162.5°	453.6	460.5	465.5	469.9	473.4	473.7	473.5
165°	442.0	446.9	450.9	454.1	455.8	455.8	455.8
167.5°	430.6	434.3	437.2	438.9	440.3	439.7	439.5
170°	424.0	426.5	428.1	429.7	430.6	430.6	429.7
172.5°	418.2	420.0	420.9	421.3	422.7	421.4	420.6
175°	409.4	411.0	411.0	411.0	411.8	410.2	409.4
177.5°	405.6	405.6	405.6	405.0	405.6	403.7	403.7
180°	403.7	403.7	403.7	403.7	403.7	403.7	403.7

(END OF REPORT)