

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333516-930

Luminaire Tested: **S125RDIP-S375D1205U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333516-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D1205U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1205 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4715.3 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 42.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33	25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29	22
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	26	25	24	18
3	77	68	61	56	68	61	55	50	48	44	40	35	33	30	24	22	21	16
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	14
5	65	54	46	40	57	48	41	37	38	33	30	28	25	23	19	17	16	12
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14	11
7	55	43	36	30	49	39	32	28	31	26	22	23	20	17	16	14	12	9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	13	11	8
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	0.9
10°-20°	129.0	2.7
20°-30°	204.5	4.3
30°-40°	246.6	5.2
40°-50°	220.2	4.7
50°-60°	168.9	3.6
60°-70°	109.7	2.3
70°-80°	53.3	1.1
80°-90°	15.4	0.3
90°-100°	340.6	7.2
100°-110°	732.2	15.5
110°-120°	687.1	14.6
120°-130°	556.9	11.8
130°-140°	446.9	9.5
140°-150°	337.2	7.2
150°-160°	237.4	5.0
160°-170°	139.9	3.0
170°-180°	45.5	1.0
0°-30°	377.5	8.0
0°-40°	624.0	13.2
0°-60°	1013.1	21.5
0°-90°	1191.6	25.3
90°-120°	1759.9	37.3
90°-150°	3100.9	65.8
90°-180°	3524.0	74.7
0°-180°	4715.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	11
90°	22	1	22	1	22	15
95°	223	31	223	31	223	315
105°	1255	107	1255	107	1255	1248
115°	1398	191	1398	191	1398	1366
125°	1102	265	1102	265	1102	997
135°	915	311	915	311	915	709
145°	722	362	722	362	722	459
155°	605	413	605	413	605	282
165°	530	451	530	451	530	152
175°	476	469	476	469	476	46
180°	470	470	470	470	470	



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	7.7	7.5	7.2	7.2	7.3	7.3	6.9	6.6	6.4	6.2	6.0
90°	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0	16.1	15.2	13.3
92.5°	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9	247.3	305.4	310.4
95°	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1	821.3	839.4	684.9
97.5°	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4	1039.3	896.3	611.6
100°	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2	1092.3	855.4	545.7
102.5°	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0	1060.5	783.4	495.6
105°	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1	958.7	686.8	447.1
107.5°	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2	854.9	620.3	426.6
110°	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4	795.7	589.2	420.6



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2	751.8	571.0	420.6
115°	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2	703.8	551.4	423.5
117.5°	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8	675.2	541.7	429.7
120°	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5	659.3	537.1	435.8
122.5°	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1	645.7	533.4	441.1
125°	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3	627.1	528.6	450.0
127.5°	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0	610.1	526.4	460.0
130°	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1	598.8	524.8	466.1
132.5°	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1	589.6	524.8	472.9
135°	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4	578.9	524.8	482.2
137.5°	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6	569.2	525.9	490.7
140°	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2	564.6	526.7	494.5
142.5°	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4	560.8	527.5	496.8
145°	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5	555.1	526.7	499.3
147.5°	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4	549.3	524.2	500.2
150°	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6	544.7	522.0	500.2
152.5°	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0	539.4	518.9	499.5
155°	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6	530.5	513.5	497.3
157.5°	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2	522.2	507.8	494.9
160°	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7	515.4	504.0	492.6
162.5°	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3	509.3	499.5	490.3
165°	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8	500.2	492.6	486.9
167.5°	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8	491.3	486.0	481.6
170°	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7	486.0	482.2	479.4
172.5°	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9	480.7	477.7	476.3
175°	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5	473.7	472.7	472.7
177.5°	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4	470.7	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	6.0	5.5	5.5	5.1	4.6	5.0	5.1	5.0	4.9	5.0	5.1
90°	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0	1.9	3.8	5.7
92.5°	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6	14.0	22.0	33.8
95°	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2	32.2	39.8	50.2
97.5°	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9	53.1	58.4	68.8
100°	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3	68.2	72.0	82.4
102.5°	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3	83.4	86.4	97.6
105°	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0	107.0	111.8	121.2
107.5°	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3	133.2	137.7	145.5
110°	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7	150.7	154.4	163.0



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2	168.0	171.0	179.6
115°	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4	193.2	196.1	204.6
117.5°	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1	217.0	220.0	228.5
120°	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3	232.1	235.9	244.4
122.5°	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2	247.3	250.3	258.8
125°	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2	267.2	271.9	280.4
127.5°	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0	283.8	289.9	300.7
130°	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8	293.7	301.3	313.6
132.5°	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4	302.0	311.1	325.0
135°	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7	314.5	325.9	341.0
137.5°	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3	329.1	339.7	354.9
140°	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3	338.2	349.6	364.8
142.5°	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9	348.1	358.7	373.8
145°	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9	363.8	373.2	386.5
147.5°	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5	379.7	387.8	400.1
150°	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4	390.3	397.0	409.3
152.5°	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0	400.1	406.0	416.9
155°	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0	413.0	418.7	428.2
157.5°	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6	425.3	429.9	438.1
160°	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9	432.9	436.8	443.4
162.5°	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7	439.8	443.5	449.4
165°	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9	449.1	451.9	456.6
167.5°	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8	456.8	458.5	461.1
170°	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3	461.4	462.3	464.2
172.5°	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4	463.7	464.6	466.4
175°	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0	467.0	468.0	469.0
177.5°	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7	469.1	469.1	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	5.3	5.6	5.7	6.4	6.1	6.7	6.8	6.8	7.1	7.3	7.5
90°	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0	18.0	18.9	20.9
92.5°	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9	121.8	91.7	77.7
95°	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1	537.1	420.6	341.0
97.5°	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4	913.5	800.0	689.3
100°	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2	1118.8	1021.2	922.7
102.5°	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0	1244.6	1197.8	1131.1
105°	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1	1315.9	1357.6	1347.1
107.5°	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2	1252.4	1359.4	1408.9
110°	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4	1180.4	1313.9	1394.5



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2	1109.1	1244.2	1339.1
115°	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2	1007.1	1136.8	1240.1
117.5°	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8	936.4	1048.1	1142.9
120°	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5	896.2	1000.4	1083.8
122.5°	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1	867.4	960.3	1038.3
125°	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3	828.9	911.3	979.6
127.5°	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0	792.1	869.1	932.9
130°	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1	766.4	840.3	901.9
132.5°	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1	742.2	809.2	868.5
135°	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4	704.8	765.5	819.5
137.5°	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6	671.5	721.9	767.8
140°	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2	651.8	695.4	735.2
142.5°	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4	635.1	672.6	707.1
145°	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5	613.8	643.3	668.8
147.5°	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4	596.2	618.8	638.1
150°	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6	586.4	604.4	621.4
152.5°	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0	576.6	593.0	606.3
155°	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6	561.7	575.0	585.5
157.5°	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2	547.7	558.0	566.1
160°	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7	537.1	546.6	553.3
162.5°	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3	528.1	536.0	541.8
165°	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8	514.4	520.1	524.8
167.5°	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8	501.2	505.5	508.9
170°	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7	493.6	496.4	498.3
172.5°	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9	486.7	488.9	490.0
175°	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5	476.5	478.4	478.4
177.5°	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4	472.1	472.1	472.1
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	7.7	7.5	7.7	7.7	7.7	7.5	7.7	7.5	7.3	7.1	6.8
90°	20.9	20.9	21.8	21.8	21.8	20.9	20.9	20.9	18.9	18.0	17.0
92.5°	65.6	63.3	62.0	60.4	62.0	63.3	65.6	77.7	91.7	121.8	167.9
95°	273.8	245.3	237.8	222.7	237.8	245.3	273.8	341.0	420.6	537.1	681.1
97.5°	630.7	577.7	550.2	538.1	550.2	577.7	630.7	689.3	800.0	913.5	1014.4
100°	857.4	789.1	754.1	738.9	754.1	789.1	857.4	922.7	1021.2	1118.8	1165.2
102.5°	1061.2	1012.7	974.6	963.3	974.6	1012.7	1061.2	1131.1	1197.8	1244.6	1216.0
105°	1316.8	1285.6	1266.6	1255.2	1266.6	1285.6	1316.8	1347.1	1357.6	1315.9	1186.1
107.5°	1424.2	1424.1	1417.8	1410.2	1417.8	1424.1	1424.2	1408.9	1359.4	1252.4	1079.2
110°	1437.1	1455.1	1461.8	1461.8	1461.8	1455.1	1437.1	1394.5	1313.9	1180.4	1000.4



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1401.5	1432.4	1448.9	1455.7	1448.9	1432.4	1401.5	1339.1	1244.2	1109.1	938.2
115°	1313.9	1359.4	1385.9	1398.2	1385.9	1359.4	1313.9	1240.1	1136.8	1007.1	860.2
117.5°	1216.8	1263.8	1290.1	1297.6	1290.1	1263.8	1216.8	1142.9	1048.1	936.4	809.8
120°	1153.9	1199.3	1224.9	1232.5	1224.9	1199.3	1153.9	1083.8	1000.4	896.2	782.5
122.5°	1100.8	1142.5	1168.1	1174.9	1168.1	1142.5	1100.8	1038.3	960.3	867.4	762.1
125°	1032.6	1071.5	1092.3	1101.8	1092.3	1071.5	1032.6	979.6	911.3	828.9	732.3
127.5°	981.0	1015.4	1035.1	1039.3	1035.1	1015.4	981.0	932.9	869.1	792.1	702.0
130°	949.3	980.5	999.5	1005.1	999.5	980.5	949.3	901.9	840.3	766.4	683.1
132.5°	915.9	947.1	964.6	971.0	964.6	947.1	915.9	868.5	809.2	742.2	664.1
135°	861.1	892.4	909.5	915.2	909.5	892.4	861.1	819.5	765.5	704.8	639.4
137.5°	805.0	833.5	849.2	855.4	849.2	833.5	805.0	767.8	721.9	671.5	618.6
140°	770.2	794.8	809.0	813.8	809.0	794.8	770.2	735.2	695.4	651.8	607.2
142.5°	736.9	757.7	771.1	775.1	771.1	757.7	736.9	707.1	672.6	635.1	597.4
145°	691.5	707.7	718.1	721.9	718.1	707.7	691.5	668.8	643.3	613.8	584.5
147.5°	656.2	669.0	675.1	676.8	675.1	669.0	656.2	638.1	618.8	596.2	572.4
150°	635.7	647.0	650.9	651.8	650.9	647.0	635.7	621.4	604.4	586.4	565.6
152.5°	618.2	627.3	631.1	632.1	631.1	627.3	618.2	606.3	593.0	576.6	558.0
155°	594.9	601.5	604.4	605.4	604.4	601.5	594.9	585.5	575.0	561.7	546.6
157.5°	573.5	579.0	581.6	581.5	581.6	579.0	573.5	566.1	558.0	547.7	535.2
160°	559.9	564.6	566.6	565.6	566.6	564.6	559.9	553.3	546.6	537.1	527.7
162.5°	547.0	551.0	551.4	551.1	551.4	551.0	547.0	541.8	536.0	528.1	519.3
165°	528.6	530.5	530.5	530.5	530.5	530.5	528.6	524.8	520.1	514.4	507.8
167.5°	510.8	512.5	511.8	511.6	511.8	512.5	510.8	508.9	505.5	501.2	496.8
170°	500.2	501.2	501.2	500.2	501.2	501.2	500.2	498.3	496.4	493.6	490.7
172.5°	490.3	492.0	490.6	489.6	490.6	492.0	490.3	490.0	488.9	486.7	483.9
175°	478.4	479.4	477.4	476.5	477.4	479.4	478.4	478.4	478.4	476.5	476.5
177.5°	471.4	472.1	469.9	469.9	469.9	472.1	471.4	472.1	472.1	472.1	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	6.8	6.7	6.1	6.4	5.7	5.6	5.3	5.1	5.0	4.9	5.0
90°	16.1	15.2	13.3	12.3	10.4	9.5	7.6	5.7	3.8	1.9	1.0
92.5°	247.3	305.4	310.4	216.2	129.4	77.7	50.1	33.8	22.0	14.0	11.6
95°	821.3	839.4	684.9	423.5	215.1	113.7	71.0	50.2	39.8	32.2	31.2
97.5°	1039.3	896.3	611.6	338.0	185.3	118.2	87.6	68.8	58.4	53.1	51.9
100°	1092.3	855.4	545.7	307.0	183.8	128.8	100.4	82.4	72.0	68.2	66.3
102.5°	1060.5	783.4	495.6	294.1	190.6	141.7	114.1	97.6	86.4	83.4	82.3
105°	958.7	686.8	447.1	288.9	204.6	163.0	136.4	121.2	111.8	107.0	107.0
107.5°	854.9	620.3	426.6	297.7	225.4	185.1	161.3	145.5	137.7	133.2	131.3
110°	795.7	589.2	420.6	306.0	240.6	201.8	177.2	163.0	154.4	150.7	148.7



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	751.8	571.0	420.6	316.6	255.0	217.7	193.8	179.6	171.0	168.0	166.2
115°	703.8	551.4	423.5	332.5	277.6	242.6	218.8	204.6	196.1	193.2	191.4
117.5°	675.2	541.7	429.7	350.7	300.7	267.5	244.6	228.5	220.0	217.0	214.1
120°	659.3	537.1	435.8	362.8	317.4	284.2	260.5	244.4	235.9	232.1	229.3
122.5°	645.7	533.4	441.1	376.5	333.3	300.1	276.5	258.8	250.3	247.3	245.2
125°	627.1	528.6	450.0	395.0	354.3	323.0	298.4	280.4	271.9	267.2	265.2
127.5°	610.1	526.4	460.0	412.1	374.5	344.5	319.8	300.7	289.9	283.8	281.0
130°	598.8	524.8	466.1	423.5	387.4	358.1	333.5	313.6	301.3	293.7	290.8
132.5°	589.6	524.8	472.9	433.3	399.6	370.2	345.6	325.0	311.1	302.0	298.4
135°	578.9	524.8	482.2	447.1	415.9	386.5	360.9	341.0	325.9	314.5	310.7
137.5°	569.2	525.9	490.7	457.4	427.5	400.7	374.4	354.9	339.7	329.1	326.3
140°	564.6	526.7	494.5	464.2	435.8	408.3	382.7	364.8	349.6	338.2	335.3
142.5°	560.8	527.5	496.8	468.0	441.1	415.2	391.1	373.8	358.7	348.1	345.9
145°	555.1	526.7	499.3	473.7	450.0	425.3	403.6	386.5	373.2	363.8	361.9
147.5°	549.3	524.2	500.2	477.1	455.7	434.1	414.9	400.1	387.8	379.7	378.5
150°	544.7	522.0	500.2	479.4	459.4	438.6	422.5	409.3	397.0	390.3	388.4
152.5°	539.4	518.9	499.5	480.9	463.3	443.9	429.3	416.9	406.0	400.1	399.0
155°	530.5	513.5	497.3	482.2	467.0	450.9	437.7	428.2	418.7	413.0	413.0
157.5°	522.2	507.8	494.9	483.1	470.3	456.4	446.4	438.1	429.9	425.3	425.6
160°	515.4	504.0	492.6	483.1	471.8	459.4	450.9	443.4	436.8	432.9	433.9
162.5°	509.3	499.5	490.3	482.4	473.3	462.5	455.5	449.4	443.5	439.8	440.7
165°	500.2	492.6	486.9	481.3	473.7	466.1	460.4	456.6	451.9	449.1	450.9
167.5°	491.3	486.0	481.6	479.0	473.7	467.4	463.8	461.1	458.5	456.8	457.8
170°	486.0	482.2	479.4	477.4	473.7	469.0	466.1	464.2	462.3	461.4	462.3
172.5°	480.7	477.7	476.3	476.0	472.9	469.0	467.6	466.4	464.6	463.7	465.4
175°	473.7	472.7	472.7	473.7	471.8	469.0	469.0	469.0	468.0	467.0	469.0
177.5°	470.7	469.9	469.9	471.4	470.7	469.1	469.1	469.9	469.1	469.1	470.7
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	5.1	5.0	4.6	5.1	5.5	5.5	6.0	6.0	6.2	6.4	6.6
90°	1.9	3.8	5.7	7.6	9.5	10.4	12.3	13.3	15.2	16.1	17.0
92.5°	14.0	22.0	33.8	50.1	77.7	129.4	216.2	310.4	305.4	247.3	167.9
95°	32.2	39.8	50.2	71.0	113.7	215.1	423.5	684.9	839.4	821.3	681.1
97.5°	53.1	58.4	68.8	87.6	118.2	185.3	338.0	611.6	896.3	1039.3	1014.4
100°	68.2	72.0	82.4	100.4	128.8	183.8	307.0	545.7	855.4	1092.3	1165.2
102.5°	83.4	86.4	97.6	114.1	141.7	190.6	294.1	495.6	783.4	1060.5	1216.0
105°	107.0	111.8	121.2	136.4	163.0	204.6	288.9	447.1	686.8	958.7	1186.1
107.5°	133.2	137.7	145.5	161.3	185.1	225.4	297.7	426.6	620.3	854.9	1079.2
110°	150.7	154.4	163.0	177.2	201.8	240.6	306.0	420.6	589.2	795.7	1000.4



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	168.0	171.0	179.6	193.8	217.7	255.0	316.6	420.6	571.0	751.8	938.2
115°	193.2	196.1	204.6	218.8	242.6	277.6	332.5	423.5	551.4	703.8	860.2
117.5°	217.0	220.0	228.5	244.6	267.5	300.7	350.7	429.7	541.7	675.2	809.8
120°	232.1	235.9	244.4	260.5	284.2	317.4	362.8	435.8	537.1	659.3	782.5
122.5°	247.3	250.3	258.8	276.5	300.1	333.3	376.5	441.1	533.4	645.7	762.1
125°	267.2	271.9	280.4	298.4	323.0	354.3	395.0	450.0	528.6	627.1	732.3
127.5°	283.8	289.9	300.7	319.8	344.5	374.5	412.1	460.0	526.4	610.1	702.0
130°	293.7	301.3	313.6	333.5	358.1	387.4	423.5	466.1	524.8	598.8	683.1
132.5°	302.0	311.1	325.0	345.6	370.2	399.6	433.3	472.9	524.8	589.6	664.1
135°	314.5	325.9	341.0	360.9	386.5	415.9	447.1	482.2	524.8	578.9	639.4
137.5°	329.1	339.7	354.9	374.4	400.7	427.5	457.4	490.7	525.9	569.2	618.6
140°	338.2	349.6	364.8	382.7	408.3	435.8	464.2	494.5	526.7	564.6	607.2
142.5°	348.1	358.7	373.8	391.1	415.2	441.1	468.0	496.8	527.5	560.8	597.4
145°	363.8	373.2	386.5	403.6	425.3	450.0	473.7	499.3	526.7	555.1	584.5
147.5°	379.7	387.8	400.1	414.9	434.1	455.7	477.1	500.2	524.2	549.3	572.4
150°	390.3	397.0	409.3	422.5	438.6	459.4	479.4	500.2	522.0	544.7	565.6
152.5°	400.1	406.0	416.9	429.3	443.9	463.3	480.9	499.5	518.9	539.4	558.0
155°	413.0	418.7	428.2	437.7	450.9	467.0	482.2	497.3	513.5	530.5	546.6
157.5°	425.3	429.9	438.1	446.4	456.4	470.3	483.1	494.9	507.8	522.2	535.2
160°	432.9	436.8	443.4	450.9	459.4	471.8	483.1	492.6	504.0	515.4	527.7
162.5°	439.8	443.5	449.4	455.5	462.5	473.3	482.4	490.3	499.5	509.3	519.3
165°	449.1	451.9	456.6	460.4	466.1	473.7	481.3	486.9	492.6	500.2	507.8
167.5°	456.8	458.5	461.1	463.8	467.4	473.7	479.0	481.6	486.0	491.3	496.8
170°	461.4	462.3	464.2	466.1	469.0	473.7	477.4	479.4	482.2	486.0	490.7
172.5°	463.7	464.6	466.4	467.6	469.0	472.9	476.0	476.3	477.7	480.7	483.9
175°	467.0	468.0	469.0	469.0	469.0	471.8	473.7	472.7	472.7	473.7	476.5
177.5°	469.1	469.1	469.9	469.1	469.1	470.7	471.4	469.9	469.9	470.7	471.4
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9	469.9



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	6.9	7.3	7.3	7.2	7.2	7.5	7.7
90°	18.0	18.9	20.9	20.9	20.9	21.8	21.8
92.5°	121.8	91.7	77.7	65.6	63.3	62.0	60.4
95°	537.1	420.6	341.0	273.8	245.3	237.8	222.7
97.5°	913.5	800.0	689.3	630.7	577.7	550.2	538.1
100°	1118.8	1021.2	922.7	857.4	789.1	754.1	738.9
102.5°	1244.6	1197.8	1131.1	1061.2	1012.7	974.6	963.3
105°	1315.9	1357.6	1347.1	1316.8	1285.6	1266.6	1255.2
107.5°	1252.4	1359.4	1408.9	1424.2	1424.1	1417.8	1410.2
110°	1180.4	1313.9	1394.5	1437.1	1455.1	1461.8	1461.8



TEST NUMBER: P333516-930

CATALOG NUMBER: S125RDIP-S375D1205U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1109.1	1244.2	1339.1	1401.5	1432.4	1448.9	1455.7
115°	1007.1	1136.8	1240.1	1313.9	1359.4	1385.9	1398.2
117.5°	936.4	1048.1	1142.9	1216.8	1263.8	1290.1	1297.6
120°	896.2	1000.4	1083.8	1153.9	1199.3	1224.9	1232.5
122.5°	867.4	960.3	1038.3	1100.8	1142.5	1168.1	1174.9
125°	828.9	911.3	979.6	1032.6	1071.5	1092.3	1101.8
127.5°	792.1	869.1	932.9	981.0	1015.4	1035.1	1039.3
130°	766.4	840.3	901.9	949.3	980.5	999.5	1005.1
132.5°	742.2	809.2	868.5	915.9	947.1	964.6	971.0
135°	704.8	765.5	819.5	861.1	892.4	909.5	915.2
137.5°	671.5	721.9	767.8	805.0	833.5	849.2	855.4
140°	651.8	695.4	735.2	770.2	794.8	809.0	813.8
142.5°	635.1	672.6	707.1	736.9	757.7	771.1	775.1
145°	613.8	643.3	668.8	691.5	707.7	718.1	721.9
147.5°	596.2	618.8	638.1	656.2	669.0	675.1	676.8
150°	586.4	604.4	621.4	635.7	647.0	650.9	651.8
152.5°	576.6	593.0	606.3	618.2	627.3	631.1	632.1
155°	561.7	575.0	585.5	594.9	601.5	604.4	605.4
157.5°	547.7	558.0	566.1	573.5	579.0	581.6	581.5
160°	537.1	546.6	553.3	559.9	564.6	566.6	565.6
162.5°	528.1	536.0	541.8	547.0	551.0	551.4	551.1
165°	514.4	520.1	524.8	528.6	530.5	530.5	530.5
167.5°	501.2	505.5	508.9	510.8	512.5	511.8	511.6
170°	493.6	496.4	498.3	500.2	501.2	501.2	500.2
172.5°	486.7	488.9	490.0	490.3	492.0	490.6	489.6
175°	476.5	478.4	478.4	478.4	479.4	477.4	476.5
177.5°	472.1	472.1	472.1	471.4	472.1	469.9	469.9
180°	469.9	469.9	469.9	469.9	469.9	469.9	469.9

(END OF REPORT)