

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333492-930

Luminaire Tested: **S125RDIP-S375D365U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333492-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIP-S375D365U930-4F0-1E-UDD-A4  
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 365 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2261.5 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 20.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	88	91	88	85	82	75	73	71	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43	39
3	83	73	66	61	76	68	62	57	59	54	50	50	46	43	42	39	37	33
4	76	65	57	52	70	61	54	49	52	47	43	45	41	38	37	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	42	37	33	36	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	1.9
10°-20°	129.0	5.7
20°-30°	204.5	9.0
30°-40°	246.6	10.9
40°-50°	220.2	9.7
50°-60°	168.9	7.5
60°-70°	109.7	4.9
70°-80°	53.3	2.4
80°-90°	13.5	0.6
90°-100°	103.6	4.6
100°-110°	222.7	9.8
110°-120°	209.0	9.2
120°-130°	169.4	7.5
130°-140°	135.9	6.0
140°-150°	102.6	4.5
150°-160°	72.2	3.2
160°-170°	42.6	1.9
170°-180°	13.8	0.6
0°-30°	377.5	16.7
0°-40°	624.0	27.6
0°-60°	1013.1	44.8
0°-90°	1189.8	52.6
90°-120°	535.3	23.7
90°-150°	943.1	41.7
90°-180°	1072.0	47.4
0°-180°	2261.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	10
90°	7	0	7	0	7	5
95°	68	10	68	10	68	96
105°	382	32	382	32	382	380
115°	425	58	425	58	425	416
125°	335	81	335	81	335	303
135°	278	94	278	94	278	216
145°	220	110	220	110	220	140
155°	184	126	184	126	184	86
165°	161	137	161	137	161	46
175°	145	143	145	143	145	14
180°	143	143	143	143	143	



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	4.6	4.5	4.3	4.3	4.4	4.6	4.4	4.2	4.2	4.1	4.2
90°	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2	4.9	4.6	4.0
92.5°	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0	75.2	92.9	94.4
95°	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2	249.8	255.3	208.3
97.5°	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5	316.1	272.6	186.1
100°	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4	332.2	260.2	166.0
102.5°	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8	322.5	238.3	150.7
105°	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8	291.6	208.9	136.0
107.5°	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2	260.0	188.7	129.8
110°	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3	242.1	179.2	127.9



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4	228.7	173.7	127.9
115°	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6	214.1	167.7	128.8
117.5°	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3	205.4	164.8	130.7
120°	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0	200.6	163.4	132.6
122.5°	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8	196.4	162.2	134.1
125°	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7	190.8	160.8	136.9
127.5°	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5	185.6	160.1	139.9
130°	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7	182.1	159.6	141.8
132.5°	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9	179.4	159.6	143.8
135°	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5	176.0	159.6	146.7
137.5°	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2	173.1	160.0	149.3
140°	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7	171.7	160.2	150.4
142.5°	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7	170.6	160.5	151.1
145°	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8	168.8	160.2	151.8
147.5°	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1	167.1	159.5	152.1
150°	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0	165.7	158.7	152.1
152.5°	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7	164.0	157.8	151.9
155°	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2	161.3	156.2	151.2
157.5°	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8	158.8	154.4	150.5
160°	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5	156.8	153.3	149.9
162.5°	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9	154.9	151.9	149.1
165°	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4	152.1	149.9	148.1
167.5°	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1	149.4	147.8	146.5
170°	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3	147.8	146.7	145.8
172.5°	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2	146.2	145.3	144.9
175°	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0	144.1	143.8	143.8
177.5°	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4	143.2	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	4.2	4.1	4.2	4.1	3.8	4.5	4.8	4.9	4.6	4.5	4.2
90°	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3	0.6	1.1	1.7
92.5°	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5	4.2	6.7	10.3
95°	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5	9.8	12.1	15.2
97.5°	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8	16.1	17.8	21.0
100°	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1	20.7	21.9	25.0
102.5°	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0	25.4	26.3	29.7
105°	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5	32.5	34.0	36.9
107.5°	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9	40.5	41.9	44.3
110°	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2	45.8	47.0	49.6





TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5	51.1	52.0	54.6
115°	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2	58.8	59.7	62.2
117.5°	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1	66.0	66.9	69.5
120°	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7	70.6	71.7	74.4
122.5°	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6	75.2	76.1	78.8
125°	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7	81.3	82.7	85.3
127.5°	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4	86.3	88.1	91.5
130°	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5	89.4	91.6	95.4
132.5°	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7	91.9	94.7	98.8
135°	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5	95.6	99.1	103.7
137.5°	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2	100.1	103.3	107.9
140°	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0	102.9	106.3	111.0
142.5°	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3	105.8	109.1	113.7
145°	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1	110.6	113.5	117.6
147.5°	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1	115.4	118.0	121.7
150°	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1	118.7	120.7	124.5
152.5°	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4	121.7	123.5	126.8
155°	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6	125.6	127.3	130.2
157.5°	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5	129.4	130.8	133.2
160°	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0	131.7	132.8	134.9
162.5°	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0	133.8	134.9	136.7
165°	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1	136.6	137.5	138.8
167.5°	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3	138.9	139.5	140.2
170°	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6	140.3	140.6	141.2
172.5°	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5	141.0	141.3	141.9
175°	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6	142.0	142.4	142.6
177.5°	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2	142.7	142.7	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	4.2	4.3	4.2	4.6	4.2	4.6	4.6	4.5	4.6	4.6	4.6
90°	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2	5.5	5.8	6.4
92.5°	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0	37.0	27.9	23.6
95°	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2	163.4	127.9	103.7
97.5°	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5	277.9	243.3	209.6
100°	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4	340.3	310.6	280.6
102.5°	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8	378.5	364.4	344.1
105°	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8	400.2	412.9	409.8
107.5°	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2	380.9	413.4	428.5
110°	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3	359.1	399.7	424.1



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4	337.4	378.5	407.3
115°	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6	306.3	345.8	377.2
117.5°	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3	284.8	318.8	347.6
120°	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0	272.6	304.3	329.6
122.5°	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8	263.8	292.0	315.8
125°	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7	252.1	277.2	297.9
127.5°	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5	240.9	264.3	283.7
130°	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7	233.1	255.6	274.3
132.5°	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9	225.8	246.1	264.2
135°	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5	214.3	232.8	249.2
137.5°	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2	204.2	219.6	233.5
140°	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7	198.2	211.5	223.6
142.5°	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7	193.1	204.6	215.1
145°	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8	186.7	195.7	203.4
147.5°	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1	181.3	188.3	194.1
150°	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0	178.4	183.8	189.0
152.5°	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7	175.4	180.3	184.4
155°	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2	170.9	174.9	178.1
157.5°	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8	166.6	169.7	172.2
160°	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5	163.4	166.2	168.3
162.5°	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9	160.6	163.1	164.9
165°	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4	156.5	158.2	159.6
167.5°	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1	152.5	153.8	154.8
170°	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3	150.1	151.0	151.6
172.5°	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2	148.1	148.7	149.0
175°	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0	145.0	145.5	145.5
177.5°	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4	143.6	143.6	143.6
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	4.7	4.6	4.6	4.6	4.6	4.6	4.7	4.6	4.6	4.6	4.5
90°	6.4	6.4	6.6	6.6	6.6	6.4	6.4	6.4	5.8	5.5	5.2
92.5°	20.0	19.2	18.8	18.3	18.8	19.2	20.0	23.6	27.9	37.0	51.0
95°	83.2	74.6	72.3	67.8	72.3	74.6	83.2	103.7	127.9	163.4	207.2
97.5°	191.8	175.7	167.4	163.6	167.4	175.7	191.8	209.6	243.3	277.9	308.5
100°	260.7	240.0	229.3	224.8	229.3	240.0	260.7	280.6	310.6	340.3	354.4
102.5°	322.8	308.0	296.4	293.0	296.4	308.0	322.8	344.1	364.4	378.5	369.8
105°	400.5	391.0	385.2	381.8	385.2	391.0	400.5	409.8	412.9	400.2	360.8
107.5°	433.2	433.2	431.2	428.9	431.2	433.2	433.2	428.5	413.4	380.9	328.2
110°	437.1	442.5	444.6	444.6	444.6	442.5	437.1	424.1	399.7	359.1	304.3



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	426.2	435.7	440.7	442.8	440.7	435.7	426.2	407.3	378.5	337.4	285.4
115°	399.7	413.4	421.5	425.3	421.5	413.4	399.7	377.2	345.8	306.3	261.6
117.5°	370.1	384.4	392.4	394.7	392.4	384.4	370.1	347.6	318.8	284.8	246.3
120°	351.0	364.8	372.6	374.9	372.6	364.8	351.0	329.6	304.3	272.6	238.0
122.5°	334.8	347.5	355.3	357.3	355.3	347.5	334.8	315.8	292.0	263.8	231.8
125°	314.1	325.9	332.2	335.1	332.2	325.9	314.1	297.9	277.2	252.1	222.7
127.5°	298.4	308.8	314.8	316.1	314.8	308.8	298.4	283.7	264.3	240.9	213.5
130°	288.7	298.2	304.0	305.7	304.0	298.2	288.7	274.3	255.6	233.1	207.7
132.5°	278.6	288.0	293.3	295.3	293.3	288.0	278.6	264.2	246.1	225.8	201.9
135°	262.0	271.4	276.6	278.3	276.6	271.4	262.0	249.2	232.8	214.3	194.5
137.5°	244.8	253.5	258.3	260.2	258.3	253.5	244.8	233.5	219.6	204.2	188.2
140°	234.2	241.7	246.1	247.5	246.1	241.7	234.2	223.6	211.5	198.2	184.7
142.5°	224.1	230.5	234.6	235.8	234.6	230.5	224.1	215.1	204.6	193.1	181.7
145°	210.3	215.2	218.4	219.6	218.4	215.2	210.3	203.4	195.7	186.7	177.8
147.5°	199.6	203.5	205.3	205.9	205.3	203.5	199.6	194.1	188.3	181.3	174.1
150°	193.3	196.8	198.0	198.2	198.0	196.8	193.3	189.0	183.8	178.4	172.0
152.5°	188.0	190.8	191.9	192.2	191.9	190.8	188.0	184.4	180.3	175.4	169.7
155°	180.9	183.0	183.8	184.1	183.8	183.0	180.9	178.1	174.9	170.9	166.2
157.5°	174.5	176.1	176.9	176.8	176.9	176.1	174.5	172.2	169.7	166.6	162.8
160°	170.3	171.7	172.3	172.0	172.3	171.7	170.3	168.3	166.2	163.4	160.5
162.5°	166.4	167.5	167.7	167.6	167.7	167.5	166.4	164.9	163.1	160.6	157.9
165°	160.8	161.3	161.3	161.3	161.3	161.3	160.8	159.6	158.2	156.5	154.4
167.5°	155.4	155.9	155.6	155.6	155.6	155.9	155.4	154.8	153.8	152.5	151.1
170°	152.1	152.5	152.5	152.1	152.5	152.5	152.1	151.6	151.0	150.1	149.3
172.5°	149.1	149.7	149.2	148.9	149.2	149.7	149.1	149.0	148.7	148.1	147.2
175°	145.5	145.8	145.2	145.0	145.2	145.8	145.5	145.5	145.5	145.0	145.0
177.5°	143.4	143.6	142.9	142.9	142.9	143.6	143.4	143.6	143.6	143.6	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	4.6	4.6	4.2	4.6	4.2	4.3	4.2	4.2	4.5	4.6	4.9
90°	4.9	4.6	4.0	3.8	3.2	2.9	2.3	1.7	1.1	0.6	0.3
92.5°	75.2	92.9	94.4	65.7	39.4	23.6	15.2	10.3	6.7	4.2	3.5
95°	249.8	255.3	208.3	128.8	65.4	34.6	21.6	15.2	12.1	9.8	9.5
97.5°	316.1	272.6	186.1	102.8	56.3	36.0	26.7	21.0	17.8	16.1	15.8
100°	332.2	260.2	166.0	93.4	55.9	39.2	30.6	25.0	21.9	20.7	20.1
102.5°	322.5	238.3	150.7	89.4	58.0	43.1	34.7	29.7	26.3	25.4	25.0
105°	291.6	208.9	136.0	87.9	62.2	49.6	41.5	36.9	34.0	32.5	32.5
107.5°	260.0	188.7	129.8	90.5	68.6	56.3	49.1	44.3	41.9	40.5	39.9
110°	242.1	179.2	127.9	93.1	73.2	61.4	53.9	49.6	47.0	45.8	45.2



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	228.7	173.7	127.9	96.3	77.5	66.2	58.9	54.6	52.0	51.1	50.5
115°	214.1	167.7	128.8	101.1	84.5	73.8	66.5	62.2	59.7	58.8	58.2
117.5°	205.4	164.8	130.7	106.6	91.5	81.4	74.4	69.5	66.9	66.0	65.1
120°	200.6	163.4	132.6	110.4	96.5	86.4	79.2	74.4	71.7	70.6	69.7
122.5°	196.4	162.2	134.1	114.5	101.3	91.3	84.1	78.8	76.1	75.2	74.6
125°	190.8	160.8	136.9	120.2	107.8	98.2	90.7	85.3	82.7	81.3	80.7
127.5°	185.6	160.1	139.9	125.3	113.9	104.8	97.3	91.5	88.1	86.3	85.4
130°	182.1	159.6	141.8	128.8	117.8	108.9	101.4	95.4	91.6	89.4	88.5
132.5°	179.4	159.6	143.8	131.8	121.6	112.6	105.1	98.8	94.7	91.9	90.7
135°	176.0	159.6	146.7	136.0	126.5	117.6	109.8	103.7	99.1	95.6	94.5
137.5°	173.1	160.0	149.3	139.1	130.0	121.9	113.9	107.9	103.3	100.1	99.2
140°	171.7	160.2	150.4	141.2	132.6	124.2	116.4	111.0	106.3	102.9	102.0
142.5°	170.6	160.5	151.1	142.4	134.1	126.3	119.0	113.7	109.1	105.8	105.3
145°	168.8	160.2	151.8	144.1	136.9	129.4	122.8	117.6	113.5	110.6	110.1
147.5°	167.1	159.5	152.1	145.1	138.6	132.0	126.2	121.7	118.0	115.4	115.1
150°	165.7	158.7	152.1	145.8	139.7	133.4	128.5	124.5	120.7	118.7	118.1
152.5°	164.0	157.8	151.9	146.3	140.9	135.0	130.6	126.8	123.5	121.7	121.4
155°	161.3	156.2	151.2	146.7	142.0	137.1	133.1	130.2	127.3	125.6	125.6
157.5°	158.8	154.4	150.5	146.9	143.0	138.8	135.7	133.2	130.8	129.4	129.5
160°	156.8	153.3	149.9	146.9	143.5	139.7	137.1	134.9	132.8	131.7	132.0
162.5°	154.9	151.9	149.1	146.8	144.0	140.6	138.5	136.7	134.9	133.8	134.0
165°	152.1	149.9	148.1	146.3	144.1	141.8	140.1	138.8	137.5	136.6	137.1
167.5°	149.4	147.8	146.5	145.7	144.1	142.2	141.0	140.2	139.5	138.9	139.3
170°	147.8	146.7	145.8	145.2	144.1	142.6	141.8	141.2	140.6	140.3	140.6
172.5°	146.2	145.3	144.9	144.8	143.8	142.6	142.2	141.9	141.3	141.0	141.5
175°	144.1	143.8	143.8	144.1	143.5	142.6	142.6	142.6	142.4	142.0	142.6
177.5°	143.2	142.9	142.9	143.4	143.2	142.7	142.7	142.9	142.7	142.7	143.2
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	4.8	4.5	3.8	4.1	4.2	4.1	4.2	4.2	4.1	4.2	4.2
90°	0.6	1.1	1.7	2.3	2.9	3.2	3.8	4.0	4.6	4.9	5.2
92.5°	4.2	6.7	10.3	15.2	23.6	39.4	65.7	94.4	92.9	75.2	51.0
95°	9.8	12.1	15.2	21.6	34.6	65.4	128.8	208.3	255.3	249.8	207.2
97.5°	16.1	17.8	21.0	26.7	36.0	56.3	102.8	186.1	272.6	316.1	308.5
100°	20.7	21.9	25.0	30.6	39.2	55.9	93.4	166.0	260.2	332.2	354.4
102.5°	25.4	26.3	29.7	34.7	43.1	58.0	89.4	150.7	238.3	322.5	369.8
105°	32.5	34.0	36.9	41.5	49.6	62.2	87.9	136.0	208.9	291.6	360.8
107.5°	40.5	41.9	44.3	49.1	56.3	68.6	90.5	129.8	188.7	260.0	328.2
110°	45.8	47.0	49.6	53.9	61.4	73.2	93.1	127.9	179.2	242.1	304.3





TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	51.1	52.0	54.6	58.9	66.2	77.5	96.3	127.9	173.7	228.7	285.4
115°	58.8	59.7	62.2	66.5	73.8	84.5	101.1	128.8	167.7	214.1	261.6
117.5°	66.0	66.9	69.5	74.4	81.4	91.5	106.6	130.7	164.8	205.4	246.3
120°	70.6	71.7	74.4	79.2	86.4	96.5	110.4	132.6	163.4	200.6	238.0
122.5°	75.2	76.1	78.8	84.1	91.3	101.3	114.5	134.1	162.2	196.4	231.8
125°	81.3	82.7	85.3	90.7	98.2	107.8	120.2	136.9	160.8	190.8	222.7
127.5°	86.3	88.1	91.5	97.3	104.8	113.9	125.3	139.9	160.1	185.6	213.5
130°	89.4	91.6	95.4	101.4	108.9	117.8	128.8	141.8	159.6	182.1	207.7
132.5°	91.9	94.7	98.8	105.1	112.6	121.6	131.8	143.8	159.6	179.4	201.9
135°	95.6	99.1	103.7	109.8	117.6	126.5	136.0	146.7	159.6	176.0	194.5
137.5°	100.1	103.3	107.9	113.9	121.9	130.0	139.1	149.3	160.0	173.1	188.2
140°	102.9	106.3	111.0	116.4	124.2	132.6	141.2	150.4	160.2	171.7	184.7
142.5°	105.8	109.1	113.7	119.0	126.3	134.1	142.4	151.1	160.5	170.6	181.7
145°	110.6	113.5	117.6	122.8	129.4	136.9	144.1	151.8	160.2	168.8	177.8
147.5°	115.4	118.0	121.7	126.2	132.0	138.6	145.1	152.1	159.5	167.1	174.1
150°	118.7	120.7	124.5	128.5	133.4	139.7	145.8	152.1	158.7	165.7	172.0
152.5°	121.7	123.5	126.8	130.6	135.0	140.9	146.3	151.9	157.8	164.0	169.7
155°	125.6	127.3	130.2	133.1	137.1	142.0	146.7	151.2	156.2	161.3	166.2
157.5°	129.4	130.8	133.2	135.7	138.8	143.0	146.9	150.5	154.4	158.8	162.8
160°	131.7	132.8	134.9	137.1	139.7	143.5	146.9	149.9	153.3	156.8	160.5
162.5°	133.8	134.9	136.7	138.5	140.6	144.0	146.8	149.1	151.9	154.9	157.9
165°	136.6	137.5	138.8	140.1	141.8	144.1	146.3	148.1	149.9	152.1	154.4
167.5°	138.9	139.5	140.2	141.0	142.2	144.1	145.7	146.5	147.8	149.4	151.1
170°	140.3	140.6	141.2	141.8	142.6	144.1	145.2	145.8	146.7	147.8	149.3
172.5°	141.0	141.3	141.9	142.2	142.6	143.8	144.8	144.9	145.3	146.2	147.2
175°	142.0	142.4	142.6	142.6	142.6	143.5	144.1	143.8	143.8	144.1	145.0
177.5°	142.7	142.7	142.9	142.7	142.7	143.2	143.4	142.9	142.9	143.2	143.4
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9	142.9



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	4.4	4.6	4.4	4.3	4.3	4.5	4.6
90°	5.5	5.8	6.4	6.4	6.4	6.6	6.6
92.5°	37.0	27.9	23.6	20.0	19.2	18.8	18.3
95°	163.4	127.9	103.7	83.2	74.6	72.3	67.8
97.5°	277.9	243.3	209.6	191.8	175.7	167.4	163.6
100°	340.3	310.6	280.6	260.7	240.0	229.3	224.8
102.5°	378.5	364.4	344.1	322.8	308.0	296.4	293.0
105°	400.2	412.9	409.8	400.5	391.0	385.2	381.8
107.5°	380.9	413.4	428.5	433.2	433.2	431.2	428.9
110°	359.1	399.7	424.1	437.1	442.5	444.6	444.6



TEST NUMBER: P333492-930

CATALOG NUMBER: S125RDIP-S375D365U930-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	337.4	378.5	407.3	426.2	435.7	440.7	442.8
115°	306.3	345.8	377.2	399.7	413.4	421.5	425.3
117.5°	284.8	318.8	347.6	370.1	384.4	392.4	394.7
120°	272.6	304.3	329.6	351.0	364.8	372.6	374.9
122.5°	263.8	292.0	315.8	334.8	347.5	355.3	357.3
125°	252.1	277.2	297.9	314.1	325.9	332.2	335.1
127.5°	240.9	264.3	283.7	298.4	308.8	314.8	316.1
130°	233.1	255.6	274.3	288.7	298.2	304.0	305.7
132.5°	225.8	246.1	264.2	278.6	288.0	293.3	295.3
135°	214.3	232.8	249.2	262.0	271.4	276.6	278.3
137.5°	204.2	219.6	233.5	244.8	253.5	258.3	260.2
140°	198.2	211.5	223.6	234.2	241.7	246.1	247.5
142.5°	193.1	204.6	215.1	224.1	230.5	234.6	235.8
145°	186.7	195.7	203.4	210.3	215.2	218.4	219.6
147.5°	181.3	188.3	194.1	199.6	203.5	205.3	205.9
150°	178.4	183.8	189.0	193.3	196.8	198.0	198.2
152.5°	175.4	180.3	184.4	188.0	190.8	191.9	192.2
155°	170.9	174.9	178.1	180.9	183.0	183.8	184.1
157.5°	166.6	169.7	172.2	174.5	176.1	176.9	176.8
160°	163.4	166.2	168.3	170.3	171.7	172.3	172.0
162.5°	160.6	163.1	164.9	166.4	167.5	167.7	167.6
165°	156.5	158.2	159.6	160.8	161.3	161.3	161.3
167.5°	152.5	153.8	154.8	155.4	155.9	155.6	155.6
170°	150.1	151.0	151.6	152.1	152.5	152.5	152.1
172.5°	148.1	148.7	149.0	149.1	149.7	149.2	148.9
175°	145.0	145.5	145.5	145.5	145.8	145.2	145.0
177.5°	143.6	143.6	143.6	143.4	143.6	142.9	142.9
180°	142.9	142.9	142.9	142.9	142.9	142.9	142.9

(END OF REPORT)