

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333498-930

Luminaire Tested: **S125RDIP-S375D590U930-4F0-1E-UDD-A4**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333498-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-19,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIP-S375D590U930-4F0-1E-UDD-A4
Description: DEFINE 5 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 590 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2920.1 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	50	43	37	56	46	39	34	39	34	30	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.5
10°-20°	129.0	4.4
20°-30°	204.5	7.0
30°-40°	246.6	8.4
40°-50°	220.2	7.5
50°-60°	168.9	5.8
60°-70°	109.7	3.8
70°-80°	53.3	1.8
80°-90°	14.0	0.5
90°-100°	167.2	5.7
100°-110°	359.4	12.3
110°-120°	337.3	11.6
120°-130°	273.4	9.4
130°-140°	219.4	7.5
140°-150°	165.6	5.7
150°-160°	116.5	4.0
160°-170°	68.7	2.4
170°-180°	22.3	0.8
0°-30°	377.5	12.9
0°-40°	624.0	21.4
0°-60°	1013.1	34.7
0°-90°	1190.2	40.8
90°-120°	864.0	29.6
90°-150°	1522.3	52.1
90°-180°	1730.0	59.2
0°-180°	2920.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	10
90°	11	0	11	0	11	8
95°	109	15	109	15	109	155
105°	616	53	616	53	616	613
115°	686	94	686	94	686	671
125°	541	130	541	130	541	489
135°	449	152	449	152	449	348
145°	354	178	354	178	354	225
155°	297	203	297	203	297	139
165°	260	221	260	221	260	74
175°	234	230	234	230	234	23
180°	231	231	231	231	231	



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	5.5	5.3	5.1	5.1	5.2	5.3	5.1	4.8	4.7	4.6	4.6
90°	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4	7.9	7.4	6.5
92.5°	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4	121.4	149.9	152.4
95°	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4	403.2	412.1	336.2
97.5°	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0	510.2	440.0	300.3
100°	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0	536.2	420.0	267.9
102.5°	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0	520.6	384.6	243.3
105°	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3	470.7	337.2	219.5
107.5°	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8	419.7	304.5	209.5
110°	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1	390.7	289.3	206.5



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6	369.1	280.4	206.5
115°	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2	345.5	270.7	207.9
117.5°	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5	331.5	266.0	210.9
120°	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2	323.7	263.7	213.9
122.5°	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1	317.0	261.9	216.5
125°	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5	307.9	259.5	220.9
127.5°	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6	299.5	258.4	225.8
130°	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3	293.9	257.6	228.9
132.5°	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0	289.4	257.6	232.2
135°	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9	284.1	257.6	236.7
137.5°	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7	279.4	258.2	240.9
140°	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1	277.2	258.6	242.8
142.5°	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3	275.3	258.9	243.9
145°	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0	272.6	258.6	245.1
147.5°	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0	269.6	257.4	245.6
150°	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6	267.4	256.2	245.6
152.5°	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9	264.8	254.8	245.2
155°	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3	260.4	252.1	244.2
157.5°	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8	256.3	249.2	243.0
160°	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0	253.0	247.4	241.8
162.5°	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9	250.1	245.2	240.8
165°	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2	245.6	241.8	239.0
167.5°	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9	241.2	238.6	236.4
170°	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9	238.6	236.7	235.3
172.5°	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6	235.9	234.5	233.8
175°	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9	232.5	232.0	232.0
177.5°	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4	231.1	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	4.6	4.5	4.6	4.3	4.0	4.6	4.9	4.9	4.7	4.6	4.5
90°	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5	0.9	1.9	2.8
92.5°	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7	6.8	10.8	16.6
95°	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3	15.8	19.6	24.6
97.5°	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5	26.0	28.6	33.8
100°	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5	33.5	35.4	40.4
102.5°	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4	40.9	42.4	47.9
105°	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6	52.6	54.9	59.5
107.5°	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5	65.4	67.6	71.4
110°	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1	73.9	75.8	80.0



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6	82.5	84.0	88.2
115°	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9	94.9	96.3	100.4
117.5°	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1	106.5	108.0	112.2
120°	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5	114.0	115.8	120.0
122.5°	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3	121.4	122.9	127.0
125°	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2	131.2	133.5	137.6
127.5°	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9	139.3	142.4	147.7
130°	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8	144.1	147.9	153.9
132.5°	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5	148.3	152.7	159.6
135°	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5	154.4	160.0	167.5
137.5°	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2	161.6	166.8	174.2
140°	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6	166.0	171.6	179.0
142.5°	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8	170.9	176.1	183.5
145°	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7	178.6	183.2	189.7
147.5°	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8	186.4	190.4	196.4
150°	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7	191.6	194.9	200.9
152.5°	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9	196.4	199.3	204.6
155°	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8	202.8	205.5	210.2
157.5°	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9	208.8	211.1	215.1
160°	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0	212.5	214.4	217.7
162.5°	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4	215.9	217.8	220.6
165°	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4	220.5	221.8	224.1
167.5°	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7	224.3	225.1	226.4
170°	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0	226.5	227.0	227.9
172.5°	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4	227.6	228.0	229.0
175°	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2	229.3	229.8	230.2
177.5°	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1	230.3	230.3	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	4.5	4.7	4.6	5.1	4.7	5.1	5.2	5.1	5.2	5.3	5.4
90°	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4	8.8	9.3	10.2
92.5°	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4	59.8	45.0	38.2
95°	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4	263.7	206.5	167.5
97.5°	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0	448.4	392.7	338.3
100°	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0	549.3	501.3	453.0
102.5°	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0	611.0	588.0	555.3
105°	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3	646.0	666.4	661.3
107.5°	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8	614.8	667.4	691.6
110°	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1	579.5	645.1	684.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6	544.5	610.8	657.5
115°	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2	494.4	558.1	608.8
117.5°	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5	459.7	514.5	561.1
120°	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2	439.9	491.1	532.1
122.5°	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1	425.8	471.4	509.7
125°	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5	406.9	447.4	480.9
127.5°	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6	388.9	426.6	458.0
130°	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3	376.3	412.5	442.7
132.5°	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0	364.4	397.3	426.4
135°	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9	346.0	375.8	402.3
137.5°	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7	329.6	354.4	376.9
140°	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1	320.0	341.4	360.9
142.5°	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3	311.8	330.2	347.2
145°	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0	301.3	315.8	328.3
147.5°	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0	292.7	303.8	313.2
150°	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6	287.9	296.7	305.1
152.5°	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9	283.1	291.1	297.7
155°	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3	275.8	282.3	287.4
157.5°	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8	268.9	273.9	277.9
160°	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0	263.7	268.3	271.6
162.5°	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9	259.3	263.1	266.0
165°	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2	252.5	255.4	257.6
167.5°	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9	246.1	248.2	249.8
170°	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9	242.3	243.7	244.6
172.5°	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6	239.0	239.9	240.5
175°	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9	233.9	234.9	234.9
177.5°	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4	231.8	231.8	231.8
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	5.5	5.4	5.5	5.5	5.5	5.4	5.5	5.4	5.3	5.2	5.1
90°	10.2	10.2	10.7	10.7	10.7	10.2	10.2	10.2	9.3	8.8	8.4
92.5°	32.2	31.1	30.4	29.7	30.4	31.1	32.2	38.2	45.0	59.8	82.4
95°	134.4	120.4	116.8	109.3	116.8	120.4	134.4	167.5	206.5	263.7	334.4
97.5°	309.7	283.6	270.1	264.2	270.1	283.6	309.7	338.3	392.7	448.4	498.0
100°	420.9	387.4	370.2	362.7	370.2	387.4	420.9	453.0	501.3	549.3	572.0
102.5°	521.0	497.2	478.5	472.9	478.5	497.2	521.0	555.3	588.0	611.0	597.0
105°	646.5	631.1	621.8	616.2	621.8	631.1	646.5	661.3	666.4	646.0	582.3
107.5°	699.2	699.1	696.0	692.3	696.0	699.1	699.2	691.6	667.4	614.8	529.8
110°	705.5	714.4	717.6	717.6	717.6	714.4	705.5	684.6	645.1	579.5	491.1



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	688.0	703.2	711.3	714.6	711.3	703.2	688.0	657.5	610.8	544.5	460.6
115°	645.1	667.4	680.4	686.5	680.4	667.4	645.1	608.8	558.1	494.4	422.2
117.5°	597.4	620.4	633.3	637.1	633.3	620.4	597.4	561.1	514.5	459.7	397.5
120°	566.5	588.8	601.4	605.0	601.4	588.8	566.5	532.1	491.1	439.9	384.2
122.5°	540.4	560.8	573.4	576.7	573.4	560.8	540.4	509.7	471.4	425.8	374.1
125°	507.0	526.0	536.2	540.9	536.2	526.0	507.0	480.9	447.4	406.9	359.5
127.5°	481.6	498.5	508.1	510.2	508.1	498.5	481.6	458.0	426.6	388.9	344.6
130°	466.0	481.4	490.6	493.4	490.6	481.4	466.0	442.7	412.5	376.3	335.3
132.5°	449.6	465.0	473.5	476.7	473.5	465.0	449.6	426.4	397.3	364.4	326.0
135°	422.7	438.1	446.5	449.2	446.5	438.1	422.7	402.3	375.8	346.0	313.9
137.5°	395.2	409.2	416.9	420.0	416.9	409.2	395.2	376.9	354.4	329.6	303.7
140°	378.1	390.2	397.1	399.5	397.1	390.2	378.1	360.9	341.4	320.0	298.1
142.5°	361.7	371.9	378.5	380.5	378.5	371.9	361.7	347.2	330.2	311.8	293.3
145°	339.5	347.4	352.5	354.4	352.5	347.4	339.5	328.3	315.8	301.3	287.0
147.5°	322.1	328.4	331.4	332.2	331.4	328.4	322.1	313.2	303.8	292.7	281.0
150°	312.1	317.6	319.5	320.0	319.5	317.6	312.1	305.1	296.7	287.9	277.6
152.5°	303.5	307.9	309.8	310.3	309.8	307.9	303.5	297.7	291.1	283.1	273.9
155°	292.0	295.3	296.7	297.2	296.7	295.3	292.0	287.4	282.3	275.8	268.3
157.5°	281.5	284.2	285.5	285.4	285.5	284.2	281.5	277.9	273.9	268.9	262.8
160°	274.8	277.2	278.1	277.6	278.1	277.2	274.8	271.6	268.3	263.7	259.0
162.5°	268.6	270.5	270.7	270.6	270.7	270.5	268.6	266.0	263.1	259.3	254.9
165°	259.5	260.4	260.4	260.4	260.4	260.4	259.5	257.6	255.4	252.5	249.2
167.5°	250.8	251.6	251.2	251.1	251.2	251.6	250.8	249.8	248.2	246.1	243.9
170°	245.6	246.1	246.1	245.6	246.1	246.1	245.6	244.6	243.7	242.3	240.9
172.5°	240.8	241.6	240.8	240.4	240.8	241.6	240.8	240.5	239.9	239.0	237.6
175°	234.9	235.3	234.4	233.9	234.4	235.3	234.9	234.9	234.9	233.9	233.9
177.5°	231.4	231.8	230.6	230.6	230.6	231.8	231.4	231.8	231.8	231.8	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	5.2	5.1	4.7	5.1	4.6	4.7	4.5	4.5	4.6	4.7	4.9
90°	7.9	7.4	6.5	6.0	5.1	4.6	3.8	2.8	1.9	0.9	0.5
92.5°	121.4	149.9	152.4	106.2	63.5	38.2	24.5	16.6	10.8	6.8	5.7
95°	403.2	412.1	336.2	207.9	105.6	55.8	34.9	24.6	19.6	15.8	15.3
97.5°	510.2	440.0	300.3	165.9	91.0	58.0	43.0	33.8	28.6	26.0	25.5
100°	536.2	420.0	267.9	150.7	90.3	63.3	49.3	40.4	35.4	33.5	32.5
102.5°	520.6	384.6	243.3	144.4	93.6	69.5	56.0	47.9	42.4	40.9	40.4
105°	470.7	337.2	219.5	141.9	100.4	80.0	66.9	59.5	54.9	52.6	52.6
107.5°	419.7	304.5	209.5	146.1	110.7	90.9	79.2	71.4	67.6	65.4	64.5
110°	390.7	289.3	206.5	150.2	118.1	99.1	87.0	80.0	75.8	73.9	73.1



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	369.1	280.4	206.5	155.4	125.2	106.9	95.1	88.2	84.0	82.5	81.6
115°	345.5	270.7	207.9	163.2	136.2	119.0	107.5	100.4	96.3	94.9	93.9
117.5°	331.5	266.0	210.9	172.2	147.7	131.3	120.1	112.2	108.0	106.5	105.1
120°	323.7	263.7	213.9	178.1	155.8	139.5	127.9	120.0	115.8	114.0	112.5
122.5°	317.0	261.9	216.5	184.8	163.6	147.3	135.7	127.0	122.9	121.4	120.3
125°	307.9	259.5	220.9	194.0	173.9	158.6	146.5	137.6	133.5	131.2	130.2
127.5°	299.5	258.4	225.8	202.3	183.8	169.1	157.0	147.7	142.4	139.3	137.9
130°	293.9	257.6	228.9	207.9	190.2	175.8	163.7	153.9	147.9	144.1	142.8
132.5°	289.4	257.6	232.2	212.7	196.2	181.7	169.7	159.6	152.7	148.3	146.5
135°	284.1	257.6	236.7	219.5	204.2	189.7	177.2	167.5	160.0	154.4	152.5
137.5°	279.4	258.2	240.9	224.5	209.9	196.7	183.8	174.2	166.8	161.6	160.2
140°	277.2	258.6	242.8	227.9	213.9	200.5	187.9	179.0	171.6	166.0	164.6
142.5°	275.3	258.9	243.9	229.8	216.5	203.8	192.0	183.5	176.1	170.9	169.8
145°	272.6	258.6	245.1	232.5	220.9	208.8	198.1	189.7	183.2	178.6	177.7
147.5°	269.6	257.4	245.6	234.2	223.7	213.1	203.7	196.4	190.4	186.4	185.8
150°	267.4	256.2	245.6	235.3	225.6	215.3	207.4	200.9	194.9	191.6	190.7
152.5°	264.8	254.8	245.2	236.0	227.4	217.9	210.8	204.6	199.3	196.4	195.9
155°	260.4	252.1	244.2	236.7	229.3	221.4	214.8	210.2	205.5	202.8	202.8
157.5°	256.3	249.2	243.0	237.2	230.9	224.0	219.2	215.1	211.1	208.8	208.9
160°	253.0	247.4	241.8	237.2	231.6	225.6	221.4	217.7	214.4	212.5	213.0
162.5°	250.1	245.2	240.8	236.8	232.4	227.1	223.6	220.6	217.8	215.9	216.4
165°	245.6	241.8	239.0	236.3	232.5	228.9	226.0	224.1	221.8	220.5	221.4
167.5°	241.2	238.6	236.4	235.1	232.5	229.4	227.7	226.4	225.1	224.3	224.7
170°	238.6	236.7	235.3	234.4	232.5	230.2	228.9	227.9	227.0	226.5	227.0
172.5°	235.9	234.5	233.8	233.7	232.2	230.2	229.6	229.0	228.0	227.6	228.4
175°	232.5	232.0	232.0	232.5	231.6	230.2	230.2	230.2	229.8	229.3	230.2
177.5°	231.1	230.6	230.6	231.4	231.1	230.3	230.3	230.6	230.3	230.3	231.1
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	4.9	4.6	4.0	4.3	4.6	4.5	4.6	4.6	4.6	4.7	4.8
90°	0.9	1.9	2.8	3.8	4.6	5.1	6.0	6.5	7.4	7.9	8.4
92.5°	6.8	10.8	16.6	24.5	38.2	63.5	106.2	152.4	149.9	121.4	82.4
95°	15.8	19.6	24.6	34.9	55.8	105.6	207.9	336.2	412.1	403.2	334.4
97.5°	26.0	28.6	33.8	43.0	58.0	91.0	165.9	300.3	440.0	510.2	498.0
100°	33.5	35.4	40.4	49.3	63.3	90.3	150.7	267.9	420.0	536.2	572.0
102.5°	40.9	42.4	47.9	56.0	69.5	93.6	144.4	243.3	384.6	520.6	597.0
105°	52.6	54.9	59.5	66.9	80.0	100.4	141.9	219.5	337.2	470.7	582.3
107.5°	65.4	67.6	71.4	79.2	90.9	110.7	146.1	209.5	304.5	419.7	529.8
110°	73.9	75.8	80.0	87.0	99.1	118.1	150.2	206.5	289.3	390.7	491.1



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	82.5	84.0	88.2	95.1	106.9	125.2	155.4	206.5	280.4	369.1	460.6
115°	94.9	96.3	100.4	107.5	119.0	136.2	163.2	207.9	270.7	345.5	422.2
117.5°	106.5	108.0	112.2	120.1	131.3	147.7	172.2	210.9	266.0	331.5	397.5
120°	114.0	115.8	120.0	127.9	139.5	155.8	178.1	213.9	263.7	323.7	384.2
122.5°	121.4	122.9	127.0	135.7	147.3	163.6	184.8	216.5	261.9	317.0	374.1
125°	131.2	133.5	137.6	146.5	158.6	173.9	194.0	220.9	259.5	307.9	359.5
127.5°	139.3	142.4	147.7	157.0	169.1	183.8	202.3	225.8	258.4	299.5	344.6
130°	144.1	147.9	153.9	163.7	175.8	190.2	207.9	228.9	257.6	293.9	335.3
132.5°	148.3	152.7	159.6	169.7	181.7	196.2	212.7	232.2	257.6	289.4	326.0
135°	154.4	160.0	167.5	177.2	189.7	204.2	219.5	236.7	257.6	284.1	313.9
137.5°	161.6	166.8	174.2	183.8	196.7	209.9	224.5	240.9	258.2	279.4	303.7
140°	166.0	171.6	179.0	187.9	200.5	213.9	227.9	242.8	258.6	277.2	298.1
142.5°	170.9	176.1	183.5	192.0	203.8	216.5	229.8	243.9	258.9	275.3	293.3
145°	178.6	183.2	189.7	198.1	208.8	220.9	232.5	245.1	258.6	272.6	287.0
147.5°	186.4	190.4	196.4	203.7	213.1	223.7	234.2	245.6	257.4	269.6	281.0
150°	191.6	194.9	200.9	207.4	215.3	225.6	235.3	245.6	256.2	267.4	277.6
152.5°	196.4	199.3	204.6	210.8	217.9	227.4	236.0	245.2	254.8	264.8	273.9
155°	202.8	205.5	210.2	214.8	221.4	229.3	236.7	244.2	252.1	260.4	268.3
157.5°	208.8	211.1	215.1	219.2	224.0	230.9	237.2	243.0	249.2	256.3	262.8
160°	212.5	214.4	217.7	221.4	225.6	231.6	237.2	241.8	247.4	253.0	259.0
162.5°	215.9	217.8	220.6	223.6	227.1	232.4	236.8	240.8	245.2	250.1	254.9
165°	220.5	221.8	224.1	226.0	228.9	232.5	236.3	239.0	241.8	245.6	249.2
167.5°	224.3	225.1	226.4	227.7	229.4	232.5	235.1	236.4	238.6	241.2	243.9
170°	226.5	227.0	227.9	228.9	230.2	232.5	234.4	235.3	236.7	238.6	240.9
172.5°	227.6	228.0	229.0	229.6	230.2	232.2	233.7	233.8	234.5	235.9	237.6
175°	229.3	229.8	230.2	230.2	230.2	231.6	232.5	232.0	232.0	232.5	233.9
177.5°	230.3	230.3	230.6	230.3	230.3	231.1	231.4	230.6	230.6	231.1	231.4
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6	230.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	5.1	5.3	5.2	5.1	5.1	5.3	5.5
90°	8.8	9.3	10.2	10.2	10.2	10.7	10.7
92.5°	59.8	45.0	38.2	32.2	31.1	30.4	29.7
95°	263.7	206.5	167.5	134.4	120.4	116.8	109.3
97.5°	448.4	392.7	338.3	309.7	283.6	270.1	264.2
100°	549.3	501.3	453.0	420.9	387.4	370.2	362.7
102.5°	611.0	588.0	555.3	521.0	497.2	478.5	472.9
105°	646.0	666.4	661.3	646.5	631.1	621.8	616.2
107.5°	614.8	667.4	691.6	699.2	699.1	696.0	692.3
110°	579.5	645.1	684.6	705.5	714.4	717.6	717.6



TEST NUMBER: P333498-930

CATALOG NUMBER: S125RDIP-S375D590U930-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	544.5	610.8	657.5	688.0	703.2	711.3	714.6
115°	494.4	558.1	608.8	645.1	667.4	680.4	686.5
117.5°	459.7	514.5	561.1	597.4	620.4	633.3	637.1
120°	439.9	491.1	532.1	566.5	588.8	601.4	605.0
122.5°	425.8	471.4	509.7	540.4	560.8	573.4	576.7
125°	406.9	447.4	480.9	507.0	526.0	536.2	540.9
127.5°	388.9	426.6	458.0	481.6	498.5	508.1	510.2
130°	376.3	412.5	442.7	466.0	481.4	490.6	493.4
132.5°	364.4	397.3	426.4	449.6	465.0	473.5	476.7
135°	346.0	375.8	402.3	422.7	438.1	446.5	449.2
137.5°	329.6	354.4	376.9	395.2	409.2	416.9	420.0
140°	320.0	341.4	360.9	378.1	390.2	397.1	399.5
142.5°	311.8	330.2	347.2	361.7	371.9	378.5	380.5
145°	301.3	315.8	328.3	339.5	347.4	352.5	354.4
147.5°	292.7	303.8	313.2	322.1	328.4	331.4	332.2
150°	287.9	296.7	305.1	312.1	317.6	319.5	320.0
152.5°	283.1	291.1	297.7	303.5	307.9	309.8	310.3
155°	275.8	282.3	287.4	292.0	295.3	296.7	297.2
157.5°	268.9	273.9	277.9	281.5	284.2	285.5	285.4
160°	263.7	268.3	271.6	274.8	277.2	278.1	277.6
162.5°	259.3	263.1	266.0	268.6	270.5	270.7	270.6
165°	252.5	255.4	257.6	259.5	260.4	260.4	260.4
167.5°	246.1	248.2	249.8	250.8	251.6	251.2	251.1
170°	242.3	243.7	244.6	245.6	246.1	246.1	245.6
172.5°	239.0	239.9	240.5	240.8	241.6	240.8	240.4
175°	233.9	234.9	234.9	234.9	235.3	234.4	233.9
177.5°	231.8	231.8	231.8	231.4	231.8	230.6	230.6
180°	230.6	230.6	230.6	230.6	230.6	230.6	230.6

(END OF REPORT)